

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930824

Luminaire Tested: DFN2DS-SQ2F0-040DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-040DS930-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2771.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 37.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930824

CATALOG NUMBER: DFN2DS-SQ2F0-040DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930824

CATALOG NUMBER: DFN2DS-SQ2F0-040DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2963	2963	2963
5°	2974	2926	2942
10°	2951	2878	2853
15°	2917	2793	2712
20°	2870	2670	2536
25°	2822	2532	2367
30°	2756	2390	2149
35°	2691	2236	1957
40°	2625	2076	1736
45°	2548	1896	1536
50°	2469	1714	1339
55°	2389	1519	1150
60°	2295	1314	955
65°	2189	1104	869
70°	2062	909	799
75°	1906	829	747
80°	1682	740	680
85°	1322	583	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2548 cd/sqm

TEST NUMBER: P930824

CATALOG NUMBER: DFN2DS-SQ2F0-040DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	4.6
10°-20°	346.7	12.5
20°-30°	486.7	17.6
30°-40°	530.5	19.1
40°-50°	487.6	17.6
50°-60°	382.9	13.8
60°-70°	249.3	9.0
70°-80°	128.3	4.6
80°-90°	32.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.6	34.6
0°-40°	1490.1	53.8
0°-60°	2360.7	85.2
0°-90°	2771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2771.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1347	1341	1325	1336	1333	128
15°	1282	1268	1227	1204	1191	361
25°	1163	1124	1044	994	975	535
35°	1002	940	833	756	729	627
45°	819	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	63
90°	0	0	0	0	0	

TEST NUMBER: P930824

CATALOG NUMBER: DFN2DS-SQ2F0-040DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.4	1347.4	1347.4	1347.4	1347.4
2.5°	1353.5	1347.4	1333.9	1346.2	1343.7
5°	1347.4	1341.2	1325.4	1336.4	1332.8
7.5°	1336.4	1329.1	1312.1	1316.8	1310.8
10°	1321.8	1313.2	1288.8	1285.1	1277.9
12.5°	1303.5	1292.5	1259.5	1252.2	1238.8
15°	1281.5	1268.1	1226.7	1203.5	1191.4
17.5°	1255.9	1236.4	1185.1	1158.4	1138.8
20°	1226.7	1202.2	1141.2	1110.8	1083.9
22.5°	1195.0	1166.9	1096.1	1054.7	1036.5
25°	1163.2	1124.2	1043.7	993.8	975.4
27.5°	1125.5	1083.9	995.0	937.7	909.5
30°	1085.3	1038.8	941.2	879.1	846.2
32.5°	1046.2	990.1	890.1	817.0	786.4
35°	1002.4	940.1	832.8	756.0	729.1
37.5°	959.7	892.5	779.1	695.0	664.6
40°	914.5	841.4	723.1	636.5	604.8
42.5°	868.1	790.1	667.0	576.7	546.3
45°	819.4	737.7	609.7	523.1	493.8
47.5°	773.1	686.6	554.9	468.2	441.4
50°	721.8	635.3	501.1	417.0	391.4
52.5°	671.8	580.4	450.0	369.4	346.3
55°	623.1	528.0	396.3	323.1	300.0
57.5°	573.1	475.6	348.7	280.4	261.0
60°	521.8	424.3	298.7	236.6	217.1
62.5°	472.0	374.4	256.0	197.6	187.9
65°	420.7	321.8	212.1	170.7	167.0
67.5°	372.0	273.1	170.7	150.0	146.3
70°	320.7	225.6	141.4	129.3	124.3
72.5°	272.0	181.7	118.3	108.6	106.1
75°	224.3	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.4
80°	132.8	70.7	58.4	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.1	23.1	23.1
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930824

CATALOG NUMBER: DFN2DS-SQ2F0-040DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.01	16.53	15.37	16.84	17.16	10.97	12.49	11.33	12.80	13.12
	3H	16.77	18.14	17.15	18.47	18.83	12.23	13.60	12.61	13.93	14.29
	4H	17.44	18.72	17.84	19.07	19.45	12.74	14.02	13.14	14.37	14.74
	6H	17.93	19.11	18.34	19.48	19.87	13.12	14.30	13.53	14.67	15.06
	8H	18.09	19.22	18.52	19.61	20.01	13.24	14.37	13.67	14.76	15.16
	12H	18.20	19.28	18.63	19.66	20.09	13.32	14.40	13.75	14.78	15.21
4H	2H	15.11	16.39	15.51	16.74	17.12	11.66	12.94	12.06	13.29	13.67
	3H	17.05	18.11	17.46	18.51	18.91	13.11	14.17	13.52	14.57	14.97
	4H	17.80	18.75	18.23	19.17	19.61	13.71	14.66	14.14	15.08	15.52
	6H	18.39	19.22	18.84	19.66	20.12	14.20	15.03	14.65	15.47	15.93
	8H	18.60	19.38	19.06	19.82	20.29	14.36	15.13	14.82	15.58	16.05
	12H	18.76	19.45	19.24	19.93	20.40	14.47	15.17	14.96	15.65	16.12
8H	4H	17.82	18.60	18.28	19.04	19.51	14.06	14.84	14.52	15.28	15.75
	6H	18.46	19.10	18.95	19.59	20.07	14.65	15.29	15.14	15.78	16.26
	8H	18.71	19.28	19.22	19.79	20.28	14.87	15.44	15.38	15.95	16.44
	12H	18.91	19.42	19.42	19.91	20.48	15.05	15.56	15.56	16.05	16.61
12H	4H	17.80	18.50	18.29	18.98	19.45	14.10	14.80	14.59	15.28	15.75
	6H	18.44	19.02	18.95	19.52	20.01	14.71	15.29	15.22	15.80	16.29
	8H	18.72	19.23	19.23	19.72	20.29	14.98	15.49	15.49	15.99	16.55