

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931008

Luminaire Tested: DFN2DS-SQ3F0-090DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-090DS940-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6823.8 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 93.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931008

CATALOG NUMBER: DFN2DS-SQ3F0-090DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931008

CATALOG NUMBER: DFN2DS-SQ3F0-090DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3802	3802	3802
5°	3816	3754	3775
10°	3787	3693	3661
15°	3743	3583	3480
20°	3683	3427	3255
25°	3622	3250	3037
30°	3536	3067	2757
35°	3453	2869	2511
40°	3368	2663	2228
45°	3270	2433	1970
50°	3169	2200	1718
55°	3065	1949	1476
60°	2945	1686	1225
65°	2809	1416	1115
70°	2646	1167	1025
75°	2445	1063	958
80°	2159	950	872
85°	1696	749	749

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3270 cd/sqm

TEST NUMBER: P931008

CATALOG NUMBER: DFN2DS-SQ3F0-090DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.0	4.6
10°-20°	853.7	12.5
20°-30°	1198.5	17.6
30°-40°	1306.5	19.1
40°-50°	1200.8	17.6
50°-60°	943.0	13.8
60°-70°	613.8	9.0
70°-80°	316.0	4.6
80°-90°	80.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2363.1	34.6
0°-40°	3669.6	53.8
0°-60°	5813.4	85.2
0°-90°	6823.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6823.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3318	3318	3318	3318	3318	
5°	3318	3303	3264	3291	3282	315
15°	3156	3123	3021	2964	2934	889
25°	2865	2768	2570	2447	2402	1317
35°	2468	2315	2051	1862	1796	1545
45°	2018	1817	1501	1288	1216	1558
55°	1534	1300	976	796	739	1371
65°	1036	793	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	155
90°	0	0	0	0	0	

TEST NUMBER: P931008

CATALOG NUMBER: DFN2DS-SQ3F0-090DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3318.0	3318.0	3318.0	3318.0	3318.0
2.5°	3333.0	3318.0	3284.8	3315.1	3309.1
5°	3318.0	3303.0	3263.8	3290.9	3281.9
7.5°	3290.9	3273.0	3231.0	3242.8	3227.8
10°	3254.9	3233.9	3174.0	3164.7	3146.9
12.5°	3210.0	3182.9	3101.7	3083.8	3050.6
15°	3155.8	3122.7	3020.8	2963.7	2933.8
17.5°	3092.7	3044.7	2918.4	2852.5	2804.4
20°	3020.8	2960.5	2810.4	2735.6	2669.3
22.5°	2942.7	2873.6	2699.3	2597.3	2552.5
25°	2864.7	2768.4	2570.3	2447.3	2402.1
27.5°	2771.6	2669.3	2450.1	2309.0	2239.9
30°	2672.5	2558.2	2318.0	2165.1	2083.8
32.5°	2576.3	2438.0	2192.1	2011.8	1936.6
35°	2468.3	2315.1	2051.0	1861.8	1795.5
37.5°	2363.2	2197.9	1918.8	1711.4	1636.6
40°	2252.0	2072.0	1780.5	1567.4	1489.4
42.5°	2137.9	1945.9	1642.5	1420.2	1345.3
45°	2017.9	1816.6	1501.4	1288.0	1216.0
47.5°	1903.8	1690.7	1366.4	1152.9	1087.0
50°	1777.7	1564.5	1234.2	1026.8	964.0
52.5°	1654.4	1429.2	1108.0	909.8	852.8
55°	1534.2	1300.1	975.8	795.8	738.8
57.5°	1411.3	1171.1	858.9	690.7	642.6
60°	1285.1	1044.9	735.6	582.7	534.6
62.5°	1162.2	922.0	630.5	486.5	462.6
65°	1036.0	792.6	522.4	420.5	411.3
67.5°	915.9	672.5	420.5	369.2	360.3
70°	789.8	555.6	348.2	318.3	306.1
72.5°	669.6	447.2	291.1	267.2	261.3
75°	552.4	342.2	240.2	219.2	216.3
77.5°	435.5	243.1	189.2	177.2	171.1
80°	327.2	174.3	144.0	132.2	132.2
82.5°	228.1	117.2	99.1	93.0	93.0
85°	129.0	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.1	21.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931008

CATALOG NUMBER: DFN2DS-SQ3F0-090DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.87	17.40	16.24	17.71	18.02	11.84	13.36	12.20	13.67	13.99
	3H	17.64	19.01	18.02	19.33	19.69	13.10	14.47	13.48	14.79	15.16
	4H	18.31	19.59	18.71	19.94	20.31	13.60	14.88	14.00	15.23	15.61
	6H	18.80	19.98	19.21	20.34	20.74	13.98	15.17	14.40	15.53	15.92
	8H	18.96	20.09	19.39	20.48	20.88	14.11	15.23	14.53	15.62	16.02
	12H	19.06	20.14	19.49	20.52	20.95	14.19	15.27	14.62	15.65	16.08
4H	2H	15.98	17.26	16.38	17.61	17.99	12.53	13.81	12.93	14.16	14.54
	3H	17.91	18.97	18.32	19.37	19.78	13.97	15.04	14.38	15.44	15.84
	4H	18.66	19.62	19.09	20.03	20.47	14.57	15.53	15.01	15.95	16.38
	6H	19.25	20.09	19.71	20.53	20.99	15.06	15.89	15.52	16.34	16.80
	8H	19.47	20.24	19.93	20.69	21.16	15.22	16.00	15.69	16.44	16.91
	12H	19.62	20.32	20.10	20.79	21.26	15.34	16.04	15.82	16.51	16.98
8H	4H	18.69	19.46	19.15	19.91	20.37	14.93	15.70	15.39	16.15	16.62
	6H	19.32	19.97	19.82	20.46	20.93	15.51	16.16	16.01	16.65	17.12
	8H	19.57	20.15	20.09	20.66	21.15	15.73	16.31	16.25	16.82	17.31
	12H	19.78	20.29	20.29	20.78	21.34	15.91	16.42	16.42	16.92	17.48
12H	4H	18.67	19.36	19.15	19.84	20.31	14.97	15.66	15.45	16.14	16.61
	6H	19.30	19.88	19.82	20.39	20.88	15.58	16.15	16.09	16.66	17.15
	8H	19.59	20.10	20.10	20.59	21.15	15.85	16.36	16.36	16.85	17.42