

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931069

Luminaire Tested: DFN2DS-SQ4F0-060DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-060DS840-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5945.9 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 57.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931069

CATALOG NUMBER: DFN2DS-SQ4F0-060DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931069

CATALOG NUMBER: DFN2DS-SQ4F0-060DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1640	1640	1640
5°	1646	1622	1632
10°	1636	1606	1614
15°	1616	1585	1584
20°	1587	1554	1552
25°	1559	1515	1515
30°	1522	1480	1467
35°	1488	1438	1417
40°	1445	1395	1369
45°	1403	1354	1320
50°	1356	1310	1263
55°	1309	1259	1212
60°	1255	1199	1154
65°	1198	1138	1086
70°	1125	1065	1014
75°	1023	981	957
80°	908	880	835
85°	741	706	634

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1403 cd/sqm

TEST NUMBER: P931069

CATALOG NUMBER: DFN2DS-SQ4F0-060DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.0	3.7
10°-20°	618.9	10.4
20°-30°	909.5	15.3
30°-40°	1056.3	17.8
40°-50°	1055.0	17.7
50°-60°	919.9	15.5
60°-70°	680.0	11.4
70°-80°	384.8	6.5
80°-90°	101.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1748.3	29.4
0°-40°	2804.6	47.2
0°-60°	4779.6	80.4
0°-90°	5945.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5945.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2328	2303	2321	2317	222
15°	2225	2211	2182	2191	2180	627
25°	2013	1996	1957	1962	1957	926
35°	1737	1715	1679	1665	1654	1085
45°	1414	1398	1364	1339	1330	1091
55°	1070	1056	1029	1002	991	956
65°	721	708	686	665	654	713
75°	377	373	362	348	353	403
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P931069

CATALOG NUMBER: DFN2DS-SQ4F0-060DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2336.9	2336.9	2336.9	2336.9	2336.9
2.5°	2350.5	2339.3	2314.5	2336.9	2332.6
5°	2336.9	2328.1	2303.3	2321.2	2316.9
7.5°	2321.2	2307.9	2283.1	2301.2	2296.7
10°	2296.7	2281.0	2254.0	2271.9	2265.2
12.5°	2262.9	2249.4	2222.5	2233.7	2229.2
15°	2224.6	2211.3	2182.0	2191.1	2179.9
17.5°	2177.5	2164.2	2134.8	2145.9	2134.8
20°	2125.7	2112.4	2080.9	2087.6	2078.8
22.5°	2074.3	2054.0	2024.6	2024.6	2020.1
25°	2013.4	1995.6	1957.4	1961.7	1957.4
27.5°	1945.9	1930.2	1901.1	1894.5	1883.3
30°	1878.8	1860.6	1827.0	1820.3	1811.2
32.5°	1806.7	1793.4	1757.4	1743.7	1734.7
35°	1737.1	1714.7	1678.7	1665.1	1653.9
37.5°	1658.5	1638.1	1602.2	1586.4	1575.2
40°	1577.6	1559.5	1523.5	1503.5	1494.4
42.5°	1498.9	1480.8	1445.0	1422.4	1409.0
45°	1413.6	1397.8	1364.0	1339.4	1330.3
47.5°	1330.3	1314.6	1278.7	1253.9	1240.4
50°	1242.6	1231.4	1200.0	1168.5	1157.3
52.5°	1157.3	1141.5	1112.4	1087.7	1072.0
55°	1069.8	1056.2	1029.2	1002.3	991.1
57.5°	982.1	970.9	941.5	914.6	905.5
60°	894.3	885.5	854.1	829.2	822.5
62.5°	808.9	793.2	770.8	748.3	739.3
65°	721.4	707.9	685.5	665.2	654.0
67.5°	631.5	620.1	600.1	584.4	575.3
70°	548.3	539.3	519.0	503.3	494.5
72.5°	463.0	454.0	442.7	427.0	420.3
75°	377.4	373.2	361.7	348.3	352.9
77.5°	301.1	292.1	287.5	280.9	274.2
80°	224.8	222.4	217.9	211.2	206.7
82.5°	152.9	152.9	150.7	141.6	141.6
85°	92.0	89.9	87.7	80.8	78.7
87.5°	40.5	36.0	31.4	24.8	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931069

CATALOG NUMBER: DFN2DS-SQ4F0-060DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.00	14.61	13.37	14.93	15.24	12.56	14.17	12.92	14.48	14.80
	3H	14.75	16.21	15.13	16.53	16.89	14.26	15.71	14.64	16.04	16.40
	4H	15.40	16.77	15.80	17.11	17.49	14.90	16.27	15.30	16.62	17.00
	6H	15.87	17.13	16.28	17.50	17.89	15.37	16.63	15.78	17.00	17.39
	8H	16.01	17.22	16.43	17.61	18.01	15.51	16.72	15.93	17.11	17.51
	12H	16.10	17.26	16.53	17.64	18.07	15.59	16.75	16.02	17.13	17.56
4H	2H	13.56	14.93	13.96	15.28	15.65	13.21	14.58	13.61	14.93	15.30
	3H	15.54	16.68	15.95	17.08	17.48	15.13	16.28	15.54	16.67	17.07
	4H	16.31	17.35	16.74	17.76	18.20	15.89	16.93	16.32	17.34	17.77
	6H	16.91	17.81	17.36	18.26	18.71	16.48	17.38	16.93	17.82	18.28
	8H	17.10	17.95	17.56	18.39	18.85	16.66	17.51	17.12	17.95	18.42
	12H	17.23	17.99	17.71	18.47	18.94	16.78	17.54	17.26	18.01	18.48
8H	4H	16.59	17.43	17.05	17.88	18.34	16.21	17.06	16.67	17.50	17.97
	6H	17.30	18.00	17.79	18.49	18.97	16.92	17.62	17.41	18.11	18.59
	8H	17.56	18.19	18.07	18.70	19.18	17.17	17.80	17.68	18.31	18.79
	12H	17.76	18.32	18.27	18.81	19.37	17.35	17.90	17.85	18.39	18.96
12H	4H	16.61	17.37	17.09	17.85	18.32	16.25	17.01	16.73	17.48	17.95
	6H	17.35	17.98	17.86	18.48	18.97	16.98	17.61	17.49	18.12	18.60
	8H	17.66	18.22	18.17	18.71	19.27	17.28	17.84	17.79	18.33	18.89