

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930826

Luminaire Tested: DFN2DS-SQ2F0-040DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-040DS935-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2924.0 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 37.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930826

CATALOG NUMBER: DFN2DS-SQ2F0-040DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930826

CATALOG NUMBER: DFN2DS-SQ2F0-040DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3126	3126	3126
5°	3138	3087	3104
10°	3114	3037	3011
15°	3078	2947	2862
20°	3029	2818	2677
25°	2978	2672	2497
30°	2908	2522	2267
35°	2839	2359	2065
40°	2770	2190	1832
45°	2689	2001	1620
50°	2606	1809	1413
55°	2521	1603	1214
60°	2422	1386	1008
65°	2310	1165	917
70°	2176	959	844
75°	2011	874	788
80°	1775	781	718
85°	1395	616	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2689 cd/sqm

TEST NUMBER: P930826

CATALOG NUMBER: DFN2DS-SQ2F0-040DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.2	4.6
10°-20°	365.8	12.5
20°-30°	513.6	17.6
30°-40°	559.8	19.1
40°-50°	514.5	17.6
50°-60°	404.1	13.8
60°-70°	263.0	9.0
70°-80°	135.4	4.6
80°-90°	34.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1012.6	34.6
0°-40°	1572.4	53.8
0°-60°	2491.0	85.2
0°-90°	2924.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2924.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1422	1422	1422	1422	1422	
5°	1422	1415	1398	1410	1406	135
15°	1352	1338	1294	1270	1257	381
25°	1228	1186	1101	1049	1029	565
35°	1058	992	879	798	769	662
45°	865	778	643	552	521	668
55°	658	557	418	341	317	588
65°	444	340	224	180	176	440
75°	237	147	103	94	93	250
85°	55	28	24	24	24	66
90°	0	0	0	0	0	

TEST NUMBER: P930826

CATALOG NUMBER: DFN2DS-SQ2F0-040DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1421.8	1421.8	1421.8	1421.8	1421.8
2.5°	1428.2	1421.8	1407.6	1420.5	1417.9
5°	1421.8	1415.3	1398.5	1410.1	1406.4
7.5°	1410.1	1402.5	1384.5	1389.5	1383.1
10°	1394.7	1385.7	1360.0	1356.0	1348.5
12.5°	1375.5	1363.9	1329.0	1321.4	1307.2
15°	1352.3	1338.1	1294.4	1270.0	1257.1
17.5°	1325.3	1304.6	1250.5	1222.3	1201.7
20°	1294.4	1268.6	1204.3	1172.2	1143.8
22.5°	1260.9	1231.3	1156.6	1112.9	1093.7
25°	1227.5	1186.3	1101.3	1048.7	1029.2
27.5°	1187.7	1143.8	1049.9	989.4	959.8
30°	1145.2	1096.2	993.2	927.7	892.9
32.5°	1104.0	1044.7	939.3	862.1	829.8
35°	1057.7	992.0	878.8	797.7	769.4
37.5°	1012.6	941.8	822.2	733.3	701.2
40°	965.0	887.9	763.0	671.7	638.2
42.5°	916.1	833.8	703.8	608.5	576.5
45°	864.6	778.4	643.4	551.9	521.1
47.5°	815.8	724.5	585.5	494.1	465.8
50°	761.7	670.4	528.8	440.0	413.1
52.5°	708.9	612.4	474.8	389.8	365.4
55°	657.5	557.1	418.1	341.0	316.6
57.5°	604.8	501.8	368.0	295.9	275.4
60°	550.7	447.7	315.2	249.7	229.1
62.5°	498.0	395.1	270.1	208.5	198.2
65°	443.9	339.6	223.9	180.2	176.2
67.5°	392.5	288.2	180.2	158.2	154.4
70°	338.4	238.0	149.2	136.4	131.2
72.5°	287.0	191.7	124.8	114.6	112.0
75°	236.7	146.6	102.9	93.9	92.7
77.5°	186.6	104.1	81.1	75.9	73.3
80°	140.2	74.6	61.7	56.7	56.7
82.5°	97.8	50.2	42.5	39.8	39.8
85°	55.3	28.3	24.4	24.4	24.4
87.5°	20.6	10.2	10.2	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930826

CATALOG NUMBER: DFN2DS-SQ2F0-040DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.19	16.72	15.56	17.03	17.34	11.15	12.68	11.52	12.99	13.30
	3H	16.96	18.33	17.34	18.65	19.02	12.42	13.79	12.80	14.11	14.48
	4H	17.63	18.91	18.03	19.26	19.63	12.92	14.20	13.32	14.55	14.93
	6H	18.12	19.30	18.53	19.66	20.06	13.30	14.49	13.72	14.85	15.24
	8H	18.28	19.41	18.71	19.80	20.20	13.43	14.55	13.85	14.94	15.35
	12H	18.38	19.46	18.81	19.84	20.27	13.51	14.59	13.94	14.97	15.40
4H	2H	15.30	16.58	15.70	16.93	17.31	11.85	13.13	12.25	13.48	13.86
	3H	17.23	18.30	17.64	18.69	19.10	13.29	14.36	13.70	14.76	15.16
	4H	17.98	18.94	18.41	19.35	19.79	13.89	14.85	14.33	15.27	15.70
	6H	18.57	19.41	19.03	19.85	20.31	14.38	15.21	14.84	15.66	16.12
	8H	18.79	19.57	19.25	20.01	20.48	14.54	15.32	15.01	15.77	16.23
	12H	18.94	19.64	19.42	20.11	20.59	14.66	15.36	15.14	15.83	16.30
8H	4H	18.01	18.78	18.47	19.23	19.69	14.25	15.02	14.71	15.47	15.94
	6H	18.64	19.29	19.14	19.78	20.25	14.83	15.48	15.33	15.97	16.45
	8H	18.89	19.47	19.41	19.98	20.47	15.05	15.63	15.57	16.14	16.63
	12H	19.10	19.61	19.61	20.10	20.66	15.23	15.74	15.74	16.24	16.80
12H	4H	17.99	18.68	18.47	19.16	19.63	14.29	14.99	14.77	15.46	15.93
	6H	18.62	19.20	19.14	19.71	20.20	14.90	15.48	15.41	15.98	16.47
	8H	18.91	19.42	19.42	19.91	20.47	15.17	15.68	15.68	16.17	16.74