

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930844

Luminaire Tested: DFN2DS-SQ2F0-050DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-050DS935-RLL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3655.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 47.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930844

CATALOG NUMBER: DFN2DS-SQ2F0-050DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930844

CATALOG NUMBER: DFN2DS-SQ2F0-050DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3908	3908	3908
5°	3923	3859	3880
10°	3893	3796	3763
15°	3848	3683	3577
20°	3786	3522	3346
25°	3723	3340	3122
30°	3635	3152	2834
35°	3549	2949	2582
40°	3462	2738	2290
45°	3361	2501	2025
50°	3257	2262	1766
55°	3150	2003	1517
60°	3027	1733	1259
65°	2887	1456	1146
70°	2720	1199	1054
75°	2514	1093	984
80°	2220	976	897
85°	1743	769	769

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3361 cd/sqm

TEST NUMBER: P930844

CATALOG NUMBER: DFN2DS-SQ2F0-050DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.6	4.6
10°-20°	457.2	12.5
20°-30°	641.9	17.6
30°-40°	699.8	19.1
40°-50°	643.2	17.6
50°-60°	505.1	13.8
60°-70°	328.8	9.0
70°-80°	169.3	4.6
80°-90°	43.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1265.8	34.6
0°-40°	1965.5	53.8
0°-60°	3113.8	85.2
0°-90°	3655.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3655.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1777	1769	1748	1763	1758	169
15°	1690	1673	1618	1588	1571	476
25°	1534	1483	1377	1311	1287	706
35°	1322	1240	1099	997	962	827
45°	1081	973	804	690	651	835
55°	822	696	523	426	396	734
65°	555	425	280	225	220	550
75°	296	183	129	117	116	313
85°	69	35	30	30	30	83
90°	0	0	0	0	0	

TEST NUMBER: P930844

CATALOG NUMBER: DFN2DS-SQ2F0-050DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1777.2	1777.2	1777.2	1777.2	1777.2
2.5°	1785.2	1777.2	1759.5	1775.6	1772.4
5°	1777.2	1769.2	1748.2	1762.7	1757.9
7.5°	1762.7	1753.1	1730.6	1736.9	1728.9
10°	1743.4	1732.1	1700.0	1695.1	1685.5
12.5°	1719.3	1704.9	1661.3	1651.8	1634.0
15°	1690.3	1672.6	1618.0	1587.5	1571.4
17.5°	1656.5	1630.8	1563.2	1527.9	1502.1
20°	1618.0	1585.8	1505.3	1465.3	1429.8
22.5°	1576.2	1539.1	1445.8	1391.2	1367.1
25°	1534.3	1482.8	1376.7	1310.8	1286.6
27.5°	1484.5	1429.8	1312.4	1236.8	1199.8
30°	1431.5	1370.2	1241.6	1159.6	1116.1
32.5°	1380.0	1305.9	1174.2	1077.6	1037.3
35°	1322.1	1240.0	1098.6	997.2	961.7
37.5°	1265.7	1177.3	1027.8	916.7	876.6
40°	1206.2	1109.8	953.7	839.5	797.7
42.5°	1145.2	1042.2	879.8	760.7	720.6
45°	1080.8	973.0	804.2	689.9	651.3
47.5°	1019.7	905.6	731.9	617.6	582.2
50°	952.2	838.0	661.1	550.0	516.3
52.5°	886.1	765.5	593.5	487.4	456.8
55°	821.8	696.3	522.6	426.2	395.7
57.5°	755.9	627.3	460.0	370.0	344.2
60°	688.3	559.7	394.0	312.1	286.3
62.5°	622.5	493.8	337.7	260.6	247.8
65°	554.9	424.6	279.8	225.2	220.3
67.5°	490.5	360.3	225.2	197.8	193.0
70°	423.0	297.6	186.5	170.5	164.0
72.5°	358.7	239.6	156.0	143.2	139.9
75°	295.9	183.3	128.7	117.4	115.8
77.5°	233.2	130.2	101.4	94.9	91.6
80°	175.3	93.3	77.1	70.8	70.8
82.5°	122.2	62.8	53.1	49.8	49.8
85°	69.1	35.3	30.5	30.5	30.5
87.5°	25.8	12.8	12.8	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930844

CATALOG NUMBER: DFN2DS-SQ2F0-050DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.97	17.49	16.34	17.81	18.12	11.93	13.45	12.30	13.77	14.08
	3H	17.74	19.10	18.11	19.43	19.79	13.20	14.56	13.57	14.89	15.25
	4H	18.40	19.68	18.80	20.03	20.41	13.70	14.98	14.10	15.33	15.71
	6H	18.89	20.07	19.30	20.44	20.83	14.08	15.26	14.49	15.63	16.02
	8H	19.06	20.18	19.48	20.57	20.97	14.20	15.33	14.63	15.72	16.12
	12H	19.16	20.24	19.59	20.62	21.05	14.28	15.36	14.71	15.74	16.17
4H	2H	16.07	17.35	16.47	17.70	18.08	12.63	13.91	13.03	14.26	14.63
	3H	18.01	19.07	18.42	19.47	19.87	14.07	15.13	14.48	15.53	15.93
	4H	18.76	19.71	19.19	20.13	20.57	14.67	15.63	15.10	16.04	16.48
	6H	19.35	20.18	19.81	20.62	21.08	15.16	15.99	15.61	16.43	16.89
	8H	19.56	20.34	20.03	20.78	21.25	15.32	16.10	15.78	16.54	17.01
	12H	19.72	20.41	20.20	20.89	21.36	15.44	16.13	15.92	16.61	17.08
8H	4H	18.78	19.56	19.24	20.00	20.47	15.02	15.80	15.49	16.24	16.71
	6H	19.42	20.06	19.92	20.55	21.03	15.61	16.25	16.11	16.74	17.22
	8H	19.67	20.25	20.18	20.76	21.24	15.83	16.41	16.34	16.92	17.40
	12H	19.87	20.38	20.38	20.88	21.44	16.01	16.52	16.52	17.01	17.58
12H	4H	18.77	19.46	19.25	19.94	20.41	15.07	15.76	15.55	16.24	16.71
	6H	19.40	19.98	19.91	20.49	20.97	15.67	16.25	16.19	16.76	17.25
	8H	19.68	20.19	20.19	20.69	21.25	15.95	16.46	16.46	16.95	17.51