

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931504

Luminaire Tested: DFN2DS-TR4F0-070DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-070DS850-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6598.5 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931504

CATALOG NUMBER: DFN2DS-TR4F0-070DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931504

CATALOG NUMBER: DFN2DS-TR4F0-070DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2549	2549	2549
5°	2559	2517	2531
10°	2539	2476	2455
15°	2510	2402	2333
20°	2469	2298	2182
25°	2428	2179	2036
30°	2371	2056	1849
35°	2315	1923	1684
40°	2258	1786	1493
45°	2192	1631	1321
50°	2125	1475	1152
55°	2055	1307	989
60°	1974	1130	821
65°	1883	950	748
70°	1774	782	688
75°	1640	713	642
80°	1448	637	585
85°	1138	502	502

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2192 cd/sqm

TEST NUMBER: P931504

CATALOG NUMBER: DFN2DS-TR4F0-070DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	4.6
10°-20°	825.5	12.5
20°-30°	1158.9	17.6
30°-40°	1263.3	19.1
40°-50°	1161.1	17.6
50°-60°	911.9	13.8
60°-70°	593.5	9.0
70°-80°	305.5	4.6
80°-90°	78.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2285.1	34.6
0°-40°	3548.4	53.8
0°-60°	5621.4	85.2
0°-90°	6598.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6598.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3208	3208	3208	3208	3208	
5°	3208	3194	3156	3182	3174	304
15°	3052	3020	2921	2866	2837	860
25°	2770	2677	2485	2366	2323	1274
35°	2387	2239	1983	1800	1736	1494
45°	1951	1756	1452	1246	1176	1507
55°	1484	1257	944	770	714	1326
65°	1002	766	505	407	398	993
75°	534	331	232	212	209	565
85°	125	64	55	55	55	150
90°	0	0	0	0	0	

TEST NUMBER: P931504

CATALOG NUMBER: DFN2DS-TR4F0-070DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3208.4	3208.4	3208.4	3208.4	3208.4
2.5°	3222.9	3208.4	3176.4	3205.7	3199.8
5°	3208.4	3193.9	3156.1	3182.3	3173.6
7.5°	3182.3	3165.0	3124.4	3135.7	3121.3
10°	3147.5	3127.2	3069.2	3060.3	3043.0
12.5°	3104.0	3077.8	2999.3	2982.0	2949.9
15°	3051.6	3019.6	2921.0	2865.9	2836.9
17.5°	2990.6	2944.2	2822.2	2758.3	2711.8
20°	2921.0	2862.8	2717.7	2645.3	2581.2
22.5°	2845.6	2778.7	2610.1	2511.6	2468.2
25°	2770.1	2677.0	2485.4	2366.5	2322.8
27.5°	2680.1	2581.2	2369.3	2232.9	2166.0
30°	2584.3	2473.7	2241.4	2093.6	2015.1
32.5°	2491.3	2357.6	2119.7	1945.4	1872.7
35°	2386.8	2238.6	1983.3	1800.4	1736.3
37.5°	2285.2	2125.3	1855.5	1654.8	1582.5
40°	2177.6	2003.6	1721.7	1515.7	1440.1
42.5°	2067.4	1881.6	1588.3	1373.3	1301.0
45°	1951.3	1756.5	1451.9	1245.5	1175.9
47.5°	1840.9	1634.9	1321.3	1114.9	1051.1
50°	1719.0	1512.9	1193.4	992.9	932.2
52.5°	1599.7	1381.9	1071.4	879.8	824.7
55°	1483.6	1257.2	943.5	769.5	714.4
57.5°	1364.7	1132.4	830.5	667.8	621.4
60°	1242.7	1010.4	711.3	563.5	516.9
62.5°	1123.7	891.5	609.6	470.4	447.3
65°	1001.8	766.4	505.3	406.7	397.7
67.5°	885.6	650.3	406.7	357.0	348.4
70°	763.7	537.2	336.7	307.7	296.0
72.5°	647.5	432.5	281.6	258.5	252.6
75°	534.2	330.8	232.2	211.9	209.2
77.5°	421.1	235.0	183.0	171.2	165.5
80°	316.4	168.5	139.3	127.9	127.9
82.5°	220.6	113.3	95.8	89.9	89.9
85°	124.8	63.8	55.1	55.1	55.1
87.5°	46.5	23.1	23.1	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931504

CATALOG NUMBER: DFN2DS-TR4F0-070DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.49	16.01	14.85	16.32	16.64	10.45	11.97	10.81	12.28	12.60
	3H	16.25	17.62	16.63	17.94	18.31	11.71	13.08	12.09	13.40	13.77
	4H	16.92	18.20	17.32	18.55	18.92	12.21	13.49	12.61	13.84	14.22
	6H	17.41	18.59	17.82	18.96	19.35	12.59	13.78	13.01	14.14	14.54
	8H	17.57	18.70	18.00	19.09	19.49	12.72	13.84	13.14	14.23	14.64
	12H	17.67	18.75	18.10	19.13	19.56	12.80	13.88	13.23	14.26	14.69
4H	2H	14.59	15.87	14.99	16.22	16.60	11.14	12.42	11.54	12.77	13.15
	3H	16.52	17.59	16.93	17.99	18.39	12.58	13.65	13.00	14.05	14.45
	4H	17.27	18.23	17.70	18.64	19.08	13.18	14.14	13.62	14.56	14.99
	6H	17.86	18.70	18.32	19.14	19.60	13.67	14.50	14.13	14.95	15.41
	8H	18.08	18.86	18.54	19.30	19.77	13.83	14.61	14.30	15.06	15.52
	12H	18.23	18.93	18.71	19.40	19.88	13.95	14.65	14.43	15.12	15.60
8H	4H	17.30	18.07	17.76	18.52	18.98	13.54	14.31	14.00	14.76	15.23
	6H	17.93	18.58	18.43	19.07	19.54	14.12	14.77	14.62	15.26	15.74
	8H	18.18	18.76	18.70	19.27	19.76	14.35	14.92	14.86	15.43	15.92
	12H	18.39	18.90	18.90	19.39	19.95	14.52	15.03	15.03	15.53	16.09
12H	4H	17.28	17.98	17.76	18.45	18.92	13.58	14.28	14.06	14.75	15.22
	6H	17.91	18.49	18.43	19.00	19.49	14.19	14.77	14.70	15.28	15.76
	8H	18.20	18.71	18.71	19.20	19.77	14.46	14.97	14.97	15.46	16.03