

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931546

Luminaire Tested: DFN2DS-TR4F0-090DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-090DS935-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6579.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 93.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931546
CATALOG NUMBER: DFN2DS-TR4F0-090DS935-RLL

Luminous Intensity Polar Plot





TEST NUMBER: P931546

CATALOG NUMBER: DFN2DS-TR4F0-090DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2541	2541	2541
5°	2551	2509	2523
10°	2531	2469	2447
15°	2502	2395	2326
20°	2462	2291	2176
25°	2421	2172	2030
30°	2364	2050	1843
35°	2308	1918	1679
40°	2252	1780	1489
45°	2186	1626	1317
50°	2118	1471	1149
55°	2049	1303	987
60°	1969	1127	819
65°	1878	947	745
70°	1769	780	686
75°	1635	711	640
80°	1443	635	583
85°	1134	501	501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2186 cd/sqm



TEST NUMBER: P931546
 CATALOG NUMBER: DFN2DS-TR4F0-090DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.8	4.6
10°-20°	823.0	12.5
20°-30°	1155.5	17.6
30°-40°	1259.6	19.1
40°-50°	1157.7	17.6
50°-60°	909.2	13.8
60°-70°	591.8	9.0
70°-80°	304.6	4.6
80°-90°	77.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2278.3	34.6
0°-40°	3537.9	53.8
0°-60°	5604.8	85.2
0°-90°	6579.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6579.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3199	3199	3199	3199	3199	
5°	3199	3184	3147	3173	3164	303
15°	3043	3011	2912	2857	2828	857
25°	2762	2669	2478	2360	2316	1270
35°	2380	2232	1977	1795	1731	1489
45°	1946	1751	1448	1242	1172	1502
55°	1479	1253	941	767	712	1322
65°	999	764	504	405	396	990
75°	533	330	232	211	209	563
85°	124	64	55	55	55	149
90°	0	0	0	0	0	



TEST NUMBER: P931546

CATALOG NUMBER: DFN2DS-TR4F0-090DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3198.9	3198.9	3198.9	3198.9	3198.9
2.5°	3213.4	3198.9	3167.0	3196.2	3190.3
5°	3198.9	3184.5	3146.7	3172.8	3164.2
7.5°	3172.8	3155.6	3115.1	3126.4	3112.0
10°	3138.1	3117.8	3060.1	3051.2	3034.0
12.5°	3094.8	3068.7	2990.4	2973.2	2941.2
15°	3042.6	3010.7	2912.4	2857.4	2828.5
17.5°	2981.8	2935.4	2813.7	2750.2	2703.8
20°	2912.4	2854.3	2709.6	2637.4	2573.6
22.5°	2837.1	2770.5	2602.4	2504.1	2460.9
25°	2761.9	2669.1	2478.1	2359.5	2315.9
27.5°	2672.2	2573.6	2362.2	2226.2	2159.5
30°	2576.6	2466.4	2234.8	2087.4	2009.0
32.5°	2483.9	2350.6	2113.4	1939.6	1867.1
35°	2379.8	2232.0	1977.4	1795.0	1731.1
37.5°	2278.4	2119.0	1849.9	1650.0	1577.8
40°	2171.2	1997.7	1716.6	1511.2	1435.9
42.5°	2061.2	1876.1	1583.6	1369.3	1297.1
45°	1945.5	1751.4	1447.6	1241.8	1172.4
47.5°	1835.5	1630.0	1317.3	1111.6	1048.0
50°	1713.9	1508.4	1189.9	989.9	929.4
52.5°	1595.0	1377.9	1068.3	877.2	822.2
55°	1479.2	1253.4	940.8	767.3	712.3
57.5°	1360.7	1129.1	828.1	665.9	619.5
60°	1239.0	1007.4	709.2	561.8	515.4
62.5°	1120.5	888.9	607.8	469.0	446.0
65°	998.8	764.2	503.7	405.4	396.5
67.5°	883.0	648.4	405.4	356.0	347.4
70°	761.4	535.7	335.7	306.8	295.2
72.5°	645.6	431.2	280.7	257.7	251.9
75°	532.6	329.9	231.6	211.3	208.6
77.5°	419.9	234.4	182.4	170.8	164.9
80°	315.4	168.0	138.8	127.5	127.5
82.5°	219.9	113.0	95.5	89.7	89.7
85°	124.4	63.6	55.0	55.0	55.0
87.5°	46.4	23.0	23.0	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P931546

CATALOG NUMBER: DFN2DS-TR4F0-090DS935-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.48	16.00	14.84	16.31	16.63	10.44	11.96	10.80	12.27	12.59
	3H	16.24	17.61	16.62	17.93	18.30	11.70	13.07	12.08	13.39	13.76
	4H	16.91	18.19	17.31	18.54	18.91	12.20	13.48	12.60	13.83	14.21
	6H	17.40	18.58	17.81	18.95	19.34	12.58	13.77	13.00	14.13	14.53
	8H	17.56	18.69	17.99	19.08	19.48	12.71	13.83	13.13	14.22	14.63
	12H	17.66	18.74	18.09	19.12	19.55	12.79	13.87	13.22	14.25	14.68
4H	2H	14.58	15.86	14.98	16.21	16.59	11.13	12.41	11.53	12.76	13.14
	3H	16.51	17.58	16.92	17.98	18.38	12.57	13.64	12.98	14.04	14.44
	4H	17.26	18.22	17.69	18.63	19.07	13.17	14.13	13.61	14.55	14.98
	6H	17.85	18.69	18.31	19.13	19.59	13.66	14.49	14.12	14.94	15.40
	8H	18.07	18.85	18.53	19.29	19.76	13.82	14.60	14.29	15.05	15.51
	12H	18.22	18.92	18.70	19.39	19.87	13.94	14.64	14.42	15.11	15.59
8H	4H	17.29	18.06	17.75	18.51	18.97	13.53	14.31	13.99	14.75	15.22
	6H	17.92	18.57	18.42	19.06	19.53	14.11	14.76	14.61	15.25	15.73
	8H	18.17	18.75	18.69	19.26	19.75	14.34	14.91	14.85	15.42	15.91
	12H	18.38	18.89	18.89	19.38	19.94	14.51	15.02	15.02	15.52	16.08
12H	4H	17.27	17.97	17.75	18.44	18.91	13.57	14.27	14.05	14.74	15.21
	6H	17.90	18.48	18.42	18.99	19.48	14.18	14.76	14.69	15.26	15.75
	8H	18.19	18.70	18.70	19.19	19.76	14.45	14.96	14.96	15.45	16.02