

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930901

Luminaire Tested: DFN2DS-SQ2F0-080DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ2F0-080DS950-FLL
Description: 2 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7484.4 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.21' x L: 2.21' x H: 0')
CIE Type: Direct

Input Watts (W): 82.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930901

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930901

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6468	6468	6468
5°	6493	6400	6438
10°	6455	6335	6366
15°	6375	6252	6246
20°	6261	6129	6123
25°	6149	5978	5978
30°	6005	5839	5789
35°	5869	5672	5588
40°	5700	5505	5399
45°	5533	5339	5208
50°	5351	5167	4983
55°	5162	4967	4782
60°	4951	4727	4553
65°	4725	4489	4283
70°	4437	4201	4001
75°	4036	3868	3774
80°	3584	3473	3295
85°	2924	2788	2498

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5533 cd/sqm

TEST NUMBER: P930901

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.9	3.7
10°-20°	779.0	10.4
20°-30°	1144.8	15.3
30°-40°	1329.6	17.8
40°-50°	1328.0	17.7
50°-60°	1158.0	15.5
60°-70°	856.0	11.4
70°-80°	484.3	6.5
80°-90°	127.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2200.7	29.4
0°-40°	3530.3	47.2
0°-60°	6016.3	80.4
0°-90°	7484.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7484.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2942	2942	2942	2942	2942	
5°	2942	2930	2899	2922	2916	279
15°	2800	2784	2746	2758	2744	789
25°	2534	2512	2464	2469	2464	1166
35°	2186	2158	2113	2096	2082	1365
45°	1779	1760	1717	1686	1675	1373
55°	1346	1329	1296	1262	1248	1204
65°	908	891	863	837	823	898
75°	475	470	455	438	444	507
85°	116	113	110	102	99	136
90°	0	0	0	0	0	

TEST NUMBER: P930901

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2941.6	2941.6	2941.6	2941.6	2941.6
2.5°	2958.7	2944.6	2913.4	2941.6	2936.2
5°	2941.6	2930.5	2899.4	2921.8	2916.5
7.5°	2921.8	2905.0	2873.8	2896.6	2890.9
10°	2890.9	2871.1	2837.2	2859.7	2851.3
12.5°	2848.3	2831.5	2797.6	2811.7	2806.0
15°	2800.3	2783.5	2746.5	2758.0	2743.9
17.5°	2740.9	2724.1	2687.1	2701.3	2687.1
20°	2675.8	2658.9	2619.4	2627.8	2616.6
22.5°	2610.9	2585.4	2548.5	2548.5	2542.8
25°	2534.4	2511.9	2463.9	2469.3	2463.9
27.5°	2449.4	2429.7	2393.0	2384.6	2370.5
30°	2364.9	2342.0	2299.8	2291.3	2279.9
32.5°	2274.2	2257.4	2212.1	2195.0	2183.6
35°	2186.5	2158.4	2113.0	2095.9	2081.8
37.5°	2087.5	2062.0	2016.7	1996.9	1982.8
40°	1985.8	1963.0	1917.7	1892.5	1881.0
42.5°	1886.8	1863.9	1818.9	1790.4	1773.7
45°	1779.3	1759.5	1716.9	1686.0	1674.6
47.5°	1674.6	1654.8	1609.4	1578.2	1561.4
50°	1564.2	1550.1	1510.4	1470.8	1456.7
52.5°	1456.7	1436.9	1400.3	1369.1	1349.3
55°	1346.5	1329.4	1295.6	1261.7	1247.5
57.5°	1236.2	1222.1	1185.1	1151.2	1139.8
60°	1125.7	1114.6	1074.9	1043.8	1035.3
62.5°	1018.2	998.5	970.2	942.1	930.6
65°	908.1	891.0	862.8	837.3	823.2
67.5°	794.9	780.6	755.3	735.6	724.2
70°	690.2	678.8	653.4	633.5	622.4
72.5°	582.8	571.4	557.3	537.5	529.1
75°	475.1	469.7	455.3	438.5	444.2
77.5°	379.0	367.6	361.9	353.5	345.1
80°	283.0	280.0	274.3	265.9	260.2
82.5°	192.4	192.4	189.7	178.2	178.2
85°	115.9	113.1	110.5	101.8	99.0
87.5°	51.0	45.4	39.6	31.2	28.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930901

CATALOG NUMBER: DFN2DS-SQ2F0-080DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.77	19.38	18.13	19.69	20.01	17.32	18.94	17.69	19.25	19.56
	3H	19.52	20.97	19.90	21.30	21.66	19.03	20.48	19.40	20.81	21.17
	4H	20.17	21.53	20.56	21.88	22.26	19.67	21.04	20.07	21.39	21.76
	6H	20.63	21.90	21.05	22.27	22.66	20.13	21.40	20.54	21.77	22.16
	8H	20.78	21.99	21.20	22.38	22.78	20.27	21.49	20.70	21.87	22.27
	12H	20.87	22.03	21.30	22.41	22.84	20.36	21.52	20.79	21.90	22.33
4H	2H	18.33	19.70	18.73	20.05	20.42	17.98	19.35	18.37	19.69	20.07
	3H	20.30	21.45	20.71	21.85	22.25	19.90	21.04	20.31	21.44	21.84
	4H	21.08	22.12	21.51	22.53	22.97	20.66	21.69	21.09	22.11	22.54
	6H	21.68	22.58	22.13	23.02	23.48	21.25	22.15	21.70	22.59	23.05
	8H	21.87	22.71	22.33	23.16	23.62	21.43	22.28	21.89	22.72	23.18
	12H	22.00	22.76	22.48	23.23	23.70	21.55	22.31	22.03	22.78	23.25
8H	4H	21.35	22.20	21.82	22.64	23.11	20.98	21.83	21.44	22.27	22.73
	6H	22.07	22.77	22.56	23.26	23.74	21.69	22.39	22.18	22.88	23.35
	8H	22.33	22.96	22.84	23.47	23.95	21.94	22.57	22.45	23.07	23.56
	12H	22.53	23.09	23.03	23.58	24.14	22.11	22.67	22.62	23.16	23.72
12H	4H	21.38	22.14	21.86	22.62	23.09	21.02	21.78	21.50	22.25	22.72
	6H	22.11	22.75	22.62	23.25	23.74	21.75	22.38	22.26	22.88	23.37
	8H	22.43	22.99	22.93	23.48	24.04	22.05	22.61	22.56	23.10	23.66

END OF REPORT