

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332243-940

Luminaire Tested: **S123RDIP-S340D365U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332243-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2451.9 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332243-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot



TEST NUMBER: P332243-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	42	41	39
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	26	23	20
8	54	42	35	29	50	39	32	28	34	28	24	28	24	21	24	20	18
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	16
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334

TEST NUMBER: P332243-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	2.0
10°-20°	133.9	5.5
20°-30°	192.7	7.9
30°-40°	217.1	8.9
40°-50°	207.7	8.5
50°-60°	170.1	6.9
60°-70°	114.8	4.7
70°-80°	57.7	2.4
80°-90°	16.5	0.7
90°-100°	15.4	0.6
100°-110°	73.5	3.0
110°-120°	176.5	7.2
120°-130°	224.8	9.2
130°-140°	240.2	9.8
140°-150°	224.6	9.2
150°-160°	181.2	7.4
160°-170°	116.9	4.8
170°-180°	40.3	1.6
0°-30°	374.7	15.3
0°-40°	591.8	24.1
0°-60°	969.6	39.5
0°-90°	1158.5	47.2
90°-120°	265.4	10.8
90°-150°	955.0	38.9
90°-180°	1293.0	52.7
0°-180°	2451.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	0	4	8	9	10	2
95°	19	7	10	12	12	24
105°	94	96	69	16	14	100
115°	176	178	181	184	185	174
125°	248	251	252	253	253	222
135°	309	311	312	313	312	238
145°	357	359	360	360	360	223
155°	393	392	393	394	392	181
165°	414	413	413	415	413	117
175°	424	423	423	425	423	40
180°	424	424	424	424	424	

TEST NUMBER: P332243-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.0	7.4	6.7	6.1	5.4	5.1	5.3	5.4	5.6	5.8	5.8
90°	0.4	1.0	1.7	2.4	3.1	3.9	4.8	5.7	6.7	7.6	7.8
92.5°	5.9	5.7	5.4	5.3	5.1	5.4	6.0	6.7	7.4	8.0	8.5
95°	19.3	16.3	13.5	10.6	7.8	6.7	7.5	8.2	9.0	9.8	10.3
97.5°	38.6	37.4	36.0	34.8	33.4	30.3	25.2	20.2	15.2	10.2	10.7
100°	53.2	54.7	56.1	57.4	58.9	54.1	43.2	32.3	21.3	10.4	11.0
102.5°	69.9	70.9	71.9	72.9	73.9	68.5	56.5	44.6	32.6	20.8	19.0
105°	93.9	94.7	95.4	96.2	97.0	94.3	87.9	81.6	75.3	69.0	56.6
107.5°	119.2	119.8	120.5	121.1	121.7	122.5	123.5	124.5	125.5	126.4	117.3
110°	136.2	136.7	137.2	137.8	138.4	139.0	139.8	140.5	141.3	142.1	139.8

TEST NUMBER: P332243-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.2	152.8	153.3	153.7	154.3	154.9	155.7	156.5	157.2	158.0	158.0
115°	176.1	176.6	177.0	177.4	177.8	178.3	179.0	179.6	180.2	180.8	181.6
117.5°	199.3	199.8	200.3	200.8	201.3	201.8	202.1	202.4	202.8	203.0	203.6
120°	213.7	214.3	214.9	215.5	216.2	216.6	216.8	217.0	217.2	217.4	218.0
122.5°	228.3	228.8	229.3	229.8	230.3	230.7	231.0	231.2	231.5	231.8	232.2
125°	248.3	248.9	249.4	249.9	250.6	250.9	251.3	251.6	251.8	252.1	252.3
127.5°	267.7	268.3	268.9	269.4	269.9	270.4	270.7	271.1	271.4	271.7	272.0
130°	279.8	280.4	280.9	281.5	282.0	282.5	282.8	283.0	283.3	283.6	283.8
132.5°	291.4	291.9	292.6	293.1	293.6	294.0	294.3	294.5	294.7	295.0	295.2
135°	309.2	309.5	310.0	310.4	310.8	311.1	311.4	311.7	312.0	312.3	312.5
137.5°	324.2	324.8	325.3	325.8	326.4	326.7	326.9	327.0	327.2	327.3	327.7
140°	334.3	334.7	335.2	335.6	336.0	336.4	336.5	336.7	337.0	337.2	337.4
142.5°	343.7	344.1	344.5	344.9	345.4	345.6	345.9	346.1	346.3	346.5	346.7
145°	356.7	357.2	357.7	358.2	358.6	359.0	359.1	359.3	359.4	359.5	359.7
147.5°	369.0	369.3	369.6	370.0	370.2	370.5	370.7	370.8	371.0	371.0	371.2
150°	376.6	376.7	376.9	377.2	377.4	377.6	377.7	377.8	378.0	378.1	378.3
152.5°	383.3	383.4	383.5	383.6	383.7	383.9	383.9	384.0	384.1	384.1	384.4
155°	393.0	392.8	392.6	392.5	392.4	392.4	392.4	392.4	392.5	392.6	393.0
157.5°	400.4	400.4	400.4	400.3	400.3	400.3	400.2	400.1	400.0	400.0	400.4
160°	404.9	404.8	404.7	404.7	404.7	404.6	404.5	404.4	404.4	404.3	404.7
162.5°	409.2	409.0	408.8	408.7	408.5	408.3	408.2	408.2	408.1	408.0	408.5
165°	414.4	414.1	413.9	413.8	413.5	413.4	413.3	413.2	413.1	413.1	413.7
167.5°	418.4	418.1	417.9	417.6	417.2	417.1	417.1	417.1	417.1	417.1	417.7
170°	420.6	420.4	420.1	419.8	419.5	419.4	419.4	419.4	419.4	419.4	420.0
172.5°	422.1	421.9	421.5	421.2	420.8	420.7	420.7	420.8	420.9	420.9	421.5
175°	424.1	423.7	423.4	423.1	422.8	422.6	422.7	422.8	422.8	422.8	423.4
177.5°	424.6	424.4	424.1	423.8	423.5	423.4	423.5	423.5	423.6	423.7	424.1
180°	424.1	424.1	424.1	424.1	424.1	424.1	424.1	424.1	424.1	424.1	424.1

TEST NUMBER: P332243-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	5.8	5.8	5.8	5.7	5.7	5.6	5.6	5.5
90°	8.1	8.4	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	9.0	9.5	9.9	10.2	10.2	10.3	10.3	10.4
95°	10.8	11.2	11.8	11.9	11.9	11.9	11.9	11.9
97.5°	11.2	11.9	12.4	12.7	12.8	12.8	12.9	13.0
100°	11.5	12.0	12.7	12.9	13.0	13.1	13.2	13.2
102.5°	17.3	15.5	13.8	13.0	13.1	13.2	13.4	13.5
105°	44.2	31.8	19.4	13.3	13.5	13.6	13.7	13.8
107.5°	108.3	99.2	90.2	80.9	71.6	62.2	52.9	43.5
110°	137.5	135.2	132.9	126.7	116.7	106.6	96.7	86.7

TEST NUMBER: P332243-940

CATALOG NUMBER: S123RDIP-S340D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	158.1	158.1	158.2	157.1	155.0	152.9	150.8	148.6
115°	182.3	183.0	183.7	184.1	184.4	184.8	185.0	185.3
117.5°	204.2	204.7	205.3	205.6	205.6	205.7	205.8	205.8
120°	218.6	219.1	219.6	220.0	220.0	220.0	220.0	220.0
122.5°	232.6	233.0	233.4	233.5	233.6	233.7	233.7	233.8
125°	252.4	252.5	252.6	252.8	252.9	253.1	253.2	253.3
127.5°	272.2	272.4	272.7	272.7	272.5	272.4	272.2	272.2
130°	284.2	284.5	284.7	284.8	284.6	284.5	284.4	284.2
132.5°	295.5	295.8	296.0	296.1	295.9	295.7	295.5	295.3
135°	312.7	312.9	313.1	313.1	312.9	312.7	312.5	312.3
137.5°	328.0	328.3	328.7	328.8	328.6	328.5	328.3	328.2
140°	337.7	338.0	338.3	338.3	338.2	338.0	338.0	337.8
142.5°	347.0	347.1	347.4	347.4	347.2	347.0	346.8	346.6
145°	359.8	360.0	360.1	360.2	360.2	360.2	360.2	360.2
147.5°	371.3	371.5	371.7	371.6	371.2	370.9	370.6	370.2
150°	378.4	378.5	378.7	378.6	378.4	378.3	378.0	377.8
152.5°	384.7	385.0	385.2	385.1	384.9	384.5	384.1	383.9
155°	393.3	393.7	394.0	394.0	393.6	393.2	392.7	392.3
157.5°	400.8	401.3	401.7	401.6	401.1	400.6	399.9	399.4
160°	405.1	405.6	406.0	405.9	405.5	404.9	404.5	403.9
162.5°	409.0	409.5	409.9	410.0	409.6	409.1	408.7	408.2
165°	414.2	414.8	415.4	415.4	414.9	414.4	413.9	413.4
167.5°	418.2	418.8	419.4	419.4	418.8	418.2	417.7	417.1
170°	420.5	421.1	421.6	421.6	421.1	420.5	420.0	419.4
172.5°	422.0	422.6	423.1	423.1	422.5	421.9	421.2	420.6
175°	423.8	424.4	424.8	424.8	424.3	423.7	423.1	422.6
177.5°	424.5	425.0	425.4	425.3	424.8	424.3	423.7	423.1
180°	424.1	424.1	424.1	424.1	424.1	424.1	424.1	424.1

(END OF REPORT)