

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333601-830

Luminaire Tested: **S125RDIP-S1090D1035U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333601-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D1035U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7881.1 lumens  
Efficiency: N/A  
Efficacy: 130.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333601-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333601-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	90	87	84	81	74	71	69	62	60	58	50	49	48	43
2	90	82	76	71	82	76	71	66	65	61	58	54	52	49	45	43	41	36
3	82	72	65	59	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333601-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.4	2.0
10°-20°	442.7	5.6
20°-30°	642.0	8.1
30°-40°	731.6	9.3
40°-50°	713.2	9.0
50°-60°	600.3	7.6
60°-70°	420.8	5.3
70°-80°	216.3	2.7
80°-90°	57.3	0.7
90°-100°	46.1	0.6
100°-110°	284.3	3.6
110°-120°	515.7	6.5
120°-130°	661.8	8.4
130°-140°	711.8	9.0
140°-150°	668.2	8.5
150°-160°	540.5	6.9
160°-170°	349.6	4.4
170°-180°	120.6	1.5
0°-30°	1243.1	15.8
0°-40°	1974.7	25.1
0°-60°	3288.2	41.7
0°-90°	3982.6	50.5
90°-120°	846.1	10.7
90°-150°	2887.9	36.6
90°-180°	3899.0	49.5
0°-180°	7881.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	8	15	20	23	5
95°	54	49	15	20	20	68
105°	277	280	280	280	280	293
115°	520	524	525	521	516	515
125°	739	745	745	742	739	660
135°	921	927	925	923	918	710
145°	1068	1070	1070	1071	1065	668
155°	1176	1171	1173	1175	1168	542
165°	1241	1236	1237	1242	1235	351
175°	1270	1264	1265	1271	1264	121
180°	1270	1270	1270	1270	1270	



TEST NUMBER: P333601-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.6	22.3	21.1	19.9	18.6	18.0	18.1	18.2	18.2	18.3	18.5
90°	0.9	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1
92.5°	14.5	13.3	12.2	10.9	9.8	9.9	11.1	12.4	13.8	15.1	16.1
95°	53.6	53.0	52.4	51.7	51.2	46.8	38.9	30.9	23.0	15.1	16.1
97.5°	112.0	113.1	114.2	115.4	116.5	109.2	93.5	77.8	62.0	46.3	40.4
100°	157.1	157.8	158.4	159.0	159.7	160.4	161.3	162.1	162.9	163.7	132.6
102.5°	203.1	203.9	204.7	205.5	206.2	206.9	207.5	207.9	208.4	209.0	203.0
105°	276.6	277.5	278.3	279.2	280.0	280.4	280.4	280.4	280.4	280.4	280.4
107.5°	353.1	353.1	353.1	353.1	353.1	353.3	353.7	354.1	354.6	355.0	355.1
110°	402.7	402.7	402.7	402.7	402.7	403.0	403.4	403.9	404.3	404.6	404.1



TEST NUMBER: P333601-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	449.5	450.0	450.4	451.0	451.5	451.9	452.1	452.3	452.6	452.9	452.0
115°	519.5	520.6	521.6	522.6	523.7	524.3	524.5	524.7	524.9	525.1	524.3
117.5°	591.9	591.9	591.8	591.8	591.8	592.2	593.0	593.7	594.6	595.3	594.3
120°	637.2	636.9	636.7	636.5	636.3	636.5	637.2	637.7	638.4	639.0	638.6
122.5°	677.0	677.8	678.6	679.4	680.2	680.7	681.1	681.4	681.6	681.9	681.5
125°	738.8	740.2	741.7	743.2	744.6	745.4	745.4	745.4	745.4	745.4	744.5
127.5°	797.7	798.7	799.7	800.8	801.8	802.3	802.2	802.1	801.9	801.8	801.3
130°	833.8	834.9	835.9	837.0	838.0	838.6	838.9	839.1	839.2	839.4	838.9
132.5°	870.0	871.2	872.4	873.5	874.8	875.2	874.7	874.3	873.8	873.4	873.2
135°	921.3	922.6	923.9	925.1	926.3	926.8	926.3	926.0	925.5	925.1	924.6
137.5°	968.6	969.7	970.7	971.9	972.9	973.3	972.9	972.5	972.1	971.8	971.9
140°	999.5	999.8	1000.3	1000.7	1001.1	1001.3	1001.0	1000.8	1000.6	1000.4	1000.8
142.5°	1027.3	1027.6	1027.8	1028.0	1028.3	1028.6	1028.9	1029.2	1029.4	1029.7	1029.8
145°	1068.2	1068.6	1068.9	1069.4	1069.8	1070.1	1070.1	1070.1	1070.1	1070.1	1070.3
147.5°	1103.9	1103.8	1103.7	1103.6	1103.5	1103.6	1103.9	1104.2	1104.4	1104.7	1104.9
150°	1126.5	1126.1	1125.7	1125.2	1124.8	1124.8	1125.2	1125.7	1126.1	1126.5	1126.9
152.5°	1148.3	1147.5	1146.5	1145.6	1144.6	1144.4	1144.8	1145.2	1145.7	1146.0	1146.5
155°	1176.4	1175.2	1173.8	1172.6	1171.4	1170.9	1171.4	1171.8	1172.1	1172.6	1173.3
157.5°	1198.0	1197.2	1196.6	1195.8	1195.0	1194.7	1194.7	1194.8	1194.8	1194.9	1195.5
160°	1213.1	1211.8	1210.6	1209.3	1208.1	1207.5	1207.8	1208.0	1208.2	1208.3	1209.2
162.5°	1225.1	1223.9	1222.6	1221.3	1220.1	1219.6	1219.7	1220.0	1220.2	1220.4	1221.6
165°	1241.3	1240.0	1238.8	1237.6	1236.3	1235.8	1236.0	1236.1	1236.4	1236.6	1237.8
167.5°	1253.4	1252.1	1250.8	1249.4	1248.2	1247.6	1247.8	1248.0	1248.2	1248.5	1250.0
170°	1260.1	1258.7	1257.2	1255.7	1254.2	1253.7	1253.9	1254.1	1254.2	1254.5	1256.1
172.5°	1264.6	1263.2	1261.7	1260.3	1258.8	1258.3	1258.6	1259.0	1259.3	1259.7	1261.2
175°	1269.5	1268.3	1267.1	1265.7	1264.5	1264.0	1264.2	1264.4	1264.6	1264.8	1266.5
177.5°	1271.8	1270.8	1269.8	1268.8	1267.8	1267.3	1267.5	1267.7	1267.9	1268.0	1269.2
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5



TEST NUMBER: P333601-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	18.7	18.9	19.1	19.1	19.0	18.9	18.9	18.8
90°	17.2	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	17.2	18.2	19.2	19.9	20.2	20.5	20.8	21.1
95°	17.2	18.2	19.2	19.8	19.8	19.8	19.8	19.8
97.5°	34.5	28.7	22.7	19.8	19.8	19.8	19.8	19.8
100°	101.4	70.3	39.1	23.1	22.2	21.4	20.6	19.8
102.5°	197.1	191.2	185.3	175.3	161.1	146.8	132.6	118.4
105°	280.4	280.4	280.4	280.3	280.1	279.9	279.7	279.5
107.5°	355.1	355.2	355.2	354.9	354.2	353.6	353.0	352.3
110°	403.4	402.7	402.2	402.0	402.2	402.4	402.6	402.7





TEST NUMBER: P333601-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.3	450.4	449.7	449.1	448.8	448.6	448.3	448.0
115°	523.5	522.6	521.8	520.8	519.5	518.2	517.0	515.8
117.5°	593.1	592.1	591.0	590.1	589.7	589.1	588.5	588.0
120°	638.2	637.7	637.3	636.6	635.6	634.5	633.5	632.4
122.5°	681.1	680.7	680.2	679.4	678.3	677.0	675.8	674.6
125°	743.7	742.8	742.0	741.3	740.6	740.0	739.4	738.8
127.5°	800.9	800.4	799.9	799.0	797.4	795.9	794.4	792.8
130°	838.2	837.5	837.0	836.1	835.1	834.1	833.0	831.9
132.5°	873.1	873.0	872.8	872.2	871.2	870.2	869.1	868.1
135°	924.3	923.9	923.4	922.6	921.3	920.1	918.8	917.6
137.5°	971.9	972.0	972.1	971.6	970.5	969.4	968.4	967.2
140°	1001.3	1001.6	1002.0	1001.6	1000.4	999.1	997.9	996.6
142.5°	1029.9	1030.0	1030.1	1029.5	1028.2	1027.0	1025.8	1024.4
145°	1070.4	1070.6	1070.8	1070.4	1069.1	1067.8	1066.6	1065.4
147.5°	1105.1	1105.4	1105.7	1105.0	1103.5	1102.0	1100.5	1099.0
150°	1127.4	1127.8	1128.1	1127.6	1125.9	1124.2	1122.5	1120.9
152.5°	1146.9	1147.4	1147.7	1147.2	1145.7	1144.2	1142.6	1141.1
155°	1173.8	1174.5	1175.2	1174.6	1172.9	1171.2	1169.6	1167.9
157.5°	1196.2	1196.8	1197.5	1197.0	1195.3	1193.6	1191.9	1190.3
160°	1210.0	1210.9	1211.7	1211.3	1209.7	1208.0	1206.3	1204.6
162.5°	1222.8	1223.9	1225.1	1224.7	1222.9	1221.1	1219.3	1217.4
165°	1239.1	1240.4	1241.6	1241.4	1239.7	1238.0	1236.4	1234.7
167.5°	1251.5	1253.0	1254.5	1254.3	1252.5	1250.6	1248.7	1246.8
170°	1257.8	1259.5	1261.2	1261.0	1259.1	1257.4	1255.5	1253.6
172.5°	1262.7	1264.2	1265.7	1265.6	1263.7	1261.8	1259.9	1258.1
175°	1268.2	1269.9	1271.5	1271.4	1269.5	1267.6	1265.7	1263.9
177.5°	1270.4	1271.6	1272.7	1272.6	1271.3	1270.0	1268.7	1267.2
180°	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5	1269.5

(END OF REPORT)