

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997798

Luminaire Tested: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P997798
REPORT IS A COMBINATION OF REPORTS P983532 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8279.0 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997798

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P997798

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	90	86	82	86	82	79	75	68	65	63	54	52	51	42	41	39
2	86	78	71	66	78	71	65	61	59	54	51	47	44	41	36	34	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	17	15
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16632	16632	16632
5°	16706	15921	15831
10°	16595	15371	15146
15°	16360	14799	14442
20°	16066	14201	13775
25°	15773	13627	13169
30°	15364	13044	12569
35°	14950	12483	12129
40°	14515	11997	11692
45°	14100	11555	11311
50°	13655	11149	10935
55°	13187	10718	10551
60°	12614	10269	10149
65°	12016	9752	9684
70°	11342	9198	9185
75°	10478	8643	8715
80°	9117	8066	8226
85°	7741	7522	7807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14100 cd/sqm

TEST NUMBER: P997798

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.2
10°-20°	285.7	3.5
20°-30°	432.8	5.2
30°-40°	527.1	6.4
40°-50°	567.1	6.8
50°-60°	550.7	6.7
60°-70°	481.0	5.8
70°-80°	370.2	4.5
80°-90°	250.5	3.0
90°-100°	219.1	2.6
100°-110°	303.8	3.7
110°-120°	557.0	6.7
120°-130°	833.0	10.1
130°-140°	855.3	10.3
140°-150°	780.3	9.4
150°-160°	624.7	7.5
160°-170°	402.5	4.9
170°-180°	138.5	1.7
0°-30°	818.1	9.9
0°-40°	1345.2	16.2
0°-60°	2463.0	29.8
0°-90°	3564.6	43.1
90°-120°	1079.9	13.0
90°-150°	3548.5	42.9
90°-180°	4714.0	56.9
0°-180°	8279.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1051	1051	1051	1051	1051	
5°	1054	1049	1040	1049	1048	100
15°	1005	1008	1008	1022	1020	283
25°	914	924	938	956	961	420
35°	787	813	842	876	886	492
45°	646	687	740	787	802	498
55°	495	550	629	684	704	443
65°	338	413	502	565	585	336
75°	187	273	370	436	455	198
85°	55	149	247	311	332	58
90°	16	116	222	288	309	15
95°	81	117	216	279	296	91
105°	328	404	195	260	281	351
115°	612	646	741	299	240	602
125°	859	873	942	990	1007	767
135°	1061	1078	1103	1145	1155	820
145°	1229	1228	1246	1262	1265	769
155°	1354	1344	1357	1363	1354	624
165°	1426	1420	1423	1430	1423	403
175°	1459	1451	1454	1461	1450	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P997798

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1050.7	1050.7	1050.7	1050.7	1050.7
2.5°	1058.3	1053.7	1043.1	1050.7	1047.6
5°	1053.7	1049.2	1040.0	1049.2	1047.6
7.5°	1046.1	1043.1	1035.4	1046.1	1044.6
10°	1037.0	1033.9	1029.4	1041.5	1040.0
12.5°	1021.7	1023.3	1020.2	1032.4	1030.9
15°	1005.0	1008.0	1008.0	1021.7	1020.2
17.5°	983.7	989.8	994.3	1008.0	1008.0
20°	962.4	970.0	976.1	992.8	992.8
22.5°	939.5	948.7	957.8	974.5	977.6
25°	913.6	924.3	938.0	956.3	960.8
27.5°	883.2	899.9	915.2	938.0	941.0
30°	852.7	872.5	892.3	916.7	921.2
32.5°	819.2	842.1	866.4	895.4	904.5
35°	787.2	813.1	842.1	875.6	886.2
37.5°	752.2	781.2	817.7	854.2	864.9
40°	717.2	750.7	791.8	831.4	845.1
42.5°	683.7	717.2	765.9	810.1	823.8
45°	645.6	686.7	740.0	787.2	802.5
47.5°	609.1	653.2	714.2	762.9	779.6
50°	571.0	618.2	686.7	738.5	755.3
52.5°	534.5	584.7	657.8	711.1	729.4
55°	494.9	549.7	628.9	683.7	703.5
57.5°	456.8	517.7	596.9	656.3	676.1
60°	415.7	481.2	568.0	625.8	647.2
62.5°	379.2	447.7	534.5	596.9	616.7
65°	338.0	412.7	502.5	564.9	584.7
67.5°	301.5	379.2	470.5	533.0	554.3
70°	261.9	341.1	435.5	501.0	519.2
72.5°	225.4	307.6	403.5	467.5	490.3
75°	187.3	272.6	370.0	435.5	455.3
77.5°	150.7	239.1	338.0	403.5	424.8
80°	114.2	207.1	306.1	370.0	391.3
82.5°	83.7	175.1	275.6	339.6	359.4
85°	54.8	149.2	246.7	310.6	332.0
87.5°	33.5	124.9	222.3	284.7	304.5
90°	16.3	116.1	222.1	288.2	308.6
92.5°	40.0	116.5	212.6	274.1	293.4
95°	80.7	117.4	216.2	279.3	296.5
97.5°	133.9	113.0	218.2	277.7	297.0
100°	197.1	109.1	212.3	277.1	296.0
102.5°	265.0	313.2	203.7	270.1	290.1
105°	327.8	403.6	195.3	260.0	281.0
107.5°	402.6	465.5	186.7	250.0	271.0
110°	472.7	525.2	295.5	238.9	259.8

TEST NUMBER: P997798

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	540.1	583.5	635.6	230.3	250.3
115°	611.7	646.3	741.3	299.2	240.2
117.5°	672.4	705.6	787.5	682.5	421.8
120°	741.9	763.8	843.7	898.9	773.5
122.5°	800.9	819.2	896.6	944.0	958.8
125°	859.3	873.0	941.8	990.3	1007.2
127.5°	914.1	927.3	984.2	1032.9	1047.6
130°	965.7	981.1	1024.6	1072.7	1083.9
132.5°	1018.4	1030.6	1065.0	1109.5	1120.7
135°	1061.1	1078.0	1102.6	1145.2	1155.3
137.5°	1107.5	1120.1	1138.2	1177.8	1185.2
140°	1152.7	1159.7	1174.3	1208.1	1212.0
142.5°	1190.7	1196.5	1210.2	1237.0	1239.3
145°	1229.2	1228.1	1246.0	1262.5	1264.8
147.5°	1263.9	1260.8	1278.7	1285.5	1285.8
150°	1297.7	1290.3	1307.1	1313.5	1308.2
152.5°	1326.1	1317.7	1333.5	1339.8	1332.4
155°	1353.5	1344.0	1356.6	1363.0	1354.5
157.5°	1375.6	1367.2	1376.6	1384.0	1375.6
160°	1394.6	1388.2	1394.6	1400.9	1393.5
162.5°	1411.4	1405.1	1410.4	1417.7	1408.2
165°	1426.2	1419.8	1423.0	1430.4	1423.0
167.5°	1437.7	1431.4	1434.6	1442.0	1432.5
170°	1447.2	1440.9	1443.0	1450.4	1440.9
172.5°	1453.5	1447.2	1449.3	1456.7	1447.2
175°	1458.8	1451.4	1453.5	1460.9	1450.4
177.5°	1460.9	1453.5	1454.6	1462.0	1452.5
180°	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P997798

CATALOG NUMBER: SA2XXDIP-B1005D1080UB2750-4F0-XX-W2A-D_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.31	15.15	15.31	16.17	17.54	17.38	18.23	18.39	19.25	20.61
	3H	15.77	16.53	16.78	17.56	18.94	19.97	20.73	20.99	21.77	23.15
	4H	16.24	16.97	17.27	18.00	19.39	21.22	21.95	22.25	22.98	24.37
	6H	16.53	17.20	17.56	18.23	19.64	22.52	23.19	23.56	24.23	25.63
	8H	16.59	17.23	17.63	18.28	19.68	23.18	23.82	24.22	24.87	26.27
	12H	16.60	17.21	17.65	18.26	19.68	23.90	24.51	24.95	25.56	26.99
4H	2H	15.36	16.08	16.39	17.12	18.51	17.71	18.44	18.74	19.47	20.86
	3H	17.06	17.68	18.10	18.74	20.14	20.50	21.12	21.54	22.18	23.58
	4H	17.69	18.25	18.73	19.30	20.73	21.92	22.48	22.97	23.54	24.96
	6H	18.10	18.59	19.16	19.67	21.09	23.39	23.88	24.44	24.95	26.37
	8H	18.21	18.67	19.27	19.74	21.17	24.14	24.60	25.20	25.67	27.11
	12H	18.25	18.67	19.33	19.75	21.19	24.97	25.39	26.05	26.47	27.91
8H	4H	18.47	18.94	19.53	20.00	21.44	22.06	22.52	23.12	23.59	25.03
	6H	19.11	19.49	20.19	20.60	22.03	23.69	24.08	24.77	25.19	26.62
	8H	19.33	19.67	20.41	20.76	22.21	24.58	24.92	25.67	26.01	27.46
	12H	19.46	19.76	20.55	20.85	22.34	25.57	25.88	26.66	26.96	28.45
12H	4H	18.67	19.09	19.75	20.17	21.61	22.03	22.45	23.11	23.54	24.98
	6H	19.44	19.78	20.53	20.88	22.33	23.71	24.06	24.80	25.15	26.60
	8H	19.74	20.05	20.84	21.14	22.63	24.64	24.95	25.73	26.03	27.52

END OF REPORT