

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931103

Luminaire Tested: DFN2DS-SQ4F0-080DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-080DS835-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7920.0 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 79.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931103

CATALOG NUMBER: DFN2DS-SQ4F0-080DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931103

CATALOG NUMBER: DFN2DS-SQ4F0-080DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2184	2184	2184
5°	2193	2161	2174
10°	2180	2139	2150
15°	2153	2111	2109
20°	2114	2070	2068
25°	2076	2019	2019
30°	2028	1972	1955
35°	1982	1915	1887
40°	1925	1859	1823
45°	1868	1803	1758
50°	1807	1745	1683
55°	1743	1677	1615
60°	1672	1596	1538
65°	1596	1516	1446
70°	1498	1418	1351
75°	1363	1306	1274
80°	1210	1173	1112
85°	987	941	844

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1868 cd/sqm

TEST NUMBER: P931103

CATALOG NUMBER: DFN2DS-SQ4F0-080DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	3.7
10°-20°	824.3	10.4
20°-30°	1211.5	15.3
30°-40°	1407.0	17.8
40°-50°	1405.3	17.7
50°-60°	1225.4	15.5
60°-70°	905.8	11.4
70°-80°	512.5	6.5
80°-90°	135.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2328.8	29.4
0°-40°	3735.8	47.2
0°-60°	6366.4	80.4
0°-90°	7920.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	144
90°	0	0	0	0	0	

TEST NUMBER: P931103

CATALOG NUMBER: DFN2DS-SQ4F0-080DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931103

CATALOG NUMBER: DFN2DS-SQ4F0-080DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.00	15.61	14.36	15.92	16.24	13.55	15.16	13.92	15.48	15.79
	3H	15.75	17.20	16.12	17.53	17.89	15.26	16.71	15.63	17.04	17.40
	4H	16.39	17.76	16.79	18.11	18.49	15.90	17.27	16.30	17.62	17.99
	6H	16.86	18.13	17.27	18.50	18.89	16.36	17.63	16.77	17.99	18.39
	8H	17.01	18.22	17.43	18.61	19.00	16.50	17.71	16.93	18.10	18.50
	12H	17.10	18.26	17.53	18.64	19.07	16.58	17.74	17.01	18.13	18.55
4H	2H	14.56	15.93	14.96	16.27	16.65	14.20	15.57	14.60	15.92	16.30
	3H	16.53	17.68	16.94	18.08	18.48	16.13	17.27	16.54	17.67	18.07
	4H	17.31	18.34	17.74	18.76	19.19	16.89	17.92	17.32	18.33	18.77
	6H	17.91	18.81	18.36	19.25	19.71	17.47	18.38	17.93	18.82	19.27
	8H	18.09	18.94	18.56	19.38	19.85	17.66	18.50	18.12	18.95	19.41
	12H	18.23	18.99	18.71	19.46	19.93	17.77	18.53	18.25	19.01	19.48
8H	4H	17.58	18.43	18.04	18.87	19.34	17.21	18.05	17.67	18.50	18.96
	6H	18.30	19.00	18.79	19.49	19.96	17.92	18.62	18.41	19.11	19.58
	8H	18.56	19.19	19.07	19.69	20.18	18.16	18.79	18.67	19.30	19.79
	12H	18.76	19.31	19.26	19.80	20.37	18.34	18.90	18.85	19.39	19.95
12H	4H	17.61	18.37	18.09	18.84	19.31	17.24	18.00	17.72	18.48	18.95
	6H	18.34	18.97	18.85	19.48	19.97	17.97	18.61	18.48	19.11	19.60
	8H	18.66	19.21	19.16	19.70	20.27	18.28	18.84	18.78	19.33	19.89