

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P997912

Luminaire Tested: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P997912
REPORT IS A COMBINATION OF REPORTS P983649 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6557.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72			68
1	102	98	94	91	96	93	90	87	83	80	78	73	72	70	65	64	62			58
2	94	87	81	75	88	82	77	72	73	69	66	65	62	59	58	56	54			50
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46			43
4	79	68	61	55	74	65	58	53	58	53	48	52	48	44	47	43	40			37
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	43	39	36			33
6	67	55	47	42	64	53	46	40	48	42	37	43	38	35	39	35	32			29
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	36	32	29			26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26			24
9	55	42	35	30	52	40	34	29	37	31	27	34	29	25	31	27	24			22
10	51	39	32	27	48	37	31	26	34	29	25	31	26	23	28	24	22			20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31769	31769	31769	31769
5°	31845	33874	31967	26949
10°	31476	36978	31673	22219
15°	30711	39004	31139	18715
20°	30233	36622	30233	16267
25°	29270	31461	29403	14546
30°	27685	24732	28213	13176
35°	26279	17101	26719	12055
40°	24665	12912	24947	11162
45°	22674	10611	23046	10198
50°	20953	9313	20991	9335
55°	18991	7935	19113	8399
60°	16899	6629	17133	7330
65°	15027	5391	15300	6259
70°	13161	4230	13494	5049
75°	11048	3070	11479	3662
80°	8622	1947	9237	2174
85°	5664	981	6102	727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32840 cd/sqm

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	2.9
10°-20°	556.4	8.5
20°-30°	807.5	12.3
30°-40°	851.2	13.0
40°-50°	753.3	11.5
50°-60°	601.5	9.2
60°-70°	408.5	6.2
70°-80°	209.0	3.2
80°-90°	50.7	0.8
90°-100°	23.9	0.4
100°-110°	89.2	1.4
110°-120°	236.6	3.6
120°-130°	392.4	6.0
130°-140°	416.8	6.4
140°-150°	387.4	5.9
150°-160°	311.5	4.8
160°-170°	200.7	3.1
170°-180°	69.1	1.1
0°-30°	1555.0	23.7
0°-40°	2406.3	36.7
0°-60°	3761.0	57.4
0°-90°	4429.3	67.6
90°-120°	349.8	5.3
90°-150°	1546.5	23.6
90°-180°	2128.0	32.5
0°-180°	6557.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2007	2007	2007	2007	2007	
5°	2008	2242	2016	1783	2008	190
15°	1887	2755	1913	1322	1887	533
25°	1695	2295	1703	1061	1695	775
35°	1384	1250	1407	881	1384	866
45°	1038	753	1055	724	1038	805
55°	713	529	717	560	713	636
65°	423	326	430	378	423	420
75°	198	160	205	191	198	212
85°	40	42	43	31	40	47
90°	0	14	0	14	0	4
95°	34	23	34	23	34	40
105°	160	40	160	40	160	171
115°	302	43	302	43	302	297
125°	427	449	427	449	427	381
135°	528	546	528	546	528	408
145°	613	622	613	622	613	383
155°	675	675	675	675	675	311
165°	711	710	711	710	711	201
175°	727	723	727	723	727	69
180°	726	726	726	726	726	

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2017.8	2022.4	2030.1	2031.7	2047.1	2059.4	2073.3	2073.3	2077.9	2076.4	2064.1
5°	2008.5	2022.4	2042.5	2059.4	2087.2	2099.5	2118.0	2131.9	2144.3	2153.5	2152.0
7.5°	1993.1	2017.8	2047.1	2079.5	2116.5	2138.1	2164.3	2189.0	2206.0	2221.4	2232.2
10°	1966.9	2008.5	2048.6	2091.8	2139.6	2169.0	2199.8	2232.2	2258.4	2287.7	2315.5
12.5°	1931.4	1991.5	2040.9	2098.0	2156.6	2189.0	2238.4	2263.1	2314.0	2388.0	2408.1
15°	1886.6	1968.4	2014.7	2087.2	2164.3	2190.6	2258.4	2298.5	2403.4	2449.7	2505.2
17.5°	1845.0	1936.0	1997.7	2081.0	2156.6	2207.5	2273.9	2355.6	2443.5	2509.9	2571.6
20°	1811.1	1899.0	1973.0	2065.6	2161.2	2226.0	2295.4	2394.2	2489.8	2557.7	2605.5
22.5°	1733.9	1846.5	1932.9	2036.3	2152.0	2241.5	2307.8	2415.8	2519.1	2560.8	2602.4
25°	1695.4	1792.5	1892.8	2010.1	2145.8	2252.3	2309.3	2429.7	2520.7	2536.1	2545.4
27.5°	1624.4	1733.9	1851.2	1985.4	2144.3	2233.7	2306.2	2415.8	2488.3	2477.5	2449.7
30°	1536.5	1670.7	1800.3	1945.3	2122.7	2219.9	2287.7	2388.0	2425.0	2369.5	2320.1
32.5°	1471.7	1598.2	1741.6	1909.8	2098.0	2190.6	2256.9	2335.6	2343.3	2243.0	2159.7
35°	1383.7	1524.1	1686.1	1863.5	2056.3	2139.6	2201.3	2249.2	2212.1	2071.8	1973.0
37.5°	1305.1	1443.9	1616.7	1797.2	1999.3	2081.0	2130.4	2138.1	2047.1	1923.7	1778.7
40°	1218.7	1362.2	1542.6	1732.4	1936.0	2007.0	2037.8	2014.7	1883.6	1740.1	1572.0
42.5°	1132.3	1274.2	1468.6	1663.0	1855.8	1916.0	1928.3	1865.1	1704.6	1536.5	1342.1
45°	1038.2	1186.3	1380.7	1576.6	1763.2	1797.2	1798.7	1707.7	1518.0	1342.1	1161.6
47.5°	961.1	1098.4	1291.2	1487.1	1644.5	1667.6	1658.3	1553.4	1346.7	1149.3	991.9
50°	876.2	1007.3	1198.6	1391.5	1525.7	1531.8	1508.7	1359.1	1157.0	976.5	851.5
52.5°	785.2	917.9	1093.7	1278.8	1399.2	1389.9	1345.2	1184.7	995.0	845.4	749.7
55°	712.7	829.9	995.0	1175.5	1260.3	1234.1	1184.7	1021.2	871.6	745.1	661.8
57.5°	632.5	735.8	897.8	1055.2	1104.5	1079.8	1030.5	877.8	738.9	643.3	587.7
60°	556.9	651.0	792.9	924.0	962.6	936.4	879.3	742.0	641.7	561.5	519.9
62.5°	487.5	569.2	688.0	808.3	823.8	797.5	748.2	637.1	550.7	487.5	456.6
65°	422.7	499.8	595.5	686.5	700.4	672.6	621.7	541.5	469.0	428.9	399.5
67.5°	359.4	421.1	506.0	572.3	580.0	553.8	512.2	447.4	402.6	359.4	337.8
70°	303.9	350.2	416.5	470.5	473.6	448.9	427.3	368.7	334.8	303.9	286.9
72.5°	249.9	282.3	333.2	373.3	374.9	359.4	339.4	302.4	273.0	251.5	234.5
75°	197.5	225.2	256.1	291.6	290.0	277.7	262.2	239.1	214.4	200.5	192.8
77.5°	151.2	168.1	192.8	216.0	216.0	209.8	200.5	183.6	168.1	154.3	146.6
80°	108.0	118.8	138.8	146.6	149.6	148.1	140.4	128.0	121.9	111.1	108.0
82.5°	69.4	77.1	86.4	94.1	98.7	95.6	94.1	87.9	78.7	75.6	72.5
85°	40.1	43.2	47.8	52.4	54.0	52.4	55.5	50.9	46.3	46.3	44.7
87.5°	17.0	18.5	21.6	21.6	23.1	23.1	21.6	23.1	23.1	21.6	20.1
90°	0.5	1.8	3.1	4.4	5.7	6.3	6.8	7.7	8.6	9.6	10.5
92.5°	13.1	12.6	12.2	11.7	11.2	11.0	11.2	11.5	11.9	12.2	12.6
95°	34.1	30.3	26.4	22.6	18.7	16.8	17.2	18.0	18.9	19.7	20.5
97.5°	61.4	51.8	42.3	32.7	23.2	18.4	19.3	21.2	23.1	24.9	26.8
100°	93.0	77.0	61.0	45.0	29.0	21.0	22.0	24.0	25.9	27.9	29.9
102.5°	127.6	127.4	127.2	126.9	126.7	126.6	116.0	94.7	73.5	52.2	31.0
105°	159.6	163.1	166.6	170.1	173.6	175.4	159.5	127.6	95.7	63.9	32.0
107.5°	196.9	199.8	202.8	205.7	208.6	210.1	190.4	151.1	111.8	72.4	33.1
110°	232.6	235.1	237.5	240.0	242.5	243.7	226.8	193.1	159.4	125.6	91.9

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	266.3	268.4	270.5	272.6	274.7	275.7	274.7	272.7	270.8	268.8	266.8
115°	302.0	304.0	306.0	307.9	309.9	310.9	312.4	315.3	318.2	321.1	324.0
117.5°	333.0	335.3	337.7	340.0	342.3	343.5	344.5	346.5	348.4	350.4	352.4
120°	367.6	369.4	371.1	372.9	374.6	375.5	376.5	378.6	380.7	382.8	384.9
122.5°	397.0	398.9	400.7	402.6	404.5	405.4	406.6	408.9	411.2	413.6	415.9
125°	427.0	428.5	430.0	431.5	433.0	433.8	434.9	437.1	439.4	441.6	443.8
127.5°	454.3	455.9	457.5	459.2	460.8	461.6	462.5	464.2	466.0	467.7	469.5
130°	480.0	481.9	483.7	485.6	487.5	488.4	489.0	490.3	491.6	492.9	494.2
132.5°	506.3	507.8	509.3	510.8	512.3	513.1	513.7	515.0	516.3	517.6	518.9
135°	528.3	530.2	532.0	533.9	535.8	536.7	537.2	538.3	539.3	540.4	541.4
137.5°	551.4	552.8	554.2	555.6	557.0	557.7	558.3	559.5	560.6	561.8	563.0
140°	574.0	574.9	575.9	576.8	577.7	578.2	578.8	580.1	581.4	582.7	584.0
142.5°	592.9	593.7	594.5	595.4	596.2	596.6	597.4	598.9	600.4	601.9	603.4
145°	612.9	612.8	612.6	612.5	612.4	612.3	613.3	615.3	617.3	619.3	621.3
147.5°	630.2	629.8	629.5	629.1	628.8	628.6	629.6	631.6	633.5	635.5	637.5
150°	647.0	646.2	645.4	644.5	643.7	643.3	644.2	646.1	648.0	649.8	651.7
152.5°	661.2	660.3	659.3	658.4	657.5	657.0	657.9	659.6	661.4	663.1	664.9
155°	674.8	673.8	672.7	671.7	670.6	670.1	670.8	672.2	673.6	675.0	676.4
157.5°	685.9	685.0	684.0	683.1	682.2	681.7	682.2	683.3	684.3	685.4	686.4
160°	695.3	694.6	693.9	693.2	692.5	692.2	692.5	693.2	693.9	694.6	695.3
162.5°	703.7	703.0	702.3	701.6	700.9	700.6	700.9	701.5	702.0	702.6	703.2
165°	711.1	710.4	709.7	709.0	708.3	707.9	708.1	708.4	708.8	709.1	709.5
167.5°	716.8	716.1	715.4	714.7	714.0	713.7	713.9	714.2	714.6	714.9	715.3
170°	721.6	720.9	720.2	719.5	718.8	718.4	718.5	718.8	719.0	719.3	719.5
172.5°	724.7	724.0	723.3	722.6	721.9	721.6	721.7	721.9	722.2	722.4	722.6
175°	727.4	726.6	725.8	724.9	724.1	723.7	723.8	724.0	724.3	724.5	724.7
177.5°	728.4	727.6	726.8	725.9	725.1	724.7	724.8	724.9	725.0	725.2	725.3
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2085.7	2087.2	2090.3	2105.7	2113.4	2115.0	2108.8	2122.7	2127.3	2122.7	2119.6
5°	2184.4	2193.6	2212.1	2232.2	2230.7	2232.2	2241.5	2250.7	2253.8	2241.5	2246.1
7.5°	2270.8	2289.3	2309.3	2340.2	2340.2	2355.6	2361.8	2369.5	2388.0	2378.8	2375.7
10°	2369.5	2394.2	2431.2	2480.6	2482.1	2497.5	2513.0	2537.6	2545.4	2539.2	2542.3
12.5°	2492.9	2540.7	2543.8	2597.8	2622.5	2625.6	2650.3	2645.6	2661.1	2661.1	2687.3
15°	2546.9	2620.9	2662.6	2715.0	2730.5	2712.0	2732.0	2753.6	2755.2	2755.2	2753.6
17.5°	2644.1	2673.4	2715.0	2742.8	2749.0	2749.0	2750.5	2759.8	2753.6	2741.3	2750.5
20°	2664.1	2676.5	2691.9	2688.8	2691.9	2676.5	2661.1	2645.6	2647.2	2639.5	2662.6
22.5°	2627.1	2624.0	2588.6	2565.4	2565.4	2534.6	2505.2	2491.4	2477.5	2482.1	2489.8
25°	2534.6	2486.7	2443.5	2409.6	2401.9	2352.5	2312.4	2300.1	2276.9	2295.4	2298.5
27.5°	2386.5	2332.5	2263.1	2233.7	2193.6	2173.6	2145.8	2108.8	2061.0	2088.7	2084.1
30°	2227.6	2147.4	2090.3	2019.3	1956.1	1951.4	1899.0	1837.3	1812.6	1812.6	1826.5
32.5°	2050.2	1943.7	1860.4	1760.2	1698.4	1672.2	1609.0	1547.3	1561.2	1514.9	1531.8
35°	1843.5	1703.1	1598.2	1501.0	1454.7	1423.9	1342.1	1308.2	1271.1	1249.5	1289.6
37.5°	1646.0	1484.0	1349.8	1243.4	1226.4	1170.9	1115.3	1093.7	1072.1	1081.4	1079.8
40°	1405.3	1261.9	1141.6	1058.3	1028.9	1002.7	965.7	939.5	925.6	933.3	934.8
42.5°	1187.8	1067.5	978.0	919.4	894.7	876.2	857.7	836.1	831.5	831.5	837.7
45°	1019.7	921.0	860.8	813.0	799.1	785.2	771.3	762.1	759.0	752.8	757.4
47.5°	885.5	806.8	769.8	734.3	718.9	715.8	703.4	698.8	692.6	691.1	692.6
50°	772.9	723.5	689.6	669.5	658.7	654.1	647.9	638.7	635.6	643.3	640.2
52.5°	694.2	647.9	629.4	609.3	603.2	597.0	587.7	589.3	587.7	584.7	584.7
55°	615.5	586.2	567.7	552.3	550.7	544.6	536.8	533.8	532.2	529.1	533.8
57.5°	552.3	529.1	512.2	498.3	492.1	492.1	484.4	478.2	478.2	476.7	478.2
60°	489.0	465.9	455.1	441.2	436.6	435.0	430.4	427.3	422.7	422.7	422.7
62.5°	430.4	411.9	399.5	387.2	388.7	381.0	374.9	371.8	371.8	373.3	373.3
65°	374.9	362.5	347.1	336.3	333.2	331.7	328.6	327.0	322.4	325.5	325.5
67.5°	324.0	307.0	297.7	293.1	288.5	286.9	283.8	280.8	279.2	277.7	280.8
70°	273.0	259.2	251.5	248.4	243.7	242.2	240.7	236.0	237.6	239.1	240.7
72.5°	226.8	214.4	212.9	203.6	203.6	203.6	197.5	200.5	199.0	195.9	199.0
75°	178.9	172.8	169.7	165.1	166.6	165.1	163.5	158.9	158.9	160.4	162.0
77.5°	141.9	135.8	134.2	129.6	126.5	129.6	126.5	125.0	125.0	126.5	126.5
80°	104.9	101.8	97.2	97.2	97.2	95.6	95.6	95.6	94.1	92.6	94.1
82.5°	69.4	69.4	67.9	66.3	67.9	64.8	66.3	66.3	66.3	66.3	66.3
85°	44.7	43.2	43.2	41.7	41.7	41.7	43.2	40.1	40.1	41.7	41.7
87.5°	20.1	20.1	20.1	21.6	20.1	20.1	20.1	21.6	20.1	20.1	20.1
90°	11.1	11.7	12.2	12.8	13.1	13.2	13.5	13.7	14.0	14.2	14.0
92.5°	12.8	13.1	13.3	13.6	13.7	13.8	13.9	14.0	14.1	14.2	14.1
95°	21.1	21.7	22.2	22.8	23.1	23.0	22.9	22.8	22.7	22.6	22.7
97.5°	27.2	27.5	27.9	28.2	28.4	28.5	28.6	28.7	28.8	28.9	28.8
100°	30.8	31.8	32.7	33.6	34.1	34.2	34.5	34.7	35.0	35.2	35.0
102.5°	32.3	33.6	34.9	36.2	36.8	37.0	37.3	37.6	38.0	38.3	38.0
105°	33.3	34.6	35.9	37.2	37.8	38.0	38.5	39.0	39.4	39.9	39.4
107.5°	34.4	35.7	37.0	38.3	38.9	39.1	39.6	40.1	40.5	41.0	40.5
110°	80.2	68.6	56.9	45.2	39.4	39.6	40.1	40.6	41.0	41.5	41.0

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	216.5	166.2	115.9	65.6	40.4	40.6	40.9	41.3	41.6	42.0	41.6
115°	270.0	216.0	161.9	107.9	80.9	76.7	68.3	59.9	51.5	43.1	51.5
117.5°	335.7	319.0	302.3	285.6	277.3	262.0	231.4	200.9	170.3	139.7	170.3
120°	386.3	387.7	389.1	390.5	391.2	383.3	367.6	351.9	336.1	320.4	336.1
122.5°	416.6	417.3	418.0	418.7	419.1	419.2	419.3	419.4	419.5	419.6	419.5
125°	444.6	445.4	446.2	447.0	447.4	447.6	447.9	448.3	448.6	449.0	448.6
127.5°	470.7	471.8	473.0	474.1	474.7	474.8	474.9	475.0	475.2	475.3	475.2
130°	495.5	496.8	498.1	499.4	500.0	499.9	499.8	499.7	499.5	499.4	499.5
132.5°	519.9	521.0	522.0	523.1	523.6	523.5	523.4	523.3	523.2	523.1	523.2
135°	542.6	543.8	544.9	546.1	546.7	546.6	546.3	546.1	545.8	545.6	545.8
137.5°	564.2	565.3	566.5	567.6	568.2	568.0	567.7	567.4	567.0	566.7	567.0
140°	585.0	586.1	587.1	588.2	588.7	588.4	587.8	587.3	586.7	586.1	586.7
142.5°	604.3	605.3	606.2	607.1	607.6	607.3	606.7	606.2	605.6	605.0	605.6
145°	622.1	622.9	623.7	624.5	624.9	624.6	624.0	623.5	622.9	622.3	622.9
147.5°	638.1	638.7	639.3	639.9	640.2	640.0	639.5	639.0	638.6	638.1	638.6
150°	652.4	653.1	653.8	654.5	654.9	654.6	654.0	653.5	652.9	652.3	652.9
152.5°	665.6	666.3	667.0	667.7	668.0	667.6	666.8	665.9	665.1	664.3	665.1
155°	677.1	677.8	678.5	679.2	679.6	679.1	678.2	677.3	676.3	675.4	676.3
157.5°	687.2	688.0	688.9	689.7	690.1	689.6	688.7	687.8	686.8	685.9	686.8
160°	696.0	696.7	697.4	698.1	698.5	698.1	697.3	696.4	695.6	694.8	695.6
162.5°	704.0	704.8	705.7	706.5	706.9	706.4	705.3	704.2	703.2	702.1	703.2
165°	710.3	711.1	712.0	712.8	713.2	712.8	712.0	711.1	710.3	709.5	710.3
167.5°	716.1	716.9	717.7	718.5	718.9	718.4	717.3	716.3	715.2	714.2	715.2
170°	720.3	721.1	722.0	722.8	723.2	722.7	721.6	720.5	719.5	718.4	719.5
172.5°	723.4	724.2	725.1	725.9	726.3	725.8	724.7	723.7	722.6	721.6	722.6
175°	725.5	726.3	727.2	728.0	728.4	727.8	726.7	725.5	724.4	723.2	724.4
177.5°	726.1	726.9	727.7	728.5	728.9	728.4	727.3	726.3	725.2	724.2	725.2
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2127.3	2116.5	2107.2	2108.8	2116.5	2110.3	2094.9	2074.9	2067.1	2057.9	2067.1
5°	2255.3	2246.1	2227.6	2229.1	2224.5	2218.3	2193.6	2162.8	2162.8	2138.1	2135.0
7.5°	2381.8	2368.0	2355.6	2352.5	2335.6	2323.2	2301.6	2258.4	2241.5	2212.1	2195.2
10°	2523.8	2513.0	2499.1	2482.1	2472.9	2451.3	2415.8	2352.5	2321.7	2281.6	2252.3
12.5°	2667.2	2665.7	2634.8	2600.9	2599.3	2565.4	2540.7	2455.9	2414.2	2360.2	2290.8
15°	2758.2	2750.5	2733.6	2716.6	2721.2	2684.2	2628.7	2528.4	2500.6	2435.8	2361.8
17.5°	2756.7	2756.7	2752.1	2749.0	2744.4	2733.6	2702.7	2636.4	2591.6	2509.9	2440.5
20°	2668.8	2688.8	2693.5	2691.9	2707.3	2715.0	2713.5	2671.9	2636.4	2563.9	2492.9
22.5°	2492.9	2539.2	2559.2	2571.6	2604.0	2620.9	2661.1	2645.6	2636.4	2582.4	2522.2
25°	2329.4	2344.8	2405.0	2408.1	2452.8	2494.5	2534.6	2560.8	2594.7	2574.7	2523.8
27.5°	2118.0	2153.5	2196.7	2229.1	2238.4	2323.2	2389.6	2438.9	2516.0	2522.2	2505.2
30°	1878.9	1895.9	1966.9	2010.1	2059.4	2121.1	2216.8	2301.6	2371.0	2434.3	2455.9
32.5°	1587.4	1656.8	1698.4	1750.9	1794.1	1903.6	2020.9	2130.4	2210.6	2317.0	2363.3
35°	1320.5	1374.5	1445.5	1467.1	1545.7	1638.3	1791.0	1931.4	2053.3	2161.2	2255.3
37.5°	1099.9	1143.1	1218.7	1252.6	1298.9	1417.7	1545.7	1720.0	1866.6	1999.3	2116.5
40°	948.7	981.1	1038.2	1049.0	1087.6	1195.5	1298.9	1462.4	1656.8	1835.7	1963.8
42.5°	845.4	860.8	899.4	913.2	937.9	1010.4	1103.0	1257.3	1437.7	1622.9	1803.3
45°	771.3	782.1	805.3	817.6	848.5	880.8	956.4	1079.8	1221.8	1408.4	1602.8
47.5°	705.0	718.9	728.1	735.8	752.8	788.3	837.7	928.7	1064.4	1235.7	1423.9
50°	649.5	654.1	671.0	672.6	683.4	706.5	752.8	808.3	916.3	1055.2	1237.2
52.5°	593.9	598.5	609.3	620.1	624.8	643.3	674.1	720.4	800.6	910.2	1072.1
55°	538.4	544.6	555.4	563.1	567.7	583.1	601.6	646.4	709.6	786.7	919.4
57.5°	482.8	496.7	499.8	504.4	512.2	529.1	546.1	572.3	621.7	692.6	789.8
60°	430.4	435.0	445.8	450.5	458.2	467.4	489.0	509.1	544.6	600.1	688.0
62.5°	376.4	387.2	391.8	396.5	402.6	413.4	427.3	448.9	479.8	524.5	593.9
65°	330.1	331.7	340.9	347.1	353.3	361.0	374.9	394.9	413.4	455.1	506.0
67.5°	285.4	288.5	291.6	297.7	305.4	313.2	325.5	336.3	359.4	387.2	427.3
70°	242.2	242.2	249.9	254.5	253.0	262.2	271.5	283.8	300.8	327.0	359.4
72.5°	203.6	202.1	208.3	209.8	212.9	219.1	225.2	237.6	246.8	266.9	291.6
75°	162.0	165.1	168.1	168.1	172.8	177.4	183.6	189.7	200.5	212.9	231.4
77.5°	128.0	128.0	131.1	132.7	137.3	135.8	141.9	148.1	155.8	166.6	180.5
80°	94.1	97.2	97.2	97.2	98.7	100.3	106.4	111.1	115.7	123.4	129.6
82.5°	66.3	66.3	69.4	69.4	69.4	72.5	72.5	74.0	77.1	81.8	86.4
85°	41.7	41.7	41.7	43.2	41.7	43.2	46.3	44.7	46.3	49.4	49.4
87.5°	20.1	20.1	20.1	20.1	20.1	21.6	20.1	21.6	23.1	23.1	23.1
90°	13.7	13.5	13.2	13.1	12.8	12.2	11.7	11.1	10.5	9.6	8.6
92.5°	14.0	13.9	13.8	13.7	13.6	13.3	13.1	12.8	12.6	12.2	11.9
95°	22.8	22.9	23.0	23.1	22.8	22.2	21.7	21.1	20.5	19.7	18.9
97.5°	28.7	28.6	28.5	28.4	28.2	27.9	27.5	27.2	26.8	24.9	23.1
100°	34.7	34.5	34.2	34.1	33.6	32.7	31.8	30.8	29.9	27.9	25.9
102.5°	37.6	37.3	37.0	36.8	36.2	34.9	33.6	32.3	31.0	52.2	73.5
105°	39.0	38.5	38.0	37.8	37.2	35.9	34.6	33.3	32.0	63.9	95.7
107.5°	40.1	39.6	39.1	38.9	38.3	37.0	35.7	34.4	33.1	72.4	111.8
110°	40.6	40.1	39.6	39.4	45.2	56.9	68.6	80.2	91.9	125.6	159.4

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	41.3	40.9	40.6	40.4	65.6	115.9	166.2	216.5	266.8	268.8	270.8
115°	59.9	68.3	76.7	80.9	107.9	161.9	216.0	270.0	324.0	321.1	318.2
117.5°	200.9	231.4	262.0	277.3	285.6	302.3	319.0	335.7	352.4	350.4	348.4
120°	351.9	367.6	383.3	391.2	390.5	389.1	387.7	386.3	384.9	382.8	380.7
122.5°	419.4	419.3	419.2	419.1	418.7	418.0	417.3	416.6	415.9	413.6	411.2
125°	448.3	447.9	447.6	447.4	447.0	446.2	445.4	444.6	443.8	441.6	439.4
127.5°	475.0	474.9	474.8	474.7	474.1	473.0	471.8	470.7	469.5	467.7	466.0
130°	499.7	499.8	499.9	500.0	499.4	498.1	496.8	495.5	494.2	492.9	491.6
132.5°	523.3	523.4	523.5	523.6	523.1	522.0	521.0	519.9	518.9	517.6	516.3
135°	546.1	546.3	546.6	546.7	546.1	544.9	543.8	542.6	541.4	540.4	539.3
137.5°	567.4	567.7	568.0	568.2	567.6	566.5	565.3	564.2	563.0	561.8	560.6
140°	587.3	587.8	588.4	588.7	588.2	587.1	586.1	585.0	584.0	582.7	581.4
142.5°	606.2	606.7	607.3	607.6	607.1	606.2	605.3	604.3	603.4	601.9	600.4
145°	623.5	624.0	624.6	624.9	624.5	623.7	622.9	622.1	621.3	619.3	617.3
147.5°	639.0	639.5	640.0	640.2	639.9	639.3	638.7	638.1	637.5	635.5	633.5
150°	653.5	654.0	654.6	654.9	654.5	653.8	653.1	652.4	651.7	649.8	648.0
152.5°	665.9	666.8	667.6	668.0	667.7	667.0	666.3	665.6	664.9	663.1	661.4
155°	677.3	678.2	679.1	679.6	679.2	678.5	677.8	677.1	676.4	675.0	673.6
157.5°	687.8	688.7	689.6	690.1	689.7	688.9	688.0	687.2	686.4	685.4	684.3
160°	696.4	697.3	698.1	698.5	698.1	697.4	696.7	696.0	695.3	694.6	693.9
162.5°	704.2	705.3	706.4	706.9	706.5	705.7	704.8	704.0	703.2	702.6	702.0
165°	711.1	712.0	712.8	713.2	712.8	712.0	711.1	710.3	709.5	709.1	708.8
167.5°	716.3	717.3	718.4	718.9	718.5	717.7	716.9	716.1	715.3	714.9	714.6
170°	720.5	721.6	722.7	723.2	722.8	722.0	721.1	720.3	719.5	719.3	719.0
172.5°	723.7	724.7	725.8	726.3	725.9	725.1	724.2	723.4	722.6	722.4	722.2
175°	725.5	726.7	727.8	728.4	728.0	727.2	726.3	725.5	724.7	724.5	724.3
177.5°	726.3	727.3	728.4	728.9	728.5	727.7	726.9	726.1	725.3	725.2	725.0
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2059.4	2051.7	2047.1	2050.2	2040.9	2017.8	2017.8	2025.5	2016.2	2007.0	1993.1
5°	2116.5	2101.1	2091.8	2090.3	2068.7	2031.7	2023.9	2016.2	1996.2	1974.6	1951.4
7.5°	2172.0	2144.3	2128.8	2118.0	2087.2	2039.4	2019.3	2002.3	1970.0	1937.6	1908.2
10°	2218.3	2178.2	2159.7	2142.7	2102.6	2042.5	2010.1	1979.2	1937.6	1895.9	1858.9
12.5°	2255.3	2209.1	2185.9	2161.2	2111.9	2033.2	1993.1	1943.7	1902.1	1846.5	1809.5
15°	2317.0	2221.4	2199.8	2176.7	2125.8	2017.8	1968.4	1912.9	1855.8	1781.8	1741.6
17.5°	2366.4	2238.4	2236.8	2187.5	2121.1	2011.6	1936.0	1863.5	1801.8	1727.8	1664.5
20°	2395.7	2264.6	2239.9	2189.0	2105.7	1970.0	1891.3	1811.1	1744.7	1655.3	1592.0
22.5°	2420.4	2301.6	2236.8	2175.1	2073.3	1956.1	1840.4	1764.8	1673.8	1576.6	1516.4
25°	2429.7	2309.3	2241.5	2170.5	2050.2	1916.0	1784.8	1703.1	1601.3	1513.3	1431.6
27.5°	2431.2	2307.8	2224.5	2150.4	2017.8	1863.5	1729.3	1642.9	1530.3	1428.5	1346.7
30°	2415.8	2290.8	2215.2	2135.0	1986.9	1815.7	1661.4	1565.8	1445.5	1343.6	1258.8
32.5°	2369.5	2256.9	2195.2	2107.2	1946.8	1749.4	1596.6	1490.2	1363.7	1263.4	1181.7
35°	2292.4	2215.2	2147.4	2065.6	1894.4	1687.6	1531.8	1406.9	1278.8	1183.2	1106.1
37.5°	2196.7	2155.1	2091.8	2011.6	1834.2	1632.1	1459.3	1320.5	1192.5	1099.9	1024.3
40°	2067.1	2077.9	2016.2	1943.7	1763.2	1556.5	1365.2	1232.6	1112.2	1025.9	951.8
42.5°	1926.8	1971.5	1936.0	1866.6	1684.6	1473.2	1295.8	1149.3	1032.0	942.6	880.8
45°	1775.6	1852.7	1831.1	1780.2	1602.8	1385.3	1197.1	1055.2	951.8	865.4	811.4
47.5°	1610.5	1720.0	1720.0	1683.0	1511.8	1297.4	1112.2	967.2	865.4	803.7	751.3
50°	1442.4	1565.8	1585.8	1561.2	1410.0	1197.1	1008.9	877.8	789.8	729.7	691.1
52.5°	1266.5	1410.0	1447.0	1434.7	1302.0	1101.4	924.0	796.0	715.8	663.3	629.4
55°	1098.4	1265.0	1305.1	1309.7	1186.3	996.5	829.9	717.3	640.2	604.7	575.4
57.5°	939.5	1099.9	1144.6	1152.4	1069.1	900.9	742.0	643.3	573.9	544.6	521.4
60°	803.7	937.9	996.5	1013.5	941.0	789.8	660.3	564.6	512.2	484.4	462.8
62.5°	692.6	800.6	862.3	867.0	834.6	692.6	575.4	495.2	450.5	425.8	415.0
65°	584.7	681.8	718.9	737.4	711.2	600.1	496.7	430.4	394.9	373.3	362.5
67.5°	498.3	560.0	590.8	615.5	589.3	506.0	422.7	368.7	342.5	320.9	314.7
70°	408.8	459.7	482.8	507.5	484.4	421.1	361.0	311.6	288.5	271.5	263.8
72.5°	327.0	367.1	388.7	404.2	390.3	337.8	288.5	254.5	237.6	225.2	220.6
75°	259.2	286.9	299.3	310.1	303.9	263.8	232.9	205.2	189.7	178.9	175.9
77.5°	197.5	217.5	231.4	234.5	226.8	200.5	174.3	157.3	145.0	138.8	135.8
80°	140.4	152.7	160.4	165.1	157.3	146.6	128.0	115.7	104.9	97.2	95.6
82.5°	94.1	100.3	106.4	104.9	101.8	92.6	81.8	75.6	71.0	64.8	64.8
85°	54.0	55.5	58.6	60.2	58.6	52.4	46.3	43.2	40.1	35.5	35.5
87.5°	23.1	24.7	24.7	26.2	23.1	23.1	20.1	17.0	17.0	15.4	13.9
90°	7.7	6.8	6.3	5.7	4.4	3.1	1.8	0.5	1.8	3.1	4.4
92.5°	11.5	11.2	11.0	11.2	11.7	12.2	12.6	13.1	12.6	12.2	11.7
95°	18.0	17.2	16.8	18.7	22.6	26.4	30.3	34.1	30.3	26.4	22.6
97.5°	21.2	19.3	18.4	23.2	32.7	42.3	51.8	61.4	51.8	42.3	32.7
100°	24.0	22.0	21.0	29.0	45.0	61.0	77.0	93.0	77.0	61.0	45.0
102.5°	94.7	116.0	126.6	126.7	126.9	127.2	127.4	127.6	127.4	127.2	126.9
105°	127.6	159.5	175.4	173.6	170.1	166.6	163.1	159.6	163.1	166.6	170.1
107.5°	151.1	190.4	210.1	208.6	205.7	202.8	199.8	196.9	199.8	202.8	205.7
110°	193.1	226.8	243.7	242.5	240.0	237.5	235.1	232.6	235.1	237.5	240.0

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	272.7	274.7	275.7	274.7	272.6	270.5	268.4	266.3	268.4	270.5	272.6
115°	315.3	312.4	310.9	309.9	307.9	306.0	304.0	302.0	304.0	306.0	307.9
117.5°	346.5	344.5	343.5	342.3	340.0	337.7	335.3	333.0	335.3	337.7	340.0
120°	378.6	376.5	375.5	374.6	372.9	371.1	369.4	367.6	369.4	371.1	372.9
122.5°	408.9	406.6	405.4	404.5	402.6	400.7	398.9	397.0	398.9	400.7	402.6
125°	437.1	434.9	433.8	433.0	431.5	430.0	428.5	427.0	428.5	430.0	431.5
127.5°	464.2	462.5	461.6	460.8	459.2	457.5	455.9	454.3	455.9	457.5	459.2
130°	490.3	489.0	488.4	487.5	485.6	483.7	481.9	480.0	481.9	483.7	485.6
132.5°	515.0	513.7	513.1	512.3	510.8	509.3	507.8	506.3	507.8	509.3	510.8
135°	538.3	537.2	536.7	535.8	533.9	532.0	530.2	528.3	530.2	532.0	533.9
137.5°	559.5	558.3	557.7	557.0	555.6	554.2	552.8	551.4	552.8	554.2	555.6
140°	580.1	578.8	578.2	577.7	576.8	575.9	574.9	574.0	574.9	575.9	576.8
142.5°	598.9	597.4	596.6	596.2	595.4	594.5	593.7	592.9	593.7	594.5	595.4
145°	615.3	613.3	612.3	612.4	612.5	612.6	612.8	612.9	612.8	612.6	612.5
147.5°	631.6	629.6	628.6	628.8	629.1	629.5	629.8	630.2	629.8	629.5	629.1
150°	646.1	644.2	643.3	643.7	644.5	645.4	646.2	647.0	646.2	645.4	644.5
152.5°	659.6	657.9	657.0	657.5	658.4	659.3	660.3	661.2	660.3	659.3	658.4
155°	672.2	670.8	670.1	670.6	671.7	672.7	673.8	674.8	673.8	672.7	671.7
157.5°	683.3	682.2	681.7	682.2	683.1	684.0	685.0	685.9	685.0	684.0	683.1
160°	693.2	692.5	692.2	692.5	693.2	693.9	694.6	695.3	694.6	693.9	693.2
162.5°	701.5	700.9	700.6	700.9	701.6	702.3	703.0	703.7	703.0	702.3	701.6
165°	708.4	708.1	707.9	708.3	709.0	709.7	710.4	711.1	710.4	709.7	709.0
167.5°	714.2	713.9	713.7	714.0	714.7	715.4	716.1	716.8	716.1	715.4	714.7
170°	718.8	718.5	718.4	718.8	719.5	720.2	720.9	721.6	720.9	720.2	719.5
172.5°	721.9	721.7	721.6	721.9	722.6	723.3	724.0	724.7	724.0	723.3	722.6
175°	724.0	723.8	723.7	724.1	724.9	725.8	726.6	727.4	726.6	725.8	724.9
177.5°	724.9	724.8	724.7	725.1	725.9	726.8	727.6	728.4	727.6	726.8	725.9
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1985.4	1993.1	1991.5	1976.1	1959.2	1945.3	1919.0	1922.1	1912.9	1914.4	1923.7
5°	1936.0	1936.0	1929.8	1908.2	1880.5	1865.1	1835.7	1828.0	1809.5	1808.0	1806.4
7.5°	1883.6	1875.9	1868.1	1837.3	1803.3	1778.7	1738.6	1729.3	1710.8	1698.4	1692.3
10°	1821.9	1811.1	1795.6	1760.2	1718.5	1687.6	1646.0	1633.7	1598.2	1582.7	1573.5
12.5°	1754.0	1747.8	1723.1	1693.8	1625.9	1592.0	1531.8	1544.2	1508.7	1477.9	1473.2
15°	1686.1	1663.0	1649.1	1601.3	1519.5	1504.1	1456.3	1431.6	1399.2	1374.5	1374.5
17.5°	1619.8	1584.3	1553.4	1502.5	1442.4	1399.2	1363.7	1351.4	1311.2	1286.6	1281.9
20°	1531.8	1491.7	1484.0	1411.5	1369.9	1322.0	1288.1	1257.3	1227.9	1217.1	1209.4
22.5°	1448.5	1402.3	1389.9	1328.2	1286.6	1238.7	1204.8	1183.2	1161.6	1153.9	1140.0
25°	1359.1	1331.3	1312.8	1246.5	1200.2	1155.4	1132.3	1116.9	1096.8	1095.3	1086.0
27.5°	1272.7	1246.5	1227.9	1164.7	1130.8	1089.1	1070.6	1053.6	1042.8	1038.2	1033.6
30°	1198.6	1169.3	1147.7	1101.4	1059.8	1025.9	1010.4	999.6	993.5	985.7	984.2
32.5°	1116.9	1099.9	1070.6	1035.1	1002.7	970.3	961.1	953.4	944.1	941.0	939.5
35°	1047.5	1024.3	1005.8	965.7	951.8	924.0	913.2	907.1	894.7	891.6	888.6
37.5°	979.6	958.0	937.9	913.2	887.0	871.6	865.4	856.2	850.0	851.5	848.5
40°	911.7	894.7	879.3	853.1	837.7	829.9	817.6	808.3	805.3	806.8	805.3
42.5°	845.4	829.9	820.7	800.6	785.2	777.5	769.8	760.5	765.1	765.1	769.8
45°	785.2	771.3	765.1	749.7	740.5	728.1	720.4	718.9	725.0	723.5	723.5
47.5°	723.5	718.9	711.2	697.3	684.9	677.2	675.7	675.7	681.8	684.9	683.4
50°	675.7	666.4	657.2	646.4	637.1	634.0	629.4	632.5	638.7	638.7	641.7
52.5°	615.5	609.3	606.3	597.0	590.8	590.8	590.8	592.4	597.0	601.6	600.1
55°	563.1	558.4	555.4	550.7	543.0	544.6	543.0	546.1	550.7	555.4	558.4
57.5°	507.5	506.0	502.9	495.2	495.2	493.6	498.3	499.8	507.5	510.6	515.2
60°	458.2	453.5	453.5	447.4	447.4	447.4	452.0	456.6	462.8	464.3	467.4
62.5°	405.7	405.7	404.2	399.5	399.5	404.2	405.7	411.9	415.0	415.0	419.6
65°	356.4	354.8	353.3	354.8	356.4	356.4	361.0	364.1	367.1	368.7	370.2
67.5°	307.0	305.4	308.5	307.0	310.1	316.2	314.7	319.3	324.0	324.0	325.5
70°	260.7	263.8	262.2	265.3	263.8	266.9	271.5	273.0	273.0	274.6	279.2
72.5°	217.5	217.5	217.5	216.0	217.5	220.6	223.7	225.2	228.3	229.9	234.5
75°	175.9	175.9	172.8	175.9	175.9	178.9	182.0	182.0	182.0	185.1	189.7
77.5°	132.7	134.2	132.7	135.8	135.8	137.3	140.4	138.8	141.9	143.5	145.0
80°	97.2	95.6	95.6	95.6	97.2	97.2	100.3	101.8	101.8	106.4	103.4
82.5°	61.7	63.2	61.7	63.2	63.2	64.8	63.2	64.8	66.3	69.4	67.9
85°	35.5	33.9	33.9	35.5	33.9	33.9	35.5	33.9	35.5	33.9	35.5
87.5°	13.9	12.3	12.3	12.3	12.3	10.8	10.8	9.3	9.3	9.3	7.7
90°	5.7	6.3	6.8	7.7	8.6	9.6	10.5	11.1	11.7	12.2	12.8
92.5°	11.2	11.0	11.2	11.5	11.9	12.2	12.6	12.8	13.1	13.3	13.6
95°	18.7	16.8	17.2	18.0	18.9	19.7	20.5	21.1	21.7	22.2	22.8
97.5°	23.2	18.4	19.3	21.2	23.1	24.9	26.8	27.2	27.5	27.9	28.2
100°	29.0	21.0	22.0	24.0	25.9	27.9	29.9	30.8	31.8	32.7	33.6
102.5°	126.7	126.6	116.0	94.7	73.5	52.2	31.0	32.3	33.6	34.9	36.2
105°	173.6	175.4	159.5	127.6	95.7	63.9	32.0	33.3	34.6	35.9	37.2
107.5°	208.6	210.1	190.4	151.1	111.8	72.4	33.1	34.4	35.7	37.0	38.3
110°	242.5	243.7	226.8	193.1	159.4	125.6	91.9	80.2	68.6	56.9	45.2



TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	274.7	275.7	274.7	272.7	270.8	268.8	266.8	216.5	166.2	115.9	65.6
115°	309.9	310.9	312.4	315.3	318.2	321.1	324.0	270.0	216.0	161.9	107.9
117.5°	342.3	343.5	344.5	346.5	348.4	350.4	352.4	335.7	319.0	302.3	285.6
120°	374.6	375.5	376.5	378.6	380.7	382.8	384.9	386.3	387.7	389.1	390.5
122.5°	404.5	405.4	406.6	408.9	411.2	413.6	415.9	416.6	417.3	418.0	418.7
125°	433.0	433.8	434.9	437.1	439.4	441.6	443.8	444.6	445.4	446.2	447.0
127.5°	460.8	461.6	462.5	464.2	466.0	467.7	469.5	470.7	471.8	473.0	474.1
130°	487.5	488.4	489.0	490.3	491.6	492.9	494.2	495.5	496.8	498.1	499.4
132.5°	512.3	513.1	513.7	515.0	516.3	517.6	518.9	519.9	521.0	522.0	523.1
135°	535.8	536.7	537.2	538.3	539.3	540.4	541.4	542.6	543.8	544.9	546.1
137.5°	557.0	557.7	558.3	559.5	560.6	561.8	563.0	564.2	565.3	566.5	567.6
140°	577.7	578.2	578.8	580.1	581.4	582.7	584.0	585.0	586.1	587.1	588.2
142.5°	596.2	596.6	597.4	598.9	600.4	601.9	603.4	604.3	605.3	606.2	607.1
145°	612.4	612.3	613.3	615.3	617.3	619.3	621.3	622.1	622.9	623.7	624.5
147.5°	628.8	628.6	629.6	631.6	633.5	635.5	637.5	638.1	638.7	639.3	639.9
150°	643.7	643.3	644.2	646.1	648.0	649.8	651.7	652.4	653.1	653.8	654.5
152.5°	657.5	657.0	657.9	659.6	661.4	663.1	664.9	665.6	666.3	667.0	667.7
155°	670.6	670.1	670.8	672.2	673.6	675.0	676.4	677.1	677.8	678.5	679.2
157.5°	682.2	681.7	682.2	683.3	684.3	685.4	686.4	687.2	688.0	688.9	689.7
160°	692.5	692.2	692.5	693.2	693.9	694.6	695.3	696.0	696.7	697.4	698.1
162.5°	700.9	700.6	700.9	701.5	702.0	702.6	703.2	704.0	704.8	705.7	706.5
165°	708.3	707.9	708.1	708.4	708.8	709.1	709.5	710.3	711.1	712.0	712.8
167.5°	714.0	713.7	713.9	714.2	714.6	714.9	715.3	716.1	716.9	717.7	718.5
170°	718.8	718.4	718.5	718.8	719.0	719.3	719.5	720.3	721.1	722.0	722.8
172.5°	721.9	721.6	721.7	721.9	722.2	722.4	722.6	723.4	724.2	725.1	725.9
175°	724.1	723.7	723.8	724.0	724.3	724.5	724.7	725.5	726.3	727.2	728.0
177.5°	725.1	724.7	724.8	724.9	725.0	725.2	725.3	726.1	726.9	727.7	728.5
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1912.9	1917.5	1906.7	1903.6	1906.7	1895.9	1899.0	1902.1	1902.1	1906.7	1909.8
5°	1801.8	1795.6	1784.8	1781.8	1778.7	1783.3	1780.2	1784.8	1786.4	1797.2	1798.7
7.5°	1692.3	1683.0	1673.8	1664.5	1661.4	1653.7	1661.4	1661.4	1672.2	1669.1	1676.9
10°	1562.7	1561.2	1548.8	1544.2	1538.0	1525.7	1542.6	1538.0	1545.7	1559.6	1562.7
12.5°	1467.1	1450.1	1457.8	1436.2	1443.9	1431.6	1433.1	1433.1	1445.5	1447.0	1443.9
15°	1376.0	1362.2	1342.1	1332.8	1328.2	1322.0	1342.1	1343.6	1334.4	1356.0	1348.3
17.5°	1283.5	1283.5	1265.0	1260.3	1248.0	1254.2	1251.1	1252.6	1249.5	1265.0	1272.7
20°	1203.3	1195.5	1189.4	1190.9	1175.5	1172.4	1169.3	1172.4	1183.2	1194.0	1197.1
22.5°	1138.5	1133.8	1118.4	1121.5	1109.2	1113.8	1110.7	1118.4	1120.0	1120.0	1130.8
25°	1076.8	1070.6	1072.1	1066.0	1061.3	1061.3	1056.7	1061.3	1067.5	1070.6	1072.1
27.5°	1030.5	1025.9	1018.1	1013.5	1016.6	1008.9	1015.1	1019.7	1019.7	1016.6	1019.7
30°	974.9	978.0	978.0	962.6	968.8	965.7	970.3	973.4	973.4	974.9	971.9
32.5°	937.9	928.7	927.1	925.6	925.6	919.4	919.4	924.0	925.6	927.1	931.8
35°	888.6	888.6	880.8	885.5	879.3	880.8	879.3	880.8	883.9	879.3	883.9
37.5°	843.8	845.4	842.3	845.4	846.9	843.8	840.7	846.9	843.8	843.8	840.7
40°	805.3	803.7	805.3	805.3	805.3	806.8	803.7	803.7	803.7	800.6	797.5
42.5°	772.9	763.6	766.7	768.2	763.6	763.6	765.1	763.6	768.2	759.0	759.0
45°	726.6	723.5	725.0	725.0	728.1	723.5	726.6	728.1	723.5	722.0	718.9
47.5°	684.9	688.0	684.9	688.0	688.0	691.1	684.9	686.5	688.0	681.8	677.2
50°	643.3	643.3	647.9	646.4	647.9	644.8	644.8	643.3	644.8	641.7	637.1
52.5°	604.7	600.1	607.8	606.3	604.7	603.2	601.6	603.2	600.1	597.0	597.0
55°	556.9	556.9	561.5	563.1	563.1	560.0	556.9	558.4	556.9	555.4	553.8
57.5°	518.3	512.2	515.2	516.8	516.8	512.2	515.2	512.2	512.2	513.7	509.1
60°	469.0	469.0	465.9	470.5	470.5	467.4	467.4	469.0	465.9	464.3	462.8
62.5°	416.5	418.1	422.7	424.2	425.8	422.7	419.6	421.1	421.1	416.5	418.1
65°	371.8	374.9	381.0	379.5	376.4	377.9	374.9	376.4	371.8	373.3	368.7
67.5°	328.6	327.0	328.6	328.6	331.7	330.1	327.0	327.0	325.5	330.1	325.5
70°	282.3	282.3	282.3	282.3	283.8	285.4	282.3	279.2	280.8	277.7	276.1
72.5°	234.5	236.0	234.5	237.6	232.9	236.0	236.0	234.5	232.9	232.9	232.9
75°	189.7	192.8	188.2	189.7	188.2	191.3	189.7	189.7	186.7	185.1	186.7
77.5°	145.0	146.6	143.5	145.0	143.5	145.0	145.0	143.5	143.5	143.5	143.5
80°	103.4	104.9	103.4	101.8	100.3	103.4	100.3	101.8	103.4	101.8	104.9
82.5°	66.3	66.3	64.8	66.3	63.2	63.2	64.8	64.8	63.2	66.3	63.2
85°	32.4	32.4	35.5	32.4	30.9	30.9	30.9	32.4	30.9	33.9	32.4
87.5°	7.7	6.2	7.7	7.7	6.2	6.2	7.7	6.2	7.7	9.3	6.2
90°	13.1	13.2	13.5	13.7	14.0	14.2	14.0	13.7	13.5	13.2	13.1
92.5°	13.7	13.8	13.9	14.0	14.1	14.2	14.1	14.0	13.9	13.8	13.7
95°	23.1	23.0	22.9	22.8	22.7	22.6	22.7	22.8	22.9	23.0	23.1
97.5°	28.4	28.5	28.6	28.7	28.8	28.9	28.8	28.7	28.6	28.5	28.4
100°	34.1	34.2	34.5	34.7	35.0	35.2	35.0	34.7	34.5	34.2	34.1
102.5°	36.8	37.0	37.3	37.6	38.0	38.3	38.0	37.6	37.3	37.0	36.8
105°	37.8	38.0	38.5	39.0	39.4	39.9	39.4	39.0	38.5	38.0	37.8
107.5°	38.9	39.1	39.6	40.1	40.5	41.0	40.5	40.1	39.6	39.1	38.9
110°	39.4	39.6	40.1	40.6	41.0	41.5	41.0	40.6	40.1	39.6	39.4

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	40.4	40.6	40.9	41.3	41.6	42.0	41.6	41.3	40.9	40.6	40.4
115°	80.9	76.7	68.3	59.9	51.5	43.1	51.5	59.9	68.3	76.7	80.9
117.5°	277.3	262.0	231.4	200.9	170.3	139.7	170.3	200.9	231.4	262.0	277.3
120°	391.2	383.3	367.6	351.9	336.1	320.4	336.1	351.9	367.6	383.3	391.2
122.5°	419.1	419.2	419.3	419.4	419.5	419.6	419.5	419.4	419.3	419.2	419.1
125°	447.4	447.6	447.9	448.3	448.6	449.0	448.6	448.3	447.9	447.6	447.4
127.5°	474.7	474.8	474.9	475.0	475.2	475.3	475.2	475.0	474.9	474.8	474.7
130°	500.0	499.9	499.8	499.7	499.5	499.4	499.5	499.7	499.8	499.9	500.0
132.5°	523.6	523.5	523.4	523.3	523.2	523.1	523.2	523.3	523.4	523.5	523.6
135°	546.7	546.6	546.3	546.1	545.8	545.6	545.8	546.1	546.3	546.6	546.7
137.5°	568.2	568.0	567.7	567.4	567.0	566.7	567.0	567.4	567.7	568.0	568.2
140°	588.7	588.4	587.8	587.3	586.7	586.1	586.7	587.3	587.8	588.4	588.7
142.5°	607.6	607.3	606.7	606.2	605.6	605.0	605.6	606.2	606.7	607.3	607.6
145°	624.9	624.6	624.0	623.5	622.9	622.3	622.9	623.5	624.0	624.6	624.9
147.5°	640.2	640.0	639.5	639.0	638.6	638.1	638.6	639.0	639.5	640.0	640.2
150°	654.9	654.6	654.0	653.5	652.9	652.3	652.9	653.5	654.0	654.6	654.9
152.5°	668.0	667.6	666.8	665.9	665.1	664.3	665.1	665.9	666.8	667.6	668.0
155°	679.6	679.1	678.2	677.3	676.3	675.4	676.3	677.3	678.2	679.1	679.6
157.5°	690.1	689.6	688.7	687.8	686.8	685.9	686.8	687.8	688.7	689.6	690.1
160°	698.5	698.1	697.3	696.4	695.6	694.8	695.6	696.4	697.3	698.1	698.5
162.5°	706.9	706.4	705.3	704.2	703.2	702.1	703.2	704.2	705.3	706.4	706.9
165°	713.2	712.8	712.0	711.1	710.3	709.5	710.3	711.1	712.0	712.8	713.2
167.5°	718.9	718.4	717.3	716.3	715.2	714.2	715.2	716.3	717.3	718.4	718.9
170°	723.2	722.7	721.6	720.5	719.5	718.4	719.5	720.5	721.6	722.7	723.2
172.5°	726.3	725.8	724.7	723.7	722.6	721.6	722.6	723.7	724.7	725.8	726.3
175°	728.4	727.8	726.7	725.5	724.4	723.2	724.4	725.5	726.7	727.8	728.4
177.5°	728.9	728.4	727.3	726.3	725.2	724.2	725.2	726.3	727.3	728.4	728.9
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1905.2	1917.5	1912.9	1895.9	1916.0	1916.0	1929.8	1929.8	1946.8	1953.0	1962.2
5°	1797.2	1806.4	1814.1	1806.4	1820.3	1841.9	1854.3	1865.1	1888.2	1897.4	1911.3
7.5°	1681.5	1698.4	1706.2	1706.2	1729.3	1754.0	1778.7	1794.1	1826.5	1838.8	1852.7
10°	1568.9	1588.9	1604.3	1602.8	1641.4	1656.8	1687.6	1723.1	1755.5	1774.0	1794.1
12.5°	1450.1	1460.9	1482.5	1513.3	1522.6	1550.4	1585.8	1630.6	1689.2	1706.2	1735.5
15°	1351.4	1380.7	1397.6	1411.5	1433.1	1459.3	1497.9	1541.1	1599.7	1636.7	1667.6
17.5°	1268.1	1306.6	1317.4	1314.3	1342.1	1382.2	1426.9	1459.3	1511.8	1556.5	1585.8
20°	1200.2	1215.6	1234.1	1241.8	1263.4	1306.6	1349.8	1386.8	1430.0	1465.5	1499.4
22.5°	1132.3	1144.6	1160.1	1173.9	1190.9	1215.6	1257.3	1303.5	1345.2	1379.1	1417.7
25°	1076.8	1084.5	1098.4	1109.2	1127.7	1144.6	1173.9	1224.9	1274.2	1294.3	1328.2
27.5°	1022.8	1028.9	1038.2	1050.5	1059.8	1076.8	1103.0	1144.6	1195.5	1215.6	1261.9
30°	974.9	979.6	988.8	995.0	999.6	1019.7	1039.7	1072.1	1110.7	1138.5	1172.4
32.5°	930.2	934.8	944.1	945.6	951.8	962.6	981.1	1010.4	1044.4	1067.5	1096.8
35°	880.8	883.9	893.2	896.3	900.9	910.2	924.0	945.6	976.5	993.5	1019.7
37.5°	842.3	840.7	846.9	851.5	857.7	862.3	867.0	888.6	911.7	927.1	947.2
40°	800.6	797.5	799.1	805.3	808.3	814.5	814.5	836.1	851.5	863.9	879.3
42.5°	759.0	757.4	754.4	757.4	760.5	762.1	763.6	779.0	794.5	805.3	822.2
45°	717.3	715.8	712.7	714.2	714.2	717.3	722.0	728.1	738.9	748.2	757.4
47.5°	678.8	675.7	671.0	669.5	672.6	672.6	672.6	678.8	689.6	692.6	701.9
50°	638.7	634.0	627.9	624.8	624.8	623.2	626.3	627.9	637.1	640.2	647.9
52.5°	595.5	592.4	586.2	580.0	581.6	578.5	580.0	581.6	584.7	589.3	593.9
55°	552.3	546.1	541.5	539.9	535.3	535.3	530.7	536.8	535.3	536.8	543.0
57.5°	510.6	504.4	496.7	493.6	489.0	487.5	484.4	482.8	484.4	489.0	493.6
60°	461.2	458.2	453.5	448.9	445.8	441.2	438.1	438.1	436.6	436.6	438.1
62.5°	413.4	411.9	405.7	404.2	401.1	398.0	393.4	390.3	390.3	393.4	394.9
65°	367.1	365.6	361.0	359.4	351.7	348.6	347.1	345.6	342.5	342.5	342.5
67.5°	324.0	319.3	319.3	311.6	305.4	302.4	299.3	297.7	297.7	297.7	299.3
70°	276.1	276.1	271.5	266.9	260.7	262.2	257.6	253.0	253.0	249.9	251.5
72.5°	229.9	228.3	223.7	222.1	217.5	212.9	209.8	212.9	208.3	206.7	208.3
75°	185.1	183.6	180.5	177.4	178.9	174.3	169.7	168.1	168.1	165.1	165.1
77.5°	141.9	145.0	138.8	137.3	134.2	131.1	129.6	128.0	128.0	128.0	131.1
80°	98.7	100.3	100.3	97.2	98.7	94.1	94.1	94.1	89.5	91.0	92.6
82.5°	63.2	63.2	61.7	63.2	61.7	61.7	60.2	60.2	58.6	58.6	60.2
85°	35.5	33.9	32.4	35.5	33.9	33.9	32.4	32.4	32.4	32.4	32.4
87.5°	7.7	9.3	9.3	9.3	9.3	10.8	10.8	10.8	12.3	12.3	12.3
90°	12.8	12.2	11.7	11.1	10.5	9.6	8.6	7.7	6.8	6.3	5.7
92.5°	13.6	13.3	13.1	12.8	12.6	12.2	11.9	11.5	11.2	11.0	11.2
95°	22.8	22.2	21.7	21.1	20.5	19.7	18.9	18.0	17.2	16.8	18.7
97.5°	28.2	27.9	27.5	27.2	26.8	24.9	23.1	21.2	19.3	18.4	23.2
100°	33.6	32.7	31.8	30.8	29.9	27.9	25.9	24.0	22.0	21.0	29.0
102.5°	36.2	34.9	33.6	32.3	31.0	52.2	73.5	94.7	116.0	126.6	126.7
105°	37.2	35.9	34.6	33.3	32.0	63.9	95.7	127.6	159.5	175.4	173.6
107.5°	38.3	37.0	35.7	34.4	33.1	72.4	111.8	151.1	190.4	210.1	208.6
110°	45.2	56.9	68.6	80.2	91.9	125.6	159.4	193.1	226.8	243.7	242.5

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	65.6	115.9	166.2	216.5	266.8	268.8	270.8	272.7	274.7	275.7	274.7
115°	107.9	161.9	216.0	270.0	324.0	321.1	318.2	315.3	312.4	310.9	309.9
117.5°	285.6	302.3	319.0	335.7	352.4	350.4	348.4	346.5	344.5	343.5	342.3
120°	390.5	389.1	387.7	386.3	384.9	382.8	380.7	378.6	376.5	375.5	374.6
122.5°	418.7	418.0	417.3	416.6	415.9	413.6	411.2	408.9	406.6	405.4	404.5
125°	447.0	446.2	445.4	444.6	443.8	441.6	439.4	437.1	434.9	433.8	433.0
127.5°	474.1	473.0	471.8	470.7	469.5	467.7	466.0	464.2	462.5	461.6	460.8
130°	499.4	498.1	496.8	495.5	494.2	492.9	491.6	490.3	489.0	488.4	487.5
132.5°	523.1	522.0	521.0	519.9	518.9	517.6	516.3	515.0	513.7	513.1	512.3
135°	546.1	544.9	543.8	542.6	541.4	540.4	539.3	538.3	537.2	536.7	535.8
137.5°	567.6	566.5	565.3	564.2	563.0	561.8	560.6	559.5	558.3	557.7	557.0
140°	588.2	587.1	586.1	585.0	584.0	582.7	581.4	580.1	578.8	578.2	577.7
142.5°	607.1	606.2	605.3	604.3	603.4	601.9	600.4	598.9	597.4	596.6	596.2
145°	624.5	623.7	622.9	622.1	621.3	619.3	617.3	615.3	613.3	612.3	612.4
147.5°	639.9	639.3	638.7	638.1	637.5	635.5	633.5	631.6	629.6	628.6	628.8
150°	654.5	653.8	653.1	652.4	651.7	649.8	648.0	646.1	644.2	643.3	643.7
152.5°	667.7	667.0	666.3	665.6	664.9	663.1	661.4	659.6	657.9	657.0	657.5
155°	679.2	678.5	677.8	677.1	676.4	675.0	673.6	672.2	670.8	670.1	670.6
157.5°	689.7	688.9	688.0	687.2	686.4	685.4	684.3	683.3	682.2	681.7	682.2
160°	698.1	697.4	696.7	696.0	695.3	694.6	693.9	693.2	692.5	692.2	692.5
162.5°	706.5	705.7	704.8	704.0	703.2	702.6	702.0	701.5	700.9	700.6	700.9
165°	712.8	712.0	711.1	710.3	709.5	709.1	708.8	708.4	708.1	707.9	708.3
167.5°	718.5	717.7	716.9	716.1	715.3	714.9	714.6	714.2	713.9	713.7	714.0
170°	722.8	722.0	721.1	720.3	719.5	719.3	719.0	718.8	718.5	718.4	718.8
172.5°	725.9	725.1	724.2	723.4	722.6	722.4	722.2	721.9	721.7	721.6	721.9
175°	728.0	727.2	726.3	725.5	724.7	724.5	724.3	724.0	723.8	723.7	724.1
177.5°	728.5	727.7	726.9	726.1	725.3	725.2	725.0	724.9	724.8	724.7	725.1
180°	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8	725.8

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2007.0	2007.0	2007.0	2007.0
2.5°	1970.0	1970.0	1993.1	2017.8
5°	1926.8	1937.6	1974.6	2008.5
7.5°	1885.1	1903.6	1949.9	1993.1
10°	1834.2	1858.9	1916.0	1966.9
12.5°	1784.8	1808.0	1874.3	1931.4
15°	1715.4	1744.7	1815.7	1886.6
17.5°	1646.0	1675.3	1761.7	1845.0
20°	1564.2	1602.8	1700.0	1811.1
22.5°	1488.6	1536.5	1644.5	1733.9
25°	1405.3	1479.4	1579.7	1695.4
27.5°	1331.3	1405.3	1507.2	1624.4
30°	1248.0	1323.6	1428.5	1536.5
32.5°	1167.8	1237.2	1339.0	1471.7
35°	1084.5	1150.8	1249.5	1383.7
37.5°	1008.9	1073.7	1181.7	1305.1
40°	934.8	1002.7	1095.3	1218.7
42.5°	865.4	925.6	1008.9	1132.3
45°	802.2	845.4	922.5	1038.2
47.5°	735.8	774.4	845.4	961.1
50°	674.1	706.5	768.2	876.2
52.5°	614.0	641.7	698.8	785.2
55°	560.0	586.2	627.9	712.7
57.5°	504.4	524.5	564.6	632.5
60°	450.5	469.0	501.4	556.9
62.5°	396.5	411.9	442.7	487.5
65°	348.6	361.0	384.1	422.7
67.5°	302.4	310.1	328.6	359.4
70°	257.6	263.8	279.2	303.9
72.5°	209.8	216.0	232.9	249.9
75°	169.7	171.2	183.6	197.5
77.5°	132.7	131.1	140.4	151.2
80°	91.0	95.6	103.4	108.0
82.5°	61.7	63.2	66.3	69.4
85°	33.9	35.5	35.5	40.1
87.5°	13.9	15.4	15.4	17.0
90°	4.4	3.1	1.8	0.5
92.5°	11.7	12.2	12.6	13.1
95°	22.6	26.4	30.3	34.1
97.5°	32.7	42.3	51.8	61.4
100°	45.0	61.0	77.0	93.0
102.5°	126.9	127.2	127.4	127.6
105°	170.1	166.6	163.1	159.6
107.5°	205.7	202.8	199.8	196.9
110°	240.0	237.5	235.1	232.6



TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	272.6	270.5	268.4	266.3
115°	307.9	306.0	304.0	302.0
117.5°	340.0	337.7	335.3	333.0
120°	372.9	371.1	369.4	367.6
122.5°	402.6	400.7	398.9	397.0
125°	431.5	430.0	428.5	427.0
127.5°	459.2	457.5	455.9	454.3
130°	485.6	483.7	481.9	480.0
132.5°	510.8	509.3	507.8	506.3
135°	533.9	532.0	530.2	528.3
137.5°	555.6	554.2	552.8	551.4
140°	576.8	575.9	574.9	574.0
142.5°	595.4	594.5	593.7	592.9
145°	612.5	612.6	612.8	612.9
147.5°	629.1	629.5	629.8	630.2
150°	644.5	645.4	646.2	647.0
152.5°	658.4	659.3	660.3	661.2
155°	671.7	672.7	673.8	674.8
157.5°	683.1	684.0	685.0	685.9
160°	693.2	693.9	694.6	695.3
162.5°	701.6	702.3	703.0	703.7
165°	709.0	709.7	710.4	711.1
167.5°	714.7	715.4	716.1	716.8
170°	719.5	720.2	720.9	721.6
172.5°	722.6	723.3	724.0	724.7
175°	724.9	725.8	726.6	727.4
177.5°	725.9	726.8	727.6	728.4
180°	725.8	725.8	725.8	725.8

TEST NUMBER: P997912

CATALOG NUMBER: SA2XXDIP-B1005D530UB2750-4F0-XX-W2A-A_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.36	20.36	20.16	21.17	22.17	16.85	17.85	17.65	18.66	19.66
	3H	20.18	21.07	20.99	21.90	22.93	18.21	19.10	19.02	19.92	20.95
	4H	20.36	21.20	21.19	22.03	23.07	18.68	19.52	19.51	20.35	21.39
	6H	20.41	21.18	21.25	22.02	23.08	18.99	19.76	19.83	20.61	21.66
	8H	20.39	21.13	21.24	21.99	23.04	19.08	19.81	19.93	20.67	21.73
	12H	20.36	21.06	21.21	21.91	22.99	19.13	19.83	19.98	20.68	21.76
4H	2H	19.42	20.26	20.25	21.09	22.13	17.32	18.16	18.15	18.99	20.03
	3H	20.41	21.11	21.26	21.97	23.03	18.79	19.49	19.63	20.35	21.41
	4H	20.69	21.33	21.55	22.19	23.27	19.33	19.96	20.19	20.83	21.91
	6H	20.83	21.38	21.70	22.26	23.35	19.72	20.26	20.59	21.15	22.24
	8H	20.83	21.34	21.71	22.22	23.32	19.83	20.34	20.70	21.22	22.32
	12H	20.80	21.26	21.70	22.16	23.27	19.89	20.35	20.79	21.25	22.36
8H	4H	20.71	21.22	21.59	22.10	23.20	19.48	19.99	20.36	20.87	21.97
	6H	20.90	21.32	21.80	22.24	23.34	19.92	20.34	20.82	21.27	22.37
	8H	20.93	21.30	21.84	22.22	23.33	20.07	20.44	20.99	21.36	22.48
	12H	20.92	21.25	21.83	22.15	23.32	20.17	20.50	21.09	21.41	22.58
12H	4H	20.68	21.13	21.57	22.04	23.14	19.46	19.92	20.36	20.82	21.93
	6H	20.87	21.25	21.79	22.17	23.28	19.92	20.29	20.83	21.21	22.33
	8H	20.91	21.24	21.83	22.15	23.32	20.08	20.41	21.00	21.32	22.49