

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931125

Luminaire Tested: DFN2DS-SQ4F0-090DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-090DS850-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9881.2 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 90.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931125

CATALOG NUMBER: DFN2DS-SQ4F0-090DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931125

CATALOG NUMBER: DFN2DS-SQ4F0-090DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2725	2725	2725
5°	2735	2696	2712
10°	2719	2669	2682
15°	2686	2634	2631
20°	2638	2582	2580
25°	2591	2518	2518
30°	2530	2460	2439
35°	2473	2390	2354
40°	2401	2319	2275
45°	2331	2249	2194
50°	2254	2177	2099
55°	2175	2092	2015
60°	2086	1992	1918
65°	1991	1891	1804
70°	1870	1770	1686
75°	1701	1630	1590
80°	1510	1463	1388
85°	1231	1174	1053

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2331 cd/sqm

TEST NUMBER: P931125

CATALOG NUMBER: DFN2DS-SQ4F0-090DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.5	3.7
10°-20°	1028.5	10.4
20°-30°	1511.4	15.3
30°-40°	1755.4	17.8
40°-50°	1753.3	17.7
50°-60°	1528.8	15.5
60°-70°	1130.1	11.4
70°-80°	639.4	6.5
80°-90°	168.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2905.4	29.4
0°-40°	4660.9	47.2
0°-60°	7942.9	80.4
0°-90°	9881.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9881.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3884	3884	3884	3884	3884	
5°	3884	3869	3828	3858	3850	369
15°	3697	3675	3626	3641	3622	1041
25°	3346	3316	3253	3260	3253	1540
35°	2887	2850	2790	2767	2748	1803
45°	2349	2323	2267	2226	2211	1813
55°	1778	1755	1710	1666	1647	1589
65°	1199	1176	1139	1106	1087	1185
75°	627	620	601	579	586	670
85°	153	149	146	134	131	180
90°	0	0	0	0	0	



TEST NUMBER: P931125

CATALOG NUMBER: DFN2DS-SQ4F0-090DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3883.6	3883.6	3883.6	3883.6	3883.6
2.5°	3906.2	3887.6	3846.5	3883.6	3876.5
5°	3883.6	3869.0	3827.8	3857.5	3850.3
7.5°	3857.5	3835.4	3794.1	3824.3	3816.7
10°	3816.7	3790.6	3745.8	3775.5	3764.4
12.5°	3760.4	3738.2	3693.5	3712.0	3704.6
15°	3697.1	3674.9	3626.1	3641.2	3622.5
17.5°	3618.6	3596.4	3547.7	3566.3	3547.7
20°	3532.6	3510.4	3458.1	3469.2	3454.5
22.5°	3447.0	3413.4	3364.6	3364.6	3357.1
25°	3346.0	3316.2	3252.9	3260.0	3252.9
27.5°	3233.8	3207.7	3159.4	3148.3	3129.7
30°	3122.2	3092.0	3036.1	3025.0	3010.0
32.5°	3002.5	2980.3	2920.4	2897.9	2882.8
35°	2886.8	2849.6	2789.7	2767.2	2748.5
37.5°	2756.1	2722.4	2662.5	2636.4	2617.8
40°	2621.7	2591.6	2531.7	2498.5	2483.5
42.5°	2490.9	2460.9	2401.4	2363.8	2341.7
45°	2349.1	2323.0	2266.7	2225.9	2210.9
47.5°	2210.9	2184.7	2124.8	2083.7	2061.5
50°	2065.1	2046.4	1994.1	1941.9	1923.2
52.5°	1923.2	1897.1	1848.7	1807.6	1781.4
55°	1777.8	1755.2	1710.4	1665.7	1647.1
57.5°	1632.0	1613.4	1564.7	1519.9	1504.8
60°	1486.2	1471.5	1419.2	1378.0	1367.0
62.5°	1344.3	1318.2	1280.9	1243.7	1228.7
65°	1198.9	1176.3	1139.1	1105.5	1086.8
67.5°	1049.6	1030.6	997.2	971.2	956.1
70°	911.3	896.2	862.6	836.4	821.8
72.5°	769.4	754.3	735.7	709.6	698.6
75°	627.3	620.0	601.1	578.9	586.4
77.5°	500.4	485.4	477.9	466.8	455.7
80°	373.6	369.6	362.1	351.0	343.6
82.5°	254.0	254.0	250.4	235.3	235.3
85°	152.9	149.4	145.8	134.3	130.8
87.5°	67.3	59.8	52.3	41.3	37.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931125

CATALOG NUMBER: DFN2DS-SQ4F0-090DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.77	16.38	15.13	16.69	17.00	14.32	15.93	14.69	16.25	16.56
	3H	16.52	17.97	16.89	18.30	18.66	16.02	17.48	16.40	17.81	18.17
	4H	17.16	18.53	17.56	18.88	19.26	16.67	18.04	17.07	18.38	18.76
	6H	17.63	18.90	18.04	19.26	19.66	17.13	18.40	17.54	18.76	19.15
	8H	17.77	18.99	18.20	19.37	19.77	17.27	18.48	17.70	18.87	19.27
	12H	17.86	19.02	18.29	19.41	19.83	17.35	18.51	17.78	18.89	19.32
4H	2H	15.33	16.70	15.72	17.04	17.42	14.97	16.34	15.37	16.69	17.07
	3H	17.30	18.45	17.71	18.85	19.25	16.89	18.04	17.30	18.44	18.84
	4H	18.08	19.11	18.51	19.53	19.96	17.65	18.69	18.09	19.10	19.54
	6H	18.67	19.58	19.13	20.02	20.48	18.24	19.15	18.70	19.59	20.04
	8H	18.86	19.71	19.32	20.15	20.62	18.43	19.27	18.89	19.71	20.18
	12H	19.00	19.76	19.48	20.23	20.70	18.54	19.30	19.02	19.78	20.25
8H	4H	18.35	19.20	18.81	19.64	20.11	17.98	18.82	18.44	19.27	19.73
	6H	19.07	19.77	19.56	20.26	20.73	18.68	19.39	19.18	19.88	20.35
	8H	19.32	19.96	19.83	20.46	20.95	18.93	19.56	19.44	20.07	20.56
	12H	19.52	20.08	20.03	20.57	21.13	19.11	19.67	19.62	20.16	20.72
12H	4H	18.38	19.14	18.86	19.61	20.08	18.01	18.77	18.49	19.25	19.72
	6H	19.11	19.74	19.62	20.25	20.74	18.74	19.37	19.25	19.88	20.37
	8H	19.42	19.98	19.93	20.47	21.03	19.05	19.60	19.55	20.10	20.66

END OF REPORT