

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998212

Luminaire Tested: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998212
REPORT IS A COMBINATION OF REPORTS P983952 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3256.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998212

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P998212

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	93	88	84	80	83	79	76	73	63	60	58	47	46	44	33	32	31
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	29	27	25
3	76	67	59	53	68	60	54	49	47	43	39	36	33	30	25	23	21
4	70	59	51	45	62	53	46	41	42	37	33	32	28	25	22	20	18
5	64	52	44	38	57	47	40	35	37	32	28	28	25	22	20	17	16
6	59	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	14
7	54	42	34	28	48	38	31	26	30	25	21	23	19	17	16	14	12
8	50	38	30	25	45	34	27	23	27	22	19	21	17	15	15	12	11
9	46	34	27	22	42	31	25	20	25	20	17	19	16	13	14	11	9
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4787	4787	4787
5°	4809	4584	4558
10°	4777	4424	4360
15°	4709	4261	4158
20°	4624	4088	3965
25°	4541	3923	3791
30°	4423	3755	3618
35°	4303	3593	3491
40°	4177	3453	3366
45°	4058	3326	3256
50°	3931	3210	3147
55°	3797	3085	3037
60°	3632	2956	2921
65°	3459	2806	2787
70°	3265	2648	2645
75°	3015	2488	2509
80°	2627	2322	2367
85°	2232	2165	2248

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4058 cd/sqm

TEST NUMBER: P998212

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.7	0.9
10°-20°	82.2	2.5
20°-30°	124.6	3.8
30°-40°	151.7	4.7
40°-50°	163.2	5.0
50°-60°	158.5	4.9
60°-70°	138.4	4.3
70°-80°	106.6	3.3
80°-90°	72.6	2.2
90°-100°	72.9	2.2
100°-110°	124.0	3.8
110°-120°	257.4	7.9
120°-130°	400.7	12.3
130°-140°	417.1	12.8
140°-150°	383.5	11.8
150°-160°	307.5	9.4
160°-170°	198.2	6.1
170°-180°	68.2	2.1
0°-30°	235.5	7.2
0°-40°	387.2	11.9
0°-60°	709.0	21.8
0°-90°	1026.6	31.5
90°-120°	454.3	14.0
90°-150°	1655.5	50.8
90°-180°	2229.0	68.5
0°-180°	3256.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	302	302	302	302	302	
5°	303	302	299	302	302	29
15°	289	290	290	294	294	81
25°	263	266	270	275	277	121
35°	227	234	242	252	255	142
45°	186	198	213	227	231	143
55°	142	158	181	197	202	127
65°	97	119	145	163	168	97
75°	54	78	106	125	131	57
85°	16	43	71	89	96	17
90°	5	36	68	88	95	5
95°	37	41	71	90	95	43
105°	160	188	69	90	97	171
115°	300	314	346	119	87	295
125°	422	429	453	468	474	377
135°	522	530	539	554	556	403
145°	605	605	613	620	619	379
155°	666	662	668	671	667	307
165°	702	699	700	704	700	198
175°	718	714	716	719	714	68
180°	717	717	717	717	717	

TEST NUMBER: P998212

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	302.4	302.4	302.4	302.4	302.4
2.5°	304.6	303.3	300.2	302.4	301.6
5°	303.3	302.0	299.4	302.0	301.6
7.5°	301.1	300.2	298.1	301.1	300.7
10°	298.5	297.6	296.3	299.8	299.4
12.5°	294.1	294.5	293.7	297.2	296.7
15°	289.3	290.2	290.2	294.1	293.7
17.5°	283.2	284.9	286.2	290.2	290.2
20°	277.0	279.2	281.0	285.8	285.8
22.5°	270.4	273.1	275.7	280.5	281.4
25°	263.0	266.1	270.0	275.3	276.6
27.5°	254.2	259.0	263.4	270.0	270.9
30°	245.5	251.2	256.9	263.9	265.2
32.5°	235.8	242.4	249.4	257.7	260.4
35°	226.6	234.1	242.4	252.0	255.1
37.5°	216.5	224.9	235.4	245.9	249.0
40°	206.4	216.1	227.9	239.3	243.3
42.5°	196.8	206.4	220.5	233.2	237.1
45°	185.8	197.7	213.0	226.6	231.0
47.5°	175.3	188.0	205.6	219.6	224.4
50°	164.4	178.0	197.7	212.6	217.4
52.5°	153.8	168.3	189.4	204.7	210.0
55°	142.5	158.2	181.0	196.8	202.5
57.5°	131.5	149.0	171.8	188.9	194.6
60°	119.7	138.5	163.5	180.1	186.3
62.5°	109.1	128.9	153.8	171.8	177.5
65°	97.3	118.8	144.6	162.6	168.3
67.5°	86.8	109.1	135.4	153.4	159.5
70°	75.4	98.2	125.4	144.2	149.5
72.5°	64.9	88.5	116.2	134.6	141.1
75°	53.9	78.5	106.5	125.4	131.1
77.5°	43.4	68.8	97.3	116.2	122.3
80°	32.9	59.6	88.1	106.5	112.6
82.5°	24.1	50.4	79.3	97.7	103.4
85°	15.8	43.0	71.0	89.4	95.6
87.5°	9.6	35.9	64.0	82.0	87.7
90°	4.9	36.0	68.3	88.4	94.7
92.5°	16.9	38.1	66.3	84.5	90.3
95°	37.2	40.7	70.6	89.9	94.6
97.5°	63.8	40.0	73.7	91.6	97.3
100°	94.9	40.0	73.4	93.7	99.6
102.5°	128.6	142.1	71.4	92.8	99.3
105°	159.8	188.1	69.3	90.3	97.3
107.5°	196.6	220.1	67.3	87.9	94.8
110°	231.5	251.1	122.7	84.9	91.8

TEST NUMBER: P998212

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	264.7	281.0	292.3	82.9	89.3
115°	299.9	313.6	346.2	119.2	86.8
117.5°	330.0	343.9	371.1	310.2	178.7
120°	364.3	373.8	400.7	419.2	354.0
122.5°	393.3	402.1	428.7	443.6	448.1
125°	422.4	429.2	453.0	468.5	474.0
127.5°	449.4	456.2	475.8	491.9	496.4
130°	474.8	482.6	497.5	513.8	516.8
132.5°	500.7	507.0	519.3	534.0	537.0
135°	522.0	530.3	539.4	553.8	556.2
137.5°	544.8	551.1	558.4	572.0	573.5
140°	567.1	570.9	577.5	589.1	589.2
142.5°	585.8	589.0	595.8	605.2	604.8
145°	605.1	604.6	613.4	619.6	619.2
147.5°	622.2	620.6	629.5	632.5	631.8
150°	638.8	635.2	643.5	646.6	644.0
152.5°	652.8	648.6	656.4	659.5	655.9
155°	666.3	661.6	667.8	670.9	666.8
157.5°	677.2	673.0	677.7	681.3	677.2
160°	686.5	683.4	686.5	689.6	686.0
162.5°	694.8	691.7	694.3	697.9	693.2
165°	702.1	698.9	700.5	704.1	700.5
167.5°	707.8	704.6	706.2	709.8	705.2
170°	712.4	709.3	710.4	714.0	709.3
172.5°	715.5	712.4	713.5	717.1	712.4
175°	718.1	714.5	715.5	719.2	714.0
177.5°	719.2	715.5	716.1	719.7	715.0
180°	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P998212

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.67	9.41	9.76	10.51	12.02	11.74	12.49	12.84	13.58	15.09
	3H	10.12	10.79	11.22	11.90	13.42	14.32	15.00	15.42	16.10	17.63
	4H	10.59	11.23	11.70	12.34	13.87	15.57	16.21	16.68	17.32	18.85
	6H	10.87	11.46	11.99	12.57	14.11	16.86	17.45	17.98	18.56	20.11
	8H	10.93	11.49	12.05	12.61	14.15	17.52	18.08	18.64	19.21	20.74
	12H	10.94	11.47	12.07	12.59	14.15	18.24	18.78	19.37	19.89	21.46
4H	2H	9.70	10.34	10.82	11.45	12.98	12.06	12.70	13.18	13.80	15.34
	3H	11.40	11.94	12.53	13.07	14.62	14.84	15.38	15.97	16.51	18.06
	4H	12.02	12.52	13.15	13.64	15.20	16.26	16.75	17.38	17.87	19.44
	6H	12.43	12.86	13.57	14.01	15.56	17.72	18.15	18.85	19.29	20.85
	8H	12.54	12.94	13.67	14.08	15.65	18.47	18.87	19.60	20.01	21.58
	12H	12.57	12.94	13.73	14.09	15.67	19.29	19.66	20.45	20.81	22.39
8H	4H	12.80	13.21	13.94	14.34	15.91	16.39	16.79	17.52	17.93	19.50
	6H	13.43	13.77	14.59	14.95	16.51	18.01	18.35	19.17	19.53	21.10
	8H	13.65	13.95	14.81	15.10	16.69	18.90	19.20	20.06	20.35	21.94
	12H	13.78	14.04	14.94	15.20	16.82	19.89	20.15	21.06	21.31	22.93
12H	4H	13.00	13.36	14.15	14.51	16.09	16.36	16.73	17.51	17.87	19.45
	6H	13.76	14.06	14.92	15.22	16.80	18.04	18.33	19.20	19.49	21.08
	8H	14.06	14.32	15.23	15.48	17.10	18.96	19.22	20.13	20.38	22.00