

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998215

Luminaire Tested: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998215
REPORT IS A COMBINATION OF REPORTS P983955 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3266.0 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998215

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P998215

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	93	88	84	80	83	79	76	73	63	60	58	47	46	44	33	32	31
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	29	27	25
3	76	67	59	53	68	60	54	49	47	43	39	36	33	30	25	23	21
4	70	59	51	45	62	53	46	41	42	37	33	32	28	25	22	20	18
5	64	52	44	38	57	47	40	35	37	32	28	28	25	22	20	17	16
6	59	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	14
7	54	42	34	28	48	38	31	26	30	25	21	23	19	17	16	14	12
8	50	38	30	25	45	34	27	23	27	22	19	21	17	15	15	12	11
9	46	34	27	22	42	31	25	20	25	20	17	19	16	13	14	11	9
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4804	4804	4804
5°	4826	4599	4573
10°	4793	4439	4375
15°	4726	4275	4172
20°	4641	4101	3979
25°	4556	3936	3803
30°	4438	3767	3631
35°	4319	3605	3504
40°	4194	3465	3377
45°	4073	3338	3267
50°	3943	3221	3159
55°	3808	3097	3048
60°	3644	2967	2931
65°	3470	2816	2797
70°	3278	2657	2654
75°	3026	2497	2517
80°	2635	2330	2376
85°	2232	2174	2255

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4073 cd/sqm

TEST NUMBER: P998215

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.8	0.9
10°-20°	82.5	2.5
20°-30°	125.0	3.8
30°-40°	152.2	4.7
40°-50°	163.8	5.0
50°-60°	159.1	4.9
60°-70°	138.9	4.3
70°-80°	106.9	3.3
80°-90°	72.9	2.2
90°-100°	73.1	2.2
100°-110°	124.4	3.8
110°-120°	258.1	7.9
120°-130°	401.8	12.3
130°-140°	418.3	12.8
140°-150°	384.5	11.8
150°-160°	308.4	9.4
160°-170°	198.7	6.1
170°-180°	68.4	2.1
0°-30°	236.3	7.2
0°-40°	388.5	11.9
0°-60°	711.5	21.8
0°-90°	1030.2	31.5
90°-120°	455.6	14.0
90°-150°	1660.3	50.8
90°-180°	2236.0	68.5
0°-180°	3266.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	304	304	304	304	304	
5°	304	303	300	303	303	29
15°	290	291	291	295	295	82
25°	264	267	271	276	278	121
35°	227	235	243	253	256	142
45°	186	198	214	227	232	144
55°	143	159	182	198	203	128
65°	98	119	145	163	169	97
75°	54	79	107	126	132	57
85°	16	43	71	90	96	17
90°	5	36	68	89	95	5
95°	37	41	71	90	95	43
105°	160	189	70	91	98	171
115°	301	314	347	120	87	296
125°	424	430	454	470	475	378
135°	524	532	541	555	558	405
145°	607	606	615	621	621	380
155°	668	664	670	673	669	308
165°	704	701	702	706	702	199
175°	720	716	718	721	716	69
180°	719	719	719	719	719	

TEST NUMBER: P998215

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	303.5	303.5	303.5	303.5	303.5
2.5°	305.7	304.4	301.3	303.5	302.6
5°	304.4	303.0	300.4	303.0	302.6
7.5°	302.2	301.3	299.1	302.2	301.7
10°	299.5	298.6	297.3	300.8	300.4
12.5°	295.1	295.6	294.7	298.2	297.8
15°	290.3	291.2	291.2	295.1	294.7
17.5°	284.1	285.9	287.2	291.2	291.2
20°	278.0	280.2	281.9	286.8	286.8
22.5°	271.4	274.0	276.7	281.5	282.4
25°	263.9	267.0	270.9	276.2	277.5
27.5°	255.1	259.9	264.3	270.9	271.8
30°	246.3	252.0	257.7	264.8	266.1
32.5°	236.6	243.2	250.3	258.6	261.3
35°	227.4	234.9	243.2	252.9	256.0
37.5°	217.3	225.6	236.2	246.7	249.8
40°	207.2	216.8	228.7	240.2	244.1
42.5°	197.5	207.2	221.2	234.0	238.0
45°	186.5	198.4	213.8	227.4	231.8
47.5°	175.9	188.7	206.3	220.4	225.2
50°	164.9	178.6	198.4	213.3	218.2
52.5°	154.4	168.9	190.0	205.4	210.7
55°	142.9	158.8	181.7	197.5	203.2
57.5°	132.0	149.5	172.4	189.6	195.3
60°	120.1	139.0	164.1	180.8	186.9
62.5°	109.5	129.3	154.4	172.4	178.1
65°	97.6	119.2	145.1	163.2	168.9
67.5°	87.1	109.5	135.9	153.9	160.1
70°	75.7	98.5	125.8	144.7	150.0
72.5°	65.1	88.8	116.6	135.0	141.6
75°	54.1	78.7	106.9	125.8	131.5
77.5°	43.5	69.1	97.6	116.6	122.7
80°	33.0	59.8	88.4	106.9	113.0
82.5°	24.2	50.6	79.6	98.1	103.8
85°	15.8	43.1	71.3	89.7	95.9
87.5°	9.7	36.1	64.2	82.2	88.0
90°	4.9	36.1	68.5	88.7	94.9
92.5°	17.0	38.2	66.6	84.8	90.5
95°	37.3	40.8	70.9	90.2	95.0
97.5°	63.9	40.2	74.0	91.9	97.7
100°	95.1	40.2	73.6	94.1	99.9
102.5°	129.0	142.5	71.6	93.1	99.6
105°	160.3	188.7	69.5	90.6	97.6
107.5°	197.2	220.8	67.5	88.2	95.1
110°	232.2	251.9	123.1	85.2	92.1

TEST NUMBER: P998215

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	265.4	281.8	293.2	83.1	89.5
115°	300.8	314.4	347.2	119.7	87.0
117.5°	331.0	344.9	372.2	311.1	179.2
120°	365.3	374.9	401.8	420.4	355.0
122.5°	394.4	403.2	429.8	444.8	449.4
125°	423.6	430.4	454.4	469.8	475.4
127.5°	450.7	457.5	477.2	493.4	497.9
130°	476.2	484.0	499.0	515.2	518.3
132.5°	502.2	508.4	520.7	535.6	538.6
135°	523.5	531.8	540.9	555.4	557.9
137.5°	546.4	552.6	560.0	573.6	575.2
140°	568.7	572.5	579.1	590.8	590.9
142.5°	587.5	590.7	597.5	606.9	606.5
145°	606.8	606.3	615.1	621.4	621.0
147.5°	624.0	622.4	631.3	634.3	633.6
150°	640.6	637.0	645.3	648.4	645.8
152.5°	654.7	650.5	658.3	661.4	657.8
155°	668.2	663.5	669.7	672.9	668.7
157.5°	679.1	674.9	679.6	683.3	679.1
160°	688.5	685.3	688.5	691.6	687.9
162.5°	696.8	693.7	696.3	699.9	695.2
165°	704.1	700.9	702.5	706.1	702.5
167.5°	709.8	706.7	708.2	711.9	707.2
170°	714.5	711.3	712.4	716.0	711.3
172.5°	717.6	714.5	715.5	719.1	714.5
175°	720.2	716.5	717.6	721.2	716.0
177.5°	721.2	717.6	718.1	721.7	717.1
180°	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998215

CATALOG NUMBER: SA2XXDIP-B290D530UB2750-4F0-XX-W2A-D_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.68	9.42	9.77	10.52	12.03	11.76	12.50	12.85	13.60	15.11
	3H	10.13	10.81	11.23	11.91	13.44	14.34	15.01	15.44	16.11	17.64
	4H	10.60	11.24	11.72	12.35	13.88	15.59	16.23	16.70	17.33	18.86
	6H	10.88	11.47	12.00	12.58	14.13	16.88	17.47	18.00	18.58	20.12
	8H	10.94	11.50	12.06	12.63	14.16	17.53	18.10	18.66	19.22	20.76
	12H	10.95	11.49	12.08	12.60	14.17	18.25	18.79	19.38	19.91	21.47
4H	2H	9.72	10.36	10.84	11.46	12.99	12.07	12.71	13.19	13.82	15.35
	3H	11.42	11.96	12.54	13.09	14.63	14.86	15.40	15.98	16.53	18.07
	4H	12.04	12.53	13.16	13.65	15.22	16.27	16.77	17.40	17.89	19.45
	6H	12.44	12.87	13.58	14.02	15.57	17.73	18.16	18.86	19.30	20.86
	8H	12.55	12.95	13.68	14.09	15.66	18.48	18.89	19.62	20.02	21.60
	12H	12.59	12.95	13.74	14.10	15.68	19.31	19.67	20.46	20.82	22.40
8H	4H	12.82	13.22	13.95	14.35	15.93	16.40	16.81	17.54	17.94	19.51
	6H	13.44	13.78	14.60	14.96	16.53	18.03	18.36	19.18	19.54	21.11
	8H	13.66	13.96	14.82	15.12	16.70	18.92	19.21	20.08	20.37	21.96
	12H	13.79	14.05	14.96	15.21	16.83	19.90	20.17	21.07	21.32	22.94
12H	4H	13.01	13.38	14.16	14.52	16.10	16.37	16.74	17.52	17.89	19.46
	6H	13.78	14.07	14.94	15.23	16.82	18.05	18.35	19.21	19.50	21.09
	8H	14.08	14.34	15.24	15.49	17.11	18.97	19.24	20.14	20.39	22.01