

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931075

Luminaire Tested: DFN2DS-SQ4F0-060DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-060DS930-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4841.1 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 57.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931075

CATALOG NUMBER: DFN2DS-SQ4F0-060DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931075

CATALOG NUMBER: DFN2DS-SQ4F0-060DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1335	1335	1335
5°	1340	1321	1329
10°	1332	1308	1314
15°	1316	1291	1289
20°	1292	1265	1264
25°	1269	1234	1234
30°	1239	1205	1195
35°	1212	1171	1153
40°	1176	1136	1114
45°	1142	1102	1075
50°	1104	1067	1029
55°	1066	1025	987
60°	1022	976	940
65°	975	927	884
70°	916	867	826
75°	833	798	779
80°	739	717	680
85°	603	575	516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1142 cd/sqm

TEST NUMBER: P931075

CATALOG NUMBER: DFN2DS-SQ4F0-060DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	3.7
10°-20°	503.9	10.4
20°-30°	740.5	15.3
30°-40°	860.0	17.8
40°-50°	859.0	17.7
50°-60°	749.0	15.5
60°-70°	553.7	11.4
70°-80°	313.3	6.5
80°-90°	82.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1423.5	29.4
0°-40°	2283.5	47.2
0°-60°	3891.5	80.4
0°-90°	4841.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4841.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1875	1890	1886	181
15°	1811	1800	1776	1784	1775	510
25°	1639	1625	1594	1597	1594	754
35°	1414	1396	1367	1356	1346	883
45°	1151	1138	1110	1091	1083	888
55°	871	860	838	816	807	779
65°	587	576	558	542	532	581
75°	307	304	294	284	287	328
85°	75	73	71	66	64	88
90°	0	0	0	0	0	

TEST NUMBER: P931075

CATALOG NUMBER: DFN2DS-SQ4F0-060DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1913.8	1904.7	1884.4	1902.7	1899.2
5°	1902.7	1895.5	1875.3	1889.9	1886.4
7.5°	1889.9	1879.1	1858.9	1873.6	1869.9
10°	1869.9	1857.1	1835.1	1849.7	1844.3
12.5°	1842.4	1831.5	1809.5	1818.7	1815.0
15°	1811.3	1800.4	1776.5	1784.0	1774.8
17.5°	1772.9	1762.0	1738.2	1747.2	1738.2
20°	1730.7	1719.9	1694.2	1699.7	1692.5
22.5°	1688.8	1672.3	1648.4	1648.4	1644.8
25°	1639.3	1624.8	1593.7	1597.2	1593.7
27.5°	1584.4	1571.6	1547.8	1542.5	1533.3
30°	1529.7	1514.8	1487.5	1482.1	1474.7
32.5°	1471.0	1460.2	1430.8	1419.7	1412.4
35°	1414.4	1396.1	1366.8	1355.7	1346.5
37.5°	1350.3	1333.7	1304.5	1291.6	1282.5
40°	1284.4	1269.7	1240.4	1224.1	1216.7
42.5°	1220.4	1205.6	1176.5	1158.1	1147.2
45°	1150.9	1138.1	1110.5	1090.6	1083.1
47.5°	1083.1	1070.3	1041.1	1020.9	1009.9
50°	1011.7	1002.6	977.0	951.3	942.2
52.5°	942.2	929.4	905.7	885.6	872.8
55°	871.0	859.9	838.0	816.1	806.9
57.5°	799.6	790.5	766.6	744.7	737.2
60°	728.1	720.9	695.4	675.1	669.7
62.5°	658.6	645.8	627.6	609.3	602.0
65°	587.4	576.4	558.1	541.6	532.4
67.5°	514.2	504.9	488.6	475.8	468.4
70°	446.5	439.1	422.6	409.8	402.6
72.5°	376.9	369.6	360.5	347.7	342.2
75°	307.3	303.8	294.5	283.6	287.3
77.5°	245.2	237.8	234.1	228.7	223.2
80°	183.0	181.1	177.4	172.0	168.3
82.5°	124.5	124.5	122.7	115.3	115.3
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.3	25.6	20.2	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931075

CATALOG NUMBER: DFN2DS-SQ4F0-060DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.29	13.90	12.65	14.21	14.53	11.84	13.45	12.21	13.77	14.08
	3H	14.04	15.49	14.41	15.82	16.18	13.55	15.00	13.92	15.33	15.69
	4H	14.68	16.05	15.08	16.40	16.78	14.19	15.56	14.59	15.91	16.28
	6H	15.15	16.42	15.56	16.79	17.18	14.65	15.92	15.06	16.28	16.68
	8H	15.30	16.51	15.72	16.90	17.29	14.79	16.00	15.22	16.39	16.79
	12H	15.39	16.55	15.82	16.93	17.36	14.87	16.03	15.30	16.42	16.84
4H	2H	12.85	14.22	13.25	14.56	14.94	12.49	13.86	12.89	14.21	14.59
	3H	14.82	15.97	15.23	16.37	16.77	14.42	15.56	14.83	15.96	16.36
	4H	15.60	16.63	16.03	17.05	17.48	15.18	16.21	15.61	16.62	17.06
	6H	16.20	17.10	16.65	17.54	18.00	15.76	16.67	16.22	17.11	17.56
	8H	16.38	17.23	16.85	17.67	18.14	15.95	16.79	16.41	17.24	17.70
	12H	16.52	17.28	17.00	17.75	18.22	16.06	16.82	16.54	17.30	17.77
8H	4H	15.87	16.72	16.33	17.16	17.63	15.50	16.34	15.96	16.79	17.25
	6H	16.59	17.29	17.08	17.78	18.25	16.20	16.91	16.70	17.40	17.87
	8H	16.85	17.48	17.36	17.98	18.47	16.45	17.08	16.96	17.59	18.08
	12H	17.05	17.60	17.55	18.09	18.66	16.63	17.19	17.14	17.68	18.24
12H	4H	15.90	16.66	16.38	17.13	17.60	15.53	16.29	16.01	16.77	17.24
	6H	16.63	17.26	17.14	17.77	18.26	16.26	16.90	16.77	17.40	17.89
	8H	16.95	17.50	17.45	17.99	18.56	16.57	17.13	17.07	17.62	18.18