

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998276

Luminaire Tested: SA2XXDIP-B290D725UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998276
REPORT IS A COMBINATION OF REPORTS P984016 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B290D725UB2750-4F0-XX-W2A-D_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3842.1 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998276

CATALOG NUMBER: SA2XXDIP-B290D725UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P998276

CATALOG NUMBER: SA2XXDIP-B290D725UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	87	83	79	81	78	74	71	60	58	56	44	42	41	29	28	27
2	83	76	69	64	74	67	62	58	52	48	45	38	36	33	25	23	22
3	76	66	59	53	67	59	53	48	46	41	38	33	30	28	22	20	19
4	69	58	50	44	61	52	45	40	40	36	32	29	26	24	19	17	16
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	14
6	58	46	38	32	51	41	34	29	32	27	23	24	20	18	16	13	12
7	53	41	34	28	47	37	30	25	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	33	27	22	26	21	18	19	16	14	13	11	9
9	46	34	27	22	41	30	24	20	24	19	16	18	14	12	12	10	8
10	43	31	24	19	38	28	22	17	22	17	14	16	13	11	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4643	4643	4643
5°	4663	4444	4419
10°	4631	4290	4228
15°	4566	4131	4032
20°	4484	3963	3845
25°	4402	3803	3676
30°	4288	3641	3508
35°	4172	3483	3386
40°	4052	3348	3264
45°	3936	3226	3157
50°	3812	3112	3052
55°	3680	2991	2946
60°	3520	2866	2832
65°	3356	2723	2703
70°	3166	2568	2563
75°	2926	2413	2433
80°	2547	2250	2296
85°	2161	2101	2180

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3936 cd/sqm

TEST NUMBER: P998276

CATALOG NUMBER: SA2XXDIP-B290D725UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.8	0.7
10°-20°	79.7	2.1
20°-30°	120.8	3.1
30°-40°	147.1	3.8
40°-50°	158.3	4.1
50°-60°	153.7	4.0
60°-70°	134.3	3.5
70°-80°	103.3	2.7
80°-90°	70.9	1.8
90°-100°	78.4	2.0
100°-110°	149.0	3.9
110°-120°	325.6	8.5
120°-130°	514.8	13.4
130°-140°	538.5	14.0
140°-150°	496.4	12.9
150°-160°	398.4	10.4
160°-170°	256.7	6.7
170°-180°	88.4	2.3
0°-30°	228.3	5.9
0°-40°	375.5	9.8
0°-60°	687.5	17.9
0°-90°	995.9	25.9
90°-120°	553.0	14.4
90°-150°	2102.7	54.7
90°-180°	2846.0	74.1
0°-180°	3842.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	293	293	293	293	293	
5°	294	293	290	293	292	28
15°	280	281	281	285	285	79
25°	255	258	262	267	268	117
35°	220	227	235	244	247	137
45°	180	192	207	220	224	139
55°	138	153	176	191	196	124
65°	94	115	140	158	163	94
75°	52	76	103	122	127	55
85°	15	42	69	87	93	16
90°	5	37	70	90	96	5
95°	47	45	75	95	99	54
105°	206	239	78	100	107	221
115°	388	404	440	142	98	382
125°	547	556	582	598	604	488
135°	676	687	697	713	715	522
145°	784	783	795	802	801	490
155°	863	857	865	869	864	398
165°	910	905	907	912	907	257
175°	930	926	927	932	925	89
180°	928	928	928	928	928	

TEST NUMBER: P998276

CATALOG NUMBER: SA2XXDIP-B290D725UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	293.3	293.3	293.3	293.3	293.3
2.5°	295.4	294.1	291.1	293.3	292.4
5°	294.1	292.8	290.3	292.8	292.4
7.5°	292.0	291.1	289.0	292.0	291.6
10°	289.4	288.6	287.3	290.7	290.3
12.5°	285.2	285.6	284.8	288.2	287.7
15°	280.5	281.4	281.4	285.2	284.8
17.5°	274.6	276.3	277.5	281.4	281.4
20°	268.6	270.7	272.4	277.1	277.1
22.5°	262.2	264.8	267.3	272.0	272.9
25°	255.0	258.0	261.8	266.9	268.2
27.5°	246.5	251.2	255.4	261.8	262.7
30°	238.0	243.5	249.1	255.9	257.1
32.5°	228.7	235.0	241.8	249.9	252.5
35°	219.7	227.0	235.0	244.4	247.4
37.5°	210.0	218.0	228.2	238.4	241.4
40°	200.2	209.5	221.0	232.1	235.9
42.5°	190.8	200.2	213.8	226.1	229.9
45°	180.2	191.7	206.6	219.7	224.0
47.5°	170.0	182.3	199.3	212.9	217.6
50°	159.4	172.6	191.7	206.1	210.8
52.5°	149.2	163.2	183.6	198.5	203.6
55°	138.1	153.4	175.5	190.8	196.4
57.5°	127.5	144.5	166.6	183.2	188.7
60°	116.0	134.3	158.5	174.7	180.6
62.5°	105.8	125.0	149.2	166.6	172.1
65°	94.4	115.2	140.3	157.7	163.2
67.5°	84.2	105.8	131.3	148.8	154.7
70°	73.1	95.2	121.6	139.8	144.9
72.5°	62.9	85.9	112.6	130.5	136.9
75°	52.3	76.1	103.3	121.6	127.1
77.5°	42.1	66.7	94.4	112.6	118.6
80°	31.9	57.8	85.4	103.3	109.2
82.5°	23.4	48.9	76.9	94.8	100.3
85°	15.3	41.7	68.9	86.7	92.7
87.5°	9.4	34.9	62.1	79.5	85.0
90°	5.0	37.0	69.5	89.9	96.3
92.5°	20.6	40.5	68.4	86.4	92.1
95°	47.1	44.9	75.1	94.6	99.0
97.5°	81.6	44.8	80.2	97.9	103.6
100°	121.9	45.6	80.8	101.9	107.9
102.5°	165.8	178.5	79.1	101.8	108.5
105°	206.3	238.8	77.6	99.8	107.1
107.5°	254.0	281.0	75.9	97.7	105.1
110°	299.3	321.9	148.5	95.0	102.4

TEST NUMBER: P998276

CATALOG NUMBER: SA2XXDIP-B290D725UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	342.2	361.1	369.3	93.4	100.0
115°	387.9	404.0	439.9	141.7	98.0
117.5°	427.1	444.0	473.2	390.0	218.2
120°	471.5	483.3	512.3	532.3	446.3
122.5°	509.1	520.2	549.4	564.9	569.4
125°	547.0	555.7	582.1	598.2	604.1
127.5°	581.9	590.8	612.4	629.7	634.3
130°	614.8	625.1	641.5	659.0	661.8
132.5°	648.4	656.6	670.4	686.3	689.0
135°	676.1	686.9	697.2	712.8	714.9
137.5°	705.7	713.7	722.6	737.4	738.4
140°	734.6	739.5	747.8	760.7	759.8
142.5°	758.7	763.0	771.8	782.2	781.0
145°	783.9	783.2	794.6	801.9	800.6
147.5°	806.0	804.0	815.4	819.2	817.8
150°	827.5	822.8	833.6	837.6	834.2
152.5°	845.7	840.3	850.4	854.4	849.7
155°	863.1	857.1	865.1	869.2	863.8
157.5°	877.2	871.8	877.9	882.6	877.2
160°	889.3	885.3	889.3	893.3	888.6
162.5°	900.1	896.0	899.4	904.1	898.0
165°	909.5	905.4	907.4	912.2	907.4
167.5°	916.9	912.8	914.8	919.5	913.5
170°	922.9	918.9	920.2	924.9	918.9
172.5°	926.9	922.9	924.2	928.9	922.9
175°	930.3	925.6	926.9	931.6	924.9
177.5°	931.6	926.9	927.6	932.3	926.3
180°	928.3	928.3	928.3	928.3	928.3

TEST NUMBER: P998276

CATALOG NUMBER: SA2XXDIP-B290D725UB2750-4F0-XX-W2A-D_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.77	8.47	8.90	9.60	11.18	10.85	11.55	11.98	12.68	14.25
	3H	9.22	9.85	10.36	10.99	12.58	13.43	14.06	14.57	15.19	16.78
	4H	9.69	10.29	10.84	11.43	13.03	14.67	15.27	15.82	16.41	18.01
	6H	9.97	10.52	11.12	11.66	13.27	15.96	16.52	17.12	17.66	19.26
	8H	10.02	10.55	11.18	11.71	13.31	16.62	17.15	17.78	18.30	19.90
	12H	10.03	10.54	11.20	11.68	13.31	17.34	17.84	18.50	18.99	20.61
4H	2H	8.81	9.41	9.96	10.54	12.14	11.16	11.76	12.32	12.90	14.49
	3H	10.50	11.01	11.66	12.17	13.78	13.94	14.45	15.10	15.61	17.22
	4H	11.12	11.59	12.28	12.74	14.36	15.35	15.82	16.51	16.97	18.60
	6H	11.52	11.93	12.69	13.10	14.72	16.81	17.21	17.98	18.39	20.00
	8H	11.63	12.01	12.80	13.17	14.81	17.56	17.94	18.73	19.11	20.74
	12H	11.66	12.01	12.85	13.18	14.82	18.38	18.73	19.57	19.90	21.54
8H	4H	11.89	12.27	13.06	13.44	15.07	15.48	15.86	16.65	17.02	18.66
	6H	12.52	12.84	13.71	14.04	15.67	17.10	17.42	18.29	18.63	20.26
	8H	12.74	13.02	13.93	14.20	15.85	17.99	18.27	19.18	19.45	21.10
	12H	12.87	13.11	14.06	14.29	15.97	18.98	19.22	20.18	20.40	22.09
12H	4H	12.08	12.43	13.27	13.60	15.24	15.45	15.79	16.63	16.97	18.61
	6H	12.85	13.13	14.05	14.31	15.96	17.13	17.40	18.32	18.59	20.24
	8H	13.15	13.39	14.35	14.58	16.26	18.05	18.29	19.25	19.47	21.15