

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998387

Luminaire Tested: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998387
REPORT IS A COMBINATION OF REPORTS P984127 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6387.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35			29
2	86	79	73	68	77	72	67	63	57	54	51	44	42	40	32	31	30			24
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26			21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22			18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20			16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18			14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16			13
8	52	41	33	28	47	37	31	26	30	25	22	24	21	18	18	16	14			12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13			11
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15188	15188	15188	15188
5°	15226	16194	15283	12885
10°	15048	17679	15142	10622
15°	14683	18647	14887	8948
20°	14455	17508	14455	7777
25°	13993	15041	14057	6954
30°	13236	11824	13488	6300
35°	12565	8176	12774	5763
40°	11791	6173	11927	5336
45°	10841	5073	11018	4875
50°	10017	4452	10037	4463
55°	9078	3794	9140	4015
60°	8078	3169	8190	3505
65°	7185	2577	7316	2993
70°	6293	2022	6453	2413
75°	5281	1468	5488	1751
80°	4120	931	4415	1039
85°	2712	468	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15700 cd/sqm

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.4
10°-20°	266.0	4.2
20°-30°	386.1	6.0
30°-40°	407.0	6.4
40°-50°	360.1	5.6
50°-60°	287.6	4.5
60°-70°	195.3	3.1
70°-80°	99.9	1.6
80°-90°	26.2	0.4
90°-100°	48.0	0.8
100°-110°	178.9	2.8
110°-120°	474.6	7.4
120°-130°	787.1	12.3
130°-140°	836.1	13.1
140°-150°	777.0	12.2
150°-160°	624.7	9.8
160°-170°	402.5	6.3
170°-180°	138.5	2.2
0°-30°	743.5	11.6
0°-40°	1150.4	18.0
0°-60°	1798.1	28.2
0°-90°	2119.6	33.2
90°-120°	701.5	11.0
90°-150°	3101.6	48.6
90°-180°	4267.0	66.8
0°-180°	6387.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	960	960	960	960	960	
5°	960	1072	964	853	960	91
15°	902	1317	914	632	902	255
25°	810	1097	814	507	810	371
35°	662	597	673	421	662	414
45°	496	360	504	346	496	385
55°	341	253	343	268	341	304
65°	202	156	206	181	202	201
75°	94	77	98	92	94	101
85°	19	20	21	15	19	22
90°	1	28	1	28	1	5
95°	68	45	68	45	68	81
105°	320	80	320	80	320	342
115°	606	86	606	86	606	596
125°	856	901	856	901	856	764
135°	1060	1094	1060	1094	1060	819
145°	1229	1248	1229	1248	1229	769
155°	1354	1354	1354	1354	1354	624
165°	1426	1423	1426	1423	1426	403
175°	1459	1450	1459	1450	1459	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	964.7	966.9	970.6	971.3	978.7	984.6	991.2	991.2	993.4	992.7	986.8
5°	960.3	966.9	976.5	984.6	997.9	1003.8	1012.6	1019.3	1025.2	1029.6	1028.9
7.5°	952.9	964.7	978.7	994.2	1011.9	1022.2	1034.8	1046.6	1054.7	1062.0	1067.2
10°	940.3	960.3	979.4	1000.1	1023.0	1037.0	1051.7	1067.2	1079.7	1093.8	1107.0
12.5°	923.4	952.1	975.7	1003.0	1031.1	1046.6	1070.2	1082.0	1106.3	1141.7	1151.3
15°	902.0	941.1	963.2	997.9	1034.8	1047.3	1079.7	1098.9	1149.1	1171.2	1197.7
17.5°	882.1	925.6	955.1	994.9	1031.1	1055.4	1087.1	1126.2	1168.2	1200.0	1229.5
20°	865.9	907.9	943.3	987.5	1033.3	1064.3	1097.4	1144.6	1190.4	1222.8	1245.7
22.5°	829.0	882.8	924.1	973.5	1028.9	1071.6	1103.3	1155.0	1204.4	1224.3	1244.2
25°	810.5	857.0	904.9	961.0	1025.9	1076.8	1104.1	1161.6	1205.1	1212.5	1216.9
27.5°	776.6	829.0	885.0	949.2	1025.2	1067.9	1102.6	1155.0	1189.6	1184.5	1171.2
30°	734.6	798.7	860.7	930.0	1014.8	1061.3	1093.8	1141.7	1159.4	1132.8	1109.2
32.5°	703.6	764.1	832.7	913.1	1003.0	1047.3	1079.0	1116.6	1120.3	1072.4	1032.5
35°	661.6	728.7	806.1	890.9	983.1	1023.0	1052.5	1075.3	1057.6	990.5	943.3
37.5°	623.9	690.3	772.9	859.2	955.8	994.9	1018.5	1022.2	978.7	919.7	850.4
40°	582.6	651.2	737.5	828.2	925.6	959.5	974.3	963.2	900.5	831.9	751.5
42.5°	541.3	609.2	702.1	795.1	887.2	916.0	921.9	891.7	815.0	734.6	641.6
45°	496.4	567.2	660.1	753.8	843.0	859.2	860.0	816.4	725.7	641.6	555.4
47.5°	459.5	525.1	617.3	711.0	786.2	797.3	792.8	742.7	643.9	549.5	474.2
50°	418.9	481.6	573.1	665.2	729.4	732.4	721.3	649.8	553.1	466.9	407.1
52.5°	375.4	438.8	522.9	611.4	668.9	664.5	643.1	566.4	475.7	404.2	358.4
55°	340.7	396.8	475.7	562.0	602.6	590.0	566.4	488.2	416.7	356.2	316.4
57.5°	302.4	351.8	429.2	504.5	528.1	516.3	492.7	419.7	353.3	307.5	281.0
60°	266.2	311.2	379.1	441.8	460.2	447.7	420.4	354.8	306.8	268.5	248.5
62.5°	233.1	272.1	328.9	386.5	393.8	381.3	357.7	304.6	263.3	233.1	218.3
65°	202.1	239.0	284.7	328.2	334.8	321.6	297.2	258.9	224.2	205.0	191.0
67.5°	171.8	201.3	241.9	273.6	277.3	264.8	244.9	213.9	192.5	171.8	161.5
70°	145.3	167.4	199.1	224.9	226.4	214.6	204.3	176.3	160.0	145.3	137.2
72.5°	119.5	135.0	159.3	178.5	179.2	171.8	162.3	144.6	130.5	120.2	112.1
75°	94.4	107.7	122.4	139.4	138.7	132.8	125.4	114.3	102.5	95.9	92.2
77.5°	72.3	80.4	92.2	103.3	103.3	100.3	95.9	87.8	80.4	73.8	70.1
80°	51.6	56.8	66.4	70.1	71.5	70.8	67.1	61.2	58.3	53.1	51.6
82.5°	33.2	36.9	41.3	45.0	47.2	45.7	45.0	42.0	37.6	36.1	34.7
85°	19.2	20.7	22.9	25.1	25.8	25.1	26.6	24.3	22.1	22.1	21.4
87.5°	8.1	8.9	10.3	10.3	11.1	11.1	10.3	11.1	11.1	10.3	9.6
90°	1.1	3.7	6.2	8.8	11.3	12.6	13.5	15.4	17.3	19.2	21.1
92.5°	26.3	25.4	24.4	23.5	22.6	22.1	22.5	23.2	23.9	24.6	25.3
95°	68.5	60.8	53.0	45.3	37.6	33.7	34.5	36.2	37.8	39.5	41.1
97.5°	123.2	104.0	84.8	65.7	46.5	36.9	38.8	42.5	46.2	50.0	53.7
100°	186.4	154.3	122.3	90.2	58.1	42.1	44.1	48.1	52.0	56.0	60.0
102.5°	255.9	255.4	255.0	254.5	254.0	253.8	232.5	189.9	147.3	104.7	62.1
105°	320.2	327.2	334.2	341.3	348.3	351.8	319.9	256.0	192.1	128.2	64.3
107.5°	395.0	400.8	406.7	412.5	418.4	421.3	381.9	303.0	224.1	145.3	66.4
110°	466.6	471.5	476.4	481.3	486.2	488.7	454.9	387.2	319.6	251.9	184.3

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	534.0	538.2	542.4	546.7	550.9	553.0	551.0	547.0	543.1	539.1	535.1
115°	605.6	609.6	613.6	617.5	621.5	623.5	626.4	632.3	638.2	644.0	649.9
117.5°	667.8	672.5	677.2	681.9	686.6	688.9	690.9	694.9	698.8	702.8	706.8
120°	737.3	740.8	744.3	747.8	751.3	753.1	755.2	759.4	763.7	767.9	772.1
122.5°	796.3	800.0	803.8	807.5	811.2	813.1	815.4	820.1	824.8	829.5	834.2
125°	856.3	859.3	862.4	865.4	868.5	870.0	872.2	876.7	881.1	885.6	890.0
127.5°	911.1	914.4	917.6	920.9	924.2	925.8	927.6	931.1	934.6	938.1	941.6
130°	962.7	966.5	970.2	974.0	977.7	979.6	980.9	983.4	986.0	988.5	991.1
132.5°	1015.4	1018.4	1021.5	1024.5	1027.6	1029.1	1030.4	1032.9	1035.5	1038.0	1040.6
135°	1059.6	1063.4	1067.1	1070.9	1074.6	1076.5	1077.5	1079.6	1081.7	1083.8	1085.9
137.5°	1106.0	1108.8	1111.6	1114.4	1117.2	1118.6	1119.8	1122.1	1124.4	1126.8	1129.1
140°	1151.2	1153.1	1155.0	1156.9	1158.8	1159.7	1161.0	1163.6	1166.1	1168.7	1171.3
142.5°	1189.2	1190.8	1192.4	1194.1	1195.7	1196.5	1198.0	1201.1	1204.1	1207.2	1210.2
145°	1229.2	1229.0	1228.7	1228.5	1228.2	1228.1	1230.1	1234.1	1238.0	1242.0	1246.0
147.5°	1263.9	1263.2	1262.5	1261.8	1261.1	1260.8	1262.8	1266.8	1270.7	1274.7	1278.7
150°	1297.7	1296.1	1294.4	1292.8	1291.1	1290.3	1292.2	1295.9	1299.6	1303.4	1307.1
152.5°	1326.1	1324.2	1322.4	1320.5	1318.6	1317.7	1319.5	1323.0	1326.5	1330.0	1333.5
155°	1353.5	1351.4	1349.3	1347.2	1345.1	1344.0	1345.4	1348.2	1351.0	1353.8	1356.6
157.5°	1375.6	1373.7	1371.9	1370.0	1368.1	1367.2	1368.2	1370.3	1372.4	1374.5	1376.6
160°	1394.6	1393.2	1391.8	1390.3	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6
162.5°	1411.4	1410.0	1408.6	1407.2	1405.8	1405.1	1405.7	1406.9	1408.0	1409.2	1410.4
165°	1426.2	1424.8	1423.4	1421.9	1420.5	1419.8	1420.2	1420.9	1421.6	1422.3	1423.0
167.5°	1437.7	1436.3	1434.9	1433.5	1432.1	1431.4	1431.8	1432.5	1433.2	1433.9	1434.6
170°	1447.2	1445.8	1444.4	1443.0	1441.6	1440.9	1441.1	1441.6	1442.1	1442.5	1443.0
172.5°	1453.5	1452.1	1450.7	1449.3	1447.9	1447.2	1447.4	1447.9	1448.4	1448.8	1449.3
175°	1458.8	1457.2	1455.5	1453.9	1452.2	1451.4	1451.6	1452.1	1452.6	1453.0	1453.5
177.5°	1460.9	1459.3	1457.6	1456.0	1454.3	1453.5	1453.6	1453.9	1454.1	1454.4	1454.6
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	997.1	997.9	999.3	1006.7	1010.4	1011.1	1008.2	1014.8	1017.1	1014.8	1013.4
5°	1044.3	1048.8	1057.6	1067.2	1066.5	1067.2	1071.6	1076.1	1077.5	1071.6	1073.8
7.5°	1085.6	1094.5	1104.1	1118.8	1118.8	1126.2	1129.2	1132.8	1141.7	1137.3	1135.8
10°	1132.8	1144.6	1162.3	1185.9	1186.7	1194.1	1201.4	1213.2	1216.9	1214.0	1215.4
12.5°	1191.8	1214.7	1216.2	1242.0	1253.8	1255.3	1267.1	1264.9	1272.2	1272.2	1284.8
15°	1217.7	1253.1	1273.0	1298.0	1305.4	1296.6	1306.2	1316.5	1317.2	1317.2	1316.5
17.5°	1264.1	1278.1	1298.0	1311.3	1314.3	1314.3	1315.0	1319.4	1316.5	1310.6	1315.0
20°	1273.7	1279.6	1287.0	1285.5	1287.0	1279.6	1272.2	1264.9	1265.6	1261.9	1273.0
22.5°	1256.0	1254.5	1237.6	1226.5	1226.5	1211.8	1197.7	1191.1	1184.5	1186.7	1190.4
25°	1211.8	1188.9	1168.2	1152.0	1148.3	1124.7	1105.6	1099.7	1088.6	1097.4	1098.9
27.5°	1141.0	1115.1	1082.0	1067.9	1048.8	1039.2	1025.9	1008.2	985.3	998.6	996.4
30°	1065.0	1026.6	999.3	965.4	935.2	933.0	907.9	878.4	866.6	866.6	873.2
32.5°	980.2	929.3	889.5	841.5	812.0	799.5	769.2	739.7	746.4	724.3	732.4
35°	881.3	814.2	764.1	717.6	695.5	680.7	641.6	625.4	607.7	597.4	616.6
37.5°	786.9	709.5	645.3	594.4	586.3	559.8	533.2	522.9	512.6	517.0	516.3
40°	671.9	603.3	545.8	505.9	491.9	479.4	461.7	449.2	442.5	446.2	446.9
42.5°	567.9	510.4	467.6	439.6	427.8	418.9	410.1	399.7	397.5	397.5	400.5
45°	487.5	440.3	411.5	388.7	382.0	375.4	368.8	364.3	362.9	359.9	362.1
47.5°	423.3	385.7	368.0	351.1	343.7	342.2	336.3	334.1	331.1	330.4	331.1
50°	369.5	345.9	329.7	320.1	314.9	312.7	309.8	305.3	303.9	307.5	306.1
52.5°	331.9	309.8	300.9	291.3	288.4	285.4	281.0	281.7	281.0	279.5	279.5
55°	294.3	280.3	271.4	264.0	263.3	260.3	256.7	255.2	254.4	253.0	255.2
57.5°	264.0	253.0	244.9	238.2	235.3	235.3	231.6	228.6	228.6	227.9	228.6
60°	233.8	222.7	217.6	210.9	208.7	208.0	205.8	204.3	202.1	202.1	202.1
62.5°	205.8	196.9	191.0	185.1	185.9	182.2	179.2	177.7	177.7	178.5	178.5
65°	179.2	173.3	165.9	160.8	159.3	158.6	157.1	156.4	154.1	155.6	155.6
67.5°	154.9	146.8	142.3	140.1	137.9	137.2	135.7	134.2	133.5	132.8	134.2
70°	130.5	123.9	120.2	118.7	116.5	115.8	115.1	112.8	113.6	114.3	115.1
72.5°	108.4	102.5	101.8	97.4	97.4	97.4	94.4	95.9	95.1	93.7	95.1
75°	85.6	82.6	81.1	78.9	79.7	78.9	78.2	76.0	76.0	76.7	77.4
77.5°	67.9	64.9	64.2	62.0	60.5	62.0	60.5	59.7	59.7	60.5	60.5
80°	50.2	48.7	46.5	46.5	46.5	45.7	45.7	45.7	45.0	44.3	45.0
82.5°	33.2	33.2	32.5	31.7	32.5	31.0	31.7	31.7	31.7	31.7	31.7
85°	21.4	20.7	20.7	19.9	19.9	19.9	20.7	19.2	19.2	19.9	19.9
87.5°	9.6	9.6	9.6	10.3	9.6	9.6	9.6	10.3	9.6	9.6	9.6
90°	22.3	23.4	24.6	25.7	26.3	26.5	27.0	27.5	27.9	28.4	27.9
92.5°	25.8	26.2	26.7	27.2	27.4	27.5	27.7	28.0	28.2	28.4	28.2
95°	42.3	43.4	44.6	45.7	46.3	46.2	46.0	45.7	45.5	45.3	45.5
97.5°	54.4	55.1	55.8	56.5	56.9	57.0	57.2	57.5	57.7	57.9	57.7
100°	61.9	63.8	65.7	67.6	68.5	68.7	69.2	69.7	70.1	70.6	70.1
102.5°	64.7	67.3	69.8	72.4	73.7	74.1	74.8	75.5	76.2	76.9	76.2
105°	66.9	69.4	72.0	74.5	75.8	76.3	77.2	78.1	79.1	80.0	79.1
107.5°	69.0	71.5	74.1	76.6	77.9	78.4	79.3	80.3	81.2	82.2	81.2
110°	160.9	137.5	114.1	90.7	79.0	79.5	80.4	81.3	82.3	83.2	82.3

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	434.2	333.3	232.4	131.5	81.1	81.5	82.2	82.9	83.6	84.3	83.6
115°	541.5	433.1	324.8	216.4	162.2	153.8	136.9	120.1	103.2	86.4	103.2
117.5°	673.3	639.8	606.3	572.8	556.1	525.4	464.1	402.8	341.5	280.2	341.5
120°	774.9	777.7	780.5	783.3	784.7	768.9	737.3	705.7	674.1	642.5	674.1
122.5°	835.6	837.0	838.4	839.8	840.5	840.6	840.9	841.1	841.4	841.6	841.4
125°	891.6	893.3	894.9	896.6	897.4	897.8	898.5	899.2	899.9	900.6	899.9
127.5°	944.0	946.3	948.7	951.0	952.2	952.3	952.5	952.8	953.0	953.2	953.0
130°	993.7	996.3	998.8	1001.4	1002.7	1002.6	1002.4	1002.1	1001.9	1001.7	1001.9
132.5°	1042.7	1044.8	1046.9	1049.0	1050.1	1050.0	1049.8	1049.5	1049.3	1049.1	1049.3
135°	1088.3	1090.6	1093.0	1095.3	1096.5	1096.3	1095.8	1095.3	1094.9	1094.4	1094.9
137.5°	1131.5	1133.8	1136.2	1138.5	1139.7	1139.3	1138.6	1137.9	1137.2	1136.5	1137.2
140°	1173.4	1175.5	1177.6	1179.7	1180.7	1180.1	1179.0	1177.8	1176.7	1175.5	1176.7
142.5°	1212.1	1214.0	1215.9	1217.8	1218.7	1218.1	1216.9	1215.8	1214.6	1213.4	1214.6
145°	1247.6	1249.3	1250.9	1252.6	1253.4	1252.8	1251.6	1250.5	1249.3	1248.1	1249.3
147.5°	1279.9	1281.1	1282.2	1283.4	1284.0	1283.5	1282.6	1281.6	1280.7	1279.7	1280.7
150°	1308.5	1309.9	1311.4	1312.8	1313.5	1312.9	1311.7	1310.6	1309.4	1308.2	1309.4
152.5°	1334.9	1336.3	1337.7	1339.1	1339.8	1339.0	1337.3	1335.7	1334.0	1332.4	1334.0
155°	1358.0	1359.4	1360.9	1362.3	1363.0	1362.1	1360.2	1358.3	1356.4	1354.5	1356.4
157.5°	1378.2	1379.9	1381.5	1383.2	1384.0	1383.1	1381.2	1379.3	1377.5	1375.6	1377.5
160°	1396.0	1397.4	1398.8	1400.2	1400.9	1400.1	1398.4	1396.8	1395.1	1393.5	1395.1
162.5°	1412.0	1413.6	1415.3	1416.9	1417.7	1416.6	1414.5	1412.4	1410.3	1408.2	1410.3
165°	1424.6	1426.3	1427.9	1429.6	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1424.6
167.5°	1436.2	1437.9	1439.5	1441.2	1442.0	1440.9	1438.8	1436.7	1434.6	1432.5	1434.6
170°	1444.6	1446.3	1447.9	1449.6	1450.4	1449.3	1447.2	1445.1	1443.0	1440.9	1443.0
172.5°	1450.9	1452.6	1454.2	1455.9	1456.7	1455.6	1453.5	1451.4	1449.3	1447.2	1449.3
175°	1455.1	1456.8	1458.4	1460.1	1460.9	1459.7	1457.4	1455.1	1452.7	1450.4	1452.7
177.5°	1456.2	1457.9	1459.5	1461.2	1462.0	1460.9	1458.8	1456.7	1454.6	1452.5	1454.6
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	1017.1	1011.9	1007.5	1008.2	1011.9	1008.9	1001.6	992.0	988.3	983.9	988.3
5°	1078.3	1073.8	1065.0	1065.7	1063.5	1060.6	1048.8	1034.0	1034.0	1022.2	1020.7
7.5°	1138.7	1132.1	1126.2	1124.7	1116.6	1110.7	1100.4	1079.7	1071.6	1057.6	1049.5
10°	1206.6	1201.4	1194.8	1186.7	1182.3	1171.9	1155.0	1124.7	1110.0	1090.8	1076.8
12.5°	1275.2	1274.4	1259.7	1243.5	1242.7	1226.5	1214.7	1174.1	1154.2	1128.4	1095.2
15°	1318.7	1315.0	1306.9	1298.8	1301.0	1283.3	1256.7	1208.8	1195.5	1164.6	1129.2
17.5°	1318.0	1318.0	1315.7	1314.3	1312.1	1306.9	1292.1	1260.4	1239.0	1200.0	1166.8
20°	1275.9	1285.5	1287.7	1287.0	1294.4	1298.0	1297.3	1277.4	1260.4	1225.8	1191.8
22.5°	1191.8	1214.0	1223.6	1229.5	1244.9	1253.1	1272.2	1264.9	1260.4	1234.6	1205.9
25°	1113.7	1121.0	1149.8	1151.3	1172.7	1192.6	1211.8	1224.3	1240.5	1230.9	1206.6
27.5°	1012.6	1029.6	1050.2	1065.7	1070.2	1110.7	1142.4	1166.0	1202.9	1205.9	1197.7
30°	898.3	906.4	940.3	961.0	984.6	1014.1	1059.8	1100.4	1133.6	1163.8	1174.1
32.5°	758.9	792.1	812.0	837.1	857.7	910.1	966.2	1018.5	1056.9	1107.8	1129.9
35°	631.3	657.1	691.1	701.4	739.0	783.3	856.3	923.4	981.6	1033.3	1078.3
37.5°	525.9	546.5	582.6	598.9	621.0	677.8	739.0	822.3	892.4	955.8	1011.9
40°	453.6	469.1	496.4	501.5	520.0	571.6	621.0	699.2	792.1	877.7	938.9
42.5°	404.2	411.5	430.0	436.6	448.4	483.1	527.3	601.1	687.4	775.9	862.2
45°	368.8	373.9	385.0	390.9	405.6	421.1	457.3	516.3	584.1	673.4	766.3
47.5°	337.0	343.7	348.1	351.8	359.9	376.9	400.5	444.0	508.9	590.8	680.7
50°	310.5	312.7	320.8	321.6	326.7	337.8	359.9	386.5	438.1	504.5	591.5
52.5°	283.9	286.2	291.3	296.5	298.7	307.5	322.3	344.4	382.8	435.1	512.6
55°	257.4	260.3	265.5	269.2	271.4	278.8	287.6	309.0	339.3	376.1	439.6
57.5°	230.8	237.5	239.0	241.2	244.9	253.0	261.1	273.6	297.2	331.1	377.6
60°	205.8	208.0	213.1	215.4	219.0	223.5	233.8	243.4	260.3	286.9	328.9
62.5°	180.0	185.1	187.3	189.5	192.5	197.7	204.3	214.6	229.4	250.8	283.9
65°	157.8	158.6	163.0	165.9	168.9	172.6	179.2	188.8	197.7	217.6	241.9
67.5°	136.4	137.9	139.4	142.3	146.0	149.7	155.6	160.8	171.8	185.1	204.3
70°	115.8	115.8	119.5	121.7	121.0	125.4	129.8	135.7	143.8	156.4	171.8
72.5°	97.4	96.6	99.6	100.3	101.8	104.7	107.7	113.6	118.0	127.6	139.4
75°	77.4	78.9	80.4	80.4	82.6	84.8	87.8	90.7	95.9	101.8	110.6
77.5°	61.2	61.2	62.7	63.4	65.6	64.9	67.9	70.8	74.5	79.7	86.3
80°	45.0	46.5	46.5	46.5	47.2	47.9	50.9	53.1	55.3	59.0	62.0
82.5°	31.7	31.7	33.2	33.2	33.2	34.7	34.7	35.4	36.9	39.1	41.3
85°	19.9	19.9	19.9	20.7	19.9	20.7	22.1	21.4	22.1	23.6	23.6
87.5°	9.6	9.6	9.6	9.6	9.6	10.3	9.6	10.3	11.1	11.1	11.1
90°	27.5	27.0	26.5	26.3	25.7	24.6	23.4	22.3	21.1	19.2	17.3
92.5°	28.0	27.7	27.5	27.4	27.2	26.7	26.2	25.8	25.3	24.6	23.9
95°	45.7	46.0	46.2	46.3	45.7	44.6	43.4	42.3	41.1	39.5	37.8
97.5°	57.5	57.2	57.0	56.9	56.5	55.8	55.1	54.4	53.7	50.0	46.2
100°	69.7	69.2	68.7	68.5	67.6	65.7	63.8	61.9	60.0	56.0	52.0
102.5°	75.5	74.8	74.1	73.7	72.4	69.8	67.3	64.7	62.1	104.7	147.3
105°	78.1	77.2	76.3	75.8	74.5	72.0	69.4	66.9	64.3	128.2	192.1
107.5°	80.3	79.3	78.4	77.9	76.6	74.1	71.5	69.0	66.4	145.3	224.1
110°	81.3	80.4	79.5	79.0	90.7	114.1	137.5	160.9	184.3	251.9	319.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	82.9	82.2	81.5	81.1	131.5	232.4	333.3	434.2	535.1	539.1	543.1
115°	120.1	136.9	153.8	162.2	216.4	324.8	433.1	541.5	649.9	644.0	638.2
117.5°	402.8	464.1	525.4	556.1	572.8	606.3	639.8	673.3	706.8	702.8	698.8
120°	705.7	737.3	768.9	784.7	783.3	780.5	777.7	774.9	772.1	767.9	763.7
122.5°	841.1	840.9	840.6	840.5	839.8	838.4	837.0	835.6	834.2	829.5	824.8
125°	899.2	898.5	897.8	897.4	896.6	894.9	893.3	891.6	890.0	885.6	881.1
127.5°	952.8	952.5	952.3	952.2	951.0	948.7	946.3	944.0	941.6	938.1	934.6
130°	1002.1	1002.4	1002.6	1002.7	1001.4	998.8	996.3	993.7	991.1	988.5	986.0
132.5°	1049.5	1049.8	1050.0	1050.1	1049.0	1046.9	1044.8	1042.7	1040.6	1038.0	1035.5
135°	1095.3	1095.8	1096.3	1096.5	1095.3	1093.0	1090.6	1088.3	1085.9	1083.8	1081.7
137.5°	1137.9	1138.6	1139.3	1139.7	1138.5	1136.2	1133.8	1131.5	1129.1	1126.8	1124.4
140°	1177.8	1179.0	1180.1	1180.7	1179.7	1177.6	1175.5	1173.4	1171.3	1168.7	1166.1
142.5°	1215.8	1216.9	1218.1	1218.7	1217.8	1215.9	1214.0	1212.1	1210.2	1207.2	1204.1
145°	1250.5	1251.6	1252.8	1253.4	1252.6	1250.9	1249.3	1247.6	1246.0	1242.0	1238.0
147.5°	1281.6	1282.6	1283.5	1284.0	1283.4	1282.2	1281.1	1279.9	1278.7	1274.7	1270.7
150°	1310.6	1311.7	1312.9	1313.5	1312.8	1311.4	1309.9	1308.5	1307.1	1303.4	1299.6
152.5°	1335.7	1337.3	1339.0	1339.8	1339.1	1337.7	1336.3	1334.9	1333.5	1330.0	1326.5
155°	1358.3	1360.2	1362.1	1363.0	1362.3	1360.9	1359.4	1358.0	1356.6	1353.8	1351.0
157.5°	1379.3	1381.2	1383.1	1384.0	1383.2	1381.5	1379.9	1378.2	1376.6	1374.5	1372.4
160°	1396.8	1398.4	1400.1	1400.9	1400.2	1398.8	1397.4	1396.0	1394.6	1393.2	1391.8
162.5°	1412.4	1414.5	1416.6	1417.7	1416.9	1415.3	1413.6	1412.0	1410.4	1409.2	1408.0
165°	1426.3	1427.9	1429.6	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1422.3	1421.6
167.5°	1436.7	1438.8	1440.9	1442.0	1441.2	1439.5	1437.9	1436.2	1434.6	1433.9	1433.2
170°	1445.1	1447.2	1449.3	1450.4	1449.6	1447.9	1446.3	1444.6	1443.0	1442.5	1442.1
172.5°	1451.4	1453.5	1455.6	1456.7	1455.9	1454.2	1452.6	1450.9	1449.3	1448.8	1448.4
175°	1455.1	1457.4	1459.7	1460.9	1460.1	1458.4	1456.8	1455.1	1453.5	1453.0	1452.6
177.5°	1456.7	1458.8	1460.9	1462.0	1461.2	1459.5	1457.9	1456.2	1454.6	1454.4	1454.1
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	984.6	980.9	978.7	980.2	975.7	964.7	964.7	968.4	963.9	959.5	952.9
5°	1011.9	1004.5	1000.1	999.3	989.0	971.3	967.6	963.9	954.4	944.0	933.0
7.5°	1038.4	1025.2	1017.8	1012.6	997.9	975.0	965.4	957.3	941.8	926.3	912.3
10°	1060.6	1041.4	1032.5	1024.4	1005.2	976.5	961.0	946.2	926.3	906.4	888.7
12.5°	1078.3	1056.1	1045.1	1033.3	1009.7	972.1	952.9	929.3	909.4	882.8	865.1
15°	1107.8	1062.0	1051.7	1040.7	1016.3	964.7	941.1	914.5	887.2	851.8	832.7
17.5°	1131.4	1070.2	1069.4	1045.8	1014.1	961.7	925.6	890.9	861.4	826.0	795.8
20°	1145.4	1082.7	1070.9	1046.6	1006.7	941.8	904.2	865.9	834.1	791.4	761.1
22.5°	1157.2	1100.4	1069.4	1039.9	991.2	935.2	879.9	843.7	800.2	753.8	725.0
25°	1161.6	1104.1	1071.6	1037.7	980.2	916.0	853.3	814.2	765.6	723.5	684.4
27.5°	1162.3	1103.3	1063.5	1028.1	964.7	890.9	826.8	785.5	731.6	683.0	643.9
30°	1155.0	1095.2	1059.1	1020.7	949.9	868.1	794.3	748.6	691.1	642.4	601.8
32.5°	1132.8	1079.0	1049.5	1007.5	930.8	836.4	763.3	712.5	652.0	604.0	564.9
35°	1096.0	1059.1	1026.6	987.5	905.7	806.9	732.4	672.6	611.4	565.7	528.8
37.5°	1050.2	1030.3	1000.1	961.7	876.9	780.3	697.7	631.3	570.1	525.9	489.7
40°	988.3	993.4	963.9	929.3	843.0	744.2	652.7	589.3	531.8	490.5	455.1
42.5°	921.2	942.6	925.6	892.4	805.4	704.3	619.5	549.5	493.4	450.6	421.1
45°	848.9	885.8	875.4	851.1	766.3	662.3	572.3	504.5	455.1	413.8	387.9
47.5°	770.0	822.3	822.3	804.6	722.8	620.3	531.8	462.4	413.8	384.3	359.2
50°	689.6	748.6	758.2	746.4	674.1	572.3	482.3	419.7	377.6	348.9	330.4
52.5°	605.5	674.1	691.8	685.9	622.5	526.6	441.8	380.6	342.2	317.1	300.9
55°	525.1	604.8	623.9	626.2	567.2	476.4	396.8	343.0	306.1	289.1	275.1
57.5°	449.2	525.9	547.2	550.9	511.1	430.7	354.8	307.5	274.4	260.3	249.3
60°	384.3	448.4	476.4	484.6	449.9	377.6	315.7	269.9	244.9	231.6	221.3
62.5°	331.1	382.8	412.3	414.5	399.0	331.1	275.1	236.7	215.4	203.6	198.4
65°	279.5	326.0	343.7	352.5	340.0	286.9	237.5	205.8	188.8	178.5	173.3
67.5°	238.2	267.7	282.5	294.3	281.7	241.9	202.1	176.3	163.7	153.4	150.5
70°	195.4	219.8	230.8	242.6	231.6	201.3	172.6	149.0	137.9	129.8	126.1
72.5°	156.4	175.5	185.9	193.2	186.6	161.5	137.9	121.7	113.6	107.7	105.5
75°	123.9	137.2	143.1	148.2	145.3	126.1	111.4	98.1	90.7	85.6	84.1
77.5°	94.4	104.0	110.6	112.1	108.4	95.9	83.3	75.2	69.3	66.4	64.9
80°	67.1	73.0	76.7	78.9	75.2	70.1	61.2	55.3	50.2	46.5	45.7
82.5°	45.0	47.9	50.9	50.2	48.7	44.3	39.1	36.1	33.9	31.0	31.0
85°	25.8	26.6	28.0	28.8	28.0	25.1	22.1	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.5	11.1	11.1	9.6	8.1	8.1	7.4	6.6
90°	15.4	13.5	12.6	11.3	8.8	6.2	3.7	1.1	3.7	6.2	8.8
92.5°	23.2	22.5	22.1	22.6	23.5	24.4	25.4	26.3	25.4	24.4	23.5
95°	36.2	34.5	33.7	37.6	45.3	53.0	60.8	68.5	60.8	53.0	45.3
97.5°	42.5	38.8	36.9	46.5	65.7	84.8	104.0	123.2	104.0	84.8	65.7
100°	48.1	44.1	42.1	58.1	90.2	122.3	154.3	186.4	154.3	122.3	90.2
102.5°	189.9	232.5	253.8	254.0	254.5	255.0	255.4	255.9	255.4	255.0	254.5
105°	256.0	319.9	351.8	348.3	341.3	334.2	327.2	320.2	327.2	334.2	341.3
107.5°	303.0	381.9	421.3	418.4	412.5	406.7	400.8	395.0	400.8	406.7	412.5
110°	387.2	454.9	488.7	486.2	481.3	476.4	471.5	466.6	471.5	476.4	481.3

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	547.0	551.0	553.0	550.9	546.7	542.4	538.2	534.0	538.2	542.4	546.7
115°	632.3	626.4	623.5	621.5	617.5	613.6	609.6	605.6	609.6	613.6	617.5
117.5°	694.9	690.9	688.9	686.6	681.9	677.2	672.5	667.8	672.5	677.2	681.9
120°	759.4	755.2	753.1	751.3	747.8	744.3	740.8	737.3	740.8	744.3	747.8
122.5°	820.1	815.4	813.1	811.2	807.5	803.8	800.0	796.3	800.0	803.8	807.5
125°	876.7	872.2	870.0	868.5	865.4	862.4	859.3	856.3	859.3	862.4	865.4
127.5°	931.1	927.6	925.8	924.2	920.9	917.6	914.4	911.1	914.4	917.6	920.9
130°	983.4	980.9	979.6	977.7	974.0	970.2	966.5	962.7	966.5	970.2	974.0
132.5°	1032.9	1030.4	1029.1	1027.6	1024.5	1021.5	1018.4	1015.4	1018.4	1021.5	1024.5
135°	1079.6	1077.5	1076.5	1074.6	1070.9	1067.1	1063.4	1059.6	1063.4	1067.1	1070.9
137.5°	1122.1	1119.8	1118.6	1117.2	1114.4	1111.6	1108.8	1106.0	1108.8	1111.6	1114.4
140°	1163.6	1161.0	1159.7	1158.8	1156.9	1155.0	1153.1	1151.2	1153.1	1155.0	1156.9
142.5°	1201.1	1198.0	1196.5	1195.7	1194.1	1192.4	1190.8	1189.2	1190.8	1192.4	1194.1
145°	1234.1	1230.1	1228.1	1228.2	1228.5	1228.7	1229.0	1229.2	1229.0	1228.7	1228.5
147.5°	1266.8	1262.8	1260.8	1261.1	1261.8	1262.5	1263.2	1263.9	1263.2	1262.5	1261.8
150°	1295.9	1292.2	1290.3	1291.1	1292.8	1294.4	1296.1	1297.7	1296.1	1294.4	1292.8
152.5°	1323.0	1319.5	1317.7	1318.6	1320.5	1322.4	1324.2	1326.1	1324.2	1322.4	1320.5
155°	1348.2	1345.4	1344.0	1345.1	1347.2	1349.3	1351.4	1353.5	1351.4	1349.3	1347.2
157.5°	1370.3	1368.2	1367.2	1368.1	1370.0	1371.9	1373.7	1375.6	1373.7	1371.9	1370.0
160°	1390.3	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6	1393.2	1391.8	1390.3
162.5°	1406.9	1405.7	1405.1	1405.8	1407.2	1408.6	1410.0	1411.4	1410.0	1408.6	1407.2
165°	1420.9	1420.2	1419.8	1420.5	1421.9	1423.4	1424.8	1426.2	1424.8	1423.4	1421.9
167.5°	1432.5	1431.8	1431.4	1432.1	1433.5	1434.9	1436.3	1437.7	1436.3	1434.9	1433.5
170°	1441.6	1441.1	1440.9	1441.6	1443.0	1444.4	1445.8	1447.2	1445.8	1444.4	1443.0
172.5°	1447.9	1447.4	1447.2	1447.9	1449.3	1450.7	1452.1	1453.5	1452.1	1450.7	1449.3
175°	1452.1	1451.6	1451.4	1452.2	1453.9	1455.5	1457.2	1458.8	1457.2	1455.5	1453.9
177.5°	1453.9	1453.6	1453.5	1454.3	1456.0	1457.6	1459.3	1460.9	1459.3	1457.6	1456.0
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	949.2	952.9	952.1	944.8	936.7	930.0	917.5	919.0	914.5	915.3	919.7
5°	925.6	925.6	922.6	912.3	899.0	891.7	877.7	874.0	865.1	864.4	863.6
7.5°	900.5	896.8	893.1	878.4	862.2	850.4	831.2	826.8	817.9	812.0	809.1
10°	871.0	865.9	858.5	841.5	821.6	806.9	786.9	781.0	764.1	756.7	752.3
12.5°	838.6	835.6	823.8	809.8	777.4	761.1	732.4	738.3	721.3	706.6	704.3
15°	806.1	795.1	788.4	765.6	726.5	719.1	696.2	684.4	668.9	657.1	657.1
17.5°	774.4	757.4	742.7	718.4	689.6	668.9	652.0	646.1	626.9	615.1	612.9
20°	732.4	713.2	709.5	674.8	654.9	632.1	615.8	601.1	587.1	581.9	578.2
22.5°	692.5	670.4	664.5	635.0	615.1	592.2	576.0	565.7	555.4	551.7	545.0
25°	649.8	636.5	627.6	595.9	573.8	552.4	541.3	534.0	524.4	523.6	519.2
27.5°	608.5	595.9	587.1	556.8	540.6	520.7	511.8	503.7	498.6	496.4	494.1
30°	573.1	559.0	548.7	526.6	506.7	490.5	483.1	477.9	475.0	471.3	470.5
32.5°	534.0	525.9	511.8	494.9	479.4	463.9	459.5	455.8	451.4	449.9	449.2
35°	500.8	489.7	480.9	461.7	455.1	441.8	436.6	433.7	427.8	426.3	424.8
37.5°	468.3	458.0	448.4	436.6	424.1	416.7	413.8	409.3	406.4	407.1	405.6
40°	435.9	427.8	420.4	407.9	400.5	396.8	390.9	386.5	385.0	385.7	385.0
42.5°	404.2	396.8	392.4	382.8	375.4	371.7	368.0	363.6	365.8	365.8	368.0
45°	375.4	368.8	365.8	358.4	354.0	348.1	344.4	343.7	346.6	345.9	345.9
47.5°	345.9	343.7	340.0	333.4	327.5	323.8	323.0	323.0	326.0	327.5	326.7
50°	323.0	318.6	314.2	309.0	304.6	303.1	300.9	302.4	305.3	305.3	306.8
52.5°	294.3	291.3	289.8	285.4	282.5	282.5	282.5	283.2	285.4	287.6	286.9
55°	269.2	267.0	265.5	263.3	259.6	260.3	259.6	261.1	263.3	265.5	267.0
57.5°	242.6	241.9	240.4	236.7	236.7	236.0	238.2	239.0	242.6	244.1	246.3
60°	219.0	216.8	216.8	213.9	213.9	213.9	216.1	218.3	221.3	222.0	223.5
62.5°	194.0	194.0	193.2	191.0	191.0	193.2	194.0	196.9	198.4	198.4	200.6
65°	170.4	169.6	168.9	169.6	170.4	170.4	172.6	174.1	175.5	176.3	177.0
67.5°	146.8	146.0	147.5	146.8	148.2	151.2	150.5	152.7	154.9	154.9	155.6
70°	124.6	126.1	125.4	126.9	126.1	127.6	129.8	130.5	130.5	131.3	133.5
72.5°	104.0	104.0	104.0	103.3	104.0	105.5	106.9	107.7	109.2	109.9	112.1
75°	84.1	84.1	82.6	84.1	84.1	85.6	87.0	87.0	87.0	88.5	90.7
77.5°	63.4	64.2	63.4	64.9	64.9	65.6	67.1	66.4	67.9	68.6	69.3
80°	46.5	45.7	45.7	45.7	46.5	46.5	47.9	48.7	48.7	50.9	49.4
82.5°	29.5	30.2	29.5	30.2	30.2	31.0	30.2	31.0	31.7	33.2	32.5
85°	17.0	16.2	16.2	17.0	16.2	16.2	17.0	16.2	17.0	16.2	17.0
87.5°	6.6	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	11.3	12.6	13.5	15.4	17.3	19.2	21.1	22.3	23.4	24.6	25.7
92.5°	22.6	22.1	22.5	23.2	23.9	24.6	25.3	25.8	26.2	26.7	27.2
95°	37.6	33.7	34.5	36.2	37.8	39.5	41.1	42.3	43.4	44.6	45.7
97.5°	46.5	36.9	38.8	42.5	46.2	50.0	53.7	54.4	55.1	55.8	56.5
100°	58.1	42.1	44.1	48.1	52.0	56.0	60.0	61.9	63.8	65.7	67.6
102.5°	254.0	253.8	232.5	189.9	147.3	104.7	62.1	64.7	67.3	69.8	72.4
105°	348.3	351.8	319.9	256.0	192.1	128.2	64.3	66.9	69.4	72.0	74.5
107.5°	418.4	421.3	381.9	303.0	224.1	145.3	66.4	69.0	71.5	74.1	76.6
110°	486.2	488.7	454.9	387.2	319.6	251.9	184.3	160.9	137.5	114.1	90.7

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	550.9	553.0	551.0	547.0	543.1	539.1	535.1	434.2	333.3	232.4	131.5
115°	621.5	623.5	626.4	632.3	638.2	644.0	649.9	541.5	433.1	324.8	216.4
117.5°	686.6	688.9	690.9	694.9	698.8	702.8	706.8	673.3	639.8	606.3	572.8
120°	751.3	753.1	755.2	759.4	763.7	767.9	772.1	774.9	777.7	780.5	783.3
122.5°	811.2	813.1	815.4	820.1	824.8	829.5	834.2	835.6	837.0	838.4	839.8
125°	868.5	870.0	872.2	876.7	881.1	885.6	890.0	891.6	893.3	894.9	896.6
127.5°	924.2	925.8	927.6	931.1	934.6	938.1	941.6	944.0	946.3	948.7	951.0
130°	977.7	979.6	980.9	983.4	986.0	988.5	991.1	993.7	996.3	998.8	1001.4
132.5°	1027.6	1029.1	1030.4	1032.9	1035.5	1038.0	1040.6	1042.7	1044.8	1046.9	1049.0
135°	1074.6	1076.5	1077.5	1079.6	1081.7	1083.8	1085.9	1088.3	1090.6	1093.0	1095.3
137.5°	1117.2	1118.6	1119.8	1122.1	1124.4	1126.8	1129.1	1131.5	1133.8	1136.2	1138.5
140°	1158.8	1159.7	1161.0	1163.6	1166.1	1168.7	1171.3	1173.4	1175.5	1177.6	1179.7
142.5°	1195.7	1196.5	1198.0	1201.1	1204.1	1207.2	1210.2	1212.1	1214.0	1215.9	1217.8
145°	1228.2	1228.1	1230.1	1234.1	1238.0	1242.0	1246.0	1247.6	1249.3	1250.9	1252.6
147.5°	1261.1	1260.8	1262.8	1266.8	1270.7	1274.7	1278.7	1279.9	1281.1	1282.2	1283.4
150°	1291.1	1290.3	1292.2	1295.9	1299.6	1303.4	1307.1	1308.5	1309.9	1311.4	1312.8
152.5°	1318.6	1317.7	1319.5	1323.0	1326.5	1330.0	1333.5	1334.9	1336.3	1337.7	1339.1
155°	1345.1	1344.0	1345.4	1348.2	1351.0	1353.8	1356.6	1358.0	1359.4	1360.9	1362.3
157.5°	1368.1	1367.2	1368.2	1370.3	1372.4	1374.5	1376.6	1378.2	1379.9	1381.5	1383.2
160°	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6	1396.0	1397.4	1398.8	1400.2
162.5°	1405.8	1405.1	1405.7	1406.9	1408.0	1409.2	1410.4	1412.0	1413.6	1415.3	1416.9
165°	1420.5	1419.8	1420.2	1420.9	1421.6	1422.3	1423.0	1424.6	1426.3	1427.9	1429.6
167.5°	1432.1	1431.4	1431.8	1432.5	1433.2	1433.9	1434.6	1436.2	1437.9	1439.5	1441.2
170°	1441.6	1440.9	1441.1	1441.6	1442.1	1442.5	1443.0	1444.6	1446.3	1447.9	1449.6
172.5°	1447.9	1447.2	1447.4	1447.9	1448.4	1448.8	1449.3	1450.9	1452.6	1454.2	1455.9
175°	1452.2	1451.4	1451.6	1452.1	1452.6	1453.0	1453.5	1455.1	1456.8	1458.4	1460.1
177.5°	1454.3	1453.5	1453.6	1453.9	1454.1	1454.4	1454.6	1456.2	1457.9	1459.5	1461.2
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	914.5	916.7	911.6	910.1	911.6	906.4	907.9	909.4	909.4	911.6	913.1
5°	861.4	858.5	853.3	851.8	850.4	852.6	851.1	853.3	854.1	859.2	860.0
7.5°	809.1	804.6	800.2	795.8	794.3	790.6	794.3	794.3	799.5	798.0	801.7
10°	747.1	746.4	740.5	738.3	735.3	729.4	737.5	735.3	739.0	745.6	747.1
12.5°	701.4	693.3	697.0	686.6	690.3	684.4	685.2	685.2	691.1	691.8	690.3
15°	657.9	651.2	641.6	637.2	635.0	632.1	641.6	642.4	638.0	648.3	644.6
17.5°	613.6	613.6	604.8	602.6	596.7	599.6	598.1	598.9	597.4	604.8	608.5
20°	575.3	571.6	568.6	569.4	562.0	560.5	559.0	560.5	565.7	570.8	572.3
22.5°	544.3	542.1	534.7	536.2	530.3	532.5	531.0	534.7	535.4	535.4	540.6
25°	514.8	511.8	512.6	509.6	507.4	507.4	505.2	507.4	510.4	511.8	512.6
27.5°	492.7	490.5	486.8	484.6	486.0	482.3	485.3	487.5	487.5	486.0	487.5
30°	466.1	467.6	467.6	460.2	463.2	461.7	463.9	465.4	465.4	466.1	464.6
32.5°	448.4	444.0	443.3	442.5	442.5	439.6	439.6	441.8	442.5	443.3	445.5
35°	424.8	424.8	421.1	423.3	420.4	421.1	420.4	421.1	422.6	420.4	422.6
37.5°	403.4	404.2	402.7	404.2	404.9	403.4	402.0	404.9	403.4	403.4	402.0
40°	385.0	384.3	385.0	385.0	385.0	385.7	384.3	384.3	384.3	382.8	381.3
42.5°	369.5	365.1	366.6	367.3	365.1	365.1	365.8	365.1	367.3	362.9	362.9
45°	347.4	345.9	346.6	346.6	348.1	345.9	347.4	348.1	345.9	345.2	343.7
47.5°	327.5	328.9	327.5	328.9	328.9	330.4	327.5	328.2	328.9	326.0	323.8
50°	307.5	307.5	309.8	309.0	309.8	308.3	308.3	307.5	308.3	306.8	304.6
52.5°	289.1	286.9	290.6	289.8	289.1	288.4	287.6	288.4	286.9	285.4	285.4
55°	266.2	266.2	268.5	269.2	269.2	267.7	266.2	267.0	266.2	265.5	264.8
57.5°	247.8	244.9	246.3	247.1	247.1	244.9	246.3	244.9	244.9	245.6	243.4
60°	224.2	224.2	222.7	224.9	224.9	223.5	223.5	224.2	222.7	222.0	221.3
62.5°	199.1	199.9	202.1	202.8	203.6	202.1	200.6	201.3	201.3	199.1	199.9
65°	177.7	179.2	182.2	181.4	180.0	180.7	179.2	180.0	177.7	178.5	176.3
67.5°	157.1	156.4	157.1	157.1	158.6	157.8	156.4	156.4	155.6	157.8	155.6
70°	135.0	135.0	135.0	135.0	135.7	136.4	135.0	133.5	134.2	132.8	132.0
72.5°	112.1	112.8	112.1	113.6	111.4	112.8	112.8	112.1	111.4	111.4	111.4
75°	90.7	92.2	90.0	90.7	90.0	91.5	90.7	90.7	89.2	88.5	89.2
77.5°	69.3	70.1	68.6	69.3	68.6	69.3	69.3	68.6	68.6	68.6	68.6
80°	49.4	50.2	49.4	48.7	47.9	49.4	47.9	48.7	49.4	48.7	50.2
82.5°	31.7	31.7	31.0	31.7	30.2	30.2	31.0	31.0	30.2	31.7	30.2
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.2	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	26.3	26.5	27.0	27.5	27.9	28.4	27.9	27.5	27.0	26.5	26.3
92.5°	27.4	27.5	27.7	28.0	28.2	28.4	28.2	28.0	27.7	27.5	27.4
95°	46.3	46.2	46.0	45.7	45.5	45.3	45.5	45.7	46.0	46.2	46.3
97.5°	56.9	57.0	57.2	57.5	57.7	57.9	57.7	57.5	57.2	57.0	56.9
100°	68.5	68.7	69.2	69.7	70.1	70.6	70.1	69.7	69.2	68.7	68.5
102.5°	73.7	74.1	74.8	75.5	76.2	76.9	76.2	75.5	74.8	74.1	73.7
105°	75.8	76.3	77.2	78.1	79.1	80.0	79.1	78.1	77.2	76.3	75.8
107.5°	77.9	78.4	79.3	80.3	81.2	82.2	81.2	80.3	79.3	78.4	77.9
110°	79.0	79.5	80.4	81.3	82.3	83.2	82.3	81.3	80.4	79.5	79.0

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	81.1	81.5	82.2	82.9	83.6	84.3	83.6	82.9	82.2	81.5	81.1
115°	162.2	153.8	136.9	120.1	103.2	86.4	103.2	120.1	136.9	153.8	162.2
117.5°	556.1	525.4	464.1	402.8	341.5	280.2	341.5	402.8	464.1	525.4	556.1
120°	784.7	768.9	737.3	705.7	674.1	642.5	674.1	705.7	737.3	768.9	784.7
122.5°	840.5	840.6	840.9	841.1	841.4	841.6	841.4	841.1	840.9	840.6	840.5
125°	897.4	897.8	898.5	899.2	899.9	900.6	899.9	899.2	898.5	897.8	897.4
127.5°	952.2	952.3	952.5	952.8	953.0	953.2	953.0	952.8	952.5	952.3	952.2
130°	1002.7	1002.6	1002.4	1002.1	1001.9	1001.7	1001.9	1002.1	1002.4	1002.6	1002.7
132.5°	1050.1	1050.0	1049.8	1049.5	1049.3	1049.1	1049.3	1049.5	1049.8	1050.0	1050.1
135°	1096.5	1096.3	1095.8	1095.3	1094.9	1094.4	1094.9	1095.3	1095.8	1096.3	1096.5
137.5°	1139.7	1139.3	1138.6	1137.9	1137.2	1136.5	1137.2	1137.9	1138.6	1139.3	1139.7
140°	1180.7	1180.1	1179.0	1177.8	1176.7	1175.5	1176.7	1177.8	1179.0	1180.1	1180.7
142.5°	1218.7	1218.1	1216.9	1215.8	1214.6	1213.4	1214.6	1215.8	1216.9	1218.1	1218.7
145°	1253.4	1252.8	1251.6	1250.5	1249.3	1248.1	1249.3	1250.5	1251.6	1252.8	1253.4
147.5°	1284.0	1283.5	1282.6	1281.6	1280.7	1279.7	1280.7	1281.6	1282.6	1283.5	1284.0
150°	1313.5	1312.9	1311.7	1310.6	1309.4	1308.2	1309.4	1310.6	1311.7	1312.9	1313.5
152.5°	1339.8	1339.0	1337.3	1335.7	1334.0	1332.4	1334.0	1335.7	1337.3	1339.0	1339.8
155°	1363.0	1362.1	1360.2	1358.3	1356.4	1354.5	1356.4	1358.3	1360.2	1362.1	1363.0
157.5°	1384.0	1383.1	1381.2	1379.3	1377.5	1375.6	1377.5	1379.3	1381.2	1383.1	1384.0
160°	1400.9	1400.1	1398.4	1396.8	1395.1	1393.5	1395.1	1396.8	1398.4	1400.1	1400.9
162.5°	1417.7	1416.6	1414.5	1412.4	1410.3	1408.2	1410.3	1412.4	1414.5	1416.6	1417.7
165°	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1424.6	1426.3	1427.9	1429.6	1430.4
167.5°	1442.0	1440.9	1438.8	1436.7	1434.6	1432.5	1434.6	1436.7	1438.8	1440.9	1442.0
170°	1450.4	1449.3	1447.2	1445.1	1443.0	1440.9	1443.0	1445.1	1447.2	1449.3	1450.4
172.5°	1456.7	1455.6	1453.5	1451.4	1449.3	1447.2	1449.3	1451.4	1453.5	1455.6	1456.7
175°	1460.9	1459.7	1457.4	1455.1	1452.7	1450.4	1452.7	1455.1	1457.4	1459.7	1460.9
177.5°	1462.0	1460.9	1458.8	1456.7	1454.6	1452.5	1454.6	1456.7	1458.8	1460.9	1462.0
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
2.5°	910.8	916.7	914.5	906.4	916.0	916.0	922.6	922.6	930.8	933.7	938.1
5°	859.2	863.6	867.3	863.6	870.3	880.6	886.5	891.7	902.7	907.2	913.8
7.5°	803.9	812.0	815.7	815.7	826.8	838.6	850.4	857.7	873.2	879.1	885.8
10°	750.1	759.7	767.0	766.3	784.7	792.1	806.9	823.8	839.3	848.2	857.7
12.5°	693.3	698.4	708.8	723.5	727.9	741.2	758.2	779.6	807.6	815.7	829.7
15°	646.1	660.1	668.2	674.8	685.2	697.7	716.1	736.8	764.8	782.5	797.3
17.5°	606.2	624.7	629.8	628.4	641.6	660.8	682.2	697.7	722.8	744.2	758.2
20°	573.8	581.2	590.0	593.7	604.0	624.7	645.3	663.0	683.7	700.7	716.9
22.5°	541.3	547.2	554.6	561.3	569.4	581.2	601.1	623.2	643.1	659.3	677.8
25°	514.8	518.5	525.1	530.3	539.1	547.2	561.3	585.6	609.2	618.8	635.0
27.5°	489.0	491.9	496.4	502.3	506.7	514.8	527.3	547.2	571.6	581.2	603.3
30°	466.1	468.3	472.8	475.7	477.9	487.5	497.1	512.6	531.0	544.3	560.5
32.5°	444.7	446.9	451.4	452.1	455.1	460.2	469.1	483.1	499.3	510.4	524.4
35°	421.1	422.6	427.0	428.5	430.7	435.1	441.8	452.1	466.9	475.0	487.5
37.5°	402.7	402.0	404.9	407.1	410.1	412.3	414.5	424.8	435.9	443.3	452.8
40°	382.8	381.3	382.0	385.0	386.5	389.4	389.4	399.7	407.1	413.0	420.4
42.5°	362.9	362.1	360.7	362.1	363.6	364.3	365.1	372.5	379.8	385.0	393.1
45°	343.0	342.2	340.7	341.5	341.5	343.0	345.2	348.1	353.3	357.7	362.1
47.5°	324.5	323.0	320.8	320.1	321.6	321.6	321.6	324.5	329.7	331.1	335.6
50°	305.3	303.1	300.2	298.7	298.7	298.0	299.4	300.2	304.6	306.1	309.8
52.5°	284.7	283.2	280.3	277.3	278.0	276.6	277.3	278.0	279.5	281.7	283.9
55°	264.0	261.1	258.9	258.1	255.9	255.9	253.7	256.7	255.9	256.7	259.6
57.5°	244.1	241.2	237.5	236.0	233.8	233.1	231.6	230.8	231.6	233.8	236.0
60°	220.5	219.0	216.8	214.6	213.1	210.9	209.5	209.5	208.7	208.7	209.5
62.5°	197.7	196.9	194.0	193.2	191.8	190.3	188.1	186.6	186.6	188.1	188.8
65°	175.5	174.8	172.6	171.8	168.2	166.7	165.9	165.2	163.7	163.7	163.7
67.5°	154.9	152.7	152.7	149.0	146.0	144.6	143.1	142.3	142.3	142.3	143.1
70°	132.0	132.0	129.8	127.6	124.6	125.4	123.2	121.0	121.0	119.5	120.2
72.5°	109.9	109.2	106.9	106.2	104.0	101.8	100.3	101.8	99.6	98.8	99.6
75°	88.5	87.8	86.3	84.8	85.6	83.3	81.1	80.4	80.4	78.9	78.9
77.5°	67.9	69.3	66.4	65.6	64.2	62.7	62.0	61.2	61.2	61.2	62.7
80°	47.2	47.9	47.9	46.5	47.2	45.0	45.0	45.0	42.8	43.5	44.3
82.5°	30.2	30.2	29.5	30.2	29.5	29.5	28.8	28.8	28.0	28.0	28.8
85°	17.0	16.2	15.5	17.0	16.2	16.2	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	25.7	24.6	23.4	22.3	21.1	19.2	17.3	15.4	13.5	12.6	11.3
92.5°	27.2	26.7	26.2	25.8	25.3	24.6	23.9	23.2	22.5	22.1	22.6
95°	45.7	44.6	43.4	42.3	41.1	39.5	37.8	36.2	34.5	33.7	37.6
97.5°	56.5	55.8	55.1	54.4	53.7	50.0	46.2	42.5	38.8	36.9	46.5
100°	67.6	65.7	63.8	61.9	60.0	56.0	52.0	48.1	44.1	42.1	58.1
102.5°	72.4	69.8	67.3	64.7	62.1	104.7	147.3	189.9	232.5	253.8	254.0
105°	74.5	72.0	69.4	66.9	64.3	128.2	192.1	256.0	319.9	351.8	348.3
107.5°	76.6	74.1	71.5	69.0	66.4	145.3	224.1	303.0	381.9	421.3	418.4
110°	90.7	114.1	137.5	160.9	184.3	251.9	319.6	387.2	454.9	488.7	486.2

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	131.5	232.4	333.3	434.2	535.1	539.1	543.1	547.0	551.0	553.0	550.9
115°	216.4	324.8	433.1	541.5	649.9	644.0	638.2	632.3	626.4	623.5	621.5
117.5°	572.8	606.3	639.8	673.3	706.8	702.8	698.8	694.9	690.9	688.9	686.6
120°	783.3	780.5	777.7	774.9	772.1	767.9	763.7	759.4	755.2	753.1	751.3
122.5°	839.8	838.4	837.0	835.6	834.2	829.5	824.8	820.1	815.4	813.1	811.2
125°	896.6	894.9	893.3	891.6	890.0	885.6	881.1	876.7	872.2	870.0	868.5
127.5°	951.0	948.7	946.3	944.0	941.6	938.1	934.6	931.1	927.6	925.8	924.2
130°	1001.4	998.8	996.3	993.7	991.1	988.5	986.0	983.4	980.9	979.6	977.7
132.5°	1049.0	1046.9	1044.8	1042.7	1040.6	1038.0	1035.5	1032.9	1030.4	1029.1	1027.6
135°	1095.3	1093.0	1090.6	1088.3	1085.9	1083.8	1081.7	1079.6	1077.5	1076.5	1074.6
137.5°	1138.5	1136.2	1133.8	1131.5	1129.1	1126.8	1124.4	1122.1	1119.8	1118.6	1117.2
140°	1179.7	1177.6	1175.5	1173.4	1171.3	1168.7	1166.1	1163.6	1161.0	1159.7	1158.8
142.5°	1217.8	1215.9	1214.0	1212.1	1210.2	1207.2	1204.1	1201.1	1198.0	1196.5	1195.7
145°	1252.6	1250.9	1249.3	1247.6	1246.0	1242.0	1238.0	1234.1	1230.1	1228.1	1228.2
147.5°	1283.4	1282.2	1281.1	1279.9	1278.7	1274.7	1270.7	1266.8	1262.8	1260.8	1261.1
150°	1312.8	1311.4	1309.9	1308.5	1307.1	1303.4	1299.6	1295.9	1292.2	1290.3	1291.1
152.5°	1339.1	1337.7	1336.3	1334.9	1333.5	1330.0	1326.5	1323.0	1319.5	1317.7	1318.6
155°	1362.3	1360.9	1359.4	1358.0	1356.6	1353.8	1351.0	1348.2	1345.4	1344.0	1345.1
157.5°	1383.2	1381.5	1379.9	1378.2	1376.6	1374.5	1372.4	1370.3	1368.2	1367.2	1368.1
160°	1400.2	1398.8	1397.4	1396.0	1394.6	1393.2	1391.8	1390.3	1388.9	1388.2	1388.9
162.5°	1416.9	1415.3	1413.6	1412.0	1410.4	1409.2	1408.0	1406.9	1405.7	1405.1	1405.8
165°	1429.6	1427.9	1426.3	1424.6	1423.0	1422.3	1421.6	1420.9	1420.2	1419.8	1420.5
167.5°	1441.2	1439.5	1437.9	1436.2	1434.6	1433.9	1433.2	1432.5	1431.8	1431.4	1432.1
170°	1449.6	1447.9	1446.3	1444.6	1443.0	1442.5	1442.1	1441.6	1441.1	1440.9	1441.6
172.5°	1455.9	1454.2	1452.6	1450.9	1449.3	1448.8	1448.4	1447.9	1447.4	1447.2	1447.9
175°	1460.1	1458.4	1456.8	1455.1	1453.5	1453.0	1452.6	1452.1	1451.6	1451.4	1452.2
177.5°	1461.2	1459.5	1457.9	1456.2	1454.6	1454.4	1454.1	1453.9	1453.6	1453.5	1454.3
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	959.5	959.5	959.5	959.5
2.5°	941.8	941.8	952.9	964.7
5°	921.2	926.3	944.0	960.3
7.5°	901.3	910.1	932.2	952.9
10°	876.9	888.7	916.0	940.3
12.5°	853.3	864.4	896.1	923.4
15°	820.1	834.1	868.1	902.0
17.5°	786.9	801.0	842.3	882.1
20°	747.9	766.3	812.8	865.9
22.5°	711.7	734.6	786.2	829.0
25°	671.9	707.3	755.2	810.5
27.5°	636.5	671.9	720.6	776.6
30°	596.7	632.8	683.0	734.6
32.5°	558.3	591.5	640.2	703.6
35°	518.5	550.2	597.4	661.6
37.5°	482.3	513.3	564.9	623.9
40°	446.9	479.4	523.6	582.6
42.5°	413.8	442.5	482.3	541.3
45°	383.5	404.2	441.0	496.4
47.5°	351.8	370.2	404.2	459.5
50°	322.3	337.8	367.3	418.9
52.5°	293.5	306.8	334.1	375.4
55°	267.7	280.3	300.2	340.7
57.5°	241.2	250.8	269.9	302.4
60°	215.4	224.2	239.7	266.2
62.5°	189.5	196.9	211.7	233.1
65°	166.7	172.6	183.6	202.1
67.5°	144.6	148.2	157.1	171.8
70°	123.2	126.1	133.5	145.3
72.5°	100.3	103.3	111.4	119.5
75°	81.1	81.9	87.8	94.4
77.5°	63.4	62.7	67.1	72.3
80°	43.5	45.7	49.4	51.6
82.5°	29.5	30.2	31.7	33.2
85°	16.2	17.0	17.0	19.2
87.5°	6.6	7.4	7.4	8.1
90°	8.8	6.2	3.7	1.1
92.5°	23.5	24.4	25.4	26.3
95°	45.3	53.0	60.8	68.5
97.5°	65.7	84.8	104.0	123.2
100°	90.2	122.3	154.3	186.4
102.5°	254.5	255.0	255.4	255.9
105°	341.3	334.2	327.2	320.2
107.5°	412.5	406.7	400.8	395.0
110°	481.3	476.4	471.5	466.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	546.7	542.4	538.2	534.0
115°	617.5	613.6	609.6	605.6
117.5°	681.9	677.2	672.5	667.8
120°	747.8	744.3	740.8	737.3
122.5°	807.5	803.8	800.0	796.3
125°	865.4	862.4	859.3	856.3
127.5°	920.9	917.6	914.4	911.1
130°	974.0	970.2	966.5	962.7
132.5°	1024.5	1021.5	1018.4	1015.4
135°	1070.9	1067.1	1063.4	1059.6
137.5°	1114.4	1111.6	1108.8	1106.0
140°	1156.9	1155.0	1153.1	1151.2
142.5°	1194.1	1192.4	1190.8	1189.2
145°	1228.5	1228.7	1229.0	1229.2
147.5°	1261.8	1262.5	1263.2	1263.9
150°	1292.8	1294.4	1296.1	1297.7
152.5°	1320.5	1322.4	1324.2	1326.1
155°	1347.2	1349.3	1351.4	1353.5
157.5°	1370.0	1371.9	1373.7	1375.6
160°	1390.3	1391.8	1393.2	1394.6
162.5°	1407.2	1408.6	1410.0	1411.4
165°	1421.9	1423.4	1424.8	1426.2
167.5°	1433.5	1434.9	1436.3	1437.7
170°	1443.0	1444.4	1445.8	1447.2
172.5°	1449.3	1450.7	1452.1	1453.5
175°	1453.9	1455.5	1457.2	1458.8
177.5°	1456.0	1457.6	1459.3	1460.9
180°	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998387

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-A_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.48	14.19	14.58	15.28	16.78	10.98	11.69	12.07	12.77	14.27
	3H	14.28	14.92	15.39	16.01	17.53	12.31	12.94	13.41	14.04	15.55
	4H	14.44	15.05	15.56	16.14	17.66	12.76	13.37	13.88	14.46	15.98
	6H	14.48	15.04	15.60	16.14	17.67	13.06	13.62	14.19	14.72	16.25
	8H	14.46	14.98	15.58	16.10	17.62	13.14	13.67	14.27	14.79	16.31
	12H	14.42	14.91	15.54	16.02	17.57	13.18	13.68	14.31	14.79	16.34
4H	2H	13.51	14.11	14.63	15.21	16.72	11.40	12.00	12.53	13.10	14.62
	3H	14.47	14.97	15.60	16.10	17.63	12.85	13.35	13.98	14.48	16.01
	4H	14.74	15.20	15.87	16.32	17.87	13.38	13.84	14.51	14.95	16.50
	6H	14.87	15.26	16.00	16.40	17.94	13.75	14.14	14.89	15.28	16.82
	8H	14.86	15.23	16.00	16.36	17.92	13.86	14.23	14.99	15.35	16.91
	12H	14.82	15.15	15.97	16.29	17.85	13.91	14.24	15.06	15.38	16.94
8H	4H	14.74	15.11	15.88	16.24	17.80	13.51	13.88	14.65	15.01	16.56
	6H	14.91	15.22	16.07	16.39	17.94	13.94	14.24	15.10	15.41	16.97
	8H	14.94	15.21	16.11	16.36	17.93	14.09	14.35	15.25	15.50	17.08
	12H	14.92	15.15	16.09	16.30	17.91	14.17	14.41	15.34	15.55	17.16
12H	4H	14.69	15.02	15.84	16.17	17.73	13.48	13.81	14.63	14.95	16.51
	6H	14.89	15.16	16.06	16.31	17.88	13.94	14.20	15.10	15.35	16.93
	8H	14.92	15.15	16.08	16.30	17.91	14.09	14.32	15.26	15.47	17.08