

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998395

Luminaire Tested: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998395
REPORT IS A COMBINATION OF REPORTS P984135 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6229.0 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998395

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P998395

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	92	87	83	80	82	78	75	72	61	58	56	45	43	42	30	29	28
2	83	76	70	64	74	68	63	58	53	49	46	39	36	34	26	25	23
3	76	66	59	53	67	59	53	48	46	42	38	34	31	29	23	21	19
4	69	58	51	45	61	52	46	40	41	36	32	30	27	24	20	18	17
5	63	52	44	38	56	46	39	34	36	31	27	27	23	21	18	16	14
6	58	46	38	32	52	41	35	29	33	27	24	24	21	18	16	14	12
7	54	41	34	28	48	37	30	26	29	24	21	22	18	16	15	13	11
8	50	37	30	25	44	34	27	22	27	22	18	20	16	14	14	11	10
9	46	34	27	22	41	31	24	20	24	19	16	18	15	12	12	10	9
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8078	8078	8078
5°	8113	7733	7689
10°	8059	7464	7356
15°	7946	7188	7014
20°	7802	6896	6690
25°	7660	6618	6395
30°	7461	6336	6104
35°	7260	6063	5891
40°	7049	5826	5678
45°	6849	5612	5493
50°	6631	5415	5310
55°	6403	5205	5125
60°	6127	4986	4929
65°	5837	4736	4704
70°	5509	4467	4462
75°	5091	4198	4232
80°	4431	3916	3996
85°	3757	3653	3791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6849 cd/sqm

TEST NUMBER: P998395

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	0.8
10°-20°	138.7	2.2
20°-30°	210.2	3.4
30°-40°	256.0	4.1
40°-50°	275.4	4.4
50°-60°	267.5	4.3
60°-70°	233.6	3.7
70°-80°	179.8	2.9
80°-90°	123.0	2.0
90°-100°	131.2	2.1
100°-110°	240.1	3.9
110°-120°	515.9	8.3
120°-130°	811.6	13.0
130°-140°	847.8	13.6
140°-150°	780.8	12.5
150°-160°	626.5	10.1
160°-170°	403.7	6.5
170°-180°	138.9	2.2
0°-30°	397.3	6.4
0°-40°	653.3	10.5
0°-60°	1196.2	19.2
0°-90°	1732.5	27.8
90°-120°	887.2	14.2
90°-150°	3327.4	53.4
90°-180°	4496.0	72.2
0°-180°	6229.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	510	510	510	510	510	
5°	512	510	505	510	509	49
15°	488	490	490	496	496	137
25°	444	449	456	464	467	204
35°	382	395	409	425	430	239
45°	314	334	359	382	390	242
55°	240	267	305	332	342	215
65°	164	200	244	274	284	163
75°	91	132	180	212	221	96
85°	27	72	120	151	161	28
90°	8	63	119	154	165	9
95°	75	74	126	160	167	86
105°	325	378	128	166	178	347
115°	610	636	696	229	161	601
125°	860	874	918	945	955	767
135°	1063	1080	1097	1123	1127	822
145°	1233	1232	1250	1261	1260	771
155°	1357	1348	1360	1367	1358	625
165°	1430	1424	1427	1434	1427	404
175°	1463	1456	1458	1465	1454	139
180°	1460	1460	1460	1460	1460	

TEST NUMBER: P998395

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	510.3	510.3	510.3	510.3	510.3
2.5°	514.0	511.7	506.6	510.3	508.8
5°	511.7	509.5	505.1	509.5	508.8
7.5°	508.0	506.6	502.9	508.0	507.3
10°	503.6	502.1	499.9	505.8	505.1
12.5°	496.2	497.0	495.5	501.4	500.7
15°	488.1	489.6	489.6	496.2	495.5
17.5°	477.7	480.7	482.9	489.6	489.6
20°	467.4	471.1	474.0	482.2	482.2
22.5°	456.3	460.7	465.2	473.3	474.8
25°	443.7	448.9	455.5	464.4	466.6
27.5°	428.9	437.1	444.4	455.5	457.0
30°	414.1	423.7	433.4	445.2	447.4
32.5°	397.9	409.0	420.8	434.8	439.3
35°	382.3	394.9	409.0	425.2	430.4
37.5°	365.3	379.4	397.1	414.9	420.0
40°	348.3	364.6	384.5	403.8	410.4
42.5°	332.0	348.3	372.0	393.4	400.1
45°	313.6	333.5	359.4	382.3	389.7
47.5°	295.8	317.3	346.8	370.5	378.6
50°	277.3	300.2	333.5	358.7	366.8
52.5°	259.6	284.0	319.5	345.4	354.2
55°	240.3	267.0	305.4	332.0	341.7
57.5°	221.9	251.4	289.9	318.7	328.3
60°	201.9	233.7	275.8	303.9	314.3
62.5°	184.1	217.4	259.6	289.9	299.5
65°	164.2	200.4	244.0	274.4	284.0
67.5°	146.4	184.1	228.5	258.8	269.2
70°	127.2	165.7	211.5	243.3	252.2
72.5°	109.4	149.4	196.0	227.0	238.1
75°	91.0	132.4	179.7	211.5	221.1
77.5°	73.2	116.1	164.2	196.0	206.3
80°	55.5	100.6	148.6	179.7	190.1
82.5°	40.7	85.0	133.9	164.9	174.5
85°	26.6	72.5	119.8	150.9	161.2
87.5°	16.3	60.6	108.0	138.3	147.9
90°	8.5	63.0	118.7	153.6	164.6
92.5°	33.1	68.1	116.3	147.3	157.2
95°	74.6	74.5	126.2	159.6	167.4
97.5°	128.8	74.0	133.8	164.2	174.2
100°	192.2	74.7	134.2	170.0	180.2
102.5°	261.1	283.4	131.1	169.3	180.6
105°	324.8	377.9	128.0	165.5	177.9
107.5°	399.8	443.9	124.9	161.8	174.1
110°	470.9	507.8	238.8	156.8	169.2

TEST NUMBER: P998395

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	538.5	569.3	585.4	153.8	165.1
115°	610.3	636.4	696.1	229.3	161.3
117.5°	671.9	698.9	747.9	619.1	349.8
120°	741.6	760.4	809.0	842.4	707.9
122.5°	800.7	818.4	866.8	893.2	900.8
125°	860.2	874.0	917.6	945.0	954.9
127.5°	915.2	929.1	965.0	994.0	1001.8
130°	966.9	983.0	1010.2	1039.5	1044.4
132.5°	1019.7	1032.7	1055.4	1081.9	1086.8
135°	1063.3	1080.2	1097.1	1123.3	1127.0
137.5°	1109.8	1122.4	1136.7	1161.4	1163.4
140°	1155.2	1162.9	1176.0	1197.4	1196.5
142.5°	1193.2	1199.9	1213.6	1231.0	1229.4
145°	1232.6	1231.6	1249.5	1261.3	1259.8
147.5°	1267.5	1264.3	1282.3	1288.3	1286.3
150°	1301.3	1293.9	1310.8	1317.1	1311.9
152.5°	1329.8	1321.4	1337.2	1343.5	1336.2
155°	1357.3	1347.8	1360.4	1366.8	1358.3
157.5°	1379.5	1371.0	1380.5	1387.9	1379.5
160°	1398.5	1392.1	1398.5	1404.8	1397.4
162.5°	1415.4	1409.0	1414.3	1421.7	1412.2
165°	1430.2	1423.8	1427.0	1434.4	1427.0
167.5°	1441.8	1435.4	1438.6	1446.0	1436.5
170°	1451.3	1444.9	1447.1	1454.5	1444.9
172.5°	1457.6	1451.3	1453.4	1460.8	1451.3
175°	1462.9	1455.5	1457.6	1465.0	1454.5
177.5°	1465.0	1457.6	1458.7	1466.1	1456.6
180°	1459.7	1459.7	1459.7	1459.7	1459.7



TEST NUMBER: P998395

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.98	10.69	11.10	11.81	13.36	13.05	13.77	14.17	14.89	16.44
	3H	11.43	12.07	12.56	13.20	14.77	15.63	16.28	16.76	17.40	18.97
	4H	11.90	12.51	13.03	13.64	15.21	16.88	17.49	18.02	18.62	20.19
	6H	12.17	12.74	13.32	13.87	15.46	18.17	18.74	19.31	19.86	21.45
	8H	12.23	12.77	13.38	13.91	15.49	18.82	19.36	19.97	20.51	22.09
	12H	12.24	12.75	13.39	13.89	15.50	19.54	20.06	20.70	21.20	22.80
4H	2H	11.01	11.63	12.16	12.75	14.33	13.37	13.98	14.51	15.11	16.68
	3H	12.71	13.23	13.86	14.38	15.96	16.15	16.66	17.30	17.82	19.40
	4H	13.33	13.80	14.48	14.94	16.55	17.56	18.04	18.71	19.18	20.78
	6H	13.73	14.15	14.89	15.31	16.90	19.02	19.43	20.18	20.59	22.19
	8H	13.84	14.22	14.99	15.38	16.99	19.77	20.16	20.93	21.31	22.93
	12H	13.87	14.23	15.05	15.39	17.01	20.59	20.95	21.77	22.11	23.73
8H	4H	14.10	14.49	15.26	15.65	17.26	17.69	18.08	18.85	19.23	20.85
	6H	14.73	15.05	15.91	16.25	17.86	19.31	19.64	20.49	20.83	22.44
	8H	14.95	15.23	16.13	16.41	18.04	20.20	20.48	21.38	21.66	23.29
	12H	15.08	15.33	16.26	16.50	18.16	21.19	21.44	22.38	22.61	24.27
12H	4H	14.29	14.65	15.47	15.81	17.43	17.66	18.01	18.83	19.18	20.79
	6H	15.06	15.35	16.25	16.52	18.15	19.34	19.62	20.52	20.79	22.42
	8H	15.36	15.61	16.55	16.78	18.44	20.26	20.51	21.45	21.68	23.34