

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931077

Luminaire Tested: DFN2DS-SQ4F0-060DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-060DS935-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5108.4 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 57.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931077

CATALOG NUMBER: DFN2DS-SQ4F0-060DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931077

CATALOG NUMBER: DFN2DS-SQ4F0-060DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1409	1409	1409
5°	1414	1394	1402
10°	1406	1380	1387
15°	1388	1362	1360
20°	1364	1335	1334
25°	1339	1302	1302
30°	1308	1272	1261
35°	1278	1235	1217
40°	1242	1199	1176
45°	1205	1163	1134
50°	1165	1125	1085
55°	1124	1082	1042
60°	1078	1030	992
65°	1029	978	933
70°	966	915	872
75°	879	842	822
80°	781	756	718
85°	636	606	544

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1205 cd/sqm

TEST NUMBER: P931077

CATALOG NUMBER: DFN2DS-SQ4F0-060DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	3.7
10°-20°	531.7	10.4
20°-30°	781.4	15.3
30°-40°	907.5	17.8
40°-50°	906.4	17.7
50°-60°	790.4	15.5
60°-70°	584.3	11.4
70°-80°	330.6	6.5
80°-90°	87.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1502.1	29.4
0°-40°	2409.6	47.2
0°-60°	4106.3	80.4
0°-90°	5108.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5108.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2008	2008	2008	2008	2008	
5°	2008	2000	1979	1994	1991	191
15°	1911	1900	1875	1882	1873	538
25°	1730	1714	1682	1685	1682	796
35°	1492	1473	1442	1430	1421	932
45°	1214	1201	1172	1151	1143	937
55°	919	907	884	861	852	822
65°	620	608	589	572	562	613
75°	324	321	311	299	303	346
85°	79	77	75	69	68	93
90°	0	0	0	0	0	

TEST NUMBER: P931077

CATALOG NUMBER: DFN2DS-SQ4F0-060DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2007.8	2007.8	2007.8	2007.8	2007.8
2.5°	2019.5	2009.8	1988.5	2007.8	2004.1
5°	2007.8	2000.2	1978.9	1994.3	1990.6
7.5°	1994.3	1982.8	1961.5	1977.1	1973.2
10°	1973.2	1959.7	1936.5	1951.9	1946.1
12.5°	1944.1	1932.6	1909.5	1919.1	1915.2
15°	1911.3	1899.8	1874.6	1882.5	1872.8
17.5°	1870.8	1859.3	1834.1	1843.7	1834.1
20°	1826.3	1814.9	1787.8	1793.5	1786.0
22.5°	1782.1	1764.6	1739.4	1739.4	1735.6
25°	1729.8	1714.5	1681.6	1685.3	1681.6
27.5°	1671.8	1658.3	1633.3	1627.6	1618.0
30°	1614.1	1598.5	1569.7	1563.9	1556.1
32.5°	1552.2	1540.8	1509.8	1498.1	1490.4
35°	1492.4	1473.2	1442.2	1430.5	1420.9
37.5°	1424.8	1407.4	1376.5	1362.9	1353.3
40°	1355.4	1339.8	1308.9	1291.7	1283.9
42.5°	1287.8	1272.2	1241.5	1222.1	1210.5
45°	1214.5	1200.9	1171.8	1150.8	1142.9
47.5°	1142.9	1129.4	1098.6	1077.2	1065.7
50°	1067.6	1058.0	1031.0	1003.9	994.2
52.5°	994.2	980.7	955.7	934.5	921.0
55°	919.1	907.4	884.3	861.1	851.5
57.5°	843.7	834.1	808.9	785.8	778.0
60°	768.3	760.8	733.8	712.4	706.7
62.5°	695.0	681.5	662.2	642.9	635.2
65°	619.8	608.2	588.9	571.5	561.8
67.5°	542.6	532.8	515.6	502.1	494.2
70°	471.1	463.4	445.9	432.4	424.8
72.5°	397.8	390.0	380.4	366.9	361.1
75°	324.2	320.6	310.7	299.3	303.2
77.5°	258.7	250.9	247.0	241.3	235.6
80°	193.2	191.1	187.2	181.5	177.6
82.5°	131.3	131.3	129.4	121.7	121.7
85°	79.0	77.2	75.3	69.4	67.6
87.5°	34.8	31.0	27.0	21.3	19.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931077

CATALOG NUMBER: DFN2DS-SQ4F0-060DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.47	14.08	12.84	14.40	14.71	12.03	13.64	12.39	13.95	14.27
	3H	14.22	15.68	14.60	16.00	16.37	13.73	15.19	14.11	15.51	15.87
	4H	14.87	16.24	15.27	16.59	16.96	14.38	15.74	14.77	16.09	16.47
	6H	15.34	16.61	15.75	16.97	17.36	14.84	16.11	15.25	16.47	16.86
	8H	15.48	16.69	15.91	17.08	17.48	14.98	16.19	15.40	16.58	16.98
	12H	15.57	16.73	16.00	17.11	17.54	15.06	16.22	15.49	16.60	17.03
4H	2H	13.03	14.40	13.43	14.75	15.13	12.68	14.05	13.08	14.40	14.77
	3H	15.01	16.16	15.42	16.55	16.95	14.60	15.75	15.01	16.15	16.55
	4H	15.79	16.82	16.22	17.24	17.67	15.36	16.40	15.79	16.81	17.25
	6H	16.38	17.29	16.84	17.73	18.18	15.95	16.85	16.40	17.30	17.75
	8H	16.57	17.42	17.03	17.86	18.33	16.13	16.98	16.59	17.42	17.89
	12H	16.70	17.46	17.18	17.94	18.41	16.25	17.01	16.73	17.49	17.96
8H	4H	16.06	16.91	16.52	17.35	17.81	15.68	16.53	16.15	16.97	17.44
	6H	16.77	17.48	17.27	17.96	18.44	16.39	17.09	16.89	17.58	18.06
	8H	17.03	17.66	17.54	18.17	18.66	16.64	17.27	17.15	17.78	18.26
	12H	17.23	17.79	17.74	18.28	18.84	16.82	17.38	17.33	17.87	18.43
12H	4H	16.08	16.84	16.57	17.32	17.79	15.72	16.48	16.20	16.96	17.43
	6H	16.82	17.45	17.33	17.96	18.44	16.45	17.08	16.96	17.59	18.07
	8H	17.13	17.69	17.64	18.18	18.74	16.75	17.31	17.26	17.80	18.36