

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998396

Luminaire Tested: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998396
REPORT IS A COMBINATION OF REPORTS P984136 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6024.0 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998396

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P998396

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36			28
1	92	87	83	80	82	78	75	72	61	58	56	45	43	42	30	29	28			22
2	83	76	70	64	74	68	63	58	53	49	46	39	36	34	26	25	23			18
3	76	66	59	53	67	59	53	48	46	42	38	34	31	29	23	21	19			14
4	69	58	51	45	61	52	46	40	41	36	32	30	27	24	20	18	17			12
5	63	52	44	38	56	46	39	34	36	31	27	27	23	21	18	16	14			10
6	58	46	38	32	52	41	35	29	33	27	24	24	21	18	16	14	12			9
7	54	41	34	28	48	37	30	26	29	24	21	22	18	16	15	13	11			8
8	50	37	30	25	44	34	27	22	27	22	18	20	16	14	14	11	10			7
9	46	34	27	22	41	31	24	20	24	19	16	18	15	12	12	10	9			6
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7812	7812	7812
5°	7847	7478	7437
10°	7795	7220	7114
15°	7684	6952	6784
20°	7545	6669	6470
25°	7408	6401	6186
30°	7216	6127	5904
35°	7023	5863	5698
40°	6819	5635	5491
45°	6622	5428	5312
50°	6414	5238	5135
55°	6193	5035	4955
60°	5926	4824	4767
65°	5645	4580	4548
70°	5327	4319	4315
75°	4923	4060	4092
80°	4279	3789	3864
85°	3630	3534	3666

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6622 cd/sqm

TEST NUMBER: P998396

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	0.8
10°-20°	134.2	2.2
20°-30°	203.3	3.4
30°-40°	247.6	4.1
40°-50°	266.4	4.4
50°-60°	258.7	4.3
60°-70°	225.9	3.8
70°-80°	173.9	2.9
80°-90°	118.9	2.0
90°-100°	126.9	2.1
100°-110°	232.2	3.9
110°-120°	499.0	8.3
120°-130°	784.9	13.0
130°-140°	819.8	13.6
140°-150°	755.1	12.5
150°-160°	605.8	10.1
160°-170°	390.4	6.5
170°-180°	134.4	2.2
0°-30°	384.3	6.4
0°-40°	631.8	10.5
0°-60°	1156.9	19.2
0°-90°	1675.6	27.8
90°-120°	858.0	14.2
90°-150°	3217.8	53.4
90°-180°	4348.0	72.2
0°-180°	6024.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	494	494	494	494	494	
5°	495	493	488	493	492	47
15°	472	474	474	480	479	133
25°	429	434	441	449	451	197
35°	370	382	396	411	416	231
45°	303	323	348	370	377	234
55°	232	258	295	321	330	208
65°	159	194	236	265	275	158
75°	88	128	174	204	214	93
85°	26	70	116	146	156	27
90°	8	61	115	148	159	9
95°	72	72	122	154	162	83
105°	314	366	124	160	172	336
115°	590	615	673	222	156	581
125°	832	845	887	914	924	742
135°	1028	1045	1061	1086	1090	795
145°	1192	1191	1208	1220	1218	746
155°	1313	1303	1316	1322	1314	605
165°	1383	1377	1380	1387	1380	391
175°	1415	1408	1410	1417	1407	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P998396

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	493.5	493.5	493.5	493.5	493.5
2.5°	497.1	494.9	489.9	493.5	492.1
5°	494.9	492.8	488.5	492.8	492.1
7.5°	491.3	489.9	486.3	491.3	490.6
10°	487.1	485.6	483.5	489.2	488.5
12.5°	479.9	480.6	479.2	484.9	484.2
15°	472.0	473.5	473.5	479.9	479.2
17.5°	462.0	464.9	467.0	473.5	473.5
20°	452.0	455.6	458.4	466.3	466.3
22.5°	441.3	445.6	449.9	457.7	459.2
25°	429.1	434.1	440.6	449.2	451.3
27.5°	414.8	422.7	429.8	440.6	442.0
30°	400.5	409.8	419.1	430.6	432.7
32.5°	384.8	395.5	407.0	420.5	424.8
35°	369.8	381.9	395.5	411.2	416.3
37.5°	353.3	366.9	384.1	401.2	406.2
40°	336.9	352.6	371.9	390.5	396.9
42.5°	321.1	336.9	359.7	380.5	386.9
45°	303.2	322.6	347.6	369.8	376.9
47.5°	286.1	306.8	335.4	358.3	366.2
50°	268.2	290.4	322.6	346.9	354.7
52.5°	251.0	274.6	309.0	334.0	342.6
55°	232.4	258.2	295.4	321.1	330.4
57.5°	214.6	243.2	280.4	308.3	317.6
60°	195.3	226.0	266.8	294.0	304.0
62.5°	178.1	210.3	251.0	280.4	289.7
65°	158.8	193.8	236.0	265.3	274.6
67.5°	141.6	178.1	221.0	250.3	260.3
70°	123.0	160.2	204.5	235.3	243.9
72.5°	105.9	144.5	189.5	219.6	230.3
75°	88.0	128.0	173.8	204.5	213.8
77.5°	70.8	112.3	158.8	189.5	199.5
80°	53.6	97.3	143.8	173.8	183.8
82.5°	39.3	82.2	129.5	159.5	168.8
85°	25.7	70.1	115.9	145.9	155.9
87.5°	15.7	58.6	104.4	133.7	143.0
90°	8.2	60.9	114.8	148.5	159.2
92.5°	31.9	65.8	112.5	142.5	152.0
95°	72.1	72.0	122.0	154.3	161.9
97.5°	124.5	71.6	129.3	158.9	168.5
100°	185.8	72.4	129.7	164.4	174.3
102.5°	252.5	274.1	126.8	163.8	174.7
105°	314.1	365.5	123.8	160.0	172.0
107.5°	386.7	429.3	120.9	156.4	168.4
110°	455.4	491.2	231.0	151.7	163.7

TEST NUMBER: P998396

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	520.8	550.6	566.1	148.8	159.7
115°	590.2	615.4	673.1	221.7	156.0
117.5°	649.7	675.9	723.3	598.7	338.2
120°	717.1	735.3	782.3	814.6	684.6
122.5°	774.3	791.5	838.3	863.7	871.3
125°	831.9	845.1	887.4	913.9	923.5
127.5°	885.0	898.6	933.2	961.3	968.7
130°	935.0	950.7	976.9	1005.3	1010.0
132.5°	986.1	998.7	1020.6	1046.3	1051.0
135°	1028.3	1044.6	1061.0	1086.2	1089.9
137.5°	1073.2	1085.5	1099.3	1123.1	1125.1
140°	1117.2	1124.6	1137.3	1158.0	1157.2
142.5°	1153.9	1160.4	1173.7	1190.4	1188.9
145°	1192.1	1191.0	1208.4	1219.8	1218.3
147.5°	1225.8	1222.7	1240.1	1245.9	1244.0
150°	1258.4	1251.3	1267.6	1273.8	1268.7
152.5°	1286.0	1277.9	1293.2	1299.3	1292.2
155°	1312.6	1303.4	1315.7	1321.8	1313.6
157.5°	1334.0	1325.9	1335.1	1342.2	1334.0
160°	1352.4	1346.3	1352.4	1358.6	1351.4
162.5°	1368.8	1362.6	1367.7	1374.9	1365.7
165°	1383.1	1376.9	1380.0	1387.2	1380.0
167.5°	1394.3	1388.2	1391.2	1398.4	1389.2
170°	1403.5	1397.4	1399.4	1406.6	1397.4
172.5°	1409.6	1403.5	1405.5	1412.7	1403.5
175°	1414.7	1407.6	1409.6	1416.8	1406.6
177.5°	1416.8	1409.6	1410.6	1417.8	1408.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998396

CATALOG NUMBER: SA2XXDIP-B485D1080UB2750-4F0-XX-W2A-D_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.86	10.58	10.98	11.70	13.25	12.94	13.65	14.06	14.77	16.33
	3H	11.31	11.96	12.44	13.08	14.65	15.52	16.16	16.64	17.29	18.86
	4H	11.78	12.40	12.92	13.52	15.10	16.76	17.38	17.90	18.50	20.08
	6H	12.06	12.63	13.20	13.76	15.34	18.05	18.62	19.20	19.75	21.33
	8H	12.11	12.65	13.26	13.80	15.38	18.71	19.25	19.86	20.39	21.97
	12H	12.13	12.64	13.28	13.78	15.38	19.43	19.94	20.58	21.08	22.68
4H	2H	10.90	11.51	12.04	12.64	14.21	13.25	13.87	14.40	14.99	16.57
	3H	12.59	13.11	13.74	14.26	15.85	16.03	16.55	17.18	17.70	19.29
	4H	13.21	13.69	14.36	14.83	16.43	17.44	17.92	18.59	19.06	20.67
	6H	13.62	14.03	14.77	15.19	16.79	18.90	19.31	20.06	20.48	22.07
	8H	13.72	14.11	14.88	15.26	16.88	19.66	20.04	20.81	21.20	22.81
	12H	13.76	14.11	14.93	15.28	16.89	20.48	20.83	21.65	22.00	23.61
8H	4H	13.99	14.37	15.14	15.53	17.14	17.57	17.96	18.73	19.12	20.73
	6H	14.62	14.94	15.79	16.13	17.74	19.20	19.52	20.37	20.72	22.33
	8H	14.83	15.12	16.02	16.29	17.92	20.09	20.37	21.27	21.54	23.17
	12H	14.96	15.21	16.15	16.38	18.04	21.07	21.32	22.26	22.50	24.16
12H	4H	14.18	14.53	15.35	15.70	17.32	17.54	17.89	18.72	19.06	20.68
	6H	14.95	15.23	16.13	16.41	18.03	19.22	19.50	20.40	20.68	22.31
	8H	15.24	15.49	16.43	16.67	18.33	20.14	20.39	21.33	21.57	23.23