

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998445

Luminaire Tested: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998445
REPORT IS A COMBINATION OF REPORTS P984188 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3454.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58
2	93	85	79	74	86	80	75	71	71	67	63	62	59	56	54	52	50
3	85	76	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	60	54	73	64	57	51	56	51	47	50	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	41	45	40	37	39	36	33
6	66	54	46	41	62	52	44	39	46	40	36	41	36	33	36	32	29
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	29	34	30	26	31	27	24
9	54	41	34	29	50	39	33	28	35	30	26	32	27	24	28	25	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15318	15318	15318	15318
5°	15354	16332	15413	12993
10°	15176	17829	15272	10713
15°	14809	18805	15014	9023
20°	14577	17657	14577	7843
25°	14112	15170	14178	7013
30°	13348	11925	13604	6353
35°	12671	8246	12882	5813
40°	11892	6226	12028	5382
45°	10933	5116	11112	4916
50°	10103	4491	10120	4501
55°	9156	3826	9217	4049
60°	8148	3196	8260	3535
65°	7245	2599	7376	3018
70°	6344	2040	6505	2434
75°	5326	1481	5533	1765
80°	4160	938	4455	1047
85°	2726	473	2938	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15834 cd/sqm

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	2.7
10°-20°	268.3	7.8
20°-30°	389.3	11.3
30°-40°	410.4	11.9
40°-50°	363.2	10.5
50°-60°	290.0	8.4
60°-70°	197.0	5.7
70°-80°	100.8	2.9
80°-90°	24.6	0.7
90°-100°	14.8	0.4
100°-110°	55.3	1.6
110°-120°	146.6	4.2
120°-130°	243.1	7.0
130°-140°	258.3	7.5
140°-150°	240.0	6.9
150°-160°	193.0	5.6
160°-170°	124.3	3.6
170°-180°	42.8	1.2
0°-30°	749.8	21.7
0°-40°	1160.2	33.6
0°-60°	1813.4	52.5
0°-90°	2135.8	61.8
90°-120°	216.7	6.3
90°-150°	958.1	27.7
90°-180°	1318.0	38.2
0°-180°	3454.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	968	968	968	968	968	
5°	968	1081	972	860	968	92
15°	910	1328	922	637	910	257
25°	817	1107	821	512	817	374
35°	667	602	678	425	667	417
45°	501	363	509	349	501	388
55°	344	255	346	270	344	307
65°	204	157	208	182	204	203
75°	95	77	99	92	95	102
85°	19	20	21	15	19	23
90°	0	9	0	9	0	2
95°	21	14	21	14	21	25
105°	99	25	99	25	99	106
115°	187	27	187	27	187	184
125°	264	278	264	278	264	236
135°	327	338	327	338	327	253
145°	380	386	380	386	380	237
155°	418	418	418	418	418	193
165°	440	440	440	440	440	124
175°	451	448	451	448	451	43
180°	450	450	450	450	450	

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	972.9	975.1	978.8	979.6	987.0	993.0	999.7	999.7	1001.9	1001.2	995.2
5°	968.4	975.1	984.8	993.0	1006.4	1012.3	1021.2	1027.9	1033.9	1038.3	1037.6
7.5°	961.0	972.9	987.0	1002.6	1020.5	1030.9	1043.5	1055.4	1063.6	1071.1	1076.3
10°	948.3	968.4	987.8	1008.6	1031.6	1045.8	1060.7	1076.3	1088.9	1103.1	1116.4
12.5°	931.2	960.2	984.0	1011.6	1039.8	1055.4	1079.3	1091.2	1115.7	1151.4	1161.1
15°	909.7	949.1	971.4	1006.4	1043.5	1056.2	1088.9	1108.3	1158.8	1181.2	1207.9
17.5°	889.6	933.5	963.2	1003.4	1039.8	1064.4	1096.4	1135.8	1178.2	1210.2	1239.9
20°	873.2	915.6	951.3	995.9	1042.1	1073.3	1106.8	1154.4	1200.5	1233.2	1256.3
22.5°	836.0	890.3	932.0	981.8	1037.6	1080.7	1112.7	1164.8	1214.6	1234.7	1254.8
25°	817.4	864.3	912.6	969.2	1034.6	1085.9	1113.5	1171.5	1215.4	1222.8	1227.3
27.5°	783.2	836.0	892.6	957.3	1033.9	1077.0	1112.0	1164.8	1199.7	1194.5	1181.2
30°	740.8	805.5	868.0	937.9	1023.5	1070.3	1103.1	1151.4	1169.3	1142.5	1118.7
32.5°	709.6	770.6	839.7	920.8	1011.6	1056.2	1088.2	1126.1	1129.8	1081.5	1041.3
35°	667.2	734.9	813.0	898.5	991.5	1031.6	1061.4	1084.5	1066.6	998.9	951.3
37.5°	629.3	696.2	779.5	866.5	964.0	1003.4	1027.2	1030.9	987.0	927.5	857.6
40°	587.6	656.8	743.8	835.3	933.5	967.7	982.6	971.4	908.2	839.0	757.9
42.5°	545.9	614.4	708.1	801.8	894.8	923.8	929.7	899.3	821.9	740.8	647.1
45°	500.6	572.0	665.7	760.2	850.2	866.5	867.3	823.4	731.9	647.1	560.1
47.5°	463.4	529.6	622.6	717.0	792.9	804.0	799.6	749.0	649.3	554.1	478.3
50°	422.5	485.7	577.9	670.9	735.6	738.6	727.4	655.3	557.8	470.8	410.6
52.5°	378.6	442.6	527.4	616.6	674.6	670.2	648.6	571.2	479.7	407.6	361.5
55°	343.6	400.2	479.7	566.8	607.7	595.0	571.2	492.4	420.2	359.3	319.1
57.5°	305.0	354.8	432.9	508.8	532.6	520.7	496.9	423.2	356.3	310.2	283.4
60°	268.5	313.9	382.3	445.5	464.1	451.5	424.0	357.8	309.4	270.7	250.7
62.5°	235.0	274.5	331.7	389.8	397.2	384.5	360.7	307.2	265.5	235.0	220.2
65°	203.8	241.0	287.1	331.0	337.7	324.3	299.8	261.1	226.1	206.8	192.6
67.5°	173.3	203.1	244.0	275.9	279.7	267.0	246.9	215.7	194.1	173.3	162.9
70°	146.5	168.8	200.8	226.9	228.3	216.4	206.0	177.8	161.4	146.5	138.3
72.5°	120.5	136.1	160.7	180.0	180.7	173.3	163.6	145.8	131.7	121.2	113.1
75°	95.2	108.6	123.5	140.6	139.8	133.9	126.4	115.3	103.4	96.7	93.0
77.5°	72.9	81.1	93.0	104.1	104.1	101.2	96.7	88.5	81.1	74.4	70.7
80°	52.1	57.3	66.9	70.7	72.1	71.4	67.7	61.7	58.8	53.6	52.1
82.5°	33.5	37.2	41.7	45.4	47.6	46.1	45.4	42.4	37.9	36.4	35.0
85°	19.3	20.8	23.1	25.3	26.0	25.3	26.8	24.5	22.3	22.3	21.6
87.5°	8.2	8.9	10.4	10.4	11.2	11.2	10.4	11.2	11.2	10.4	9.7
90°	0.3	1.1	1.9	2.7	3.5	3.9	4.2	4.8	5.3	5.9	6.5
92.5°	8.1	7.8	7.5	7.2	6.9	6.8	6.9	7.1	7.4	7.6	7.8
95°	21.1	18.7	16.3	14.0	11.6	10.4	10.7	11.2	11.7	12.2	12.7
97.5°	38.1	32.2	26.2	20.3	14.4	11.4	12.0	13.1	14.3	15.4	16.6
100°	57.6	47.7	37.8	27.9	18.0	13.0	13.6	14.8	16.1	17.3	18.5
102.5°	79.1	78.9	78.8	78.6	78.5	78.4	71.8	58.7	45.5	32.4	19.2
105°	98.9	101.1	103.3	105.4	107.6	108.7	98.8	79.1	59.3	39.6	19.8
107.5°	122.0	123.8	125.6	127.4	129.2	130.1	117.9	93.6	69.2	44.9	20.5
110°	144.1	145.6	147.2	148.7	150.2	151.0	140.5	119.6	98.7	77.8	56.9



TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	165.0	166.3	167.6	168.9	170.2	170.8	170.2	169.0	167.7	166.5	165.3
115°	187.1	188.3	189.5	190.8	192.0	192.6	193.5	195.3	197.1	198.9	200.7
117.5°	206.3	207.7	209.2	210.6	212.1	212.8	213.4	214.6	215.9	217.1	218.3
120°	227.8	228.9	229.9	231.0	232.1	232.6	233.3	234.6	235.9	237.2	238.5
122.5°	246.0	247.2	248.3	249.5	250.6	251.2	251.9	253.4	254.8	256.3	257.7
125°	264.5	265.4	266.4	267.3	268.2	268.7	269.4	270.8	272.1	273.5	274.9
127.5°	281.4	282.4	283.4	284.5	285.5	286.0	286.5	287.6	288.7	289.8	290.9
130°	297.4	298.6	299.7	300.9	302.0	302.6	303.0	303.8	304.6	305.4	306.2
132.5°	313.6	314.6	315.5	316.5	317.4	317.9	318.3	319.1	319.9	320.7	321.5
135°	327.3	328.5	329.6	330.8	331.9	332.5	332.8	333.5	334.1	334.8	335.4
137.5°	341.6	342.5	343.3	344.2	345.1	345.5	345.9	346.6	347.3	348.1	348.8
140°	355.6	356.2	356.8	357.3	357.9	358.2	358.6	359.4	360.2	361.0	361.8
142.5°	367.3	367.8	368.3	368.8	369.3	369.6	370.1	371.0	371.9	372.9	373.8
145°	379.7	379.6	379.6	379.5	379.4	379.4	380.0	381.2	382.5	383.7	384.9
147.5°	390.4	390.2	390.0	389.8	389.6	389.5	390.1	391.3	392.6	393.8	395.0
150°	400.8	400.3	399.8	399.3	398.8	398.6	399.2	400.3	401.5	402.6	403.8
152.5°	409.6	409.0	408.4	407.9	407.3	407.0	407.5	408.6	409.7	410.8	411.9
155°	418.1	417.5	416.8	416.2	415.5	415.2	415.6	416.5	417.4	418.2	419.1
157.5°	424.9	424.3	423.7	423.2	422.6	422.3	422.6	423.3	423.9	424.6	425.2
160°	430.8	430.4	429.9	429.5	429.0	428.8	429.0	429.5	429.9	430.4	430.8
162.5°	436.0	435.6	435.1	434.7	434.2	434.0	434.2	434.6	434.9	435.3	435.7
165°	440.5	440.1	439.7	439.2	438.8	438.6	438.7	438.9	439.2	439.4	439.6
167.5°	444.1	443.7	443.3	442.8	442.4	442.2	442.3	442.5	442.7	442.9	443.1
170°	447.0	446.6	446.2	445.7	445.3	445.1	445.2	445.3	445.4	445.6	445.7
172.5°	449.0	448.6	448.1	447.7	447.2	447.0	447.1	447.2	447.4	447.5	447.7
175°	450.6	450.1	449.6	449.1	448.6	448.3	448.4	448.5	448.7	448.8	449.0
177.5°	451.3	450.8	450.3	449.8	449.3	449.0	449.0	449.1	449.2	449.2	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1005.6	1006.4	1007.8	1015.3	1019.0	1019.7	1016.8	1023.5	1025.7	1023.5	1022.0
5°	1053.2	1057.7	1066.6	1076.3	1075.5	1076.3	1080.7	1085.2	1086.7	1080.7	1083.0
7.5°	1094.9	1103.8	1113.5	1128.3	1128.3	1135.8	1138.8	1142.5	1151.4	1146.9	1145.4
10°	1142.5	1154.4	1172.2	1196.0	1196.8	1204.2	1211.6	1223.5	1227.3	1224.3	1225.8
12.5°	1202.0	1225.0	1226.5	1252.6	1264.5	1265.9	1277.8	1275.6	1283.1	1283.1	1295.7
15°	1228.0	1263.7	1283.8	1309.1	1316.5	1307.6	1317.3	1327.7	1328.4	1328.4	1327.7
17.5°	1274.9	1289.0	1309.1	1322.5	1325.4	1325.4	1326.2	1330.7	1327.7	1321.7	1326.2
20°	1284.5	1290.5	1297.9	1296.4	1297.9	1290.5	1283.1	1275.6	1276.4	1272.6	1283.8
22.5°	1266.7	1265.2	1248.1	1236.9	1236.9	1222.1	1207.9	1201.2	1194.5	1196.8	1200.5
25°	1222.1	1199.0	1178.2	1161.8	1158.1	1134.3	1115.0	1109.0	1097.8	1106.8	1108.3
27.5°	1150.7	1124.6	1091.2	1077.0	1057.7	1048.0	1034.6	1016.8	993.7	1007.1	1004.9
30°	1074.0	1035.4	1007.8	973.6	943.1	940.9	915.6	885.9	874.0	874.0	880.7
32.5°	988.5	937.2	897.0	848.7	818.9	806.3	775.8	746.0	752.7	730.4	738.6
35°	888.8	821.2	770.6	723.7	701.4	686.5	647.1	630.7	612.9	602.5	621.8
37.5°	793.6	715.5	650.8	599.5	591.3	564.5	537.8	527.4	516.9	521.4	520.7
40°	677.6	608.4	550.4	510.2	496.1	483.5	465.6	453.0	446.3	450.0	450.7
42.5°	572.7	514.7	471.6	443.3	431.4	422.5	413.6	403.1	400.9	400.9	403.9
45°	491.7	444.0	415.0	392.0	385.3	378.6	371.9	367.4	365.9	363.0	365.2
47.5°	426.9	389.0	371.2	354.0	346.6	345.1	339.2	336.9	334.0	333.2	334.0
50°	372.6	348.8	332.5	322.8	317.6	315.4	312.4	307.9	306.4	310.2	308.7
52.5°	334.7	312.4	303.5	293.8	290.8	287.8	283.4	284.1	283.4	281.9	281.9
55°	296.8	282.6	273.7	266.3	265.5	262.6	258.8	257.4	256.6	255.1	257.4
57.5°	266.3	255.1	246.9	240.2	237.3	237.3	233.6	230.6	230.6	229.8	230.6
60°	235.8	224.6	219.4	212.7	210.5	209.8	207.5	206.0	203.8	203.8	203.8
62.5°	207.5	198.6	192.6	186.7	187.4	183.7	180.7	179.3	179.3	180.0	180.0
65°	180.7	174.8	167.4	162.1	160.7	159.9	158.4	157.7	155.5	156.9	156.9
67.5°	156.2	148.0	143.6	141.3	139.1	138.3	136.9	135.4	134.6	133.9	135.4
70°	131.7	125.0	121.2	119.8	117.5	116.8	116.0	113.8	114.5	115.3	116.0
72.5°	109.3	103.4	102.6	98.2	98.2	98.2	95.2	96.7	95.9	94.5	95.9
75°	86.3	83.3	81.8	79.6	80.3	79.6	78.8	76.6	76.6	77.4	78.1
77.5°	68.4	65.5	64.7	62.5	61.0	62.5	61.0	60.2	60.2	61.0	61.0
80°	50.6	49.1	46.9	46.9	46.9	46.1	46.1	46.1	45.4	44.6	45.4
82.5°	33.5	33.5	32.7	32.0	32.7	31.2	32.0	32.0	32.0	32.0	32.0
85°	21.6	20.8	20.8	20.1	20.1	20.1	20.8	19.3	19.3	20.1	20.1
87.5°	9.7	9.7	9.7	10.4	9.7	9.7	9.7	10.4	9.7	9.7	9.7
90°	6.9	7.2	7.6	7.9	8.1	8.2	8.3	8.5	8.6	8.8	8.6
92.5°	8.0	8.1	8.3	8.4	8.5	8.5	8.6	8.7	8.7	8.8	8.7
95°	13.1	13.4	13.8	14.1	14.3	14.3	14.2	14.1	14.1	14.0	14.1
97.5°	16.8	17.0	17.3	17.5	17.6	17.6	17.7	17.8	17.8	17.9	17.8
100°	19.1	19.7	20.2	20.8	21.1	21.2	21.3	21.5	21.6	21.8	21.6
102.5°	20.0	20.8	21.6	22.4	22.8	22.9	23.1	23.4	23.6	23.8	23.6
105°	20.6	21.4	22.2	23.0	23.4	23.5	23.8	24.1	24.4	24.7	24.4
107.5°	21.3	22.1	22.9	23.7	24.1	24.2	24.5	24.8	25.1	25.4	25.1
110°	49.7	42.5	35.2	28.0	24.4	24.5	24.8	25.1	25.4	25.7	25.4

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	134.1	103.0	71.8	40.7	25.1	25.2	25.4	25.6	25.8	26.0	25.8
115°	167.2	133.8	100.3	66.8	50.1	47.5	42.3	37.1	31.9	26.7	31.9
117.5°	208.0	197.6	187.3	177.0	171.8	162.3	143.4	124.4	105.5	86.5	105.5
120°	239.4	240.2	241.1	242.0	242.4	237.5	227.8	218.0	208.3	198.5	208.3
122.5°	258.1	258.5	259.0	259.4	259.6	259.6	259.7	259.8	259.9	260.0	259.9
125°	275.4	275.9	276.4	276.9	277.2	277.3	277.5	277.8	278.0	278.2	278.0
127.5°	291.6	292.3	293.0	293.7	294.1	294.1	294.2	294.3	294.4	294.5	294.4
130°	307.0	307.8	308.5	309.3	309.7	309.7	309.6	309.5	309.5	309.4	309.5
132.5°	322.1	322.8	323.4	324.1	324.4	324.4	324.3	324.2	324.2	324.1	324.2
135°	336.1	336.9	337.6	338.3	338.7	338.6	338.5	338.3	338.2	338.0	338.2
137.5°	349.5	350.2	350.9	351.6	352.0	351.9	351.7	351.5	351.3	351.1	351.3
140°	362.4	363.1	363.7	364.4	364.7	364.5	364.2	363.8	363.5	363.1	363.5
142.5°	374.4	375.0	375.5	376.1	376.4	376.2	375.9	375.5	375.2	374.8	375.2
145°	385.4	385.9	386.4	386.9	387.2	387.0	386.7	386.3	386.0	385.6	386.0
147.5°	395.4	395.7	396.1	396.4	396.6	396.5	396.2	395.9	395.6	395.3	395.6
150°	404.2	404.6	405.1	405.5	405.7	405.5	405.2	404.8	404.5	404.1	404.5
152.5°	412.3	412.8	413.2	413.7	413.9	413.6	413.1	412.6	412.1	411.6	412.1
155°	419.5	419.9	420.4	420.8	421.0	420.7	420.1	419.6	419.0	418.4	419.0
157.5°	425.7	426.2	426.7	427.2	427.5	427.2	426.6	426.1	425.5	424.9	425.5
160°	431.2	431.6	432.1	432.5	432.7	432.5	432.0	431.5	431.0	430.5	431.0
162.5°	436.2	436.7	437.2	437.7	437.9	437.6	436.9	436.3	435.6	435.0	435.6
165°	440.1	440.6	441.1	441.6	441.8	441.6	441.1	440.6	440.1	439.6	440.1
167.5°	443.6	444.1	444.6	445.1	445.4	445.1	444.4	443.8	443.1	442.5	443.1
170°	446.2	446.7	447.2	447.7	448.0	447.7	447.0	446.4	445.7	445.1	445.7
172.5°	448.2	448.7	449.2	449.7	450.0	449.7	449.0	448.3	447.7	447.0	447.7
175°	449.5	450.0	450.5	451.0	451.3	450.9	450.2	449.5	448.7	448.0	448.7
177.5°	449.8	450.3	450.8	451.3	451.6	451.3	450.6	450.0	449.3	448.7	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1025.7	1020.5	1016.0	1016.8	1020.5	1017.5	1010.1	1000.4	996.7	992.2	996.7
5°	1087.4	1083.0	1074.0	1074.8	1072.6	1069.6	1057.7	1042.8	1042.8	1030.9	1029.4
7.5°	1148.4	1141.7	1135.8	1134.3	1126.1	1120.2	1109.7	1088.9	1080.7	1066.6	1058.4
10°	1216.9	1211.6	1205.0	1196.8	1192.3	1181.9	1164.8	1134.3	1119.4	1100.1	1085.9
12.5°	1286.0	1285.3	1270.4	1254.0	1253.3	1236.9	1225.0	1184.1	1164.0	1138.0	1104.5
15°	1329.9	1326.2	1318.0	1309.8	1312.1	1294.2	1267.4	1219.1	1205.7	1174.5	1138.8
17.5°	1329.2	1329.2	1326.9	1325.4	1323.2	1318.0	1303.1	1271.2	1249.6	1210.2	1176.7
20°	1286.8	1296.4	1298.7	1297.9	1305.4	1309.1	1308.3	1288.3	1271.2	1236.2	1202.0
22.5°	1202.0	1224.3	1234.0	1239.9	1255.5	1263.7	1283.1	1275.6	1271.2	1245.1	1216.1
25°	1123.1	1130.6	1159.6	1161.1	1182.6	1202.7	1222.1	1234.7	1251.1	1241.4	1216.9
27.5°	1021.2	1038.3	1059.2	1074.8	1079.3	1120.2	1152.1	1175.9	1213.1	1216.1	1207.9
30°	905.9	914.1	948.3	969.2	993.0	1022.7	1068.8	1109.7	1143.2	1173.7	1184.1
32.5°	765.4	798.8	818.9	844.2	865.0	917.8	974.4	1027.2	1065.9	1117.2	1139.5
35°	636.7	662.7	696.9	707.4	745.3	789.9	863.5	931.2	990.0	1042.1	1087.4
37.5°	530.3	551.2	587.6	604.0	626.3	683.6	745.3	829.3	900.0	964.0	1020.5
40°	457.4	473.1	500.6	505.8	524.4	576.4	626.3	705.1	798.8	885.1	946.9
42.5°	407.6	415.0	433.6	440.3	452.2	487.2	531.8	606.2	693.2	782.5	869.5
45°	371.9	377.1	388.3	394.2	409.1	424.7	461.2	520.7	589.1	679.1	772.8
47.5°	339.9	346.6	351.1	354.8	363.0	380.1	403.9	447.8	513.2	595.8	686.5
50°	313.1	315.4	323.6	324.3	329.5	340.7	363.0	389.8	441.8	508.8	596.5
52.5°	286.4	288.6	293.8	299.0	301.2	310.2	325.0	347.4	386.0	438.8	516.9
55°	259.6	262.6	267.8	271.5	273.7	281.2	290.1	311.7	342.1	379.3	443.3
57.5°	232.8	239.5	241.0	243.2	246.9	255.1	263.3	275.9	299.8	334.0	380.8
60°	207.5	209.8	215.0	217.2	220.9	225.4	235.8	245.5	262.6	289.3	331.7
62.5°	181.5	186.7	188.9	191.2	194.1	199.3	206.0	216.4	231.3	252.9	286.4
65°	159.2	159.9	164.4	167.4	170.3	174.0	180.7	190.4	199.3	219.4	244.0
67.5°	137.6	139.1	140.6	143.6	147.3	151.0	156.9	162.1	173.3	186.7	206.0
70°	116.8	116.8	120.5	122.7	122.0	126.4	130.9	136.9	145.0	157.7	173.3
72.5°	98.2	97.4	100.4	101.2	102.6	105.6	108.6	114.5	119.0	128.7	140.6
75°	78.1	79.6	81.1	81.1	83.3	85.5	88.5	91.5	96.7	102.6	111.6
77.5°	61.7	61.7	63.2	64.0	66.2	65.5	68.4	71.4	75.1	80.3	87.0
80°	45.4	46.9	46.9	46.9	47.6	48.3	51.3	53.6	55.8	59.5	62.5
82.5°	32.0	32.0	33.5	33.5	33.5	35.0	35.0	35.7	37.2	39.4	41.7
85°	20.1	20.1	20.1	20.8	20.1	20.8	22.3	21.6	22.3	23.8	23.8
87.5°	9.7	9.7	9.7	9.7	9.7	10.4	9.7	10.4	11.2	11.2	11.2
90°	8.5	8.3	8.2	8.1	7.9	7.6	7.2	6.9	6.5	5.9	5.3
92.5°	8.7	8.6	8.5	8.5	8.4	8.3	8.1	8.0	7.8	7.6	7.4
95°	14.1	14.2	14.3	14.3	14.1	13.8	13.4	13.1	12.7	12.2	11.7
97.5°	17.8	17.7	17.6	17.6	17.5	17.3	17.0	16.8	16.6	15.4	14.3
100°	21.5	21.3	21.2	21.1	20.8	20.2	19.7	19.1	18.5	17.3	16.1
102.5°	23.4	23.1	22.9	22.8	22.4	21.6	20.8	20.0	19.2	32.4	45.5
105°	24.1	23.8	23.5	23.4	23.0	22.2	21.4	20.6	19.8	39.6	59.3
107.5°	24.8	24.5	24.2	24.1	23.7	22.9	22.1	21.3	20.5	44.9	69.2
110°	25.1	24.8	24.5	24.4	28.0	35.2	42.5	49.7	56.9	77.8	98.7

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	25.6	25.4	25.2	25.1	40.7	71.8	103.0	134.1	165.3	166.5	167.7
115°	37.1	42.3	47.5	50.1	66.8	100.3	133.8	167.2	200.7	198.9	197.1
117.5°	124.4	143.4	162.3	171.8	177.0	187.3	197.6	208.0	218.3	217.1	215.9
120°	218.0	227.8	237.5	242.4	242.0	241.1	240.2	239.4	238.5	237.2	235.9
122.5°	259.8	259.7	259.6	259.6	259.4	259.0	258.5	258.1	257.7	256.3	254.8
125°	277.8	277.5	277.3	277.2	276.9	276.4	275.9	275.4	274.9	273.5	272.1
127.5°	294.3	294.2	294.1	294.1	293.7	293.0	292.3	291.6	290.9	289.8	288.7
130°	309.5	309.6	309.7	309.7	309.3	308.5	307.8	307.0	306.2	305.4	304.6
132.5°	324.2	324.3	324.4	324.4	324.1	323.4	322.8	322.1	321.5	320.7	319.9
135°	338.3	338.5	338.6	338.7	338.3	337.6	336.9	336.1	335.4	334.8	334.1
137.5°	351.5	351.7	351.9	352.0	351.6	350.9	350.2	349.5	348.8	348.1	347.3
140°	363.8	364.2	364.5	364.7	364.4	363.7	363.1	362.4	361.8	361.0	360.2
142.5°	375.5	375.9	376.2	376.4	376.1	375.5	375.0	374.4	373.8	372.9	371.9
145°	386.3	386.7	387.0	387.2	386.9	386.4	385.9	385.4	384.9	383.7	382.5
147.5°	395.9	396.2	396.5	396.6	396.4	396.1	395.7	395.4	395.0	393.8	392.6
150°	404.8	405.2	405.5	405.7	405.5	405.1	404.6	404.2	403.8	402.6	401.5
152.5°	412.6	413.1	413.6	413.9	413.7	413.2	412.8	412.3	411.9	410.8	409.7
155°	419.6	420.1	420.7	421.0	420.8	420.4	419.9	419.5	419.1	418.2	417.4
157.5°	426.1	426.6	427.2	427.5	427.2	426.7	426.2	425.7	425.2	424.6	423.9
160°	431.5	432.0	432.5	432.7	432.5	432.1	431.6	431.2	430.8	430.4	429.9
162.5°	436.3	436.9	437.6	437.9	437.7	437.2	436.7	436.2	435.7	435.3	434.9
165°	440.6	441.1	441.6	441.8	441.6	441.1	440.6	440.1	439.6	439.4	439.2
167.5°	443.8	444.4	445.1	445.4	445.1	444.6	444.1	443.6	443.1	442.9	442.7
170°	446.4	447.0	447.7	448.0	447.7	447.2	446.7	446.2	445.7	445.6	445.4
172.5°	448.3	449.0	449.7	450.0	449.7	449.2	448.7	448.2	447.7	447.5	447.4
175°	449.5	450.2	450.9	451.3	451.0	450.5	450.0	449.5	449.0	448.8	448.7
177.5°	450.0	450.6	451.3	451.6	451.3	450.8	450.3	449.8	449.3	449.2	449.2
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	993.0	989.3	987.0	988.5	984.0	972.9	972.9	976.6	972.1	967.7	961.0
5°	1020.5	1013.1	1008.6	1007.8	997.4	979.6	975.9	972.1	962.5	952.1	940.9
7.5°	1047.3	1033.9	1026.4	1021.2	1006.4	983.3	973.6	965.5	949.8	934.2	920.1
10°	1069.6	1050.2	1041.3	1033.1	1013.8	984.8	969.2	954.3	934.2	914.1	896.3
12.5°	1087.4	1065.1	1054.0	1042.1	1018.3	980.3	961.0	937.2	917.1	890.3	872.5
15°	1117.2	1071.1	1060.7	1049.5	1025.0	972.9	949.1	922.3	894.8	859.1	839.7
17.5°	1141.0	1079.3	1078.5	1054.7	1022.7	969.9	933.5	898.5	868.8	833.1	802.6
20°	1155.1	1091.9	1080.0	1055.4	1015.3	949.8	911.9	873.2	841.2	798.1	767.6
22.5°	1167.0	1109.7	1078.5	1048.8	999.7	943.1	887.4	850.9	807.0	760.2	731.2
25°	1171.5	1113.5	1080.7	1046.5	988.5	923.8	860.6	821.2	772.1	729.7	690.2
27.5°	1172.2	1112.7	1072.6	1036.9	972.9	898.5	833.8	792.1	737.8	688.8	649.3
30°	1164.8	1104.5	1068.1	1029.4	958.0	875.5	801.1	755.0	696.9	647.8	606.9
32.5°	1142.5	1088.2	1058.4	1016.0	938.7	843.5	769.8	718.5	657.5	609.2	569.7
35°	1105.3	1068.1	1035.4	995.9	913.4	813.7	738.6	678.3	616.6	570.5	533.3
37.5°	1059.2	1039.1	1008.6	969.9	884.4	786.9	703.6	636.7	575.0	530.3	493.9
40°	996.7	1001.9	972.1	937.2	850.2	750.5	658.3	594.3	536.3	494.6	458.9
42.5°	929.0	950.6	933.5	900.0	812.2	710.3	624.8	554.1	497.6	454.5	424.7
45°	856.1	893.3	882.9	858.3	772.8	667.9	577.2	508.8	458.9	417.3	391.2
47.5°	776.5	829.3	829.3	811.5	728.9	625.5	536.3	466.4	417.3	387.5	362.2
50°	695.5	755.0	764.6	752.7	679.8	577.2	486.4	423.2	380.8	351.8	333.2
52.5°	610.7	679.8	697.7	691.7	627.8	531.1	445.5	383.8	345.1	319.8	303.5
55°	529.6	609.9	629.3	631.5	572.0	480.5	400.2	345.9	308.7	291.6	277.4
57.5°	453.0	530.3	551.9	555.6	515.5	434.4	357.8	310.2	276.7	262.6	251.4
60°	387.5	452.2	480.5	488.7	453.7	380.8	318.3	272.2	246.9	233.6	223.1
62.5°	334.0	386.0	415.8	418.0	402.4	334.0	277.4	238.8	217.2	205.3	200.1
65°	281.9	328.8	346.6	355.5	342.9	289.3	239.5	207.5	190.4	180.0	174.8
67.5°	240.2	270.0	284.9	296.8	284.1	244.0	203.8	177.8	165.1	154.7	151.7
70°	197.1	221.7	232.8	244.7	233.6	203.1	174.0	150.2	139.1	130.9	127.2
72.5°	157.7	177.0	187.4	194.9	188.2	162.9	139.1	122.7	114.5	108.6	106.4
75°	125.0	138.3	144.3	149.5	146.5	127.2	112.3	98.9	91.5	86.3	84.8
77.5°	95.2	104.9	111.6	113.1	109.3	96.7	84.0	75.9	69.9	66.9	65.5
80°	67.7	73.6	77.4	79.6	75.9	70.7	61.7	55.8	50.6	46.9	46.1
82.5°	45.4	48.3	51.3	50.6	49.1	44.6	39.4	36.4	34.2	31.2	31.2
85°	26.0	26.8	28.3	29.0	28.3	25.3	22.3	20.8	19.3	17.1	17.1
87.5°	11.2	11.9	11.9	12.6	11.2	11.2	9.7	8.2	8.2	7.4	6.7
90°	4.8	4.2	3.9	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.1	6.9	6.8	6.9	7.2	7.5	7.8	8.1	7.8	7.5	7.2
95°	11.2	10.7	10.4	11.6	14.0	16.3	18.7	21.1	18.7	16.3	14.0
97.5°	13.1	12.0	11.4	14.4	20.3	26.2	32.2	38.1	32.2	26.2	20.3
100°	14.8	13.6	13.0	18.0	27.9	37.8	47.7	57.6	47.7	37.8	27.9
102.5°	58.7	71.8	78.4	78.5	78.6	78.8	78.9	79.1	78.9	78.8	78.6
105°	79.1	98.8	108.7	107.6	105.4	103.3	101.1	98.9	101.1	103.3	105.4
107.5°	93.6	117.9	130.1	129.2	127.4	125.6	123.8	122.0	123.8	125.6	127.4
110°	119.6	140.5	151.0	150.2	148.7	147.2	145.6	144.1	145.6	147.2	148.7

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	169.0	170.2	170.8	170.2	168.9	167.6	166.3	165.0	166.3	167.6	168.9
115°	195.3	193.5	192.6	192.0	190.8	189.5	188.3	187.1	188.3	189.5	190.8
117.5°	214.6	213.4	212.8	212.1	210.6	209.2	207.7	206.3	207.7	209.2	210.6
120°	234.6	233.3	232.6	232.1	231.0	229.9	228.9	227.8	228.9	229.9	231.0
122.5°	253.4	251.9	251.2	250.6	249.5	248.3	247.2	246.0	247.2	248.3	249.5
125°	270.8	269.4	268.7	268.2	267.3	266.4	265.4	264.5	265.4	266.4	267.3
127.5°	287.6	286.5	286.0	285.5	284.5	283.4	282.4	281.4	282.4	283.4	284.5
130°	303.8	303.0	302.6	302.0	300.9	299.7	298.6	297.4	298.6	299.7	300.9
132.5°	319.1	318.3	317.9	317.4	316.5	315.5	314.6	313.6	314.6	315.5	316.5
135°	333.5	332.8	332.5	331.9	330.8	329.6	328.5	327.3	328.5	329.6	330.8
137.5°	346.6	345.9	345.5	345.1	344.2	343.3	342.5	341.6	342.5	343.3	344.2
140°	359.4	358.6	358.2	357.9	357.3	356.8	356.2	355.6	356.2	356.8	357.3
142.5°	371.0	370.1	369.6	369.3	368.8	368.3	367.8	367.3	367.8	368.3	368.8
145°	381.2	380.0	379.4	379.4	379.5	379.6	379.6	379.7	379.6	379.6	379.5
147.5°	391.3	390.1	389.5	389.6	389.8	390.0	390.2	390.4	390.2	390.0	389.8
150°	400.3	399.2	398.6	398.8	399.3	399.8	400.3	400.8	400.3	399.8	399.3
152.5°	408.6	407.5	407.0	407.3	407.9	408.4	409.0	409.6	409.0	408.4	407.9
155°	416.5	415.6	415.2	415.5	416.2	416.8	417.5	418.1	417.5	416.8	416.2
157.5°	423.3	422.6	422.3	422.6	423.2	423.7	424.3	424.9	424.3	423.7	423.2
160°	429.5	429.0	428.8	429.0	429.5	429.9	430.4	430.8	430.4	429.9	429.5
162.5°	434.6	434.2	434.0	434.2	434.7	435.1	435.6	436.0	435.6	435.1	434.7
165°	438.9	438.7	438.6	438.8	439.2	439.7	440.1	440.5	440.1	439.7	439.2
167.5°	442.5	442.3	442.2	442.4	442.8	443.3	443.7	444.1	443.7	443.3	442.8
170°	445.3	445.2	445.1	445.3	445.7	446.2	446.6	447.0	446.6	446.2	445.7
172.5°	447.2	447.1	447.0	447.2	447.7	448.1	448.6	449.0	448.6	448.1	447.7
175°	448.5	448.4	448.3	448.6	449.1	449.6	450.1	450.6	450.1	449.6	449.1
177.5°	449.1	449.0	449.0	449.3	449.8	450.3	450.8	451.3	450.8	450.3	449.8
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	957.3	961.0	960.2	952.8	944.6	937.9	925.3	926.8	922.3	923.1	927.5
5°	933.5	933.5	930.5	920.1	906.7	899.3	885.1	881.4	872.5	871.7	871.0
7.5°	908.2	904.5	900.7	885.9	869.5	857.6	838.3	833.8	824.9	818.9	815.9
10°	878.4	873.2	865.8	848.7	828.6	813.7	793.6	787.7	770.6	763.1	758.7
12.5°	845.7	842.7	830.8	816.7	784.0	767.6	738.6	744.5	727.4	712.6	710.3
15°	813.0	801.8	795.1	772.1	732.6	725.2	702.1	690.2	674.6	662.7	662.7
17.5°	781.0	763.9	749.0	724.5	695.5	674.6	657.5	651.6	632.2	620.3	618.1
20°	738.6	719.3	715.5	680.6	660.5	637.4	621.1	606.2	592.1	586.9	583.1
22.5°	698.4	676.1	670.2	640.4	620.3	597.3	580.9	570.5	560.1	556.4	549.7
25°	655.3	641.9	633.0	601.0	578.7	557.1	545.9	538.5	528.8	528.1	523.6
27.5°	613.6	601.0	592.1	561.6	545.2	525.1	516.2	508.0	502.8	500.6	498.3
30°	577.9	563.8	553.4	531.1	511.0	494.6	487.2	482.0	479.0	475.3	474.5
32.5°	538.5	530.3	516.2	499.1	483.5	467.8	463.4	459.7	455.2	453.7	453.0
35°	505.0	493.9	485.0	465.6	458.9	445.5	440.3	437.4	431.4	429.9	428.4
37.5°	472.3	461.9	452.2	440.3	427.7	420.2	417.3	412.8	409.8	410.6	409.1
40°	439.6	431.4	424.0	411.3	403.9	400.2	394.2	389.8	388.3	389.0	388.3
42.5°	407.6	400.2	395.7	386.0	378.6	374.9	371.2	366.7	368.9	368.9	371.2
45°	378.6	371.9	368.9	361.5	357.0	351.1	347.4	346.6	349.6	348.8	348.8
47.5°	348.8	346.6	342.9	336.2	330.2	326.5	325.8	325.8	328.8	330.2	329.5
50°	325.8	321.3	316.9	311.7	307.2	305.7	303.5	305.0	307.9	307.9	309.4
52.5°	296.8	293.8	292.3	287.8	284.9	284.9	284.9	285.6	287.8	290.1	289.3
55°	271.5	269.3	267.8	265.5	261.8	262.6	261.8	263.3	265.5	267.8	269.3
57.5°	244.7	244.0	242.5	238.8	238.8	238.0	240.2	241.0	244.7	246.2	248.4
60°	220.9	218.7	218.7	215.7	215.7	215.7	217.9	220.2	223.1	223.9	225.4
62.5°	195.6	195.6	194.9	192.6	192.6	194.9	195.6	198.6	200.1	200.1	202.3
65°	171.8	171.1	170.3	171.1	171.8	171.8	174.0	175.5	177.0	177.8	178.5
67.5°	148.0	147.3	148.8	148.0	149.5	152.5	151.7	154.0	156.2	156.2	156.9
70°	125.7	127.2	126.4	127.9	127.2	128.7	130.9	131.7	131.7	132.4	134.6
72.5°	104.9	104.9	104.9	104.1	104.9	106.4	107.9	108.6	110.1	110.8	113.1
75°	84.8	84.8	83.3	84.8	84.8	86.3	87.8	87.8	87.8	89.3	91.5
77.5°	64.0	64.7	64.0	65.5	65.5	66.2	67.7	66.9	68.4	69.2	69.9
80°	46.9	46.1	46.1	46.1	46.9	46.9	48.3	49.1	49.1	51.3	49.8
82.5°	29.8	30.5	29.8	30.5	30.5	31.2	30.5	31.2	32.0	33.5	32.7
85°	17.1	16.4	16.4	17.1	16.4	16.4	17.1	16.4	17.1	16.4	17.1
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	3.5	3.9	4.2	4.8	5.3	5.9	6.5	6.9	7.2	7.6	7.9
92.5°	6.9	6.8	6.9	7.1	7.4	7.6	7.8	8.0	8.1	8.3	8.4
95°	11.6	10.4	10.7	11.2	11.7	12.2	12.7	13.1	13.4	13.8	14.1
97.5°	14.4	11.4	12.0	13.1	14.3	15.4	16.6	16.8	17.0	17.3	17.5
100°	18.0	13.0	13.6	14.8	16.1	17.3	18.5	19.1	19.7	20.2	20.8
102.5°	78.5	78.4	71.8	58.7	45.5	32.4	19.2	20.0	20.8	21.6	22.4
105°	107.6	108.7	98.8	79.1	59.3	39.6	19.8	20.6	21.4	22.2	23.0
107.5°	129.2	130.1	117.9	93.6	69.2	44.9	20.5	21.3	22.1	22.9	23.7
110°	150.2	151.0	140.5	119.6	98.7	77.8	56.9	49.7	42.5	35.2	28.0

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	170.2	170.8	170.2	169.0	167.7	166.5	165.3	134.1	103.0	71.8	40.7
115°	192.0	192.6	193.5	195.3	197.1	198.9	200.7	167.2	133.8	100.3	66.8
117.5°	212.1	212.8	213.4	214.6	215.9	217.1	218.3	208.0	197.6	187.3	177.0
120°	232.1	232.6	233.3	234.6	235.9	237.2	238.5	239.4	240.2	241.1	242.0
122.5°	250.6	251.2	251.9	253.4	254.8	256.3	257.7	258.1	258.5	259.0	259.4
125°	268.2	268.7	269.4	270.8	272.1	273.5	274.9	275.4	275.9	276.4	276.9
127.5°	285.5	286.0	286.5	287.6	288.7	289.8	290.9	291.6	292.3	293.0	293.7
130°	302.0	302.6	303.0	303.8	304.6	305.4	306.2	307.0	307.8	308.5	309.3
132.5°	317.4	317.9	318.3	319.1	319.9	320.7	321.5	322.1	322.8	323.4	324.1
135°	331.9	332.5	332.8	333.5	334.1	334.8	335.4	336.1	336.9	337.6	338.3
137.5°	345.1	345.5	345.9	346.6	347.3	348.1	348.8	349.5	350.2	350.9	351.6
140°	357.9	358.2	358.6	359.4	360.2	361.0	361.8	362.4	363.1	363.7	364.4
142.5°	369.3	369.6	370.1	371.0	371.9	372.9	373.8	374.4	375.0	375.5	376.1
145°	379.4	379.4	380.0	381.2	382.5	383.7	384.9	385.4	385.9	386.4	386.9
147.5°	389.6	389.5	390.1	391.3	392.6	393.8	395.0	395.4	395.7	396.1	396.4
150°	398.8	398.6	399.2	400.3	401.5	402.6	403.8	404.2	404.6	405.1	405.5
152.5°	407.3	407.0	407.5	408.6	409.7	410.8	411.9	412.3	412.8	413.2	413.7
155°	415.5	415.2	415.6	416.5	417.4	418.2	419.1	419.5	419.9	420.4	420.8
157.5°	422.6	422.3	422.6	423.3	423.9	424.6	425.2	425.7	426.2	426.7	427.2
160°	429.0	428.8	429.0	429.5	429.9	430.4	430.8	431.2	431.6	432.1	432.5
162.5°	434.2	434.0	434.2	434.6	434.9	435.3	435.7	436.2	436.7	437.2	437.7
165°	438.8	438.6	438.7	438.9	439.2	439.4	439.6	440.1	440.6	441.1	441.6
167.5°	442.4	442.2	442.3	442.5	442.7	442.9	443.1	443.6	444.1	444.6	445.1
170°	445.3	445.1	445.2	445.3	445.4	445.6	445.7	446.2	446.7	447.2	447.7
172.5°	447.2	447.0	447.1	447.2	447.4	447.5	447.7	448.2	448.7	449.2	449.7
175°	448.6	448.3	448.4	448.5	448.7	448.8	449.0	449.5	450.0	450.5	451.0
177.5°	449.3	449.0	449.0	449.1	449.2	449.2	449.3	449.8	450.3	450.8	451.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	922.3	924.5	919.3	917.8	919.3	914.1	915.6	917.1	917.1	919.3	920.8
5°	868.8	865.8	860.6	859.1	857.6	859.8	858.3	860.6	861.3	866.5	867.3
7.5°	815.9	811.5	807.0	802.6	801.1	797.4	801.1	801.1	806.3	804.8	808.5
10°	753.5	752.7	746.8	744.5	741.6	735.6	743.8	741.6	745.3	752.0	753.5
12.5°	707.4	699.2	702.9	692.5	696.2	690.2	691.0	691.0	696.9	697.7	696.2
15°	663.5	656.8	647.1	642.6	640.4	637.4	647.1	647.8	643.4	653.8	650.1
17.5°	618.8	618.8	609.9	607.7	601.7	604.7	603.2	604.0	602.5	609.9	613.6
20°	580.2	576.4	573.5	574.2	566.8	565.3	563.8	565.3	570.5	575.7	577.2
22.5°	548.9	546.7	539.3	540.7	534.8	537.0	535.5	539.3	540.0	540.0	545.2
25°	519.2	516.2	516.9	514.0	511.7	511.7	509.5	511.7	514.7	516.2	516.9
27.5°	496.9	494.6	490.9	488.7	490.2	486.4	489.4	491.7	491.7	490.2	491.7
30°	470.1	471.6	471.6	464.1	467.1	465.6	467.8	469.3	469.3	470.1	468.6
32.5°	452.2	447.8	447.0	446.3	446.3	443.3	443.3	445.5	446.3	447.0	449.3
35°	428.4	428.4	424.7	426.9	424.0	424.7	424.0	424.7	426.2	424.0	426.2
37.5°	406.9	407.6	406.1	407.6	408.3	406.9	405.4	408.3	406.9	406.9	405.4
40°	388.3	387.5	388.3	388.3	388.3	389.0	387.5	387.5	387.5	386.0	384.5
42.5°	372.6	368.2	369.7	370.4	368.2	368.2	368.9	368.2	370.4	365.9	365.9
45°	350.3	348.8	349.6	349.6	351.1	348.8	350.3	351.1	348.8	348.1	346.6
47.5°	330.2	331.7	330.2	331.7	331.7	333.2	330.2	331.0	331.7	328.8	326.5
50°	310.2	310.2	312.4	311.7	312.4	310.9	310.9	310.2	310.9	309.4	307.2
52.5°	291.6	289.3	293.1	292.3	291.6	290.8	290.1	290.8	289.3	287.8	287.8
55°	268.5	268.5	270.7	271.5	271.5	270.0	268.5	269.3	268.5	267.8	267.0
57.5°	249.9	246.9	248.4	249.2	249.2	246.9	248.4	246.9	246.9	247.7	245.5
60°	226.1	226.1	224.6	226.9	226.9	225.4	225.4	226.1	224.6	223.9	223.1
62.5°	200.8	201.6	203.8	204.5	205.3	203.8	202.3	203.1	203.1	200.8	201.6
65°	179.3	180.7	183.7	183.0	181.5	182.2	180.7	181.5	179.3	180.0	177.8
67.5°	158.4	157.7	158.4	158.4	159.9	159.2	157.7	157.7	156.9	159.2	156.9
70°	136.1	136.1	136.1	136.1	136.9	137.6	136.1	134.6	135.4	133.9	133.1
72.5°	113.1	113.8	113.1	114.5	112.3	113.8	113.8	113.1	112.3	112.3	112.3
75°	91.5	93.0	90.7	91.5	90.7	92.2	91.5	91.5	90.0	89.3	90.0
77.5°	69.9	70.7	69.2	69.9	69.2	69.9	69.9	69.2	69.2	69.2	69.2
80°	49.8	50.6	49.8	49.1	48.3	49.8	48.3	49.1	49.8	49.1	50.6
82.5°	32.0	32.0	31.2	32.0	30.5	30.5	31.2	31.2	30.5	32.0	30.5
85°	15.6	15.6	17.1	15.6	14.9	14.9	14.9	15.6	14.9	16.4	15.6
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	8.1	8.2	8.3	8.5	8.6	8.8	8.6	8.5	8.3	8.2	8.1
92.5°	8.5	8.5	8.6	8.7	8.7	8.8	8.7	8.7	8.6	8.5	8.5
95°	14.3	14.3	14.2	14.1	14.1	14.0	14.1	14.1	14.2	14.3	14.3
97.5°	17.6	17.6	17.7	17.8	17.8	17.9	17.8	17.8	17.7	17.6	17.6
100°	21.1	21.2	21.3	21.5	21.6	21.8	21.6	21.5	21.3	21.2	21.1
102.5°	22.8	22.9	23.1	23.4	23.6	23.8	23.6	23.4	23.1	22.9	22.8
105°	23.4	23.5	23.8	24.1	24.4	24.7	24.4	24.1	23.8	23.5	23.4
107.5°	24.1	24.2	24.5	24.8	25.1	25.4	25.1	24.8	24.5	24.2	24.1
110°	24.4	24.5	24.8	25.1	25.4	25.7	25.4	25.1	24.8	24.5	24.4

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	25.1	25.2	25.4	25.6	25.8	26.0	25.8	25.6	25.4	25.2	25.1
115°	50.1	47.5	42.3	37.1	31.9	26.7	31.9	37.1	42.3	47.5	50.1
117.5°	171.8	162.3	143.4	124.4	105.5	86.5	105.5	124.4	143.4	162.3	171.8
120°	242.4	237.5	227.8	218.0	208.3	198.5	208.3	218.0	227.8	237.5	242.4
122.5°	259.6	259.6	259.7	259.8	259.9	260.0	259.9	259.8	259.7	259.6	259.6
125°	277.2	277.3	277.5	277.8	278.0	278.2	278.0	277.8	277.5	277.3	277.2
127.5°	294.1	294.1	294.2	294.3	294.4	294.5	294.4	294.3	294.2	294.1	294.1
130°	309.7	309.7	309.6	309.5	309.5	309.4	309.5	309.5	309.6	309.7	309.7
132.5°	324.4	324.4	324.3	324.2	324.2	324.1	324.2	324.2	324.3	324.4	324.4
135°	338.7	338.6	338.5	338.3	338.2	338.0	338.2	338.3	338.5	338.6	338.7
137.5°	352.0	351.9	351.7	351.5	351.3	351.1	351.3	351.5	351.7	351.9	352.0
140°	364.7	364.5	364.2	363.8	363.5	363.1	363.5	363.8	364.2	364.5	364.7
142.5°	376.4	376.2	375.9	375.5	375.2	374.8	375.2	375.5	375.9	376.2	376.4
145°	387.2	387.0	386.7	386.3	386.0	385.6	386.0	386.3	386.7	387.0	387.2
147.5°	396.6	396.5	396.2	395.9	395.6	395.3	395.6	395.9	396.2	396.5	396.6
150°	405.7	405.5	405.2	404.8	404.5	404.1	404.5	404.8	405.2	405.5	405.7
152.5°	413.9	413.6	413.1	412.6	412.1	411.6	412.1	412.6	413.1	413.6	413.9
155°	421.0	420.7	420.1	419.6	419.0	418.4	419.0	419.6	420.1	420.7	421.0
157.5°	427.5	427.2	426.6	426.1	425.5	424.9	425.5	426.1	426.6	427.2	427.5
160°	432.7	432.5	432.0	431.5	431.0	430.5	431.0	431.5	432.0	432.5	432.7
162.5°	437.9	437.6	436.9	436.3	435.6	435.0	435.6	436.3	436.9	437.6	437.9
165°	441.8	441.6	441.1	440.6	440.1	439.6	440.1	440.6	441.1	441.6	441.8
167.5°	445.4	445.1	444.4	443.8	443.1	442.5	443.1	443.8	444.4	445.1	445.4
170°	448.0	447.7	447.0	446.4	445.7	445.1	445.7	446.4	447.0	447.7	448.0
172.5°	450.0	449.7	449.0	448.3	447.7	447.0	447.7	448.3	449.0	449.7	450.0
175°	451.3	450.9	450.2	449.5	448.7	448.0	448.7	449.5	450.2	450.9	451.3
177.5°	451.6	451.3	450.6	450.0	449.3	448.7	449.3	450.0	450.6	451.3	451.6
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	918.6	924.5	922.3	914.1	923.8	923.8	930.5	930.5	938.7	941.6	946.1
5°	866.5	871.0	874.7	871.0	877.7	888.1	894.0	899.3	910.4	914.9	921.6
7.5°	810.7	818.9	822.6	822.6	833.8	845.7	857.6	865.0	880.7	886.6	893.3
10°	756.4	766.1	773.6	772.8	791.4	798.8	813.7	830.8	846.4	855.4	865.0
12.5°	699.2	704.4	714.8	729.7	734.1	747.5	764.6	786.2	814.5	822.6	836.8
15°	651.6	665.7	673.9	680.6	691.0	703.6	722.2	743.1	771.3	789.2	804.0
17.5°	611.4	630.0	635.2	633.7	647.1	666.4	688.0	703.6	728.9	750.5	764.6
20°	578.7	586.1	595.0	598.8	609.2	630.0	650.8	668.7	689.5	706.6	723.0
22.5°	545.9	551.9	559.3	566.0	574.2	586.1	606.2	628.5	648.6	665.0	683.6
25°	519.2	522.9	529.6	534.8	543.7	551.9	566.0	590.6	614.4	624.0	640.4
27.5°	493.1	496.1	500.6	506.5	511.0	519.2	531.8	551.9	576.4	586.1	608.4
30°	470.1	472.3	476.8	479.7	482.0	491.7	501.3	516.9	535.5	548.9	565.3
32.5°	448.5	450.7	455.2	455.9	458.9	464.1	473.1	487.2	503.6	514.7	528.8
35°	424.7	426.2	430.7	432.1	434.4	438.8	445.5	455.9	470.8	479.0	491.7
37.5°	406.1	405.4	408.3	410.6	413.6	415.8	418.0	428.4	439.6	447.0	456.7
40°	386.0	384.5	385.3	388.3	389.8	392.7	392.7	403.1	410.6	416.5	424.0
42.5°	365.9	365.2	363.7	365.2	366.7	367.4	368.2	375.6	383.1	388.3	396.4
45°	345.9	345.1	343.6	344.4	344.4	345.9	348.1	351.1	356.3	360.7	365.2
47.5°	327.3	325.8	323.6	322.8	324.3	324.3	324.3	327.3	332.5	334.0	338.4
50°	307.9	305.7	302.7	301.2	301.2	300.5	302.0	302.7	307.2	308.7	312.4
52.5°	287.1	285.6	282.6	279.7	280.4	278.9	279.7	280.4	281.9	284.1	286.4
55°	266.3	263.3	261.1	260.3	258.1	258.1	255.9	258.8	258.1	258.8	261.8
57.5°	246.2	243.2	239.5	238.0	235.8	235.0	233.6	232.8	233.6	235.8	238.0
60°	222.4	220.9	218.7	216.4	215.0	212.7	211.2	211.2	210.5	210.5	211.2
62.5°	199.3	198.6	195.6	194.9	193.4	191.9	189.7	188.2	188.2	189.7	190.4
65°	177.0	176.3	174.0	173.3	169.6	168.1	167.4	166.6	165.1	165.1	165.1
67.5°	156.2	154.0	154.0	150.2	147.3	145.8	144.3	143.6	143.6	143.6	144.3
70°	133.1	133.1	130.9	128.7	125.7	126.4	124.2	122.0	122.0	120.5	121.2
72.5°	110.8	110.1	107.9	107.1	104.9	102.6	101.2	102.6	100.4	99.7	100.4
75°	89.3	88.5	87.0	85.5	86.3	84.0	81.8	81.1	81.1	79.6	79.6
77.5°	68.4	69.9	66.9	66.2	64.7	63.2	62.5	61.7	61.7	61.7	63.2
80°	47.6	48.3	48.3	46.9	47.6	45.4	45.4	45.4	43.1	43.9	44.6
82.5°	30.5	30.5	29.8	30.5	29.8	29.8	29.0	29.0	28.3	28.3	29.0
85°	17.1	16.4	15.6	17.1	16.4	16.4	15.6	15.6	15.6	15.6	15.6
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	7.9	7.6	7.2	6.9	6.5	5.9	5.3	4.8	4.2	3.9	3.5
92.5°	8.4	8.3	8.1	8.0	7.8	7.6	7.4	7.1	6.9	6.8	6.9
95°	14.1	13.8	13.4	13.1	12.7	12.2	11.7	11.2	10.7	10.4	11.6
97.5°	17.5	17.3	17.0	16.8	16.6	15.4	14.3	13.1	12.0	11.4	14.4
100°	20.8	20.2	19.7	19.1	18.5	17.3	16.1	14.8	13.6	13.0	18.0
102.5°	22.4	21.6	20.8	20.0	19.2	32.4	45.5	58.7	71.8	78.4	78.5
105°	23.0	22.2	21.4	20.6	19.8	39.6	59.3	79.1	98.8	108.7	107.6
107.5°	23.7	22.9	22.1	21.3	20.5	44.9	69.2	93.6	117.9	130.1	129.2
110°	28.0	35.2	42.5	49.7	56.9	77.8	98.7	119.6	140.5	151.0	150.2

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	40.7	71.8	103.0	134.1	165.3	166.5	167.7	169.0	170.2	170.8	170.2
115°	66.8	100.3	133.8	167.2	200.7	198.9	197.1	195.3	193.5	192.6	192.0
117.5°	177.0	187.3	197.6	208.0	218.3	217.1	215.9	214.6	213.4	212.8	212.1
120°	242.0	241.1	240.2	239.4	238.5	237.2	235.9	234.6	233.3	232.6	232.1
122.5°	259.4	259.0	258.5	258.1	257.7	256.3	254.8	253.4	251.9	251.2	250.6
125°	276.9	276.4	275.9	275.4	274.9	273.5	272.1	270.8	269.4	268.7	268.2
127.5°	293.7	293.0	292.3	291.6	290.9	289.8	288.7	287.6	286.5	286.0	285.5
130°	309.3	308.5	307.8	307.0	306.2	305.4	304.6	303.8	303.0	302.6	302.0
132.5°	324.1	323.4	322.8	322.1	321.5	320.7	319.9	319.1	318.3	317.9	317.4
135°	338.3	337.6	336.9	336.1	335.4	334.8	334.1	333.5	332.8	332.5	331.9
137.5°	351.6	350.9	350.2	349.5	348.8	348.1	347.3	346.6	345.9	345.5	345.1
140°	364.4	363.7	363.1	362.4	361.8	361.0	360.2	359.4	358.6	358.2	357.9
142.5°	376.1	375.5	375.0	374.4	373.8	372.9	371.9	371.0	370.1	369.6	369.3
145°	386.9	386.4	385.9	385.4	384.9	383.7	382.5	381.2	380.0	379.4	379.4
147.5°	396.4	396.1	395.7	395.4	395.0	393.8	392.6	391.3	390.1	389.5	389.6
150°	405.5	405.1	404.6	404.2	403.8	402.6	401.5	400.3	399.2	398.6	398.8
152.5°	413.7	413.2	412.8	412.3	411.9	410.8	409.7	408.6	407.5	407.0	407.3
155°	420.8	420.4	419.9	419.5	419.1	418.2	417.4	416.5	415.6	415.2	415.5
157.5°	427.2	426.7	426.2	425.7	425.2	424.6	423.9	423.3	422.6	422.3	422.6
160°	432.5	432.1	431.6	431.2	430.8	430.4	429.9	429.5	429.0	428.8	429.0
162.5°	437.7	437.2	436.7	436.2	435.7	435.3	434.9	434.6	434.2	434.0	434.2
165°	441.6	441.1	440.6	440.1	439.6	439.4	439.2	438.9	438.7	438.6	438.8
167.5°	445.1	444.6	444.1	443.6	443.1	442.9	442.7	442.5	442.3	442.2	442.4
170°	447.7	447.2	446.7	446.2	445.7	445.6	445.4	445.3	445.2	445.1	445.3
172.5°	449.7	449.2	448.7	448.2	447.7	447.5	447.4	447.2	447.1	447.0	447.2
175°	451.0	450.5	450.0	449.5	449.0	448.8	448.7	448.5	448.4	448.3	448.6
177.5°	451.3	450.8	450.3	449.8	449.3	449.2	449.2	449.1	449.0	449.0	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	967.7	967.7	967.7	967.7
2.5°	949.8	949.8	961.0	972.9
5°	929.0	934.2	952.1	968.4
7.5°	908.9	917.8	940.2	961.0
10°	884.4	896.3	923.8	948.3
12.5°	860.6	871.7	903.7	931.2
15°	827.1	841.2	875.5	909.7
17.5°	793.6	807.8	849.4	889.6
20°	754.2	772.8	819.7	873.2
22.5°	717.8	740.8	792.9	836.0
25°	677.6	713.3	761.6	817.4
27.5°	641.9	677.6	726.7	783.2
30°	601.7	638.2	688.8	740.8
32.5°	563.1	596.5	645.6	709.6
35°	522.9	554.9	602.5	667.2
37.5°	486.4	517.7	569.7	629.3
40°	450.7	483.5	528.1	587.6
42.5°	417.3	446.3	486.4	545.9
45°	386.8	407.6	444.8	500.6
47.5°	354.8	373.4	407.6	463.4
50°	325.0	340.7	370.4	422.5
52.5°	296.0	309.4	336.9	378.6
55°	270.0	282.6	302.7	343.6
57.5°	243.2	252.9	272.2	305.0
60°	217.2	226.1	241.7	268.5
62.5°	191.2	198.6	213.5	235.0
65°	168.1	174.0	185.2	203.8
67.5°	145.8	149.5	158.4	173.3
70°	124.2	127.2	134.6	146.5
72.5°	101.2	104.1	112.3	120.5
75°	81.8	82.6	88.5	95.2
77.5°	64.0	63.2	67.7	72.9
80°	43.9	46.1	49.8	52.1
82.5°	29.8	30.5	32.0	33.5
85°	16.4	17.1	17.1	19.3
87.5°	6.7	7.4	7.4	8.2
90°	2.7	1.9	1.1	0.3
92.5°	7.2	7.5	7.8	8.1
95°	14.0	16.3	18.7	21.1
97.5°	20.3	26.2	32.2	38.1
100°	27.9	37.8	47.7	57.6
102.5°	78.6	78.8	78.9	79.1
105°	105.4	103.3	101.1	98.9
107.5°	127.4	125.6	123.8	122.0
110°	148.7	147.2	145.6	144.1

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	168.9	167.6	166.3	165.0
115°	190.8	189.5	188.3	187.1
117.5°	210.6	209.2	207.7	206.3
120°	231.0	229.9	228.9	227.8
122.5°	249.5	248.3	247.2	246.0
125°	267.3	266.4	265.4	264.5
127.5°	284.5	283.4	282.4	281.4
130°	300.9	299.7	298.6	297.4
132.5°	316.5	315.5	314.6	313.6
135°	330.8	329.6	328.5	327.3
137.5°	344.2	343.3	342.5	341.6
140°	357.3	356.8	356.2	355.6
142.5°	368.8	368.3	367.8	367.3
145°	379.5	379.6	379.6	379.7
147.5°	389.8	390.0	390.2	390.4
150°	399.3	399.8	400.3	400.8
152.5°	407.9	408.4	409.0	409.6
155°	416.2	416.8	417.5	418.1
157.5°	423.2	423.7	424.3	424.9
160°	429.5	429.9	430.4	430.8
162.5°	434.7	435.1	435.6	436.0
165°	439.2	439.7	440.1	440.5
167.5°	442.8	443.3	443.7	444.1
170°	445.7	446.2	446.6	447.0
172.5°	447.7	448.1	448.6	449.0
175°	449.1	449.6	450.1	450.6
177.5°	449.8	450.3	450.8	451.3
180°	449.6	449.6	449.6	449.6

TEST NUMBER: P998445

CATALOG NUMBER: SA2XXDIP-B485D330UB2750-4F0-XX-W2A-A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.36	17.30	17.22	18.17	19.27	13.86	14.79	14.71	15.67	16.76
	3H	17.18	18.02	18.05	18.90	20.02	15.21	16.05	16.08	16.93	18.05
	4H	17.35	18.14	18.24	19.03	20.16	15.67	16.46	16.56	17.35	18.48
	6H	17.40	18.13	18.30	19.03	20.17	15.99	16.71	16.88	17.61	18.75
	8H	17.38	18.08	18.29	18.99	20.13	16.07	16.76	16.98	17.67	18.82
	12H	17.35	18.01	18.26	18.91	20.08	16.12	16.77	17.03	17.68	18.85
4H	2H	16.42	17.20	17.31	18.09	19.22	14.31	15.10	15.20	15.99	17.12
	3H	17.40	18.06	18.30	18.98	20.12	15.78	16.44	16.68	17.36	18.50
	4H	17.68	18.28	18.59	19.20	20.37	16.32	16.91	17.23	17.83	19.00
	6H	17.82	18.33	18.74	19.27	20.44	16.70	17.22	17.63	18.15	19.33
	8H	17.82	18.30	18.74	19.23	20.42	16.81	17.29	17.74	18.23	19.41
	12H	17.78	18.22	18.73	19.17	20.36	16.87	17.31	17.82	18.26	19.45
8H	4H	17.70	18.18	18.62	19.11	20.30	16.47	16.95	17.39	17.88	19.07
	6H	17.88	18.27	18.83	19.25	20.44	16.90	17.30	17.86	18.27	19.46
	8H	17.91	18.26	18.87	19.23	20.43	17.05	17.40	18.02	18.37	19.57
	12H	17.90	18.20	18.86	19.16	20.42	17.15	17.46	18.12	18.42	19.67
12H	4H	17.66	18.09	18.60	19.04	20.23	16.44	16.87	17.39	17.83	19.02
	6H	17.86	18.21	18.82	19.17	20.38	16.90	17.25	17.87	18.22	19.42
	8H	17.89	18.20	18.86	19.16	20.41	17.06	17.37	18.03	18.33	19.58