

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931115

Luminaire Tested: DFN2DS-SQ4F0-080DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-080DS940-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7064.6 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 79.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931115

CATALOG NUMBER: DFN2DS-SQ4F0-080DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931115

CATALOG NUMBER: DFN2DS-SQ4F0-080DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1948	1948	1948
5°	1956	1928	1939
10°	1944	1908	1918
15°	1920	1883	1881
20°	1886	1846	1844
25°	1852	1801	1801
30°	1809	1759	1744
35°	1768	1708	1683
40°	1717	1658	1626
45°	1667	1608	1569
50°	1612	1556	1501
55°	1555	1496	1440
60°	1491	1424	1371
65°	1423	1352	1290
70°	1337	1265	1205
75°	1216	1165	1136
80°	1080	1046	992
85°	881	840	753

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1667 cd/sqm

TEST NUMBER: P931115

CATALOG NUMBER: DFN2DS-SQ4F0-080DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	3.7
10°-20°	735.3	10.4
20°-30°	1080.6	15.3
30°-40°	1255.1	17.8
40°-50°	1253.5	17.7
50°-60°	1093.0	15.5
60°-70°	808.0	11.4
70°-80°	457.1	6.5
80°-90°	120.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2077.3	29.4
0°-40°	3332.3	47.2
0°-60°	5678.8	80.4
0°-90°	7064.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7064.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2777	2777	2777	2777	2777	
5°	2777	2766	2737	2758	2753	264
15°	2643	2627	2592	2603	2590	744
25°	2392	2371	2326	2331	2326	1101
35°	2064	2037	1994	1978	1965	1289
45°	1680	1661	1621	1591	1581	1296
55°	1271	1255	1223	1191	1178	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	129
90°	0	0	0	0	0	

TEST NUMBER: P931115

CATALOG NUMBER: DFN2DS-SQ4F0-080DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2776.6	2776.6	2776.6	2776.6	2776.6
2.5°	2792.8	2779.5	2750.0	2776.6	2771.5
5°	2776.6	2766.2	2736.7	2758.0	2752.9
7.5°	2758.0	2742.1	2712.7	2734.2	2728.8
10°	2728.8	2710.1	2678.1	2699.3	2691.4
12.5°	2688.6	2672.7	2640.7	2654.0	2648.6
15°	2643.3	2627.4	2592.5	2603.3	2590.0
17.5°	2587.2	2571.3	2536.4	2549.8	2536.4
20°	2525.7	2509.8	2472.4	2480.4	2469.9
22.5°	2464.5	2440.4	2405.5	2405.5	2400.2
25°	2392.3	2371.0	2325.7	2330.8	2325.7
27.5°	2312.1	2293.4	2258.8	2250.9	2237.6
30°	2232.2	2210.6	2170.8	2162.8	2152.0
32.5°	2146.7	2130.8	2088.0	2071.8	2061.1
35°	2063.9	2037.3	1994.5	1978.4	1965.1
37.5°	1970.4	1946.3	1903.6	1884.9	1871.6
40°	1874.4	1852.9	1810.1	1786.3	1775.5
42.5°	1781.0	1759.4	1716.9	1690.0	1674.2
45°	1679.5	1660.8	1620.6	1591.4	1580.7
47.5°	1580.7	1562.0	1519.2	1489.7	1473.9
50°	1476.4	1463.1	1425.7	1388.3	1375.0
52.5°	1375.0	1356.3	1321.8	1292.3	1273.6
55°	1271.0	1254.9	1222.9	1190.9	1177.5
57.5°	1166.8	1153.5	1118.7	1086.6	1075.8
60°	1062.6	1052.1	1014.6	985.2	977.3
62.5°	961.1	942.5	915.8	889.2	878.4
65°	857.2	841.1	814.4	790.3	777.0
67.5°	750.4	736.8	713.0	694.3	683.5
70°	651.5	640.7	616.7	598.0	587.5
72.5°	550.1	539.4	526.0	507.4	499.4
75°	448.4	443.3	429.8	413.9	419.2
77.5°	357.8	347.0	341.6	333.7	325.8
80°	267.2	264.3	258.9	251.0	245.6
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.4	106.8	104.3	96.1	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931115

CATALOG NUMBER: DFN2DS-SQ4F0-080DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.60	15.21	13.96	15.52	15.84	13.16	14.77	13.52	15.08	15.39
	3H	15.35	16.80	15.73	17.13	17.49	14.86	16.31	15.24	16.64	17.00
	4H	16.00	17.37	16.39	17.71	18.09	15.50	16.87	15.90	17.22	17.59
	6H	16.47	17.73	16.88	18.10	18.49	15.96	17.23	16.37	17.60	17.99
	8H	16.61	17.82	17.03	18.21	18.61	16.11	17.32	16.53	17.71	18.10
	12H	16.70	17.86	17.13	18.24	18.67	16.19	17.35	16.62	17.73	18.16
4H	2H	14.16	15.53	14.56	15.88	16.25	13.81	15.18	14.21	15.52	15.90
	3H	16.14	17.28	16.55	17.68	18.08	15.73	16.87	16.14	17.27	17.67
	4H	16.91	17.95	17.34	18.36	18.80	16.49	17.52	16.92	17.94	18.37
	6H	17.51	18.41	17.96	18.85	19.31	17.08	17.98	17.53	18.42	18.88
	8H	17.70	18.54	18.16	18.99	19.45	17.26	18.11	17.72	18.55	19.01
	12H	17.83	18.59	18.31	19.07	19.54	17.38	18.14	17.86	18.61	19.08
8H	4H	17.19	18.03	17.65	18.47	18.94	16.81	17.66	17.27	18.10	18.57
	6H	17.90	18.60	18.39	19.09	19.57	17.52	18.22	18.01	18.71	19.18
	8H	18.16	18.79	18.67	19.30	19.78	17.77	18.40	18.28	18.90	19.39
	12H	18.36	18.92	18.87	19.41	19.97	17.95	18.50	18.45	18.99	19.55
12H	4H	17.21	17.97	17.69	18.45	18.92	16.85	17.61	17.33	18.08	18.55
	6H	17.94	18.58	18.45	19.08	19.57	17.58	18.21	18.09	18.71	19.20
	8H	18.26	18.82	18.77	19.31	19.87	17.88	18.44	18.39	18.93	19.49