

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931152

Luminaire Tested: DFN2DS-SQ4F0-100DS940-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931152
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-100DS940-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7582.0 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 100.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931152

CATALOG NUMBER: DFN2DS-SQ4F0-100DS940-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931152

CATALOG NUMBER: DFN2DS-SQ4F0-100DS940-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2587	2587	2587
5°	2597	2554	2569
10°	2577	2513	2491
15°	2547	2438	2368
20°	2506	2332	2215
25°	2464	2211	2066
30°	2406	2087	1876
35°	2349	1952	1709
40°	2292	1812	1516
45°	2225	1655	1341
50°	2156	1497	1169
55°	2085	1326	1004
60°	2004	1147	834
65°	1911	964	759
70°	1800	794	698
75°	1664	724	651
80°	1469	647	594
85°	1154	510	510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2225 cd/sqm

TEST NUMBER: P931152

CATALOG NUMBER: DFN2DS-SQ4F0-100DS940-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.5	4.6
10°-20°	948.5	12.5
20°-30°	1331.7	17.6
30°-40°	1451.6	19.1
40°-50°	1334.2	17.6
50°-60°	1047.8	13.8
60°-70°	682.0	9.0
70°-80°	351.1	4.6
80°-90°	89.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2625.7	34.6
0°-40°	4077.3	53.8
0°-60°	6459.3	85.2
0°-90°	7582.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7582.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3687	3687	3687	3687	3687	
5°	3687	3670	3626	3657	3647	350
15°	3506	3470	3356	3293	3260	988
25°	3183	3076	2856	2719	2669	1464
35°	2742	2572	2279	2069	1995	1717
45°	2242	2018	1668	1431	1351	1731
55°	1705	1445	1084	884	821	1523
65°	1151	881	580	467	457	1141
75°	614	380	267	244	240	649
85°	143	73	63	63	63	172
90°	0	0	0	0	0	

TEST NUMBER: P931152

CATALOG NUMBER: DFN2DS-SQ4F0-100DS940-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3686.6	3686.6	3686.6	3686.6	3686.6
2.5°	3703.2	3686.6	3649.8	3683.4	3676.7
5°	3686.6	3670.0	3626.4	3656.6	3646.6
7.5°	3656.6	3636.7	3589.9	3603.1	3586.5
10°	3616.5	3593.2	3526.6	3516.4	3496.6
12.5°	3566.7	3536.5	3446.2	3426.4	3389.6
15°	3506.5	3469.6	3356.3	3293.0	3259.7
17.5°	3436.3	3382.9	3242.8	3169.5	3116.0
20°	3356.3	3289.4	3122.7	3039.6	2965.9
22.5°	3269.6	3192.8	2999.2	2886.0	2836.0
25°	3182.9	3076.1	2855.8	2719.2	2669.0
27.5°	3079.5	2965.9	2722.4	2565.6	2488.8
30°	2969.5	2842.4	2575.5	2405.6	2315.4
32.5°	2862.6	2708.9	2435.7	2235.4	2151.8
35°	2742.5	2572.3	2278.9	2068.6	1995.0
37.5°	2625.8	2442.0	2132.0	1901.6	1818.3
40°	2502.2	2302.3	1978.4	1741.5	1654.8
42.5°	2375.5	2162.0	1825.1	1578.0	1494.8
45°	2242.0	2018.3	1668.3	1431.1	1351.1
47.5°	2115.4	1878.6	1518.2	1281.0	1207.8
50°	1975.2	1738.3	1371.3	1140.9	1071.1
52.5°	1838.1	1587.9	1231.1	1010.9	947.6
55°	1704.7	1444.6	1084.2	884.2	820.8
57.5°	1568.1	1301.2	954.4	767.4	714.0
60°	1427.9	1161.0	817.3	647.4	594.0
62.5°	1291.3	1024.4	700.5	540.6	514.0
65°	1151.1	880.7	580.5	467.2	457.0
67.5°	1017.7	747.2	467.2	410.2	400.3
70°	877.5	617.4	386.9	353.6	340.2
72.5°	744.0	496.9	323.5	296.9	290.3
75°	613.8	380.2	266.9	243.5	240.3
77.5°	483.9	270.1	210.2	196.8	190.1
80°	363.5	193.7	160.0	146.9	146.9
82.5°	253.4	130.2	110.1	103.4	103.4
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931152

CATALOG NUMBER: DFN2DS-SQ4F0-100DS940-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.54	16.06	14.90	16.37	16.69	10.50	12.02	10.86	12.33	12.65
	3H	16.30	17.67	16.68	18.00	18.36	11.76	13.13	12.14	13.46	13.82
	4H	16.97	18.25	17.37	18.60	18.98	12.26	13.54	12.66	13.89	14.27
	6H	17.46	18.64	17.87	19.01	19.40	12.64	13.83	13.06	14.19	14.59
	8H	17.62	18.75	18.05	19.14	19.54	12.77	13.90	13.20	14.29	14.69
	12H	17.73	18.80	18.16	19.19	19.62	12.85	13.93	13.28	14.31	14.74
4H	2H	14.64	15.92	15.04	16.27	16.65	11.19	12.47	11.59	12.82	13.20
	3H	16.57	17.64	16.98	18.04	18.44	12.64	13.70	13.05	14.10	14.50
	4H	17.32	18.28	17.76	18.70	19.13	13.24	14.19	13.67	14.61	15.05
	6H	17.92	18.75	18.37	19.19	19.65	13.72	14.56	14.18	15.00	15.46
	8H	18.13	18.91	18.59	19.35	19.82	13.89	14.66	14.35	15.11	15.57
	12H	18.28	18.98	18.77	19.46	19.93	14.00	14.70	14.48	15.18	15.65
8H	4H	17.35	18.13	17.81	18.57	19.04	13.59	14.37	14.05	14.81	15.28
	6H	17.99	18.63	18.48	19.12	19.60	14.18	14.82	14.67	15.31	15.79
	8H	18.24	18.81	18.75	19.32	19.81	14.40	14.97	14.91	15.48	15.97
	12H	18.44	18.95	18.95	19.44	20.01	14.58	15.09	15.09	15.58	16.14
12H	4H	17.33	18.03	17.81	18.51	18.98	13.63	14.33	14.11	14.81	15.28
	6H	17.97	18.54	18.48	19.05	19.54	14.24	14.82	14.75	15.33	15.81
	8H	18.25	18.76	18.76	19.25	19.82	14.51	15.02	15.02	15.51	16.08

END OF REPORT