

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998690

Luminaire Tested: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998690
REPORT IS A COMBINATION OF REPORTS P984433 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7009.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998690

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P998690

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	93	89	84	81	84	80	76	73	64	61	59	49	47	46	35	34	33
2	84	77	70	65	76	69	64	59	55	51	48	42	40	37	30	29	27
3	77	67	60	54	69	61	54	49	48	44	40	37	34	31	27	24	23
4	70	59	51	45	63	53	46	41	43	38	34	33	29	26	24	21	19
5	64	52	44	38	57	47	40	35	38	33	29	29	25	22	21	19	16
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14
7	54	42	34	28	49	38	31	26	31	25	22	24	20	17	17	15	13
8	50	38	30	25	45	34	28	23	28	23	19	22	18	15	16	13	11
9	47	35	27	22	42	31	25	20	25	20	17	20	16	13	15	12	10
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11209	11209	11209
5°	11260	10732	10671
10°	11184	10360	10209
15°	11026	9975	9734
20°	10827	9570	9284
25°	10631	9185	8876
30°	10355	8791	8472
35°	10077	8412	8175
40°	9784	8086	7880
45°	9503	7789	7624
50°	9204	7516	7369
55°	8886	7225	7111
60°	8503	6921	6840
65°	8098	6573	6527
70°	7644	6199	6192
75°	7060	5826	5874
80°	6148	5436	5546
85°	5212	5071	5260

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9503 cd/sqm

TEST NUMBER: P998690

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.1	1.0
10°-20°	192.5	2.7
20°-30°	291.7	4.2
30°-40°	355.2	5.1
40°-50°	382.2	5.5
50°-60°	371.2	5.3
60°-70°	324.2	4.6
70°-80°	249.5	3.6
80°-90°	169.7	2.4
90°-100°	163.7	2.3
100°-110°	264.7	3.8
110°-120°	534.3	7.6
120°-130°	824.9	11.8
130°-140°	856.3	12.2
140°-150°	786.0	11.2
150°-160°	630.1	9.0
160°-170°	406.0	5.8
170°-180°	139.7	2.0
0°-30°	551.4	7.9
0°-40°	906.6	12.9
0°-60°	1660.0	23.7
0°-90°	2403.4	34.3
90°-120°	962.6	13.7
90°-150°	3429.7	48.9
90°-180°	4606.0	65.7
0°-180°	7009.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	708	708	708	708	708	
5°	710	707	701	707	706	67
15°	677	679	679	689	688	191
25°	616	623	632	644	648	283
35°	531	548	568	590	597	332
45°	435	463	499	531	541	336
55°	334	370	424	461	474	298
65°	228	278	339	381	394	226
75°	126	184	249	294	307	134
85°	37	101	166	209	224	39
90°	11	82	157	203	218	11
95°	77	90	159	204	215	88
105°	328	390	153	201	216	351
115°	615	644	717	256	191	605
125°	866	880	933	968	980	773
135°	1070	1087	1107	1139	1145	827
145°	1240	1239	1257	1270	1270	776
155°	1365	1356	1368	1375	1366	629
165°	1438	1432	1435	1443	1435	406
175°	1471	1464	1466	1474	1463	140
180°	1468	1468	1468	1468	1468	

TEST NUMBER: P998690

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	708.1	708.1	708.1	708.1	708.1
2.5°	713.3	710.2	703.0	708.1	706.1
5°	710.2	707.1	701.0	707.1	706.1
7.5°	705.1	703.0	697.9	705.1	704.0
10°	698.9	696.8	693.8	702.0	701.0
12.5°	688.6	689.7	687.6	695.8	694.8
15°	677.3	679.4	679.4	688.6	687.6
17.5°	663.0	667.1	670.2	679.4	679.4
20°	648.6	653.7	657.8	669.1	669.1
22.5°	633.2	639.4	645.5	656.8	658.9
25°	615.8	623.0	632.2	644.5	647.6
27.5°	595.2	606.5	616.8	632.2	634.2
30°	574.7	588.1	601.4	617.8	620.9
32.5°	552.1	567.5	584.0	603.5	609.6
35°	530.6	548.0	567.5	590.1	597.3
37.5°	507.0	526.5	551.1	575.7	582.9
40°	483.4	506.0	533.7	560.4	569.6
42.5°	460.8	483.4	516.2	546.0	555.2
45°	435.1	462.9	498.8	530.6	540.9
47.5°	410.5	440.3	481.3	514.2	525.5
50°	384.9	416.7	462.9	497.7	509.0
52.5°	360.2	394.1	443.4	479.3	491.6
55°	333.5	370.5	423.9	460.8	474.1
57.5°	307.9	348.9	402.3	442.3	455.7
60°	280.2	324.3	382.8	421.8	436.2
62.5°	255.5	301.7	360.2	402.3	415.6
65°	227.8	278.1	338.7	380.8	394.1
67.5°	203.2	255.5	317.1	359.2	373.6
70°	176.5	229.9	293.5	337.6	350.0
72.5°	151.9	207.3	272.0	315.1	330.5
75°	126.2	183.7	249.4	293.5	306.9
77.5°	101.6	161.1	227.8	272.0	286.3
80°	77.0	139.6	206.3	249.4	263.8
82.5°	56.4	118.0	185.8	228.9	242.2
85°	36.9	100.6	166.3	209.4	223.7
87.5°	22.6	84.2	149.8	191.9	205.3
90°	11.4	82.5	156.7	203.1	217.5
92.5°	35.8	85.9	151.7	193.9	207.3
95°	77.3	90.4	159.4	203.7	215.0
97.5°	131.5	88.5	165.0	206.2	219.5
100°	195.2	87.7	163.2	209.7	223.1
102.5°	264.4	296.0	158.1	206.8	221.3
105°	328.1	389.7	153.1	200.7	216.2
107.5°	403.5	454.8	148.0	194.6	210.2
110°	474.7	517.6	260.8	187.5	202.9

TEST NUMBER: P998690

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	542.7	578.3	607.4	182.4	196.9
115°	615.0	644.3	717.1	256.0	190.8
117.5°	676.7	706.1	767.3	646.2	378.0
120°	746.8	766.8	827.0	868.5	736.4
122.5°	806.3	824.3	883.5	917.6	927.9
125°	865.8	879.7	932.6	967.8	980.2
127.5°	921.1	934.9	978.5	1014.8	1025.1
130°	973.1	989.0	1022.3	1058.6	1065.8
132.5°	1026.3	1039.0	1066.1	1099.2	1106.4
135°	1069.8	1086.8	1106.6	1138.8	1144.9
137.5°	1116.5	1129.3	1145.1	1175.2	1179.1
140°	1162.2	1169.7	1183.5	1209.5	1210.3
142.5°	1200.5	1206.9	1220.7	1241.5	1241.3
145°	1239.8	1238.8	1256.8	1270.5	1270.3
147.5°	1274.9	1271.7	1289.8	1296.1	1294.9
150°	1308.9	1301.5	1318.5	1324.8	1319.5
152.5°	1337.6	1329.1	1345.0	1351.4	1344.0
155°	1365.2	1355.6	1368.4	1374.8	1366.3
157.5°	1387.5	1379.0	1388.6	1396.0	1387.5
160°	1406.6	1400.3	1406.6	1413.0	1405.6
162.5°	1423.6	1417.3	1422.6	1430.0	1420.4
165°	1438.5	1432.1	1435.3	1442.8	1435.3
167.5°	1450.2	1443.8	1447.0	1454.4	1444.9
170°	1459.8	1453.4	1455.5	1462.9	1453.4
172.5°	1466.1	1459.8	1461.9	1469.3	1459.8
175°	1471.4	1464.0	1466.1	1473.6	1462.9
177.5°	1473.6	1466.1	1467.2	1474.6	1465.1
180°	1468.3	1468.3	1468.3	1468.3	1468.3

TEST NUMBER: P998690

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-D_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.97	12.74	13.04	13.81	15.29	15.04	15.81	16.12	16.89	18.37
	3H	13.42	14.12	14.50	15.20	16.70	17.63	18.32	18.71	19.41	20.90
	4H	13.89	14.55	14.99	15.64	17.14	18.88	19.54	19.97	20.63	22.12
	6H	14.17	14.78	15.28	15.88	17.39	20.17	20.78	21.27	21.87	23.38
	8H	14.23	14.81	15.34	15.92	17.42	20.83	21.41	21.93	22.51	24.02
	12H	14.24	14.80	15.35	15.90	17.43	21.55	22.10	22.66	23.20	24.73
4H	2H	13.01	13.67	14.11	14.76	16.26	15.36	16.02	16.46	17.11	18.61
	3H	14.71	15.27	15.82	16.38	17.89	18.15	18.70	19.25	19.82	21.33
	4H	15.33	15.84	16.44	16.95	18.48	19.56	20.08	20.67	21.18	22.71
	6H	15.74	16.18	16.86	17.31	18.83	21.02	21.47	22.14	22.60	24.12
	8H	15.85	16.26	16.96	17.38	18.92	21.78	22.20	22.90	23.32	24.86
	12H	15.88	16.26	17.02	17.40	18.94	22.60	22.98	23.74	24.12	25.66
8H	4H	16.11	16.53	17.23	17.65	19.19	19.70	20.11	20.81	21.24	22.78
	6H	16.74	17.09	17.88	18.25	19.79	21.32	21.67	22.46	22.83	24.37
	8H	16.96	17.27	18.10	18.41	19.97	22.21	22.52	23.36	23.66	25.22
	12H	17.09	17.36	18.24	18.50	20.09	23.20	23.47	24.35	24.61	26.20
12H	4H	16.30	16.68	17.44	17.82	19.36	19.67	20.05	20.80	21.18	22.73
	6H	17.07	17.38	18.22	18.52	20.08	21.35	21.65	22.49	22.80	24.35
	8H	17.37	17.64	18.52	18.78	20.37	22.27	22.54	23.42	23.68	25.27