

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998694

Luminaire Tested: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P998694
REPORT IS A COMBINATION OF REPORTS P984437 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6962.0 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998694

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P998694

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	39
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16749	16749	16749
5°	16776	15964	15853
10°	16640	15238	14936
15°	16396	14504	13971
20°	16067	13707	13057
25°	15738	12875	12146
30°	15326	12092	11188
35°	14937	11266	10249
40°	14455	10451	9361
45°	13978	9644	8489
50°	13454	8821	7586
55°	12905	7942	6730
60°	12287	6990	5840
65°	11610	6022	4904
70°	10749	4963	3959
75°	9560	3826	3057
80°	8119	2601	1968
85°	5890	1211	837

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13978 cd/sqm

TEST NUMBER: P998694

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.4
10°-20°	280.2	4.0
20°-30°	411.8	5.9
30°-40°	478.3	6.9
40°-50°	477.7	6.9
50°-60°	416.5	6.0
60°-70°	307.9	4.4
70°-80°	174.2	2.5
80°-90°	48.5	0.7
90°-100°	48.0	0.7
100°-110°	178.9	2.6
110°-120°	474.6	6.8
120°-130°	787.1	11.3
130°-140°	836.1	12.0
140°-150°	777.0	11.2
150°-160°	624.7	9.0
160°-170°	402.5	5.8
170°-180°	138.5	2.0
0°-30°	791.6	11.4
0°-40°	1269.8	18.2
0°-60°	2164.0	31.1
0°-90°	2694.6	38.7
90°-120°	701.5	10.1
90°-150°	3101.6	44.6
90°-180°	4267.0	61.3
0°-180°	6962.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1058	1058	1058	1058	1058	
5°	1058	1054	1043	1051	1049	100
15°	1007	1001	988	992	987	284
25°	912	904	886	888	886	419
35°	786	776	760	754	749	491
45°	640	633	618	606	602	494
55°	484	478	466	454	449	433
65°	327	320	310	301	296	323
75°	171	169	164	158	160	182
85°	42	41	40	37	36	46
90°	1	13	21	26	28	6
95°	68	34	41	46	45	81
105°	320	352	64	76	80	342
115°	606	624	650	162	86	596
125°	856	870	890	897	901	764
135°	1060	1076	1086	1096	1094	819
145°	1229	1228	1246	1253	1248	769
155°	1354	1344	1357	1363	1354	624
165°	1426	1420	1423	1430	1423	403
175°	1459	1451	1454	1461	1450	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P998694

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1058.1	1058.1	1058.1	1058.1	1058.1
2.5°	1064.2	1059.1	1047.9	1058.1	1056.1
5°	1058.1	1054.0	1042.8	1051.0	1049.0
7.5°	1051.0	1044.9	1033.7	1041.8	1039.8
10°	1039.8	1032.7	1020.5	1028.6	1025.6
12.5°	1024.5	1018.4	1006.2	1011.3	1009.3
15°	1007.2	1001.1	987.9	992.0	986.9
17.5°	985.9	979.8	966.5	971.6	966.5
20°	962.5	956.4	942.1	945.2	941.1
22.5°	939.1	929.9	916.7	916.7	914.7
25°	911.6	903.5	886.2	888.2	886.2
27.5°	881.1	874.0	860.7	857.7	852.6
30°	850.6	842.4	827.2	824.1	820.0
32.5°	818.0	811.9	795.6	789.5	785.4
35°	786.5	776.3	760.0	753.9	748.8
37.5°	750.9	741.7	725.4	718.3	713.2
40°	714.2	706.1	689.8	680.6	676.6
42.5°	678.6	670.5	654.2	644.0	637.9
45°	640.0	632.8	617.6	606.4	602.3
47.5°	602.3	595.2	578.9	567.7	561.6
50°	562.6	557.5	543.3	529.1	524.0
52.5°	524.0	516.8	503.6	492.4	485.3
55°	484.3	478.2	466.0	453.8	448.7
57.5°	444.6	439.5	426.3	414.1	410.0
60°	404.9	400.9	386.6	375.4	372.4
62.5°	366.3	359.1	349.0	338.8	334.7
65°	326.6	320.5	310.3	301.2	296.1
67.5°	285.9	280.8	271.6	264.5	260.5
70°	248.2	244.2	235.0	227.9	223.8
72.5°	209.6	205.5	200.4	193.3	190.3
75°	170.9	168.9	163.8	157.7	159.7
77.5°	136.3	132.3	130.2	127.2	124.1
80°	101.7	100.7	98.7	95.6	93.6
82.5°	69.2	69.2	68.2	64.1	64.1
85°	41.7	40.7	39.7	36.6	35.6
87.5°	18.3	16.3	14.2	11.2	10.2
90°	1.1	12.6	21.1	26.3	28.4
92.5°	26.3	22.1	25.3	27.4	28.4
95°	68.5	33.7	41.1	46.3	45.3
97.5°	123.2	36.9	53.7	56.9	57.9
100°	186.4	42.1	60.0	68.5	70.6
102.5°	255.9	253.8	62.1	73.7	76.9
105°	320.2	351.8	64.3	75.8	80.0
107.5°	395.0	421.3	66.4	77.9	82.2
110°	466.6	488.7	184.3	79.0	83.2

TEST NUMBER: P998694

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	534.0	553.0	535.1	81.1	84.3
115°	605.6	623.5	649.9	162.2	86.4
117.5°	667.8	688.9	706.8	556.1	280.2
120°	737.3	753.1	772.1	784.7	642.5
122.5°	796.3	813.1	834.2	840.5	841.6
125°	856.3	870.0	890.0	897.4	900.6
127.5°	911.1	925.8	941.6	952.2	953.2
130°	962.7	979.6	991.1	1002.7	1001.7
132.5°	1015.4	1029.1	1040.6	1050.1	1049.1
135°	1059.6	1076.5	1085.9	1096.5	1094.4
137.5°	1106.0	1118.6	1129.1	1139.7	1136.5
140°	1151.2	1159.7	1171.3	1180.7	1175.5
142.5°	1189.2	1196.5	1210.2	1218.7	1213.4
145°	1229.2	1228.1	1246.0	1253.4	1248.1
147.5°	1263.9	1260.8	1278.7	1284.0	1279.7
150°	1297.7	1290.3	1307.1	1313.5	1308.2
152.5°	1326.1	1317.7	1333.5	1339.8	1332.4
155°	1353.5	1344.0	1356.6	1363.0	1354.5
157.5°	1375.6	1367.2	1376.6	1384.0	1375.6
160°	1394.6	1388.2	1394.6	1400.9	1393.5
162.5°	1411.4	1405.1	1410.4	1417.7	1408.2
165°	1426.2	1419.8	1423.0	1430.4	1423.0
167.5°	1437.7	1431.4	1434.6	1442.0	1432.5
170°	1447.2	1440.9	1443.0	1450.4	1440.9
172.5°	1453.5	1447.2	1449.3	1456.7	1447.2
175°	1458.8	1451.4	1453.5	1460.9	1450.4
177.5°	1460.9	1453.5	1454.6	1462.0	1452.5
180°	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P998694

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.88	14.65	14.93	15.71	17.13	14.67	15.43	15.71	16.49	17.91
	3H	15.21	15.90	16.27	16.96	18.41	16.29	16.97	17.34	18.04	19.48
	4H	15.62	16.27	16.68	17.33	18.78	16.87	17.53	17.94	18.59	20.04
	6H	15.83	16.43	16.91	17.50	18.96	17.27	17.87	18.35	18.94	20.40
	8H	15.86	16.43	16.94	17.51	18.97	17.38	17.95	18.46	19.03	20.49
	12H	15.85	16.39	16.93	17.47	18.95	17.42	17.96	18.51	19.04	20.52
4H	2H	14.34	14.99	15.42	16.06	17.51	14.99	15.64	16.06	16.70	18.15
	3H	15.85	16.39	16.93	17.49	18.95	16.76	17.30	17.84	18.39	19.85
	4H	16.35	16.85	17.44	17.93	19.42	17.43	17.93	18.52	19.02	20.50
	6H	16.65	17.08	17.75	18.18	19.66	17.92	18.35	19.02	19.46	20.94
	8H	16.70	17.11	17.80	18.20	19.70	18.07	18.47	19.16	19.56	21.06
	12H	16.70	17.06	17.82	18.17	19.67	18.12	18.49	19.24	19.60	21.09
8H	4H	16.52	16.92	17.62	18.02	19.51	17.51	17.91	18.61	19.01	20.50
	6H	16.90	17.23	18.02	18.37	19.86	18.08	18.41	19.20	19.55	21.04
	8H	17.00	17.29	18.13	18.41	19.92	18.27	18.56	19.39	19.68	21.19
	12H	17.03	17.28	18.16	18.40	19.95	18.36	18.61	19.49	19.73	21.28
12H	4H	16.50	16.86	17.61	17.97	19.47	17.47	17.83	18.59	18.94	20.44
	6H	16.92	17.21	18.04	18.33	19.84	18.07	18.36	19.19	19.48	20.99
	8H	17.03	17.28	18.16	18.40	19.94	18.26	18.51	19.39	19.63	21.18