

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998698

Luminaire Tested: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998698
REPORT IS A COMBINATION OF REPORTS P984441 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6752.0 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998698

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P998698

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	39
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16246	16246	16246
5°	16272	15485	15375
10°	16139	14779	14486
15°	15903	14068	13550
20°	15583	13295	12665
25°	15265	12487	11780
30°	14865	11728	10853
35°	14487	10926	9941
40°	14020	10138	9078
45°	13556	9353	8234
50°	13050	8556	7357
55°	12516	7703	6527
60°	11916	6780	5664
65°	11262	5842	4757
70°	10428	4815	3841
75°	9275	3712	2965
80°	7880	2522	1909
85°	5721	1174	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13556 cd/sqm

TEST NUMBER: P998698

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	1.4
10°-20°	271.8	4.0
20°-30°	399.4	5.9
30°-40°	463.9	6.9
40°-50°	463.3	6.9
50°-60°	404.0	6.0
60°-70°	298.6	4.4
70°-80°	169.0	2.5
80°-90°	47.1	0.7
90°-100°	46.6	0.7
100°-110°	173.5	2.6
110°-120°	460.2	6.8
120°-130°	763.3	11.3
130°-140°	810.8	12.0
140°-150°	753.6	11.2
150°-160°	605.8	9.0
160°-170°	390.4	5.8
170°-180°	134.4	2.0
0°-30°	767.7	11.4
0°-40°	1231.6	18.2
0°-60°	2098.9	31.1
0°-90°	2613.5	38.7
90°-120°	680.3	10.1
90°-150°	3007.9	44.5
90°-180°	4139.0	61.3
0°-180°	6752.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1026	1026	1026	1026	1026	
5°	1026	1022	1012	1019	1017	97
15°	977	971	958	962	957	275
25°	884	876	860	862	860	407
35°	763	753	737	731	726	476
45°	621	614	599	588	584	479
55°	470	464	452	440	435	420
65°	317	311	301	292	287	313
75°	166	164	159	153	155	177
85°	40	40	38	36	34	45
90°	1	12	20	26	28	6
95°	66	33	40	45	44	79
105°	310	341	62	74	78	332
115°	587	605	630	157	84	578
125°	830	844	863	870	873	741
135°	1028	1044	1053	1063	1061	794
145°	1192	1191	1208	1216	1210	746
155°	1313	1303	1316	1322	1314	605
165°	1383	1377	1380	1387	1380	391
175°	1415	1408	1410	1417	1407	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P998698

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1026.3	1026.3	1026.3	1026.3	1026.3
2.5°	1032.2	1027.3	1016.4	1026.3	1024.3
5°	1026.3	1022.3	1011.5	1019.4	1017.4
7.5°	1019.4	1013.4	1002.6	1010.5	1008.5
10°	1008.5	1001.6	989.8	997.7	994.7
12.5°	993.7	987.8	975.9	980.9	978.9
15°	976.9	971.0	958.2	962.1	957.2
17.5°	956.2	950.3	937.5	942.4	937.5
20°	933.5	927.6	913.8	916.7	912.8
22.5°	910.8	901.9	889.1	889.1	887.1
25°	884.2	876.3	859.5	861.5	859.5
27.5°	854.6	847.7	834.8	831.9	826.9
30°	825.0	817.1	802.3	799.3	795.4
32.5°	793.4	787.5	771.7	765.8	761.8
35°	762.8	752.9	737.1	731.2	726.3
37.5°	728.3	719.4	703.6	696.7	691.7
40°	692.7	684.8	669.1	660.2	656.2
42.5°	658.2	650.3	634.5	624.6	618.7
45°	620.7	613.8	599.0	588.1	584.2
47.5°	584.2	577.3	561.5	550.6	544.7
50°	545.7	540.8	527.0	513.1	508.2
52.5°	508.2	501.3	488.5	477.6	470.7
55°	469.7	463.8	452.0	440.1	435.2
57.5°	431.2	426.3	413.5	401.6	397.7
60°	392.7	388.8	375.0	364.1	361.2
62.5°	355.2	348.3	338.5	328.6	324.7
65°	316.8	310.8	301.0	292.1	287.2
67.5°	277.3	272.4	263.5	256.6	252.6
70°	240.8	236.8	228.0	221.0	217.1
72.5°	203.3	199.3	194.4	187.5	184.5
75°	165.8	163.8	158.9	153.0	154.9
77.5°	132.2	128.3	126.3	123.3	120.4
80°	98.7	97.7	95.7	92.8	90.8
82.5°	67.1	67.1	66.1	62.2	62.2
85°	40.5	39.5	38.5	35.5	34.5
87.5°	17.8	15.8	13.8	10.9	9.9
90°	1.0	12.3	20.4	25.5	27.6
92.5°	25.5	21.5	24.5	26.6	27.6
95°	66.4	32.7	39.8	44.9	43.9
97.5°	119.5	35.8	52.1	55.2	56.2
100°	180.8	40.9	58.2	66.4	68.4
102.5°	248.2	246.2	60.3	71.5	74.6
105°	310.5	341.2	62.3	73.5	77.6
107.5°	383.1	408.6	64.4	75.6	79.7
110°	452.5	474.0	178.8	76.6	80.7

TEST NUMBER: P998698

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	517.9	536.3	518.9	78.7	81.7
115°	587.3	604.7	630.2	157.3	83.8
117.5°	647.6	668.0	685.4	539.3	271.7
120°	715.0	730.3	748.7	761.0	623.1
122.5°	772.2	788.6	809.0	815.1	816.2
125°	830.5	843.7	863.1	870.3	873.4
127.5°	883.6	897.9	913.2	923.4	924.4
130°	933.6	950.0	961.2	972.4	971.4
132.5°	984.7	998.0	1009.2	1018.4	1017.4
135°	1027.6	1043.9	1053.1	1063.3	1061.3
137.5°	1072.5	1084.8	1095.0	1105.2	1102.2
140°	1116.5	1124.6	1135.9	1145.1	1140.0
142.5°	1153.2	1160.4	1173.7	1181.8	1176.7
145°	1192.1	1191.0	1208.4	1215.5	1210.4
147.5°	1225.8	1222.7	1240.1	1245.2	1241.1
150°	1258.4	1251.3	1267.6	1273.8	1268.7
152.5°	1286.0	1277.9	1293.2	1299.3	1292.2
155°	1312.6	1303.4	1315.7	1321.8	1313.6
157.5°	1334.0	1325.9	1335.1	1342.2	1334.0
160°	1352.4	1346.3	1352.4	1358.6	1351.4
162.5°	1368.8	1362.6	1367.7	1374.9	1365.7
165°	1383.1	1376.9	1380.0	1387.2	1380.0
167.5°	1394.3	1388.2	1391.2	1398.4	1389.2
170°	1403.5	1397.4	1399.4	1406.6	1397.4
172.5°	1409.6	1403.5	1405.5	1412.7	1403.5
175°	1414.7	1407.6	1409.6	1416.8	1406.6
177.5°	1416.8	1409.6	1410.6	1417.8	1408.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7

TEST NUMBER: P998698

CATALOG NUMBER: SA2XXDIP-B675D1080UB2750-4F0-XX-W2A-F_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.78	14.55	14.83	15.60	17.02	14.56	15.33	15.61	16.38	17.81
	3H	15.11	15.80	16.17	16.86	18.30	16.18	16.87	17.24	17.93	19.37
	4H	15.51	16.16	16.58	17.23	18.68	16.77	17.42	17.84	18.48	19.93
	6H	15.72	16.32	16.80	17.39	18.85	17.17	17.77	18.24	18.83	20.30
	8H	15.75	16.32	16.83	17.41	18.86	17.27	17.84	18.35	18.93	20.38
	12H	15.74	16.28	16.83	17.36	18.84	17.31	17.86	18.40	18.93	20.41
4H	2H	14.24	14.89	15.31	15.95	17.40	14.88	15.53	15.96	16.60	18.05
	3H	15.74	16.29	16.83	17.38	18.84	16.65	17.20	17.73	18.29	19.75
	4H	16.25	16.75	17.34	17.83	19.31	17.33	17.83	18.42	18.91	20.39
	6H	16.54	16.97	17.64	18.08	19.56	17.82	18.25	18.92	19.35	20.83
	8H	16.60	17.00	17.70	18.10	19.59	17.96	18.36	19.06	19.46	20.95
	12H	16.59	16.96	17.71	18.07	19.57	18.02	18.38	19.13	19.49	20.99
8H	4H	16.41	16.82	17.51	17.91	19.41	17.41	17.81	18.50	18.90	20.40
	6H	16.79	17.13	17.91	18.26	19.75	17.97	18.30	19.09	19.44	20.93
	8H	16.90	17.19	18.02	18.31	19.82	18.16	18.45	19.29	19.57	21.08
	12H	16.92	17.18	18.05	18.30	19.84	18.25	18.51	19.38	19.63	21.17
12H	4H	16.39	16.76	17.51	17.87	19.36	17.37	17.73	18.48	18.84	20.34
	6H	16.81	17.10	17.94	18.22	19.73	17.96	18.25	19.09	19.37	20.88
	8H	16.92	17.17	18.05	18.29	19.84	18.15	18.41	19.28	19.53	21.07