

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931389

Luminaire Tested: DFN2DS-TR3F0-070DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931389
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-070DS830-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6528.1 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 74.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931389

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931389

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3197	3197	3197
5°	3209	3163	3182
10°	3191	3131	3147
15°	3151	3090	3087
20°	3095	3030	3027
25°	3039	2955	2955
30°	2968	2886	2861
35°	2901	2804	2762
40°	2818	2721	2669
45°	2735	2639	2574
50°	2645	2554	2463
55°	2552	2455	2364
60°	2447	2337	2251
65°	2336	2219	2117
70°	2193	2076	1978
75°	1995	1912	1865
80°	1771	1717	1628
85°	1445	1378	1235

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2735 cd/sqm

TEST NUMBER: P931389

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.5	3.7
10°-20°	679.5	10.4
20°-30°	998.5	15.3
30°-40°	1159.7	17.8
40°-50°	1158.3	17.7
50°-60°	1010.0	15.5
60°-70°	746.6	11.4
70°-80°	422.4	6.5
80°-90°	111.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1919.5	29.4
0°-40°	3079.2	47.2
0°-60°	5247.5	80.4
0°-90°	6528.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6528.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2566	2566	2566	2566	2566	
5°	2566	2556	2529	2548	2544	244
15°	2442	2428	2396	2406	2393	688
25°	2211	2191	2149	2154	2149	1017
35°	1907	1883	1843	1828	1816	1191
45°	1552	1535	1498	1471	1461	1198
55°	1174	1160	1130	1100	1088	1050
65°	792	777	753	730	718	783
75°	414	410	397	382	387	442
85°	101	99	96	89	86	119
90°	0	0	0	0	0	

TEST NUMBER: P931389

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2565.7	2565.7	2565.7	2565.7	2565.7
2.5°	2580.7	2568.4	2541.1	2565.7	2561.0
5°	2565.7	2556.1	2528.9	2548.5	2543.8
7.5°	2548.5	2533.8	2506.6	2526.5	2521.5
10°	2521.5	2504.2	2474.6	2494.3	2487.0
12.5°	2484.3	2469.7	2440.2	2452.4	2447.4
15°	2442.5	2427.8	2395.6	2405.6	2393.2
17.5°	2390.6	2376.0	2343.8	2356.1	2343.8
20°	2333.8	2319.2	2284.6	2292.0	2282.3
22.5°	2277.3	2255.1	2222.8	2222.8	2217.8
25°	2210.6	2190.9	2149.1	2153.8	2149.1
27.5°	2136.5	2119.2	2087.3	2079.9	2067.6
30°	2062.7	2042.7	2005.9	1998.5	1988.6
32.5°	1983.6	1969.0	1929.4	1914.5	1904.5
35°	1907.2	1882.6	1843.0	1828.1	1815.8
37.5°	1820.8	1798.6	1759.0	1741.8	1729.4
40°	1732.1	1712.2	1672.6	1650.7	1640.7
42.5°	1645.7	1625.8	1586.5	1561.6	1547.0
45°	1551.9	1534.7	1497.5	1470.6	1460.6
47.5°	1460.6	1443.3	1403.8	1376.5	1361.9
50°	1364.3	1352.0	1317.4	1282.9	1270.6
52.5°	1270.6	1253.3	1221.4	1194.2	1176.8
55°	1174.5	1159.6	1130.0	1100.4	1088.1
57.5°	1078.2	1065.9	1033.7	1004.1	994.2
60°	981.8	972.1	937.7	910.4	903.1
62.5°	888.1	870.9	846.3	821.7	811.7
65°	792.1	777.2	752.6	730.3	718.0
67.5°	693.4	680.9	658.8	641.6	631.6
70°	602.0	592.1	569.8	552.6	542.9
72.5°	508.3	498.4	486.1	468.8	461.5
75°	414.4	409.7	397.1	382.5	387.4
77.5°	330.6	320.7	315.7	308.3	301.1
80°	246.8	244.3	239.3	231.9	226.9
82.5°	167.8	167.8	165.4	155.5	155.5
85°	101.1	98.7	96.4	88.7	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931389

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.32	16.93	15.69	17.25	17.56	14.88	16.49	15.24	16.80	17.12
	3H	17.07	18.53	17.45	18.85	19.21	16.58	18.03	16.96	18.36	18.72
	4H	17.72	19.09	18.12	19.43	19.81	17.22	18.59	17.62	18.94	19.32
	6H	18.19	19.45	18.60	19.82	20.21	17.69	18.95	18.10	19.32	19.71
	8H	18.33	19.54	18.75	19.93	20.33	17.83	19.04	18.25	19.43	19.83
	12H	18.42	19.58	18.85	19.96	20.39	17.91	19.07	18.34	19.45	19.88
4H	2H	15.88	17.25	16.28	17.60	17.97	15.53	16.90	15.93	17.25	17.62
	3H	17.86	19.00	18.27	19.40	19.80	17.45	18.60	17.86	18.99	19.39
	4H	18.63	19.67	19.06	20.08	20.52	18.21	19.25	18.64	19.66	20.09
	6H	19.23	20.13	19.68	20.58	21.03	18.80	19.70	19.25	20.14	20.60
	8H	19.42	20.27	19.88	20.71	21.17	18.98	19.83	19.44	20.27	20.74
	12H	19.55	20.31	20.03	20.79	21.26	19.10	19.86	19.58	20.33	20.80
8H	4H	18.91	19.75	19.37	20.20	20.66	18.53	19.38	18.99	19.82	20.29
	6H	19.62	20.32	20.11	20.81	21.29	19.24	19.94	19.73	20.43	20.91
	8H	19.88	20.51	20.39	21.02	21.50	19.49	20.12	20.00	20.63	21.11
	12H	20.08	20.64	20.59	21.13	21.69	19.67	20.22	20.17	20.71	21.28
12H	4H	18.93	19.69	19.41	20.17	20.64	18.57	19.33	19.05	19.80	20.27
	6H	19.67	20.30	20.18	20.80	21.29	19.30	19.93	19.81	20.44	20.92
	8H	19.98	20.54	20.49	21.03	21.59	19.60	20.16	20.11	20.65	21.21