

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931390

Luminaire Tested: DFN2DS-TR3F0-070DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-070DS830-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5604.9 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 74.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931390

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931390

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3396	3396	3396
5°	3409	3353	3372
10°	3383	3299	3271
15°	3344	3201	3109
20°	3290	3061	2907
25°	3235	2903	2713
30°	3158	2739	2463
35°	3084	2563	2243
40°	3009	2379	1990
45°	2921	2173	1760
50°	2831	1965	1535
55°	2738	1741	1318
60°	2631	1506	1094
65°	2509	1266	996
70°	2363	1042	916
75°	2185	950	856
80°	1929	849	779
85°	1516	669	669

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2921 cd/sqm

TEST NUMBER: P931390

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.4	4.6
10°-20°	701.2	12.5
20°-30°	984.4	17.6
30°-40°	1073.1	19.1
40°-50°	986.3	17.6
50°-60°	774.6	13.8
60°-70°	504.2	9.0
70°-80°	259.5	4.6
80°-90°	66.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1941.0	34.6
0°-40°	3014.1	53.8
0°-60°	4775.0	85.2
0°-90°	5604.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5604.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2725	2725	2725	2725	2725	
5°	2725	2713	2681	2703	2696	258
15°	2592	2565	2481	2434	2410	730
25°	2353	2274	2111	2010	1973	1082
35°	2027	1902	1685	1529	1475	1269
45°	1657	1492	1233	1058	999	1280
55°	1260	1068	802	654	607	1126
65°	851	651	429	345	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	127
90°	0	0	0	0	0	

TEST NUMBER: P931390

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2725.3	2725.3	2725.3	2725.3	2725.3
2.5°	2737.5	2725.3	2698.1	2722.9	2718.0
5°	2725.3	2713.0	2680.8	2703.1	2695.7
7.5°	2703.1	2688.4	2653.9	2663.5	2651.3
10°	2673.5	2656.3	2607.0	2599.4	2584.8
12.5°	2636.6	2614.3	2547.6	2532.9	2505.7
15°	2592.1	2564.9	2481.1	2434.3	2409.7
17.5°	2540.3	2500.8	2397.2	2342.9	2303.5
20°	2481.1	2431.7	2308.5	2247.0	2192.5
22.5°	2417.1	2360.3	2217.1	2133.3	2096.5
25°	2352.9	2273.9	2111.1	2010.1	1973.0
27.5°	2276.5	2192.5	2012.5	1896.6	1839.8
30°	2195.1	2101.2	1903.9	1778.3	1711.6
32.5°	2116.1	2002.6	1800.5	1652.5	1590.7
35°	2027.4	1901.5	1684.7	1529.2	1474.8
37.5°	1941.1	1805.2	1576.1	1405.7	1344.2
40°	1849.7	1701.9	1462.5	1287.4	1223.3
42.5°	1756.1	1598.3	1349.1	1166.5	1105.1
45°	1657.4	1492.0	1233.3	1058.0	998.8
47.5°	1563.7	1388.7	1122.3	947.0	892.8
50°	1460.1	1285.1	1013.7	843.4	791.8
52.5°	1358.8	1173.8	910.1	747.3	700.5
55°	1260.2	1067.9	801.5	653.7	606.8
57.5°	1159.2	961.9	705.5	567.3	527.8
60°	1055.6	858.3	604.2	478.6	439.1
62.5°	954.5	757.3	517.8	399.6	379.9
65°	850.9	651.0	429.2	345.4	337.8
67.5°	752.3	552.4	345.4	303.2	296.0
70°	648.7	456.3	286.0	261.4	251.4
72.5°	550.0	367.4	239.2	219.6	214.6
75°	453.8	281.0	197.3	180.0	177.7
77.5°	357.7	199.6	155.4	145.4	140.5
80°	268.8	143.1	118.3	108.6	108.6
82.5°	187.4	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931390

CATALOG NUMBER: DFN2DS-TR3F0-070DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.48	17.00	15.85	17.32	17.63	11.44	12.96	11.81	13.28	13.59
	3H	17.25	18.61	17.63	18.94	19.30	12.71	14.07	13.09	14.40	14.76
	4H	17.91	19.19	18.31	19.54	19.92	13.21	14.49	13.61	14.84	15.22
	6H	18.40	19.59	18.82	19.95	20.34	13.59	14.77	14.00	15.14	15.53
	8H	18.57	19.69	18.99	20.08	20.49	13.72	14.84	14.14	15.23	15.63
	12H	18.67	19.75	19.10	20.13	20.56	13.80	14.87	14.23	15.26	15.69
4H	2H	15.59	16.87	15.99	17.22	17.59	12.14	13.42	12.54	13.77	14.15
	3H	17.52	18.58	17.93	18.98	19.38	13.58	14.64	13.99	15.04	15.45
	4H	18.27	19.23	18.70	19.64	20.08	14.18	15.14	14.61	15.55	15.99
	6H	18.86	19.69	19.32	20.14	20.60	14.67	15.50	15.13	15.94	16.40
	8H	19.08	19.85	19.54	20.30	20.76	14.83	15.61	15.29	16.05	16.52
	12H	19.23	19.92	19.71	20.40	20.87	14.95	15.64	15.43	16.12	16.59
8H	4H	18.29	19.07	18.76	19.51	19.98	14.53	15.31	15.00	15.76	16.22
	6H	18.93	19.57	19.43	20.06	20.54	15.12	15.76	15.62	16.25	16.73
	8H	19.18	19.76	19.70	20.27	20.76	15.34	15.92	15.86	16.43	16.92
	12H	19.39	19.90	19.90	20.39	20.95	15.52	16.03	16.03	16.52	17.09
12H	4H	18.28	18.97	18.76	19.45	19.92	14.58	15.27	15.06	15.75	16.22
	6H	18.91	19.49	19.43	20.00	20.49	15.18	15.76	15.70	16.27	16.76
	8H	19.20	19.71	19.71	20.20	20.76	15.46	15.97	15.97	16.46	17.02