

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931321

Luminaire Tested: DFN2DS-TR3F0-030DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931321
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-030DS840-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2973.0 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 28.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931321

CATALOG NUMBER: DFN2DS-TR3F0-030DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931321

CATALOG NUMBER: DFN2DS-TR3F0-030DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1456	1456	1456
5°	1462	1441	1449
10°	1453	1426	1433
15°	1435	1407	1406
20°	1409	1380	1378
25°	1384	1346	1346
30°	1352	1314	1303
35°	1321	1277	1258
40°	1283	1239	1215
45°	1246	1202	1172
50°	1204	1163	1122
55°	1162	1118	1077
60°	1114	1064	1025
65°	1064	1010	964
70°	999	946	901
75°	909	871	850
80°	807	781	742
85°	658	626	562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1246 cd/sqm

TEST NUMBER: P931321

CATALOG NUMBER: DFN2DS-TR3F0-030DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.0	3.7
10°-20°	309.4	10.4
20°-30°	454.7	15.3
30°-40°	528.2	17.8
40°-50°	527.5	17.7
50°-60°	460.0	15.5
60°-70°	340.0	11.4
70°-80°	192.4	6.5
80°-90°	50.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	874.2	29.4
0°-40°	1402.3	47.2
0°-60°	2389.8	80.4
0°-90°	2973.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2973.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1168	1168	1168	1168	1168	
5°	1168	1164	1152	1161	1158	111
15°	1112	1106	1091	1096	1090	313
25°	1007	998	979	981	979	463
35°	869	857	839	832	827	542
45°	707	699	682	670	665	545
55°	535	528	515	501	496	478
65°	361	354	343	333	327	357
75°	189	187	181	174	176	201
85°	46	45	44	40	39	54
90°	0	0	0	0	0	

TEST NUMBER: P931321

CATALOG NUMBER: DFN2DS-TR3F0-030DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.5	1168.5	1168.5	1168.5	1168.5
2.5°	1175.3	1169.7	1157.3	1168.5	1166.4
5°	1168.5	1164.1	1151.7	1160.7	1158.5
7.5°	1160.7	1154.0	1141.5	1150.6	1148.3
10°	1148.3	1140.4	1127.0	1135.9	1132.6
12.5°	1131.4	1124.7	1111.3	1116.8	1114.6
15°	1112.3	1105.7	1091.0	1095.5	1089.9
17.5°	1088.7	1082.1	1067.4	1073.0	1067.4
20°	1062.9	1056.2	1040.4	1043.7	1039.3
22.5°	1037.1	1027.0	1012.3	1012.3	1010.0
25°	1006.7	997.8	978.7	980.9	978.7
27.5°	973.0	965.1	950.5	947.2	941.6
30°	939.3	930.3	913.5	910.1	905.6
32.5°	903.4	896.7	878.7	871.9	867.4
35°	868.6	857.4	839.3	832.5	826.9
37.5°	829.2	819.1	801.1	793.2	787.6
40°	788.8	779.8	761.8	751.8	747.2
42.5°	749.4	740.4	722.5	711.2	704.5
45°	706.8	698.9	682.0	669.7	665.2
47.5°	665.2	657.4	639.3	626.9	620.2
50°	621.3	615.7	600.0	584.3	578.7
52.5°	578.7	570.8	556.3	543.8	535.9
55°	534.9	528.1	514.6	501.2	495.6
57.5°	491.0	485.4	470.8	457.3	452.8
60°	447.1	442.7	427.0	414.6	411.3
62.5°	404.5	396.6	385.4	374.2	369.7
65°	360.8	354.0	342.7	332.6	327.0
67.5°	315.8	310.1	300.0	292.2	287.7
70°	274.2	269.7	259.6	251.7	247.2
72.5°	231.5	226.9	221.3	213.5	210.2
75°	188.7	186.6	180.9	174.2	176.5
77.5°	150.6	146.0	143.7	140.4	137.1
80°	112.4	111.2	108.9	105.6	103.4
82.5°	76.4	76.4	75.4	70.8	70.8
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931321

CATALOG NUMBER: DFN2DS-TR3F0-030DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.59	14.20	12.95	14.51	14.83	12.14	13.75	12.51	14.07	14.38
	3H	14.34	15.79	14.72	16.12	16.48	13.85	15.30	14.22	15.63	15.99
	4H	14.98	16.35	15.38	16.70	17.08	14.49	15.86	14.89	16.21	16.58
	6H	15.45	16.72	15.86	17.09	17.48	14.95	16.22	15.36	16.59	16.98
	8H	15.60	16.81	16.02	17.20	17.60	15.09	16.31	15.52	16.69	17.09
	12H	15.69	16.85	16.12	17.23	17.66	15.18	16.34	15.60	16.72	17.15
4H	2H	13.15	14.52	13.55	14.87	15.24	12.80	14.16	13.19	14.51	14.89
	3H	15.12	16.27	15.53	16.67	17.07	14.72	15.86	15.13	16.26	16.66
	4H	15.90	16.94	16.33	17.35	17.79	15.48	16.51	15.91	16.93	17.36
	6H	16.50	17.40	16.95	17.84	18.30	16.06	16.97	16.52	17.41	17.87
	8H	16.69	17.53	17.15	17.97	18.44	16.25	17.09	16.71	17.54	18.00
	12H	16.82	17.58	17.30	18.05	18.52	16.37	17.13	16.85	17.60	18.07
8H	4H	16.17	17.02	16.63	17.46	17.93	15.80	16.65	16.26	17.09	17.55
	6H	16.89	17.59	17.38	18.08	18.55	16.51	17.21	17.00	17.70	18.17
	8H	17.15	17.78	17.66	18.28	18.77	16.76	17.39	17.27	17.89	18.38
	12H	17.35	17.90	17.85	18.39	18.96	16.93	17.49	17.44	17.98	18.54
12H	4H	16.20	16.96	16.68	17.44	17.90	15.84	16.60	16.32	17.07	17.54
	6H	16.93	17.56	17.44	18.07	18.56	16.56	17.20	17.07	17.70	18.19
	8H	17.25	17.80	17.75	18.30	18.86	16.87	17.43	17.38	17.92	18.48