

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931340

Luminaire Tested: DFN2DS-TR3F0-040DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-040DS840-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3403.4 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 39.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931340

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931340

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2062	2062	2062
5°	2070	2036	2048
10°	2054	2003	1986
15°	2031	1944	1888
20°	1998	1859	1765
25°	1964	1763	1647
30°	1918	1663	1495
35°	1873	1556	1362
40°	1827	1445	1208
45°	1774	1320	1069
50°	1719	1193	932
55°	1663	1057	801
60°	1597	914	665
65°	1524	768	605
70°	1435	633	556
75°	1326	577	519
80°	1171	515	474
85°	921	406	406

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1774 cd/sqm

TEST NUMBER: P931340

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.1	4.6
10°-20°	425.8	12.5
20°-30°	597.8	17.6
30°-40°	651.6	19.1
40°-50°	598.9	17.6
50°-60°	470.3	13.8
60°-70°	306.1	9.0
70°-80°	157.6	4.6
80°-90°	40.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.6	34.6
0°-40°	1830.2	53.8
0°-60°	2899.4	85.2
0°-90°	3403.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3403.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1655	1655	1655	1655	1655	
5°	1655	1647	1628	1641	1637	157
15°	1574	1558	1507	1478	1463	444
25°	1429	1381	1282	1221	1198	657
35°	1231	1155	1023	928	896	771
45°	1006	906	749	642	606	777
55°	765	648	487	397	368	684
65°	517	395	261	210	205	512
75°	276	171	120	109	108	291
85°	64	33	28	28	28	77
90°	0	0	0	0	0	

TEST NUMBER: P931340

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1654.9	1654.9	1654.9	1654.9	1654.9
2.5°	1662.4	1654.9	1638.3	1653.5	1650.3
5°	1654.9	1647.3	1627.8	1641.3	1636.9
7.5°	1641.3	1632.4	1611.5	1617.3	1609.9
10°	1623.4	1612.9	1583.0	1578.4	1569.6
12.5°	1601.0	1587.5	1546.9	1538.0	1521.5
15°	1574.0	1557.5	1506.6	1478.2	1463.3
17.5°	1542.5	1518.5	1455.6	1422.7	1398.7
20°	1506.6	1476.6	1401.7	1364.4	1331.3
22.5°	1467.7	1433.2	1346.2	1295.4	1273.1
25°	1428.7	1380.8	1281.9	1220.6	1198.0
27.5°	1382.4	1331.3	1222.0	1151.7	1117.1
30°	1332.9	1275.9	1156.1	1079.8	1039.3
32.5°	1285.0	1216.0	1093.3	1003.4	965.9
35°	1231.1	1154.7	1022.9	928.5	895.5
37.5°	1178.7	1096.2	957.0	853.6	816.2
40°	1123.2	1033.4	888.1	781.8	742.8
42.5°	1066.3	970.5	819.2	708.3	671.0
45°	1006.4	906.0	748.8	642.4	606.5
47.5°	949.5	843.2	681.5	575.1	542.1
50°	886.6	780.3	615.5	512.1	480.8
52.5°	825.1	712.8	552.7	453.8	425.3
55°	765.3	648.4	486.7	396.9	368.5
57.5°	703.9	584.1	428.3	344.4	320.5
60°	640.9	521.1	366.9	290.6	266.7
62.5°	579.7	459.9	314.4	242.6	230.7
65°	516.7	395.3	260.6	209.7	205.1
67.5°	456.9	335.4	209.7	184.2	179.7
70°	393.9	277.1	173.7	158.8	152.7
72.5°	334.0	223.1	145.2	133.3	130.3
75°	275.5	170.7	119.8	109.3	107.9
77.5°	217.2	121.2	94.4	88.4	85.3
80°	163.2	86.9	71.8	66.0	66.0
82.5°	113.8	58.5	49.4	46.3	46.3
85°	64.4	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931340

CATALOG NUMBER: DFN2DS-TR3F0-040DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.75	15.27	14.11	15.58	15.90	9.71	11.23	10.07	11.54	11.86
	3H	15.51	16.88	15.89	17.21	17.57	10.97	12.34	11.35	12.67	13.03
	4H	16.18	17.46	16.58	17.81	18.19	11.48	12.76	11.88	13.11	13.48
	6H	16.67	17.85	17.08	18.22	18.61	11.86	13.04	12.27	13.41	13.80
	8H	16.84	17.96	17.26	18.35	18.75	11.98	13.11	12.41	13.50	13.90
	12H	16.94	18.02	17.37	18.40	18.83	12.06	13.14	12.49	13.52	13.95
4H	2H	13.85	15.13	14.25	15.48	15.86	10.40	11.69	10.80	12.03	12.41
	3H	15.79	16.85	16.20	17.25	17.65	11.85	12.91	12.26	13.31	13.71
	4H	16.54	17.49	16.97	17.91	18.35	12.45	13.40	12.88	13.82	14.26
	6H	17.13	17.96	17.59	18.40	18.86	12.94	13.77	13.39	14.21	14.67
	8H	17.34	18.12	17.81	18.56	19.03	13.10	13.88	13.56	14.32	14.79
	12H	17.50	18.19	17.98	18.67	19.14	13.21	13.91	13.70	14.39	14.86
8H	4H	16.56	17.34	17.02	17.78	18.25	12.80	13.58	13.26	14.02	14.49
	6H	17.20	17.84	17.69	18.33	18.81	13.39	14.03	13.89	14.52	15.00
	8H	17.45	18.02	17.96	18.53	19.02	13.61	14.19	14.12	14.70	15.18
	12H	17.65	18.16	18.16	18.65	19.22	13.79	14.30	14.30	14.79	15.35
12H	4H	16.54	17.24	17.03	17.72	18.19	12.84	13.54	13.33	14.02	14.49
	6H	17.18	17.76	17.69	18.27	18.75	13.45	14.03	13.97	14.54	15.03
	8H	17.46	17.97	17.97	18.47	19.03	13.72	14.23	14.23	14.73	15.29