

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998862

Luminaire Tested: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998862
REPORT IS A COMBINATION OF REPORTS P984608 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5778.0 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21137	21137	21137	21137
5°	21187	22537	21268	17929
10°	20941	24603	21073	14781
15°	20433	25949	20718	12452
20°	20114	24365	20114	10822
25°	19473	20932	19562	9678
30°	18418	16454	18769	8766
35°	17484	11378	17776	8020
40°	16410	8590	16596	7427
45°	15085	7060	15332	6785
50°	13942	6196	13965	6211
55°	12636	5279	12716	5588
60°	11243	4410	11397	4877
65°	9996	3587	10178	4165
70°	8757	2815	8978	3359
75°	7351	2042	7636	2437
80°	5732	1295	6148	1446
85°	3772	651	4054	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21850 cd/sqm

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	2.2
10°-20°	370.2	6.4
20°-30°	537.2	9.3
30°-40°	566.3	9.8
40°-50°	501.2	8.7
50°-60°	400.2	6.9
60°-70°	271.8	4.7
70°-80°	139.1	2.4
80°-90°	34.6	0.6
90°-100°	31.8	0.6
100°-110°	118.7	2.1
110°-120°	314.7	5.4
120°-130°	522.0	9.0
130°-140°	554.5	9.6
140°-150°	515.4	8.9
150°-160°	414.3	7.2
160°-170°	267.0	4.6
170°-180°	91.9	1.6
0°-30°	1034.6	17.9
0°-40°	1600.9	27.7
0°-60°	2502.3	43.3
0°-90°	2947.7	51.0
90°-120°	465.3	8.1
90°-150°	2057.1	35.6
90°-180°	2830.0	49.0
0°-180°	5778.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1335	1335	1335	1335	1335	
5°	1336	1491	1341	1186	1336	127
15°	1255	1833	1273	880	1255	355
25°	1128	1527	1133	706	1128	516
35°	921	831	936	586	921	576
45°	691	501	702	481	691	536
55°	474	352	477	373	474	423
65°	281	217	286	252	281	280
75°	131	107	136	127	131	141
85°	27	28	29	20	27	31
90°	1	19	1	19	1	4
95°	45	30	45	30	45	54
105°	212	53	212	53	212	227
115°	402	57	402	57	402	395
125°	568	597	568	597	568	507
135°	703	726	703	726	703	543
145°	815	828	815	828	815	510
155°	898	898	898	898	898	414
165°	946	944	946	944	946	267
175°	968	962	968	962	968	92
180°	965	965	965	965	965	

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1342.4	1345.5	1350.7	1351.7	1361.9	1370.2	1379.4	1379.4	1382.5	1381.4	1373.2
5°	1336.3	1345.5	1358.9	1370.2	1388.6	1396.8	1409.2	1418.4	1426.6	1432.8	1431.7
7.5°	1326.0	1342.4	1361.9	1383.5	1408.1	1422.5	1440.0	1456.4	1467.7	1477.9	1485.1
10°	1308.6	1336.3	1363.0	1391.7	1423.5	1443.0	1463.6	1485.1	1502.6	1522.1	1540.5
12.5°	1285.0	1325.0	1357.8	1395.8	1434.8	1456.4	1489.2	1505.6	1539.5	1588.8	1602.1
15°	1255.2	1309.6	1340.4	1388.6	1440.0	1457.4	1502.6	1529.2	1599.0	1629.8	1666.8
17.5°	1227.5	1288.1	1329.1	1384.5	1434.8	1468.7	1512.8	1567.2	1625.7	1669.9	1710.9
20°	1204.9	1263.4	1312.7	1374.3	1437.9	1481.0	1527.2	1592.9	1656.5	1701.7	1733.5
22.5°	1153.6	1228.5	1286.0	1354.8	1431.7	1491.3	1535.4	1607.2	1676.0	1703.7	1731.4
25°	1127.9	1192.6	1259.3	1337.3	1427.6	1498.5	1536.4	1616.5	1677.0	1687.3	1693.5
27.5°	1080.7	1153.6	1231.6	1320.9	1426.6	1486.1	1534.4	1607.2	1655.5	1648.3	1629.8
30°	1022.2	1111.5	1197.7	1294.2	1412.2	1476.9	1522.1	1588.8	1613.4	1576.5	1543.6
32.5°	979.1	1063.3	1158.7	1270.6	1395.8	1457.4	1501.5	1553.9	1559.0	1492.3	1436.9
35°	920.6	1014.0	1121.8	1239.8	1368.1	1423.5	1464.6	1496.4	1471.8	1378.4	1312.7
37.5°	868.3	960.7	1075.6	1195.7	1330.1	1384.5	1417.4	1422.5	1361.9	1279.8	1183.4
40°	810.8	906.3	1026.3	1152.6	1288.1	1335.3	1355.8	1340.4	1253.2	1157.7	1045.8
42.5°	753.3	847.8	977.1	1106.4	1234.7	1274.7	1282.9	1240.8	1134.1	1022.2	892.9
45°	690.7	789.3	918.6	1048.9	1173.1	1195.7	1196.7	1136.2	1009.9	892.9	772.8
47.5°	639.4	730.8	859.0	989.4	1094.1	1109.5	1103.3	1033.5	896.0	764.6	659.9
50°	583.0	670.2	797.5	925.8	1015.0	1019.2	1003.8	904.2	769.8	649.7	566.5
52.5°	522.4	610.7	727.7	850.8	930.9	924.7	895.0	788.2	662.0	562.4	498.8
55°	474.2	552.2	662.0	782.1	838.5	821.1	788.2	679.4	579.9	495.7	440.3
57.5°	420.8	489.6	597.3	702.0	734.9	718.4	685.6	584.0	491.6	428.0	391.0
60°	370.5	433.1	527.5	614.8	640.4	623.0	585.0	493.7	427.0	373.6	345.9
62.5°	324.3	378.7	457.7	537.8	548.1	530.6	497.8	423.9	366.4	324.3	303.8
65°	281.2	332.5	396.2	456.7	466.0	447.5	413.6	360.2	312.0	285.3	265.8
67.5°	239.1	280.2	336.6	380.8	385.9	368.5	340.7	297.6	267.9	239.1	224.8
70°	202.2	233.0	277.1	313.0	315.1	298.7	284.3	245.3	222.7	202.2	190.9
72.5°	166.3	187.8	221.7	248.4	249.4	239.1	225.8	201.2	181.7	167.3	156.0
75°	131.4	149.8	170.4	194.0	193.0	184.7	174.5	159.1	142.7	133.4	128.3
77.5°	100.6	111.9	128.3	143.7	143.7	139.6	133.4	122.1	111.9	102.6	97.5
80°	71.8	79.0	92.4	97.5	99.6	98.5	93.4	85.2	81.1	73.9	71.8
82.5°	46.2	51.3	57.5	62.6	65.7	63.6	62.6	58.5	52.3	50.3	48.2
85°	26.7	28.7	31.8	34.9	35.9	34.9	36.9	33.9	30.8	30.8	29.8
87.5°	11.3	12.3	14.4	14.4	15.4	15.4	14.4	15.4	15.4	14.4	13.3
90°	0.7	2.4	4.1	5.8	7.5	8.4	9.0	10.3	11.5	12.8	14.0
92.5°	17.5	16.9	16.3	15.6	15.0	14.7	14.9	15.4	15.9	16.3	16.8
95°	45.4	40.3	35.2	30.1	25.0	22.4	22.9	24.0	25.1	26.1	27.2
97.5°	81.7	69.0	56.3	43.6	30.9	24.5	25.7	28.2	30.7	33.1	35.6
100°	123.6	102.3	81.1	59.8	38.5	27.9	29.2	31.9	34.5	37.2	39.8
102.5°	169.8	169.5	169.2	168.9	168.6	168.4	154.3	126.0	97.7	69.5	41.2
105°	212.4	217.0	221.7	226.3	231.0	233.3	212.1	169.7	127.4	85.0	42.6
107.5°	262.0	265.9	269.7	273.6	277.5	279.4	253.2	200.9	148.6	96.3	44.0
110°	309.5	312.7	316.0	319.2	322.5	324.1	301.7	256.8	212.0	167.1	122.3

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	354.2	357.0	359.8	362.6	365.4	366.8	365.5	362.8	360.2	357.5	354.9
115°	401.7	404.3	407.0	409.6	412.3	413.6	415.5	419.4	423.3	427.1	431.0
117.5°	442.9	446.0	449.1	452.2	455.3	456.9	458.2	460.8	463.5	466.1	468.7
120°	489.0	491.3	493.7	496.0	498.3	499.5	500.9	503.7	506.5	509.3	512.1
122.5°	528.1	530.6	533.1	535.6	538.1	539.3	540.9	544.0	547.1	550.2	553.3
125°	567.9	569.9	571.9	574.0	576.0	577.0	578.5	581.4	584.4	587.3	590.3
127.5°	604.3	606.5	608.6	610.8	612.9	614.0	615.2	617.5	619.8	622.2	624.5
130°	638.5	641.0	643.5	646.0	648.5	649.7	650.6	652.3	654.0	655.7	657.4
132.5°	673.4	675.4	677.4	679.5	681.5	682.5	683.4	685.1	686.8	688.5	690.2
135°	702.8	705.3	707.7	710.2	712.7	713.9	714.6	716.0	717.4	718.8	720.2
137.5°	733.5	735.4	737.2	739.1	741.0	741.9	742.7	744.2	745.8	747.3	748.9
140°	763.5	764.7	766.0	767.2	768.5	769.1	770.0	771.7	773.4	775.1	776.8
142.5°	788.7	789.8	790.9	792.0	793.1	793.6	794.6	796.6	798.7	800.7	802.7
145°	815.2	815.0	814.9	814.7	814.6	814.5	815.8	818.5	821.1	823.8	826.4
147.5°	838.3	837.8	837.4	836.9	836.4	836.2	837.5	840.2	842.8	845.5	848.1
150°	860.6	859.5	858.5	857.4	856.3	855.8	857.0	859.5	862.0	864.4	866.9
152.5°	879.5	878.3	877.0	875.8	874.5	873.9	875.1	877.4	879.7	882.1	884.4
155°	897.7	896.3	894.9	893.5	892.1	891.4	892.3	894.2	896.1	897.9	899.8
157.5°	912.3	911.1	909.8	908.6	907.3	906.7	907.4	908.8	910.2	911.6	913.0
160°	924.9	924.0	923.0	922.1	921.2	920.7	921.2	922.1	923.0	924.0	924.9
162.5°	936.1	935.2	934.2	933.3	932.4	931.9	932.3	933.1	933.8	934.6	935.4
165°	945.9	945.0	944.0	943.1	942.2	941.7	941.9	942.4	942.9	943.3	943.8
167.5°	953.6	952.7	951.7	950.8	949.9	949.4	949.6	950.1	950.6	951.0	951.5
170°	959.8	958.9	957.9	957.0	956.1	955.6	955.8	956.1	956.4	956.7	957.0
172.5°	964.0	963.1	962.1	961.2	960.3	959.8	960.0	960.3	960.6	960.9	961.2
175°	967.5	966.4	965.3	964.2	963.1	962.6	962.8	963.1	963.4	963.7	964.0
177.5°	968.9	967.8	966.7	965.6	964.5	964.0	964.1	964.2	964.4	964.5	964.7
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1387.6	1388.6	1390.7	1400.9	1406.1	1407.1	1403.0	1412.2	1415.3	1412.2	1410.2
5°	1453.3	1459.5	1471.8	1485.1	1484.1	1485.1	1491.3	1497.4	1499.5	1491.3	1494.3
7.5°	1510.8	1523.1	1536.4	1557.0	1557.0	1567.2	1571.3	1576.5	1588.8	1582.6	1580.6
10°	1576.5	1592.9	1617.5	1650.3	1651.4	1661.6	1671.9	1688.3	1693.5	1689.4	1691.4
12.5°	1658.6	1690.4	1692.4	1728.4	1744.8	1746.8	1763.2	1760.2	1770.4	1770.4	1787.9
15°	1694.5	1743.7	1771.5	1806.4	1816.6	1804.3	1817.6	1832.0	1833.0	1833.0	1832.0
17.5°	1759.1	1778.6	1806.4	1824.8	1828.9	1828.9	1830.0	1836.1	1832.0	1823.8	1830.0
20°	1772.5	1780.7	1791.0	1788.9	1791.0	1780.7	1770.4	1760.2	1761.2	1756.1	1771.5
22.5°	1747.9	1745.8	1722.2	1706.8	1706.8	1686.3	1666.8	1657.5	1648.3	1651.4	1656.5
25°	1686.3	1654.5	1625.7	1603.1	1598.0	1565.2	1538.5	1530.3	1514.9	1527.2	1529.2
27.5°	1587.7	1551.8	1505.6	1486.1	1459.5	1446.1	1427.6	1403.0	1371.2	1389.7	1386.6
30°	1482.0	1428.7	1390.7	1343.5	1301.4	1298.3	1263.4	1222.4	1205.9	1205.9	1215.2
32.5°	1364.0	1293.2	1237.8	1171.1	1130.0	1112.5	1070.5	1029.4	1038.7	1007.9	1019.2
35°	1226.5	1133.1	1063.3	998.6	967.8	947.3	892.9	870.3	845.7	831.3	858.0
37.5°	1095.1	987.3	898.0	827.2	815.9	779.0	742.0	727.7	713.3	719.5	718.4
40°	935.0	839.5	759.5	704.1	684.6	667.1	642.5	625.0	615.8	620.9	622.0
42.5°	790.3	710.2	650.7	611.7	595.3	583.0	570.6	556.3	553.2	553.2	557.3
45°	678.4	612.7	572.7	540.9	531.6	522.4	513.2	507.0	505.0	500.9	503.9
47.5°	589.1	536.8	512.1	488.5	478.3	476.2	468.0	464.9	460.8	459.8	460.8
50°	514.2	481.4	458.8	445.4	438.2	435.2	431.1	424.9	422.9	428.0	425.9
52.5°	461.9	431.1	418.7	405.4	401.3	397.2	391.0	392.1	391.0	389.0	389.0
55°	409.5	390.0	377.7	367.4	366.4	362.3	357.2	355.1	354.1	352.0	355.1
57.5°	367.4	352.0	340.7	331.5	327.4	327.4	322.3	318.2	318.2	317.1	318.2
60°	325.3	310.0	302.8	293.5	290.5	289.4	286.3	284.3	281.2	281.2	281.2
62.5°	286.3	274.0	265.8	257.6	258.6	253.5	249.4	247.3	247.3	248.4	248.4
65°	249.4	241.2	230.9	223.7	221.7	220.7	218.6	217.6	214.5	216.6	216.6
67.5°	215.5	204.2	198.1	195.0	191.9	190.9	188.8	186.8	185.8	184.7	186.8
70°	181.7	172.4	167.3	165.2	162.2	161.1	160.1	157.0	158.1	159.1	160.1
72.5°	150.9	142.7	141.6	135.5	135.5	135.5	131.4	133.4	132.4	130.3	132.4
75°	119.1	114.9	112.9	109.8	110.8	109.8	108.8	105.7	105.7	106.7	107.8
77.5°	94.4	90.3	89.3	86.2	84.2	86.2	84.2	83.1	83.1	84.2	84.2
80°	69.8	67.7	64.7	64.7	64.7	63.6	63.6	63.6	62.6	61.6	62.6
82.5°	46.2	46.2	45.2	44.1	45.2	43.1	44.1	44.1	44.1	44.1	44.1
85°	29.8	28.7	28.7	27.7	27.7	27.7	28.7	26.7	26.7	27.7	27.7
87.5°	13.3	13.3	13.3	14.4	13.3	13.3	13.3	14.4	13.3	13.3	13.3
90°	14.8	15.6	16.3	17.1	17.5	17.7	18.0	18.3	18.6	18.9	18.6
92.5°	17.1	17.4	17.7	18.0	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.0	28.8	29.5	30.3	30.7	30.6	30.5	30.3	30.2	30.0	30.2
97.5°	36.1	36.5	37.0	37.5	37.7	37.8	37.9	38.1	38.2	38.4	38.2
100°	41.0	42.3	43.5	44.8	45.4	45.6	45.9	46.2	46.5	46.8	46.5
102.5°	42.9	44.6	46.3	48.0	48.9	49.1	49.6	50.1	50.5	51.0	50.5
105°	44.3	46.0	47.7	49.4	50.3	50.6	51.2	51.9	52.5	53.1	52.5
107.5°	45.7	47.4	49.1	50.8	51.7	52.0	52.6	53.3	53.9	54.5	53.9
110°	106.8	91.2	75.7	60.2	52.4	52.7	53.3	54.0	54.6	55.2	54.6

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	288.0	221.1	154.2	87.3	53.8	54.0	54.5	55.0	55.4	55.9	55.4
115°	359.1	287.3	215.4	143.5	107.6	102.0	90.8	79.7	68.5	57.3	68.5
117.5°	446.5	424.3	402.1	379.9	368.8	348.5	307.8	267.1	226.5	185.8	226.5
120°	513.9	515.8	517.6	519.5	520.4	509.9	489.0	468.0	447.1	426.1	447.1
122.5°	554.2	555.2	556.1	557.0	557.5	557.6	557.7	557.9	558.0	558.2	558.0
125°	591.4	592.5	593.6	594.7	595.2	595.4	595.9	596.4	596.8	597.3	596.8
127.5°	626.1	627.6	629.2	630.7	631.5	631.6	631.7	631.9	632.0	632.2	632.0
130°	659.1	660.8	662.5	664.2	665.0	664.9	664.8	664.6	664.5	664.3	664.5
132.5°	691.6	693.0	694.4	695.8	696.5	696.4	696.3	696.1	696.0	695.8	696.0
135°	721.8	723.3	724.9	726.4	727.2	727.0	726.7	726.4	726.1	725.8	726.1
137.5°	750.5	752.0	753.6	755.1	755.9	755.7	755.2	754.7	754.3	753.8	754.3
140°	778.2	779.6	781.0	782.4	783.1	782.7	781.9	781.2	780.4	779.6	780.4
142.5°	803.9	805.2	806.4	807.7	808.3	807.9	807.1	806.4	805.6	804.8	805.6
145°	827.5	828.6	829.7	830.8	831.3	830.9	830.1	829.4	828.6	827.8	828.6
147.5°	848.9	849.7	850.4	851.2	851.6	851.3	850.7	850.0	849.4	848.8	849.4
150°	867.8	868.8	869.7	870.6	871.1	870.7	869.9	869.2	868.4	867.6	868.4
152.5°	885.3	886.3	887.2	888.1	888.6	888.1	887.0	885.9	884.8	883.7	884.8
155°	900.7	901.7	902.6	903.5	904.0	903.4	902.1	900.9	899.6	898.4	899.6
157.5°	914.1	915.2	916.3	917.4	917.9	917.3	916.0	914.8	913.5	912.3	913.5
160°	925.8	926.8	927.7	928.6	929.1	928.6	927.5	926.4	925.3	924.2	925.3
162.5°	936.5	937.6	938.7	939.8	940.3	939.6	938.2	936.8	935.4	934.0	935.4
165°	944.9	946.0	947.1	948.2	948.7	948.2	947.1	946.0	944.9	943.8	944.9
167.5°	952.6	953.6	954.7	955.8	956.3	955.6	954.2	952.9	951.5	950.1	951.5
170°	958.1	959.2	960.3	961.4	961.9	961.2	959.8	958.4	957.0	955.6	957.0
172.5°	962.3	963.4	964.5	965.6	966.1	965.4	964.0	962.6	961.2	959.8	961.2
175°	965.1	966.2	967.3	968.4	968.9	968.1	966.6	965.0	963.5	961.9	963.5
177.5°	965.8	966.9	968.0	969.1	969.6	968.9	967.5	966.1	964.7	963.3	964.7
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1415.3	1408.1	1402.0	1403.0	1408.1	1404.0	1393.8	1380.4	1375.3	1369.1	1375.3
5°	1500.5	1494.3	1482.0	1483.1	1480.0	1475.9	1459.5	1438.9	1438.9	1422.5	1420.5
7.5°	1584.7	1575.4	1567.2	1565.2	1553.9	1545.7	1531.3	1502.6	1491.3	1471.8	1460.5
10°	1679.1	1671.9	1662.7	1651.4	1645.2	1630.8	1607.2	1565.2	1544.6	1518.0	1498.5
12.5°	1774.5	1773.5	1753.0	1730.4	1729.4	1706.8	1690.4	1633.9	1606.2	1570.3	1524.1
15°	1835.1	1830.0	1818.7	1807.4	1810.5	1785.8	1748.9	1682.2	1663.7	1620.6	1571.3
17.5°	1834.1	1834.1	1831.0	1828.9	1825.9	1818.7	1798.1	1754.0	1724.2	1669.9	1623.7
20°	1775.6	1788.9	1792.0	1791.0	1801.2	1806.4	1805.3	1777.6	1754.0	1705.8	1658.6
22.5°	1658.6	1689.4	1702.7	1710.9	1732.5	1743.7	1770.4	1760.2	1754.0	1718.1	1678.1
25°	1549.8	1560.0	1600.1	1602.1	1631.9	1659.6	1686.3	1703.7	1726.3	1713.0	1679.1
27.5°	1409.2	1432.8	1461.5	1483.1	1489.2	1545.7	1589.8	1622.6	1674.0	1678.1	1666.8
30°	1250.1	1261.4	1308.6	1337.3	1370.2	1411.2	1474.8	1531.3	1577.5	1619.6	1633.9
32.5°	1056.1	1102.3	1130.0	1164.9	1193.6	1266.5	1344.5	1417.4	1470.7	1541.6	1572.3
35°	878.5	914.5	961.7	976.0	1028.4	1090.0	1191.6	1285.0	1366.1	1437.9	1500.5
37.5°	731.8	760.5	810.8	833.4	864.2	943.2	1028.4	1144.4	1241.9	1330.1	1408.1
40°	631.2	652.8	690.7	697.9	723.6	795.4	864.2	973.0	1102.3	1221.3	1306.5
42.5°	562.4	572.7	598.4	607.6	624.0	672.3	733.8	836.5	956.5	1079.7	1199.8
45°	513.2	520.4	535.7	544.0	564.5	586.0	636.3	718.4	812.9	937.0	1066.4
47.5°	469.0	478.3	484.4	489.6	500.9	524.5	557.3	617.9	708.2	822.1	947.3
50°	432.1	435.2	446.5	447.5	454.7	470.1	500.9	537.8	609.6	702.0	823.1
52.5°	395.1	398.2	405.4	412.6	415.7	428.0	448.5	479.3	532.7	605.5	713.3
55°	358.2	362.3	369.5	374.6	377.7	388.0	400.3	430.0	472.1	523.4	611.7
57.5°	321.2	330.5	332.5	335.6	340.7	352.0	363.3	380.8	413.6	460.8	525.5
60°	286.3	289.4	296.6	299.7	304.8	311.0	325.3	338.7	362.3	399.2	457.7
62.5°	250.4	257.6	260.7	263.8	267.9	275.1	284.3	298.7	319.2	349.0	395.1
65°	219.6	220.7	226.8	230.9	235.0	240.2	249.4	262.7	275.1	302.8	336.6
67.5°	189.9	191.9	194.0	198.1	203.2	208.3	216.6	223.7	239.1	257.6	284.3
70°	161.1	161.1	166.3	169.3	168.3	174.5	180.6	188.8	200.1	217.6	239.1
72.5°	135.5	134.5	138.6	139.6	141.6	145.7	149.8	158.1	164.2	177.6	194.0
75°	107.8	109.8	111.9	111.9	114.9	118.0	122.1	126.2	133.4	141.6	154.0
77.5°	85.2	85.2	87.2	88.3	91.3	90.3	94.4	98.5	103.7	110.8	120.1
80°	62.6	64.7	64.7	64.7	65.7	66.7	70.8	73.9	77.0	82.1	86.2
82.5°	44.1	44.1	46.2	46.2	46.2	48.2	48.2	49.3	51.3	54.4	57.5
85°	27.7	27.7	27.7	28.7	27.7	28.7	30.8	29.8	30.8	32.8	32.8
87.5°	13.3	13.3	13.3	13.3	13.3	14.4	13.3	14.4	15.4	15.4	15.4
90°	18.3	18.0	17.7	17.5	17.1	16.3	15.6	14.8	14.0	12.8	11.5
92.5°	18.6	18.4	18.3	18.2	18.0	17.7	17.4	17.1	16.8	16.3	15.9
95°	30.3	30.5	30.6	30.7	30.3	29.5	28.8	28.0	27.2	26.1	25.1
97.5°	38.1	37.9	37.8	37.7	37.5	37.0	36.5	36.1	35.6	33.1	30.7
100°	46.2	45.9	45.6	45.4	44.8	43.5	42.3	41.0	39.8	37.2	34.5
102.5°	50.1	49.6	49.1	48.9	48.0	46.3	44.6	42.9	41.2	39.5	37.7
105°	51.9	51.2	50.6	50.3	49.4	47.7	46.0	44.3	42.6	40.9	39.1
107.5°	53.3	52.6	52.0	51.7	50.8	49.1	47.4	45.7	44.0	42.3	40.6
110°	54.0	53.3	52.7	52.4	50.2	48.5	46.8	45.1	43.4	41.7	40.0

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.0	54.5	54.0	53.8	87.3	154.2	221.1	288.0	354.9	357.5	360.2
115°	79.7	90.8	102.0	107.6	143.5	215.4	287.3	359.1	431.0	427.1	423.3
117.5°	267.1	307.8	348.5	368.8	379.9	402.1	424.3	446.5	468.7	466.1	463.5
120°	468.0	489.0	509.9	520.4	519.5	517.6	515.8	513.9	512.1	509.3	506.5
122.5°	557.9	557.7	557.6	557.5	557.0	556.1	555.2	554.2	553.3	550.2	547.1
125°	596.4	595.9	595.4	595.2	594.7	593.6	592.5	591.4	590.3	587.3	584.4
127.5°	631.9	631.7	631.6	631.5	630.7	629.2	627.6	626.1	624.5	622.2	619.8
130°	664.6	664.8	664.9	665.0	664.2	662.5	660.8	659.1	657.4	655.7	654.0
132.5°	696.1	696.3	696.4	696.5	695.8	694.4	693.0	691.6	690.2	688.5	686.8
135°	726.4	726.7	727.0	727.2	726.4	724.9	723.3	721.8	720.2	718.8	717.4
137.5°	754.7	755.2	755.7	755.9	755.1	753.6	752.0	750.5	748.9	747.3	745.8
140°	781.2	781.9	782.7	783.1	782.4	781.0	779.6	778.2	776.8	775.1	773.4
142.5°	806.4	807.1	807.9	808.3	807.7	806.4	805.2	803.9	802.7	800.7	798.7
145°	829.4	830.1	830.9	831.3	830.8	829.7	828.6	827.5	826.4	823.8	821.1
147.5°	850.0	850.7	851.3	851.6	851.2	850.4	849.7	848.9	848.1	845.5	842.8
150°	869.2	869.9	870.7	871.1	870.6	869.7	868.8	867.8	866.9	864.4	862.0
152.5°	885.9	887.0	888.1	888.6	888.1	887.2	886.3	885.3	884.4	882.1	879.7
155°	900.9	902.1	903.4	904.0	903.5	902.6	901.7	900.7	899.8	897.9	896.1
157.5°	914.8	916.0	917.3	917.9	917.4	916.3	915.2	914.1	913.0	911.6	910.2
160°	926.4	927.5	928.6	929.1	928.6	927.7	926.8	925.8	924.9	924.0	923.0
162.5°	936.8	938.2	939.6	940.3	939.8	938.7	937.6	936.5	935.4	934.6	933.8
165°	946.0	947.1	948.2	948.7	948.2	947.1	946.0	944.9	943.8	943.3	942.9
167.5°	952.9	954.2	955.6	956.3	955.8	954.7	953.6	952.6	951.5	951.0	950.6
170°	958.4	959.8	961.2	961.9	961.4	960.3	959.2	958.1	957.0	956.7	956.4
172.5°	962.6	964.0	965.4	966.1	965.6	964.5	963.4	962.3	961.2	960.9	960.6
175°	965.0	966.6	968.1	968.9	968.4	967.3	966.2	965.1	964.0	963.7	963.4
177.5°	966.1	967.5	968.9	969.6	969.1	968.0	966.9	965.8	964.7	964.5	964.4
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1370.2	1365.0	1361.9	1364.0	1357.8	1342.4	1342.4	1347.6	1341.4	1335.3	1326.0
5°	1408.1	1397.9	1391.7	1390.7	1376.3	1351.7	1346.6	1341.4	1328.1	1313.7	1298.3
7.5°	1445.1	1426.6	1416.3	1409.2	1388.6	1356.8	1343.5	1332.2	1310.6	1289.1	1269.6
10°	1475.9	1449.2	1436.9	1425.6	1398.9	1358.9	1337.3	1316.8	1289.1	1261.4	1236.7
12.5°	1500.5	1469.7	1454.3	1437.9	1405.1	1352.7	1326.0	1293.2	1265.5	1228.5	1203.9
15°	1541.6	1477.9	1463.6	1448.2	1414.3	1342.4	1309.6	1272.7	1234.7	1185.4	1158.7
17.5°	1574.4	1489.2	1488.2	1455.3	1411.2	1338.3	1288.1	1239.8	1198.8	1149.5	1107.4
20°	1593.9	1506.7	1490.2	1456.4	1400.9	1310.6	1258.3	1204.9	1160.8	1101.3	1059.2
22.5°	1610.3	1531.3	1488.2	1447.1	1379.4	1301.4	1224.4	1174.1	1113.6	1048.9	1008.9
25°	1616.5	1536.4	1491.3	1444.1	1364.0	1274.7	1187.5	1133.1	1065.3	1006.8	952.4
27.5°	1617.5	1535.4	1480.0	1430.7	1342.4	1239.8	1150.5	1093.0	1018.1	950.4	896.0
30°	1607.2	1524.1	1473.8	1420.5	1321.9	1208.0	1105.4	1041.7	961.7	893.9	837.5
32.5°	1576.5	1501.5	1460.5	1402.0	1295.2	1163.9	1062.3	991.4	907.3	840.6	786.2
35°	1525.1	1473.8	1428.7	1374.3	1260.3	1122.8	1019.2	936.0	850.8	787.2	735.9
37.5°	1461.5	1433.8	1391.7	1338.3	1220.3	1085.9	970.9	878.5	793.4	731.8	681.5
40°	1375.3	1382.5	1341.4	1293.2	1173.1	1035.6	908.3	820.0	740.0	682.5	633.2
42.5°	1281.9	1311.7	1288.1	1241.9	1120.8	980.2	862.1	764.6	686.6	627.1	586.0
45°	1181.3	1232.6	1218.3	1184.4	1066.4	921.7	796.4	702.0	633.2	575.8	539.9
47.5°	1071.5	1144.4	1144.4	1119.7	1005.8	863.1	740.0	643.5	575.8	534.7	499.8
50°	959.6	1041.7	1055.1	1038.7	938.1	796.4	671.2	584.0	525.5	485.5	459.8
52.5°	842.6	938.1	962.7	954.5	866.2	732.8	614.8	529.6	476.2	441.3	418.7
55°	730.8	841.6	868.3	871.4	789.3	663.0	552.2	477.2	425.9	402.3	382.8
57.5°	625.0	731.8	761.5	766.7	711.3	599.4	493.7	428.0	381.8	362.3	346.9
60°	534.7	624.0	663.0	674.3	626.1	525.5	439.3	375.6	340.7	322.3	307.9
62.5°	460.8	532.7	573.7	576.8	555.2	460.8	382.8	329.5	299.7	283.3	276.1
65°	389.0	453.6	478.3	490.6	473.1	399.2	330.5	286.3	262.7	248.4	241.2
67.5°	331.5	372.6	393.1	409.5	392.1	336.6	281.2	245.3	227.8	213.5	209.4
70°	272.0	305.8	321.2	337.7	322.3	280.2	240.2	207.3	191.9	180.6	175.5
72.5°	217.6	244.3	258.6	268.9	259.7	224.8	191.9	169.3	158.1	149.8	146.8
75°	172.4	190.9	199.1	206.3	202.2	175.5	155.0	136.5	126.2	119.1	117.0
77.5°	131.4	144.7	154.0	156.0	150.9	133.4	116.0	104.7	96.5	92.4	90.3
80°	93.4	101.6	106.7	109.8	104.7	97.5	85.2	77.0	69.8	64.7	63.6
82.5°	62.6	66.7	70.8	69.8	67.7	61.6	54.4	50.3	47.2	43.1	43.1
85°	35.9	36.9	39.0	40.0	39.0	34.9	30.8	28.7	26.7	23.6	23.6
87.5°	15.4	16.4	16.4	17.4	15.4	15.4	13.3	11.3	11.3	10.3	9.2
90°	10.3	9.0	8.4	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.4	14.9	14.7	15.0	15.6	16.3	16.9	17.5	16.9	16.3	15.6
95°	24.0	22.9	22.4	25.0	30.1	35.2	40.3	45.4	40.3	35.2	30.1
97.5°	28.2	25.7	24.5	30.9	43.6	56.3	69.0	81.7	69.0	56.3	43.6
100°	31.9	29.2	27.9	38.5	59.8	81.1	102.3	123.6	102.3	81.1	59.8
102.5°	126.0	154.3	168.4	168.6	168.9	169.2	169.5	169.8	169.5	169.2	168.9
105°	169.7	212.1	233.3	231.0	226.3	221.7	217.0	212.4	217.0	221.7	226.3
107.5°	200.9	253.2	279.4	277.5	273.6	269.7	265.9	262.0	265.9	269.7	273.6
110°	256.8	301.7	324.1	322.5	319.2	316.0	312.7	309.5	312.7	316.0	319.2

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	362.8	365.5	366.8	365.4	362.6	359.8	357.0	354.2	357.0	359.8	362.6
115°	419.4	415.5	413.6	412.3	409.6	407.0	404.3	401.7	404.3	407.0	409.6
117.5°	460.8	458.2	456.9	455.3	452.2	449.1	446.0	442.9	446.0	449.1	452.2
120°	503.7	500.9	499.5	498.3	496.0	493.7	491.3	489.0	491.3	493.7	496.0
122.5°	544.0	540.9	539.3	538.1	535.6	533.1	530.6	528.1	530.6	533.1	535.6
125°	581.4	578.5	577.0	576.0	574.0	571.9	569.9	567.9	569.9	571.9	574.0
127.5°	617.5	615.2	614.0	612.9	610.8	608.6	606.5	604.3	606.5	608.6	610.8
130°	652.3	650.6	649.7	648.5	646.0	643.5	641.0	638.5	641.0	643.5	646.0
132.5°	685.1	683.4	682.5	681.5	679.5	677.4	675.4	673.4	675.4	677.4	679.5
135°	716.0	714.6	713.9	712.7	710.2	707.7	705.3	702.8	705.3	707.7	710.2
137.5°	744.2	742.7	741.9	741.0	739.1	737.2	735.4	733.5	735.4	737.2	739.1
140°	771.7	770.0	769.1	768.5	767.2	766.0	764.7	763.5	764.7	766.0	767.2
142.5°	796.6	794.6	793.6	793.1	792.0	790.9	789.8	788.7	789.8	790.9	792.0
145°	818.5	815.8	814.5	814.6	814.7	814.9	815.0	815.2	815.0	814.9	814.7
147.5°	840.2	837.5	836.2	836.4	836.9	837.4	837.8	838.3	837.8	837.4	836.9
150°	859.5	857.0	855.8	856.3	857.4	858.5	859.5	860.6	859.5	858.5	857.4
152.5°	877.4	875.1	873.9	874.5	875.8	877.0	878.3	879.5	878.3	877.0	875.8
155°	894.2	892.3	891.4	892.1	893.5	894.9	896.3	897.7	896.3	894.9	893.5
157.5°	908.8	907.4	906.7	907.3	908.6	909.8	911.1	912.3	911.1	909.8	908.6
160°	922.1	921.2	920.7	921.2	922.1	923.0	924.0	924.9	924.0	923.0	922.1
162.5°	933.1	932.3	931.9	932.4	933.3	934.2	935.2	936.1	935.2	934.2	933.3
165°	942.4	941.9	941.7	942.2	943.1	944.0	945.0	945.9	945.0	944.0	943.1
167.5°	950.1	949.6	949.4	949.9	950.8	951.7	952.7	953.6	952.7	951.7	950.8
170°	956.1	955.8	955.6	956.1	957.0	957.9	958.9	959.8	958.9	957.9	957.0
172.5°	960.3	960.0	959.8	960.3	961.2	962.1	963.1	964.0	963.1	962.1	961.2
175°	963.1	962.8	962.6	963.1	964.2	965.3	966.4	967.5	966.4	965.3	964.2
177.5°	964.2	964.1	964.0	964.5	965.6	966.7	967.8	968.9	967.8	966.7	965.6
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1320.9	1326.0	1325.0	1314.7	1303.4	1294.2	1276.8	1278.8	1272.7	1273.7	1279.8
5°	1288.1	1288.1	1283.9	1269.6	1251.1	1240.8	1221.3	1216.2	1203.9	1202.9	1201.8
7.5°	1253.2	1248.0	1242.9	1222.4	1199.8	1183.4	1156.7	1150.5	1138.2	1130.0	1125.9
10°	1212.1	1204.9	1194.7	1171.1	1143.3	1122.8	1095.1	1086.9	1063.3	1053.0	1046.9
12.5°	1166.9	1162.8	1146.4	1126.9	1081.8	1059.2	1019.2	1027.4	1003.8	983.2	980.2
15°	1121.8	1106.4	1097.2	1065.3	1010.9	1000.7	968.9	952.4	930.9	914.5	914.5
17.5°	1077.7	1054.0	1033.5	999.7	959.6	930.9	907.3	899.1	872.4	856.0	852.9
20°	1019.2	992.5	987.3	939.1	911.4	879.6	857.0	836.5	817.0	809.8	804.6
22.5°	963.7	932.9	924.7	883.7	856.0	824.1	801.6	787.2	772.8	767.7	758.5
25°	904.2	885.7	873.4	829.3	798.5	768.7	753.3	743.1	729.7	728.7	722.5
27.5°	846.7	829.3	817.0	774.9	752.3	724.6	712.3	701.0	693.8	690.7	687.6
30°	797.5	778.0	763.6	732.8	705.1	682.5	672.3	665.1	661.0	655.8	654.8
32.5°	743.1	731.8	712.3	688.7	667.1	645.6	639.4	634.3	628.1	626.1	625.0
35°	696.9	681.5	669.2	642.5	633.2	614.8	607.6	603.5	595.3	593.2	591.2
37.5°	651.7	637.4	624.0	607.6	590.1	579.9	575.8	569.6	565.5	566.5	564.5
40°	606.6	595.3	585.0	567.6	557.3	552.2	544.0	537.8	535.7	536.8	535.7
42.5°	562.4	552.2	546.0	532.7	522.4	517.3	512.1	506.0	509.1	509.1	512.1
45°	522.4	513.2	509.1	498.8	492.6	484.4	479.3	478.3	482.4	481.4	481.4
47.5°	481.4	478.3	473.1	463.9	455.7	450.6	449.5	449.5	453.6	455.7	454.7
50°	449.5	443.4	437.2	430.0	423.9	421.8	418.7	420.8	424.9	424.9	427.0
52.5°	409.5	405.4	403.4	397.2	393.1	393.1	393.1	394.1	397.2	400.3	399.2
55°	374.6	371.5	369.5	366.4	361.3	362.3	361.3	363.3	366.4	369.5	371.5
57.5°	337.7	336.6	334.6	329.5	329.5	328.4	331.5	332.5	337.7	339.7	342.8
60°	304.8	301.7	301.7	297.6	297.6	297.6	300.7	303.8	307.9	308.9	311.0
62.5°	269.9	269.9	268.9	265.8	265.8	268.9	269.9	274.0	276.1	276.1	279.2
65°	237.1	236.1	235.0	236.1	237.1	237.1	240.2	242.2	244.3	245.3	246.3
67.5°	204.2	203.2	205.3	204.2	206.3	210.4	209.4	212.5	215.5	215.5	216.6
70°	173.5	175.5	174.5	176.5	175.5	177.6	180.6	181.7	181.7	182.7	185.8
72.5°	144.7	144.7	144.7	143.7	144.7	146.8	148.8	149.8	151.9	152.9	156.0
75°	117.0	117.0	114.9	117.0	117.0	119.1	121.1	121.1	121.1	123.2	126.2
77.5°	88.3	89.3	88.3	90.3	90.3	91.3	93.4	92.4	94.4	95.4	96.5
80°	64.7	63.6	63.6	63.6	64.7	64.7	66.7	67.7	67.7	70.8	68.8
82.5°	41.1	42.1	41.1	42.1	42.1	43.1	42.1	43.1	44.1	46.2	45.2
85°	23.6	22.6	22.6	23.6	22.6	22.6	23.6	22.6	23.6	22.6	23.6
87.5°	9.2	8.2	8.2	8.2	8.2	7.2	7.2	6.2	6.2	6.2	5.1
90°	7.5	8.4	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1
92.5°	15.0	14.7	14.9	15.4	15.9	16.3	16.8	17.1	17.4	17.7	18.0
95°	25.0	22.4	22.9	24.0	25.1	26.1	27.2	28.0	28.8	29.5	30.3
97.5°	30.9	24.5	25.7	28.2	30.7	33.1	35.6	36.1	36.5	37.0	37.5
100°	38.5	27.9	29.2	31.9	34.5	37.2	39.8	41.0	42.3	43.5	44.8
102.5°	168.6	168.4	154.3	126.0	97.7	69.5	41.2	42.9	44.6	46.3	48.0
105°	231.0	233.3	212.1	169.7	127.4	85.0	42.6	44.3	46.0	47.7	49.4
107.5°	277.5	279.4	253.2	200.9	148.6	96.3	44.0	45.7	47.4	49.1	50.8
110°	322.5	324.1	301.7	256.8	212.0	167.1	122.3	106.8	91.2	75.7	60.2

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	365.4	366.8	365.5	362.8	360.2	357.5	354.9	288.0	221.1	154.2	87.3
115°	412.3	413.6	415.5	419.4	423.3	427.1	431.0	359.1	287.3	215.4	143.5
117.5°	455.3	456.9	458.2	460.8	463.5	466.1	468.7	446.5	424.3	402.1	379.9
120°	498.3	499.5	500.9	503.7	506.5	509.3	512.1	513.9	515.8	517.6	519.5
122.5°	538.1	539.3	540.9	544.0	547.1	550.2	553.3	554.2	555.2	556.1	557.0
125°	576.0	577.0	578.5	581.4	584.4	587.3	590.3	591.4	592.5	593.6	594.7
127.5°	612.9	614.0	615.2	617.5	619.8	622.2	624.5	626.1	627.6	629.2	630.7
130°	648.5	649.7	650.6	652.3	654.0	655.7	657.4	659.1	660.8	662.5	664.2
132.5°	681.5	682.5	683.4	685.1	686.8	688.5	690.2	691.6	693.0	694.4	695.8
135°	712.7	713.9	714.6	716.0	717.4	718.8	720.2	721.8	723.3	724.9	726.4
137.5°	741.0	741.9	742.7	744.2	745.8	747.3	748.9	750.5	752.0	753.6	755.1
140°	768.5	769.1	770.0	771.7	773.4	775.1	776.8	778.2	779.6	781.0	782.4
142.5°	793.1	793.6	794.6	796.6	798.7	800.7	802.7	803.9	805.2	806.4	807.7
145°	814.6	814.5	815.8	818.5	821.1	823.8	826.4	827.5	828.6	829.7	830.8
147.5°	836.4	836.2	837.5	840.2	842.8	845.5	848.1	848.9	849.7	850.4	851.2
150°	856.3	855.8	857.0	859.5	862.0	864.4	866.9	867.8	868.8	869.7	870.6
152.5°	874.5	873.9	875.1	877.4	879.7	882.1	884.4	885.3	886.3	887.2	888.1
155°	892.1	891.4	892.3	894.2	896.1	897.9	899.8	900.7	901.7	902.6	903.5
157.5°	907.3	906.7	907.4	908.8	910.2	911.6	913.0	914.1	915.2	916.3	917.4
160°	921.2	920.7	921.2	922.1	923.0	924.0	924.9	925.8	926.8	927.7	928.6
162.5°	932.4	931.9	932.3	933.1	933.8	934.6	935.4	936.5	937.6	938.7	939.8
165°	942.2	941.7	941.9	942.4	942.9	943.3	943.8	944.9	946.0	947.1	948.2
167.5°	949.9	949.4	949.6	950.1	950.6	951.0	951.5	952.6	953.6	954.7	955.8
170°	956.1	955.6	955.8	956.1	956.4	956.7	957.0	958.1	959.2	960.3	961.4
172.5°	960.3	959.8	960.0	960.3	960.6	960.9	961.2	962.3	963.4	964.5	965.6
175°	963.1	962.6	962.8	963.1	963.4	963.7	964.0	965.1	966.2	967.3	968.4
177.5°	964.5	964.0	964.1	964.2	964.4	964.5	964.7	965.8	966.9	968.0	969.1
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1272.7	1275.7	1268.6	1266.5	1268.6	1261.4	1263.4	1265.5	1265.5	1268.6	1270.6
5°	1198.8	1194.7	1187.5	1185.4	1183.4	1186.4	1184.4	1187.5	1188.5	1195.7	1196.7
7.5°	1125.9	1119.7	1113.6	1107.4	1105.4	1100.2	1105.4	1105.4	1112.5	1110.5	1115.6
10°	1039.7	1038.7	1030.4	1027.4	1023.3	1015.0	1026.3	1023.3	1028.4	1037.6	1039.7
12.5°	976.0	964.8	969.9	955.5	960.7	952.4	953.5	953.5	961.7	962.7	960.7
15°	915.5	906.3	892.9	886.8	883.7	879.6	892.9	893.9	887.8	902.2	897.0
17.5°	853.9	853.9	841.6	838.5	830.3	834.4	832.4	833.4	831.3	841.6	846.7
20°	800.5	795.4	791.3	792.3	782.1	780.0	778.0	780.0	787.2	794.4	796.4
22.5°	757.4	754.4	744.1	746.1	737.9	741.0	739.0	744.1	745.1	745.1	752.3
25°	716.4	712.3	713.3	709.2	706.1	706.1	703.0	706.1	710.2	712.3	713.3
27.5°	685.6	682.5	677.4	674.3	676.4	671.2	675.3	678.4	678.4	676.4	678.4
30°	648.6	650.7	650.7	640.4	644.5	642.5	645.6	647.6	647.6	648.6	646.6
32.5°	624.0	617.9	616.8	615.8	615.8	611.7	611.7	614.8	615.8	616.8	619.9
35°	591.2	591.2	586.0	589.1	585.0	586.0	585.0	586.0	588.1	585.0	588.1
37.5°	561.4	562.4	560.4	562.4	563.5	561.4	559.4	563.5	561.4	561.4	559.4
40°	535.7	534.7	535.7	535.7	535.7	536.8	534.7	534.7	534.7	532.7	530.6
42.5°	514.2	508.0	510.1	511.1	508.0	508.0	509.1	508.0	511.1	505.0	505.0
45°	483.4	481.4	482.4	482.4	484.4	481.4	483.4	484.4	481.4	480.3	478.3
47.5°	455.7	457.7	455.7	457.7	457.7	459.8	455.7	456.7	457.7	453.6	450.6
50°	428.0	428.0	431.1	430.0	431.1	429.0	429.0	428.0	429.0	427.0	423.9
52.5°	402.3	399.2	404.4	403.4	402.3	401.3	400.3	401.3	399.2	397.2	397.2
55°	370.5	370.5	373.6	374.6	374.6	372.6	370.5	371.5	370.5	369.5	368.5
57.5°	344.8	340.7	342.8	343.8	343.8	340.7	342.8	340.7	340.7	341.8	338.7
60°	312.0	312.0	310.0	313.0	313.0	311.0	311.0	312.0	310.0	308.9	307.9
62.5°	277.1	278.1	281.2	282.2	283.3	281.2	279.2	280.2	280.2	277.1	278.1
65°	247.3	249.4	253.5	252.5	250.4	251.5	249.4	250.4	247.3	248.4	245.3
67.5°	218.6	217.6	218.6	218.6	220.7	219.6	217.6	217.6	216.6	219.6	216.6
70°	187.8	187.8	187.8	187.8	188.8	189.9	187.8	185.8	186.8	184.7	183.7
72.5°	156.0	157.0	156.0	158.1	155.0	157.0	157.0	156.0	155.0	155.0	155.0
75°	126.2	128.3	125.2	126.2	125.2	127.3	126.2	126.2	124.2	123.2	124.2
77.5°	96.5	97.5	95.4	96.5	95.4	96.5	96.5	95.4	95.4	95.4	95.4
80°	68.8	69.8	68.8	67.7	66.7	68.8	66.7	67.7	68.8	67.7	69.8
82.5°	44.1	44.1	43.1	44.1	42.1	42.1	43.1	43.1	42.1	44.1	42.1
85°	21.6	21.6	23.6	21.6	20.5	20.5	20.5	21.6	20.5	22.6	21.6
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.2	4.1
90°	17.5	17.7	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.7	30.6	30.5	30.3	30.2	30.0	30.2	30.3	30.5	30.6	30.7
97.5°	37.7	37.8	37.9	38.1	38.2	38.4	38.2	38.1	37.9	37.8	37.7
100°	45.4	45.6	45.9	46.2	46.5	46.8	46.5	46.2	45.9	45.6	45.4
102.5°	48.9	49.1	49.6	50.1	50.5	51.0	50.5	50.1	49.6	49.1	48.9
105°	50.3	50.6	51.2	51.9	52.5	53.1	52.5	51.9	51.2	50.6	50.3
107.5°	51.7	52.0	52.6	53.3	53.9	54.5	53.9	53.3	52.6	52.0	51.7
110°	52.4	52.7	53.3	54.0	54.6	55.2	54.6	54.0	53.3	52.7	52.4



TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.8	54.0	54.5	55.0	55.4	55.9	55.4	55.0	54.5	54.0	53.8
115°	107.6	102.0	90.8	79.7	68.5	57.3	68.5	79.7	90.8	102.0	107.6
117.5°	368.8	348.5	307.8	267.1	226.5	185.8	226.5	267.1	307.8	348.5	368.8
120°	520.4	509.9	489.0	468.0	447.1	426.1	447.1	468.0	489.0	509.9	520.4
122.5°	557.5	557.6	557.7	557.9	558.0	558.2	558.0	557.9	557.7	557.6	557.5
125°	595.2	595.4	595.9	596.4	596.8	597.3	596.8	596.4	595.9	595.4	595.2
127.5°	631.5	631.6	631.7	631.9	632.0	632.2	632.0	631.9	631.7	631.6	631.5
130°	665.0	664.9	664.8	664.6	664.5	664.3	664.5	664.6	664.8	664.9	665.0
132.5°	696.5	696.4	696.3	696.1	696.0	695.8	696.0	696.1	696.3	696.4	696.5
135°	727.2	727.0	726.7	726.4	726.1	725.8	726.1	726.4	726.7	727.0	727.2
137.5°	755.9	755.7	755.2	754.7	754.3	753.8	754.3	754.7	755.2	755.7	755.9
140°	783.1	782.7	781.9	781.2	780.4	779.6	780.4	781.2	781.9	782.7	783.1
142.5°	808.3	807.9	807.1	806.4	805.6	804.8	805.6	806.4	807.1	807.9	808.3
145°	831.3	830.9	830.1	829.4	828.6	827.8	828.6	829.4	830.1	830.9	831.3
147.5°	851.6	851.3	850.7	850.0	849.4	848.8	849.4	850.0	850.7	851.3	851.6
150°	871.1	870.7	869.9	869.2	868.4	867.6	868.4	869.2	869.9	870.7	871.1
152.5°	888.6	888.1	887.0	885.9	884.8	883.7	884.8	885.9	887.0	888.1	888.6
155°	904.0	903.4	902.1	900.9	899.6	898.4	899.6	900.9	902.1	903.4	904.0
157.5°	917.9	917.3	916.0	914.8	913.5	912.3	913.5	914.8	916.0	917.3	917.9
160°	929.1	928.6	927.5	926.4	925.3	924.2	925.3	926.4	927.5	928.6	929.1
162.5°	940.3	939.6	938.2	936.8	935.4	934.0	935.4	936.8	938.2	939.6	940.3
165°	948.7	948.2	947.1	946.0	944.9	943.8	944.9	946.0	947.1	948.2	948.7
167.5°	956.3	955.6	954.2	952.9	951.5	950.1	951.5	952.9	954.2	955.6	956.3
170°	961.9	961.2	959.8	958.4	957.0	955.6	957.0	958.4	959.8	961.2	961.9
172.5°	966.1	965.4	964.0	962.6	961.2	959.8	961.2	962.6	964.0	965.4	966.1
175°	968.9	968.1	966.6	965.0	963.5	961.9	963.5	965.0	966.6	968.1	968.9
177.5°	969.6	968.9	967.5	966.1	964.7	963.3	964.7	966.1	967.5	968.9	969.6
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1267.5	1275.7	1272.7	1261.4	1274.7	1274.7	1283.9	1283.9	1295.2	1299.3	1305.5
5°	1195.7	1201.8	1207.0	1201.8	1211.1	1225.4	1233.7	1240.8	1256.2	1262.4	1271.6
7.5°	1118.7	1130.0	1135.1	1135.1	1150.5	1166.9	1183.4	1193.6	1215.2	1223.4	1232.6
10°	1043.8	1057.1	1067.4	1066.4	1092.0	1102.3	1122.8	1146.4	1168.0	1180.3	1193.6
12.5°	964.8	971.9	986.3	1006.8	1013.0	1031.5	1055.1	1084.8	1123.8	1135.1	1154.6
15°	899.1	918.6	929.9	939.1	953.5	970.9	996.6	1025.3	1064.3	1088.9	1109.5
17.5°	843.6	869.3	876.5	874.4	892.9	919.6	949.4	970.9	1005.8	1035.6	1055.1
20°	798.5	808.8	821.1	826.2	840.6	869.3	898.0	922.7	951.4	975.0	997.6
22.5°	753.3	761.5	771.8	781.0	792.3	808.8	836.5	867.3	895.0	917.5	943.2
25°	716.4	721.5	730.8	737.9	750.3	761.5	781.0	814.9	847.8	861.1	883.7
27.5°	680.5	684.6	690.7	698.9	705.1	716.4	733.8	761.5	795.4	808.8	839.5
30°	648.6	651.7	657.9	662.0	665.1	678.4	691.8	713.3	739.0	757.4	780.0
32.5°	618.9	622.0	628.1	629.1	633.2	640.4	652.8	672.3	694.8	710.2	729.7
35°	586.0	588.1	594.2	596.3	599.4	605.5	614.8	629.1	649.7	661.0	678.4
37.5°	560.4	559.4	563.5	566.5	570.6	573.7	576.8	591.2	606.6	616.8	630.2
40°	532.7	530.6	531.6	535.7	537.8	541.9	541.9	556.3	566.5	574.7	585.0
42.5°	505.0	503.9	501.9	503.9	506.0	507.0	508.0	518.3	528.6	535.7	547.0
45°	477.2	476.2	474.2	475.2	475.2	477.2	480.3	484.4	491.6	497.8	503.9
47.5°	451.6	449.5	446.5	445.4	447.5	447.5	447.5	451.6	458.8	460.8	467.0
50°	424.9	421.8	417.7	415.7	415.7	414.6	416.7	417.7	423.9	425.9	431.1
52.5°	396.2	394.1	390.0	385.9	386.9	384.9	385.9	386.9	389.0	392.1	395.1
55°	367.4	363.3	360.2	359.2	356.1	356.1	353.1	357.2	356.1	357.2	361.3
57.5°	339.7	335.6	330.5	328.4	325.3	324.3	322.3	321.2	322.3	325.3	328.4
60°	306.9	304.8	301.7	298.7	296.6	293.5	291.5	291.5	290.5	290.5	291.5
62.5°	275.1	274.0	269.9	268.9	266.8	264.8	261.7	259.7	259.7	261.7	262.7
65°	244.3	243.2	240.2	239.1	234.0	232.0	230.9	229.9	227.8	227.8	227.8
67.5°	215.5	212.5	212.5	207.3	203.2	201.2	199.1	198.1	198.1	198.1	199.1
70°	183.7	183.7	180.6	177.6	173.5	174.5	171.4	168.3	168.3	166.3	167.3
72.5°	152.9	151.9	148.8	147.8	144.7	141.6	139.6	141.6	138.6	137.5	138.6
75°	123.2	122.1	120.1	118.0	119.1	116.0	112.9	111.9	111.9	109.8	109.8
77.5°	94.4	96.5	92.4	91.3	89.3	87.2	86.2	85.2	85.2	85.2	87.2
80°	65.7	66.7	66.7	64.7	65.7	62.6	62.6	62.6	59.5	60.6	61.6
82.5°	42.1	42.1	41.1	42.1	41.1	41.1	40.0	40.0	39.0	39.0	40.0
85°	23.6	22.6	21.6	23.6	22.6	22.6	21.6	21.6	21.6	21.6	21.6
87.5°	5.1	6.2	6.2	6.2	6.2	7.2	7.2	7.2	8.2	8.2	8.2
90°	17.1	16.3	15.6	14.8	14.0	12.8	11.5	10.3	9.0	8.4	7.5
92.5°	18.0	17.7	17.4	17.1	16.8	16.3	15.9	15.4	14.9	14.7	15.0
95°	30.3	29.5	28.8	28.0	27.2	26.1	25.1	24.0	22.9	22.4	25.0
97.5°	37.5	37.0	36.5	36.1	35.6	33.1	30.7	28.2	25.7	24.5	30.9
100°	44.8	43.5	42.3	41.0	39.8	37.2	34.5	31.9	29.2	27.9	38.5
102.5°	48.0	46.3	44.6	42.9	41.2	69.5	97.7	126.0	154.3	168.4	168.6
105°	49.4	47.7	46.0	44.3	42.6	85.0	127.4	169.7	212.1	233.3	231.0
107.5°	50.8	49.1	47.4	45.7	44.0	96.3	148.6	200.9	253.2	279.4	277.5
110°	60.2	75.7	91.2	106.8	122.3	167.1	212.0	256.8	301.7	324.1	322.5

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	87.3	154.2	221.1	288.0	354.9	357.5	360.2	362.8	365.5	366.8	365.4
115°	143.5	215.4	287.3	359.1	431.0	427.1	423.3	419.4	415.5	413.6	412.3
117.5°	379.9	402.1	424.3	446.5	468.7	466.1	463.5	460.8	458.2	456.9	455.3
120°	519.5	517.6	515.8	513.9	512.1	509.3	506.5	503.7	500.9	499.5	498.3
122.5°	557.0	556.1	555.2	554.2	553.3	550.2	547.1	544.0	540.9	539.3	538.1
125°	594.7	593.6	592.5	591.4	590.3	587.3	584.4	581.4	578.5	577.0	576.0
127.5°	630.7	629.2	627.6	626.1	624.5	622.2	619.8	617.5	615.2	614.0	612.9
130°	664.2	662.5	660.8	659.1	657.4	655.7	654.0	652.3	650.6	649.7	648.5
132.5°	695.8	694.4	693.0	691.6	690.2	688.5	686.8	685.1	683.4	682.5	681.5
135°	726.4	724.9	723.3	721.8	720.2	718.8	717.4	716.0	714.6	713.9	712.7
137.5°	755.1	753.6	752.0	750.5	748.9	747.3	745.8	744.2	742.7	741.9	741.0
140°	782.4	781.0	779.6	778.2	776.8	775.1	773.4	771.7	770.0	769.1	768.5
142.5°	807.7	806.4	805.2	803.9	802.7	800.7	798.7	796.6	794.6	793.6	793.1
145°	830.8	829.7	828.6	827.5	826.4	823.8	821.1	818.5	815.8	814.5	814.6
147.5°	851.2	850.4	849.7	848.9	848.1	845.5	842.8	840.2	837.5	836.2	836.4
150°	870.6	869.7	868.8	867.8	866.9	864.4	862.0	859.5	857.0	855.8	856.3
152.5°	888.1	887.2	886.3	885.3	884.4	882.1	879.7	877.4	875.1	873.9	874.5
155°	903.5	902.6	901.7	900.7	899.8	897.9	896.1	894.2	892.3	891.4	892.1
157.5°	917.4	916.3	915.2	914.1	913.0	911.6	910.2	908.8	907.4	906.7	907.3
160°	928.6	927.7	926.8	925.8	924.9	924.0	923.0	922.1	921.2	920.7	921.2
162.5°	939.8	938.7	937.6	936.5	935.4	934.6	933.8	933.1	932.3	931.9	932.4
165°	948.2	947.1	946.0	944.9	943.8	943.3	942.9	942.4	941.9	941.7	942.2
167.5°	955.8	954.7	953.6	952.6	951.5	951.0	950.6	950.1	949.6	949.4	949.9
170°	961.4	960.3	959.2	958.1	957.0	956.7	956.4	956.1	955.8	955.6	956.1
172.5°	965.6	964.5	963.4	962.3	961.2	960.9	960.6	960.3	960.0	959.8	960.3
175°	968.4	967.3	966.2	965.1	964.0	963.7	963.4	963.1	962.8	962.6	963.1
177.5°	969.1	968.0	966.9	965.8	964.7	964.5	964.4	964.2	964.1	964.0	964.5
180°	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4	965.4

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1335.3	1335.3	1335.3	1335.3
2.5°	1310.6	1310.6	1326.0	1342.4
5°	1281.9	1289.1	1313.7	1336.3
7.5°	1254.2	1266.5	1297.3	1326.0
10°	1220.3	1236.7	1274.7	1308.6
12.5°	1187.5	1202.9	1247.0	1285.0
15°	1141.3	1160.8	1208.0	1255.2
17.5°	1095.1	1114.6	1172.1	1227.5
20°	1040.7	1066.4	1131.0	1204.9
22.5°	990.4	1022.2	1094.1	1153.6
25°	935.0	984.3	1051.0	1127.9
27.5°	885.7	935.0	1002.7	1080.7
30°	830.3	880.6	950.4	1022.2
32.5°	776.9	823.1	890.9	979.1
35°	721.5	765.6	831.3	920.6
37.5°	671.2	714.3	786.2	868.3
40°	622.0	667.1	728.7	810.8
42.5°	575.8	615.8	671.2	753.3
45°	533.7	562.4	613.7	690.7
47.5°	489.6	515.2	562.4	639.4
50°	448.5	470.1	511.1	583.0
52.5°	408.5	427.0	464.9	522.4
55°	372.6	390.0	417.7	474.2
57.5°	335.6	349.0	375.6	420.8
60°	299.7	312.0	333.6	370.5
62.5°	263.8	274.0	294.6	324.3
65°	232.0	240.2	255.6	281.2
67.5°	201.2	206.3	218.6	239.1
70°	171.4	175.5	185.8	202.2
72.5°	139.6	143.7	155.0	166.3
75°	112.9	113.9	122.1	131.4
77.5°	88.3	87.2	93.4	100.6
80°	60.6	63.6	68.8	71.8
82.5°	41.1	42.1	44.1	46.2
85°	22.6	23.6	23.6	26.7
87.5°	9.2	10.3	10.3	11.3
90°	5.8	4.1	2.4	0.7
92.5°	15.6	16.3	16.9	17.5
95°	30.1	35.2	40.3	45.4
97.5°	43.6	56.3	69.0	81.7
100°	59.8	81.1	102.3	123.6
102.5°	168.9	169.2	169.5	169.8
105°	226.3	221.7	217.0	212.4
107.5°	273.6	269.7	265.9	262.0
110°	319.2	316.0	312.7	309.5



TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	362.6	359.8	357.0	354.2
115°	409.6	407.0	404.3	401.7
117.5°	452.2	449.1	446.0	442.9
120°	496.0	493.7	491.3	489.0
122.5°	535.6	533.1	530.6	528.1
125°	574.0	571.9	569.9	567.9
127.5°	610.8	608.6	606.5	604.3
130°	646.0	643.5	641.0	638.5
132.5°	679.5	677.4	675.4	673.4
135°	710.2	707.7	705.3	702.8
137.5°	739.1	737.2	735.4	733.5
140°	767.2	766.0	764.7	763.5
142.5°	792.0	790.9	789.8	788.7
145°	814.7	814.9	815.0	815.2
147.5°	836.9	837.4	837.8	838.3
150°	857.4	858.5	859.5	860.6
152.5°	875.8	877.0	878.3	879.5
155°	893.5	894.9	896.3	897.7
157.5°	908.6	909.8	911.1	912.3
160°	922.1	923.0	924.0	924.9
162.5°	933.3	934.2	935.2	936.1
165°	943.1	944.0	945.0	945.9
167.5°	950.8	951.7	952.7	953.6
170°	957.0	957.9	958.9	959.8
172.5°	961.2	962.1	963.1	964.0
175°	964.2	965.3	966.4	967.5
177.5°	965.6	966.7	967.8	968.9
180°	965.4	965.4	965.4	965.4

TEST NUMBER: P998862

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.54	17.38	17.49	18.34	19.60	14.03	14.87	14.99	15.83	17.09
	3H	17.35	18.10	18.32	19.07	20.35	15.37	16.12	16.34	17.10	18.38
	4H	17.52	18.22	18.50	19.20	20.49	15.84	16.54	16.82	17.52	18.81
	6H	17.56	18.21	18.55	19.20	20.50	16.14	16.79	17.13	17.78	19.08
	8H	17.54	18.16	18.54	19.16	20.46	16.23	16.84	17.22	17.85	19.15
	12H	17.50	18.09	18.50	19.08	20.41	16.27	16.86	17.27	17.85	19.17
4H	2H	16.58	17.28	17.56	18.26	19.56	14.47	15.18	15.46	16.16	17.45
	3H	17.56	18.14	18.55	19.15	20.46	15.93	16.52	16.93	17.53	18.83
	4H	17.83	18.37	18.84	19.37	20.70	16.47	17.00	17.47	18.01	19.33
	6H	17.96	18.42	18.98	19.45	20.77	16.85	17.31	17.86	18.33	19.66
	8H	17.96	18.39	18.97	19.41	20.75	16.96	17.39	17.97	18.40	19.74
	12H	17.92	18.31	18.96	19.34	20.69	17.01	17.40	18.04	18.43	19.78
8H	4H	17.84	18.27	18.86	19.29	20.63	16.61	17.04	17.62	18.06	19.40
	6H	18.02	18.37	19.06	19.43	20.77	17.04	17.40	18.08	18.46	19.79
	8H	18.05	18.36	19.10	19.41	20.76	17.19	17.50	18.24	18.55	19.91
	12H	18.03	18.31	19.08	19.35	20.75	17.28	17.56	18.33	18.60	20.00
12H	4H	17.80	18.18	18.83	19.22	20.56	16.58	16.97	17.62	18.00	19.35
	6H	18.00	18.31	19.04	19.35	20.71	17.04	17.35	18.09	18.40	19.76
	8H	18.03	18.30	19.08	19.34	20.74	17.20	17.47	18.25	18.51	19.91