

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998868

Luminaire Tested: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998868
REPORT IS A COMBINATION OF REPORTS P984614 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5557.9 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998868

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P998868

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43		
1	95	90	86	82	87	82	79	75	68	65	63	54	53	51	42	41	40	34		
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32	27		
3	78	68	60	54	71	62	56	50	51	46	42	41	38	34	32	29	27	23		
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23	19		
5	65	53	45	39	59	49	41	36	40	35	30	33	28	25	25	22	20	16		
6	60	48	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17	14		
7	55	43	35	29	50	39	32	27	33	27	23	27	22	19	21	18	15	12		
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11		
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10		
10	44	32	25	20	41	30	23	19	25	20	16	20	16	14	16	13	11	9		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11259	11259	11259
5°	11309	10779	10717
10°	11234	10404	10254
15°	11076	10019	9778
20°	10876	9614	9325
25°	10678	9225	8916
30°	10402	8831	8510
35°	10121	8451	8212
40°	9826	8121	7915
45°	9546	7823	7658
50°	9245	7548	7402
55°	8926	7255	7142
60°	8539	6952	6870
65°	8134	6603	6555
70°	7678	6226	6218
75°	7093	5851	5899
80°	6171	5460	5569
85°	5241	5092	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9546 cd/sqm

TEST NUMBER: P998868

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	1.2
10°-20°	193.4	3.5
20°-30°	293.0	5.3
30°-40°	356.8	6.4
40°-50°	383.9	6.9
50°-60°	372.8	6.7
60°-70°	325.6	5.9
70°-80°	250.6	4.5
80°-90°	169.5	3.1
90°-100°	147.8	2.7
100°-110°	203.7	3.7
110°-120°	371.9	6.7
120°-130°	555.3	10.0
130°-140°	569.9	10.3
140°-150°	519.7	9.4
150°-160°	416.1	7.5
160°-170°	268.1	4.8
170°-180°	92.3	1.7
0°-30°	553.8	10.0
0°-40°	910.7	16.4
0°-60°	1667.4	30.0
0°-90°	2413.1	43.4
90°-120°	723.4	13.0
90°-150°	2368.4	42.6
90°-180°	3145.0	56.6
0°-180°	5557.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	711	711	711	711	711	
5°	713	710	704	710	709	68
15°	680	682	682	692	691	192
25°	618	626	635	647	650	284
35°	533	550	570	593	600	333
45°	437	465	501	533	543	337
55°	335	372	426	463	476	300
65°	229	279	340	382	396	227
75°	127	184	250	295	308	134
85°	37	101	167	210	225	39
90°	11	78	150	195	209	10
95°	54	79	146	189	200	60
105°	218	269	132	175	189	234
115°	408	431	495	201	162	401
125°	572	582	628	661	672	511
135°	707	718	735	763	770	546
145°	819	818	830	841	843	512
155°	902	895	904	908	902	415
165°	950	946	948	953	948	268
175°	972	967	968	973	966	92
180°	970	970	970	970	970	

TEST NUMBER: P998868

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.3	711.3	711.3	711.3	711.3
2.5°	716.4	713.3	706.1	711.3	709.2
5°	713.3	710.3	704.1	710.3	709.2
7.5°	708.2	706.1	701.0	708.2	707.2
10°	702.0	699.9	696.8	705.1	704.1
12.5°	691.7	692.7	690.7	698.9	697.9
15°	680.4	682.4	682.4	691.7	690.7
17.5°	665.9	670.0	673.1	682.4	682.4
20°	651.5	656.6	660.8	672.1	672.1
22.5°	636.0	642.2	648.4	659.7	661.8
25°	618.5	625.7	635.0	647.4	650.5
27.5°	597.9	609.2	619.5	635.0	637.1
30°	577.3	590.7	604.1	620.6	623.7
32.5°	554.6	570.1	586.5	606.1	612.3
35°	532.9	550.5	570.1	592.7	600.0
37.5°	509.2	528.8	553.6	578.3	585.5
40°	485.5	508.2	536.0	562.8	572.1
42.5°	462.8	485.5	518.5	548.4	557.7
45°	437.1	464.9	501.0	532.9	543.3
47.5°	412.3	442.2	483.5	516.5	527.8
50°	386.6	418.5	464.9	500.0	511.3
52.5°	361.8	395.8	445.3	481.4	493.8
55°	335.0	372.1	425.7	462.8	476.2
57.5°	309.3	350.5	404.1	444.3	457.7
60°	281.4	325.7	384.5	423.7	438.1
62.5°	256.7	303.1	361.8	404.1	417.5
65°	228.8	279.4	340.2	382.4	395.8
67.5°	204.1	256.7	318.5	360.8	375.2
70°	177.3	230.9	294.8	339.1	351.5
72.5°	152.6	208.2	273.2	316.5	331.9
75°	126.8	184.5	250.5	294.8	308.2
77.5°	102.1	161.8	228.8	273.2	287.6
80°	77.3	140.2	207.2	250.5	264.9
82.5°	56.7	118.5	186.6	229.9	243.3
85°	37.1	101.0	167.0	210.3	224.7
87.5°	22.7	84.5	150.5	192.8	206.2
90°	11.0	78.5	150.1	194.8	208.6
92.5°	26.8	78.6	143.6	185.2	198.3
95°	53.8	79.1	145.9	188.6	200.3
97.5°	89.3	76.1	147.1	187.4	200.4
100°	131.4	73.5	143.1	186.8	199.6
102.5°	176.7	209.3	137.3	182.1	195.5
105°	218.5	269.3	131.5	175.2	189.4
107.5°	268.3	310.5	125.6	168.4	182.5
110°	314.9	350.2	198.1	160.8	175.0

TEST NUMBER: P998868

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.8	388.9	424.4	155.0	168.5
115°	407.5	430.8	494.7	200.8	161.6
117.5°	447.9	470.1	525.3	456.0	282.5
120°	494.2	508.8	562.6	599.9	516.6
122.5°	533.5	545.7	597.9	629.9	639.9
125°	572.4	581.6	627.8	660.6	672.0
127.5°	608.9	617.6	656.1	688.8	698.8
130°	643.3	653.4	682.8	715.3	722.9
132.5°	678.4	686.4	709.6	739.6	747.1
135°	706.7	718.0	734.6	763.3	770.1
137.5°	737.6	746.0	758.2	784.9	790.0
140°	767.8	772.4	782.2	805.0	807.6
142.5°	793.0	796.9	806.1	824.1	825.7
145°	818.7	818.0	829.9	841.0	842.6
147.5°	841.8	839.7	851.7	856.2	856.5
150°	864.3	859.4	870.6	874.8	871.3
152.5°	883.2	877.6	888.1	892.4	887.4
155°	901.5	895.2	903.6	907.8	902.2
157.5°	916.2	910.6	916.9	921.8	916.2
160°	928.8	924.6	928.8	933.0	928.1
162.5°	940.1	935.8	939.4	944.3	938.0
165°	949.9	945.7	947.8	952.7	947.8
167.5°	957.6	953.4	955.5	960.4	954.1
170°	963.9	959.7	961.1	966.0	959.7
172.5°	968.1	963.9	965.3	970.2	963.9
175°	971.6	966.7	968.1	973.0	966.0
177.5°	973.0	968.1	968.8	973.7	967.4
180°	969.5	969.5	969.5	969.5	969.5

TEST NUMBER: P998868

CATALOG NUMBER: SA2XXDIP-B675D725UB2750-4F0-XX-W2A-D_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.99	13.84	13.99	14.86	16.21	16.07	16.91	17.07	17.93	19.29
	3H	14.45	15.22	15.46	16.24	17.62	18.65	19.42	19.66	20.45	21.82
	4H	14.92	15.65	15.95	16.68	18.07	19.91	20.63	20.93	21.66	23.05
	6H	15.21	15.88	16.24	16.92	18.32	21.20	21.88	22.24	22.91	24.31
	8H	15.27	15.91	16.31	16.96	18.36	21.86	22.50	22.90	23.56	24.95
	12H	15.28	15.90	16.33	16.94	18.36	22.59	23.20	23.63	24.24	25.66
4H	2H	14.04	14.77	15.07	15.80	17.18	16.39	17.12	17.42	18.15	19.54
	3H	15.75	16.36	16.78	17.42	18.82	19.18	19.80	20.22	20.86	22.26
	4H	16.37	16.94	17.41	17.99	19.41	20.60	21.17	21.64	22.22	23.64
	6H	16.78	17.28	17.84	18.35	19.76	22.07	22.56	23.12	23.63	25.05
	8H	16.89	17.35	17.94	18.42	19.85	22.82	23.29	23.88	24.35	25.78
	12H	16.93	17.35	18.01	18.43	19.87	23.65	24.07	24.73	25.15	26.59
8H	4H	17.16	17.62	18.21	18.69	20.12	20.74	21.21	21.80	22.27	23.70
	6H	17.79	18.18	18.87	19.28	20.71	22.37	22.76	23.45	23.87	25.29
	8H	18.01	18.35	19.09	19.44	20.89	23.26	23.61	24.35	24.70	26.14
	12H	18.14	18.45	19.23	19.53	21.02	24.26	24.56	25.34	25.65	27.13
12H	4H	17.35	17.78	18.43	18.85	20.29	20.72	21.14	21.79	22.22	23.65
	6H	18.12	18.47	19.21	19.56	21.00	22.40	22.74	23.48	23.83	25.28
	8H	18.43	18.73	19.52	19.82	21.30	23.33	23.63	24.41	24.72	26.20