

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931429

Luminaire Tested: DFN2DS-TR3F0-090DS840-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931429
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-090DS840-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8918.9 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 99.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931429

CATALOG NUMBER: DFN2DS-TR3F0-090DS840-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931429

CATALOG NUMBER: DFN2DS-TR3F0-090DS840-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4368	4368	4368
5°	4385	4322	4347
10°	4359	4278	4299
15°	4305	4222	4218
20°	4228	4139	4135
25°	4152	4037	4037
30°	4055	3943	3909
35°	3964	3830	3774
40°	3849	3717	3646
45°	3737	3605	3517
50°	3614	3489	3365
55°	3486	3354	3230
60°	3343	3193	3075
65°	3191	3031	2893
70°	2997	2837	2702
75°	2726	2612	2548
80°	2420	2345	2225
85°	1973	1882	1687

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3737 cd/sqm

TEST NUMBER: P931429

CATALOG NUMBER: DFN2DS-TR3F0-090DS840-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.9	3.7
10°-20°	928.3	10.4
20°-30°	1364.2	15.3
30°-40°	1584.5	17.8
40°-50°	1582.5	17.7
50°-60°	1379.9	15.5
60°-70°	1020.1	11.4
70°-80°	577.1	6.5
80°-90°	152.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2622.5	29.4
0°-40°	4207.0	47.2
0°-60°	7169.4	80.4
0°-90°	8918.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8918.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3505	3505	3505	3505	3505	
5°	3505	3492	3455	3482	3475	333
15°	3337	3317	3273	3287	3270	940
25°	3020	2993	2936	2942	2936	1390
35°	2606	2572	2518	2498	2481	1627
45°	2120	2097	2046	2009	1996	1636
55°	1605	1584	1544	1504	1487	1435
65°	1082	1062	1028	998	981	1070
75°	566	560	542	522	529	604
85°	138	135	132	121	118	162
90°	0	0	0	0	0	

TEST NUMBER: P931429

CATALOG NUMBER: DFN2DS-TR3F0-090DS840-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3505.4	3505.4	3505.4	3505.4	3505.4
2.5°	3525.8	3509.0	3471.9	3505.4	3499.0
5°	3505.4	3492.2	3455.1	3481.9	3475.4
7.5°	3481.9	3461.9	3424.6	3451.8	3445.0
10°	3445.0	3421.4	3381.0	3407.8	3397.8
12.5°	3394.2	3374.2	3333.8	3350.5	3343.8
15°	3337.0	3317.0	3273.0	3286.6	3269.8
17.5°	3266.2	3246.1	3202.2	3219.0	3202.2
20°	3188.6	3168.6	3121.3	3131.3	3118.1
22.5°	3111.3	3081.0	3036.9	3036.9	3030.1
25°	3020.1	2993.3	2936.1	2942.5	2936.1
27.5°	2918.9	2895.3	2851.7	2841.7	2824.9
30°	2818.1	2790.9	2740.4	2730.4	2716.9
32.5°	2710.1	2690.1	2636.0	2615.7	2602.1
35°	2605.7	2572.1	2518.0	2497.7	2480.9
37.5°	2487.7	2457.3	2403.2	2379.7	2362.9
40°	2366.4	2339.2	2285.2	2255.2	2241.6
42.5°	2248.3	2221.2	2167.6	2133.6	2113.6
45°	2120.3	2096.8	2045.9	2009.1	1995.6
47.5°	1995.6	1972.0	1917.9	1880.8	1860.8
50°	1864.0	1847.1	1799.9	1752.8	1735.9
52.5°	1735.9	1712.3	1668.7	1631.5	1607.9
55°	1604.7	1584.3	1543.8	1503.5	1486.7
57.5°	1473.1	1456.3	1412.3	1371.9	1358.3
60°	1341.4	1328.2	1281.0	1243.8	1233.8
62.5°	1213.4	1189.8	1156.2	1122.6	1109.0
65°	1082.2	1061.8	1028.1	997.8	981.0
67.5°	947.3	930.2	900.1	876.6	863.0
70°	822.5	808.9	778.6	755.0	741.7
72.5°	694.5	680.9	664.1	640.5	630.5
75°	566.2	559.7	542.5	522.5	529.3
77.5°	451.7	438.1	431.3	421.3	411.3
80°	337.2	333.6	326.8	316.8	310.1
82.5°	229.2	229.2	226.0	212.4	212.4
85°	138.0	134.8	131.6	121.2	118.0
87.5°	60.8	54.0	47.2	37.2	33.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931429

CATALOG NUMBER: DFN2DS-TR3F0-090DS840-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.41	18.02	16.77	18.33	18.64	15.96	17.57	16.33	17.89	18.20
	3H	18.16	19.61	18.53	19.94	20.30	17.66	19.12	18.04	19.45	19.81
	4H	18.80	20.17	19.20	20.52	20.89	18.31	19.68	18.71	20.02	20.40
	6H	19.27	20.54	19.68	20.90	21.29	18.77	20.04	19.18	20.40	20.79
	8H	19.41	20.62	19.84	21.01	21.41	18.91	20.12	19.34	20.51	20.91
	12H	19.50	20.66	19.93	21.05	21.47	18.99	20.15	19.42	20.53	20.96
4H	2H	16.97	18.33	17.36	18.68	19.06	16.61	17.98	17.01	18.33	18.71
	3H	18.94	20.09	19.35	20.48	20.88	18.53	19.68	18.94	20.08	20.48
	4H	19.72	20.75	20.15	21.17	21.60	19.29	20.33	19.72	20.74	21.18
	6H	20.31	21.22	20.77	21.66	22.12	19.88	20.79	20.34	21.23	21.68
	8H	20.50	21.35	20.96	21.79	22.26	20.07	20.91	20.53	21.35	21.82
	12H	20.63	21.39	21.11	21.87	22.34	20.18	20.94	20.66	21.42	21.89
8H	4H	19.99	20.84	20.45	21.28	21.74	19.62	20.46	20.08	20.91	21.37
	6H	20.70	21.41	21.20	21.90	22.37	20.32	21.03	20.82	21.51	21.99
	8H	20.96	21.59	21.47	22.10	22.59	20.57	21.20	21.08	21.71	22.20
	12H	21.16	21.72	21.67	22.21	22.77	20.75	21.31	21.26	21.80	22.36
12H	4H	20.02	20.78	20.50	21.25	21.72	19.65	20.41	20.13	20.89	21.36
	6H	20.75	21.38	21.26	21.89	22.37	20.38	21.01	20.89	21.52	22.01
	8H	21.06	21.62	21.57	22.11	22.67	20.69	21.24	21.19	21.73	22.30