

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998922

Luminaire Tested: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998922
REPORT IS A COMBINATION OF REPORTS P984668 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6611.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	34	33
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	31	28
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22
7	58	47	39	33	54	43	36	32	37	31	28	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	18	16
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21137	21137	21137	21137
5°	21187	22537	21268	17929
10°	20941	24603	21073	14781
15°	20433	25949	20718	12452
20°	20114	24365	20114	10822
25°	19473	20932	19562	9678
30°	18418	16454	18769	8766
35°	17484	11378	17776	8020
40°	16410	8590	16596	7427
45°	15085	7060	15332	6785
50°	13942	6196	13965	6211
55°	12636	5279	12716	5588
60°	11243	4410	11397	4877
65°	9996	3587	10178	4165
70°	8757	2815	8978	3359
75°	7351	2042	7636	2437
80°	5732	1295	6148	1446
85°	3772	651	4054	482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21850 cd/sqm

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	1.9
10°-20°	370.2	5.6
20°-30°	537.2	8.1
30°-40°	566.3	8.6
40°-50°	501.2	7.6
50°-60°	400.2	6.1
60°-70°	271.8	4.1
70°-80°	139.1	2.1
80°-90°	35.1	0.5
90°-100°	41.2	0.6
100°-110°	153.6	2.3
110°-120°	407.3	6.2
120°-130°	675.6	10.2
130°-140°	717.6	10.9
140°-150°	666.9	10.1
150°-160°	536.2	8.1
160°-170°	345.5	5.2
170°-180°	118.9	1.8
0°-30°	1034.6	15.6
0°-40°	1600.9	24.2
0°-60°	2502.3	37.8
0°-90°	2948.2	44.6
90°-120°	602.1	9.1
90°-150°	2662.2	40.3
90°-180°	3663.0	55.4
0°-180°	6611.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1335	1335	1335	1335	1335	
5°	1336	1491	1341	1186	1336	127
15°	1255	1833	1273	880	1255	355
25°	1128	1527	1133	706	1128	516
35°	921	831	936	586	921	576
45°	691	501	702	481	691	536
55°	474	352	477	373	474	423
65°	281	217	286	252	281	280
75°	131	107	136	127	131	141
85°	27	28	29	20	27	31
90°	1	24	1	24	1	5
95°	59	39	59	39	59	70
105°	275	69	275	69	275	294
115°	520	74	520	74	520	512
125°	735	773	735	773	735	656
135°	910	939	910	939	910	703
145°	1055	1071	1055	1071	1055	660
155°	1162	1163	1162	1163	1162	535
165°	1224	1221	1224	1221	1224	346
175°	1252	1245	1252	1245	1252	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1342.4	1345.5	1350.7	1351.7	1361.9	1370.2	1379.4	1379.4	1382.5	1381.4	1373.2
5°	1336.3	1345.5	1358.9	1370.2	1388.6	1396.8	1409.2	1418.4	1426.6	1432.8	1431.7
7.5°	1326.0	1342.4	1361.9	1383.5	1408.1	1422.5	1440.0	1456.4	1467.7	1477.9	1485.1
10°	1308.6	1336.3	1363.0	1391.7	1423.5	1443.0	1463.6	1485.1	1502.6	1522.1	1540.5
12.5°	1285.0	1325.0	1357.8	1395.8	1434.8	1456.4	1489.2	1505.6	1539.5	1588.8	1602.1
15°	1255.2	1309.6	1340.4	1388.6	1440.0	1457.4	1502.6	1529.2	1599.0	1629.8	1666.8
17.5°	1227.5	1288.1	1329.1	1384.5	1434.8	1468.7	1512.8	1567.2	1625.7	1669.9	1710.9
20°	1204.9	1263.4	1312.7	1374.3	1437.9	1481.0	1527.2	1592.9	1656.5	1701.7	1733.5
22.5°	1153.6	1228.5	1286.0	1354.8	1431.7	1491.3	1535.4	1607.2	1676.0	1703.7	1731.4
25°	1127.9	1192.6	1259.3	1337.3	1427.6	1498.5	1536.4	1616.5	1677.0	1687.3	1693.5
27.5°	1080.7	1153.6	1231.6	1320.9	1426.6	1486.1	1534.4	1607.2	1655.5	1648.3	1629.8
30°	1022.2	1111.5	1197.7	1294.2	1412.2	1476.9	1522.1	1588.8	1613.4	1576.5	1543.6
32.5°	979.1	1063.3	1158.7	1270.6	1395.8	1457.4	1501.5	1553.9	1559.0	1492.3	1436.9
35°	920.6	1014.0	1121.8	1239.8	1368.1	1423.5	1464.6	1496.4	1471.8	1378.4	1312.7
37.5°	868.3	960.7	1075.6	1195.7	1330.1	1384.5	1417.4	1422.5	1361.9	1279.8	1183.4
40°	810.8	906.3	1026.3	1152.6	1288.1	1335.3	1355.8	1340.4	1253.2	1157.7	1045.8
42.5°	753.3	847.8	977.1	1106.4	1234.7	1274.7	1282.9	1240.8	1134.1	1022.2	892.9
45°	690.7	789.3	918.6	1048.9	1173.1	1195.7	1196.7	1136.2	1009.9	892.9	772.8
47.5°	639.4	730.8	859.0	989.4	1094.1	1109.5	1103.3	1033.5	896.0	764.6	659.9
50°	583.0	670.2	797.5	925.8	1015.0	1019.2	1003.8	904.2	769.8	649.7	566.5
52.5°	522.4	610.7	727.7	850.8	930.9	924.7	895.0	788.2	662.0	562.4	498.8
55°	474.2	552.2	662.0	782.1	838.5	821.1	788.2	679.4	579.9	495.7	440.3
57.5°	420.8	489.6	597.3	702.0	734.9	718.4	685.6	584.0	491.6	428.0	391.0
60°	370.5	433.1	527.5	614.8	640.4	623.0	585.0	493.7	427.0	373.6	345.9
62.5°	324.3	378.7	457.7	537.8	548.1	530.6	497.8	423.9	366.4	324.3	303.8
65°	281.2	332.5	396.2	456.7	466.0	447.5	413.6	360.2	312.0	285.3	265.8
67.5°	239.1	280.2	336.6	380.8	385.9	368.5	340.7	297.6	267.9	239.1	224.8
70°	202.2	233.0	277.1	313.0	315.1	298.7	284.3	245.3	222.7	202.2	190.9
72.5°	166.3	187.8	221.7	248.4	249.4	239.1	225.8	201.2	181.7	167.3	156.0
75°	131.4	149.8	170.4	194.0	193.0	184.7	174.5	159.1	142.7	133.4	128.3
77.5°	100.6	111.9	128.3	143.7	143.7	139.6	133.4	122.1	111.9	102.6	97.5
80°	71.8	79.0	92.4	97.5	99.6	98.5	93.4	85.2	81.1	73.9	71.8
82.5°	46.2	51.3	57.5	62.6	65.7	63.6	62.6	58.5	52.3	50.3	48.2
85°	26.7	28.7	31.8	34.9	35.9	34.9	36.9	33.9	30.8	30.8	29.8
87.5°	11.3	12.3	14.4	14.4	15.4	15.4	14.4	15.4	15.4	14.4	13.3
90°	0.9	3.1	5.3	7.5	9.7	10.8	11.6	13.2	14.9	16.5	18.1
92.5°	22.6	21.8	21.0	20.2	19.4	19.0	19.3	19.9	20.5	21.1	21.7
95°	58.8	52.2	45.5	38.9	32.2	28.9	29.6	31.0	32.5	33.9	35.3
97.5°	105.8	89.3	72.8	56.3	39.8	31.6	33.2	36.4	39.7	42.9	46.1
100°	160.0	132.5	105.0	77.5	50.0	36.2	37.9	41.3	44.7	48.1	51.5
102.5°	219.7	219.3	218.9	218.5	218.1	217.9	199.6	163.0	126.5	89.9	53.3
105°	274.8	280.8	286.9	292.9	299.0	302.0	274.6	219.7	164.8	110.0	55.1
107.5°	339.0	344.0	349.0	354.1	359.1	361.6	327.8	260.1	192.4	124.7	57.0
110°	400.5	404.7	408.9	413.2	417.4	419.5	390.5	332.4	274.3	216.3	158.2

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	458.4	462.0	465.6	469.2	472.8	474.6	472.9	469.5	466.1	462.7	459.3
115°	519.8	523.2	526.6	530.1	533.5	535.2	537.7	542.7	547.8	552.8	557.8
117.5°	573.2	577.2	581.2	585.2	589.2	591.2	592.9	596.3	599.8	603.2	606.6
120°	632.8	635.8	638.8	641.9	644.9	646.4	648.2	651.8	655.5	659.1	662.7
122.5°	683.5	686.7	689.9	693.1	696.3	697.9	699.9	703.9	708.0	712.0	716.0
125°	735.0	737.6	740.2	742.8	745.4	746.7	748.6	752.4	756.3	760.1	763.9
127.5°	782.0	784.8	787.6	790.5	793.3	794.7	796.2	799.2	802.2	805.2	808.2
130°	826.3	829.5	832.7	836.0	839.2	840.8	841.9	844.1	846.3	848.5	850.7
132.5°	871.5	874.1	876.7	879.4	882.0	883.3	884.4	886.6	888.8	891.0	893.2
135°	909.5	912.7	915.9	919.1	922.3	923.9	924.8	926.6	928.5	930.3	932.1
137.5°	949.3	951.7	954.1	956.5	958.9	960.1	961.1	963.1	965.1	967.1	969.1
140°	988.1	989.7	991.3	993.0	994.6	995.4	996.5	998.7	1000.9	1003.1	1005.3
142.5°	1020.7	1022.1	1023.5	1024.9	1026.3	1027.0	1028.3	1030.9	1033.6	1036.2	1038.8
145°	1055.0	1054.8	1054.6	1054.4	1054.2	1054.1	1055.8	1059.2	1062.7	1066.1	1069.5
147.5°	1084.9	1084.3	1083.7	1083.1	1082.5	1082.2	1083.9	1087.3	1090.7	1094.1	1097.5
150°	1113.8	1112.4	1111.0	1109.6	1108.2	1107.5	1109.1	1112.3	1115.5	1118.7	1121.9
152.5°	1138.2	1136.6	1135.0	1133.4	1131.8	1131.0	1132.5	1135.5	1138.5	1141.5	1144.5
155°	1161.7	1159.9	1158.1	1156.3	1154.5	1153.6	1154.8	1157.2	1159.6	1162.0	1164.4
157.5°	1180.7	1179.1	1177.5	1175.9	1174.3	1173.5	1174.4	1176.2	1178.0	1179.8	1181.6
160°	1197.0	1195.8	1194.6	1193.3	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0
162.5°	1211.4	1210.2	1209.0	1207.8	1206.6	1206.0	1206.5	1207.5	1208.5	1209.5	1210.5
165°	1224.1	1222.9	1221.7	1220.5	1219.3	1218.7	1219.0	1219.6	1220.2	1220.8	1221.4
167.5°	1234.0	1232.8	1231.6	1230.4	1229.2	1228.6	1228.9	1229.5	1230.1	1230.7	1231.3
170°	1242.2	1241.0	1239.8	1238.5	1237.3	1236.7	1236.9	1237.3	1237.8	1238.2	1238.6
172.5°	1247.6	1246.4	1245.2	1244.0	1242.8	1242.2	1242.4	1242.8	1243.2	1243.6	1244.0
175°	1252.1	1250.7	1249.3	1247.9	1246.5	1245.8	1246.0	1246.4	1246.8	1247.2	1247.6
177.5°	1253.9	1252.5	1251.1	1249.7	1248.3	1247.6	1247.7	1247.9	1248.1	1248.3	1248.5
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1387.6	1388.6	1390.7	1400.9	1406.1	1407.1	1403.0	1412.2	1415.3	1412.2	1410.2
5°	1453.3	1459.5	1471.8	1485.1	1484.1	1485.1	1491.3	1497.4	1499.5	1491.3	1494.3
7.5°	1510.8	1523.1	1536.4	1557.0	1557.0	1567.2	1571.3	1576.5	1588.8	1582.6	1580.6
10°	1576.5	1592.9	1617.5	1650.3	1651.4	1661.6	1671.9	1688.3	1693.5	1689.4	1691.4
12.5°	1658.6	1690.4	1692.4	1728.4	1744.8	1746.8	1763.2	1760.2	1770.4	1770.4	1787.9
15°	1694.5	1743.7	1771.5	1806.4	1816.6	1804.3	1817.6	1832.0	1833.0	1833.0	1832.0
17.5°	1759.1	1778.6	1806.4	1824.8	1828.9	1828.9	1830.0	1836.1	1832.0	1823.8	1830.0
20°	1772.5	1780.7	1791.0	1788.9	1791.0	1780.7	1770.4	1760.2	1761.2	1756.1	1771.5
22.5°	1747.9	1745.8	1722.2	1706.8	1706.8	1686.3	1666.8	1657.5	1648.3	1651.4	1656.5
25°	1686.3	1654.5	1625.7	1603.1	1598.0	1565.2	1538.5	1530.3	1514.9	1527.2	1529.2
27.5°	1587.7	1551.8	1505.6	1486.1	1459.5	1446.1	1427.6	1403.0	1371.2	1389.7	1386.6
30°	1482.0	1428.7	1390.7	1343.5	1301.4	1298.3	1263.4	1222.4	1205.9	1205.9	1215.2
32.5°	1364.0	1293.2	1237.8	1171.1	1130.0	1112.5	1070.5	1029.4	1038.7	1007.9	1019.2
35°	1226.5	1133.1	1063.3	998.6	967.8	947.3	892.9	870.3	845.7	831.3	858.0
37.5°	1095.1	987.3	898.0	827.2	815.9	779.0	742.0	727.7	713.3	719.5	718.4
40°	935.0	839.5	759.5	704.1	684.6	667.1	642.5	625.0	615.8	620.9	622.0
42.5°	790.3	710.2	650.7	611.7	595.3	583.0	570.6	556.3	553.2	553.2	557.3
45°	678.4	612.7	572.7	540.9	531.6	522.4	513.2	507.0	505.0	500.9	503.9
47.5°	589.1	536.8	512.1	488.5	478.3	476.2	468.0	464.9	460.8	459.8	460.8
50°	514.2	481.4	458.8	445.4	438.2	435.2	431.1	424.9	422.9	428.0	425.9
52.5°	461.9	431.1	418.7	405.4	401.3	397.2	391.0	392.1	391.0	389.0	389.0
55°	409.5	390.0	377.7	367.4	366.4	362.3	357.2	355.1	354.1	352.0	355.1
57.5°	367.4	352.0	340.7	331.5	327.4	327.4	322.3	318.2	318.2	317.1	318.2
60°	325.3	310.0	302.8	293.5	290.5	289.4	286.3	284.3	281.2	281.2	281.2
62.5°	286.3	274.0	265.8	257.6	258.6	253.5	249.4	247.3	247.3	248.4	248.4
65°	249.4	241.2	230.9	223.7	221.7	220.7	218.6	217.6	214.5	216.6	216.6
67.5°	215.5	204.2	198.1	195.0	191.9	190.9	188.8	186.8	185.8	184.7	186.8
70°	181.7	172.4	167.3	165.2	162.2	161.1	160.1	157.0	158.1	159.1	160.1
72.5°	150.9	142.7	141.6	135.5	135.5	135.5	131.4	133.4	132.4	130.3	132.4
75°	119.1	114.9	112.9	109.8	110.8	109.8	108.8	105.7	105.7	106.7	107.8
77.5°	94.4	90.3	89.3	86.2	84.2	86.2	84.2	83.1	83.1	84.2	84.2
80°	69.8	67.7	64.7	64.7	64.7	63.6	63.6	63.6	62.6	61.6	62.6
82.5°	46.2	46.2	45.2	44.1	45.2	43.1	44.1	44.1	44.1	44.1	44.1
85°	29.8	28.7	28.7	27.7	27.7	27.7	28.7	26.7	26.7	27.7	27.7
87.5°	13.3	13.3	13.3	14.4	13.3	13.3	13.3	14.4	13.3	13.3	13.3
90°	19.1	20.1	21.1	22.1	22.6	22.8	23.2	23.6	24.0	24.4	24.0
92.5°	22.1	22.5	22.9	23.3	23.5	23.6	23.8	24.0	24.2	24.4	24.2
95°	36.3	37.3	38.3	39.3	39.8	39.7	39.5	39.3	39.1	38.9	39.1
97.5°	46.7	47.3	47.9	48.5	48.8	48.9	49.1	49.3	49.5	49.7	49.5
100°	53.1	54.7	56.4	58.0	58.8	59.0	59.4	59.8	60.2	60.6	60.2
102.5°	55.5	57.7	60.0	62.2	63.3	63.6	64.2	64.8	65.4	66.0	65.4
105°	57.3	59.5	61.8	64.0	65.1	65.5	66.3	67.1	67.9	68.7	67.9
107.5°	59.2	61.4	63.6	65.8	66.9	67.3	68.1	68.9	69.7	70.5	69.7
110°	138.1	118.0	97.9	77.8	67.8	68.2	69.0	69.8	70.6	71.4	70.6

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	372.7	286.1	199.5	112.9	69.6	69.9	70.5	71.1	71.7	72.3	71.7
115°	464.8	371.8	278.7	185.7	139.2	132.0	117.5	103.0	88.6	74.1	88.6
117.5°	577.9	549.1	520.4	491.7	477.3	451.0	398.4	345.7	293.1	240.5	293.1
120°	665.1	667.5	669.9	672.3	673.5	659.9	632.8	605.7	578.6	551.5	578.6
122.5°	717.2	718.4	719.6	720.8	721.4	721.5	721.7	721.9	722.1	722.3	722.1
125°	765.3	766.7	768.2	769.6	770.3	770.6	771.2	771.8	772.4	773.0	772.4
127.5°	810.2	812.2	814.3	816.3	817.3	817.4	817.6	817.8	818.0	818.2	818.0
130°	852.9	855.1	857.4	859.6	860.7	860.6	860.4	860.2	860.0	859.8	860.0
132.5°	895.0	896.8	898.6	900.4	901.3	901.2	901.0	900.8	900.6	900.4	900.6
135°	934.1	936.1	938.1	940.1	941.1	940.9	940.5	940.1	939.7	939.3	939.7
137.5°	971.1	973.1	975.2	977.2	978.2	977.9	977.3	976.7	976.1	975.5	976.1
140°	1007.1	1008.9	1010.7	1012.5	1013.4	1012.9	1011.9	1010.9	1009.9	1008.9	1009.9
142.5°	1040.4	1042.0	1043.6	1045.2	1046.0	1045.5	1044.5	1043.5	1042.5	1041.5	1042.5
145°	1070.9	1072.3	1073.7	1075.1	1075.8	1075.3	1074.3	1073.3	1072.3	1071.3	1072.3
147.5°	1098.5	1099.5	1100.5	1101.5	1102.0	1101.6	1100.8	1100.0	1099.2	1098.4	1099.2
150°	1123.1	1124.3	1125.6	1126.8	1127.4	1126.9	1125.9	1124.8	1123.8	1122.8	1123.8
152.5°	1145.7	1146.9	1148.2	1149.4	1150.0	1149.3	1147.9	1146.4	1145.0	1143.6	1145.0
155°	1165.6	1166.8	1168.0	1169.2	1169.8	1169.0	1167.4	1165.8	1164.2	1162.6	1164.2
157.5°	1183.0	1184.4	1185.8	1187.2	1187.9	1187.1	1185.5	1183.9	1182.3	1180.7	1182.3
160°	1198.2	1199.4	1200.6	1201.8	1202.4	1201.7	1200.3	1198.9	1197.5	1196.1	1197.5
162.5°	1211.9	1213.3	1214.8	1216.2	1216.9	1216.0	1214.2	1212.3	1210.5	1208.7	1210.5
165°	1222.8	1224.2	1225.6	1227.0	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1222.8
167.5°	1232.7	1234.1	1235.5	1236.9	1237.6	1236.7	1234.9	1233.1	1231.3	1229.5	1231.3
170°	1240.0	1241.4	1242.8	1244.2	1244.9	1244.0	1242.2	1240.3	1238.5	1236.7	1238.5
172.5°	1245.4	1246.8	1248.2	1249.6	1250.3	1249.4	1247.6	1245.8	1244.0	1242.2	1244.0
175°	1249.0	1250.4	1251.8	1253.2	1253.9	1252.9	1250.9	1248.9	1246.9	1244.9	1246.9
177.5°	1249.9	1251.3	1252.7	1254.1	1254.8	1253.9	1252.1	1250.3	1248.5	1246.7	1248.5
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1415.3	1408.1	1402.0	1403.0	1408.1	1404.0	1393.8	1380.4	1375.3	1369.1	1375.3
5°	1500.5	1494.3	1482.0	1483.1	1480.0	1475.9	1459.5	1438.9	1438.9	1422.5	1420.5
7.5°	1584.7	1575.4	1567.2	1565.2	1553.9	1545.7	1531.3	1502.6	1491.3	1471.8	1460.5
10°	1679.1	1671.9	1662.7	1651.4	1645.2	1630.8	1607.2	1565.2	1544.6	1518.0	1498.5
12.5°	1774.5	1773.5	1753.0	1730.4	1729.4	1706.8	1690.4	1633.9	1606.2	1570.3	1524.1
15°	1835.1	1830.0	1818.7	1807.4	1810.5	1785.8	1748.9	1682.2	1663.7	1620.6	1571.3
17.5°	1834.1	1834.1	1831.0	1828.9	1825.9	1818.7	1798.1	1754.0	1724.2	1669.9	1623.7
20°	1775.6	1788.9	1792.0	1791.0	1801.2	1806.4	1805.3	1777.6	1754.0	1705.8	1658.6
22.5°	1658.6	1689.4	1702.7	1710.9	1732.5	1743.7	1770.4	1760.2	1754.0	1718.1	1678.1
25°	1549.8	1560.0	1600.1	1602.1	1631.9	1659.6	1686.3	1703.7	1726.3	1713.0	1679.1
27.5°	1409.2	1432.8	1461.5	1483.1	1489.2	1545.7	1589.8	1622.6	1674.0	1678.1	1666.8
30°	1250.1	1261.4	1308.6	1337.3	1370.2	1411.2	1474.8	1531.3	1577.5	1619.6	1633.9
32.5°	1056.1	1102.3	1130.0	1164.9	1193.6	1266.5	1344.5	1417.4	1470.7	1541.6	1572.3
35°	878.5	914.5	961.7	976.0	1028.4	1090.0	1191.6	1285.0	1366.1	1437.9	1500.5
37.5°	731.8	760.5	810.8	833.4	864.2	943.2	1028.4	1144.4	1241.9	1330.1	1408.1
40°	631.2	652.8	690.7	697.9	723.6	795.4	864.2	973.0	1102.3	1221.3	1306.5
42.5°	562.4	572.7	598.4	607.6	624.0	672.3	733.8	836.5	956.5	1079.7	1199.8
45°	513.2	520.4	535.7	544.0	564.5	586.0	636.3	718.4	812.9	937.0	1066.4
47.5°	469.0	478.3	484.4	489.6	500.9	524.5	557.3	617.9	708.2	822.1	947.3
50°	432.1	435.2	446.5	447.5	454.7	470.1	500.9	537.8	609.6	702.0	823.1
52.5°	395.1	398.2	405.4	412.6	415.7	428.0	448.5	479.3	532.7	605.5	713.3
55°	358.2	362.3	369.5	374.6	377.7	388.0	400.3	430.0	472.1	523.4	611.7
57.5°	321.2	330.5	332.5	335.6	340.7	352.0	363.3	380.8	413.6	460.8	525.5
60°	286.3	289.4	296.6	299.7	304.8	311.0	325.3	338.7	362.3	399.2	457.7
62.5°	250.4	257.6	260.7	263.8	267.9	275.1	284.3	298.7	319.2	349.0	395.1
65°	219.6	220.7	226.8	230.9	235.0	240.2	249.4	262.7	275.1	302.8	336.6
67.5°	189.9	191.9	194.0	198.1	203.2	208.3	216.6	223.7	239.1	257.6	284.3
70°	161.1	161.1	166.3	169.3	168.3	174.5	180.6	188.8	200.1	217.6	239.1
72.5°	135.5	134.5	138.6	139.6	141.6	145.7	149.8	158.1	164.2	177.6	194.0
75°	107.8	109.8	111.9	111.9	114.9	118.0	122.1	126.2	133.4	141.6	154.0
77.5°	85.2	85.2	87.2	88.3	91.3	90.3	94.4	98.5	103.7	110.8	120.1
80°	62.6	64.7	64.7	64.7	65.7	66.7	70.8	73.9	77.0	82.1	86.2
82.5°	44.1	44.1	46.2	46.2	46.2	48.2	48.2	49.3	51.3	54.4	57.5
85°	27.7	27.7	27.7	28.7	27.7	28.7	30.8	29.8	30.8	32.8	32.8
87.5°	13.3	13.3	13.3	13.3	13.3	14.4	13.3	14.4	15.4	15.4	15.4
90°	23.6	23.2	22.8	22.6	22.1	21.1	20.1	19.1	18.1	16.5	14.9
92.5°	24.0	23.8	23.6	23.5	23.3	22.9	22.5	22.1	21.7	21.1	20.5
95°	39.3	39.5	39.7	39.8	39.3	38.3	37.3	36.3	35.3	33.9	32.5
97.5°	49.3	49.1	48.9	48.8	48.5	47.9	47.3	46.7	46.1	42.9	39.7
100°	59.8	59.4	59.0	58.8	58.0	56.4	54.7	53.1	51.5	48.1	44.7
102.5°	64.8	64.2	63.6	63.3	62.2	60.0	57.7	55.5	53.3	49.9	46.5
105°	67.1	66.3	65.5	65.1	64.0	61.8	59.5	57.3	55.1	51.0	47.8
107.5°	68.9	68.1	67.3	66.9	65.8	63.6	61.4	59.2	57.0	52.7	49.5
110°	69.8	69.0	68.2	67.8	77.8	97.9	118.0	138.1	158.2	216.3	274.3

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	71.1	70.5	69.9	69.6	112.9	199.5	286.1	372.7	459.3	462.7	466.1
115°	103.0	117.5	132.0	139.2	185.7	278.7	371.8	464.8	557.8	552.8	547.8
117.5°	345.7	398.4	451.0	477.3	491.7	520.4	549.1	577.9	606.6	603.2	599.8
120°	605.7	632.8	659.9	673.5	672.3	669.9	667.5	665.1	662.7	659.1	655.5
122.5°	721.9	721.7	721.5	721.4	720.8	719.6	718.4	717.2	716.0	712.0	708.0
125°	771.8	771.2	770.6	770.3	769.6	768.2	766.7	765.3	763.9	760.1	756.3
127.5°	817.8	817.6	817.4	817.3	816.3	814.3	812.2	810.2	808.2	805.2	802.2
130°	860.2	860.4	860.6	860.7	859.6	857.4	855.1	852.9	850.7	848.5	846.3
132.5°	900.8	901.0	901.2	901.3	900.4	898.6	896.8	895.0	893.2	891.0	888.8
135°	940.1	940.5	940.9	941.1	940.1	938.1	936.1	934.1	932.1	930.3	928.5
137.5°	976.7	977.3	977.9	978.2	977.2	975.2	973.1	971.1	969.1	967.1	965.1
140°	1010.9	1011.9	1012.9	1013.4	1012.5	1010.7	1008.9	1007.1	1005.3	1003.1	1000.9
142.5°	1043.5	1044.5	1045.5	1046.0	1045.2	1043.6	1042.0	1040.4	1038.8	1036.2	1033.6
145°	1073.3	1074.3	1075.3	1075.8	1075.1	1073.7	1072.3	1070.9	1069.5	1066.1	1062.7
147.5°	1100.0	1100.8	1101.6	1102.0	1101.5	1100.5	1099.5	1098.5	1097.5	1094.1	1090.7
150°	1124.8	1125.9	1126.9	1127.4	1126.8	1125.6	1124.3	1123.1	1121.9	1118.7	1115.5
152.5°	1146.4	1147.9	1149.3	1150.0	1149.4	1148.2	1146.9	1145.7	1144.5	1141.5	1138.5
155°	1165.8	1167.4	1169.0	1169.8	1169.2	1168.0	1166.8	1165.6	1164.4	1162.0	1159.6
157.5°	1183.9	1185.5	1187.1	1187.9	1187.2	1185.8	1184.4	1183.0	1181.6	1179.8	1178.0
160°	1198.9	1200.3	1201.7	1202.4	1201.8	1200.6	1199.4	1198.2	1197.0	1195.8	1194.6
162.5°	1212.3	1214.2	1216.0	1216.9	1216.2	1214.8	1213.3	1211.9	1210.5	1209.5	1208.5
165°	1224.2	1225.6	1227.0	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1220.8	1220.2
167.5°	1233.1	1234.9	1236.7	1237.6	1236.9	1235.5	1234.1	1232.7	1231.3	1230.7	1230.1
170°	1240.3	1242.2	1244.0	1244.9	1244.2	1242.8	1241.4	1240.0	1238.6	1238.2	1237.8
172.5°	1245.8	1247.6	1249.4	1250.3	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2
175°	1248.9	1250.9	1252.9	1253.9	1253.2	1251.8	1250.4	1249.0	1247.6	1247.2	1246.8
177.5°	1250.3	1252.1	1253.9	1254.8	1254.1	1252.7	1251.3	1249.9	1248.5	1248.3	1248.1
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1370.2	1365.0	1361.9	1364.0	1357.8	1342.4	1342.4	1347.6	1341.4	1335.3	1326.0
5°	1408.1	1397.9	1391.7	1390.7	1376.3	1351.7	1346.6	1341.4	1328.1	1313.7	1298.3
7.5°	1445.1	1426.6	1416.3	1409.2	1388.6	1356.8	1343.5	1332.2	1310.6	1289.1	1269.6
10°	1475.9	1449.2	1436.9	1425.6	1398.9	1358.9	1337.3	1316.8	1289.1	1261.4	1236.7
12.5°	1500.5	1469.7	1454.3	1437.9	1405.1	1352.7	1326.0	1293.2	1265.5	1228.5	1203.9
15°	1541.6	1477.9	1463.6	1448.2	1414.3	1342.4	1309.6	1272.7	1234.7	1185.4	1158.7
17.5°	1574.4	1489.2	1488.2	1455.3	1411.2	1338.3	1288.1	1239.8	1198.8	1149.5	1107.4
20°	1593.9	1506.7	1490.2	1456.4	1400.9	1310.6	1258.3	1204.9	1160.8	1101.3	1059.2
22.5°	1610.3	1531.3	1488.2	1447.1	1379.4	1301.4	1224.4	1174.1	1113.6	1048.9	1008.9
25°	1616.5	1536.4	1491.3	1444.1	1364.0	1274.7	1187.5	1133.1	1065.3	1006.8	952.4
27.5°	1617.5	1535.4	1480.0	1430.7	1342.4	1239.8	1150.5	1093.0	1018.1	950.4	896.0
30°	1607.2	1524.1	1473.8	1420.5	1321.9	1208.0	1105.4	1041.7	961.7	893.9	837.5
32.5°	1576.5	1501.5	1460.5	1402.0	1295.2	1163.9	1062.3	991.4	907.3	840.6	786.2
35°	1525.1	1473.8	1428.7	1374.3	1260.3	1122.8	1019.2	936.0	850.8	787.2	735.9
37.5°	1461.5	1433.8	1391.7	1338.3	1220.3	1085.9	970.9	878.5	793.4	731.8	681.5
40°	1375.3	1382.5	1341.4	1293.2	1173.1	1035.6	908.3	820.0	740.0	682.5	633.2
42.5°	1281.9	1311.7	1288.1	1241.9	1120.8	980.2	862.1	764.6	686.6	627.1	586.0
45°	1181.3	1232.6	1218.3	1184.4	1066.4	921.7	796.4	702.0	633.2	575.8	539.9
47.5°	1071.5	1144.4	1144.4	1119.7	1005.8	863.1	740.0	643.5	575.8	534.7	499.8
50°	959.6	1041.7	1055.1	1038.7	938.1	796.4	671.2	584.0	525.5	485.5	459.8
52.5°	842.6	938.1	962.7	954.5	866.2	732.8	614.8	529.6	476.2	441.3	418.7
55°	730.8	841.6	868.3	871.4	789.3	663.0	552.2	477.2	425.9	402.3	382.8
57.5°	625.0	731.8	761.5	766.7	711.3	599.4	493.7	428.0	381.8	362.3	346.9
60°	534.7	624.0	663.0	674.3	626.1	525.5	439.3	375.6	340.7	322.3	307.9
62.5°	460.8	532.7	573.7	576.8	555.2	460.8	382.8	329.5	299.7	283.3	276.1
65°	389.0	453.6	478.3	490.6	473.1	399.2	330.5	286.3	262.7	248.4	241.2
67.5°	331.5	372.6	393.1	409.5	392.1	336.6	281.2	245.3	227.8	213.5	209.4
70°	272.0	305.8	321.2	337.7	322.3	280.2	240.2	207.3	191.9	180.6	175.5
72.5°	217.6	244.3	258.6	268.9	259.7	224.8	191.9	169.3	158.1	149.8	146.8
75°	172.4	190.9	199.1	206.3	202.2	175.5	155.0	136.5	126.2	119.1	117.0
77.5°	131.4	144.7	154.0	156.0	150.9	133.4	116.0	104.7	96.5	92.4	90.3
80°	93.4	101.6	106.7	109.8	104.7	97.5	85.2	77.0	69.8	64.7	63.6
82.5°	62.6	66.7	70.8	69.8	67.7	61.6	54.4	50.3	47.2	43.1	43.1
85°	35.9	36.9	39.0	40.0	39.0	34.9	30.8	28.7	26.7	23.6	23.6
87.5°	15.4	16.4	16.4	17.4	15.4	15.4	13.3	11.3	11.3	10.3	9.2
90°	13.2	11.6	10.8	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.9	19.3	19.0	19.4	20.2	21.0	21.8	22.6	21.8	21.0	20.2
95°	31.0	29.6	28.9	32.2	38.9	45.5	52.2	58.8	52.2	45.5	38.9
97.5°	36.4	33.2	31.6	39.8	56.3	72.8	89.3	105.8	89.3	72.8	56.3
100°	41.3	37.9	36.2	50.0	77.5	105.0	132.5	160.0	132.5	105.0	77.5
102.5°	163.0	199.6	217.9	218.1	218.5	218.9	219.3	219.7	219.3	218.9	218.5
105°	219.7	274.6	302.0	299.0	292.9	286.9	280.8	274.8	280.8	286.9	292.9
107.5°	260.1	327.8	361.6	359.1	354.1	349.0	344.0	339.0	344.0	349.0	354.1
110°	332.4	390.5	419.5	417.4	413.2	408.9	404.7	400.5	404.7	408.9	413.2

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	469.5	472.9	474.6	472.8	469.2	465.6	462.0	458.4	462.0	465.6	469.2
115°	542.7	537.7	535.2	533.5	530.1	526.6	523.2	519.8	523.2	526.6	530.1
117.5°	596.3	592.9	591.2	589.2	585.2	581.2	577.2	573.2	577.2	581.2	585.2
120°	651.8	648.2	646.4	644.9	641.9	638.8	635.8	632.8	635.8	638.8	641.9
122.5°	703.9	699.9	697.9	696.3	693.1	689.9	686.7	683.5	686.7	689.9	693.1
125°	752.4	748.6	746.7	745.4	742.8	740.2	737.6	735.0	737.6	740.2	742.8
127.5°	799.2	796.2	794.7	793.3	790.5	787.6	784.8	782.0	784.8	787.6	790.5
130°	844.1	841.9	840.8	839.2	836.0	832.7	829.5	826.3	829.5	832.7	836.0
132.5°	886.6	884.4	883.3	882.0	879.4	876.7	874.1	871.5	874.1	876.7	879.4
135°	926.6	924.8	923.9	922.3	919.1	915.9	912.7	909.5	912.7	915.9	919.1
137.5°	963.1	961.1	960.1	958.9	956.5	954.1	951.7	949.3	951.7	954.1	956.5
140°	998.7	996.5	995.4	994.6	993.0	991.3	989.7	988.1	989.7	991.3	993.0
142.5°	1030.9	1028.3	1027.0	1026.3	1024.9	1023.5	1022.1	1020.7	1022.1	1023.5	1024.9
145°	1059.2	1055.8	1054.1	1054.2	1054.4	1054.6	1054.8	1055.0	1054.8	1054.6	1054.4
147.5°	1087.3	1083.9	1082.2	1082.5	1083.1	1083.7	1084.3	1084.9	1084.3	1083.7	1083.1
150°	1112.3	1109.1	1107.5	1108.2	1109.6	1111.0	1112.4	1113.8	1112.4	1111.0	1109.6
152.5°	1135.5	1132.5	1131.0	1131.8	1133.4	1135.0	1136.6	1138.2	1136.6	1135.0	1133.4
155°	1157.2	1154.8	1153.6	1154.5	1156.3	1158.1	1159.9	1161.7	1159.9	1158.1	1156.3
157.5°	1176.2	1174.4	1173.5	1174.3	1175.9	1177.5	1179.1	1180.7	1179.1	1177.5	1175.9
160°	1193.3	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0	1195.8	1194.6	1193.3
162.5°	1207.5	1206.5	1206.0	1206.6	1207.8	1209.0	1210.2	1211.4	1210.2	1209.0	1207.8
165°	1219.6	1219.0	1218.7	1219.3	1220.5	1221.7	1222.9	1224.1	1222.9	1221.7	1220.5
167.5°	1229.5	1228.9	1228.6	1229.2	1230.4	1231.6	1232.8	1234.0	1232.8	1231.6	1230.4
170°	1237.3	1236.9	1236.7	1237.3	1238.5	1239.8	1241.0	1242.2	1241.0	1239.8	1238.5
172.5°	1242.8	1242.4	1242.2	1242.8	1244.0	1245.2	1246.4	1247.6	1246.4	1245.2	1244.0
175°	1246.4	1246.0	1245.8	1246.5	1247.9	1249.3	1250.7	1252.1	1250.7	1249.3	1247.9
177.5°	1247.9	1247.7	1247.6	1248.3	1249.7	1251.1	1252.5	1253.9	1252.5	1251.1	1249.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1320.9	1326.0	1325.0	1314.7	1303.4	1294.2	1276.8	1278.8	1272.7	1273.7	1279.8
5°	1288.1	1288.1	1283.9	1269.6	1251.1	1240.8	1221.3	1216.2	1203.9	1202.9	1201.8
7.5°	1253.2	1248.0	1242.9	1222.4	1199.8	1183.4	1156.7	1150.5	1138.2	1130.0	1125.9
10°	1212.1	1204.9	1194.7	1171.1	1143.3	1122.8	1095.1	1086.9	1063.3	1053.0	1046.9
12.5°	1166.9	1162.8	1146.4	1126.9	1081.8	1059.2	1019.2	1027.4	1003.8	983.2	980.2
15°	1121.8	1106.4	1097.2	1065.3	1010.9	1000.7	968.9	952.4	930.9	914.5	914.5
17.5°	1077.7	1054.0	1033.5	999.7	959.6	930.9	907.3	899.1	872.4	856.0	852.9
20°	1019.2	992.5	987.3	939.1	911.4	879.6	857.0	836.5	817.0	809.8	804.6
22.5°	963.7	932.9	924.7	883.7	856.0	824.1	801.6	787.2	772.8	767.7	758.5
25°	904.2	885.7	873.4	829.3	798.5	768.7	753.3	743.1	729.7	728.7	722.5
27.5°	846.7	829.3	817.0	774.9	752.3	724.6	712.3	701.0	693.8	690.7	687.6
30°	797.5	778.0	763.6	732.8	705.1	682.5	672.3	665.1	661.0	655.8	654.8
32.5°	743.1	731.8	712.3	688.7	667.1	645.6	639.4	634.3	628.1	626.1	625.0
35°	696.9	681.5	669.2	642.5	633.2	614.8	607.6	603.5	595.3	593.2	591.2
37.5°	651.7	637.4	624.0	607.6	590.1	579.9	575.8	569.6	565.5	566.5	564.5
40°	606.6	595.3	585.0	567.6	557.3	552.2	544.0	537.8	535.7	536.8	535.7
42.5°	562.4	552.2	546.0	532.7	522.4	517.3	512.1	506.0	509.1	509.1	512.1
45°	522.4	513.2	509.1	498.8	492.6	484.4	479.3	478.3	482.4	481.4	481.4
47.5°	481.4	478.3	473.1	463.9	455.7	450.6	449.5	449.5	453.6	455.7	454.7
50°	449.5	443.4	437.2	430.0	423.9	421.8	418.7	420.8	424.9	424.9	427.0
52.5°	409.5	405.4	403.4	397.2	393.1	393.1	393.1	394.1	397.2	400.3	399.2
55°	374.6	371.5	369.5	366.4	361.3	362.3	361.3	363.3	366.4	369.5	371.5
57.5°	337.7	336.6	334.6	329.5	329.5	328.4	331.5	332.5	337.7	339.7	342.8
60°	304.8	301.7	301.7	297.6	297.6	297.6	300.7	303.8	307.9	308.9	311.0
62.5°	269.9	269.9	268.9	265.8	265.8	268.9	269.9	274.0	276.1	276.1	279.2
65°	237.1	236.1	235.0	236.1	237.1	237.1	240.2	242.2	244.3	245.3	246.3
67.5°	204.2	203.2	205.3	204.2	206.3	210.4	209.4	212.5	215.5	215.5	216.6
70°	173.5	175.5	174.5	176.5	175.5	177.6	180.6	181.7	181.7	182.7	185.8
72.5°	144.7	144.7	144.7	143.7	144.7	146.8	148.8	149.8	151.9	152.9	156.0
75°	117.0	117.0	114.9	117.0	117.0	119.1	121.1	121.1	121.1	123.2	126.2
77.5°	88.3	89.3	88.3	90.3	90.3	91.3	93.4	92.4	94.4	95.4	96.5
80°	64.7	63.6	63.6	63.6	64.7	64.7	66.7	67.7	67.7	70.8	68.8
82.5°	41.1	42.1	41.1	42.1	42.1	43.1	42.1	43.1	44.1	46.2	45.2
85°	23.6	22.6	22.6	23.6	22.6	22.6	23.6	22.6	23.6	22.6	23.6
87.5°	9.2	8.2	8.2	8.2	8.2	7.2	7.2	6.2	6.2	6.2	5.1
90°	9.7	10.8	11.6	13.2	14.9	16.5	18.1	19.1	20.1	21.1	22.1
92.5°	19.4	19.0	19.3	19.9	20.5	21.1	21.7	22.1	22.5	22.9	23.3
95°	32.2	28.9	29.6	31.0	32.5	33.9	35.3	36.3	37.3	38.3	39.3
97.5°	39.8	31.6	33.2	36.4	39.7	42.9	46.1	46.7	47.3	47.9	48.5
100°	50.0	36.2	37.9	41.3	44.7	48.1	51.5	53.1	54.7	56.4	58.0
102.5°	218.1	217.9	199.6	163.0	126.5	89.9	53.3	55.5	57.7	60.0	62.2
105°	299.0	302.0	274.6	219.7	164.8	110.0	55.1	57.3	59.5	61.8	64.0
107.5°	359.1	361.6	327.8	260.1	192.4	124.7	57.0	59.2	61.4	63.6	65.8
110°	417.4	419.5	390.5	332.4	274.3	216.3	158.2	138.1	118.0	97.9	77.8

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	472.8	474.6	472.9	469.5	466.1	462.7	459.3	372.7	286.1	199.5	112.9
115°	533.5	535.2	537.7	542.7	547.8	552.8	557.8	464.8	371.8	278.7	185.7
117.5°	589.2	591.2	592.9	596.3	599.8	603.2	606.6	577.9	549.1	520.4	491.7
120°	644.9	646.4	648.2	651.8	655.5	659.1	662.7	665.1	667.5	669.9	672.3
122.5°	696.3	697.9	699.9	703.9	708.0	712.0	716.0	717.2	718.4	719.6	720.8
125°	745.4	746.7	748.6	752.4	756.3	760.1	763.9	765.3	766.7	768.2	769.6
127.5°	793.3	794.7	796.2	799.2	802.2	805.2	808.2	810.2	812.2	814.3	816.3
130°	839.2	840.8	841.9	844.1	846.3	848.5	850.7	852.9	855.1	857.4	859.6
132.5°	882.0	883.3	884.4	886.6	888.8	891.0	893.2	895.0	896.8	898.6	900.4
135°	922.3	923.9	924.8	926.6	928.5	930.3	932.1	934.1	936.1	938.1	940.1
137.5°	958.9	960.1	961.1	963.1	965.1	967.1	969.1	971.1	973.1	975.2	977.2
140°	994.6	995.4	996.5	998.7	1000.9	1003.1	1005.3	1007.1	1008.9	1010.7	1012.5
142.5°	1026.3	1027.0	1028.3	1030.9	1033.6	1036.2	1038.8	1040.4	1042.0	1043.6	1045.2
145°	1054.2	1054.1	1055.8	1059.2	1062.7	1066.1	1069.5	1070.9	1072.3	1073.7	1075.1
147.5°	1082.5	1082.2	1083.9	1087.3	1090.7	1094.1	1097.5	1098.5	1099.5	1100.5	1101.5
150°	1108.2	1107.5	1109.1	1112.3	1115.5	1118.7	1121.9	1123.1	1124.3	1125.6	1126.8
152.5°	1131.8	1131.0	1132.5	1135.5	1138.5	1141.5	1144.5	1145.7	1146.9	1148.2	1149.4
155°	1154.5	1153.6	1154.8	1157.2	1159.6	1162.0	1164.4	1165.6	1166.8	1168.0	1169.2
157.5°	1174.3	1173.5	1174.4	1176.2	1178.0	1179.8	1181.6	1183.0	1184.4	1185.8	1187.2
160°	1192.1	1191.5	1192.1	1193.3	1194.6	1195.8	1197.0	1198.2	1199.4	1200.6	1201.8
162.5°	1206.6	1206.0	1206.5	1207.5	1208.5	1209.5	1210.5	1211.9	1213.3	1214.8	1216.2
165°	1219.3	1218.7	1219.0	1219.6	1220.2	1220.8	1221.4	1222.8	1224.2	1225.6	1227.0
167.5°	1229.2	1228.6	1228.9	1229.5	1230.1	1230.7	1231.3	1232.7	1234.1	1235.5	1236.9
170°	1237.3	1236.7	1236.9	1237.3	1237.8	1238.2	1238.6	1240.0	1241.4	1242.8	1244.2
172.5°	1242.8	1242.2	1242.4	1242.8	1243.2	1243.6	1244.0	1245.4	1246.8	1248.2	1249.6
175°	1246.5	1245.8	1246.0	1246.4	1246.8	1247.2	1247.6	1249.0	1250.4	1251.8	1253.2
177.5°	1248.3	1247.6	1247.7	1247.9	1248.1	1248.3	1248.5	1249.9	1251.3	1252.7	1254.1
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1272.7	1275.7	1268.6	1266.5	1268.6	1261.4	1263.4	1265.5	1265.5	1268.6	1270.6
5°	1198.8	1194.7	1187.5	1185.4	1183.4	1186.4	1184.4	1187.5	1188.5	1195.7	1196.7
7.5°	1125.9	1119.7	1113.6	1107.4	1105.4	1100.2	1105.4	1105.4	1112.5	1110.5	1115.6
10°	1039.7	1038.7	1030.4	1027.4	1023.3	1015.0	1026.3	1023.3	1028.4	1037.6	1039.7
12.5°	976.0	964.8	969.9	955.5	960.7	952.4	953.5	953.5	961.7	962.7	960.7
15°	915.5	906.3	892.9	886.8	883.7	879.6	892.9	893.9	887.8	902.2	897.0
17.5°	853.9	853.9	841.6	838.5	830.3	834.4	832.4	833.4	831.3	841.6	846.7
20°	800.5	795.4	791.3	792.3	782.1	780.0	778.0	780.0	787.2	794.4	796.4
22.5°	757.4	754.4	744.1	746.1	737.9	741.0	739.0	744.1	745.1	745.1	752.3
25°	716.4	712.3	713.3	709.2	706.1	706.1	703.0	706.1	710.2	712.3	713.3
27.5°	685.6	682.5	677.4	674.3	676.4	671.2	675.3	678.4	678.4	676.4	678.4
30°	648.6	650.7	650.7	640.4	644.5	642.5	645.6	647.6	647.6	648.6	646.6
32.5°	624.0	617.9	616.8	615.8	615.8	611.7	611.7	614.8	615.8	616.8	619.9
35°	591.2	591.2	586.0	589.1	585.0	586.0	585.0	586.0	588.1	585.0	588.1
37.5°	561.4	562.4	560.4	562.4	563.5	561.4	559.4	563.5	561.4	561.4	559.4
40°	535.7	534.7	535.7	535.7	535.7	536.8	534.7	534.7	534.7	532.7	530.6
42.5°	514.2	508.0	510.1	511.1	508.0	508.0	509.1	508.0	511.1	505.0	505.0
45°	483.4	481.4	482.4	482.4	484.4	481.4	483.4	484.4	481.4	480.3	478.3
47.5°	455.7	457.7	455.7	457.7	457.7	459.8	455.7	456.7	457.7	453.6	450.6
50°	428.0	428.0	431.1	430.0	431.1	429.0	429.0	428.0	429.0	427.0	423.9
52.5°	402.3	399.2	404.4	403.4	402.3	401.3	400.3	401.3	399.2	397.2	397.2
55°	370.5	370.5	373.6	374.6	374.6	372.6	370.5	371.5	370.5	369.5	368.5
57.5°	344.8	340.7	342.8	343.8	343.8	340.7	342.8	340.7	340.7	341.8	338.7
60°	312.0	312.0	310.0	313.0	313.0	311.0	311.0	312.0	310.0	308.9	307.9
62.5°	277.1	278.1	281.2	282.2	283.3	281.2	279.2	280.2	280.2	277.1	278.1
65°	247.3	249.4	253.5	252.5	250.4	251.5	249.4	250.4	247.3	248.4	245.3
67.5°	218.6	217.6	218.6	218.6	220.7	219.6	217.6	217.6	216.6	219.6	216.6
70°	187.8	187.8	187.8	187.8	188.8	189.9	187.8	185.8	186.8	184.7	183.7
72.5°	156.0	157.0	156.0	158.1	155.0	157.0	157.0	156.0	155.0	155.0	155.0
75°	126.2	128.3	125.2	126.2	125.2	127.3	126.2	126.2	124.2	123.2	124.2
77.5°	96.5	97.5	95.4	96.5	95.4	96.5	96.5	95.4	95.4	95.4	95.4
80°	68.8	69.8	68.8	67.7	66.7	68.8	66.7	67.7	68.8	67.7	69.8
82.5°	44.1	44.1	43.1	44.1	42.1	42.1	43.1	43.1	42.1	44.1	42.1
85°	21.6	21.6	23.6	21.6	20.5	20.5	20.5	21.6	20.5	22.6	21.6
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.2	4.1
90°	22.6	22.8	23.2	23.6	24.0	24.4	24.0	23.6	23.2	22.8	22.6
92.5°	23.5	23.6	23.8	24.0	24.2	24.4	24.2	24.0	23.8	23.6	23.5
95°	39.8	39.7	39.5	39.3	39.1	38.9	39.1	39.3	39.5	39.7	39.8
97.5°	48.8	48.9	49.1	49.3	49.5	49.7	49.5	49.3	49.1	48.9	48.8
100°	58.8	59.0	59.4	59.8	60.2	60.6	60.2	59.8	59.4	59.0	58.8
102.5°	63.3	63.6	64.2	64.8	65.4	66.0	65.4	64.8	64.2	63.6	63.3
105°	65.1	65.5	66.3	67.1	67.9	68.7	67.9	67.1	66.3	65.5	65.1
107.5°	66.9	67.3	68.1	68.9	69.7	70.5	69.7	68.9	68.1	67.3	66.9
110°	67.8	68.2	69.0	69.8	70.6	71.4	70.6	69.8	69.0	68.2	67.8

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.6	69.9	70.5	71.1	71.7	72.3	71.7	71.1	70.5	69.9	69.6
115°	139.2	132.0	117.5	103.0	88.6	74.1	88.6	103.0	117.5	132.0	139.2
117.5°	477.3	451.0	398.4	345.7	293.1	240.5	293.1	345.7	398.4	451.0	477.3
120°	673.5	659.9	632.8	605.7	578.6	551.5	578.6	605.7	632.8	659.9	673.5
122.5°	721.4	721.5	721.7	721.9	722.1	722.3	722.1	721.9	721.7	721.5	721.4
125°	770.3	770.6	771.2	771.8	772.4	773.0	772.4	771.8	771.2	770.6	770.3
127.5°	817.3	817.4	817.6	817.8	818.0	818.2	818.0	817.8	817.6	817.4	817.3
130°	860.7	860.6	860.4	860.2	860.0	859.8	860.0	860.2	860.4	860.6	860.7
132.5°	901.3	901.2	901.0	900.8	900.6	900.4	900.6	900.8	901.0	901.2	901.3
135°	941.1	940.9	940.5	940.1	939.7	939.3	939.7	940.1	940.5	940.9	941.1
137.5°	978.2	977.9	977.3	976.7	976.1	975.5	976.1	976.7	977.3	977.9	978.2
140°	1013.4	1012.9	1011.9	1010.9	1009.9	1008.9	1009.9	1010.9	1011.9	1012.9	1013.4
142.5°	1046.0	1045.5	1044.5	1043.5	1042.5	1041.5	1042.5	1043.5	1044.5	1045.5	1046.0
145°	1075.8	1075.3	1074.3	1073.3	1072.3	1071.3	1072.3	1073.3	1074.3	1075.3	1075.8
147.5°	1102.0	1101.6	1100.8	1100.0	1099.2	1098.4	1099.2	1100.0	1100.8	1101.6	1102.0
150°	1127.4	1126.9	1125.9	1124.8	1123.8	1122.8	1123.8	1124.8	1125.9	1126.9	1127.4
152.5°	1150.0	1149.3	1147.9	1146.4	1145.0	1143.6	1145.0	1146.4	1147.9	1149.3	1150.0
155°	1169.8	1169.0	1167.4	1165.8	1164.2	1162.6	1164.2	1165.8	1167.4	1169.0	1169.8
157.5°	1187.9	1187.1	1185.5	1183.9	1182.3	1180.7	1182.3	1183.9	1185.5	1187.1	1187.9
160°	1202.4	1201.7	1200.3	1198.9	1197.5	1196.1	1197.5	1198.9	1200.3	1201.7	1202.4
162.5°	1216.9	1216.0	1214.2	1212.3	1210.5	1208.7	1210.5	1212.3	1214.2	1216.0	1216.9
165°	1227.7	1227.0	1225.6	1224.2	1222.8	1221.4	1222.8	1224.2	1225.6	1227.0	1227.7
167.5°	1237.6	1236.7	1234.9	1233.1	1231.3	1229.5	1231.3	1233.1	1234.9	1236.7	1237.6
170°	1244.9	1244.0	1242.2	1240.3	1238.5	1236.7	1238.5	1240.3	1242.2	1244.0	1244.9
172.5°	1250.3	1249.4	1247.6	1245.8	1244.0	1242.2	1244.0	1245.8	1247.6	1249.4	1250.3
175°	1253.9	1252.9	1250.9	1248.9	1246.9	1244.9	1246.9	1248.9	1250.9	1252.9	1253.9
177.5°	1254.8	1253.9	1252.1	1250.3	1248.5	1246.7	1248.5	1250.3	1252.1	1253.9	1254.8
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3	1335.3
2.5°	1267.5	1275.7	1272.7	1261.4	1274.7	1274.7	1283.9	1283.9	1295.2	1299.3	1305.5
5°	1195.7	1201.8	1207.0	1201.8	1211.1	1225.4	1233.7	1240.8	1256.2	1262.4	1271.6
7.5°	1118.7	1130.0	1135.1	1135.1	1150.5	1166.9	1183.4	1193.6	1215.2	1223.4	1232.6
10°	1043.8	1057.1	1067.4	1066.4	1092.0	1102.3	1122.8	1146.4	1168.0	1180.3	1193.6
12.5°	964.8	971.9	986.3	1006.8	1013.0	1031.5	1055.1	1084.8	1123.8	1135.1	1154.6
15°	899.1	918.6	929.9	939.1	953.5	970.9	996.6	1025.3	1064.3	1088.9	1109.5
17.5°	843.6	869.3	876.5	874.4	892.9	919.6	949.4	970.9	1005.8	1035.6	1055.1
20°	798.5	808.8	821.1	826.2	840.6	869.3	898.0	922.7	951.4	975.0	997.6
22.5°	753.3	761.5	771.8	781.0	792.3	808.8	836.5	867.3	895.0	917.5	943.2
25°	716.4	721.5	730.8	737.9	750.3	761.5	781.0	814.9	847.8	861.1	883.7
27.5°	680.5	684.6	690.7	698.9	705.1	716.4	733.8	761.5	795.4	808.8	839.5
30°	648.6	651.7	657.9	662.0	665.1	678.4	691.8	713.3	739.0	757.4	780.0
32.5°	618.9	622.0	628.1	629.1	633.2	640.4	652.8	672.3	694.8	710.2	729.7
35°	586.0	588.1	594.2	596.3	599.4	605.5	614.8	629.1	649.7	661.0	678.4
37.5°	560.4	559.4	563.5	566.5	570.6	573.7	576.8	591.2	606.6	616.8	630.2
40°	532.7	530.6	531.6	535.7	537.8	541.9	541.9	556.3	566.5	574.7	585.0
42.5°	505.0	503.9	501.9	503.9	506.0	507.0	508.0	518.3	528.6	535.7	547.0
45°	477.2	476.2	474.2	475.2	475.2	477.2	480.3	484.4	491.6	497.8	503.9
47.5°	451.6	449.5	446.5	445.4	447.5	447.5	447.5	451.6	458.8	460.8	467.0
50°	424.9	421.8	417.7	415.7	415.7	414.6	416.7	417.7	423.9	425.9	431.1
52.5°	396.2	394.1	390.0	385.9	386.9	384.9	385.9	386.9	389.0	392.1	395.1
55°	367.4	363.3	360.2	359.2	356.1	356.1	353.1	357.2	356.1	357.2	361.3
57.5°	339.7	335.6	330.5	328.4	325.3	324.3	322.3	321.2	322.3	325.3	328.4
60°	306.9	304.8	301.7	298.7	296.6	293.5	291.5	291.5	290.5	290.5	291.5
62.5°	275.1	274.0	269.9	268.9	266.8	264.8	261.7	259.7	259.7	261.7	262.7
65°	244.3	243.2	240.2	239.1	234.0	232.0	230.9	229.9	227.8	227.8	227.8
67.5°	215.5	212.5	212.5	207.3	203.2	201.2	199.1	198.1	198.1	198.1	199.1
70°	183.7	183.7	180.6	177.6	173.5	174.5	171.4	168.3	168.3	166.3	167.3
72.5°	152.9	151.9	148.8	147.8	144.7	141.6	139.6	141.6	138.6	137.5	138.6
75°	123.2	122.1	120.1	118.0	119.1	116.0	112.9	111.9	111.9	109.8	109.8
77.5°	94.4	96.5	92.4	91.3	89.3	87.2	86.2	85.2	85.2	85.2	87.2
80°	65.7	66.7	66.7	64.7	65.7	62.6	62.6	62.6	59.5	60.6	61.6
82.5°	42.1	42.1	41.1	42.1	41.1	41.1	40.0	40.0	39.0	39.0	40.0
85°	23.6	22.6	21.6	23.6	22.6	22.6	21.6	21.6	21.6	21.6	21.6
87.5°	5.1	6.2	6.2	6.2	6.2	7.2	7.2	7.2	8.2	8.2	8.2
90°	22.1	21.1	20.1	19.1	18.1	16.5	14.9	13.2	11.6	10.8	9.7
92.5°	23.3	22.9	22.5	22.1	21.7	21.1	20.5	19.9	19.3	19.0	19.4
95°	39.3	38.3	37.3	36.3	35.3	33.9	32.5	31.0	29.6	28.9	32.2
97.5°	48.5	47.9	47.3	46.7	46.1	42.9	39.7	36.4	33.2	31.6	39.8
100°	58.0	56.4	54.7	53.1	51.5	48.1	44.7	41.3	37.9	36.2	50.0
102.5°	62.2	60.0	57.7	55.5	53.3	49.9	46.5	43.0	39.6	38.1	53.6
105°	64.0	61.8	59.5	57.3	55.1	51.0	47.8	44.6	41.4	39.2	55.0
107.5°	65.8	63.6	61.4	59.2	57.0	52.7	49.5	46.3	43.1	40.9	56.8
110°	77.8	97.9	118.0	138.1	158.2	216.3	274.3	332.4	390.5	419.5	417.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	112.9	199.5	286.1	372.7	459.3	462.7	466.1	469.5	472.9	474.6	472.8
115°	185.7	278.7	371.8	464.8	557.8	552.8	547.8	542.7	537.7	535.2	533.5
117.5°	491.7	520.4	549.1	577.9	606.6	603.2	599.8	596.3	592.9	591.2	589.2
120°	672.3	669.9	667.5	665.1	662.7	659.1	655.5	651.8	648.2	646.4	644.9
122.5°	720.8	719.6	718.4	717.2	716.0	712.0	708.0	703.9	699.9	697.9	696.3
125°	769.6	768.2	766.7	765.3	763.9	760.1	756.3	752.4	748.6	746.7	745.4
127.5°	816.3	814.3	812.2	810.2	808.2	805.2	802.2	799.2	796.2	794.7	793.3
130°	859.6	857.4	855.1	852.9	850.7	848.5	846.3	844.1	841.9	840.8	839.2
132.5°	900.4	898.6	896.8	895.0	893.2	891.0	888.8	886.6	884.4	883.3	882.0
135°	940.1	938.1	936.1	934.1	932.1	930.3	928.5	926.6	924.8	923.9	922.3
137.5°	977.2	975.2	973.1	971.1	969.1	967.1	965.1	963.1	961.1	960.1	958.9
140°	1012.5	1010.7	1008.9	1007.1	1005.3	1003.1	1000.9	998.7	996.5	995.4	994.6
142.5°	1045.2	1043.6	1042.0	1040.4	1038.8	1036.2	1033.6	1030.9	1028.3	1027.0	1026.3
145°	1075.1	1073.7	1072.3	1070.9	1069.5	1066.1	1062.7	1059.2	1055.8	1054.1	1054.2
147.5°	1101.5	1100.5	1099.5	1098.5	1097.5	1094.1	1090.7	1087.3	1083.9	1082.2	1082.5
150°	1126.8	1125.6	1124.3	1123.1	1121.9	1118.7	1115.5	1112.3	1109.1	1107.5	1108.2
152.5°	1149.4	1148.2	1146.9	1145.7	1144.5	1141.5	1138.5	1135.5	1132.5	1131.0	1131.8
155°	1169.2	1168.0	1166.8	1165.6	1164.4	1162.0	1159.6	1157.2	1154.8	1153.6	1154.5
157.5°	1187.2	1185.8	1184.4	1183.0	1181.6	1179.8	1178.0	1176.2	1174.4	1173.5	1174.3
160°	1201.8	1200.6	1199.4	1198.2	1197.0	1195.8	1194.6	1193.3	1192.1	1191.5	1192.1
162.5°	1216.2	1214.8	1213.3	1211.9	1210.5	1209.5	1208.5	1207.5	1206.5	1206.0	1206.6
165°	1227.0	1225.6	1224.2	1222.8	1221.4	1220.8	1220.2	1219.6	1219.0	1218.7	1219.3
167.5°	1236.9	1235.5	1234.1	1232.7	1231.3	1230.7	1230.1	1229.5	1228.9	1228.6	1229.2
170°	1244.2	1242.8	1241.4	1240.0	1238.6	1238.2	1237.8	1237.3	1236.9	1236.7	1237.3
172.5°	1249.6	1248.2	1246.8	1245.4	1244.0	1243.6	1243.2	1242.8	1242.4	1242.2	1242.8
175°	1253.2	1251.8	1250.4	1249.0	1247.6	1247.2	1246.8	1246.4	1246.0	1245.8	1246.5
177.5°	1254.1	1252.7	1251.3	1249.9	1248.5	1248.3	1248.1	1247.9	1247.7	1247.6	1248.3
180°	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1335.3	1335.3	1335.3	1335.3
2.5°	1310.6	1310.6	1326.0	1342.4
5°	1281.9	1289.1	1313.7	1336.3
7.5°	1254.2	1266.5	1297.3	1326.0
10°	1220.3	1236.7	1274.7	1308.6
12.5°	1187.5	1202.9	1247.0	1285.0
15°	1141.3	1160.8	1208.0	1255.2
17.5°	1095.1	1114.6	1172.1	1227.5
20°	1040.7	1066.4	1131.0	1204.9
22.5°	990.4	1022.2	1094.1	1153.6
25°	935.0	984.3	1051.0	1127.9
27.5°	885.7	935.0	1002.7	1080.7
30°	830.3	880.6	950.4	1022.2
32.5°	776.9	823.1	890.9	979.1
35°	721.5	765.6	831.3	920.6
37.5°	671.2	714.3	786.2	868.3
40°	622.0	667.1	728.7	810.8
42.5°	575.8	615.8	671.2	753.3
45°	533.7	562.4	613.7	690.7
47.5°	489.6	515.2	562.4	639.4
50°	448.5	470.1	511.1	583.0
52.5°	408.5	427.0	464.9	522.4
55°	372.6	390.0	417.7	474.2
57.5°	335.6	349.0	375.6	420.8
60°	299.7	312.0	333.6	370.5
62.5°	263.8	274.0	294.6	324.3
65°	232.0	240.2	255.6	281.2
67.5°	201.2	206.3	218.6	239.1
70°	171.4	175.5	185.8	202.2
72.5°	139.6	143.7	155.0	166.3
75°	112.9	113.9	122.1	131.4
77.5°	88.3	87.2	93.4	100.6
80°	60.6	63.6	68.8	71.8
82.5°	41.1	42.1	44.1	46.2
85°	22.6	23.6	23.6	26.7
87.5°	9.2	10.3	10.3	11.3
90°	7.5	5.3	3.1	0.9
92.5°	20.2	21.0	21.8	22.6
95°	38.9	45.5	52.2	58.8
97.5°	56.3	72.8	89.3	105.8
100°	77.5	105.0	132.5	160.0
102.5°	218.5	218.9	219.3	219.7
105°	292.9	286.9	280.8	274.8
107.5°	354.1	349.0	344.0	339.0
110°	413.2	408.9	404.7	400.5



TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	469.2	465.6	462.0	458.4
115°	530.1	526.6	523.2	519.8
117.5°	585.2	581.2	577.2	573.2
120°	641.9	638.8	635.8	632.8
122.5°	693.1	689.9	686.7	683.5
125°	742.8	740.2	737.6	735.0
127.5°	790.5	787.6	784.8	782.0
130°	836.0	832.7	829.5	826.3
132.5°	879.4	876.7	874.1	871.5
135°	919.1	915.9	912.7	909.5
137.5°	956.5	954.1	951.7	949.3
140°	993.0	991.3	989.7	988.1
142.5°	1024.9	1023.5	1022.1	1020.7
145°	1054.4	1054.6	1054.8	1055.0
147.5°	1083.1	1083.7	1084.3	1084.9
150°	1109.6	1111.0	1112.4	1113.8
152.5°	1133.4	1135.0	1136.6	1138.2
155°	1156.3	1158.1	1159.9	1161.7
157.5°	1175.9	1177.5	1179.1	1180.7
160°	1193.3	1194.6	1195.8	1197.0
162.5°	1207.8	1209.0	1210.2	1211.4
165°	1220.5	1221.7	1222.9	1224.1
167.5°	1230.4	1231.6	1232.8	1234.0
170°	1238.5	1239.8	1241.0	1242.2
172.5°	1244.0	1245.2	1246.4	1247.6
175°	1247.9	1249.3	1250.7	1252.1
177.5°	1249.7	1251.1	1252.5	1253.9
180°	1249.4	1249.4	1249.4	1249.4

TEST NUMBER: P998922

CATALOG NUMBER: SA2XXDIP-B675D925UB2750-4F0-XX-W2A-A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.92	16.70	16.93	17.72	19.07	13.41	14.20	14.42	15.21	16.56
	3H	16.72	17.43	17.74	18.45	19.82	14.75	15.45	15.77	16.48	17.85
	4H	16.89	17.55	17.92	18.58	19.96	15.21	15.87	16.24	16.90	18.28
	6H	16.93	17.54	17.97	18.57	19.96	15.51	16.12	16.55	17.15	18.54
	8H	16.91	17.49	17.95	18.54	19.92	15.59	16.18	16.64	17.22	18.61
	12H	16.87	17.42	17.92	18.46	19.87	15.63	16.19	16.68	17.23	18.63
4H	2H	15.95	16.62	16.99	17.64	19.02	13.85	14.51	14.89	15.54	16.92
	3H	16.92	17.48	17.97	18.53	19.92	15.30	15.85	16.35	16.91	18.30
	4H	17.20	17.70	18.25	18.75	20.16	15.83	16.34	16.89	17.39	18.80
	6H	17.32	17.76	18.39	18.83	20.24	16.21	16.64	17.27	17.71	19.12
	8H	17.32	17.73	18.38	18.79	20.21	16.32	16.72	17.38	17.78	19.21
	12H	17.28	17.65	18.36	18.72	20.15	16.37	16.74	17.45	17.81	19.24
8H	4H	17.20	17.61	18.26	18.67	20.09	15.97	16.38	17.03	17.44	18.86
	6H	17.38	17.71	18.46	18.82	20.24	16.40	16.74	17.49	17.84	19.26
	8H	17.41	17.70	18.50	18.79	20.23	16.55	16.84	17.64	17.93	19.37
	12H	17.39	17.65	18.48	18.73	20.21	16.64	16.90	17.74	17.98	19.46
12H	4H	17.15	17.52	18.23	18.60	20.02	15.94	16.31	17.02	17.38	18.81
	6H	17.36	17.65	18.45	18.74	20.18	16.40	16.70	17.49	17.78	19.22
	8H	17.38	17.64	18.48	18.72	20.20	16.56	16.81	17.65	17.90	19.38