

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931431

Luminaire Tested: DFN2DS-TR3F0-090DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-090DS850-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9881.2 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 99.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931431

CATALOG NUMBER: DFN2DS-TR3F0-090DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931431

CATALOG NUMBER: DFN2DS-TR3F0-090DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4839	4839	4839
5°	4858	4788	4816
10°	4829	4740	4763
15°	4769	4678	4673
20°	4685	4586	4581
25°	4601	4472	4472
30°	4492	4369	4331
35°	4391	4244	4181
40°	4265	4118	4040
45°	4140	3995	3896
50°	4003	3866	3728
55°	3862	3716	3578
60°	3704	3537	3407
65°	3535	3359	3204
70°	3320	3143	2994
75°	3020	2894	2823
80°	2681	2598	2466
85°	2186	2085	1870

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4140 cd/sqm

TEST NUMBER: P931431

CATALOG NUMBER: DFN2DS-TR3F0-090DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.5	3.7
10°-20°	1028.5	10.4
20°-30°	1511.4	15.3
30°-40°	1755.4	17.8
40°-50°	1753.3	17.7
50°-60°	1528.8	15.5
60°-70°	1130.1	11.4
70°-80°	639.4	6.5
80°-90°	168.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2905.4	29.4
0°-40°	4660.9	47.2
0°-60°	7942.9	80.4
0°-90°	9881.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9881.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3884	3884	3884	3884	3884	
5°	3884	3869	3828	3858	3850	369
15°	3697	3675	3626	3641	3622	1041
25°	3346	3316	3253	3260	3253	1540
35°	2887	2850	2790	2767	2748	1803
45°	2349	2323	2267	2226	2211	1813
55°	1778	1755	1710	1666	1647	1589
65°	1199	1176	1139	1106	1087	1185
75°	627	620	601	579	586	670
85°	153	149	146	134	131	180
90°	0	0	0	0	0	

TEST NUMBER: P931431

CATALOG NUMBER: DFN2DS-TR3F0-090DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3883.6	3883.6	3883.6	3883.6	3883.6
2.5°	3906.2	3887.6	3846.5	3883.6	3876.5
5°	3883.6	3869.0	3827.8	3857.5	3850.3
7.5°	3857.5	3835.4	3794.1	3824.3	3816.7
10°	3816.7	3790.6	3745.8	3775.5	3764.4
12.5°	3760.4	3738.2	3693.5	3712.0	3704.6
15°	3697.1	3674.9	3626.1	3641.2	3622.5
17.5°	3618.6	3596.4	3547.7	3566.3	3547.7
20°	3532.6	3510.4	3458.1	3469.2	3454.5
22.5°	3447.0	3413.4	3364.6	3364.6	3357.1
25°	3346.0	3316.2	3252.9	3260.0	3252.9
27.5°	3233.8	3207.7	3159.4	3148.3	3129.7
30°	3122.2	3092.0	3036.1	3025.0	3010.0
32.5°	3002.5	2980.3	2920.4	2897.9	2882.8
35°	2886.8	2849.6	2789.7	2767.2	2748.5
37.5°	2756.1	2722.4	2662.5	2636.4	2617.8
40°	2621.7	2591.6	2531.7	2498.5	2483.5
42.5°	2490.9	2460.9	2401.4	2363.8	2341.7
45°	2349.1	2323.0	2266.7	2225.9	2210.9
47.5°	2210.9	2184.7	2124.8	2083.7	2061.5
50°	2065.1	2046.4	1994.1	1941.9	1923.2
52.5°	1923.2	1897.1	1848.7	1807.6	1781.4
55°	1777.8	1755.2	1710.4	1665.7	1647.1
57.5°	1632.0	1613.4	1564.7	1519.9	1504.8
60°	1486.2	1471.5	1419.2	1378.0	1367.0
62.5°	1344.3	1318.2	1280.9	1243.7	1228.7
65°	1198.9	1176.3	1139.1	1105.5	1086.8
67.5°	1049.6	1030.6	997.2	971.2	956.1
70°	911.3	896.2	862.6	836.4	821.8
72.5°	769.4	754.3	735.7	709.6	698.6
75°	627.3	620.0	601.1	578.9	586.4
77.5°	500.4	485.4	477.9	466.8	455.7
80°	373.6	369.6	362.1	351.0	343.6
82.5°	254.0	254.0	250.4	235.3	235.3
85°	152.9	149.4	145.8	134.3	130.8
87.5°	67.3	59.8	52.3	41.3	37.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931431

CATALOG NUMBER: DFN2DS-TR3F0-090DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.76	18.37	17.13	18.69	19.00	16.32	17.93	16.68	18.24	18.56
	3H	18.51	19.97	18.89	20.29	20.65	18.02	19.47	18.40	19.80	20.16
	4H	19.16	20.53	19.56	20.87	21.25	18.66	20.03	19.06	20.38	20.76
	6H	19.63	20.90	20.04	21.26	21.65	19.13	20.39	19.54	20.76	21.15
	8H	19.77	20.98	20.19	21.37	21.77	19.27	20.48	19.69	20.87	21.27
	12H	19.86	21.02	20.29	21.40	21.83	19.35	20.51	19.78	20.89	21.32
4H	2H	17.32	18.69	17.72	19.04	19.41	16.97	18.34	17.37	18.69	19.06
	3H	19.30	20.44	19.71	20.84	21.24	18.89	20.04	19.30	20.43	20.83
	4H	20.07	21.11	20.50	21.52	21.96	19.65	20.69	20.08	21.10	21.54
	6H	20.67	21.57	21.12	22.02	22.47	20.24	21.14	20.69	21.58	22.04
	8H	20.86	21.71	21.32	22.15	22.61	20.42	21.27	20.88	21.71	22.18
	12H	20.99	21.75	21.47	22.23	22.70	20.54	21.30	21.02	21.77	22.24
8H	4H	20.35	21.19	20.81	21.64	22.10	19.97	20.82	20.43	21.26	21.73
	6H	21.06	21.76	21.55	22.25	22.73	20.68	21.38	21.17	21.87	22.35
	8H	21.32	21.95	21.83	22.46	22.94	20.93	21.56	21.44	22.07	22.55
	12H	21.52	22.08	22.03	22.57	23.13	21.11	21.66	21.61	22.16	22.72
12H	4H	20.37	21.13	20.85	21.61	22.08	20.01	20.77	20.49	21.24	21.71
	6H	21.11	21.74	21.62	22.24	22.73	20.74	21.37	21.25	21.88	22.36
	8H	21.42	21.98	21.93	22.47	23.03	21.04	21.60	21.55	22.09	22.65