

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931343

Luminaire Tested: DFN2DS-TR3F0-040DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931343
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-040DS927-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3136.3 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 39.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931343

CATALOG NUMBER: DFN2DS-TR3F0-040DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931343

CATALOG NUMBER: DFN2DS-TR3F0-040DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1536	1536	1536
5°	1542	1520	1529
10°	1533	1504	1512
15°	1514	1485	1483
20°	1487	1456	1454
25°	1460	1420	1420
30°	1426	1387	1375
35°	1394	1347	1327
40°	1354	1307	1282
45°	1314	1268	1237
50°	1271	1227	1183
55°	1226	1179	1136
60°	1176	1123	1081
65°	1122	1066	1017
70°	1054	998	950
75°	959	919	896
80°	851	825	783
85°	693	662	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1314 cd/sqm

TEST NUMBER: P931343

CATALOG NUMBER: DFN2DS-TR3F0-040DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	3.7
10°-20°	326.4	10.4
20°-30°	479.7	15.3
30°-40°	557.2	17.8
40°-50°	556.5	17.7
50°-60°	485.2	15.5
60°-70°	358.7	11.4
70°-80°	202.9	6.5
80°-90°	53.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.2	29.4
0°-40°	1479.4	47.2
0°-60°	2521.1	80.4
0°-90°	3136.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3136.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1224	1222	117
15°	1173	1166	1151	1156	1150	330
25°	1062	1053	1032	1035	1032	489
35°	916	904	886	878	872	572
45°	746	737	720	706	702	575
55°	564	557	543	529	523	504
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	48	47	46	43	42	57
90°	0	0	0	0	0	

TEST NUMBER: P931343

CATALOG NUMBER: DFN2DS-TR3F0-040DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.7	1232.7	1232.7	1232.7	1232.7
2.5°	1239.9	1233.9	1220.9	1232.7	1230.5
5°	1232.7	1228.0	1214.9	1224.4	1222.1
7.5°	1224.4	1217.3	1204.2	1213.8	1211.4
10°	1211.4	1203.1	1189.0	1198.4	1194.8
12.5°	1193.5	1186.5	1172.3	1178.3	1175.8
15°	1173.4	1166.4	1150.9	1155.7	1149.8
17.5°	1148.6	1141.5	1126.1	1131.9	1126.1
20°	1121.2	1114.2	1097.6	1101.1	1096.5
22.5°	1094.1	1083.4	1067.9	1067.9	1065.6
25°	1062.0	1052.6	1032.5	1034.7	1032.5
27.5°	1026.4	1018.1	1002.8	999.3	993.4
30°	991.0	981.4	963.7	960.1	955.4
32.5°	953.0	946.0	927.0	919.8	915.0
35°	916.3	904.5	885.5	878.3	872.4
37.5°	874.8	864.1	845.1	836.8	830.9
40°	832.2	822.6	803.6	793.0	788.3
42.5°	790.7	781.1	762.2	750.3	743.2
45°	745.6	737.4	719.5	706.5	701.7
47.5°	701.7	693.4	674.5	661.4	654.4
50°	655.5	649.5	633.0	616.3	610.4
52.5°	610.4	602.2	586.8	573.7	565.4
55°	564.3	557.1	542.9	528.7	522.8
57.5°	518.0	512.1	496.6	482.4	477.7
60°	471.7	467.0	450.5	437.4	433.9
62.5°	426.7	418.4	406.6	394.7	390.0
65°	380.6	373.3	361.5	350.9	345.0
67.5°	333.1	327.1	316.6	308.2	303.5
70°	289.2	284.5	273.8	265.5	260.8
72.5°	244.3	239.4	233.6	225.2	221.7
75°	199.1	196.8	190.8	183.7	186.1
77.5°	158.8	154.0	151.7	148.1	144.6
80°	118.6	117.3	114.9	111.4	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.5	47.4	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931343

CATALOG NUMBER: DFN2DS-TR3F0-040DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.77	14.38	13.14	14.70	15.01	12.33	13.94	12.69	14.25	14.57
	3H	14.52	15.98	14.90	16.30	16.67	14.03	15.49	14.41	15.81	16.17
	4H	15.17	16.54	15.57	16.89	17.26	14.68	16.04	15.07	16.39	16.77
	6H	15.64	16.91	16.05	17.27	17.66	15.14	16.41	15.55	16.77	17.16
	8H	15.78	16.99	16.21	17.38	17.78	15.28	16.49	15.70	16.88	17.28
	12H	15.87	17.03	16.30	17.41	17.84	15.36	16.52	15.79	16.90	17.33
4H	2H	13.33	14.70	13.73	15.05	15.43	12.98	14.35	13.38	14.70	15.07
	3H	15.31	16.46	15.72	16.85	17.25	14.90	16.05	15.31	16.45	16.85
	4H	16.09	17.12	16.52	17.54	17.97	15.66	16.70	16.09	17.11	17.55
	6H	16.68	17.59	17.14	18.03	18.48	16.25	17.15	16.70	17.60	18.05
	8H	16.87	17.72	17.33	18.16	18.63	16.43	17.28	16.89	17.72	18.19
	12H	17.00	17.76	17.48	18.24	18.71	16.55	17.31	17.03	17.79	18.26
8H	4H	16.36	17.21	16.82	17.65	18.11	15.98	16.83	16.45	17.27	17.74
	6H	17.07	17.78	17.57	18.26	18.74	16.69	17.39	17.19	17.88	18.36
	8H	17.33	17.96	17.84	18.47	18.96	16.94	17.57	17.45	18.08	18.56
	12H	17.53	18.09	18.04	18.58	19.14	17.12	17.68	17.63	18.17	18.73
12H	4H	16.39	17.15	16.87	17.62	18.09	16.02	16.78	16.50	17.26	17.73
	6H	17.12	17.75	17.63	18.26	18.74	16.75	17.38	17.26	17.89	18.37
	8H	17.43	17.99	17.94	18.48	19.04	17.05	17.61	17.56	18.10	18.66