

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931398

Luminaire Tested: DFN2DS-TR3F0-070DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931398
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-070DS927-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4712.4 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 74.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931398

CATALOG NUMBER: DFN2DS-TR3F0-070DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931398

CATALOG NUMBER: DFN2DS-TR3F0-070DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2855	2855	2855
5°	2866	2819	2835
10°	2844	2773	2750
15°	2811	2691	2614
20°	2766	2574	2444
25°	2720	2440	2281
30°	2656	2303	2071
35°	2593	2155	1886
40°	2530	2000	1673
45°	2456	1827	1480
50°	2380	1652	1291
55°	2302	1464	1108
60°	2212	1266	920
65°	2109	1064	837
70°	1987	876	770
75°	1837	798	719
80°	1622	714	655
85°	1274	563	563

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2456 cd/sqm

TEST NUMBER: P931398

CATALOG NUMBER: DFN2DS-TR3F0-070DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.7	4.6
10°-20°	589.5	12.5
20°-30°	827.7	17.6
30°-40°	902.2	19.1
40°-50°	829.2	17.6
50°-60°	651.2	13.8
60°-70°	423.9	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.9	34.6
0°-40°	2534.1	53.8
0°-60°	4014.6	85.2
0°-90°	4712.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4712.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2291	2291	2291	2291	2291	
5°	2291	2281	2254	2273	2266	217
15°	2179	2156	2086	2047	2026	614
25°	1978	1912	1775	1690	1659	910
35°	1704	1599	1416	1286	1240	1067
45°	1394	1254	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	715	547	361	290	284	709
75°	382	236	166	151	149	403
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P931398

CATALOG NUMBER: DFN2DS-TR3F0-070DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.3	2291.3	2291.3	2291.3	2291.3
2.5°	2301.6	2291.3	2268.4	2289.4	2285.2
5°	2291.3	2281.0	2254.0	2272.6	2266.5
7.5°	2272.6	2260.3	2231.3	2239.4	2229.1
10°	2247.8	2233.3	2191.9	2185.5	2173.2
12.5°	2216.7	2198.0	2142.0	2129.6	2106.7
15°	2179.3	2156.5	2086.0	2046.7	2026.0
17.5°	2135.8	2102.6	2015.5	1969.9	1936.7
20°	2086.0	2044.5	1940.9	1889.2	1843.4
22.5°	2032.2	1984.4	1864.1	1793.6	1762.7
25°	1978.3	1911.8	1775.0	1690.0	1658.8
27.5°	1914.0	1843.4	1692.0	1594.6	1546.9
30°	1845.6	1766.6	1600.7	1495.1	1439.1
32.5°	1779.1	1683.7	1513.8	1389.3	1337.4
35°	1704.5	1598.7	1416.4	1285.7	1240.0
37.5°	1632.0	1517.8	1325.1	1181.8	1130.2
40°	1555.2	1430.9	1229.6	1082.4	1028.5
42.5°	1476.4	1343.8	1134.3	980.7	929.1
45°	1393.5	1254.4	1036.9	889.5	839.8
47.5°	1314.7	1167.6	943.6	796.2	750.7
50°	1227.6	1080.4	852.3	709.1	665.8
52.5°	1142.5	986.9	765.2	628.3	588.9
55°	1059.5	897.8	673.8	549.6	510.2
57.5°	974.6	808.7	593.1	476.9	443.8
60°	887.5	721.6	508.0	402.4	369.2
62.5°	802.5	636.7	435.4	336.0	319.4
65°	715.4	547.4	360.8	290.4	284.0
67.5°	632.5	464.4	290.4	254.9	248.8
70°	545.4	383.6	240.5	219.8	211.4
72.5°	462.4	308.9	201.1	184.6	180.4
75°	381.5	236.3	165.8	151.4	149.4
77.5°	300.7	167.8	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.5	80.9	68.4	64.2	64.2
85°	89.1	45.5	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931398

CATALOG NUMBER: DFN2DS-TR3F0-070DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.88	16.40	15.24	16.71	17.03	10.84	12.36	11.20	12.68	12.99
	3H	16.64	18.01	17.02	18.34	18.70	12.10	13.47	12.48	13.80	14.16
	4H	17.31	18.59	17.71	18.94	19.32	12.61	13.89	13.01	14.24	14.61
	6H	17.80	18.98	18.21	19.35	19.74	12.99	14.17	13.40	14.54	14.93
	8H	17.97	19.09	18.39	19.48	19.88	13.11	14.24	13.54	14.63	15.03
	12H	18.07	19.15	18.50	19.53	19.96	13.19	14.27	13.62	14.65	15.08
4H	2H	14.98	16.26	15.38	16.61	16.99	11.54	12.82	11.94	13.16	13.54
	3H	16.92	17.98	17.33	18.38	18.78	12.98	14.04	13.39	14.44	14.84
	4H	17.67	18.62	18.10	19.04	19.48	13.58	14.53	14.01	14.95	15.39
	6H	18.26	19.09	18.72	19.53	19.99	14.07	14.90	14.52	15.34	15.80
	8H	18.47	19.25	18.94	19.69	20.16	14.23	15.01	14.69	15.45	15.92
	12H	18.63	19.32	19.11	19.80	20.27	14.35	15.04	14.83	15.52	15.99
8H	4H	17.69	18.47	18.15	18.91	19.38	13.93	14.71	14.40	15.15	15.62
	6H	18.33	18.97	18.82	19.46	19.94	14.52	15.16	15.02	15.65	16.13
	8H	18.58	19.15	19.09	19.66	20.15	14.74	15.32	15.25	15.83	16.31
	12H	18.78	19.29	19.29	19.78	20.35	14.92	15.43	15.43	15.92	16.49
12H	4H	17.67	18.37	18.16	18.85	19.32	13.98	14.67	14.46	15.15	15.62
	6H	18.31	18.89	18.82	19.40	19.88	14.58	15.16	15.10	15.67	16.16
	8H	18.59	19.10	19.10	19.60	20.16	14.86	15.37	15.36	15.86	16.42