

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999038

Luminaire Tested: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999038
REPORT IS A COMBINATION OF REPORTS P984787 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5061.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74		
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68	64		
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58	55		
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50	47		
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	41		
5	74	63	54	49	70	60	53	47	55	49	44	50	45	42	46	42	39	36		
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35	32		
7	64	52	44	38	61	50	42	37	46	39	35	42	37	33	39	34	31	29		
8	60	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28	26		
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26	24		
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26934	26934	26934	26934
5°	26998	28717	27101	22848
10°	26685	31350	26851	18836
15°	26038	33067	26399	15866
20°	25631	31047	25631	13791
25°	24814	26673	24926	12333
30°	23470	20967	23917	11171
35°	22279	14498	22651	10221
40°	20911	10946	21150	9463
45°	19224	8995	19538	8646
50°	17763	7896	17796	7915
55°	16100	6728	16204	7120
60°	14326	5619	14526	6215
65°	12737	4571	12972	5307
70°	11156	3586	11442	4279
75°	9364	2603	9728	3105
80°	7305	1650	7832	1842
85°	4803	830	5170	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 27842 cd/sqm

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.1	3.2
10°-20°	471.7	9.3
20°-30°	684.6	13.5
30°-40°	721.7	14.3
40°-50°	638.6	12.6
50°-60°	509.9	10.1
60°-70°	346.4	6.8
70°-80°	177.2	3.5
80°-90°	42.7	0.8
90°-100°	14.7	0.3
100°-110°	54.8	1.1
110°-120°	145.3	2.9
120°-130°	240.9	4.8
130°-140°	255.9	5.1
140°-150°	237.8	4.7
150°-160°	191.2	3.8
160°-170°	123.2	2.4
170°-180°	42.4	0.8
0°-30°	1318.3	26.0
0°-40°	2040.0	40.3
0°-60°	3188.6	63.0
0°-90°	3754.8	74.2
90°-120°	214.7	4.2
90°-150°	949.4	18.8
90°-180°	1306.0	25.8
0°-180°	5061.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1702	1702	1702	1702	1702	
5°	1703	1900	1709	1512	1703	161
15°	1600	2336	1622	1121	1600	452
25°	1437	1946	1444	900	1437	657
35°	1173	1059	1193	747	1173	734
45°	880	638	895	613	880	683
55°	604	449	608	475	604	539
65°	358	276	365	320	358	356
75°	167	136	174	162	167	180
85°	34	35	37	26	34	40
90°	0	9	0	9	0	3
95°	21	14	21	14	21	25
105°	98	24	98	24	98	105
115°	185	26	185	26	185	183
125°	262	276	262	276	262	234
135°	324	335	324	335	324	251
145°	376	382	376	382	376	235
155°	414	415	414	415	414	191
165°	436	436	436	436	436	123
175°	446	444	446	444	446	42
180°	446	446	446	446	446	

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1710.6	1714.6	1721.1	1722.4	1735.5	1746.0	1757.7	1757.7	1761.6	1760.3	1749.9
5°	1702.8	1714.6	1731.6	1746.0	1769.5	1780.0	1795.7	1807.4	1817.9	1825.7	1824.4
7.5°	1689.7	1710.6	1735.5	1763.0	1794.3	1812.7	1834.9	1855.8	1870.2	1883.3	1892.4
10°	1667.5	1702.8	1736.8	1773.4	1814.0	1838.8	1865.0	1892.4	1914.7	1939.5	1963.1
12.5°	1637.4	1688.4	1730.3	1778.6	1828.3	1855.8	1897.7	1918.6	1961.7	2024.5	2041.5
15°	1599.5	1668.8	1708.0	1769.5	1834.9	1857.1	1914.7	1948.7	2037.6	2076.8	2123.9
17.5°	1564.2	1641.3	1693.6	1764.3	1828.3	1871.5	1927.7	1997.1	2071.6	2127.8	2180.2
20°	1535.4	1609.9	1672.7	1751.2	1832.3	1887.2	1946.1	2029.8	2110.8	2168.4	2208.9
22.5°	1470.0	1565.5	1638.7	1726.3	1824.4	1900.3	1956.5	2048.1	2135.7	2171.0	2206.3
25°	1437.3	1519.7	1604.7	1704.1	1819.2	1909.4	1957.8	2059.8	2137.0	2150.1	2157.9
27.5°	1377.1	1470.0	1569.4	1683.2	1817.9	1893.7	1955.2	2048.1	2109.5	2100.4	2076.8
30°	1302.6	1416.4	1526.2	1649.2	1799.6	1882.0	1939.5	2024.5	2055.9	2008.8	1967.0
32.5°	1247.7	1354.9	1476.5	1619.1	1778.6	1857.1	1913.4	1980.1	1986.6	1901.6	1831.0
35°	1173.1	1292.1	1429.5	1579.9	1743.3	1814.0	1866.3	1906.8	1875.4	1756.4	1672.7
37.5°	1106.4	1224.1	1370.6	1523.6	1694.9	1764.3	1806.1	1812.7	1735.5	1630.9	1507.9
40°	1033.2	1154.8	1307.8	1468.7	1641.3	1701.5	1727.6	1708.0	1596.9	1475.2	1332.7
42.5°	959.9	1080.3	1245.1	1409.8	1573.3	1624.3	1634.8	1581.2	1445.2	1302.6	1137.8
45°	880.2	1005.7	1170.5	1336.6	1494.9	1523.6	1524.9	1447.8	1286.9	1137.8	984.8
47.5°	814.8	931.2	1094.7	1260.7	1394.1	1413.8	1405.9	1317.0	1141.7	974.3	840.9
50°	742.8	854.0	1016.2	1179.7	1293.4	1298.7	1279.1	1152.2	980.9	827.9	721.9
52.5°	665.7	778.2	927.3	1084.2	1186.2	1178.4	1140.4	1004.4	843.6	716.7	635.6
55°	604.2	703.6	843.6	996.6	1068.5	1046.3	1004.4	865.8	738.9	631.7	561.1
57.5°	536.2	623.8	761.2	894.6	936.4	915.5	873.6	744.2	626.5	545.4	498.3
60°	472.1	551.9	672.2	783.4	816.1	793.9	745.5	629.1	544.1	476.1	440.7
62.5°	413.3	482.6	583.3	685.3	698.4	676.1	634.3	540.1	466.9	413.3	387.1
65°	358.3	423.7	504.8	582.0	593.8	570.2	527.1	459.0	397.6	363.6	338.7
67.5°	304.7	357.0	429.0	485.2	491.7	469.5	434.2	379.3	341.3	304.7	286.4
70°	257.6	296.9	353.1	398.9	401.5	380.6	362.3	312.6	283.8	257.6	243.3
72.5°	211.9	239.3	282.5	316.5	317.8	304.7	287.7	256.3	231.5	213.2	198.8
75°	167.4	190.9	217.1	247.2	245.9	235.4	222.3	202.7	181.8	170.0	163.5
77.5°	128.2	142.6	163.5	183.1	183.1	177.9	170.0	155.6	142.6	130.8	124.2
80°	91.5	100.7	117.7	124.2	126.9	125.6	119.0	108.5	103.3	94.2	91.5
82.5°	58.9	65.4	73.2	79.8	83.7	81.1	79.8	74.5	66.7	64.1	61.5
85°	34.0	36.6	40.5	44.5	45.8	44.5	47.1	43.2	39.2	39.2	37.9
87.5°	14.4	15.7	18.3	18.3	19.6	19.6	18.3	19.6	19.6	18.3	17.0
90°	0.3	1.1	1.9	2.7	3.5	3.9	4.2	4.7	5.3	5.8	6.4
92.5°	8.1	7.8	7.5	7.2	6.9	6.8	6.9	7.1	7.3	7.5	7.7
95°	21.0	18.6	16.2	13.9	11.5	10.3	10.6	11.1	11.6	12.1	12.6
97.5°	37.7	31.8	26.0	20.1	14.2	11.3	11.9	13.0	14.1	15.3	16.4
100°	57.1	47.3	37.5	27.6	17.8	12.9	13.5	14.7	16.0	17.2	18.4
102.5°	78.3	78.2	78.0	77.9	77.8	77.7	71.2	58.1	45.1	32.0	19.0
105°	98.0	100.2	102.3	104.5	106.6	107.7	97.9	78.4	58.8	39.3	19.7
107.5°	120.9	122.7	124.5	126.3	128.1	129.0	116.9	92.8	68.6	44.5	20.3
110°	142.8	144.3	145.8	147.3	148.8	149.6	139.2	118.5	97.8	77.1	56.4

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	163.5	164.8	166.1	167.4	168.7	169.3	168.7	167.5	166.2	165.0	163.8
115°	185.4	186.6	187.8	189.1	190.3	190.9	191.8	193.6	195.3	197.1	198.9
117.5°	204.4	205.8	207.2	208.7	210.1	210.8	211.4	212.6	213.9	215.1	216.3
120°	225.7	226.8	227.8	228.9	230.0	230.5	231.1	232.4	233.7	235.0	236.3
122.5°	243.7	244.9	246.0	247.2	248.3	248.9	249.6	251.0	252.5	253.9	255.3
125°	262.1	263.0	264.0	264.9	265.8	266.3	267.0	268.3	269.7	271.0	272.4
127.5°	278.9	279.9	280.9	281.9	282.9	283.4	283.9	285.0	286.1	287.1	288.2
130°	294.7	295.8	297.0	298.1	299.2	299.8	300.2	301.0	301.8	302.6	303.4
132.5°	310.8	311.7	312.7	313.6	314.5	315.0	315.4	316.2	316.9	317.7	318.5
135°	324.3	325.5	326.6	327.8	328.9	329.5	329.8	330.5	331.1	331.8	332.4
137.5°	338.5	339.4	340.2	341.1	342.0	342.4	342.8	343.5	344.2	344.9	345.6
140°	352.4	353.0	353.6	354.1	354.7	355.0	355.4	356.2	356.9	357.7	358.5
142.5°	364.0	364.5	365.0	365.5	366.0	366.2	366.7	367.6	368.5	369.5	370.4
145°	376.2	376.1	376.1	376.0	375.9	375.9	376.5	377.7	379.0	380.2	381.4
147.5°	386.9	386.7	386.5	386.2	386.0	385.9	386.5	387.7	389.0	390.2	391.4
150°	397.2	396.7	396.2	395.7	395.2	394.9	395.5	396.6	397.8	398.9	400.1
152.5°	405.9	405.3	404.7	404.2	403.6	403.3	403.8	404.9	406.0	407.1	408.2
155°	414.3	413.7	413.0	412.4	411.7	411.4	411.8	412.7	413.6	414.4	415.3
157.5°	421.1	420.5	419.9	419.4	418.8	418.5	418.8	419.5	420.1	420.8	421.4
160°	426.9	426.5	426.0	425.6	425.1	424.9	425.1	425.6	426.0	426.5	426.9
162.5°	432.0	431.6	431.2	430.7	430.3	430.1	430.3	430.6	431.0	431.3	431.7
165°	436.5	436.1	435.7	435.2	434.8	434.6	434.7	434.9	435.2	435.4	435.6
167.5°	440.1	439.7	439.2	438.8	438.3	438.1	438.2	438.4	438.7	438.9	439.1
170°	443.0	442.6	442.1	441.7	441.2	441.0	441.1	441.2	441.4	441.5	441.7
172.5°	444.9	444.5	444.1	443.6	443.2	443.0	443.1	443.2	443.3	443.5	443.6
175°	446.5	446.0	445.5	445.0	444.5	444.3	444.4	444.5	444.6	444.8	444.9
177.5°	447.2	446.7	446.2	445.7	445.2	444.9	444.9	445.0	445.1	445.1	445.2
180°	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1768.2	1769.5	1772.1	1785.2	1791.7	1793.0	1787.8	1799.6	1803.5	1799.6	1797.0
5°	1851.9	1859.7	1875.4	1892.4	1891.1	1892.4	1900.3	1908.1	1910.7	1900.3	1904.2
7.5°	1925.1	1940.8	1957.8	1984.0	1984.0	1997.1	2002.3	2008.8	2024.5	2016.7	2014.1
10°	2008.8	2029.8	2061.1	2103.0	2104.3	2117.4	2130.5	2151.4	2157.9	2152.7	2155.3
12.5°	2113.5	2154.0	2156.6	2202.4	2223.3	2225.9	2246.9	2242.9	2256.0	2256.0	2278.2
15°	2159.2	2222.0	2257.3	2301.8	2314.9	2299.2	2316.2	2334.5	2335.8	2335.8	2334.5
17.5°	2241.6	2266.5	2301.8	2325.3	2330.6	2330.6	2331.9	2339.7	2334.5	2324.0	2331.9
20°	2258.6	2269.1	2282.2	2279.5	2282.2	2269.1	2256.0	2242.9	2244.2	2237.7	2257.3
22.5°	2227.2	2224.6	2194.5	2174.9	2174.9	2148.8	2123.9	2112.1	2100.4	2104.3	2110.8
25°	2148.8	2108.2	2071.6	2042.8	2036.3	1994.4	1960.4	1950.0	1930.4	1946.1	1948.7
27.5°	2023.2	1977.4	1918.6	1893.7	1859.7	1842.7	1819.2	1787.8	1747.3	1770.8	1766.9
30°	1888.5	1820.5	1772.1	1712.0	1658.3	1654.4	1609.9	1557.6	1536.7	1536.7	1548.5
32.5°	1738.1	1647.9	1577.2	1492.2	1439.9	1417.7	1364.1	1311.8	1323.5	1284.3	1298.7
35°	1562.9	1443.8	1354.9	1272.5	1233.3	1207.1	1137.8	1109.0	1077.7	1059.3	1093.3
37.5°	1395.5	1258.1	1144.4	1054.1	1039.7	992.6	945.6	927.3	908.9	916.8	915.5
40°	1191.4	1069.8	967.8	897.2	872.3	850.1	818.7	796.5	784.7	791.2	792.5
42.5°	1007.0	905.0	829.2	779.5	758.5	742.8	727.2	708.8	704.9	704.9	710.2
45°	864.5	780.8	729.8	689.2	677.5	665.7	653.9	646.1	643.5	638.2	642.1
47.5°	750.7	684.0	652.6	622.5	609.4	606.8	596.4	592.4	587.2	585.9	587.2
50°	655.2	613.4	584.6	567.6	558.4	554.5	549.3	541.4	538.8	545.4	542.7
52.5°	588.5	549.3	533.6	516.6	511.4	506.1	498.3	499.6	498.3	495.7	495.7
55°	521.8	497.0	481.3	468.2	466.9	461.7	455.1	452.5	451.2	448.6	452.5
57.5°	468.2	448.6	434.2	422.4	417.2	417.2	410.7	405.4	405.4	404.1	405.4
60°	414.6	395.0	385.8	374.0	370.1	368.8	364.9	362.3	358.3	358.3	358.3
62.5°	364.9	349.2	338.7	328.3	329.6	323.0	317.8	315.2	315.2	316.5	316.5
65°	317.8	307.3	294.3	285.1	282.5	281.2	278.6	277.3	273.3	276.0	276.0
67.5°	274.6	260.3	252.4	248.5	244.6	243.3	240.6	238.0	236.7	235.4	238.0
70°	231.5	219.7	213.2	210.6	206.6	205.3	204.0	200.1	201.4	202.7	204.0
72.5°	192.3	181.8	180.5	172.6	172.6	172.6	167.4	170.0	168.7	166.1	168.7
75°	151.7	146.5	143.9	139.9	141.2	139.9	138.6	134.7	134.7	136.0	137.3
77.5°	120.3	115.1	113.8	109.9	107.2	109.9	107.2	105.9	105.9	107.2	107.2
80°	88.9	86.3	82.4	82.4	82.4	81.1	81.1	81.1	79.8	78.5	79.8
82.5°	58.9	58.9	57.5	56.2	57.5	54.9	56.2	56.2	56.2	56.2	56.2
85°	37.9	36.6	36.6	35.3	35.3	35.3	36.6	34.0	34.0	35.3	35.3
87.5°	17.0	17.0	17.0	18.3	17.0	17.0	17.0	18.3	17.0	17.0	17.0
90°	6.8	7.2	7.5	7.9	8.1	8.2	8.3	8.4	8.6	8.7	8.6
92.5°	7.9	8.0	8.2	8.3	8.4	8.4	8.5	8.6	8.6	8.7	8.6
95°	13.0	13.3	13.7	14.0	14.2	14.2	14.1	14.0	14.0	13.9	14.0
97.5°	16.6	16.8	17.1	17.3	17.4	17.4	17.5	17.6	17.6	17.7	17.6
100°	19.0	19.6	20.1	20.7	21.0	21.1	21.2	21.3	21.5	21.6	21.5
102.5°	19.8	20.6	21.4	22.2	22.6	22.7	22.9	23.1	23.3	23.5	23.3
105°	20.5	21.3	22.0	22.8	23.2	23.3	23.6	23.9	24.2	24.5	24.2
107.5°	21.1	21.9	22.7	23.5	23.9	24.0	24.3	24.6	24.8	25.1	24.8
110°	49.2	42.1	34.9	27.8	24.2	24.3	24.6	24.9	25.2	25.5	25.2

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	132.9	102.0	71.1	40.2	24.8	24.9	25.1	25.4	25.6	25.8	25.6
115°	165.7	132.5	99.4	66.2	49.6	47.0	41.9	36.7	31.6	26.4	31.6
117.5°	206.1	195.8	185.6	175.3	170.2	160.8	142.1	123.3	104.6	85.8	104.6
120°	237.2	238.0	238.9	239.8	240.2	235.4	225.7	216.0	206.4	196.7	206.4
122.5°	255.7	256.2	256.6	257.1	257.3	257.3	257.4	257.5	257.5	257.6	257.5
125°	272.9	273.4	273.9	274.4	274.7	274.8	275.0	275.3	275.5	275.7	275.5
127.5°	288.9	289.6	290.3	291.0	291.4	291.4	291.5	291.6	291.7	291.8	291.7
130°	304.2	305.0	305.7	306.5	306.9	306.9	306.8	306.7	306.7	306.6	306.7
132.5°	319.1	319.8	320.4	321.1	321.4	321.4	321.3	321.2	321.2	321.1	321.2
135°	333.1	333.8	334.5	335.2	335.6	335.5	335.4	335.3	335.1	335.0	335.1
137.5°	346.3	347.0	347.7	348.4	348.8	348.7	348.5	348.3	348.1	347.9	348.1
140°	359.1	359.8	360.4	361.1	361.4	361.2	360.9	360.5	360.2	359.8	360.2
142.5°	371.0	371.6	372.1	372.7	373.0	372.8	372.5	372.1	371.8	371.4	371.8
145°	381.9	382.4	382.9	383.4	383.7	383.5	383.1	382.8	382.4	382.0	382.4
147.5°	391.8	392.1	392.5	392.8	393.0	392.9	392.6	392.3	392.0	391.7	392.0
150°	400.5	400.9	401.4	401.8	402.0	401.8	401.5	401.1	400.8	400.4	400.8
152.5°	408.6	409.0	409.5	409.9	410.1	409.8	409.3	408.8	408.3	407.8	408.3
155°	415.7	416.1	416.6	417.0	417.2	416.9	416.3	415.8	415.2	414.6	415.2
157.5°	421.9	422.4	422.9	423.4	423.6	423.3	422.8	422.2	421.7	421.1	421.7
160°	427.3	427.7	428.2	428.6	428.8	428.5	428.0	427.5	427.0	426.5	427.0
162.5°	432.2	432.7	433.2	433.7	434.0	433.7	433.0	432.3	431.7	431.0	431.7
165°	436.1	436.6	437.1	437.6	437.8	437.6	437.1	436.6	436.1	435.6	436.1
167.5°	439.6	440.1	440.6	441.1	441.4	441.1	440.4	439.8	439.1	438.5	439.1
170°	442.2	442.7	443.2	443.7	443.9	443.6	442.9	442.3	441.6	441.0	441.6
172.5°	444.1	444.6	445.1	445.6	445.9	445.6	444.9	444.3	443.6	443.0	443.6
175°	445.4	445.9	446.4	446.9	447.2	446.8	446.1	445.4	444.6	443.9	444.6
177.5°	445.7	446.2	446.7	447.2	447.5	447.2	446.5	445.9	445.2	444.6	445.2
180°	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1803.5	1794.3	1786.5	1787.8	1794.3	1789.1	1776.0	1759.0	1752.5	1744.6	1752.5
5°	1912.0	1904.2	1888.5	1889.8	1885.9	1880.7	1859.7	1833.6	1833.6	1812.7	1810.0
7.5°	2019.3	2007.5	1997.1	1994.4	1980.1	1969.6	1951.3	1914.7	1900.3	1875.4	1861.0
10°	2139.6	2130.5	2118.7	2104.3	2096.5	2078.1	2048.1	1994.4	1968.3	1934.3	1909.4
12.5°	2261.2	2259.9	2233.8	2205.0	2203.7	2174.9	2154.0	2082.1	2046.8	2001.0	1942.1
15°	2338.4	2331.9	2317.5	2303.1	2307.0	2275.6	2228.5	2143.5	2120.0	2065.1	2002.3
17.5°	2337.1	2337.1	2333.2	2330.6	2326.6	2317.5	2291.3	2235.1	2197.2	2127.8	2069.0
20°	2262.5	2279.5	2283.5	2282.2	2295.2	2301.8	2300.5	2265.2	2235.1	2173.6	2113.5
22.5°	2113.5	2152.7	2169.7	2180.2	2207.6	2222.0	2256.0	2242.9	2235.1	2189.3	2138.3
25°	1974.8	1987.9	2038.9	2041.5	2079.5	2114.8	2148.8	2171.0	2199.8	2182.8	2139.6
27.5°	1795.7	1825.7	1862.4	1889.8	1897.7	1969.6	2025.8	2067.7	2133.1	2138.3	2123.9
30°	1592.9	1607.3	1667.5	1704.1	1746.0	1798.3	1879.4	1951.3	2010.1	2063.8	2082.1
32.5°	1345.8	1404.6	1439.9	1484.4	1521.0	1613.9	1713.3	1806.1	1874.1	1964.4	2003.6
35°	1119.5	1165.3	1225.4	1243.7	1310.4	1388.9	1518.4	1637.4	1740.7	1832.3	1912.0
37.5°	932.5	969.1	1033.2	1062.0	1101.2	1201.9	1310.4	1458.2	1582.5	1694.9	1794.3
40°	804.3	831.8	880.2	889.3	922.0	1013.6	1101.2	1239.8	1404.6	1556.3	1664.9
42.5°	716.7	729.8	762.5	774.2	795.2	856.6	935.1	1065.9	1218.9	1375.8	1528.9
45°	653.9	663.1	682.7	693.2	719.3	746.8	810.9	915.5	1035.8	1194.0	1358.8
47.5°	597.7	609.4	617.3	623.8	638.2	668.3	710.2	787.3	902.4	1047.6	1207.1
50°	550.6	554.5	568.9	570.2	579.4	599.0	638.2	685.3	776.9	894.6	1048.9
52.5°	503.5	507.4	516.6	525.7	529.7	545.4	571.5	610.8	678.8	771.6	908.9
55°	456.4	461.7	470.8	477.4	481.3	494.4	510.1	548.0	601.6	667.0	779.5
57.5°	409.4	421.1	423.7	427.7	434.2	448.6	463.0	485.2	527.1	587.2	669.6
60°	364.9	368.8	378.0	381.9	388.4	396.3	414.6	431.6	461.7	508.7	583.3
62.5°	319.1	328.3	332.2	336.1	341.3	350.5	362.3	380.6	406.7	444.7	503.5
65°	279.9	281.2	289.0	294.3	299.5	306.0	317.8	334.8	350.5	385.8	429.0
67.5°	241.9	244.6	247.2	252.4	259.0	265.5	276.0	285.1	304.7	328.3	362.3
70°	205.3	205.3	211.9	215.8	214.5	222.3	230.2	240.6	255.0	277.3	304.7
72.5°	172.6	171.3	176.6	177.9	180.5	185.7	190.9	201.4	209.3	226.3	247.2
75°	137.3	139.9	142.6	142.6	146.5	150.4	155.6	160.9	170.0	180.5	196.2
77.5°	108.5	108.5	111.2	112.5	116.4	115.1	120.3	125.6	132.1	141.2	153.0
80°	79.8	82.4	82.4	82.4	83.7	85.0	90.2	94.2	98.1	104.6	109.9
82.5°	56.2	56.2	58.9	58.9	58.9	61.5	61.5	62.8	65.4	69.3	73.2
85°	35.3	35.3	35.3	36.6	35.3	36.6	39.2	37.9	39.2	41.9	41.9
87.5°	17.0	17.0	17.0	17.0	17.0	18.3	17.0	18.3	19.6	19.6	19.6
90°	8.4	8.3	8.2	8.1	7.9	7.5	7.2	6.8	6.4	5.8	5.3
92.5°	8.6	8.5	8.4	8.4	8.3	8.2	8.0	7.9	7.7	7.5	7.3
95°	14.0	14.1	14.2	14.2	14.0	13.7	13.3	13.0	12.6	12.1	11.6
97.5°	17.6	17.5	17.4	17.4	17.3	17.1	16.8	16.6	16.4	15.3	14.1
100°	21.3	21.2	21.1	21.0	20.7	20.1	19.6	19.0	18.4	17.2	16.0
102.5°	23.1	22.9	22.7	22.6	22.2	21.4	20.6	19.8	19.0	32.0	45.1
105°	23.9	23.6	23.3	23.2	22.8	22.0	21.3	20.5	19.7	39.3	58.8
107.5°	24.6	24.3	24.0	23.9	23.5	22.7	21.9	21.1	20.3	44.5	68.6
110°	24.9	24.6	24.3	24.2	27.8	34.9	42.1	49.2	56.4	77.1	97.8

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	25.4	25.1	24.9	24.8	40.2	71.1	102.0	132.9	163.8	165.0	166.2
115°	36.7	41.9	47.0	49.6	66.2	99.4	132.5	165.7	198.9	197.1	195.3
117.5°	123.3	142.1	160.8	170.2	175.3	185.6	195.8	206.1	216.3	215.1	213.9
120°	216.0	225.7	235.4	240.2	239.8	238.9	238.0	237.2	236.3	235.0	233.7
122.5°	257.5	257.4	257.3	257.3	257.1	256.6	256.2	255.7	255.3	253.9	252.5
125°	275.3	275.0	274.8	274.7	274.4	273.9	273.4	272.9	272.4	271.0	269.7
127.5°	291.6	291.5	291.4	291.4	291.0	290.3	289.6	288.9	288.2	287.1	286.1
130°	306.7	306.8	306.9	306.9	306.5	305.7	305.0	304.2	303.4	302.6	301.8
132.5°	321.2	321.3	321.4	321.4	321.1	320.4	319.8	319.1	318.5	317.7	316.9
135°	335.3	335.4	335.5	335.6	335.2	334.5	333.8	333.1	332.4	331.8	331.1
137.5°	348.3	348.5	348.7	348.8	348.4	347.7	347.0	346.3	345.6	344.9	344.2
140°	360.5	360.9	361.2	361.4	361.1	360.4	359.8	359.1	358.5	357.7	356.9
142.5°	372.1	372.5	372.8	373.0	372.7	372.1	371.6	371.0	370.4	369.5	368.5
145°	382.8	383.1	383.5	383.7	383.4	382.9	382.4	381.9	381.4	380.2	379.0
147.5°	392.3	392.6	392.9	393.0	392.8	392.5	392.1	391.8	391.4	390.2	389.0
150°	401.1	401.5	401.8	402.0	401.8	401.4	400.9	400.5	400.1	398.9	397.8
152.5°	408.8	409.3	409.8	410.1	409.9	409.5	409.0	408.6	408.2	407.1	406.0
155°	415.8	416.3	416.9	417.2	417.0	416.6	416.1	415.7	415.3	414.4	413.6
157.5°	422.2	422.8	423.3	423.6	423.4	422.9	422.4	421.9	421.4	420.8	420.1
160°	427.5	428.0	428.5	428.8	428.6	428.2	427.7	427.3	426.9	426.5	426.0
162.5°	432.3	433.0	433.7	434.0	433.7	433.2	432.7	432.2	431.7	431.3	431.0
165°	436.6	437.1	437.6	437.8	437.6	437.1	436.6	436.1	435.6	435.4	435.2
167.5°	439.8	440.4	441.1	441.4	441.1	440.6	440.1	439.6	439.1	438.9	438.7
170°	442.3	442.9	443.6	443.9	443.7	443.2	442.7	442.2	441.7	441.5	441.4
172.5°	444.3	444.9	445.6	445.9	445.6	445.1	444.6	444.1	443.6	443.5	443.3
175°	445.4	446.1	446.8	447.2	446.9	446.4	445.9	445.4	444.9	444.8	444.6
177.5°	445.9	446.5	447.2	447.5	447.2	446.7	446.2	445.7	445.2	445.1	445.1
180°	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1746.0	1739.4	1735.5	1738.1	1730.3	1710.6	1710.6	1717.2	1709.3	1701.5	1689.7
5°	1794.3	1781.3	1773.4	1772.1	1753.8	1722.4	1715.9	1709.3	1692.3	1674.0	1654.4
7.5°	1841.4	1817.9	1804.8	1795.7	1769.5	1729.0	1712.0	1697.6	1670.1	1642.6	1617.8
10°	1880.7	1846.7	1831.0	1816.6	1782.6	1731.6	1704.1	1677.9	1642.6	1607.3	1575.9
12.5°	1912.0	1872.8	1853.2	1832.3	1790.4	1723.7	1689.7	1647.9	1612.6	1565.5	1534.1
15°	1964.4	1883.3	1865.0	1845.3	1802.2	1710.6	1668.8	1621.7	1573.3	1510.5	1476.5
17.5°	2006.2	1897.7	1896.4	1854.5	1798.3	1705.4	1641.3	1579.9	1527.5	1464.8	1411.1
20°	2031.1	1919.9	1899.0	1855.8	1785.2	1670.1	1603.4	1535.4	1479.2	1403.3	1349.7
22.5°	2052.0	1951.3	1896.4	1844.0	1757.7	1658.3	1560.2	1496.2	1419.0	1336.6	1285.6
25°	2059.8	1957.8	1900.3	1840.1	1738.1	1624.3	1513.2	1443.8	1357.5	1283.0	1213.7
27.5°	2061.1	1956.5	1885.9	1823.1	1710.6	1579.9	1466.1	1392.8	1297.4	1211.1	1141.7
30°	2048.1	1942.1	1878.0	1810.0	1684.5	1539.3	1408.5	1327.4	1225.4	1139.1	1067.2
32.5°	2008.8	1913.4	1861.0	1786.5	1650.5	1483.1	1353.6	1263.4	1156.1	1071.1	1001.8
35°	1943.4	1878.0	1820.5	1751.2	1606.0	1430.8	1298.7	1192.7	1084.2	1003.1	937.7
37.5°	1862.4	1827.0	1773.4	1705.4	1555.0	1383.7	1237.2	1119.5	1011.0	932.5	868.4
40°	1752.5	1761.6	1709.3	1647.9	1494.9	1319.6	1157.4	1045.0	942.9	869.7	806.9
42.5°	1633.5	1671.4	1641.3	1582.5	1428.2	1249.0	1098.6	974.3	874.9	799.1	746.8
45°	1505.3	1570.7	1552.4	1509.2	1358.8	1174.4	1014.9	894.6	806.9	733.7	687.9
47.5°	1365.4	1458.2	1458.2	1426.8	1281.7	1099.9	942.9	820.0	733.7	681.4	636.9
50°	1222.8	1327.4	1344.4	1323.5	1195.4	1014.9	855.3	744.2	669.6	618.6	585.9
52.5°	1073.7	1195.4	1226.7	1216.3	1103.8	933.8	783.4	674.8	606.8	562.4	533.6
55°	931.2	1072.4	1106.4	1110.3	1005.7	844.9	703.6	608.1	542.7	512.7	487.8
57.5°	796.5	932.5	970.4	976.9	906.3	763.8	629.1	545.4	486.5	461.7	442.0
60°	681.4	795.2	844.9	859.2	797.8	669.6	559.8	478.7	434.2	410.7	392.3
62.5°	587.2	678.8	731.1	735.0	707.5	587.2	487.8	419.8	381.9	361.0	351.8
65°	495.7	578.1	609.4	625.1	602.9	508.7	421.1	364.9	334.8	316.5	307.3
67.5°	422.4	474.7	500.9	521.8	499.6	429.0	358.3	312.6	290.3	272.0	266.8
70°	346.6	389.7	409.4	430.3	410.7	357.0	306.0	264.2	244.6	230.2	223.6
72.5°	277.3	311.3	329.6	342.7	330.9	286.4	244.6	215.8	201.4	190.9	187.0
75°	219.7	243.3	253.7	262.9	257.6	223.6	197.5	173.9	160.9	151.7	149.1
77.5°	167.4	184.4	196.2	198.8	192.3	170.0	147.8	133.4	122.9	117.7	115.1
80°	119.0	129.5	136.0	139.9	133.4	124.2	108.5	98.1	88.9	82.4	81.1
82.5°	79.8	85.0	90.2	88.9	86.3	78.5	69.3	64.1	60.2	54.9	54.9
85°	45.8	47.1	49.7	51.0	49.7	44.5	39.2	36.6	34.0	30.1	30.1
87.5°	19.6	20.9	20.9	22.2	19.6	19.6	17.0	14.4	14.4	13.1	11.8
90°	4.7	4.2	3.9	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.1	6.9	6.8	6.9	7.2	7.5	7.8	8.1	7.8	7.5	7.2
95°	11.1	10.6	10.3	11.5	13.9	16.2	18.6	21.0	18.6	16.2	13.9
97.5°	13.0	11.9	11.3	14.2	20.1	26.0	31.8	37.7	31.8	26.0	20.1
100°	14.7	13.5	12.9	17.8	27.6	37.5	47.3	57.1	47.3	37.5	27.6
102.5°	58.1	71.2	77.7	77.8	77.9	78.0	78.2	78.3	78.2	78.0	77.9
105°	78.4	97.9	107.7	106.6	104.5	102.3	100.2	98.0	100.2	102.3	104.5
107.5°	92.8	116.9	129.0	128.1	126.3	124.5	122.7	120.9	122.7	124.5	126.3
110°	118.5	139.2	149.6	148.8	147.3	145.8	144.3	142.8	144.3	145.8	147.3

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	167.5	168.7	169.3	168.7	167.4	166.1	164.8	163.5	164.8	166.1	167.4
115°	193.6	191.8	190.9	190.3	189.1	187.8	186.6	185.4	186.6	187.8	189.1
117.5°	212.6	211.4	210.8	210.1	208.7	207.2	205.8	204.4	205.8	207.2	208.7
120°	232.4	231.1	230.5	230.0	228.9	227.8	226.8	225.7	226.8	227.8	228.9
122.5°	251.0	249.6	248.9	248.3	247.2	246.0	244.9	243.7	244.9	246.0	247.2
125°	268.3	267.0	266.3	265.8	264.9	264.0	263.0	262.1	263.0	264.0	264.9
127.5°	285.0	283.9	283.4	282.9	281.9	280.9	279.9	278.9	279.9	280.9	281.9
130°	301.0	300.2	299.8	299.2	298.1	297.0	295.8	294.7	295.8	297.0	298.1
132.5°	316.2	315.4	315.0	314.5	313.6	312.7	311.7	310.8	311.7	312.7	313.6
135°	330.5	329.8	329.5	328.9	327.8	326.6	325.5	324.3	325.5	326.6	327.8
137.5°	343.5	342.8	342.4	342.0	341.1	340.2	339.4	338.5	339.4	340.2	341.1
140°	356.2	355.4	355.0	354.7	354.1	353.6	353.0	352.4	353.0	353.6	354.1
142.5°	367.6	366.7	366.2	366.0	365.5	365.0	364.5	364.0	364.5	365.0	365.5
145°	377.7	376.5	375.9	375.9	376.0	376.1	376.1	376.2	376.1	376.1	376.0
147.5°	387.7	386.5	385.9	386.0	386.2	386.5	386.7	386.9	386.7	386.5	386.2
150°	396.6	395.5	394.9	395.2	395.7	396.2	396.7	397.2	396.7	396.2	395.7
152.5°	404.9	403.8	403.3	403.6	404.2	404.7	405.3	405.9	405.3	404.7	404.2
155°	412.7	411.8	411.4	411.7	412.4	413.0	413.7	414.3	413.7	413.0	412.4
157.5°	419.5	418.8	418.5	418.8	419.4	419.9	420.5	421.1	420.5	419.9	419.4
160°	425.6	425.1	424.9	425.1	425.6	426.0	426.5	426.9	426.5	426.0	425.6
162.5°	430.6	430.3	430.1	430.3	430.7	431.2	431.6	432.0	431.6	431.2	430.7
165°	434.9	434.7	434.6	434.8	435.2	435.7	436.1	436.5	436.1	435.7	435.2
167.5°	438.4	438.2	438.1	438.3	438.8	439.2	439.7	440.1	439.7	439.2	438.8
170°	441.2	441.1	441.0	441.2	441.7	442.1	442.6	443.0	442.6	442.1	441.7
172.5°	443.2	443.1	443.0	443.2	443.6	444.1	444.5	444.9	444.5	444.1	443.6
175°	444.5	444.4	444.3	444.5	445.0	445.5	446.0	446.5	446.0	445.5	445.0
177.5°	445.0	444.9	444.9	445.2	445.7	446.2	446.7	447.2	446.7	446.2	445.7
180°	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1683.2	1689.7	1688.4	1675.3	1660.9	1649.2	1626.9	1629.6	1621.7	1623.0	1630.9
5°	1641.3	1641.3	1636.1	1617.8	1594.2	1581.2	1556.3	1549.8	1534.1	1532.8	1531.5
7.5°	1596.9	1590.3	1583.8	1557.6	1528.9	1507.9	1473.9	1466.1	1450.4	1439.9	1434.7
10°	1544.5	1535.4	1522.3	1492.2	1456.9	1430.8	1395.5	1385.0	1354.9	1341.8	1334.0
12.5°	1487.0	1481.8	1460.8	1436.0	1378.5	1349.7	1298.7	1309.1	1279.1	1252.9	1249.0
15°	1429.5	1409.8	1398.1	1357.5	1288.2	1275.1	1234.6	1213.7	1186.2	1165.3	1165.3
17.5°	1373.2	1343.1	1317.0	1273.8	1222.8	1186.2	1156.1	1145.7	1111.7	1090.7	1086.8
20°	1298.7	1264.7	1258.1	1196.7	1161.4	1120.8	1092.0	1065.9	1041.0	1031.9	1025.3
22.5°	1228.1	1188.8	1178.4	1126.0	1090.7	1050.2	1021.4	1003.1	984.8	978.3	966.5
25°	1152.2	1128.7	1113.0	1056.7	1017.5	979.6	959.9	946.9	929.9	928.6	920.7
27.5°	1079.0	1056.7	1041.0	987.4	958.6	923.3	907.6	893.2	884.1	880.2	876.2
30°	1016.2	991.3	973.0	933.8	898.5	869.7	856.6	847.5	842.2	835.7	834.4
32.5°	946.9	932.5	907.6	877.6	850.1	822.6	814.8	808.2	800.4	797.8	796.5
35°	888.0	868.4	852.7	818.7	806.9	783.4	774.2	769.0	758.5	755.9	753.3
37.5°	830.5	812.2	795.2	774.2	752.0	738.9	733.7	725.8	720.6	721.9	719.3
40°	772.9	758.5	745.5	723.2	710.2	703.6	693.2	685.3	682.7	684.0	682.7
42.5°	716.7	703.6	695.8	678.8	665.7	659.1	652.6	644.8	648.7	648.7	652.6
45°	665.7	653.9	648.7	635.6	627.8	617.3	610.8	609.4	614.7	613.4	613.4
47.5°	613.4	609.4	602.9	591.1	580.7	574.1	572.8	572.8	578.1	580.7	579.4
50°	572.8	565.0	557.1	548.0	540.1	537.5	533.6	536.2	541.4	541.4	544.1
52.5°	521.8	516.6	514.0	506.1	500.9	500.9	500.9	502.2	506.1	510.1	508.7
55°	477.4	473.4	470.8	466.9	460.4	461.7	460.4	463.0	466.9	470.8	473.4
57.5°	430.3	429.0	426.4	419.8	419.8	418.5	422.4	423.7	430.3	432.9	436.8
60°	388.4	384.5	384.5	379.3	379.3	379.3	383.2	387.1	392.3	393.7	396.3
62.5°	344.0	344.0	342.7	338.7	338.7	342.7	344.0	349.2	351.8	351.8	355.7
65°	302.1	300.8	299.5	300.8	302.1	302.1	306.0	308.6	311.3	312.6	313.9
67.5°	260.3	259.0	261.6	260.3	262.9	268.1	266.8	270.7	274.6	274.6	276.0
70°	221.0	223.6	222.3	224.9	223.6	226.3	230.2	231.5	231.5	232.8	236.7
72.5°	184.4	184.4	184.4	183.1	184.4	187.0	189.6	190.9	193.6	194.9	198.8
75°	149.1	149.1	146.5	149.1	149.1	151.7	154.3	154.3	154.3	156.9	160.9
77.5°	112.5	113.8	112.5	115.1	115.1	116.4	119.0	117.7	120.3	121.6	122.9
80°	82.4	81.1	81.1	81.1	82.4	82.4	85.0	86.3	86.3	90.2	87.6
82.5°	52.3	53.6	52.3	53.6	53.6	54.9	53.6	54.9	56.2	58.9	57.5
85°	30.1	28.8	28.8	30.1	28.8	28.8	30.1	28.8	30.1	28.8	30.1
87.5°	11.8	10.5	10.5	10.5	10.5	9.2	9.2	7.8	7.8	7.8	6.5
90°	3.5	3.9	4.2	4.7	5.3	5.8	6.4	6.8	7.2	7.5	7.9
92.5°	6.9	6.8	6.9	7.1	7.3	7.5	7.7	7.9	8.0	8.2	8.3
95°	11.5	10.3	10.6	11.1	11.6	12.1	12.6	13.0	13.3	13.7	14.0
97.5°	14.2	11.3	11.9	13.0	14.1	15.3	16.4	16.6	16.8	17.1	17.3
100°	17.8	12.9	13.5	14.7	16.0	17.2	18.4	19.0	19.6	20.1	20.7
102.5°	77.8	77.7	71.2	58.1	45.1	32.0	19.0	19.8	20.6	21.4	22.2
105°	106.6	107.7	97.9	78.4	58.8	39.3	19.7	20.5	21.3	22.0	22.8
107.5°	128.1	129.0	116.9	92.8	68.6	44.5	20.3	21.1	21.9	22.7	23.5
110°	148.8	149.6	139.2	118.5	97.8	77.1	56.4	49.2	42.1	34.9	27.8

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	168.7	169.3	168.7	167.5	166.2	165.0	163.8	132.9	102.0	71.1	40.2
115°	190.3	190.9	191.8	193.6	195.3	197.1	198.9	165.7	132.5	99.4	66.2
117.5°	210.1	210.8	211.4	212.6	213.9	215.1	216.3	206.1	195.8	185.6	175.3
120°	230.0	230.5	231.1	232.4	233.7	235.0	236.3	237.2	238.0	238.9	239.8
122.5°	248.3	248.9	249.6	251.0	252.5	253.9	255.3	255.7	256.2	256.6	257.1
125°	265.8	266.3	267.0	268.3	269.7	271.0	272.4	272.9	273.4	273.9	274.4
127.5°	282.9	283.4	283.9	285.0	286.1	287.1	288.2	288.9	289.6	290.3	291.0
130°	299.2	299.8	300.2	301.0	301.8	302.6	303.4	304.2	305.0	305.7	306.5
132.5°	314.5	315.0	315.4	316.2	316.9	317.7	318.5	319.1	319.8	320.4	321.1
135°	328.9	329.5	329.8	330.5	331.1	331.8	332.4	333.1	333.8	334.5	335.2
137.5°	342.0	342.4	342.8	343.5	344.2	344.9	345.6	346.3	347.0	347.7	348.4
140°	354.7	355.0	355.4	356.2	356.9	357.7	358.5	359.1	359.8	360.4	361.1
142.5°	366.0	366.2	366.7	367.6	368.5	369.5	370.4	371.0	371.6	372.1	372.7
145°	375.9	375.9	376.5	377.7	379.0	380.2	381.4	381.9	382.4	382.9	383.4
147.5°	386.0	385.9	386.5	387.7	389.0	390.2	391.4	391.8	392.1	392.5	392.8
150°	395.2	394.9	395.5	396.6	397.8	398.9	400.1	400.5	400.9	401.4	401.8
152.5°	403.6	403.3	403.8	404.9	406.0	407.1	408.2	408.6	409.0	409.5	409.9
155°	411.7	411.4	411.8	412.7	413.6	414.4	415.3	415.7	416.1	416.6	417.0
157.5°	418.8	418.5	418.8	419.5	420.1	420.8	421.4	421.9	422.4	422.9	423.4
160°	425.1	424.9	425.1	425.6	426.0	426.5	426.9	427.3	427.7	428.2	428.6
162.5°	430.3	430.1	430.3	430.6	431.0	431.3	431.7	432.2	432.7	433.2	433.7
165°	434.8	434.6	434.7	434.9	435.2	435.4	435.6	436.1	436.6	437.1	437.6
167.5°	438.3	438.1	438.2	438.4	438.7	438.9	439.1	439.6	440.1	440.6	441.1
170°	441.2	441.0	441.1	441.2	441.4	441.5	441.7	442.2	442.7	443.2	443.7
172.5°	443.2	443.0	443.1	443.2	443.3	443.5	443.6	444.1	444.6	445.1	445.6
175°	444.5	444.3	444.4	444.5	444.6	444.8	444.9	445.4	445.9	446.4	446.9
177.5°	445.2	444.9	444.9	445.0	445.1	445.1	445.2	445.7	446.2	446.7	447.2
180°	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1621.7	1625.6	1616.5	1613.9	1616.5	1607.3	1609.9	1612.6	1612.6	1616.5	1619.1
5°	1527.5	1522.3	1513.2	1510.5	1507.9	1511.9	1509.2	1513.2	1514.5	1523.6	1524.9
7.5°	1434.7	1426.8	1419.0	1411.1	1408.5	1402.0	1408.5	1408.5	1417.7	1415.1	1421.6
10°	1324.8	1323.5	1313.1	1309.1	1303.9	1293.4	1307.8	1303.9	1310.4	1322.2	1324.8
12.5°	1243.7	1229.4	1235.9	1217.6	1224.1	1213.7	1215.0	1215.0	1225.4	1226.7	1224.1
15°	1166.6	1154.8	1137.8	1130.0	1126.0	1120.8	1137.8	1139.1	1131.3	1149.6	1143.0
17.5°	1088.1	1088.1	1072.4	1068.5	1058.0	1063.3	1060.7	1062.0	1059.3	1072.4	1079.0
20°	1020.1	1013.6	1008.3	1009.6	996.6	994.0	991.3	994.0	1003.1	1012.3	1014.9
22.5°	965.2	961.3	948.2	950.8	940.3	944.3	941.6	948.2	949.5	949.5	958.6
25°	912.9	907.6	908.9	903.7	899.8	899.8	895.9	899.8	905.0	907.6	908.9
27.5°	873.6	869.7	863.2	859.2	861.9	855.3	860.6	864.5	864.5	861.9	864.5
30°	826.5	829.2	829.2	816.1	821.3	818.7	822.6	825.2	825.2	826.5	823.9
32.5°	795.2	787.3	786.0	784.7	784.7	779.5	779.5	783.4	784.7	786.0	789.9
35°	753.3	753.3	746.8	750.7	745.5	746.8	745.5	746.8	749.4	745.5	749.4
37.5°	715.4	716.7	714.1	716.7	718.0	715.4	712.8	718.0	715.4	715.4	712.8
40°	682.7	681.4	682.7	682.7	682.7	684.0	681.4	681.4	681.4	678.8	676.1
42.5°	655.2	647.4	650.0	651.3	647.4	647.4	648.7	647.4	651.3	643.5	643.5
45°	616.0	613.4	614.7	614.7	617.3	613.4	616.0	617.3	613.4	612.1	609.4
47.5°	580.7	583.3	580.7	583.3	583.3	585.9	580.7	582.0	583.3	578.1	574.1
50°	545.4	545.4	549.3	548.0	549.3	546.7	546.7	545.4	546.7	544.1	540.1
52.5°	512.7	508.7	515.3	514.0	512.7	511.4	510.1	511.4	508.7	506.1	506.1
55°	472.1	472.1	476.1	477.4	477.4	474.7	472.1	473.4	472.1	470.8	469.5
57.5°	439.4	434.2	436.8	438.1	438.1	434.2	436.8	434.2	434.2	435.5	431.6
60°	397.6	397.6	395.0	398.9	398.9	396.3	396.3	397.6	395.0	393.7	392.3
62.5°	353.1	354.4	358.3	359.7	361.0	358.3	355.7	357.0	357.0	353.1	354.4
65°	315.2	317.8	323.0	321.7	319.1	320.4	317.8	319.1	315.2	316.5	312.6
67.5°	278.6	277.3	278.6	278.6	281.2	279.9	277.3	277.3	276.0	279.9	276.0
70°	239.3	239.3	239.3	239.3	240.6	241.9	239.3	236.7	238.0	235.4	234.1
72.5°	198.8	200.1	198.8	201.4	197.5	200.1	200.1	198.8	197.5	197.5	197.5
75°	160.9	163.5	159.6	160.9	159.6	162.2	160.9	160.9	158.2	156.9	158.2
77.5°	122.9	124.2	121.6	122.9	121.6	122.9	122.9	121.6	121.6	121.6	121.6
80°	87.6	88.9	87.6	86.3	85.0	87.6	85.0	86.3	87.6	86.3	88.9
82.5°	56.2	56.2	54.9	56.2	53.6	53.6	54.9	54.9	53.6	56.2	53.6
85°	27.5	27.5	30.1	27.5	26.2	26.2	26.2	27.5	26.2	28.8	27.5
87.5°	6.5	5.2	6.5	6.5	5.2	5.2	6.5	5.2	6.5	7.8	5.2
90°	8.1	8.2	8.3	8.4	8.6	8.7	8.6	8.4	8.3	8.2	8.1
92.5°	8.4	8.4	8.5	8.6	8.6	8.7	8.6	8.6	8.5	8.4	8.4
95°	14.2	14.2	14.1	14.0	14.0	13.9	14.0	14.0	14.1	14.2	14.2
97.5°	17.4	17.4	17.5	17.6	17.6	17.7	17.6	17.6	17.5	17.4	17.4
100°	21.0	21.1	21.2	21.3	21.5	21.6	21.5	21.3	21.2	21.1	21.0
102.5°	22.6	22.7	22.9	23.1	23.3	23.5	23.3	23.1	22.9	22.7	22.6
105°	23.2	23.3	23.6	23.9	24.2	24.5	24.2	23.9	23.6	23.3	23.2
107.5°	23.9	24.0	24.3	24.6	24.8	25.1	24.8	24.6	24.3	24.0	23.9
110°	24.2	24.3	24.6	24.9	25.2	25.5	25.2	24.9	24.6	24.3	24.2

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	24.8	24.9	25.1	25.4	25.6	25.8	25.6	25.4	25.1	24.9	24.8
115°	49.6	47.0	41.9	36.7	31.6	26.4	31.6	36.7	41.9	47.0	49.6
117.5°	170.2	160.8	142.1	123.3	104.6	85.8	104.6	123.3	142.1	160.8	170.2
120°	240.2	235.4	225.7	216.0	206.4	196.7	206.4	216.0	225.7	235.4	240.2
122.5°	257.3	257.3	257.4	257.5	257.5	257.6	257.5	257.5	257.4	257.3	257.3
125°	274.7	274.8	275.0	275.3	275.5	275.7	275.5	275.3	275.0	274.8	274.7
127.5°	291.4	291.4	291.5	291.6	291.7	291.8	291.7	291.6	291.5	291.4	291.4
130°	306.9	306.9	306.8	306.7	306.7	306.6	306.7	306.7	306.8	306.9	306.9
132.5°	321.4	321.4	321.3	321.2	321.2	321.1	321.2	321.2	321.3	321.4	321.4
135°	335.6	335.5	335.4	335.3	335.1	335.0	335.1	335.3	335.4	335.5	335.6
137.5°	348.8	348.7	348.5	348.3	348.1	347.9	348.1	348.3	348.5	348.7	348.8
140°	361.4	361.2	360.9	360.5	360.2	359.8	360.2	360.5	360.9	361.2	361.4
142.5°	373.0	372.8	372.5	372.1	371.8	371.4	371.8	372.1	372.5	372.8	373.0
145°	383.7	383.5	383.1	382.8	382.4	382.0	382.4	382.8	383.1	383.5	383.7
147.5°	393.0	392.9	392.6	392.3	392.0	391.7	392.0	392.3	392.6	392.9	393.0
150°	402.0	401.8	401.5	401.1	400.8	400.4	400.8	401.1	401.5	401.8	402.0
152.5°	410.1	409.8	409.3	408.8	408.3	407.8	408.3	408.8	409.3	409.8	410.1
155°	417.2	416.9	416.3	415.8	415.2	414.6	415.2	415.8	416.3	416.9	417.2
157.5°	423.6	423.3	422.8	422.2	421.7	421.1	421.7	422.2	422.8	423.3	423.6
160°	428.8	428.5	428.0	427.5	427.0	426.5	427.0	427.5	428.0	428.5	428.8
162.5°	434.0	433.7	433.0	432.3	431.7	431.0	431.7	432.3	433.0	433.7	434.0
165°	437.8	437.6	437.1	436.6	436.1	435.6	436.1	436.6	437.1	437.6	437.8
167.5°	441.4	441.1	440.4	439.8	439.1	438.5	439.1	439.8	440.4	441.1	441.4
170°	443.9	443.6	442.9	442.3	441.6	441.0	441.6	442.3	442.9	443.6	443.9
172.5°	445.9	445.6	444.9	444.3	443.6	443.0	443.6	444.3	444.9	445.6	445.9
175°	447.2	446.8	446.1	445.4	444.6	443.9	444.6	445.4	446.1	446.8	447.2
177.5°	447.5	447.2	446.5	445.9	445.2	444.6	445.2	445.9	446.5	447.2	447.5
180°	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5	1701.5
2.5°	1615.2	1625.6	1621.7	1607.3	1624.3	1624.3	1636.1	1636.1	1650.5	1655.7	1663.6
5°	1523.6	1531.5	1538.0	1531.5	1543.2	1561.5	1572.0	1581.2	1600.8	1608.6	1620.4
7.5°	1425.5	1439.9	1446.5	1446.5	1466.1	1487.0	1507.9	1521.0	1548.5	1558.9	1570.7
10°	1330.1	1347.1	1360.1	1358.8	1391.5	1404.6	1430.8	1460.8	1488.3	1504.0	1521.0
12.5°	1229.4	1238.5	1256.8	1283.0	1290.8	1314.4	1344.4	1382.4	1432.1	1446.5	1471.3
15°	1145.7	1170.5	1184.9	1196.7	1215.0	1237.2	1269.9	1306.5	1356.2	1387.6	1413.8
17.5°	1075.0	1107.7	1116.9	1114.3	1137.8	1171.8	1209.7	1237.2	1281.7	1319.6	1344.4
20°	1017.5	1030.6	1046.3	1052.8	1071.1	1107.7	1144.4	1175.7	1212.4	1242.4	1271.2
22.5°	959.9	970.4	983.5	995.3	1009.6	1030.6	1065.9	1105.1	1140.4	1169.2	1201.9
25°	912.9	919.4	931.2	940.3	956.0	970.4	995.3	1038.4	1080.3	1097.3	1126.0
27.5°	867.1	872.3	880.2	890.6	898.5	912.9	935.1	970.4	1013.6	1030.6	1069.8
30°	826.5	830.5	838.3	843.6	847.5	864.5	881.5	908.9	941.6	965.2	994.0
32.5°	788.6	792.5	800.4	801.7	806.9	816.1	831.8	856.6	885.4	905.0	929.9
35°	746.8	749.4	757.2	759.8	763.8	771.6	783.4	801.7	827.9	842.2	864.5
37.5°	714.1	712.8	718.0	721.9	727.2	731.1	735.0	753.3	772.9	786.0	803.0
40°	678.8	676.1	677.5	682.7	685.3	690.5	690.5	708.8	721.9	732.4	745.5
42.5°	643.5	642.1	639.5	642.1	644.8	646.1	647.4	660.5	673.5	682.7	697.1
45°	608.1	606.8	604.2	605.5	605.5	608.1	612.1	617.3	626.5	634.3	642.1
47.5°	575.4	572.8	568.9	567.6	570.2	570.2	570.2	575.4	584.6	587.2	595.1
50°	541.4	537.5	532.3	529.7	529.7	528.4	531.0	532.3	540.1	542.7	549.3
52.5°	504.8	502.2	497.0	491.7	493.1	490.4	491.7	493.1	495.7	499.6	503.5
55°	468.2	463.0	459.0	457.7	453.8	453.8	449.9	455.1	453.8	455.1	460.4
57.5°	432.9	427.7	421.1	418.5	414.6	413.3	410.7	409.4	410.7	414.6	418.5
60°	391.0	388.4	384.5	380.6	378.0	374.0	371.4	371.4	370.1	370.1	371.4
62.5°	350.5	349.2	344.0	342.7	340.0	337.4	333.5	330.9	330.9	333.5	334.8
65°	311.3	310.0	306.0	304.7	298.2	295.6	294.3	293.0	290.3	290.3	290.3
67.5°	274.6	270.7	270.7	264.2	259.0	256.3	253.7	252.4	252.4	252.4	253.7
70°	234.1	234.1	230.2	226.3	221.0	222.3	218.4	214.5	214.5	211.9	213.2
72.5°	194.9	193.6	189.6	188.3	184.4	180.5	177.9	180.5	176.6	175.2	176.6
75°	156.9	155.6	153.0	150.4	151.7	147.8	143.9	142.6	142.6	139.9	139.9
77.5°	120.3	122.9	117.7	116.4	113.8	111.2	109.9	108.5	108.5	108.5	111.2
80°	83.7	85.0	85.0	82.4	83.7	79.8	79.8	79.8	75.9	77.2	78.5
82.5°	53.6	53.6	52.3	53.6	52.3	52.3	51.0	51.0	49.7	49.7	51.0
85°	30.1	28.8	27.5	30.1	28.8	28.8	27.5	27.5	27.5	27.5	27.5
87.5°	6.5	7.8	7.8	7.8	7.8	9.2	9.2	9.2	10.5	10.5	10.5
90°	7.9	7.5	7.2	6.8	6.4	5.8	5.3	4.7	4.2	3.9	3.5
92.5°	8.3	8.2	8.0	7.9	7.7	7.5	7.3	7.1	6.9	6.8	6.9
95°	14.0	13.7	13.3	13.0	12.6	12.1	11.6	11.1	10.6	10.3	11.5
97.5°	17.3	17.1	16.8	16.6	16.4	15.3	14.1	13.0	11.9	11.3	14.2
100°	20.7	20.1	19.6	19.0	18.4	17.2	16.0	14.7	13.5	12.9	17.8
102.5°	22.2	21.4	20.6	19.8	19.0	32.0	45.1	58.1	71.2	77.7	77.8
105°	22.8	22.0	21.3	20.5	19.7	39.3	58.8	78.4	97.9	107.7	106.6
107.5°	23.5	22.7	21.9	21.1	20.3	44.5	68.6	92.8	116.9	129.0	128.1
110°	27.8	34.9	42.1	49.2	56.4	77.1	97.8	118.5	139.2	149.6	148.8

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	40.2	71.1	102.0	132.9	163.8	165.0	166.2	167.5	168.7	169.3	168.7
115°	66.2	99.4	132.5	165.7	198.9	197.1	195.3	193.6	191.8	190.9	190.3
117.5°	175.3	185.6	195.8	206.1	216.3	215.1	213.9	212.6	211.4	210.8	210.1
120°	239.8	238.9	238.0	237.2	236.3	235.0	233.7	232.4	231.1	230.5	230.0
122.5°	257.1	256.6	256.2	255.7	255.3	253.9	252.5	251.0	249.6	248.9	248.3
125°	274.4	273.9	273.4	272.9	272.4	271.0	269.7	268.3	267.0	266.3	265.8
127.5°	291.0	290.3	289.6	288.9	288.2	287.1	286.1	285.0	283.9	283.4	282.9
130°	306.5	305.7	305.0	304.2	303.4	302.6	301.8	301.0	300.2	299.8	299.2
132.5°	321.1	320.4	319.8	319.1	318.5	317.7	316.9	316.2	315.4	315.0	314.5
135°	335.2	334.5	333.8	333.1	332.4	331.8	331.1	330.5	329.8	329.5	328.9
137.5°	348.4	347.7	347.0	346.3	345.6	344.9	344.2	343.5	342.8	342.4	342.0
140°	361.1	360.4	359.8	359.1	358.5	357.7	356.9	356.2	355.4	355.0	354.7
142.5°	372.7	372.1	371.6	371.0	370.4	369.5	368.5	367.6	366.7	366.2	366.0
145°	383.4	382.9	382.4	381.9	381.4	380.2	379.0	377.7	376.5	375.9	375.9
147.5°	392.8	392.5	392.1	391.8	391.4	390.2	389.0	387.7	386.5	385.9	386.0
150°	401.8	401.4	400.9	400.5	400.1	398.9	397.8	396.6	395.5	394.9	395.2
152.5°	409.9	409.5	409.0	408.6	408.2	407.1	406.0	404.9	403.8	403.3	403.6
155°	417.0	416.6	416.1	415.7	415.3	414.4	413.6	412.7	411.8	411.4	411.7
157.5°	423.4	422.9	422.4	421.9	421.4	420.8	420.1	419.5	418.8	418.5	418.8
160°	428.6	428.2	427.7	427.3	426.9	426.5	426.0	425.6	425.1	424.9	425.1
162.5°	433.7	433.2	432.7	432.2	431.7	431.3	431.0	430.6	430.3	430.1	430.3
165°	437.6	437.1	436.6	436.1	435.6	435.4	435.2	434.9	434.7	434.6	434.8
167.5°	441.1	440.6	440.1	439.6	439.1	438.9	438.7	438.4	438.2	438.1	438.3
170°	443.7	443.2	442.7	442.2	441.7	441.5	441.4	441.2	441.1	441.0	441.2
172.5°	445.6	445.1	444.6	444.1	443.6	443.5	443.3	443.2	443.1	443.0	443.2
175°	446.9	446.4	445.9	445.4	444.9	444.8	444.6	444.5	444.4	444.3	444.5
177.5°	447.2	446.7	446.2	445.7	445.2	445.1	445.1	445.0	444.9	444.9	445.2
180°	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6	445.6

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1701.5	1701.5	1701.5	1701.5
2.5°	1670.1	1670.1	1689.7	1710.6
5°	1633.5	1642.6	1674.0	1702.8
7.5°	1598.2	1613.9	1653.1	1689.7
10°	1555.0	1575.9	1624.3	1667.5
12.5°	1513.2	1532.8	1589.0	1637.4
15°	1454.3	1479.2	1539.3	1599.5
17.5°	1395.5	1420.3	1493.5	1564.2
20°	1326.1	1358.8	1441.2	1535.4
22.5°	1262.1	1302.6	1394.1	1470.0
25°	1191.4	1254.2	1339.2	1437.3
27.5°	1128.7	1191.4	1277.8	1377.1
30°	1058.0	1122.1	1211.1	1302.6
32.5°	990.0	1048.9	1135.2	1247.7
35°	919.4	975.6	1059.3	1173.1
37.5°	855.3	910.3	1001.8	1106.4
40°	792.5	850.1	928.6	1033.2
42.5°	733.7	784.7	855.3	959.9
45°	680.1	716.7	782.1	880.2
47.5°	623.8	656.5	716.7	814.8
50°	571.5	599.0	651.3	742.8
52.5°	520.5	544.1	592.4	665.7
55°	474.7	497.0	532.3	604.2
57.5°	427.7	444.7	478.7	536.2
60°	381.9	397.6	425.0	472.1
62.5°	336.1	349.2	375.3	413.3
65°	295.6	306.0	325.6	358.3
67.5°	256.3	262.9	278.6	304.7
70°	218.4	223.6	236.7	257.6
72.5°	177.9	183.1	197.5	211.9
75°	143.9	145.2	155.6	167.4
77.5°	112.5	111.2	119.0	128.2
80°	77.2	81.1	87.6	91.5
82.5°	52.3	53.6	56.2	58.9
85°	28.8	30.1	30.1	34.0
87.5°	11.8	13.1	13.1	14.4
90°	2.7	1.9	1.1	0.3
92.5°	7.2	7.5	7.8	8.1
95°	13.9	16.2	18.6	21.0
97.5°	20.1	26.0	31.8	37.7
100°	27.6	37.5	47.3	57.1
102.5°	77.9	78.0	78.2	78.3
105°	104.5	102.3	100.2	98.0
107.5°	126.3	124.5	122.7	120.9
110°	147.3	145.8	144.3	142.8



TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	167.4	166.1	164.8	163.5
115°	189.1	187.8	186.6	185.4
117.5°	208.7	207.2	205.8	204.4
120°	228.9	227.8	226.8	225.7
122.5°	247.2	246.0	244.9	243.7
125°	264.9	264.0	263.0	262.1
127.5°	281.9	280.9	279.9	278.9
130°	298.1	297.0	295.8	294.7
132.5°	313.6	312.7	311.7	310.8
135°	327.8	326.6	325.5	324.3
137.5°	341.1	340.2	339.4	338.5
140°	354.1	353.6	353.0	352.4
142.5°	365.5	365.0	364.5	364.0
145°	376.0	376.1	376.1	376.2
147.5°	386.2	386.5	386.7	386.9
150°	395.7	396.2	396.7	397.2
152.5°	404.2	404.7	405.3	405.9
155°	412.4	413.0	413.7	414.3
157.5°	419.4	419.9	420.5	421.1
160°	425.6	426.0	426.5	426.9
162.5°	430.7	431.2	431.6	432.0
165°	435.2	435.7	436.1	436.5
167.5°	438.8	439.2	439.7	440.1
170°	441.7	442.1	442.6	443.0
172.5°	443.6	444.1	444.5	444.9
175°	445.0	445.5	446.0	446.5
177.5°	445.7	446.2	446.7	447.2
180°	445.6	445.6	445.6	445.6

TEST NUMBER: P999038

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.30	20.38	20.03	21.12	22.00	16.80	17.87	17.52	18.61	19.49
	3H	20.13	21.09	20.87	21.84	22.75	18.16	19.12	18.90	19.87	20.78
	4H	20.31	21.21	21.07	21.97	22.90	18.63	19.53	19.39	20.29	21.22
	6H	20.36	21.20	21.13	21.97	22.91	18.95	19.78	19.72	20.55	21.49
	8H	20.35	21.14	21.13	21.93	22.87	19.04	19.83	19.82	20.62	21.56
	12H	20.32	21.08	21.10	21.86	22.82	19.08	19.84	19.87	20.62	21.59
4H	2H	19.37	20.27	20.13	21.03	21.96	17.27	18.17	18.03	18.93	19.86
	3H	20.37	21.12	21.14	21.92	22.86	18.75	19.50	19.52	20.29	21.24
	4H	20.65	21.34	21.44	22.13	23.10	19.29	19.97	20.08	20.77	21.74
	6H	20.80	21.38	21.60	22.20	23.18	19.68	20.27	20.49	21.09	22.07
	8H	20.80	21.35	21.61	22.16	23.15	19.79	20.34	20.60	21.16	22.15
	12H	20.77	21.26	21.60	22.10	23.10	19.86	20.35	20.69	21.19	22.19
8H	4H	20.68	21.23	21.49	22.04	23.03	19.45	20.00	20.26	20.81	21.80
	6H	20.86	21.32	21.70	22.18	23.17	19.89	20.34	20.73	21.20	22.19
	8H	20.90	21.30	21.75	22.15	23.16	20.04	20.44	20.89	21.30	22.31
	12H	20.89	21.24	21.74	22.09	23.15	20.14	20.50	20.99	21.34	22.41
12H	4H	20.65	21.14	21.47	21.98	22.97	19.43	19.92	20.26	20.76	21.76
	6H	20.84	21.25	21.69	22.10	23.11	19.89	20.29	20.74	21.15	22.16
	8H	20.89	21.24	21.74	22.09	23.15	20.06	20.41	20.91	21.26	22.32