

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999039

Luminaire Tested: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999039
REPORT IS A COMBINATION OF REPORTS P984788 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5105.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74		
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68	64		
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58	55		
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50	47		
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	41		
5	74	63	54	49	70	60	53	47	55	49	44	50	45	42	46	42	39	36		
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35	32		
7	64	52	44	38	61	50	42	37	46	39	35	42	37	33	39	34	31	29		
8	60	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28	26		
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26	24		
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27163	27163	27163	27163
5°	27228	28962	27333	23041
10°	26912	31616	27080	18997
15°	26259	33348	26624	16002
20°	25850	31312	25850	13908
25°	25027	26900	25140	12438
30°	23670	21146	24123	11266
35°	22469	14623	22845	10307
40°	21089	11040	21330	9543
45°	19387	9073	19704	8719
50°	17916	7962	17947	7981
55°	16238	6785	16342	7181
60°	14450	5667	14647	6268
65°	12848	4609	13082	5351
70°	11251	3616	11537	4317
75°	9443	2626	9812	3131
80°	7369	1663	7896	1858
85°	4845	837	5212	621

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 28078 cd/sqm

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.4	3.2
10°-20°	475.7	9.3
20°-30°	690.4	13.5
30°-40°	727.8	14.3
40°-50°	644.1	12.6
50°-60°	514.3	10.1
60°-70°	349.3	6.8
70°-80°	178.7	3.5
80°-90°	43.0	0.8
90°-100°	14.8	0.3
100°-110°	55.3	1.1
110°-120°	146.6	2.9
120°-130°	243.1	4.8
130°-140°	258.3	5.1
140°-150°	240.0	4.7
150°-160°	193.0	3.8
160°-170°	124.3	2.4
170°-180°	42.8	0.8
0°-30°	1329.6	26.0
0°-40°	2057.4	40.3
0°-60°	3215.7	63.0
0°-90°	3786.8	74.2
90°-120°	216.7	4.2
90°-150°	958.1	18.8
90°-180°	1318.0	25.8
0°-180°	5105.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1716	1716	1716	1716	1716	
5°	1717	1916	1724	1525	1717	163
15°	1613	2356	1636	1130	1613	456
25°	1450	1963	1456	908	1450	663
35°	1183	1068	1203	753	1183	740
45°	888	644	902	619	888	689
55°	609	452	613	479	609	544
65°	361	278	368	323	361	359
75°	169	137	175	164	169	181
85°	34	36	37	26	34	40
90°	0	9	0	9	0	3
95°	21	14	21	14	21	25
105°	99	25	99	25	99	106
115°	187	27	187	27	187	184
125°	264	278	264	278	264	236
135°	327	338	327	338	327	253
145°	380	386	380	386	380	237
155°	418	418	418	418	418	193
165°	440	440	440	440	440	124
175°	451	448	451	448	451	43
180°	450	450	450	450	450	

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1725.2	1729.2	1735.8	1737.1	1750.3	1760.8	1772.7	1772.7	1776.7	1775.3	1764.8
5°	1717.3	1729.2	1746.3	1760.8	1784.6	1795.1	1811.0	1822.8	1833.4	1841.3	1840.0
7.5°	1704.1	1725.2	1750.3	1778.0	1809.6	1828.1	1850.5	1871.6	1886.1	1899.3	1908.6
10°	1681.7	1717.3	1751.6	1788.5	1829.4	1854.5	1880.9	1908.6	1931.0	1956.0	1979.8
12.5°	1651.4	1702.8	1745.0	1793.8	1843.9	1871.6	1913.8	1934.9	1978.5	2041.8	2058.9
15°	1613.1	1683.0	1722.6	1784.6	1850.5	1873.0	1931.0	1965.3	2055.0	2094.5	2142.0
17.5°	1577.5	1655.3	1708.1	1779.3	1843.9	1887.5	1944.2	2014.1	2089.3	2146.0	2198.7
20°	1548.5	1623.7	1687.0	1766.1	1847.9	1903.3	1962.6	2047.1	2128.8	2186.9	2227.8
22.5°	1482.5	1578.8	1652.7	1741.1	1840.0	1916.5	1973.2	2065.5	2153.9	2189.5	2225.1
25°	1449.6	1532.7	1618.4	1718.6	1834.7	1925.7	1974.5	2077.4	2155.2	2168.4	2176.3
27.5°	1388.9	1482.5	1582.8	1697.5	1833.4	1909.9	1971.9	2065.5	2127.5	2118.3	2094.5
30°	1313.7	1428.5	1539.2	1663.2	1814.9	1898.0	1956.0	2041.8	2073.4	2026.0	1983.7
32.5°	1258.3	1366.5	1489.1	1632.9	1793.8	1873.0	1929.7	1996.9	2003.5	1917.8	1846.6
35°	1183.1	1303.2	1441.6	1593.3	1758.2	1829.4	1882.2	1923.1	1891.4	1771.4	1687.0
37.5°	1115.9	1234.6	1382.3	1536.6	1709.4	1779.3	1821.5	1828.1	1750.3	1644.8	1520.8
40°	1042.0	1164.7	1319.0	1481.2	1655.3	1716.0	1742.4	1722.6	1610.5	1487.8	1344.0
42.5°	968.1	1089.5	1255.7	1421.9	1586.7	1638.2	1648.7	1594.6	1457.5	1313.7	1147.5
45°	887.7	1014.3	1180.5	1348.0	1507.6	1536.6	1537.9	1460.1	1297.9	1147.5	993.2
47.5°	821.7	939.1	1104.0	1271.5	1406.0	1425.8	1417.9	1328.2	1151.5	982.6	848.1
50°	749.2	861.3	1024.8	1189.7	1304.5	1309.7	1290.0	1162.0	989.2	834.9	728.1
52.5°	671.4	784.8	935.2	1093.4	1196.3	1188.4	1150.1	1013.0	850.7	722.8	641.0
55°	609.4	709.6	850.7	1005.1	1077.6	1055.2	1013.0	873.2	745.2	637.1	565.8
57.5°	540.8	629.2	767.6	902.2	944.4	923.3	881.1	750.5	631.8	550.0	502.5
60°	476.2	556.6	678.0	790.1	823.0	800.6	751.8	634.4	548.7	480.1	444.5
62.5°	416.8	486.7	588.3	691.1	704.3	681.9	639.7	544.7	470.9	416.8	390.4
65°	361.4	427.3	509.1	586.9	598.8	575.1	531.5	463.0	401.0	366.7	341.6
67.5°	307.3	360.1	432.6	489.3	495.9	473.5	437.9	382.5	344.3	307.3	288.9
70°	259.8	299.4	356.1	402.3	404.9	383.8	365.4	315.2	286.2	259.8	245.3
72.5°	213.7	241.4	284.9	319.2	320.5	307.3	290.2	258.5	233.5	215.0	200.5
75°	168.8	192.6	219.0	249.3	248.0	237.4	224.2	204.4	183.3	171.5	164.9
77.5°	129.3	143.8	164.9	184.7	184.7	179.4	171.5	157.0	143.8	131.9	125.3
80°	92.3	101.6	118.7	125.3	127.9	126.6	120.0	109.5	104.2	95.0	92.3
82.5°	59.4	65.9	73.9	80.5	84.4	81.8	80.5	75.2	67.3	64.6	62.0
85°	34.3	36.9	40.9	44.8	46.2	44.8	47.5	43.5	39.6	39.6	38.3
87.5°	14.5	15.8	18.5	18.5	19.8	19.8	18.5	19.8	19.8	18.5	17.1
90°	0.3	1.1	1.9	2.7	3.5	3.9	4.2	4.8	5.3	5.9	6.5
92.5°	8.1	7.8	7.5	7.2	6.9	6.8	6.9	7.1	7.4	7.6	7.8
95°	21.1	18.7	16.3	14.0	11.6	10.4	10.7	11.2	11.7	12.2	12.7
97.5°	38.1	32.2	26.2	20.3	14.4	11.4	12.0	13.1	14.3	15.4	16.6
100°	57.6	47.7	37.8	27.9	18.0	13.0	13.6	14.8	16.1	17.3	18.5
102.5°	79.1	78.9	78.8	78.6	78.5	78.4	71.8	58.7	45.5	32.4	19.2
105°	98.9	101.1	103.3	105.4	107.6	108.7	98.8	79.1	59.3	39.6	19.8
107.5°	122.0	123.8	125.6	127.4	129.2	130.1	117.9	93.6	69.2	44.9	20.5
110°	144.1	145.6	147.2	148.7	150.2	151.0	140.5	119.6	98.7	77.8	56.9



TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	165.0	166.3	167.6	168.9	170.2	170.8	170.2	169.0	167.7	166.5	165.3
115°	187.1	188.3	189.5	190.8	192.0	192.6	193.5	195.3	197.1	198.9	200.7
117.5°	206.3	207.7	209.2	210.6	212.1	212.8	213.4	214.6	215.9	217.1	218.3
120°	227.8	228.9	229.9	231.0	232.1	232.6	233.3	234.6	235.9	237.2	238.5
122.5°	246.0	247.2	248.3	249.5	250.6	251.2	251.9	253.4	254.8	256.3	257.7
125°	264.5	265.4	266.4	267.3	268.2	268.7	269.4	270.8	272.1	273.5	274.9
127.5°	281.4	282.4	283.4	284.5	285.5	286.0	286.5	287.6	288.7	289.8	290.9
130°	297.4	298.6	299.7	300.9	302.0	302.6	303.0	303.8	304.6	305.4	306.2
132.5°	313.6	314.6	315.5	316.5	317.4	317.9	318.3	319.1	319.9	320.7	321.5
135°	327.3	328.5	329.6	330.8	331.9	332.5	332.8	333.5	334.1	334.8	335.4
137.5°	341.6	342.5	343.3	344.2	345.1	345.5	345.9	346.6	347.3	348.1	348.8
140°	355.6	356.2	356.8	357.3	357.9	358.2	358.6	359.4	360.2	361.0	361.8
142.5°	367.3	367.8	368.3	368.8	369.3	369.6	370.1	371.0	371.9	372.9	373.8
145°	379.7	379.6	379.6	379.5	379.4	379.4	380.0	381.2	382.5	383.7	384.9
147.5°	390.4	390.2	390.0	389.8	389.6	389.5	390.1	391.3	392.6	393.8	395.0
150°	400.8	400.3	399.8	399.3	398.8	398.6	399.2	400.3	401.5	402.6	403.8
152.5°	409.6	409.0	408.4	407.9	407.3	407.0	407.5	408.6	409.7	410.8	411.9
155°	418.1	417.5	416.8	416.2	415.5	415.2	415.6	416.5	417.4	418.2	419.1
157.5°	424.9	424.3	423.7	423.2	422.6	422.3	422.6	423.3	423.9	424.6	425.2
160°	430.8	430.4	429.9	429.5	429.0	428.8	429.0	429.5	429.9	430.4	430.8
162.5°	436.0	435.6	435.1	434.7	434.2	434.0	434.2	434.6	434.9	435.3	435.7
165°	440.5	440.1	439.7	439.2	438.8	438.6	438.7	438.9	439.2	439.4	439.6
167.5°	444.1	443.7	443.3	442.8	442.4	442.2	442.3	442.5	442.7	442.9	443.1
170°	447.0	446.6	446.2	445.7	445.3	445.1	445.2	445.3	445.4	445.6	445.7
172.5°	449.0	448.6	448.1	447.7	447.2	447.0	447.1	447.2	447.4	447.5	447.7
175°	450.6	450.1	449.6	449.1	448.6	448.3	448.4	448.5	448.7	448.8	449.0
177.5°	451.3	450.8	450.3	449.8	449.3	449.0	449.0	449.1	449.2	449.2	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1783.3	1784.6	1787.2	1800.4	1807.0	1808.3	1803.0	1814.9	1818.9	1814.9	1812.3
5°	1867.7	1875.6	1891.4	1908.6	1907.2	1908.6	1916.5	1924.4	1927.0	1916.5	1920.4
7.5°	1941.5	1957.4	1974.5	2000.9	2000.9	2014.1	2019.4	2026.0	2041.8	2033.9	2031.2
10°	2026.0	2047.1	2078.7	2120.9	2122.2	2135.4	2148.6	2169.7	2176.3	2171.0	2173.7
12.5°	2131.5	2172.4	2175.0	2221.2	2242.3	2244.9	2266.0	2262.0	2275.2	2275.2	2297.7
15°	2177.6	2240.9	2276.6	2321.4	2334.6	2318.8	2335.9	2354.4	2355.7	2355.7	2354.4
17.5°	2260.7	2285.8	2321.4	2345.1	2350.4	2350.4	2351.7	2359.7	2354.4	2343.8	2351.7
20°	2277.9	2288.4	2301.6	2299.0	2301.6	2288.4	2275.2	2262.0	2263.4	2256.8	2276.6
22.5°	2246.2	2243.6	2213.2	2193.5	2193.5	2167.1	2142.0	2130.2	2118.3	2122.2	2128.8
25°	2167.1	2126.2	2089.3	2060.2	2053.7	2011.4	1977.1	1966.6	1946.8	1962.6	1965.3
27.5°	2040.5	1994.3	1934.9	1909.9	1875.6	1858.4	1834.7	1803.0	1762.2	1785.9	1781.9
30°	1904.6	1836.0	1787.2	1726.5	1672.5	1668.5	1623.7	1570.9	1549.8	1549.8	1561.7
32.5°	1752.9	1661.9	1590.7	1505.0	1452.2	1429.8	1375.7	1322.9	1334.8	1295.2	1309.7
35°	1576.2	1456.2	1366.5	1283.4	1243.8	1217.4	1147.5	1118.5	1086.8	1068.4	1102.7
37.5°	1407.4	1268.9	1154.1	1063.1	1048.6	1001.1	953.6	935.2	916.7	924.6	923.3
40°	1201.6	1078.9	976.0	904.8	879.8	857.3	825.7	803.3	791.4	798.0	799.3
42.5°	1015.6	912.7	836.2	786.1	765.0	749.2	733.4	714.9	710.9	710.9	716.2
45°	871.8	787.4	736.0	695.1	683.2	671.4	659.5	651.6	648.9	643.7	647.6
47.5°	757.1	689.8	658.2	627.8	614.6	612.0	601.5	597.5	592.2	590.9	592.2
50°	660.8	618.6	589.6	572.4	563.2	559.2	554.0	546.1	543.4	550.0	547.4
52.5°	593.5	554.0	538.1	521.0	515.7	510.4	502.5	503.8	502.5	499.9	499.9
55°	526.3	501.2	485.4	472.2	470.9	465.6	459.0	456.4	455.0	452.4	456.4
57.5°	472.2	452.4	437.9	426.0	420.8	420.8	414.2	408.9	408.9	407.6	408.9
60°	418.1	398.3	389.1	377.2	373.3	372.0	368.0	365.4	361.4	361.4	361.4
62.5°	368.0	352.2	341.6	331.1	332.4	325.8	320.5	317.9	317.9	319.2	319.2
65°	320.5	310.0	296.8	287.5	284.9	283.6	280.9	279.6	275.7	278.3	278.3
67.5°	277.0	262.5	254.6	250.6	246.6	245.3	242.7	240.1	238.7	237.4	240.1
70°	233.5	221.6	215.0	212.4	208.4	207.1	205.8	201.8	203.1	204.4	205.8
72.5°	193.9	183.3	182.0	174.1	174.1	174.1	168.8	171.5	170.1	167.5	170.1
75°	153.0	147.7	145.1	141.1	142.4	141.1	139.8	135.9	135.9	137.2	138.5
77.5°	121.3	116.1	114.8	110.8	108.2	110.8	108.2	106.8	106.8	108.2	108.2
80°	89.7	87.1	83.1	83.1	83.1	81.8	81.8	81.8	80.5	79.1	80.5
82.5°	59.4	59.4	58.0	56.7	58.0	55.4	56.7	56.7	56.7	56.7	56.7
85°	38.3	36.9	36.9	35.6	35.6	35.6	36.9	34.3	34.3	35.6	35.6
87.5°	17.1	17.1	17.1	18.5	17.1	17.1	17.1	18.5	17.1	17.1	17.1
90°	6.9	7.2	7.6	7.9	8.1	8.2	8.3	8.5	8.6	8.8	8.6
92.5°	8.0	8.1	8.3	8.4	8.5	8.5	8.6	8.7	8.7	8.8	8.7
95°	13.1	13.4	13.8	14.1	14.3	14.3	14.2	14.1	14.1	14.0	14.1
97.5°	16.8	17.0	17.3	17.5	17.6	17.6	17.7	17.8	17.8	17.9	17.8
100°	19.1	19.7	20.2	20.8	21.1	21.2	21.3	21.5	21.6	21.8	21.6
102.5°	20.0	20.8	21.6	22.4	22.8	22.9	23.1	23.4	23.6	23.8	23.6
105°	20.6	21.4	22.2	23.0	23.4	23.5	23.8	24.1	24.4	24.7	24.4
107.5°	21.3	22.1	22.9	23.7	24.1	24.2	24.5	24.8	25.1	25.4	25.1
110°	49.7	42.5	35.2	28.0	24.4	24.5	24.8	25.1	25.4	25.7	25.4

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	134.1	103.0	71.8	40.7	25.1	25.2	25.4	25.6	25.8	26.0	25.8
115°	167.2	133.8	100.3	66.8	50.1	47.5	42.3	37.1	31.9	26.7	31.9
117.5°	208.0	197.6	187.3	177.0	171.8	162.3	143.4	124.4	105.5	86.5	105.5
120°	239.4	240.2	241.1	242.0	242.4	237.5	227.8	218.0	208.3	198.5	208.3
122.5°	258.1	258.5	259.0	259.4	259.6	259.6	259.7	259.8	259.9	260.0	259.9
125°	275.4	275.9	276.4	276.9	277.2	277.3	277.5	277.8	278.0	278.2	278.0
127.5°	291.6	292.3	293.0	293.7	294.1	294.1	294.2	294.3	294.4	294.5	294.4
130°	307.0	307.8	308.5	309.3	309.7	309.7	309.6	309.5	309.5	309.4	309.5
132.5°	322.1	322.8	323.4	324.1	324.4	324.4	324.3	324.2	324.2	324.1	324.2
135°	336.1	336.9	337.6	338.3	338.7	338.6	338.5	338.3	338.2	338.0	338.2
137.5°	349.5	350.2	350.9	351.6	352.0	351.9	351.7	351.5	351.3	351.1	351.3
140°	362.4	363.1	363.7	364.4	364.7	364.5	364.2	363.8	363.5	363.1	363.5
142.5°	374.4	375.0	375.5	376.1	376.4	376.2	375.9	375.5	375.2	374.8	375.2
145°	385.4	385.9	386.4	386.9	387.2	387.0	386.7	386.3	386.0	385.6	386.0
147.5°	395.4	395.7	396.1	396.4	396.6	396.5	396.2	395.9	395.6	395.3	395.6
150°	404.2	404.6	405.1	405.5	405.7	405.5	405.2	404.8	404.5	404.1	404.5
152.5°	412.3	412.8	413.2	413.7	413.9	413.6	413.1	412.6	412.1	411.6	412.1
155°	419.5	419.9	420.4	420.8	421.0	420.7	420.1	419.6	419.0	418.4	419.0
157.5°	425.7	426.2	426.7	427.2	427.5	427.2	426.6	426.1	425.5	424.9	425.5
160°	431.2	431.6	432.1	432.5	432.7	432.5	432.0	431.5	431.0	430.5	431.0
162.5°	436.2	436.7	437.2	437.7	437.9	437.6	436.9	436.3	435.6	435.0	435.6
165°	440.1	440.6	441.1	441.6	441.8	441.6	441.1	440.6	440.1	439.6	440.1
167.5°	443.6	444.1	444.6	445.1	445.4	445.1	444.4	443.8	443.1	442.5	443.1
170°	446.2	446.7	447.2	447.7	448.0	447.7	447.0	446.4	445.7	445.1	445.7
172.5°	448.2	448.7	449.2	449.7	450.0	449.7	449.0	448.3	447.7	447.0	447.7
175°	449.5	450.0	450.5	451.0	451.3	450.9	450.2	449.5	448.7	448.0	448.7
177.5°	449.8	450.3	450.8	451.3	451.6	451.3	450.6	450.0	449.3	448.7	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1818.9	1809.6	1801.7	1803.0	1809.6	1804.4	1791.2	1774.0	1767.4	1759.5	1767.4
5°	1928.3	1920.4	1904.6	1905.9	1902.0	1896.7	1875.6	1849.2	1849.2	1828.1	1825.5
7.5°	2036.5	2024.6	2014.1	2011.4	1996.9	1986.4	1967.9	1931.0	1916.5	1891.4	1876.9
10°	2157.8	2148.6	2136.7	2122.2	2114.3	2095.9	2065.5	2011.4	1985.1	1950.8	1925.7
12.5°	2280.5	2279.2	2252.8	2223.8	2222.5	2193.5	2172.4	2099.8	2064.2	2018.0	1958.7
15°	2358.3	2351.7	2337.2	2322.7	2326.7	2295.0	2247.5	2161.8	2138.1	2082.7	2019.4
17.5°	2357.0	2357.0	2353.1	2350.4	2346.5	2337.2	2310.9	2254.1	2215.9	2146.0	2086.6
20°	2281.8	2299.0	2302.9	2301.6	2314.8	2321.4	2320.1	2284.5	2254.1	2192.1	2131.5
22.5°	2131.5	2171.0	2188.2	2198.7	2226.4	2240.9	2275.2	2262.0	2254.1	2208.0	2156.5
25°	1991.7	2004.8	2056.3	2058.9	2097.2	2132.8	2167.1	2189.5	2218.5	2201.4	2157.8
27.5°	1811.0	1841.3	1878.2	1905.9	1913.8	1986.4	2043.1	2085.3	2151.3	2156.5	2142.0
30°	1606.5	1621.0	1681.7	1718.6	1760.8	1813.6	1895.4	1967.9	2027.3	2081.3	2099.8
32.5°	1357.2	1416.6	1452.2	1497.0	1534.0	1627.6	1727.9	1821.5	1890.1	1981.1	2020.7
35°	1129.0	1175.2	1235.9	1254.3	1321.6	1400.8	1531.3	1651.4	1755.6	1847.9	1928.3
37.5°	940.4	977.4	1042.0	1071.0	1110.6	1212.1	1321.6	1470.7	1596.0	1709.4	1809.6
40°	811.2	838.9	887.7	896.9	929.9	1022.2	1110.6	1250.4	1416.6	1569.6	1679.1
42.5°	722.8	736.0	769.0	780.8	801.9	863.9	943.1	1075.0	1229.3	1387.6	1541.9
45°	659.5	668.7	688.5	699.1	725.4	753.1	817.8	923.3	1044.6	1204.2	1370.4
47.5°	602.8	614.6	622.6	629.2	643.7	674.0	716.2	794.0	910.1	1056.5	1217.4
50°	555.3	559.2	573.8	575.1	584.3	604.1	643.7	691.1	783.5	902.2	1057.8
52.5°	507.8	511.8	521.0	530.2	534.2	550.0	576.4	616.0	684.6	778.2	916.7
55°	460.3	465.6	474.8	481.4	485.4	498.6	514.4	552.7	606.7	672.7	786.1
57.5°	412.8	424.7	427.3	431.3	437.9	452.4	466.9	489.3	531.5	592.2	675.3
60°	368.0	372.0	381.2	385.1	391.7	399.7	418.1	435.3	465.6	513.1	588.3
62.5°	321.8	331.1	335.0	339.0	344.3	353.5	365.4	383.8	410.2	448.5	507.8
65°	282.3	283.6	291.5	296.8	302.0	308.6	320.5	337.7	353.5	389.1	432.6
67.5°	244.0	246.6	249.3	254.6	261.2	267.8	278.3	287.5	307.3	331.1	365.4
70°	207.1	207.1	213.7	217.6	216.3	224.2	232.1	242.7	257.2	279.6	307.3
72.5°	174.1	172.8	178.1	179.4	182.0	187.3	192.6	203.1	211.0	228.2	249.3
75°	138.5	141.1	143.8	143.8	147.7	151.7	157.0	162.2	171.5	182.0	197.8
77.5°	109.5	109.5	112.1	113.4	117.4	116.1	121.3	126.6	133.2	142.4	154.3
80°	80.5	83.1	83.1	83.1	84.4	85.7	91.0	95.0	98.9	105.5	110.8
82.5°	56.7	56.7	59.4	59.4	59.4	62.0	62.0	63.3	65.9	69.9	73.9
85°	35.6	35.6	35.6	36.9	35.6	36.9	39.6	38.3	39.6	42.2	42.2
87.5°	17.1	17.1	17.1	17.1	17.1	18.5	17.1	18.5	19.8	19.8	19.8
90°	8.5	8.3	8.2	8.1	7.9	7.6	7.2	6.9	6.5	5.9	5.3
92.5°	8.7	8.6	8.5	8.5	8.4	8.3	8.1	8.0	7.8	7.6	7.4
95°	14.1	14.2	14.3	14.3	14.1	13.8	13.4	13.1	12.7	12.2	11.7
97.5°	17.8	17.7	17.6	17.6	17.5	17.3	17.0	16.8	16.6	15.4	14.3
100°	21.5	21.3	21.2	21.1	20.8	20.2	19.7	19.1	18.5	17.3	16.1
102.5°	23.4	23.1	22.9	22.8	22.4	21.6	20.8	20.0	19.2	32.4	45.5
105°	24.1	23.8	23.5	23.4	23.0	22.2	21.4	20.6	19.8	39.6	59.3
107.5°	24.8	24.5	24.2	24.1	23.7	22.9	22.1	21.3	20.5	44.9	69.2
110°	25.1	24.8	24.5	24.4	28.0	35.2	42.5	49.7	56.9	77.8	98.7

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	25.6	25.4	25.2	25.1	40.7	71.8	103.0	134.1	165.3	166.5	167.7
115°	37.1	42.3	47.5	50.1	66.8	100.3	133.8	167.2	200.7	198.9	197.1
117.5°	124.4	143.4	162.3	171.8	177.0	187.3	197.6	208.0	218.3	217.1	215.9
120°	218.0	227.8	237.5	242.4	242.0	241.1	240.2	239.4	238.5	237.2	235.9
122.5°	259.8	259.7	259.6	259.6	259.4	259.0	258.5	258.1	257.7	256.3	254.8
125°	277.8	277.5	277.3	277.2	276.9	276.4	275.9	275.4	274.9	273.5	272.1
127.5°	294.3	294.2	294.1	294.1	293.7	293.0	292.3	291.6	290.9	289.8	288.7
130°	309.5	309.6	309.7	309.7	309.3	308.5	307.8	307.0	306.2	305.4	304.6
132.5°	324.2	324.3	324.4	324.4	324.1	323.4	322.8	322.1	321.5	320.7	319.9
135°	338.3	338.5	338.6	338.7	338.3	337.6	336.9	336.1	335.4	334.8	334.1
137.5°	351.5	351.7	351.9	352.0	351.6	350.9	350.2	349.5	348.8	348.1	347.3
140°	363.8	364.2	364.5	364.7	364.4	363.7	363.1	362.4	361.8	361.0	360.2
142.5°	375.5	375.9	376.2	376.4	376.1	375.5	375.0	374.4	373.8	372.9	371.9
145°	386.3	386.7	387.0	387.2	386.9	386.4	385.9	385.4	384.9	383.7	382.5
147.5°	395.9	396.2	396.5	396.6	396.4	396.1	395.7	395.4	395.0	393.8	392.6
150°	404.8	405.2	405.5	405.7	405.5	405.1	404.6	404.2	403.8	402.6	401.5
152.5°	412.6	413.1	413.6	413.9	413.7	413.2	412.8	412.3	411.9	410.8	409.7
155°	419.6	420.1	420.7	421.0	420.8	420.4	419.9	419.5	419.1	418.2	417.4
157.5°	426.1	426.6	427.2	427.5	427.2	426.7	426.2	425.7	425.2	424.6	423.9
160°	431.5	432.0	432.5	432.7	432.5	432.1	431.6	431.2	430.8	430.4	429.9
162.5°	436.3	436.9	437.6	437.9	437.7	437.2	436.7	436.2	435.7	435.3	434.9
165°	440.6	441.1	441.6	441.8	441.6	441.1	440.6	440.1	439.6	439.4	439.2
167.5°	443.8	444.4	445.1	445.4	445.1	444.6	444.1	443.6	443.1	442.9	442.7
170°	446.4	447.0	447.7	448.0	447.7	447.2	446.7	446.2	445.7	445.6	445.4
172.5°	448.3	449.0	449.7	450.0	449.7	449.2	448.7	448.2	447.7	447.5	447.4
175°	449.5	450.2	450.9	451.3	451.0	450.5	450.0	449.5	449.0	448.8	448.7
177.5°	450.0	450.6	451.3	451.6	451.3	450.8	450.3	449.8	449.3	449.2	449.2
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1760.8	1754.2	1750.3	1752.9	1745.0	1725.2	1725.2	1731.8	1723.9	1716.0	1704.1
5°	1809.6	1796.4	1788.5	1787.2	1768.8	1737.1	1730.5	1723.9	1706.8	1688.3	1668.5
7.5°	1857.1	1833.4	1820.2	1811.0	1784.6	1743.7	1726.5	1712.0	1684.3	1656.6	1631.6
10°	1896.7	1862.4	1846.6	1832.1	1797.8	1746.3	1718.6	1692.2	1656.6	1621.0	1589.4
12.5°	1928.3	1888.8	1869.0	1847.9	1805.7	1738.4	1704.1	1661.9	1626.3	1578.8	1547.2
15°	1981.1	1899.3	1880.9	1861.1	1817.6	1725.2	1683.0	1635.5	1586.7	1523.4	1489.1
17.5°	2023.3	1913.8	1912.5	1870.3	1813.6	1719.9	1655.3	1593.3	1540.6	1477.3	1423.2
20°	2048.4	1936.3	1915.2	1871.6	1800.4	1684.3	1617.1	1548.5	1491.8	1415.3	1361.2
22.5°	2069.5	1967.9	1912.5	1859.8	1772.7	1672.5	1573.5	1508.9	1431.1	1348.0	1296.6
25°	2077.4	1974.5	1916.5	1855.8	1752.9	1638.2	1526.1	1456.2	1369.1	1293.9	1224.0
27.5°	2078.7	1973.2	1902.0	1838.7	1725.2	1593.3	1478.6	1404.7	1308.4	1221.4	1151.5
30°	2065.5	1958.7	1894.1	1825.5	1698.8	1552.4	1420.5	1338.8	1235.9	1148.8	1076.3
32.5°	2026.0	1929.7	1876.9	1801.7	1664.6	1495.7	1365.1	1274.1	1166.0	1080.2	1010.3
35°	1960.0	1894.1	1836.0	1766.1	1619.7	1443.0	1309.7	1202.9	1093.4	1011.7	945.7
37.5°	1878.2	1842.6	1788.5	1719.9	1568.3	1395.5	1247.8	1129.0	1019.6	940.4	875.8
40°	1767.4	1776.7	1723.9	1661.9	1507.6	1330.8	1167.3	1053.9	951.0	877.1	813.8
42.5°	1647.4	1685.7	1655.3	1596.0	1440.3	1259.6	1107.9	982.6	882.4	805.9	753.1
45°	1518.1	1584.1	1565.6	1522.1	1370.4	1184.4	1023.5	902.2	813.8	739.9	693.8
47.5°	1377.0	1470.7	1470.7	1439.0	1292.6	1109.3	951.0	827.0	739.9	687.2	642.3
50°	1233.2	1338.8	1355.9	1334.8	1205.5	1023.5	862.6	750.5	675.3	623.9	590.9
52.5°	1082.9	1205.5	1237.2	1226.7	1113.2	941.8	790.1	680.6	612.0	567.2	538.1
55°	939.1	1081.6	1115.9	1119.8	1014.3	852.1	709.6	613.3	547.4	517.0	492.0
57.5°	803.3	940.4	978.7	985.3	914.1	770.3	634.4	550.0	490.7	465.6	445.8
60°	687.2	801.9	852.1	866.6	804.6	675.3	564.5	482.7	437.9	414.2	395.7
62.5°	592.2	684.6	737.3	741.3	713.6	592.2	492.0	423.4	385.1	364.0	354.8
65°	499.9	583.0	614.6	630.5	608.0	513.1	424.7	368.0	337.7	319.2	310.0
67.5°	426.0	478.8	505.2	526.3	503.8	432.6	361.4	315.2	292.8	274.3	269.1
70°	349.5	393.1	412.8	433.9	414.2	360.1	308.6	266.4	246.6	232.1	225.5
72.5°	279.6	313.9	332.4	345.6	333.7	288.9	246.6	217.6	203.1	192.6	188.6
75°	221.6	245.3	255.9	265.1	259.8	225.5	199.2	175.4	162.2	153.0	150.4
77.5°	168.8	186.0	197.8	200.5	193.9	171.5	149.0	134.5	124.0	118.7	116.1
80°	120.0	130.6	137.2	141.1	134.5	125.3	109.5	98.9	89.7	83.1	81.8
82.5°	80.5	85.7	91.0	89.7	87.1	79.1	69.9	64.6	60.7	55.4	55.4
85°	46.2	47.5	50.1	51.4	50.1	44.8	39.6	36.9	34.3	30.3	30.3
87.5°	19.8	21.1	21.1	22.4	19.8	19.8	17.1	14.5	14.5	13.2	11.9
90°	4.8	4.2	3.9	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.1	6.9	6.8	6.9	7.2	7.5	7.8	8.1	7.8	7.5	7.2
95°	11.2	10.7	10.4	11.6	14.0	16.3	18.7	21.1	18.7	16.3	14.0
97.5°	13.1	12.0	11.4	14.4	20.3	26.2	32.2	38.1	32.2	26.2	20.3
100°	14.8	13.6	13.0	18.0	27.9	37.8	47.7	57.6	47.7	37.8	27.9
102.5°	58.7	71.8	78.4	78.5	78.6	78.8	78.9	79.1	78.9	78.8	78.6
105°	79.1	98.8	108.7	107.6	105.4	103.3	101.1	98.9	101.1	103.3	105.4
107.5°	93.6	117.9	130.1	129.2	127.4	125.6	123.8	122.0	123.8	125.6	127.4
110°	119.6	140.5	151.0	150.2	148.7	147.2	145.6	144.1	145.6	147.2	148.7

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	169.0	170.2	170.8	170.2	168.9	167.6	166.3	165.0	166.3	167.6	168.9
115°	195.3	193.5	192.6	192.0	190.8	189.5	188.3	187.1	188.3	189.5	190.8
117.5°	214.6	213.4	212.8	212.1	210.6	209.2	207.7	206.3	207.7	209.2	210.6
120°	234.6	233.3	232.6	232.1	231.0	229.9	228.9	227.8	228.9	229.9	231.0
122.5°	253.4	251.9	251.2	250.6	249.5	248.3	247.2	246.0	247.2	248.3	249.5
125°	270.8	269.4	268.7	268.2	267.3	266.4	265.4	264.5	265.4	266.4	267.3
127.5°	287.6	286.5	286.0	285.5	284.5	283.4	282.4	281.4	282.4	283.4	284.5
130°	303.8	303.0	302.6	302.0	300.9	299.7	298.6	297.4	298.6	299.7	300.9
132.5°	319.1	318.3	317.9	317.4	316.5	315.5	314.6	313.6	314.6	315.5	316.5
135°	333.5	332.8	332.5	331.9	330.8	329.6	328.5	327.3	328.5	329.6	330.8
137.5°	346.6	345.9	345.5	345.1	344.2	343.3	342.5	341.6	342.5	343.3	344.2
140°	359.4	358.6	358.2	357.9	357.3	356.8	356.2	355.6	356.2	356.8	357.3
142.5°	371.0	370.1	369.6	369.3	368.8	368.3	367.8	367.3	367.8	368.3	368.8
145°	381.2	380.0	379.4	379.4	379.5	379.6	379.6	379.7	379.6	379.6	379.5
147.5°	391.3	390.1	389.5	389.6	389.8	390.0	390.2	390.4	390.2	390.0	389.8
150°	400.3	399.2	398.6	398.8	399.3	399.8	400.3	400.8	400.3	399.8	399.3
152.5°	408.6	407.5	407.0	407.3	407.9	408.4	409.0	409.6	409.0	408.4	407.9
155°	416.5	415.6	415.2	415.5	416.2	416.8	417.5	418.1	417.5	416.8	416.2
157.5°	423.3	422.6	422.3	422.6	423.2	423.7	424.3	424.9	424.3	423.7	423.2
160°	429.5	429.0	428.8	429.0	429.5	429.9	430.4	430.8	430.4	429.9	429.5
162.5°	434.6	434.2	434.0	434.2	434.7	435.1	435.6	436.0	435.6	435.1	434.7
165°	438.9	438.7	438.6	438.8	439.2	439.7	440.1	440.5	440.1	439.7	439.2
167.5°	442.5	442.3	442.2	442.4	442.8	443.3	443.7	444.1	443.7	443.3	442.8
170°	445.3	445.2	445.1	445.3	445.7	446.2	446.6	447.0	446.6	446.2	445.7
172.5°	447.2	447.1	447.0	447.2	447.7	448.1	448.6	449.0	448.6	448.1	447.7
175°	448.5	448.4	448.3	448.6	449.1	449.6	450.1	450.6	450.1	449.6	449.1
177.5°	449.1	449.0	449.0	449.3	449.8	450.3	450.8	451.3	450.8	450.3	449.8
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1697.5	1704.1	1702.8	1689.6	1675.1	1663.2	1640.8	1643.4	1635.5	1636.9	1644.8
5°	1655.3	1655.3	1650.0	1631.6	1607.8	1594.6	1569.6	1563.0	1547.2	1545.8	1544.5
7.5°	1610.5	1603.9	1597.3	1570.9	1541.9	1520.8	1486.5	1478.6	1462.7	1452.2	1446.9
10°	1557.7	1548.5	1535.3	1505.0	1469.3	1443.0	1407.4	1396.8	1366.5	1353.3	1345.4
12.5°	1499.7	1494.4	1473.3	1448.2	1390.2	1361.2	1309.7	1320.3	1290.0	1263.6	1259.6
15°	1441.6	1421.9	1410.0	1369.1	1299.2	1286.0	1245.1	1224.0	1196.3	1175.2	1175.2
17.5°	1384.9	1354.6	1328.2	1284.7	1233.2	1196.3	1166.0	1155.4	1121.1	1100.0	1096.1
20°	1309.7	1275.5	1268.9	1206.9	1171.3	1130.4	1101.3	1075.0	1049.9	1040.7	1034.1
22.5°	1238.5	1199.0	1188.4	1135.6	1100.0	1059.1	1030.1	1011.7	993.2	986.6	974.7
25°	1162.0	1138.3	1122.5	1065.7	1026.2	987.9	968.1	954.9	937.8	936.5	928.6
27.5°	1088.2	1065.7	1049.9	995.8	966.8	931.2	915.4	900.9	891.6	887.7	883.7
30°	1024.8	999.8	981.3	941.8	906.1	877.1	863.9	854.7	849.4	842.8	841.5
32.5°	954.9	940.4	915.4	885.0	857.3	829.6	821.7	815.1	807.2	804.6	803.3
35°	895.6	875.8	860.0	825.7	813.8	790.1	780.8	775.6	765.0	762.4	759.7
37.5°	837.6	819.1	801.9	780.8	758.4	745.2	739.9	732.0	726.8	728.1	725.4
40°	779.5	765.0	751.8	729.4	716.2	709.6	699.1	691.1	688.5	689.8	688.5
42.5°	722.8	709.6	701.7	684.6	671.4	664.8	658.2	650.3	654.2	654.2	658.2
45°	671.4	659.5	654.2	641.0	633.1	622.6	616.0	614.6	619.9	618.6	618.6
47.5°	618.6	614.6	608.0	596.2	585.6	579.0	577.7	577.7	583.0	585.6	584.3
50°	577.7	569.8	561.9	552.7	544.7	542.1	538.1	540.8	546.1	546.1	548.7
52.5°	526.3	521.0	518.4	510.4	505.2	505.2	505.2	506.5	510.4	514.4	513.1
55°	481.4	477.5	474.8	470.9	464.3	465.6	464.3	466.9	470.9	474.8	477.5
57.5°	433.9	432.6	430.0	423.4	423.4	422.1	426.0	427.3	433.9	436.6	440.5
60°	391.7	387.8	387.8	382.5	382.5	382.5	386.5	390.4	395.7	397.0	399.7
62.5°	346.9	346.9	345.6	341.6	341.6	345.6	346.9	352.2	354.8	354.8	358.8
65°	304.7	303.4	302.0	303.4	304.7	304.7	308.6	311.3	313.9	315.2	316.6
67.5°	262.5	261.2	263.8	262.5	265.1	270.4	269.1	273.0	277.0	277.0	278.3
70°	222.9	225.5	224.2	226.9	225.5	228.2	232.1	233.5	233.5	234.8	238.7
72.5°	186.0	186.0	186.0	184.7	186.0	188.6	191.3	192.6	195.2	196.5	200.5
75°	150.4	150.4	147.7	150.4	150.4	153.0	155.6	155.6	155.6	158.3	162.2
77.5°	113.4	114.8	113.4	116.1	116.1	117.4	120.0	118.7	121.3	122.7	124.0
80°	83.1	81.8	81.8	81.8	83.1	83.1	85.7	87.1	87.1	91.0	88.4
82.5°	52.8	54.1	52.8	54.1	54.1	55.4	54.1	55.4	56.7	59.4	58.0
85°	30.3	29.0	29.0	30.3	29.0	29.0	30.3	29.0	30.3	29.0	30.3
87.5°	11.9	10.6	10.6	10.6	10.6	9.2	9.2	7.9	7.9	7.9	6.6
90°	3.5	3.9	4.2	4.8	5.3	5.9	6.5	6.9	7.2	7.6	7.9
92.5°	6.9	6.8	6.9	7.1	7.4	7.6	7.8	8.0	8.1	8.3	8.4
95°	11.6	10.4	10.7	11.2	11.7	12.2	12.7	13.1	13.4	13.8	14.1
97.5°	14.4	11.4	12.0	13.1	14.3	15.4	16.6	16.8	17.0	17.3	17.5
100°	18.0	13.0	13.6	14.8	16.1	17.3	18.5	19.1	19.7	20.2	20.8
102.5°	78.5	78.4	71.8	58.7	45.5	32.4	19.2	20.0	20.8	21.6	22.4
105°	107.6	108.7	98.8	79.1	59.3	39.6	19.8	20.6	21.4	22.2	23.0
107.5°	129.2	130.1	117.9	93.6	69.2	44.9	20.5	21.3	22.1	22.9	23.7
110°	150.2	151.0	140.5	119.6	98.7	77.8	56.9	49.7	42.5	35.2	28.0

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	170.2	170.8	170.2	169.0	167.7	166.5	165.3	134.1	103.0	71.8	40.7
115°	192.0	192.6	193.5	195.3	197.1	198.9	200.7	167.2	133.8	100.3	66.8
117.5°	212.1	212.8	213.4	214.6	215.9	217.1	218.3	208.0	197.6	187.3	177.0
120°	232.1	232.6	233.3	234.6	235.9	237.2	238.5	239.4	240.2	241.1	242.0
122.5°	250.6	251.2	251.9	253.4	254.8	256.3	257.7	258.1	258.5	259.0	259.4
125°	268.2	268.7	269.4	270.8	272.1	273.5	274.9	275.4	275.9	276.4	276.9
127.5°	285.5	286.0	286.5	287.6	288.7	289.8	290.9	291.6	292.3	293.0	293.7
130°	302.0	302.6	303.0	303.8	304.6	305.4	306.2	307.0	307.8	308.5	309.3
132.5°	317.4	317.9	318.3	319.1	319.9	320.7	321.5	322.1	322.8	323.4	324.1
135°	331.9	332.5	332.8	333.5	334.1	334.8	335.4	336.1	336.9	337.6	338.3
137.5°	345.1	345.5	345.9	346.6	347.3	348.1	348.8	349.5	350.2	350.9	351.6
140°	357.9	358.2	358.6	359.4	360.2	361.0	361.8	362.4	363.1	363.7	364.4
142.5°	369.3	369.6	370.1	371.0	371.9	372.9	373.8	374.4	375.0	375.5	376.1
145°	379.4	379.4	380.0	381.2	382.5	383.7	384.9	385.4	385.9	386.4	386.9
147.5°	389.6	389.5	390.1	391.3	392.6	393.8	395.0	395.4	395.7	396.1	396.4
150°	398.8	398.6	399.2	400.3	401.5	402.6	403.8	404.2	404.6	405.1	405.5
152.5°	407.3	407.0	407.5	408.6	409.7	410.8	411.9	412.3	412.8	413.2	413.7
155°	415.5	415.2	415.6	416.5	417.4	418.2	419.1	419.5	419.9	420.4	420.8
157.5°	422.6	422.3	422.6	423.3	423.9	424.6	425.2	425.7	426.2	426.7	427.2
160°	429.0	428.8	429.0	429.5	429.9	430.4	430.8	431.2	431.6	432.1	432.5
162.5°	434.2	434.0	434.2	434.6	434.9	435.3	435.7	436.2	436.7	437.2	437.7
165°	438.8	438.6	438.7	438.9	439.2	439.4	439.6	440.1	440.6	441.1	441.6
167.5°	442.4	442.2	442.3	442.5	442.7	442.9	443.1	443.6	444.1	444.6	445.1
170°	445.3	445.1	445.2	445.3	445.4	445.6	445.7	446.2	446.7	447.2	447.7
172.5°	447.2	447.0	447.1	447.2	447.4	447.5	447.7	448.2	448.7	449.2	449.7
175°	448.6	448.3	448.4	448.5	448.7	448.8	449.0	449.5	450.0	450.5	451.0
177.5°	449.3	449.0	449.0	449.1	449.2	449.2	449.3	449.8	450.3	450.8	451.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1635.5	1639.5	1630.3	1627.6	1630.3	1621.0	1623.7	1626.3	1626.3	1630.3	1632.9
5°	1540.6	1535.3	1526.1	1523.4	1520.8	1524.7	1522.1	1526.1	1527.4	1536.6	1537.9
7.5°	1446.9	1439.0	1431.1	1423.2	1420.5	1413.9	1420.5	1420.5	1429.8	1427.1	1433.7
10°	1336.1	1334.8	1324.3	1320.3	1315.0	1304.5	1319.0	1315.0	1321.6	1333.5	1336.1
12.5°	1254.3	1239.8	1246.4	1228.0	1234.6	1224.0	1225.3	1225.3	1235.9	1237.2	1234.6
15°	1176.5	1164.7	1147.5	1139.6	1135.6	1130.4	1147.5	1148.8	1140.9	1159.4	1152.8
17.5°	1097.4	1097.4	1081.6	1077.6	1067.1	1072.3	1069.7	1071.0	1068.4	1081.6	1088.2
20°	1028.8	1022.2	1016.9	1018.3	1005.1	1002.4	999.8	1002.4	1011.7	1020.9	1023.5
22.5°	973.4	969.4	956.3	958.9	948.3	952.3	949.7	956.3	957.6	957.6	966.8
25°	920.6	915.4	916.7	911.4	907.5	907.5	903.5	907.5	912.7	915.4	916.7
27.5°	881.1	877.1	870.5	866.6	869.2	862.6	867.9	871.8	871.8	869.2	871.8
30°	833.6	836.2	836.2	823.0	828.3	825.7	829.6	832.3	832.3	833.6	831.0
32.5°	801.9	794.0	792.7	791.4	791.4	786.1	786.1	790.1	791.4	792.7	796.7
35°	759.7	759.7	753.1	757.1	751.8	753.1	751.8	753.1	755.8	751.8	755.8
37.5°	721.5	722.8	720.2	722.8	724.1	721.5	718.8	724.1	721.5	721.5	718.8
40°	688.5	687.2	688.5	688.5	688.5	689.8	687.2	687.2	687.2	684.6	681.9
42.5°	660.8	652.9	655.5	656.9	652.9	652.9	654.2	652.9	656.9	648.9	648.9
45°	621.2	618.6	619.9	619.9	622.6	618.6	621.2	622.6	618.6	617.3	614.6
47.5°	585.6	588.3	585.6	588.3	588.3	590.9	585.6	586.9	588.3	583.0	579.0
50°	550.0	550.0	554.0	552.7	554.0	551.3	551.3	550.0	551.3	548.7	544.7
52.5°	517.0	513.1	519.7	518.4	517.0	515.7	514.4	515.7	513.1	510.4	510.4
55°	476.2	476.2	480.1	481.4	481.4	478.8	476.2	477.5	476.2	474.8	473.5
57.5°	443.2	437.9	440.5	441.9	441.9	437.9	440.5	437.9	437.9	439.2	435.3
60°	401.0	401.0	398.3	402.3	402.3	399.7	399.7	401.0	398.3	397.0	395.7
62.5°	356.1	357.4	361.4	362.7	364.0	361.4	358.8	360.1	360.1	356.1	357.4
65°	317.9	320.5	325.8	324.5	321.8	323.1	320.5	321.8	317.9	319.2	315.2
67.5°	280.9	279.6	280.9	280.9	283.6	282.3	279.6	279.6	278.3	282.3	278.3
70°	241.4	241.4	241.4	241.4	242.7	244.0	241.4	238.7	240.1	237.4	236.1
72.5°	200.5	201.8	200.5	203.1	199.2	201.8	201.8	200.5	199.2	199.2	199.2
75°	162.2	164.9	160.9	162.2	160.9	163.6	162.2	162.2	159.6	158.3	159.6
77.5°	124.0	125.3	122.7	124.0	122.7	124.0	124.0	122.7	122.7	122.7	122.7
80°	88.4	89.7	88.4	87.1	85.7	88.4	85.7	87.1	88.4	87.1	89.7
82.5°	56.7	56.7	55.4	56.7	54.1	54.1	55.4	55.4	54.1	56.7	54.1
85°	27.7	27.7	30.3	27.7	26.4	26.4	26.4	27.7	26.4	29.0	27.7
87.5°	6.6	5.3	6.6	6.6	5.3	5.3	6.6	5.3	6.6	7.9	5.3
90°	8.1	8.2	8.3	8.5	8.6	8.8	8.6	8.5	8.3	8.2	8.1
92.5°	8.5	8.5	8.6	8.7	8.7	8.8	8.7	8.7	8.6	8.5	8.5
95°	14.3	14.3	14.2	14.1	14.1	14.0	14.1	14.1	14.2	14.3	14.3
97.5°	17.6	17.6	17.7	17.8	17.8	17.9	17.8	17.8	17.7	17.6	17.6
100°	21.1	21.2	21.3	21.5	21.6	21.8	21.6	21.5	21.3	21.2	21.1
102.5°	22.8	22.9	23.1	23.4	23.6	23.8	23.6	23.4	23.1	22.9	22.8
105°	23.4	23.5	23.8	24.1	24.4	24.7	24.4	24.1	23.8	23.5	23.4
107.5°	24.1	24.2	24.5	24.8	25.1	25.4	25.1	24.8	24.5	24.2	24.1
110°	24.4	24.5	24.8	25.1	25.4	25.7	25.4	25.1	24.8	24.5	24.4

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	25.1	25.2	25.4	25.6	25.8	26.0	25.8	25.6	25.4	25.2	25.1
115°	50.1	47.5	42.3	37.1	31.9	26.7	31.9	37.1	42.3	47.5	50.1
117.5°	171.8	162.3	143.4	124.4	105.5	86.5	105.5	124.4	143.4	162.3	171.8
120°	242.4	237.5	227.8	218.0	208.3	198.5	208.3	218.0	227.8	237.5	242.4
122.5°	259.6	259.6	259.7	259.8	259.9	260.0	259.9	259.8	259.7	259.6	259.6
125°	277.2	277.3	277.5	277.8	278.0	278.2	278.0	277.8	277.5	277.3	277.2
127.5°	294.1	294.1	294.2	294.3	294.4	294.5	294.4	294.3	294.2	294.1	294.1
130°	309.7	309.7	309.6	309.5	309.5	309.4	309.5	309.5	309.6	309.7	309.7
132.5°	324.4	324.4	324.3	324.2	324.2	324.1	324.2	324.2	324.3	324.4	324.4
135°	338.7	338.6	338.5	338.3	338.2	338.0	338.2	338.3	338.5	338.6	338.7
137.5°	352.0	351.9	351.7	351.5	351.3	351.1	351.3	351.5	351.7	351.9	352.0
140°	364.7	364.5	364.2	363.8	363.5	363.1	363.5	363.8	364.2	364.5	364.7
142.5°	376.4	376.2	375.9	375.5	375.2	374.8	375.2	375.5	375.9	376.2	376.4
145°	387.2	387.0	386.7	386.3	386.0	385.6	386.0	386.3	386.7	387.0	387.2
147.5°	396.6	396.5	396.2	395.9	395.6	395.3	395.6	395.9	396.2	396.5	396.6
150°	405.7	405.5	405.2	404.8	404.5	404.1	404.5	404.8	405.2	405.5	405.7
152.5°	413.9	413.6	413.1	412.6	412.1	411.6	412.1	412.6	413.1	413.6	413.9
155°	421.0	420.7	420.1	419.6	419.0	418.4	419.0	419.6	420.1	420.7	421.0
157.5°	427.5	427.2	426.6	426.1	425.5	424.9	425.5	426.1	426.6	427.2	427.5
160°	432.7	432.5	432.0	431.5	431.0	430.5	431.0	431.5	432.0	432.5	432.7
162.5°	437.9	437.6	436.9	436.3	435.6	435.0	435.6	436.3	436.9	437.6	437.9
165°	441.8	441.6	441.1	440.6	440.1	439.6	440.1	440.6	441.1	441.6	441.8
167.5°	445.4	445.1	444.4	443.8	443.1	442.5	443.1	443.8	444.4	445.1	445.4
170°	448.0	447.7	447.0	446.4	445.7	445.1	445.7	446.4	447.0	447.7	448.0
172.5°	450.0	449.7	449.0	448.3	447.7	447.0	447.7	448.3	449.0	449.7	450.0
175°	451.3	450.9	450.2	449.5	448.7	448.0	448.7	449.5	450.2	450.9	451.3
177.5°	451.6	451.3	450.6	450.0	449.3	448.7	449.3	450.0	450.6	451.3	451.6
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0	1716.0
2.5°	1628.9	1639.5	1635.5	1621.0	1638.2	1638.2	1650.0	1650.0	1664.6	1669.8	1677.7
5°	1536.6	1544.5	1551.1	1544.5	1556.4	1574.9	1585.4	1594.6	1614.4	1622.3	1634.2
7.5°	1437.7	1452.2	1458.8	1458.8	1478.6	1499.7	1520.8	1534.0	1561.7	1572.2	1584.1
10°	1341.4	1358.5	1371.7	1370.4	1403.4	1416.6	1443.0	1473.3	1501.0	1516.8	1534.0
12.5°	1239.8	1249.1	1267.5	1293.9	1301.8	1325.6	1355.9	1394.2	1444.3	1458.8	1483.9
15°	1155.4	1180.5	1195.0	1206.9	1225.3	1247.8	1280.7	1317.7	1367.8	1399.4	1425.8
17.5°	1084.2	1117.2	1126.4	1123.8	1147.5	1181.8	1220.1	1247.8	1292.6	1330.8	1355.9
20°	1026.2	1039.4	1055.2	1061.8	1080.2	1117.2	1154.1	1185.8	1222.7	1253.0	1282.0
22.5°	968.1	978.7	991.9	1003.7	1018.3	1039.4	1075.0	1114.5	1150.1	1179.2	1212.1
25°	920.6	927.2	939.1	948.3	964.2	978.7	1003.7	1047.3	1089.5	1106.6	1135.6
27.5°	874.5	879.8	887.7	898.2	906.1	920.6	943.1	978.7	1022.2	1039.4	1078.9
30°	833.6	837.6	845.5	850.7	854.7	871.8	889.0	916.7	949.7	973.4	1002.4
32.5°	795.3	799.3	807.2	808.5	813.8	823.0	838.9	863.9	892.9	912.7	937.8
35°	753.1	755.8	763.7	766.3	770.3	778.2	790.1	808.5	834.9	849.4	871.8
37.5°	720.2	718.8	724.1	728.1	733.4	737.3	741.3	759.7	779.5	792.7	809.9
40°	684.6	681.9	683.2	688.5	691.1	696.4	696.4	714.9	728.1	738.6	751.8
42.5°	648.9	647.6	645.0	647.6	650.3	651.6	652.9	666.1	679.3	688.5	703.0
45°	613.3	612.0	609.4	610.7	610.7	613.3	617.3	622.6	631.8	639.7	647.6
47.5°	580.4	577.7	573.8	572.4	575.1	575.1	575.1	580.4	589.6	592.2	600.1
50°	546.1	542.1	536.8	534.2	534.2	532.9	535.5	536.8	544.7	547.4	554.0
52.5°	509.1	506.5	501.2	495.9	497.3	494.6	495.9	497.3	499.9	503.8	507.8
55°	472.2	466.9	463.0	461.6	457.7	457.7	453.7	459.0	457.7	459.0	464.3
57.5°	436.6	431.3	424.7	422.1	418.1	416.8	414.2	412.8	414.2	418.1	422.1
60°	394.4	391.7	387.8	383.8	381.2	377.2	374.6	374.6	373.3	373.3	374.6
62.5°	353.5	352.2	346.9	345.6	342.9	340.3	336.3	333.7	333.7	336.3	337.7
65°	313.9	312.6	308.6	307.3	300.7	298.1	296.8	295.5	292.8	292.8	292.8
67.5°	277.0	273.0	273.0	266.4	261.2	258.5	255.9	254.6	254.6	254.6	255.9
70°	236.1	236.1	232.1	228.2	222.9	224.2	220.3	216.3	216.3	213.7	215.0
72.5°	196.5	195.2	191.3	189.9	186.0	182.0	179.4	182.0	178.1	176.7	178.1
75°	158.3	157.0	154.3	151.7	153.0	149.0	145.1	143.8	143.8	141.1	141.1
77.5°	121.3	124.0	118.7	117.4	114.8	112.1	110.8	109.5	109.5	109.5	112.1
80°	84.4	85.7	85.7	83.1	84.4	80.5	80.5	80.5	76.5	77.8	79.1
82.5°	54.1	54.1	52.8	54.1	52.8	52.8	51.4	51.4	50.1	50.1	51.4
85°	30.3	29.0	27.7	30.3	29.0	29.0	27.7	27.7	27.7	27.7	27.7
87.5°	6.6	7.9	7.9	7.9	7.9	9.2	9.2	9.2	10.6	10.6	10.6
90°	7.9	7.6	7.2	6.9	6.5	5.9	5.3	4.8	4.2	3.9	3.5
92.5°	8.4	8.3	8.1	8.0	7.8	7.6	7.4	7.1	6.9	6.8	6.9
95°	14.1	13.8	13.4	13.1	12.7	12.2	11.7	11.2	10.7	10.4	11.6
97.5°	17.5	17.3	17.0	16.8	16.6	15.4	14.3	13.1	12.0	11.4	14.4
100°	20.8	20.2	19.7	19.1	18.5	17.3	16.1	14.8	13.6	13.0	18.0
102.5°	22.4	21.6	20.8	20.0	19.2	32.4	45.5	58.7	71.8	78.4	78.5
105°	23.0	22.2	21.4	20.6	19.8	39.6	59.3	79.1	98.8	108.7	107.6
107.5°	23.7	22.9	22.1	21.3	20.5	44.9	69.2	93.6	117.9	130.1	129.2
110°	28.0	35.2	42.5	49.7	56.9	77.8	98.7	119.6	140.5	151.0	150.2

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	40.7	71.8	103.0	134.1	165.3	166.5	167.7	169.0	170.2	170.8	170.2
115°	66.8	100.3	133.8	167.2	200.7	198.9	197.1	195.3	193.5	192.6	192.0
117.5°	177.0	187.3	197.6	208.0	218.3	217.1	215.9	214.6	213.4	212.8	212.1
120°	242.0	241.1	240.2	239.4	238.5	237.2	235.9	234.6	233.3	232.6	232.1
122.5°	259.4	259.0	258.5	258.1	257.7	256.3	254.8	253.4	251.9	251.2	250.6
125°	276.9	276.4	275.9	275.4	274.9	273.5	272.1	270.8	269.4	268.7	268.2
127.5°	293.7	293.0	292.3	291.6	290.9	289.8	288.7	287.6	286.5	286.0	285.5
130°	309.3	308.5	307.8	307.0	306.2	305.4	304.6	303.8	303.0	302.6	302.0
132.5°	324.1	323.4	322.8	322.1	321.5	320.7	319.9	319.1	318.3	317.9	317.4
135°	338.3	337.6	336.9	336.1	335.4	334.8	334.1	333.5	332.8	332.5	331.9
137.5°	351.6	350.9	350.2	349.5	348.8	348.1	347.3	346.6	345.9	345.5	345.1
140°	364.4	363.7	363.1	362.4	361.8	361.0	360.2	359.4	358.6	358.2	357.9
142.5°	376.1	375.5	375.0	374.4	373.8	372.9	371.9	371.0	370.1	369.6	369.3
145°	386.9	386.4	385.9	385.4	384.9	383.7	382.5	381.2	380.0	379.4	379.4
147.5°	396.4	396.1	395.7	395.4	395.0	393.8	392.6	391.3	390.1	389.5	389.6
150°	405.5	405.1	404.6	404.2	403.8	402.6	401.5	400.3	399.2	398.6	398.8
152.5°	413.7	413.2	412.8	412.3	411.9	410.8	409.7	408.6	407.5	407.0	407.3
155°	420.8	420.4	419.9	419.5	419.1	418.2	417.4	416.5	415.6	415.2	415.5
157.5°	427.2	426.7	426.2	425.7	425.2	424.6	423.9	423.3	422.6	422.3	422.6
160°	432.5	432.1	431.6	431.2	430.8	430.4	429.9	429.5	429.0	428.8	429.0
162.5°	437.7	437.2	436.7	436.2	435.7	435.3	434.9	434.6	434.2	434.0	434.2
165°	441.6	441.1	440.6	440.1	439.6	439.4	439.2	438.9	438.7	438.6	438.8
167.5°	445.1	444.6	444.1	443.6	443.1	442.9	442.7	442.5	442.3	442.2	442.4
170°	447.7	447.2	446.7	446.2	445.7	445.6	445.4	445.3	445.2	445.1	445.3
172.5°	449.7	449.2	448.7	448.2	447.7	447.5	447.4	447.2	447.1	447.0	447.2
175°	451.0	450.5	450.0	449.5	449.0	448.8	448.7	448.5	448.4	448.3	448.6
177.5°	451.3	450.8	450.3	449.8	449.3	449.2	449.2	449.1	449.0	449.0	449.3
180°	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6	449.6

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1716.0	1716.0	1716.0	1716.0
2.5°	1684.3	1684.3	1704.1	1725.2
5°	1647.4	1656.6	1688.3	1717.3
7.5°	1611.8	1627.6	1667.2	1704.1
10°	1568.3	1589.4	1638.2	1681.7
12.5°	1526.1	1545.8	1602.6	1651.4
15°	1466.7	1491.8	1552.4	1613.1
17.5°	1407.4	1432.4	1506.3	1577.5
20°	1337.4	1370.4	1453.5	1548.5
22.5°	1272.8	1313.7	1406.0	1482.5
25°	1201.6	1264.9	1350.6	1449.6
27.5°	1138.3	1201.6	1288.6	1388.9
30°	1067.1	1131.7	1221.4	1313.7
32.5°	998.5	1057.8	1144.9	1258.3
35°	927.2	984.0	1068.4	1183.1
37.5°	862.6	918.0	1010.3	1115.9
40°	799.3	857.3	936.5	1042.0
42.5°	739.9	791.4	862.6	968.1
45°	685.9	722.8	788.7	887.7
47.5°	629.2	662.1	722.8	821.7
50°	576.4	604.1	656.9	749.2
52.5°	525.0	548.7	597.5	671.4
55°	478.8	501.2	536.8	609.4
57.5°	431.3	448.5	482.7	540.8
60°	385.1	401.0	428.7	476.2
62.5°	339.0	352.2	378.5	416.8
65°	298.1	308.6	328.4	361.4
67.5°	258.5	265.1	280.9	307.3
70°	220.3	225.5	238.7	259.8
72.5°	179.4	184.7	199.2	213.7
75°	145.1	146.4	157.0	168.8
77.5°	113.4	112.1	120.0	129.3
80°	77.8	81.8	88.4	92.3
82.5°	52.8	54.1	56.7	59.4
85°	29.0	30.3	30.3	34.3
87.5°	11.9	13.2	13.2	14.5
90°	2.7	1.9	1.1	0.3
92.5°	7.2	7.5	7.8	8.1
95°	14.0	16.3	18.7	21.1
97.5°	20.3	26.2	32.2	38.1
100°	27.9	37.8	47.7	57.6
102.5°	78.6	78.8	78.9	79.1
105°	105.4	103.3	101.1	98.9
107.5°	127.4	125.6	123.8	122.0
110°	148.7	147.2	145.6	144.1

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	168.9	167.6	166.3	165.0
115°	190.8	189.5	188.3	187.1
117.5°	210.6	209.2	207.7	206.3
120°	231.0	229.9	228.9	227.8
122.5°	249.5	248.3	247.2	246.0
125°	267.3	266.4	265.4	264.5
127.5°	284.5	283.4	282.4	281.4
130°	300.9	299.7	298.6	297.4
132.5°	316.5	315.5	314.6	313.6
135°	330.8	329.6	328.5	327.3
137.5°	344.2	343.3	342.5	341.6
140°	357.3	356.8	356.2	355.6
142.5°	368.8	368.3	367.8	367.3
145°	379.5	379.6	379.6	379.7
147.5°	389.8	390.0	390.2	390.4
150°	399.3	399.8	400.3	400.8
152.5°	407.9	408.4	409.0	409.6
155°	416.2	416.8	417.5	418.1
157.5°	423.2	423.7	424.3	424.9
160°	429.5	429.9	430.4	430.8
162.5°	434.7	435.1	435.6	436.0
165°	439.2	439.7	440.1	440.5
167.5°	442.8	443.3	443.7	444.1
170°	445.7	446.2	446.6	447.0
172.5°	447.7	448.1	448.6	449.0
175°	449.1	449.6	450.1	450.6
177.5°	449.8	450.3	450.8	451.3
180°	449.6	449.6	449.6	449.6

TEST NUMBER: P999039

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.33	20.40	20.06	21.14	22.03	16.82	17.90	17.55	18.64	19.52
	3H	20.16	21.12	20.90	21.87	22.78	18.19	19.15	18.92	19.90	20.81
	4H	20.34	21.24	21.09	22.00	22.93	18.66	19.56	19.41	20.32	21.25
	6H	20.39	21.23	21.16	22.00	22.93	18.98	19.81	19.75	20.58	21.52
	8H	20.38	21.17	21.16	21.96	22.90	19.06	19.86	19.84	20.65	21.59
	12H	20.35	21.10	21.13	21.88	22.85	19.11	19.87	19.90	20.65	21.62
4H	2H	19.40	20.30	20.16	21.06	21.99	17.30	18.20	18.06	18.96	19.89
	3H	20.40	21.15	21.17	21.94	22.89	18.78	19.53	19.55	20.32	21.26
	4H	20.68	21.36	21.47	22.16	23.13	19.32	20.00	20.11	20.80	21.77
	6H	20.82	21.41	21.63	22.23	23.21	19.71	20.30	20.51	21.12	22.10
	8H	20.83	21.38	21.64	22.19	23.18	19.82	20.37	20.63	21.19	22.18
	12H	20.80	21.29	21.63	22.13	23.13	19.89	20.38	20.72	21.22	22.22
8H	4H	20.71	21.26	21.52	22.07	23.06	19.48	20.03	20.28	20.84	21.83
	6H	20.89	21.35	21.73	22.21	23.20	19.92	20.37	20.76	21.23	22.22
	8H	20.92	21.33	21.77	22.18	23.19	20.07	20.47	20.92	21.33	22.34
	12H	20.92	21.27	21.77	22.12	23.18	20.17	20.53	21.02	21.37	22.44
12H	4H	20.67	21.17	21.50	22.00	23.00	19.46	19.95	20.29	20.79	21.79
	6H	20.87	21.28	21.72	22.13	23.14	19.92	20.32	20.77	21.18	22.19
	8H	20.91	21.27	21.77	22.11	23.18	20.09	20.44	20.94	21.29	22.35