

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999045

Luminaire Tested: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999045
REPORT IS A COMBINATION OF REPORTS P984794 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4812.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999045

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P999045

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69
1	99	94	89	85	93	88	84	80	77	74	71	67	65	63	58	56	55
2	89	81	74	68	83	76	70	64	67	62	57	58	54	51	50	47	45
3	81	70	62	56	76	66	59	53	58	52	47	51	46	42	44	40	37
4	74	62	53	47	69	58	50	44	51	45	40	45	40	36	39	35	32
5	68	55	46	40	63	52	44	38	46	39	34	40	35	31	35	31	27
6	62	49	41	34	58	46	38	33	41	35	30	36	31	27	31	27	24
7	58	44	36	30	54	42	34	29	37	31	26	33	27	23	29	24	21
8	54	40	32	26	50	38	31	25	34	28	23	30	25	21	26	22	19
9	50	37	29	23	47	35	28	23	31	25	21	28	22	19	24	20	17
10	47	34	26	21	44	32	25	20	29	23	19	25	20	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14470	14470	14470
5°	14536	13853	13775
10°	14438	13373	13178
15°	14234	12876	12565
20°	13977	12355	11985
25°	13723	11856	11458
30°	13368	11348	10936
35°	13007	10860	10552
40°	12629	10437	10173
45°	12268	10054	9841
50°	11880	9701	9513
55°	11474	9326	9180
60°	10976	8935	8830
65°	10455	8485	8425
70°	9870	8002	7993
75°	9118	7519	7581
80°	7936	7018	7158
85°	6738	6544	6791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12268 cd/sqm

TEST NUMBER: P999045

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	1.8
10°-20°	248.5	5.2
20°-30°	376.6	7.8
30°-40°	458.6	9.5
40°-50°	493.4	10.3
50°-60°	479.2	10.0
60°-70°	418.5	8.7
70°-80°	322.1	6.7
80°-90°	216.5	4.5
90°-100°	163.7	3.4
100°-110°	164.2	3.4
110°-120°	218.9	4.5
120°-130°	284.0	5.9
130°-140°	276.0	5.7
140°-150°	243.8	5.1
150°-160°	193.7	4.0
160°-170°	124.8	2.6
170°-180°	43.0	0.9
0°-30°	711.8	14.8
0°-40°	1170.4	24.3
0°-60°	2142.9	44.5
0°-90°	3099.9	64.4
90°-120°	546.8	11.4
90°-150°	1350.5	28.1
90°-180°	1712.0	35.6
0°-180°	4812.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	917	913	905	913	912	87
15°	874	877	877	889	888	246
25°	795	804	816	832	836	366
35°	685	708	733	762	771	428
45°	562	598	644	685	698	434
55°	431	478	547	595	612	385
65°	294	359	437	492	509	292
75°	163	237	322	379	396	172
85°	48	130	215	270	289	50
90°	14	94	181	236	253	10
95°	32	83	165	217	233	33
105°	106	154	134	184	200	114
115°	193	213	281	170	161	190
125°	268	272	321	359	372	240
135°	330	335	351	382	392	255
145°	381	381	386	396	402	239
155°	420	417	421	423	420	193
165°	442	440	441	444	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	

TEST NUMBER: P999045

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	914.1	914.1	914.1	914.1	914.1
2.5°	920.8	916.8	907.5	914.1	911.5
5°	916.8	912.8	904.9	912.8	911.5
7.5°	910.2	907.5	900.9	910.2	908.8
10°	902.2	899.6	895.6	906.2	904.9
12.5°	889.0	890.3	887.6	898.2	896.9
15°	874.4	877.0	877.0	889.0	887.6
17.5°	855.8	861.1	865.1	877.0	877.0
20°	837.3	843.9	849.2	863.8	863.8
22.5°	817.4	825.4	833.3	847.9	850.5
25°	794.9	804.2	816.1	832.0	836.0
27.5°	768.4	783.0	796.2	816.1	818.7
30°	741.9	759.1	776.3	797.5	801.5
32.5°	712.8	732.6	753.8	779.0	786.9
35°	684.9	707.5	732.6	761.8	771.0
37.5°	654.5	679.6	711.4	743.2	752.5
40°	624.0	653.1	688.9	723.4	735.3
42.5°	594.8	624.0	666.4	704.8	716.7
45°	561.7	597.5	643.9	684.9	698.2
47.5°	529.9	568.4	621.3	663.7	678.3
50°	496.8	537.9	597.5	642.5	657.1
52.5°	465.0	508.7	572.3	618.7	634.6
55°	430.6	478.3	547.2	594.8	612.1
57.5°	397.4	450.4	519.3	571.0	588.2
60°	361.7	418.6	494.2	544.5	563.1
62.5°	329.9	389.5	465.0	519.3	536.6
65°	294.1	359.0	437.2	491.5	508.7
67.5°	262.3	329.9	409.4	463.7	482.2
70°	227.9	296.8	378.9	435.9	451.8
72.5°	196.1	267.6	351.1	406.7	426.6
75°	163.0	237.1	321.9	378.9	396.1
77.5°	131.2	208.0	294.1	351.1	369.6
80°	99.4	180.2	266.3	321.9	340.5
82.5°	72.9	152.4	239.8	295.4	312.7
85°	47.7	129.8	214.6	270.3	288.8
87.5°	29.1	108.6	193.4	247.7	265.0
90°	13.5	94.0	181.4	236.1	252.6
92.5°	20.1	89.0	170.8	223.1	239.3
95°	31.8	83.4	165.1	217.1	232.6
97.5°	47.5	77.6	159.8	209.7	226.0
100°	67.1	71.4	151.1	202.7	218.0
102.5°	87.3	130.4	142.5	193.8	209.3
105°	105.9	154.1	133.8	183.8	199.7
107.5°	129.1	169.0	125.3	173.9	189.8
110°	150.0	183.3	153.9	163.6	179.5



TEST NUMBER: P999045

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	170.9	198.0	253.3	154.9	170.5
115°	193.1	213.2	281.0	169.5	160.6
117.5°	211.1	228.2	289.3	282.4	210.1
120°	232.6	242.8	301.7	342.7	313.1
122.5°	250.9	257.4	313.0	350.7	362.9
125°	268.1	272.4	321.0	359.1	371.9
127.5°	285.1	288.4	329.1	365.4	377.7
130°	301.1	305.0	336.4	371.8	382.1
132.5°	317.4	320.4	343.9	377.3	387.6
135°	329.9	335.1	351.3	382.4	392.3
137.5°	344.2	348.1	358.0	386.5	394.8
140°	358.3	359.6	365.8	389.9	396.3
142.5°	370.0	371.0	375.3	393.8	398.7
145°	381.1	380.8	386.4	396.5	401.6
147.5°	391.9	390.9	396.5	399.4	402.1
150°	402.4	400.1	405.3	407.3	405.6
152.5°	411.2	408.6	413.5	415.4	413.1
155°	419.7	416.7	420.7	422.6	420.0
157.5°	426.5	423.9	426.9	429.1	426.5
160°	432.4	430.5	432.4	434.4	432.1
162.5°	437.6	435.7	437.3	439.6	436.7
165°	442.2	440.2	441.2	443.5	441.2
167.5°	445.8	443.8	444.8	447.1	444.2
170°	448.7	446.8	447.4	449.7	446.8
172.5°	450.7	448.7	449.4	451.7	448.7
175°	452.3	450.0	450.7	453.0	449.7
177.5°	453.0	450.7	451.0	453.3	450.4
180°	451.4	451.4	451.4	451.4	451.4

TEST NUMBER: P999045

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-D_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.70	16.78	16.51	17.62	18.66	18.78	19.85	19.59	20.70	21.74
	3H	17.17	18.15	18.00	19.00	20.08	21.38	22.36	22.20	23.21	24.28
	4H	17.66	18.59	18.50	19.45	20.53	22.64	23.57	23.48	24.43	25.51
	6H	17.95	18.82	18.80	19.68	20.78	23.95	24.81	24.80	25.68	26.77
	8H	18.02	18.84	18.88	19.73	20.82	24.61	25.44	25.47	26.32	27.42
	12H	18.04	18.83	18.91	19.71	20.83	25.34	26.13	26.21	27.01	28.14
4H	2H	16.77	17.70	17.62	18.56	19.64	19.13	20.06	19.97	20.92	22.00
	3H	18.50	19.29	19.35	20.18	21.28	21.93	22.73	22.79	23.62	24.71
	4H	19.13	19.85	19.99	20.74	21.86	23.36	24.09	24.23	24.97	26.10
	6H	19.55	20.19	20.43	21.10	22.23	24.84	25.48	25.72	26.39	27.51
	8H	19.67	20.27	20.55	21.17	22.31	25.60	26.20	26.49	27.11	28.25
	12H	19.72	20.27	20.63	21.19	22.34	26.44	26.99	27.35	27.91	29.06
8H	4H	19.93	20.53	20.82	21.44	22.58	23.52	24.12	24.40	25.03	26.17
	6H	20.58	21.08	21.49	22.03	23.17	25.16	25.67	26.07	26.61	27.75
	8H	20.80	21.25	21.72	22.19	23.35	26.05	26.51	26.97	27.44	28.60
	12H	20.94	21.35	21.87	22.28	23.48	27.06	27.46	27.98	28.39	29.60
12H	4H	20.14	20.69	21.05	21.61	22.76	23.51	24.05	24.41	24.98	26.12
	6H	20.91	21.37	21.83	22.30	23.46	25.19	25.64	26.11	26.58	27.73
	8H	21.23	21.63	22.15	22.56	23.77	26.13	26.53	27.05	27.46	28.67