

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999051

Luminaire Tested: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999051
REPORT IS A COMBINATION OF REPORTS P984800 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-F_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4781.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999051

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999051

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	66	65
2	94	86	80	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	53	74	64	56	51	58	52	47	53	48	44	47	44	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35
6	66	54	45	39	63	52	44	38	47	41	36	43	37	33	39	34	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	38	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21590	21590	21590
5°	21625	20578	20433
10°	21449	19641	19251
15°	21135	18696	18008
20°	20710	17668	16831
25°	20287	16595	15656
30°	19755	15586	14422
35°	19254	14522	13210
40°	18632	13472	12065
45°	18016	12431	10943
50°	17342	11370	9778
55°	16635	10236	8673
60°	15840	9011	7527
65°	14966	7763	6320
70°	13858	6397	5104
75°	12324	4931	3941
80°	10467	3352	2537
85°	7600	1558	1079

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18016 cd/sqm

TEST NUMBER: P999051

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	2.7
10°-20°	361.2	7.6
20°-30°	530.8	11.1
30°-40°	616.5	12.9
40°-50°	615.7	12.9
50°-60°	536.9	11.2
60°-70°	396.9	8.3
70°-80°	224.5	4.7
80°-90°	60.0	1.3
90°-100°	14.7	0.3
100°-110°	54.9	1.1
110°-120°	145.7	3.0
120°-130°	241.7	5.1
130°-140°	256.7	5.4
140°-150°	238.6	5.0
150°-160°	191.8	4.0
160°-170°	123.6	2.6
170°-180°	42.5	0.9
0°-30°	1020.3	21.3
0°-40°	1636.8	34.2
0°-60°	2789.4	58.3
0°-90°	3470.8	72.6
90°-120°	215.4	4.5
90°-150°	952.3	19.9
90°-180°	1310.0	27.4
0°-180°	4781.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1364	1364	1364	1364	1364	
5°	1364	1359	1344	1355	1352	129
15°	1298	1290	1273	1279	1272	366
25°	1175	1165	1142	1145	1142	541
35°	1014	1001	980	972	965	633
45°	825	816	796	782	776	637
55°	624	616	601	585	578	558
65°	421	413	400	388	382	416
75°	220	218	211	203	206	235
85°	54	52	51	47	46	60
90°	0	4	6	8	9	4
95°	21	10	13	14	14	25
105°	98	108	20	23	25	105
115°	186	191	200	50	26	183
125°	263	267	273	276	276	234
135°	325	330	333	337	336	251
145°	377	377	383	385	383	236
155°	416	413	416	418	416	191
165°	438	436	437	439	437	124
175°	448	446	446	448	445	43
180°	447	447	447	447	447	

TEST NUMBER: P999051

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1363.9	1363.9	1363.9	1363.9	1363.9
2.5°	1371.8	1365.2	1350.8	1363.9	1361.3
5°	1363.9	1358.7	1344.2	1354.7	1352.1
7.5°	1354.7	1346.9	1332.4	1342.9	1340.3
10°	1340.3	1331.1	1315.4	1325.9	1321.9
12.5°	1320.6	1312.8	1297.0	1303.6	1301.0
15°	1298.3	1290.5	1273.4	1278.7	1272.1
17.5°	1270.8	1262.9	1245.9	1252.4	1245.9
20°	1240.6	1232.8	1214.4	1218.3	1213.1
22.5°	1210.5	1198.7	1181.6	1181.6	1179.0
25°	1175.1	1164.6	1142.3	1144.9	1142.3
27.5°	1135.7	1126.5	1109.5	1105.6	1099.0
30°	1096.4	1085.9	1066.2	1062.3	1057.0
32.5°	1054.4	1046.5	1025.6	1017.7	1012.4
35°	1013.8	1000.6	979.7	971.8	965.2
37.5°	967.9	956.0	935.1	925.9	919.3
40°	920.6	910.1	889.2	877.4	872.1
42.5°	874.7	864.2	843.3	830.1	822.3
45°	824.9	815.7	796.1	781.6	776.4
47.5°	776.4	767.2	746.2	731.8	723.9
50°	725.2	718.7	700.3	682.0	675.4
52.5°	675.4	666.2	649.2	634.7	625.6
55°	624.3	616.4	600.6	584.9	578.3
57.5°	573.1	566.5	549.5	533.8	528.5
60°	522.0	516.7	498.4	483.9	480.0
62.5°	472.1	462.9	449.8	436.7	431.5
65°	421.0	413.1	400.0	388.2	381.6
67.5°	368.5	362.0	350.2	341.0	335.7
70°	320.0	314.7	302.9	293.8	288.5
72.5°	270.2	264.9	258.4	249.2	245.2
75°	220.3	217.7	211.1	203.3	205.9
77.5°	175.7	170.5	167.9	163.9	160.0
80°	131.1	129.8	127.2	123.3	120.7
82.5°	89.2	89.2	87.9	82.6	82.6
85°	53.8	52.5	51.1	47.2	45.9
87.5°	23.6	21.0	18.4	14.4	13.1
90°	0.3	3.9	6.5	8.1	8.7
92.5°	8.1	6.8	7.8	8.4	8.7
95°	21.0	10.3	12.6	14.2	13.9
97.5°	37.8	11.3	16.5	17.5	17.8
100°	57.2	12.9	18.4	21.0	21.7
102.5°	78.6	77.9	19.1	22.6	23.6
105°	98.3	108.0	19.7	23.3	24.6
107.5°	121.3	129.4	20.4	23.9	25.2
110°	143.3	150.1	56.6	24.3	25.5



TEST NUMBER: P999051

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.0	169.8	164.3	24.9	25.9
115°	185.9	191.4	199.5	49.8	26.5
117.5°	205.0	211.5	217.0	170.7	86.0
120°	226.4	231.2	237.0	240.9	197.3
122.5°	244.5	249.7	256.1	258.1	258.4
125°	262.9	267.1	273.3	275.5	276.5
127.5°	279.7	284.3	289.1	292.3	292.7
130°	295.6	300.7	304.3	307.9	307.5
132.5°	311.7	315.9	319.5	322.4	322.1
135°	325.3	330.5	333.4	336.6	336.0
137.5°	339.6	343.4	346.7	349.9	348.9
140°	353.5	356.0	359.6	362.5	360.9
142.5°	365.1	367.4	371.6	374.2	372.5
145°	377.4	377.1	382.6	384.8	383.2
147.5°	388.1	387.1	392.6	394.2	392.9
150°	398.4	396.1	401.3	403.3	401.6
152.5°	407.1	404.6	409.4	411.3	409.1
155°	415.6	412.6	416.5	418.5	415.9
157.5°	422.3	419.8	422.7	424.9	422.3
160°	428.2	426.2	428.2	430.1	427.8
162.5°	433.3	431.4	433.0	435.3	432.4
165°	437.9	435.9	436.9	439.2	436.9
167.5°	441.4	439.5	440.5	442.7	439.8
170°	444.3	442.4	443.0	445.3	442.4
172.5°	446.3	444.3	445.0	447.2	444.3
175°	447.9	445.6	446.3	448.5	445.3
177.5°	448.5	446.3	446.6	448.9	446.0
180°	446.9	446.9	446.9	446.9	446.9

TEST NUMBER: P999051

CATALOG NUMBER: SA2XXDIP-B865D330UB2750-4F0-XX-W2A-F_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.78	18.88	18.51	19.64	20.55	18.56	19.67	19.29	20.42	21.33
	3H	19.13	20.13	19.88	20.89	21.83	20.20	21.20	20.95	21.97	22.90
	4H	19.55	20.49	20.31	21.26	22.21	20.81	21.75	21.57	22.52	23.47
	6H	19.78	20.65	20.56	21.43	22.40	21.22	22.09	22.00	22.88	23.84
	8H	19.82	20.64	20.61	21.45	22.41	21.34	22.16	22.13	22.97	23.93
	12H	19.82	20.61	20.61	21.40	22.40	21.39	22.18	22.19	22.98	23.97
4H	2H	18.27	19.21	19.04	19.99	20.94	18.92	19.86	19.69	20.64	21.59
	3H	19.81	20.60	20.60	21.41	22.38	20.72	21.51	21.50	22.32	23.28
	4H	20.33	21.04	21.13	21.86	22.85	21.41	22.13	22.21	22.94	23.93
	6H	20.65	21.27	21.46	22.10	23.10	21.92	22.54	22.74	23.38	24.38
	8H	20.71	21.29	21.53	22.12	23.13	22.07	22.65	22.89	23.48	24.49
	12H	20.72	21.24	21.56	22.09	23.11	22.14	22.67	22.98	23.52	24.54
8H	4H	20.52	21.10	21.34	21.93	22.95	21.52	22.10	22.34	22.93	23.94
	6H	20.92	21.40	21.77	22.27	23.29	22.10	22.58	22.94	23.45	24.46
	8H	21.02	21.45	21.88	22.32	23.35	22.29	22.71	23.15	23.58	24.61
	12H	21.07	21.44	21.93	22.30	23.39	22.40	22.77	23.26	23.63	24.72
12H	4H	20.52	21.04	21.36	21.89	22.91	21.49	22.01	22.33	22.87	23.89
	6H	20.94	21.37	21.80	22.23	23.27	22.09	22.52	22.95	23.39	24.42
	8H	21.06	21.44	21.92	22.30	23.39	22.30	22.67	23.16	23.53	24.62