

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931418

Luminaire Tested: DFN2DS-TR3F0-080DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-080DS930-RLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5542.0 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 85.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931418

CATALOG NUMBER: DFN2DS-TR3F0-080DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931418

CATALOG NUMBER: DFN2DS-TR3F0-080DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3358	3358	3358
5°	3371	3316	3334
10°	3345	3262	3234
15°	3306	3165	3074
20°	3253	3027	2875
25°	3199	2870	2682
30°	3123	2709	2435
35°	3050	2534	2218
40°	2975	2352	1967
45°	2888	2149	1740
50°	2799	1943	1518
55°	2707	1722	1304
60°	2601	1489	1082
65°	2481	1251	985
70°	2337	1030	906
75°	2160	939	846
80°	1907	840	770
85°	1498	662	662

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2888 cd/sqm

TEST NUMBER: P931418

CATALOG NUMBER: DFN2DS-TR3F0-080DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	4.6
10°-20°	693.3	12.5
20°-30°	973.4	17.6
30°-40°	1061.0	19.1
40°-50°	975.2	17.6
50°-60°	765.9	13.8
60°-70°	498.5	9.0
70°-80°	256.6	4.6
80°-90°	65.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1919.2	34.6
0°-40°	2980.3	53.8
0°-60°	4721.4	85.2
0°-90°	5542.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5542.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2695	2695	2695	2695	2695	
5°	2695	2683	2651	2673	2666	256
15°	2563	2536	2453	2407	2383	722
25°	2326	2248	2088	1988	1951	1070
35°	2005	1880	1666	1512	1458	1255
45°	1639	1475	1219	1046	988	1266
55°	1246	1056	792	646	600	1113
65°	841	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	126
90°	0	0	0	0	0	

TEST NUMBER: P931418

CATALOG NUMBER: DFN2DS-TR3F0-080DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2694.7	2694.7	2694.7	2694.7	2694.7
2.5°	2706.9	2694.7	2667.8	2692.4	2687.5
5°	2694.7	2682.6	2650.7	2672.7	2665.5
7.5°	2672.7	2658.2	2624.1	2633.7	2621.4
10°	2643.5	2626.4	2577.8	2570.3	2555.8
12.5°	2607.0	2585.0	2519.0	2504.5	2477.6
15°	2563.0	2536.1	2453.3	2407.0	2382.7
17.5°	2511.7	2472.7	2370.3	2316.7	2277.6
20°	2453.3	2404.4	2282.6	2221.8	2167.9
22.5°	2389.9	2333.8	2192.3	2109.5	2073.0
25°	2326.5	2248.4	2087.5	1987.6	1950.9
27.5°	2250.9	2167.9	1989.9	1875.3	1819.2
30°	2170.5	2077.6	1882.6	1758.4	1692.3
32.5°	2092.3	1980.1	1780.4	1633.9	1572.9
35°	2004.7	1880.2	1665.7	1512.1	1458.2
37.5°	1919.2	1785.0	1558.4	1389.9	1329.1
40°	1829.0	1682.8	1446.1	1272.9	1209.5
42.5°	1736.4	1580.4	1334.0	1153.5	1092.6
45°	1638.8	1475.3	1219.4	1046.1	987.6
47.5°	1546.2	1373.1	1109.7	936.4	882.8
50°	1443.7	1270.7	1002.4	833.9	782.9
52.5°	1343.6	1160.6	899.8	739.0	692.7
55°	1246.1	1055.9	792.5	646.3	600.0
57.5°	1146.2	951.1	697.6	561.0	521.8
60°	1043.7	848.7	597.4	473.2	434.2
62.5°	943.9	748.7	512.1	395.1	375.7
65°	841.4	643.7	424.3	341.6	334.0
67.5°	743.9	546.2	341.6	299.8	292.7
70°	641.4	451.3	282.8	258.4	248.7
72.5°	543.8	363.2	236.5	217.1	212.1
75°	448.7	277.9	195.1	178.0	175.7
77.5°	353.7	197.4	153.7	143.8	139.0
80°	265.7	141.6	117.0	107.3	107.3
82.5°	185.2	95.2	80.4	75.6	75.6
85°	104.8	53.5	46.3	46.3	46.3
87.5°	39.0	19.4	19.4	17.1	17.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931418

CATALOG NUMBER: DFN2DS-TR3F0-080DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.44	16.96	15.81	17.28	17.59	11.40	12.93	11.77	13.24	13.55
	3H	17.21	18.57	17.59	18.90	19.26	12.67	14.03	13.05	14.36	14.72
	4H	17.87	19.16	18.27	19.50	19.88	13.17	14.45	13.57	14.80	15.18
	6H	18.36	19.55	18.78	19.91	20.31	13.55	14.73	13.96	15.10	15.49
	8H	18.53	19.66	18.96	20.05	20.45	13.68	14.80	14.10	15.19	15.59
	12H	18.63	19.71	19.06	20.09	20.52	13.76	14.84	14.19	15.22	15.65
4H	2H	15.55	16.83	15.95	17.18	17.55	12.10	13.38	12.50	13.73	14.11
	3H	17.48	18.54	17.89	18.94	19.34	13.54	14.61	13.95	15.01	15.41
	4H	18.23	19.19	18.66	19.60	20.04	14.14	15.10	14.57	15.51	15.95
	6H	18.82	19.65	19.28	20.10	20.56	14.63	15.46	15.09	15.90	16.36
	8H	19.04	19.81	19.50	20.26	20.73	14.79	15.57	15.26	16.01	16.48
	12H	19.19	19.88	19.67	20.36	20.83	14.91	15.60	15.39	16.08	16.55
8H	4H	18.25	19.03	18.72	19.48	19.94	14.50	15.27	14.96	15.72	16.18
	6H	18.89	19.53	19.39	20.03	20.50	15.08	15.72	15.58	16.22	16.69
	8H	19.14	19.72	19.66	20.23	20.72	15.30	15.88	15.82	16.39	16.88
	12H	19.35	19.86	19.86	20.35	20.91	15.48	15.99	15.99	16.48	17.05
12H	4H	18.24	18.93	18.72	19.41	19.88	14.54	15.23	15.02	15.71	16.18
	6H	18.87	19.45	19.39	19.96	20.45	15.15	15.72	15.66	16.23	16.72
	8H	19.16	19.67	19.67	20.16	20.72	15.42	15.93	15.93	16.42	16.99