

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931435

Luminaire Tested: DFN2DS-TR3F0-090DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-090DS930-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7261.7 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 99.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931435

CATALOG NUMBER: DFN2DS-TR3F0-090DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931435

CATALOG NUMBER: DFN2DS-TR3F0-090DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3556	3556	3556
5°	3570	3519	3539
10°	3549	3483	3500
15°	3505	3438	3434
20°	3443	3370	3367
25°	3381	3287	3287
30°	3302	3210	3183
35°	3227	3119	3073
40°	3134	3027	2969
45°	3042	2936	2863
50°	2942	2841	2740
55°	2838	2731	2630
60°	2722	2599	2504
65°	2598	2468	2355
70°	2440	2310	2200
75°	2220	2127	2075
80°	1971	1910	1812
85°	1607	1533	1374

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3042 cd/sqm

TEST NUMBER: P931435

CATALOG NUMBER: DFN2DS-TR3F0-090DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.6	3.7
10°-20°	755.8	10.4
20°-30°	1110.7	15.3
30°-40°	1290.1	17.8
40°-50°	1288.5	17.7
50°-60°	1123.5	15.5
60°-70°	830.5	11.4
70°-80°	469.9	6.5
80°-90°	124.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2135.2	29.4
0°-40°	3425.3	47.2
0°-60°	5837.3	80.4
0°-90°	7261.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7261.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2854	2854	2854	2854	2854	
5°	2854	2843	2813	2835	2830	271
15°	2717	2701	2665	2676	2662	765
25°	2459	2437	2391	2396	2391	1131
35°	2122	2094	2050	2034	2020	1325
45°	1726	1707	1666	1636	1625	1332
55°	1306	1290	1257	1224	1210	1168
65°	881	864	837	812	799	871
75°	461	456	442	425	431	492
85°	112	110	107	99	96	132
90°	0	0	0	0	0	

TEST NUMBER: P931435

CATALOG NUMBER: DFN2DS-TR3F0-090DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2854.0	2854.0	2854.0	2854.0	2854.0
2.5°	2870.7	2857.0	2826.7	2854.0	2848.8
5°	2854.0	2843.3	2813.1	2834.9	2829.6
7.5°	2834.9	2818.6	2788.3	2810.4	2804.9
10°	2804.9	2785.7	2752.7	2774.6	2766.4
12.5°	2763.5	2747.2	2714.4	2728.0	2722.5
15°	2717.0	2700.7	2664.8	2675.9	2662.2
17.5°	2659.3	2643.0	2607.2	2620.9	2607.2
20°	2596.1	2579.8	2541.3	2549.5	2538.7
22.5°	2533.2	2508.5	2472.6	2472.6	2467.1
25°	2458.9	2437.1	2390.6	2395.8	2390.6
27.5°	2376.5	2357.3	2321.9	2313.7	2300.0
30°	2294.5	2272.3	2231.2	2223.1	2212.1
32.5°	2206.5	2190.2	2146.2	2129.7	2118.6
35°	2121.5	2094.1	2050.1	2033.6	2019.9
37.5°	2025.4	2000.7	1956.7	1937.5	1923.8
40°	1926.7	1904.6	1860.6	1836.1	1825.1
42.5°	1830.6	1808.5	1764.8	1737.2	1720.9
45°	1726.3	1707.2	1665.8	1635.8	1624.8
47.5°	1624.8	1605.6	1561.5	1531.3	1515.0
50°	1517.6	1503.9	1465.5	1427.1	1413.4
52.5°	1413.4	1394.1	1358.6	1328.4	1309.1
55°	1306.5	1289.9	1257.0	1224.1	1210.4
57.5°	1199.4	1185.7	1149.9	1117.0	1105.9
60°	1092.2	1081.4	1043.0	1012.7	1004.6
62.5°	987.9	968.7	941.3	914.0	902.9
65°	881.1	864.5	837.1	812.4	798.7
67.5°	771.3	757.4	732.8	713.7	702.6
70°	669.7	658.6	633.9	614.7	603.9
72.5°	565.4	554.4	540.7	521.5	513.4
75°	461.0	455.7	441.7	425.4	431.0
77.5°	367.7	356.7	351.2	343.0	334.9
80°	274.6	271.6	266.1	257.9	252.5
82.5°	186.6	186.6	184.0	172.9	172.9
85°	112.4	109.8	107.2	98.7	96.1
87.5°	49.5	43.9	38.5	30.3	27.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931435

CATALOG NUMBER: DFN2DS-TR3F0-090DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.69	17.30	16.06	17.62	17.93	15.25	16.86	15.61	17.17	17.49
	3H	17.44	18.90	17.82	19.22	19.58	16.95	18.40	17.33	18.73	19.09
	4H	18.09	19.46	18.49	19.80	20.18	17.59	18.96	17.99	19.31	19.69
	6H	18.56	19.82	18.97	20.19	20.58	18.06	19.32	18.47	19.69	20.08
	8H	18.70	19.91	19.12	20.30	20.70	18.20	19.41	18.62	19.80	20.20
	12H	18.79	19.95	19.22	20.33	20.76	18.28	19.44	18.71	19.82	20.25
4H	2H	16.25	17.62	16.65	17.97	18.34	15.90	17.27	16.30	17.62	17.99
	3H	18.23	19.37	18.64	19.77	20.17	17.82	18.97	18.23	19.36	19.76
	4H	19.00	20.04	19.43	20.45	20.89	18.58	19.62	19.01	20.03	20.46
	6H	19.60	20.50	20.05	20.94	21.40	19.17	20.07	19.62	20.51	20.97
	8H	19.79	20.64	20.25	21.08	21.54	19.35	20.20	19.81	20.64	21.11
	12H	19.92	20.68	20.40	21.16	21.63	19.47	20.23	19.95	20.70	21.17
8H	4H	19.28	20.12	19.74	20.57	21.03	18.90	19.75	19.36	20.19	20.66
	6H	19.99	20.69	20.48	21.18	21.66	19.61	20.31	20.10	20.80	21.28
	8H	20.25	20.88	20.76	21.39	21.87	19.86	20.49	20.37	21.00	21.48
	12H	20.45	21.01	20.96	21.50	22.06	20.04	20.59	20.54	21.08	21.65
12H	4H	19.30	20.06	19.78	20.54	21.01	18.94	19.70	19.42	20.17	20.64
	6H	20.04	20.67	20.55	21.17	21.66	19.67	20.30	20.18	20.81	21.29
	8H	20.35	20.91	20.86	21.40	21.96	19.97	20.53	20.48	21.02	21.58

END OF REPORT