

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999103

Luminaire Tested: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999103
REPORT IS A COMBINATION OF REPORTS P984852 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5545.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999103

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999103

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	97	92	88	84	90	86	82	78	73	70	67	62	60	57	51	50	48
2	88	80	73	67	81	74	68	63	63	59	55	53	50	47	44	42	39
3	80	69	61	55	74	64	57	52	55	50	45	47	42	39	39	35	33
4	73	61	53	46	67	57	49	43	49	43	38	41	37	33	34	31	28
5	67	54	46	39	61	50	43	37	43	37	32	37	32	28	31	27	24
6	61	49	40	34	57	45	37	32	39	33	28	33	28	24	28	24	21
7	57	44	35	29	52	41	33	28	35	29	25	30	25	21	25	21	18
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	24	19	25	20	17	21	17	15
10	46	33	26	21	42	31	24	20	27	21	17	23	19	15	20	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14283	14283	14283
5°	14349	13674	13596
10°	14252	13200	13008
15°	14050	12710	12404
20°	13797	12196	11829
25°	13546	11704	11310
30°	13195	11202	10795
35°	12840	10720	10417
40°	12465	10303	10041
45°	12110	9925	9714
50°	11727	9576	9390
55°	11325	9205	9062
60°	10833	8819	8716
65°	10320	8376	8318
70°	9740	7899	7888
75°	9001	7423	7484
80°	7832	6928	7066
85°	6653	6461	6704

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12110 cd/sqm

TEST NUMBER: P999103

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.5	1.5
10°-20°	245.3	4.4
20°-30°	371.7	6.7
30°-40°	452.7	8.2
40°-50°	487.0	8.8
50°-60°	473.0	8.5
60°-70°	413.1	7.4
70°-80°	317.9	5.7
80°-90°	214.2	3.9
90°-100°	170.5	3.1
100°-110°	195.4	3.5
110°-120°	304.4	5.5
120°-130°	426.9	7.7
130°-140°	428.1	7.7
140°-150°	385.3	6.9
150°-160°	307.5	5.5
160°-170°	198.2	3.6
170°-180°	68.2	1.2
0°-30°	702.6	12.7
0°-40°	1155.3	20.8
0°-60°	2115.3	38.1
0°-90°	3060.4	55.2
90°-120°	670.3	12.1
90°-150°	1910.7	34.5
90°-180°	2485.0	44.8
0°-180°	5545.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	902	902	902	902	902	
5°	905	901	893	901	900	86
15°	863	866	866	878	876	243
25°	785	794	806	821	825	361
35°	676	698	723	752	761	423
45°	554	590	636	676	689	428
55°	425	472	540	587	604	380
65°	290	354	432	485	502	288
75°	161	234	318	374	391	170
85°	47	128	212	267	285	50
90°	14	95	183	238	255	11
95°	44	88	171	223	238	48
105°	164	218	144	196	212	176
115°	303	327	398	198	175	298
125°	424	431	483	522	535	379
135°	523	531	549	582	591	404
145°	605	605	613	625	629	379
155°	666	662	668	671	667	307
165°	702	699	700	704	700	198
175°	718	714	716	719	714	68
180°	717	717	717	717	717	

TEST NUMBER: P999103

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	902.3	902.3	902.3	902.3	902.3
2.5°	908.9	905.0	895.8	902.3	899.7
5°	905.0	901.0	893.2	901.0	899.7
7.5°	898.4	895.8	889.3	898.4	897.1
10°	890.6	888.0	884.0	894.5	893.2
12.5°	877.5	878.8	876.2	886.6	885.3
15°	863.1	865.7	865.7	877.5	876.2
17.5°	844.8	850.0	854.0	865.7	865.7
20°	826.5	833.0	838.3	852.6	852.6
22.5°	806.9	814.7	822.6	836.9	839.6
25°	784.6	793.8	805.6	821.3	825.2
27.5°	758.5	772.9	785.9	805.6	808.2
30°	732.3	749.3	766.3	787.3	791.2
32.5°	703.6	723.2	744.1	768.9	776.8
35°	676.1	698.3	723.2	751.9	761.1
37.5°	646.0	670.9	702.3	733.6	742.8
40°	615.9	644.7	680.0	714.0	725.8
42.5°	587.2	615.9	657.8	695.7	707.5
45°	554.5	589.8	635.6	676.1	689.2
47.5°	523.1	561.0	613.3	655.2	669.6
50°	490.4	530.9	589.8	634.3	648.6
52.5°	459.0	502.2	564.9	610.7	626.4
55°	425.0	472.1	540.1	587.2	604.2
57.5°	392.3	444.6	512.6	563.6	580.6
60°	357.0	413.2	487.8	537.5	555.8
62.5°	325.6	384.5	459.0	512.6	529.6
65°	290.3	354.4	431.6	485.2	502.2
67.5°	258.9	325.6	404.1	457.7	476.0
70°	224.9	292.9	374.0	430.2	445.9
72.5°	193.5	264.2	346.5	401.5	421.1
75°	160.9	234.1	317.8	374.0	391.0
77.5°	129.5	205.3	290.3	346.5	364.9
80°	98.1	177.9	262.9	317.8	336.1
82.5°	71.9	150.4	236.7	291.6	308.6
85°	47.1	128.2	211.9	266.8	285.1
87.5°	28.8	107.2	190.9	244.5	261.5
90°	13.6	95.1	183.0	237.9	254.6
92.5°	24.8	92.0	173.3	225.4	241.5
95°	44.2	88.5	170.6	222.9	238.1
97.5°	69.9	83.5	167.6	217.6	233.8
100°	101.0	78.2	160.4	212.9	228.2
102.5°	133.8	176.0	152.2	205.0	221.0
105°	164.1	217.7	144.1	195.5	212.0
107.5°	200.9	245.3	136.0	186.2	202.6
110°	234.9	272.0	186.2	176.2	192.7



TEST NUMBER: P999103

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	268.1	298.4	349.7	168.1	184.0
115°	303.3	326.6	398.4	197.5	174.6
117.5°	332.6	353.5	417.2	382.3	259.5
120°	366.9	379.9	441.6	484.4	428.8
122.5°	395.9	405.5	464.3	502.7	515.0
125°	424.1	430.9	482.6	521.6	534.8
127.5°	451.1	457.1	500.1	538.0	550.3
130°	476.5	483.5	516.7	553.8	563.7
132.5°	502.4	507.9	533.2	567.9	577.9
135°	522.9	531.2	549.0	581.6	591.0
137.5°	545.7	552.0	563.6	593.7	601.3
140°	568.0	570.9	579.2	604.7	610.1
142.5°	586.7	589.0	595.8	615.6	619.5
145°	605.1	604.6	613.4	624.8	628.8
147.5°	622.2	620.6	629.5	633.4	635.2
150°	638.8	635.2	643.5	646.6	644.0
152.5°	652.8	648.6	656.4	659.5	655.9
155°	666.3	661.6	667.8	670.9	666.8
157.5°	677.2	673.0	677.7	681.3	677.2
160°	686.5	683.4	686.5	689.6	686.0
162.5°	694.8	691.7	694.3	697.9	693.2
165°	702.1	698.9	700.5	704.1	700.5
167.5°	707.8	704.6	706.2	709.8	705.2
170°	712.4	709.3	710.4	714.0	709.3
172.5°	715.5	712.4	713.5	717.1	712.4
175°	718.1	714.5	715.5	719.2	714.0
177.5°	719.2	715.5	716.1	719.7	715.0
180°	716.6	716.6	716.6	716.6	716.6

TEST NUMBER: P999103

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_2700K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.90	15.87	15.80	16.80	17.99	17.98	18.95	18.88	19.88	21.07
	3H	16.37	17.25	17.28	18.18	19.40	20.58	21.45	21.49	22.39	23.60
	4H	16.85	17.68	17.78	18.63	19.85	21.83	22.67	22.76	23.61	24.83
	6H	17.14	17.91	18.08	18.86	20.10	23.13	23.91	24.07	24.85	26.09
	8H	17.20	17.94	18.15	18.91	20.14	23.80	24.53	24.74	25.50	26.74
	12H	17.22	17.93	18.17	18.89	20.15	24.53	25.23	25.48	26.19	27.45
4H	2H	15.97	16.80	16.90	17.74	18.96	18.32	19.15	19.25	20.10	21.32
	3H	17.68	18.39	18.62	19.36	20.60	21.12	21.83	22.06	22.80	24.04
	4H	18.31	18.96	19.26	19.92	21.19	22.54	23.19	23.49	24.16	25.42
	6H	18.73	19.30	19.69	20.29	21.55	24.01	24.58	24.98	25.57	26.83
	8H	18.84	19.37	19.80	20.36	21.63	24.77	25.31	25.74	26.29	27.57
	12H	18.89	19.38	19.87	20.37	21.66	25.61	26.09	26.59	27.09	28.38
8H	4H	19.11	19.64	20.07	20.62	21.90	22.69	23.23	23.66	24.21	25.49
	6H	19.74	20.19	20.73	21.22	22.49	24.33	24.78	25.32	25.80	27.07
	8H	19.97	20.37	20.96	21.38	22.67	25.22	25.62	26.22	26.63	27.92
	12H	20.11	20.46	21.11	21.47	22.80	26.22	26.57	27.22	27.58	28.91
12H	4H	19.31	19.80	20.29	20.79	22.08	22.67	23.16	23.66	24.16	25.44
	6H	20.08	20.48	21.08	21.49	22.78	24.35	24.75	25.35	25.76	27.06
	8H	20.39	20.74	21.39	21.75	23.09	25.29	25.64	26.29	26.65	27.98

END OF REPORT