

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931365

Luminaire Tested: DFN2DS-TR3F0-050DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931365
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-050DS935-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4257.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931365

CATALOG NUMBER: DFN2DS-TR3F0-050DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931365

CATALOG NUMBER: DFN2DS-TR3F0-050DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2085	2085	2085
5°	2093	2063	2075
10°	2081	2042	2052
15°	2055	2015	2013
20°	2018	1976	1974
25°	1982	1927	1927
30°	1935	1882	1866
35°	1892	1828	1801
40°	1837	1774	1740
45°	1783	1721	1678
50°	1725	1665	1606
55°	1664	1601	1542
60°	1596	1524	1468
65°	1523	1447	1381
70°	1430	1354	1290
75°	1301	1246	1217
80°	1155	1119	1062
85°	942	898	805

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1783 cd/sqm

TEST NUMBER: P931365

CATALOG NUMBER: DFN2DS-TR3F0-050DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	3.7
10°-20°	443.1	10.4
20°-30°	651.1	15.3
30°-40°	756.3	17.8
40°-50°	755.3	17.7
50°-60°	658.6	15.5
60°-70°	486.9	11.4
70°-80°	275.5	6.5
80°-90°	72.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1251.7	29.4
0°-40°	2008.0	47.2
0°-60°	3421.9	80.4
0°-90°	4257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4257.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1673	1673	1673	1673	1673	
5°	1673	1667	1649	1662	1659	159
15°	1593	1583	1562	1569	1561	449
25°	1442	1429	1401	1404	1401	663
35°	1244	1228	1202	1192	1184	777
45°	1012	1001	976	959	952	781
55°	766	756	737	718	710	685
65°	516	507	491	476	468	511
75°	270	267	259	249	253	288
85°	66	64	63	58	56	77
90°	0	0	0	0	0	

TEST NUMBER: P931365

CATALOG NUMBER: DFN2DS-TR3F0-050DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1673.1	1673.1	1673.1	1673.1	1673.1
2.5°	1682.8	1674.8	1657.1	1673.1	1670.1
5°	1673.1	1666.9	1649.0	1661.9	1658.9
7.5°	1661.9	1652.3	1634.6	1647.6	1644.3
10°	1644.3	1633.1	1613.8	1626.5	1621.8
12.5°	1620.1	1610.5	1591.3	1599.3	1596.0
15°	1592.7	1583.2	1562.2	1568.7	1560.6
17.5°	1558.9	1549.4	1528.4	1536.4	1528.4
20°	1521.9	1512.4	1489.9	1494.6	1488.3
22.5°	1485.0	1470.5	1449.5	1449.5	1446.3
25°	1441.5	1428.7	1401.4	1404.5	1401.4
27.5°	1393.2	1381.9	1361.1	1356.3	1348.3
30°	1345.0	1332.1	1308.1	1303.2	1296.8
32.5°	1293.5	1284.0	1258.2	1248.5	1242.0
35°	1243.6	1227.6	1201.8	1192.1	1184.1
37.5°	1187.3	1172.9	1147.1	1135.8	1127.8
40°	1129.5	1116.5	1090.7	1076.4	1069.9
42.5°	1073.2	1060.2	1034.6	1018.3	1008.8
45°	1012.0	1000.8	976.5	959.0	952.4
47.5°	952.4	941.2	915.5	897.7	888.1
50°	889.7	881.7	859.1	836.6	828.5
52.5°	828.5	817.3	796.4	778.7	767.5
55°	765.9	756.2	736.8	717.6	709.6
57.5°	703.0	695.1	674.1	654.8	648.3
60°	640.3	634.0	611.5	593.7	588.9
62.5°	579.2	567.9	551.9	535.8	529.3
65°	516.5	506.8	490.7	476.3	468.2
67.5°	452.2	444.0	429.7	418.4	411.9
70°	392.6	386.1	371.6	360.3	354.1
72.5°	331.5	325.0	317.0	305.7	300.9
75°	270.2	267.1	258.9	249.4	252.7
77.5°	215.6	209.1	205.9	201.1	196.3
80°	161.0	159.3	156.0	151.3	148.0
82.5°	109.4	109.4	107.8	101.4	101.4
85°	65.9	64.3	62.8	57.9	56.3
87.5°	29.0	25.8	22.5	17.7	16.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931365

CATALOG NUMBER: DFN2DS-TR3F0-050DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.84	15.45	14.20	15.76	16.07	13.39	15.00	13.76	15.32	15.63
	3H	15.59	17.04	15.96	17.37	17.73	15.09	16.55	15.47	16.88	17.24
	4H	16.23	17.60	16.63	17.95	18.32	15.74	17.11	16.14	17.45	17.83
	6H	16.70	17.97	17.11	18.33	18.73	16.20	17.47	16.61	17.83	18.22
	8H	16.84	18.05	17.27	18.44	18.84	16.34	17.55	16.77	17.94	18.34
	12H	16.93	18.09	17.36	18.48	18.90	16.42	17.58	16.85	17.96	18.39
4H	2H	14.40	15.76	14.79	16.11	16.49	14.04	15.41	14.44	15.76	16.14
	3H	16.37	17.52	16.78	17.91	18.31	15.96	17.11	16.37	17.51	17.91
	4H	17.15	18.18	17.58	18.60	19.03	16.72	17.76	17.16	18.17	18.61
	6H	17.74	18.65	18.20	19.09	19.55	17.31	18.22	17.77	18.66	19.11
	8H	17.93	18.78	18.39	19.22	19.69	17.50	18.34	17.96	18.78	19.25
	12H	18.07	18.83	18.55	19.30	19.77	17.61	18.37	18.09	18.85	19.32
8H	4H	17.42	18.27	17.88	18.71	19.18	17.05	17.89	17.51	18.34	18.80
	6H	18.14	18.84	18.63	19.33	19.80	17.75	18.46	18.25	18.95	19.42
	8H	18.39	19.02	18.90	19.53	20.02	18.00	18.63	18.51	19.14	19.63
	12H	18.59	19.15	19.10	19.64	20.20	18.18	18.74	18.69	19.23	19.79
12H	4H	17.45	18.21	17.93	18.68	19.15	17.08	17.84	17.56	18.32	18.79
	6H	18.18	18.81	18.69	19.32	19.81	17.81	18.44	18.32	18.95	19.44
	8H	18.49	19.05	19.00	19.54	20.10	18.12	18.67	18.62	19.16	19.73