

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999106

Luminaire Tested: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999106
REPORT IS A COMBINATION OF REPORTS P984855 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5561.0 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999106

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999106

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	97	92	88	84	90	86	82	78	73	70	67	62	60	57	51	50	48
2	88	80	73	67	81	74	68	63	63	59	55	53	50	47	44	42	39
3	80	69	61	55	74	64	57	52	55	50	45	47	42	39	39	35	33
4	73	61	53	46	67	57	49	43	49	43	38	41	37	33	34	31	28
5	67	54	46	39	61	50	43	37	43	37	32	37	32	28	31	27	24
6	61	49	40	34	57	45	37	32	39	33	28	33	28	24	28	24	21
7	57	44	35	29	52	41	33	28	35	29	25	30	25	21	25	21	18
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	24	19	25	20	17	21	17	15
10	46	33	26	21	42	31	24	20	27	21	17	23	19	15	20	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14326	14326	14326
5°	14390	13714	13636
10°	14294	13239	13046
15°	14091	12747	12439
20°	13837	12231	11864
25°	13585	11737	11343
30°	13234	11236	10827
35°	12878	10751	10447
40°	12502	10333	10070
45°	12145	9953	9742
50°	11761	9603	9417
55°	11357	9232	9087
60°	10863	8845	8741
65°	10352	8400	8341
70°	9770	7922	7911
75°	9023	7444	7505
80°	7856	6946	7087
85°	6667	6480	6723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12145 cd/sqm

TEST NUMBER: P999106

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	1.5
10°-20°	246.0	4.4
20°-30°	372.8	6.7
30°-40°	454.0	8.2
40°-50°	488.4	8.8
50°-60°	474.4	8.5
60°-70°	414.3	7.4
70°-80°	318.8	5.7
80°-90°	214.8	3.9
90°-100°	171.0	3.1
100°-110°	195.9	3.5
110°-120°	305.3	5.5
120°-130°	428.1	7.7
130°-140°	429.3	7.7
140°-150°	386.4	6.9
150°-160°	308.4	5.5
160°-170°	198.7	3.6
170°-180°	68.4	1.2
0°-30°	704.6	12.7
0°-40°	1158.6	20.8
0°-60°	2121.4	38.1
0°-90°	3069.3	55.2
90°-120°	672.3	12.1
90°-150°	1916.1	34.5
90°-180°	2492.0	44.8
0°-180°	5561.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	908	904	896	904	902	86
15°	866	868	868	880	879	244
25°	787	796	808	824	828	362
35°	678	700	725	754	763	424
45°	556	592	637	678	691	429
55°	426	474	542	589	606	381
65°	291	355	433	487	504	289
75°	161	235	319	375	392	171
85°	47	128	212	268	286	50
90°	14	95	184	239	255	11
95°	44	89	171	224	239	48
105°	165	218	144	196	213	176
115°	304	328	400	198	175	299
125°	425	432	484	523	536	380
135°	524	533	550	583	593	406
145°	607	606	615	627	631	380
155°	668	664	670	673	669	308
165°	704	701	702	706	702	199
175°	720	716	718	721	716	69
180°	719	719	719	719	719	

TEST NUMBER: P999106

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	905.0	905.0	905.0	905.0	905.0
2.5°	911.5	907.6	898.4	905.0	902.3
5°	907.6	903.6	895.8	903.6	902.3
7.5°	901.0	898.4	891.8	901.0	899.7
10°	893.2	890.5	886.6	897.1	895.8
12.5°	880.0	881.3	878.7	889.2	887.9
15°	865.6	868.2	868.2	880.0	878.7
17.5°	847.2	852.5	856.4	868.2	868.2
20°	828.9	835.4	840.7	855.1	855.1
22.5°	809.2	817.1	825.0	839.4	842.0
25°	786.9	796.1	807.9	823.6	827.6
27.5°	760.7	775.1	788.2	807.9	810.5
30°	734.5	751.5	768.6	789.5	793.5
32.5°	705.6	725.3	746.3	771.2	779.1
35°	678.1	700.4	725.3	754.1	763.3
37.5°	647.9	672.8	704.3	735.8	745.0
40°	617.7	646.6	682.0	716.1	727.9
42.5°	588.9	617.7	659.7	697.7	709.5
45°	556.1	591.5	637.4	678.1	691.2
47.5°	524.6	562.6	615.1	657.1	671.5
50°	491.8	532.5	591.5	636.1	650.5
52.5°	460.3	503.6	566.6	612.5	628.2
55°	426.2	473.5	541.7	588.9	605.9
57.5°	393.5	445.9	514.1	565.3	582.3
60°	358.0	414.4	489.2	539.0	557.4
62.5°	326.6	385.6	460.3	514.1	531.2
65°	291.2	355.4	432.8	486.6	503.6
67.5°	259.7	326.6	405.3	459.0	477.4
70°	225.6	293.8	375.1	431.5	447.2
72.5°	194.1	264.9	347.6	402.6	422.3
75°	161.3	234.8	318.7	375.1	392.1
77.5°	129.8	205.9	291.2	347.6	365.9
80°	98.4	178.4	263.6	318.7	337.1
82.5°	72.1	150.8	237.4	292.5	309.5
85°	47.2	128.5	212.5	267.6	285.9
87.5°	28.9	107.5	191.5	245.3	262.3
90°	13.6	95.4	183.5	238.6	255.3
92.5°	24.8	92.2	173.8	226.0	242.2
95°	44.3	88.7	171.1	223.6	238.8
97.5°	70.0	83.8	168.1	218.3	234.5
100°	101.2	78.5	160.8	213.5	228.9
102.5°	134.3	176.4	152.7	205.6	221.6
105°	164.7	218.3	144.5	196.1	212.6
107.5°	201.6	246.0	136.4	186.7	203.2
110°	235.6	272.8	186.7	176.7	193.2



TEST NUMBER: P999106

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	268.8	299.2	350.8	168.5	184.6
115°	304.2	327.5	399.5	198.1	175.1
117.5°	333.6	354.5	418.4	383.5	260.3
120°	367.9	381.0	442.7	485.8	430.0
122.5°	397.0	406.6	465.6	504.1	516.5
125°	425.3	432.1	484.0	523.0	536.4
127.5°	452.4	458.4	501.6	539.6	551.9
130°	477.9	484.9	518.2	555.3	565.3
132.5°	503.9	509.3	534.7	569.5	579.5
135°	524.4	532.7	550.5	583.3	592.8
137.5°	547.3	553.5	565.3	595.4	603.1
140°	569.6	572.5	580.8	606.5	611.8
142.5°	588.4	590.7	597.5	617.3	621.3
145°	606.8	606.3	615.1	626.7	630.6
147.5°	624.0	622.4	631.3	635.2	637.0
150°	640.6	637.0	645.3	648.4	645.8
152.5°	654.7	650.5	658.3	661.4	657.8
155°	668.2	663.5	669.7	672.9	668.7
157.5°	679.1	674.9	679.6	683.3	679.1
160°	688.5	685.3	688.5	691.6	687.9
162.5°	696.8	693.7	696.3	699.9	695.2
165°	704.1	700.9	702.5	706.1	702.5
167.5°	709.8	706.7	708.2	711.9	707.2
170°	714.5	711.3	712.4	716.0	711.3
172.5°	717.6	714.5	715.5	719.1	714.5
175°	720.2	716.5	717.6	721.2	716.0
177.5°	721.2	717.6	718.1	721.7	717.1
180°	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P999106

CATALOG NUMBER: SA2XXDIP-B865D530UB2750-4F0-XX-W2A-D_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.92	15.88	15.81	16.81	18.00	17.99	18.96	18.89	19.89	21.08
	3H	16.38	17.26	17.29	18.20	19.41	20.59	21.46	21.50	22.40	23.61
	4H	16.86	17.69	17.79	18.64	19.86	21.84	22.68	22.77	23.62	24.84
	6H	17.15	17.92	18.09	18.87	20.11	23.15	23.92	24.08	24.86	26.10
	8H	17.21	17.95	18.16	18.92	20.15	23.81	24.55	24.75	25.51	26.75
	12H	17.23	17.94	18.18	18.90	20.16	24.54	25.24	25.49	26.20	27.46
4H	2H	15.98	16.81	16.91	17.75	18.97	18.33	19.16	19.26	20.11	21.33
	3H	17.69	18.40	18.63	19.37	20.61	21.13	21.84	22.07	22.81	24.05
	4H	18.32	18.97	19.27	19.93	21.20	22.55	23.20	23.50	24.17	25.43
	6H	18.74	19.31	19.70	20.30	21.56	24.02	24.59	24.99	25.58	26.84
	8H	18.85	19.38	19.81	20.37	21.64	24.78	25.32	25.75	26.30	27.58
	12H	18.90	19.39	19.88	20.38	21.67	25.62	26.10	26.60	27.10	28.39
8H	4H	19.12	19.65	20.08	20.63	21.91	22.70	23.24	23.67	24.22	25.50
	6H	19.75	20.20	20.74	21.23	22.50	24.34	24.79	25.33	25.81	27.08
	8H	19.98	20.38	20.97	21.39	22.68	25.23	25.63	26.23	26.64	27.93
	12H	20.12	20.47	21.12	21.48	22.81	26.23	26.58	27.23	27.59	28.92
12H	4H	19.32	19.81	20.30	20.81	22.09	22.68	23.17	23.67	24.17	25.45
	6H	20.09	20.49	21.09	21.50	22.79	24.36	24.76	25.36	25.78	27.07
	8H	20.40	20.75	21.40	21.76	23.10	25.30	25.65	26.30	26.66	27.99

END OF REPORT