

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931421

Luminaire Tested: DFN2DS-TR3F0-080DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR3F0-080DS940-FLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7064.6 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.16' x L: 2.74' x H: 0')
CIE Type: Direct

Input Watts (W): 85.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931421

CATALOG NUMBER: DFN2DS-TR3F0-080DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931421

CATALOG NUMBER: DFN2DS-TR3F0-080DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3460	3460	3460
5°	3473	3423	3444
10°	3453	3389	3406
15°	3410	3344	3341
20°	3349	3279	3275
25°	3289	3198	3198
30°	3212	3124	3096
35°	3140	3034	2989
40°	3049	2944	2888
45°	2960	2856	2786
50°	2862	2764	2666
55°	2761	2657	2558
60°	2648	2529	2436
65°	2527	2401	2291
70°	2374	2247	2140
75°	2159	2069	2018
80°	1917	1858	1762
85°	1564	1491	1337

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2960 cd/sqm

TEST NUMBER: P931421

CATALOG NUMBER: DFN2DS-TR3F0-080DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	3.7
10°-20°	735.3	10.4
20°-30°	1080.6	15.3
30°-40°	1255.1	17.8
40°-50°	1253.5	17.7
50°-60°	1093.0	15.5
60°-70°	808.0	11.4
70°-80°	457.1	6.5
80°-90°	120.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2077.3	29.4
0°-40°	3332.3	47.2
0°-60°	5678.8	80.4
0°-90°	7064.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7064.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2777	2777	2777	2777	2777	
5°	2777	2766	2737	2758	2753	264
15°	2643	2627	2592	2603	2590	744
25°	2392	2371	2326	2331	2326	1101
35°	2064	2037	1994	1978	1965	1289
45°	1680	1661	1621	1591	1581	1296
55°	1271	1255	1223	1191	1178	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	129
90°	0	0	0	0	0	

TEST NUMBER: P931421

CATALOG NUMBER: DFN2DS-TR3F0-080DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2776.6	2776.6	2776.6	2776.6	2776.6
2.5°	2792.8	2779.5	2750.0	2776.6	2771.5
5°	2776.6	2766.2	2736.7	2758.0	2752.9
7.5°	2758.0	2742.1	2712.7	2734.2	2728.8
10°	2728.8	2710.1	2678.1	2699.3	2691.4
12.5°	2688.6	2672.7	2640.7	2654.0	2648.6
15°	2643.3	2627.4	2592.5	2603.3	2590.0
17.5°	2587.2	2571.3	2536.4	2549.8	2536.4
20°	2525.7	2509.8	2472.4	2480.4	2469.9
22.5°	2464.5	2440.4	2405.5	2405.5	2400.2
25°	2392.3	2371.0	2325.7	2330.8	2325.7
27.5°	2312.1	2293.4	2258.8	2250.9	2237.6
30°	2232.2	2210.6	2170.8	2162.8	2152.0
32.5°	2146.7	2130.8	2088.0	2071.8	2061.1
35°	2063.9	2037.3	1994.5	1978.4	1965.1
37.5°	1970.4	1946.3	1903.6	1884.9	1871.6
40°	1874.4	1852.9	1810.1	1786.3	1775.5
42.5°	1781.0	1759.4	1716.9	1690.0	1674.2
45°	1679.5	1660.8	1620.6	1591.4	1580.7
47.5°	1580.7	1562.0	1519.2	1489.7	1473.9
50°	1476.4	1463.1	1425.7	1388.3	1375.0
52.5°	1375.0	1356.3	1321.8	1292.3	1273.6
55°	1271.0	1254.9	1222.9	1190.9	1177.5
57.5°	1166.8	1153.5	1118.7	1086.6	1075.8
60°	1062.6	1052.1	1014.6	985.2	977.3
62.5°	961.1	942.5	915.8	889.2	878.4
65°	857.2	841.1	814.4	790.3	777.0
67.5°	750.4	736.8	713.0	694.3	683.5
70°	651.5	640.7	616.7	598.0	587.5
72.5°	550.1	539.4	526.0	507.4	499.4
75°	448.4	443.3	429.8	413.9	419.2
77.5°	357.8	347.0	341.6	333.7	325.8
80°	267.2	264.3	258.9	251.0	245.6
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.4	106.8	104.3	96.1	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931421

CATALOG NUMBER: DFN2DS-TR3F0-080DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.60	17.21	15.96	17.52	17.83	15.15	16.76	15.52	17.08	17.39
	3H	17.35	18.80	17.72	19.13	19.49	16.85	18.31	17.23	18.64	19.00
	4H	17.99	19.36	18.39	19.71	20.08	17.50	18.87	17.89	19.21	19.59
	6H	18.46	19.73	18.87	20.09	20.48	17.96	19.23	18.37	19.59	19.98
	8H	18.60	19.81	19.03	20.20	20.60	18.10	19.31	18.53	19.70	20.10
	12H	18.69	19.85	19.12	20.24	20.66	18.18	19.34	18.61	19.72	20.15
4H	2H	16.16	17.52	16.55	17.87	18.25	15.80	17.17	16.20	17.52	17.90
	3H	18.13	19.28	18.54	19.67	20.07	17.72	18.87	18.13	19.27	19.67
	4H	18.91	19.94	19.34	20.36	20.79	18.48	19.52	18.91	19.93	20.37
	6H	19.50	20.41	19.96	20.85	21.31	19.07	19.98	19.53	20.42	20.87
	8H	19.69	20.54	20.15	20.98	21.45	19.26	20.10	19.72	20.54	21.01
	12H	19.83	20.59	20.31	21.06	21.53	19.37	20.13	19.85	20.61	21.08
8H	4H	19.18	20.03	19.64	20.47	20.93	18.81	19.65	19.27	20.10	20.56
	6H	19.89	20.60	20.39	21.09	21.56	19.51	20.22	20.01	20.70	21.18
	8H	20.15	20.78	20.66	21.29	21.78	19.76	20.39	20.27	20.90	21.39
	12H	20.35	20.91	20.86	21.40	21.96	19.94	20.50	20.45	20.99	21.55
12H	4H	19.21	19.97	19.69	20.44	20.91	18.84	19.60	19.32	20.08	20.55
	6H	19.94	20.57	20.45	21.08	21.56	19.57	20.20	20.08	20.71	21.20
	8H	20.25	20.81	20.76	21.30	21.86	19.88	20.43	20.38	20.92	21.49