

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999161

Luminaire Tested: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P999161
REPORT IS A COMBINATION OF REPORTS P984910 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6581.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46
3	84	75	67	62	78	70	64	59	61	56	52	53	49	46	45	42	40
4	77	66	59	53	72	62	55	50	55	49	45	47	43	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	38	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27013	27013	27013	27013
5°	27077	28801	27180	22914
10°	26763	31441	26931	18891
15°	26114	33163	26477	15913
20°	25706	31139	25706	13832
25°	24887	26752	25001	12368
30°	23539	21029	23987	11203
35°	22345	14541	22718	10251
40°	20972	10979	21211	9491
45°	19278	9022	19595	8671
50°	17816	7919	17847	7938
55°	16148	6748	16251	7141
60°	14368	5636	14568	6232
65°	12776	4584	13011	5323
70°	11191	3597	11476	4294
75°	9392	2611	9762	3112
80°	7329	1655	7856	1848
85°	4817	832	5184	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 27922 cd/sqm

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.5
10°-20°	473.1	7.2
20°-30°	686.6	10.4
30°-40°	723.8	11.0
40°-50°	640.5	9.7
50°-60°	511.4	7.8
60°-70°	347.4	5.3
70°-80°	177.7	2.7
80°-90°	43.7	0.7
90°-100°	31.7	0.5
100°-110°	118.0	1.8
110°-120°	313.0	4.8
120°-130°	519.1	7.9
130°-140°	551.4	8.4
140°-150°	512.4	7.8
150°-160°	412.0	6.3
160°-170°	265.5	4.0
170°-180°	91.4	1.4
0°-30°	1322.2	20.1
0°-40°	2046.0	31.1
0°-60°	3197.9	48.6
0°-90°	3766.7	57.2
90°-120°	462.7	7.0
90°-150°	2045.5	31.1
90°-180°	2814.0	42.8
0°-180°	6581.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1708	1906	1714	1516	1708	162
15°	1604	2343	1626	1124	1604	453
25°	1442	1952	1448	902	1442	659
35°	1177	1062	1196	749	1177	736
45°	883	640	897	615	883	685
55°	606	450	610	476	606	541
65°	359	277	366	321	359	357
75°	168	136	174	163	168	180
85°	34	35	37	26	34	40
90°	1	19	1	19	1	5
95°	45	30	45	30	45	53
105°	211	53	211	53	211	226
115°	399	57	399	57	399	393
125°	565	594	565	594	565	504
135°	699	722	699	722	699	540
145°	811	823	811	823	811	507
155°	893	893	893	893	893	411
165°	940	938	940	938	940	266
175°	962	956	962	956	962	92
180°	960	960	960	960	960	

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1715.7	1719.6	1726.1	1727.5	1740.6	1751.1	1762.9	1762.9	1766.8	1765.5	1755.0
5°	1707.8	1719.6	1736.6	1751.1	1774.7	1785.2	1800.9	1812.7	1823.2	1831.1	1829.8
7.5°	1694.7	1715.7	1740.6	1768.1	1799.6	1818.0	1840.3	1861.2	1875.7	1888.8	1898.0
10°	1672.4	1707.8	1741.9	1778.6	1819.3	1844.2	1870.4	1898.0	1920.3	1945.2	1968.8
12.5°	1642.2	1693.4	1735.3	1783.9	1833.7	1861.2	1903.2	1924.2	1967.5	2030.5	2047.5
15°	1604.2	1673.7	1713.0	1774.7	1840.3	1862.6	1920.3	1954.4	2043.6	2082.9	2130.1
17.5°	1568.7	1646.1	1698.6	1769.4	1833.7	1877.0	1933.4	2002.9	2077.7	2134.1	2186.5
20°	1539.9	1614.7	1677.6	1756.3	1837.6	1892.7	1951.8	2035.7	2117.0	2174.7	2215.4
22.5°	1474.3	1570.1	1643.5	1731.4	1829.8	1905.8	1962.2	2054.1	2141.9	2177.4	2212.8
25°	1441.5	1524.2	1609.4	1709.1	1824.5	1915.0	1963.6	2065.9	2143.3	2156.4	2164.2
27.5°	1381.2	1474.3	1574.0	1688.1	1823.2	1899.3	1960.9	2054.1	2115.7	2106.5	2082.9
30°	1306.4	1420.5	1530.7	1654.0	1804.8	1887.5	1945.2	2030.5	2061.9	2014.7	1972.7
32.5°	1251.3	1358.9	1480.9	1623.8	1783.9	1862.6	1919.0	1985.9	1992.4	1907.2	1836.3
35°	1176.6	1295.9	1433.6	1584.5	1748.4	1819.3	1871.7	1912.4	1880.9	1761.6	1677.6
37.5°	1109.7	1227.7	1374.6	1528.1	1699.9	1769.4	1811.4	1818.0	1740.6	1635.6	1512.3
40°	1036.2	1158.2	1311.7	1473.0	1646.1	1706.5	1732.7	1713.0	1601.5	1479.6	1336.6
42.5°	962.8	1083.4	1248.7	1414.0	1577.9	1629.1	1639.6	1585.8	1449.4	1306.4	1141.1
45°	882.7	1008.7	1173.9	1340.5	1499.2	1528.1	1529.4	1452.0	1290.7	1141.1	987.7
47.5°	817.2	933.9	1097.9	1264.4	1398.2	1417.9	1410.0	1320.8	1145.1	977.2	843.4
50°	745.0	856.5	1019.2	1183.1	1297.2	1302.5	1282.8	1155.6	983.7	830.3	724.0
52.5°	667.6	780.4	930.0	1087.4	1189.7	1181.8	1143.8	1007.4	846.0	718.8	637.5
55°	606.0	705.7	846.0	999.5	1071.6	1049.3	1007.4	868.3	741.1	633.5	562.7
57.5°	537.8	625.7	763.4	897.2	939.2	918.2	876.2	746.3	628.3	547.0	499.7
60°	473.5	553.5	674.2	785.7	818.5	796.2	747.6	630.9	545.7	477.4	442.0
62.5°	414.5	484.0	585.0	687.3	700.4	678.1	636.2	541.7	468.3	414.5	388.3
65°	359.4	425.0	506.3	583.7	595.5	571.9	528.6	460.4	398.7	364.6	339.7
67.5°	305.6	358.1	430.2	486.6	493.2	470.9	435.5	380.4	342.3	305.6	287.3
70°	258.4	297.7	354.1	400.1	402.7	381.7	363.3	313.5	284.6	258.4	244.0
72.5°	212.5	240.0	283.3	317.4	318.7	305.6	288.6	257.1	232.2	213.8	199.4
75°	167.9	191.5	217.7	247.9	246.6	236.1	223.0	203.3	182.3	170.5	164.0
77.5°	128.5	143.0	164.0	183.6	183.6	178.4	170.5	156.1	143.0	131.2	124.6
80°	91.8	101.0	118.0	124.6	127.2	125.9	119.4	108.9	103.6	94.4	91.8
82.5°	59.0	65.6	73.5	80.0	83.9	81.3	80.0	74.8	66.9	64.3	61.6
85°	34.1	36.7	40.7	44.6	45.9	44.6	47.2	43.3	39.3	39.3	38.0
87.5°	14.4	15.7	18.4	18.4	19.7	19.7	18.4	19.7	19.7	18.4	17.1
90°	0.7	2.4	4.1	5.8	7.5	8.3	8.9	10.2	11.4	12.7	13.9
92.5°	17.4	16.8	16.2	15.5	14.9	14.6	14.8	15.3	15.8	16.2	16.7
95°	45.2	40.1	35.0	29.9	24.8	22.2	22.7	23.8	24.9	26.0	27.1
97.5°	81.3	68.6	56.0	43.3	30.6	24.3	25.5	28.0	30.5	32.9	35.4
100°	122.9	101.8	80.6	59.5	38.4	27.8	29.1	31.7	34.4	37.0	39.6
102.5°	168.8	168.5	168.2	167.9	167.6	167.4	153.4	125.3	97.2	69.1	41.0
105°	211.2	215.8	220.4	225.1	229.7	232.0	210.9	168.8	126.7	84.5	42.4
107.5°	260.5	264.4	268.2	272.1	276.0	277.9	251.9	199.9	147.8	95.8	43.8
110°	307.7	310.9	314.2	317.4	320.7	322.3	300.0	255.4	210.8	166.2	121.6

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	352.2	355.0	357.8	360.5	363.3	364.7	363.4	360.8	358.1	355.5	352.9
115°	399.4	402.0	404.6	407.3	409.9	411.2	413.1	417.0	420.9	424.7	428.6
117.5°	440.4	443.5	446.6	449.7	452.8	454.3	455.6	458.2	460.9	463.5	466.1
120°	486.2	488.5	490.9	493.2	495.5	496.7	498.1	500.9	503.6	506.4	509.2
122.5°	525.1	527.6	530.1	532.6	535.1	536.3	537.8	540.9	544.0	547.0	550.1
125°	564.7	566.7	568.7	570.8	572.8	573.8	575.3	578.2	581.1	584.1	587.0
127.5°	600.9	603.1	605.2	607.4	609.5	610.6	611.8	614.1	616.4	618.7	621.0
130°	634.9	637.4	639.8	642.3	644.8	646.0	646.8	648.5	650.2	651.9	653.6
132.5°	669.6	671.6	673.6	675.7	677.7	678.7	679.5	681.2	682.9	684.6	686.3
135°	698.8	701.3	703.7	706.2	708.7	709.9	710.6	712.0	713.4	714.8	716.2
137.5°	729.4	731.2	733.1	734.9	736.8	737.7	738.5	740.0	741.5	743.1	744.6
140°	759.2	760.4	761.7	762.9	764.2	764.8	765.6	767.3	769.0	770.7	772.4
142.5°	784.2	785.3	786.4	787.5	788.6	789.1	790.1	792.1	794.1	796.1	798.1
145°	810.6	810.4	810.3	810.1	810.0	809.9	811.2	813.8	816.5	819.1	821.7
147.5°	833.6	833.1	832.7	832.2	831.7	831.5	832.8	835.4	838.1	840.7	843.3
150°	855.8	854.7	853.6	852.5	851.4	850.9	852.1	854.6	857.1	859.5	862.0
152.5°	874.5	873.3	872.1	870.8	869.6	869.0	870.2	872.5	874.8	877.1	879.4
155°	892.6	891.2	889.8	888.4	887.0	886.3	887.2	889.1	891.0	892.8	894.7
157.5°	907.2	906.0	904.7	903.5	902.2	901.6	902.3	903.7	905.1	906.5	907.9
160°	919.7	918.8	917.8	916.9	916.0	915.5	916.0	916.9	917.8	918.8	919.7
162.5°	930.8	929.9	928.9	928.0	927.1	926.6	927.0	927.8	928.5	929.3	930.1
165°	940.5	939.6	938.7	937.8	936.9	936.4	936.6	937.1	937.5	938.0	938.4
167.5°	948.2	947.3	946.3	945.4	944.5	944.0	944.2	944.7	945.2	945.6	946.1
170°	954.4	953.5	952.6	951.7	950.8	950.3	950.4	950.7	951.0	951.3	951.6
172.5°	958.6	957.7	956.7	955.8	954.9	954.4	954.6	954.9	955.2	955.5	955.8
175°	962.1	961.0	959.9	958.8	957.7	957.2	957.4	957.7	958.0	958.3	958.6
177.5°	963.4	962.3	961.3	960.2	959.1	958.6	958.7	958.8	959.0	959.1	959.3
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1773.4	1774.7	1777.3	1790.4	1797.0	1798.3	1793.0	1804.8	1808.8	1804.8	1802.2
5°	1857.3	1865.2	1880.9	1898.0	1896.7	1898.0	1905.8	1913.7	1916.3	1905.8	1909.8
7.5°	1930.8	1946.5	1963.6	1989.8	1989.8	2002.9	2008.2	2014.7	2030.5	2022.6	2020.0
10°	2014.7	2035.7	2067.2	2109.2	2110.5	2123.6	2136.7	2157.7	2164.2	2159.0	2161.6
12.5°	2119.6	2160.3	2162.9	2208.8	2229.8	2232.5	2253.4	2249.5	2262.6	2262.6	2284.9
15°	2165.6	2228.5	2263.9	2308.5	2321.6	2305.9	2323.0	2341.3	2342.6	2342.6	2341.3
17.5°	2248.2	2273.1	2308.5	2332.1	2337.4	2337.4	2338.7	2346.6	2341.3	2330.8	2338.7
20°	2265.2	2275.7	2288.9	2286.2	2288.9	2275.7	2262.6	2249.5	2250.8	2244.3	2263.9
22.5°	2233.8	2231.1	2201.0	2181.3	2181.3	2155.1	2130.1	2118.3	2106.5	2110.5	2117.0
25°	2155.1	2114.4	2077.7	2048.8	2042.3	2000.3	1966.2	1955.7	1936.0	1951.8	1954.4
27.5°	2029.1	1983.2	1924.2	1899.3	1865.2	1848.1	1824.5	1793.0	1752.4	1776.0	1772.1
30°	1894.0	1825.8	1777.3	1717.0	1663.2	1659.3	1614.7	1562.2	1541.2	1541.2	1553.0
32.5°	1743.2	1652.7	1581.9	1496.6	1444.1	1421.8	1368.1	1315.6	1327.4	1288.1	1302.5
35°	1567.4	1448.1	1358.9	1276.2	1236.9	1210.7	1141.1	1112.3	1080.8	1062.4	1096.6
37.5°	1399.5	1261.8	1147.7	1057.2	1042.8	995.6	948.3	930.0	911.6	919.5	918.2
40°	1194.9	1072.9	970.6	899.8	874.9	852.6	821.1	798.8	787.0	793.6	794.9
42.5°	1010.0	907.7	831.6	781.8	760.8	745.0	729.3	710.9	707.0	707.0	712.2
45°	867.0	783.1	731.9	691.2	679.4	667.6	655.8	648.0	645.3	640.1	644.0
47.5°	752.9	686.0	654.5	624.4	611.2	608.6	598.1	594.2	588.9	587.6	588.9
50°	657.1	615.2	586.3	569.3	560.1	556.1	550.9	543.0	540.4	547.0	544.3
52.5°	590.2	550.9	535.2	518.1	512.9	507.6	499.7	501.1	499.7	497.1	497.1
55°	523.4	498.4	482.7	469.6	468.3	463.0	456.5	453.8	452.5	449.9	453.8
57.5°	469.6	449.9	435.5	423.7	418.4	418.4	411.9	406.6	406.6	405.3	406.6
60°	415.8	396.1	386.9	375.1	371.2	369.9	366.0	363.3	359.4	359.4	359.4
62.5°	366.0	350.2	339.7	329.2	330.5	324.0	318.7	316.1	316.1	317.4	317.4
65°	318.7	308.2	295.1	285.9	283.3	282.0	279.4	278.1	274.1	276.8	276.8
67.5°	275.4	261.0	253.2	249.2	245.3	244.0	241.3	238.7	237.4	236.1	238.7
70°	232.2	220.4	213.8	211.2	207.2	205.9	204.6	200.7	202.0	203.3	204.6
72.5°	192.8	182.3	181.0	173.1	173.1	173.1	167.9	170.5	169.2	166.6	169.2
75°	152.2	146.9	144.3	140.3	141.7	140.3	139.0	135.1	135.1	136.4	137.7
77.5°	120.7	115.4	114.1	110.2	107.6	110.2	107.6	106.2	106.2	107.6	107.6
80°	89.2	86.6	82.6	82.6	82.6	81.3	81.3	81.3	80.0	78.7	80.0
82.5°	59.0	59.0	57.7	56.4	57.7	55.1	56.4	56.4	56.4	56.4	56.4
85°	38.0	36.7	36.7	35.4	35.4	35.4	36.7	34.1	34.1	35.4	35.4
87.5°	17.1	17.1	17.1	18.4	17.1	17.1	17.1	18.4	17.1	17.1	17.1
90°	14.7	15.5	16.2	17.0	17.4	17.6	17.9	18.2	18.5	18.8	18.5
92.5°	17.0	17.3	17.6	17.9	18.1	18.2	18.3	18.5	18.6	18.8	18.6
95°	27.9	28.7	29.4	30.2	30.6	30.5	30.4	30.2	30.1	29.9	30.1
97.5°	35.9	36.3	36.8	37.3	37.5	37.6	37.7	37.9	38.0	38.2	38.0
100°	40.8	42.1	43.3	44.6	45.2	45.3	45.6	45.9	46.2	46.5	46.2
102.5°	42.7	44.4	46.1	47.8	48.6	48.8	49.3	49.8	50.2	50.7	50.2
105°	44.1	45.8	47.5	49.2	50.0	50.3	50.9	51.6	52.2	52.8	52.2
107.5°	45.5	47.2	48.9	50.6	51.4	51.7	52.3	53.0	53.6	54.2	53.6
110°	106.2	90.7	75.3	59.8	52.1	52.4	53.0	53.7	54.3	54.9	54.3

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	286.4	219.8	153.3	86.8	53.5	53.7	54.2	54.7	55.1	55.6	55.1
115°	357.1	285.7	214.2	142.7	107.0	101.4	90.3	79.2	68.1	57.0	68.1
117.5°	444.0	422.0	399.9	377.8	366.8	346.6	306.1	265.7	225.2	184.8	225.2
120°	511.0	512.9	514.7	516.6	517.5	507.1	486.2	465.4	444.5	423.7	444.5
122.5°	551.0	552.0	552.9	553.8	554.3	554.4	554.5	554.7	554.8	555.0	554.8
125°	588.1	589.1	590.2	591.3	591.8	592.0	592.5	593.0	593.4	593.9	593.4
127.5°	622.5	624.1	625.6	627.1	627.9	628.0	628.1	628.3	628.4	628.6	628.4
130°	655.3	657.0	658.7	660.4	661.3	661.2	661.1	660.9	660.8	660.6	660.8
132.5°	687.7	689.1	690.4	691.8	692.5	692.4	692.3	692.1	692.0	691.8	692.0
135°	717.7	719.3	720.8	722.3	723.1	722.9	722.6	722.3	722.0	721.7	722.0
137.5°	746.2	747.7	749.3	750.8	751.6	751.4	750.9	750.4	750.0	749.5	750.0
140°	773.8	775.2	776.6	778.0	778.7	778.3	777.5	776.8	776.0	775.2	776.0
142.5°	799.3	800.6	801.8	803.1	803.7	803.3	802.5	801.8	801.0	800.2	801.0
145°	822.8	823.9	825.0	826.1	826.6	826.2	825.4	824.7	823.9	823.1	823.9
147.5°	844.1	844.9	845.6	846.4	846.8	846.5	845.9	845.2	844.6	844.0	844.6
150°	862.9	863.9	864.8	865.7	866.2	865.8	865.0	864.3	863.5	862.7	863.5
152.5°	880.3	881.3	882.2	883.1	883.6	883.1	882.0	880.9	879.8	878.7	879.8
155°	895.6	896.5	897.4	898.3	898.8	898.2	897.0	895.7	894.5	893.3	894.5
157.5°	909.0	910.0	911.1	912.2	912.7	912.1	910.9	909.6	908.4	907.2	908.4
160°	920.6	921.6	922.5	923.4	923.9	923.4	922.3	921.2	920.1	919.0	920.1
162.5°	931.2	932.3	933.4	934.5	935.0	934.3	932.9	931.5	930.1	928.7	930.1
165°	939.5	940.6	941.7	942.8	943.3	942.8	941.7	940.6	939.5	938.4	939.5
167.5°	947.2	948.2	949.3	950.4	950.9	950.2	948.8	947.5	946.1	944.7	946.1
170°	952.7	953.8	954.9	956.0	956.5	955.8	954.4	953.1	951.7	950.3	951.7
172.5°	956.9	958.0	959.1	960.2	960.7	960.0	958.6	957.2	955.8	954.4	955.8
175°	959.7	960.7	961.8	962.9	963.4	962.6	961.1	959.6	958.0	956.5	958.0
177.5°	960.4	961.4	962.5	963.6	964.1	963.4	962.0	960.7	959.3	957.9	959.3
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1808.8	1799.6	1791.7	1793.0	1799.6	1794.4	1781.2	1764.2	1757.6	1749.8	1757.6
5°	1917.7	1909.8	1894.0	1895.4	1891.4	1886.2	1865.2	1839.0	1839.0	1818.0	1815.3
7.5°	2025.2	2013.4	2002.9	2000.3	1985.9	1975.4	1957.0	1920.3	1905.8	1880.9	1866.5
10°	2145.9	2136.7	2124.9	2110.5	2102.6	2084.2	2054.1	2000.3	1974.1	1939.9	1915.0
12.5°	2267.9	2266.6	2240.3	2211.5	2210.2	2181.3	2160.3	2088.2	2052.8	2006.8	1947.8
15°	2345.3	2338.7	2324.3	2309.8	2313.8	2282.3	2235.1	2149.8	2126.2	2071.1	2008.2
17.5°	2343.9	2343.9	2340.0	2337.4	2333.4	2324.3	2298.0	2241.6	2203.6	2134.1	2075.1
20°	2269.2	2286.2	2290.2	2288.9	2302.0	2308.5	2307.2	2271.8	2241.6	2180.0	2119.6
22.5°	2119.6	2159.0	2176.0	2186.5	2214.1	2228.5	2262.6	2249.5	2241.6	2195.7	2144.6
25°	1980.6	1993.7	2044.9	2047.5	2085.5	2121.0	2155.1	2177.4	2206.2	2189.2	2145.9
27.5°	1800.9	1831.1	1867.8	1895.4	1903.2	1975.4	2031.8	2073.7	2139.3	2144.6	2130.1
30°	1597.6	1612.0	1672.4	1709.1	1751.1	1803.5	1884.9	1957.0	2016.0	2069.8	2088.2
32.5°	1349.7	1408.7	1444.1	1488.7	1525.5	1618.6	1718.3	1811.4	1879.6	1970.1	2009.5
35°	1122.8	1168.7	1229.0	1247.4	1314.3	1393.0	1522.8	1642.2	1745.8	1837.6	1917.7
37.5°	935.2	971.9	1036.2	1065.1	1104.4	1205.4	1314.3	1462.5	1587.1	1699.9	1799.6
40°	806.7	834.2	882.7	891.9	924.7	1016.5	1104.4	1243.5	1408.7	1560.9	1669.7
42.5°	718.8	731.9	764.7	776.5	797.5	859.1	937.8	1069.0	1222.5	1379.9	1533.3
45°	655.8	665.0	684.7	695.2	721.4	749.0	813.2	918.2	1038.8	1197.5	1362.8
47.5°	599.4	611.2	619.1	625.7	640.1	670.3	712.2	789.6	905.0	1050.6	1210.7
50°	552.2	556.1	570.6	571.9	581.1	600.7	640.1	687.3	779.1	897.2	1052.0
52.5°	505.0	508.9	518.1	527.3	531.2	547.0	573.2	612.5	680.8	773.9	911.6
55°	457.8	463.0	472.2	478.8	482.7	495.8	511.5	549.6	603.4	668.9	781.8
57.5°	410.6	422.4	425.0	428.9	435.5	449.9	464.3	486.6	528.6	588.9	671.6
60°	366.0	369.9	379.1	383.0	389.6	397.4	415.8	432.8	463.0	510.2	585.0
62.5°	320.0	329.2	333.2	337.1	342.3	351.5	363.3	381.7	407.9	446.0	505.0
65°	280.7	282.0	289.9	295.1	300.4	306.9	318.7	335.8	351.5	386.9	430.2
67.5°	242.7	245.3	247.9	253.2	259.7	266.3	276.8	285.9	305.6	329.2	363.3
70°	205.9	205.9	212.5	216.4	215.1	223.0	230.9	241.3	255.8	278.1	305.6
72.5°	173.1	171.8	177.1	178.4	181.0	186.3	191.5	202.0	209.9	226.9	247.9
75°	137.7	140.3	143.0	143.0	146.9	150.8	156.1	161.3	170.5	181.0	196.7
77.5°	108.9	108.9	111.5	112.8	116.7	115.4	120.7	125.9	132.5	141.7	153.5
80°	80.0	82.6	82.6	82.6	83.9	85.3	90.5	94.4	98.4	104.9	110.2
82.5°	56.4	56.4	59.0	59.0	59.0	61.6	61.6	63.0	65.6	69.5	73.5
85°	35.4	35.4	35.4	36.7	35.4	36.7	39.3	38.0	39.3	42.0	42.0
87.5°	17.1	17.1	17.1	17.1	17.1	18.4	17.1	18.4	19.7	19.7	19.7
90°	18.2	17.9	17.6	17.4	17.0	16.2	15.5	14.7	13.9	12.7	11.4
92.5°	18.5	18.3	18.2	18.1	17.9	17.6	17.3	17.0	16.7	16.2	15.8
95°	30.2	30.4	30.5	30.6	30.2	29.4	28.7	27.9	27.1	26.0	24.9
97.5°	37.9	37.7	37.6	37.5	37.3	36.8	36.3	35.9	35.4	32.9	30.5
100°	45.9	45.6	45.3	45.2	44.6	43.3	42.1	40.8	39.6	37.0	34.4
102.5°	49.8	49.3	48.8	48.6	47.8	46.1	44.4	42.7	41.0	39.1	37.2
105°	51.6	50.9	50.3	50.0	49.2	47.5	45.8	44.1	42.4	40.5	38.7
107.5°	53.0	52.3	51.7	51.4	50.6	48.9	47.2	45.5	43.8	42.0	40.2
110°	53.7	53.0	52.4	52.1	51.8	50.7	49.7	48.7	47.6	46.5	45.4

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	54.7	54.2	53.7	53.5	86.8	153.3	219.8	286.4	352.9	355.5	358.1
115°	79.2	90.3	101.4	107.0	142.7	214.2	285.7	357.1	428.6	424.7	420.9
117.5°	265.7	306.1	346.6	366.8	377.8	399.9	422.0	444.0	466.1	463.5	460.9
120°	465.4	486.2	507.1	517.5	516.6	514.7	512.9	511.0	509.2	506.4	503.6
122.5°	554.7	554.5	554.4	554.3	553.8	552.9	552.0	551.0	550.1	547.0	544.0
125°	593.0	592.5	592.0	591.8	591.3	590.2	589.1	588.1	587.0	584.1	581.1
127.5°	628.3	628.1	628.0	627.9	627.1	625.6	624.1	622.5	621.0	618.7	616.4
130°	660.9	661.1	661.2	661.3	660.4	658.7	657.0	655.3	653.6	651.9	650.2
132.5°	692.1	692.3	692.4	692.5	691.8	690.4	689.1	687.7	686.3	684.6	682.9
135°	722.3	722.6	722.9	723.1	722.3	720.8	719.3	717.7	716.2	714.8	713.4
137.5°	750.4	750.9	751.4	751.6	750.8	749.3	747.7	746.2	744.6	743.1	741.5
140°	776.8	777.5	778.3	778.7	778.0	776.6	775.2	773.8	772.4	770.7	769.0
142.5°	801.8	802.5	803.3	803.7	803.1	801.8	800.6	799.3	798.1	796.1	794.1
145°	824.7	825.4	826.2	826.6	826.1	825.0	823.9	822.8	821.7	819.1	816.5
147.5°	845.2	845.9	846.5	846.8	846.4	845.6	844.9	844.1	843.3	840.7	838.1
150°	864.3	865.0	865.8	866.2	865.7	864.8	863.9	862.9	862.0	859.5	857.1
152.5°	880.9	882.0	883.1	883.6	883.1	882.2	881.3	880.3	879.4	877.1	874.8
155°	895.7	897.0	898.2	898.8	898.3	897.4	896.5	895.6	894.7	892.8	891.0
157.5°	909.6	910.9	912.1	912.7	912.2	911.1	910.0	909.0	907.9	906.5	905.1
160°	921.2	922.3	923.4	923.9	923.4	922.5	921.6	920.6	919.7	918.8	917.8
162.5°	931.5	932.9	934.3	935.0	934.5	933.4	932.3	931.2	930.1	929.3	928.5
165°	940.6	941.7	942.8	943.3	942.8	941.7	940.6	939.5	938.4	938.0	937.5
167.5°	947.5	948.8	950.2	950.9	950.4	949.3	948.2	947.2	946.1	945.6	945.2
170°	953.1	954.4	955.8	956.5	956.0	954.9	953.8	952.7	951.6	951.3	951.0
172.5°	957.2	958.6	960.0	960.7	960.2	959.1	958.0	956.9	955.8	955.5	955.2
175°	959.6	961.1	962.6	963.4	962.9	961.8	960.7	959.7	958.6	958.3	958.0
177.5°	960.7	962.0	963.4	964.1	963.6	962.5	961.4	960.4	959.3	959.1	959.0
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1751.1	1744.5	1740.6	1743.2	1735.3	1715.7	1715.7	1722.2	1714.3	1706.5	1694.7
5°	1799.6	1786.5	1778.6	1777.3	1758.9	1727.5	1720.9	1714.3	1697.3	1678.9	1659.3
7.5°	1846.8	1823.2	1810.1	1800.9	1774.7	1734.0	1717.0	1702.5	1675.0	1647.4	1622.5
10°	1886.2	1852.1	1836.3	1821.9	1787.8	1736.6	1709.1	1682.9	1647.4	1612.0	1580.6
12.5°	1917.7	1878.3	1858.6	1837.6	1795.7	1728.8	1694.7	1652.7	1617.3	1570.1	1538.6
15°	1970.1	1888.8	1870.4	1850.8	1807.5	1715.7	1673.7	1626.5	1577.9	1515.0	1480.9
17.5°	2012.1	1903.2	1901.9	1859.9	1803.5	1710.4	1646.1	1584.5	1532.0	1469.1	1415.3
20°	2037.0	1925.5	1904.5	1861.2	1790.4	1675.0	1608.1	1539.9	1483.5	1407.4	1353.6
22.5°	2058.0	1957.0	1901.9	1849.4	1762.9	1663.2	1564.8	1500.5	1423.2	1340.5	1289.4
25°	2065.9	1963.6	1905.8	1845.5	1743.2	1629.1	1517.6	1448.1	1361.5	1286.7	1217.2
27.5°	2067.2	1962.2	1891.4	1828.5	1715.7	1584.5	1470.4	1396.9	1301.2	1214.6	1145.1
30°	2054.1	1947.8	1883.5	1815.3	1689.4	1543.8	1412.7	1331.3	1229.0	1142.5	1070.3
32.5°	2014.7	1919.0	1866.5	1791.7	1655.3	1487.4	1357.6	1267.1	1159.5	1074.3	1004.7
35°	1949.1	1883.5	1825.8	1756.3	1610.7	1435.0	1302.5	1196.2	1087.4	1006.0	940.5
37.5°	1867.8	1832.4	1778.6	1710.4	1559.6	1387.7	1240.8	1122.8	1013.9	935.2	870.9
40°	1757.6	1766.8	1714.3	1652.7	1499.2	1323.5	1160.8	1048.0	945.7	872.3	809.3
42.5°	1638.3	1676.3	1646.1	1587.1	1432.3	1252.6	1101.8	977.2	877.5	801.4	749.0
45°	1509.7	1575.3	1556.9	1513.7	1362.8	1177.9	1017.9	897.2	809.3	735.8	689.9
47.5°	1369.4	1462.5	1462.5	1431.0	1285.4	1103.1	945.7	822.4	735.8	683.4	638.8
50°	1226.4	1331.3	1348.4	1327.4	1198.9	1017.9	857.8	746.3	671.6	620.4	587.6
52.5°	1076.9	1198.9	1230.3	1219.8	1107.0	936.5	785.7	676.8	608.6	564.0	535.2
55°	933.9	1075.6	1109.7	1113.6	1008.7	847.3	705.7	609.9	544.3	514.2	489.3
57.5°	798.8	935.2	973.3	979.8	909.0	766.0	630.9	547.0	487.9	463.0	443.3
60°	683.4	797.5	847.3	861.8	800.1	671.6	561.4	480.1	435.5	411.9	393.5
62.5°	588.9	680.8	733.2	737.2	709.6	588.9	489.3	421.0	383.0	362.0	352.8
65°	497.1	579.8	611.2	627.0	604.7	510.2	422.4	366.0	335.8	317.4	308.2
67.5°	423.7	476.1	502.4	523.4	501.1	430.2	359.4	313.5	291.2	272.8	267.6
70°	347.6	390.9	410.6	431.5	411.9	358.1	306.9	265.0	245.3	230.9	224.3
72.5°	278.1	312.2	330.5	343.7	331.9	287.3	245.3	216.4	202.0	191.5	187.6
75°	220.4	244.0	254.5	263.6	258.4	224.3	198.1	174.5	161.3	152.2	149.5
77.5°	167.9	184.9	196.7	199.4	192.8	170.5	148.2	133.8	123.3	118.0	115.4
80°	119.4	129.9	136.4	140.3	133.8	124.6	108.9	98.4	89.2	82.6	81.3
82.5°	80.0	85.3	90.5	89.2	86.6	78.7	69.5	64.3	60.3	55.1	55.1
85°	45.9	47.2	49.8	51.2	49.8	44.6	39.3	36.7	34.1	30.2	30.2
87.5°	19.7	21.0	21.0	22.3	19.7	19.7	17.1	14.4	14.4	13.1	11.8
90°	10.2	8.9	8.3	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.3	14.8	14.6	14.9	15.5	16.2	16.8	17.4	16.8	16.2	15.5
95°	23.8	22.7	22.2	24.8	29.9	35.0	40.1	45.2	40.1	35.0	29.9
97.5°	28.0	25.5	24.3	30.6	43.3	56.0	68.6	81.3	68.6	56.0	43.3
100°	31.7	29.1	27.8	38.4	59.5	80.6	101.8	122.9	101.8	80.6	59.5
102.5°	125.3	153.4	167.4	167.6	167.9	168.2	168.5	168.8	168.5	168.2	167.9
105°	168.8	210.9	232.0	229.7	225.1	220.4	215.8	211.2	215.8	220.4	225.1
107.5°	199.9	251.9	277.9	276.0	272.1	268.2	264.4	260.5	264.4	268.2	272.1
110°	255.4	300.0	322.3	320.7	317.4	314.2	310.9	307.7	310.9	314.2	317.4

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	360.8	363.4	364.7	363.3	360.5	357.8	355.0	352.2	355.0	357.8	360.5
115°	417.0	413.1	411.2	409.9	407.3	404.6	402.0	399.4	402.0	404.6	407.3
117.5°	458.2	455.6	454.3	452.8	449.7	446.6	443.5	440.4	443.5	446.6	449.7
120°	500.9	498.1	496.7	495.5	493.2	490.9	488.5	486.2	488.5	490.9	493.2
122.5°	540.9	537.8	536.3	535.1	532.6	530.1	527.6	525.1	527.6	530.1	532.6
125°	578.2	575.3	573.8	572.8	570.8	568.7	566.7	564.7	566.7	568.7	570.8
127.5°	614.1	611.8	610.6	609.5	607.4	605.2	603.1	600.9	603.1	605.2	607.4
130°	648.5	646.8	646.0	644.8	642.3	639.8	637.4	634.9	637.4	639.8	642.3
132.5°	681.2	679.5	678.7	677.7	675.7	673.6	671.6	669.6	671.6	673.6	675.7
135°	712.0	710.6	709.9	708.7	706.2	703.7	701.3	698.8	701.3	703.7	706.2
137.5°	740.0	738.5	737.7	736.8	734.9	733.1	731.2	729.4	731.2	733.1	734.9
140°	767.3	765.6	764.8	764.2	762.9	761.7	760.4	759.2	760.4	761.7	762.9
142.5°	792.1	790.1	789.1	788.6	787.5	786.4	785.3	784.2	785.3	786.4	787.5
145°	813.8	811.2	809.9	810.0	810.1	810.3	810.4	810.6	810.4	810.3	810.1
147.5°	835.4	832.8	831.5	831.7	832.2	832.7	833.1	833.6	833.1	832.7	832.2
150°	854.6	852.1	850.9	851.4	852.5	853.6	854.7	855.8	854.7	853.6	852.5
152.5°	872.5	870.2	869.0	869.6	870.8	872.1	873.3	874.5	873.3	872.1	870.8
155°	889.1	887.2	886.3	887.0	888.4	889.8	891.2	892.6	891.2	889.8	888.4
157.5°	903.7	902.3	901.6	902.2	903.5	904.7	906.0	907.2	906.0	904.7	903.5
160°	916.9	916.0	915.5	916.0	916.9	917.8	918.8	919.7	918.8	917.8	916.9
162.5°	927.8	927.0	926.6	927.1	928.0	928.9	929.9	930.8	929.9	928.9	928.0
165°	937.1	936.6	936.4	936.9	937.8	938.7	939.6	940.5	939.6	938.7	937.8
167.5°	944.7	944.2	944.0	944.5	945.4	946.3	947.3	948.2	947.3	946.3	945.4
170°	950.7	950.4	950.3	950.8	951.7	952.6	953.5	954.4	953.5	952.6	951.7
172.5°	954.9	954.6	954.4	954.9	955.8	956.7	957.7	958.6	957.7	956.7	955.8
175°	957.7	957.4	957.2	957.7	958.8	959.9	961.0	962.1	961.0	959.9	958.8
177.5°	958.8	958.7	958.6	959.1	960.2	961.3	962.3	963.4	962.3	961.3	960.2
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1688.1	1694.7	1693.4	1680.2	1665.8	1654.0	1631.7	1634.3	1626.5	1627.8	1635.6
5°	1646.1	1646.1	1640.9	1622.5	1598.9	1585.8	1560.9	1554.3	1538.6	1537.3	1536.0
7.5°	1601.5	1595.0	1588.4	1562.2	1533.3	1512.3	1478.2	1470.4	1454.6	1444.1	1438.9
10°	1549.1	1539.9	1526.8	1496.6	1461.2	1435.0	1399.5	1389.1	1358.9	1345.8	1337.9
12.5°	1491.4	1486.1	1465.1	1440.2	1382.5	1353.6	1302.5	1313.0	1282.8	1256.6	1252.6
15°	1433.6	1414.0	1402.2	1361.5	1292.0	1278.9	1238.2	1217.2	1189.7	1168.7	1168.7
17.5°	1377.2	1347.1	1320.8	1277.6	1226.4	1189.7	1159.5	1149.0	1114.9	1093.9	1090.0
20°	1302.5	1268.4	1261.8	1200.2	1164.8	1124.1	1095.2	1069.0	1044.1	1034.9	1028.3
22.5°	1231.7	1192.3	1181.8	1129.3	1093.9	1053.3	1024.4	1006.0	987.7	981.1	969.3
25°	1155.6	1132.0	1116.2	1059.8	1020.5	982.4	962.8	949.6	932.6	931.3	923.4
27.5°	1082.1	1059.8	1044.1	990.3	961.4	926.0	910.3	895.9	886.7	882.7	878.8
30°	1019.2	994.2	975.9	936.5	901.1	872.3	859.1	850.0	844.7	838.2	836.8
32.5°	949.6	935.2	910.3	880.1	852.6	825.0	817.2	810.6	802.7	800.1	798.8
35°	890.6	870.9	855.2	821.1	809.3	785.7	776.5	771.3	760.8	758.1	755.5
37.5°	832.9	814.5	797.5	776.5	754.2	741.1	735.8	728.0	722.7	724.0	721.4
40°	775.2	760.8	747.6	725.3	712.2	705.7	695.2	687.3	684.7	686.0	684.7
42.5°	718.8	705.7	697.8	680.8	667.6	661.1	654.5	646.6	650.6	650.6	654.5
45°	667.6	655.8	650.6	637.5	629.6	619.1	612.5	611.2	616.5	615.2	615.2
47.5°	615.2	611.2	604.7	592.9	582.4	575.8	574.5	574.5	579.8	582.4	581.1
50°	574.5	566.6	558.8	549.6	541.7	539.1	535.2	537.8	543.0	543.0	545.7
52.5°	523.4	518.1	515.5	507.6	502.4	502.4	502.4	503.7	507.6	511.5	510.2
55°	478.8	474.8	472.2	468.3	461.7	463.0	461.7	464.3	468.3	472.2	474.8
57.5°	431.5	430.2	427.6	421.0	421.0	419.7	423.7	425.0	431.5	434.2	438.1
60°	389.6	385.6	385.6	380.4	380.4	380.4	384.3	388.3	393.5	394.8	397.4
62.5°	345.0	345.0	343.7	339.7	339.7	343.7	345.0	350.2	352.8	352.8	356.8
65°	303.0	301.7	300.4	301.7	303.0	303.0	306.9	309.6	312.2	313.5	314.8
67.5°	261.0	259.7	262.3	261.0	263.6	268.9	267.6	271.5	275.4	275.4	276.8
70°	221.7	224.3	223.0	225.6	224.3	226.9	230.9	232.2	232.2	233.5	237.4
72.5°	184.9	184.9	184.9	183.6	184.9	187.6	190.2	191.5	194.1	195.4	199.4
75°	149.5	149.5	146.9	149.5	149.5	152.2	154.8	154.8	154.8	157.4	161.3
77.5°	112.8	114.1	112.8	115.4	115.4	116.7	119.4	118.0	120.7	122.0	123.3
80°	82.6	81.3	81.3	81.3	82.6	82.6	85.3	86.6	86.6	90.5	87.9
82.5°	52.5	53.8	52.5	53.8	53.8	55.1	53.8	55.1	56.4	59.0	57.7
85°	30.2	28.9	28.9	30.2	28.9	28.9	30.2	28.9	30.2	28.9	30.2
87.5°	11.8	10.5	10.5	10.5	10.5	9.2	9.2	7.9	7.9	7.9	6.6
90°	7.5	8.3	8.9	10.2	11.4	12.7	13.9	14.7	15.5	16.2	17.0
92.5°	14.9	14.6	14.8	15.3	15.8	16.2	16.7	17.0	17.3	17.6	17.9
95°	24.8	22.2	22.7	23.8	24.9	26.0	27.1	27.9	28.7	29.4	30.2
97.5°	30.6	24.3	25.5	28.0	30.5	32.9	35.4	35.9	36.3	36.8	37.3
100°	38.4	27.8	29.1	31.7	34.4	37.0	39.6	40.8	42.1	43.3	44.6
102.5°	167.6	167.4	153.4	125.3	97.2	69.1	41.0	42.7	44.4	46.1	47.8
105°	229.7	232.0	210.9	168.8	126.7	84.5	42.4	44.1	45.8	47.5	49.2
107.5°	276.0	277.9	251.9	199.9	147.8	95.8	43.8	45.5	47.2	48.9	50.6
110°	320.7	322.3	300.0	255.4	210.8	166.2	121.6	106.2	90.7	75.3	59.8

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	363.3	364.7	363.4	360.8	358.1	355.5	352.9	286.4	219.8	153.3	86.8
115°	409.9	411.2	413.1	417.0	420.9	424.7	428.6	357.1	285.7	214.2	142.7
117.5°	452.8	454.3	455.6	458.2	460.9	463.5	466.1	444.0	422.0	399.9	377.8
120°	495.5	496.7	498.1	500.9	503.6	506.4	509.2	511.0	512.9	514.7	516.6
122.5°	535.1	536.3	537.8	540.9	544.0	547.0	550.1	551.0	552.0	552.9	553.8
125°	572.8	573.8	575.3	578.2	581.1	584.1	587.0	588.1	589.1	590.2	591.3
127.5°	609.5	610.6	611.8	614.1	616.4	618.7	621.0	622.5	624.1	625.6	627.1
130°	644.8	646.0	646.8	648.5	650.2	651.9	653.6	655.3	657.0	658.7	660.4
132.5°	677.7	678.7	679.5	681.2	682.9	684.6	686.3	687.7	689.1	690.4	691.8
135°	708.7	709.9	710.6	712.0	713.4	714.8	716.2	717.7	719.3	720.8	722.3
137.5°	736.8	737.7	738.5	740.0	741.5	743.1	744.6	746.2	747.7	749.3	750.8
140°	764.2	764.8	765.6	767.3	769.0	770.7	772.4	773.8	775.2	776.6	778.0
142.5°	788.6	789.1	790.1	792.1	794.1	796.1	798.1	799.3	800.6	801.8	803.1
145°	810.0	809.9	811.2	813.8	816.5	819.1	821.7	822.8	823.9	825.0	826.1
147.5°	831.7	831.5	832.8	835.4	838.1	840.7	843.3	844.1	844.9	845.6	846.4
150°	851.4	850.9	852.1	854.6	857.1	859.5	862.0	862.9	863.9	864.8	865.7
152.5°	869.6	869.0	870.2	872.5	874.8	877.1	879.4	880.3	881.3	882.2	883.1
155°	887.0	886.3	887.2	889.1	891.0	892.8	894.7	895.6	896.5	897.4	898.3
157.5°	902.2	901.6	902.3	903.7	905.1	906.5	907.9	909.0	910.0	911.1	912.2
160°	916.0	915.5	916.0	916.9	917.8	918.8	919.7	920.6	921.6	922.5	923.4
162.5°	927.1	926.6	927.0	927.8	928.5	929.3	930.1	931.2	932.3	933.4	934.5
165°	936.9	936.4	936.6	937.1	937.5	938.0	938.4	939.5	940.6	941.7	942.8
167.5°	944.5	944.0	944.2	944.7	945.2	945.6	946.1	947.2	948.2	949.3	950.4
170°	950.8	950.3	950.4	950.7	951.0	951.3	951.6	952.7	953.8	954.9	956.0
172.5°	954.9	954.4	954.6	954.9	955.2	955.5	955.8	956.9	958.0	959.1	960.2
175°	957.7	957.2	957.4	957.7	958.0	958.3	958.6	959.7	960.7	961.8	962.9
177.5°	959.1	958.6	958.7	958.8	959.0	959.1	959.3	960.4	961.4	962.5	963.6
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1626.5	1630.4	1621.2	1618.6	1621.2	1612.0	1614.7	1617.3	1617.3	1621.2	1623.8
5°	1532.0	1526.8	1517.6	1515.0	1512.3	1516.3	1513.7	1517.6	1518.9	1528.1	1529.4
7.5°	1438.9	1431.0	1423.2	1415.3	1412.7	1406.1	1412.7	1412.7	1421.8	1419.2	1425.8
10°	1328.7	1327.4	1316.9	1313.0	1307.7	1297.2	1311.7	1307.7	1314.3	1326.1	1328.7
12.5°	1247.4	1233.0	1239.5	1221.2	1227.7	1217.2	1218.5	1218.5	1229.0	1230.3	1227.7
15°	1170.0	1158.2	1141.1	1133.3	1129.3	1124.1	1141.1	1142.5	1134.6	1153.0	1146.4
17.5°	1091.3	1091.3	1075.6	1071.6	1061.1	1066.4	1063.8	1065.1	1062.4	1075.6	1082.1
20°	1023.1	1016.5	1011.3	1012.6	999.5	996.9	994.2	996.9	1006.0	1015.2	1017.9
22.5°	968.0	964.1	951.0	953.6	943.1	947.0	944.4	951.0	952.3	952.3	961.4
25°	915.5	910.3	911.6	906.4	902.4	902.4	898.5	902.4	907.7	910.3	911.6
27.5°	876.2	872.3	865.7	861.8	864.4	857.8	863.1	867.0	867.0	864.4	867.0
30°	829.0	831.6	831.6	818.5	823.7	821.1	825.0	827.7	827.7	829.0	826.3
32.5°	797.5	789.6	788.3	787.0	787.0	781.8	781.8	785.7	787.0	788.3	792.2
35°	755.5	755.5	749.0	752.9	747.6	749.0	747.6	749.0	751.6	747.6	751.6
37.5°	717.5	718.8	716.2	718.8	720.1	717.5	714.9	720.1	717.5	717.5	714.9
40°	684.7	683.4	684.7	684.7	684.7	686.0	683.4	683.4	683.4	680.8	678.1
42.5°	657.1	649.3	651.9	653.2	649.3	649.3	650.6	649.3	653.2	645.3	645.3
45°	617.8	615.2	616.5	616.5	619.1	615.2	617.8	619.1	615.2	613.9	611.2
47.5°	582.4	585.0	582.4	585.0	585.0	587.6	582.4	583.7	585.0	579.8	575.8
50°	547.0	547.0	550.9	549.6	550.9	548.3	548.3	547.0	548.3	545.7	541.7
52.5°	514.2	510.2	516.8	515.5	514.2	512.9	511.5	512.9	510.2	507.6	507.6
55°	473.5	473.5	477.4	478.8	478.8	476.1	473.5	474.8	473.5	472.2	470.9
57.5°	440.7	435.5	438.1	439.4	439.4	435.5	438.1	435.5	435.5	436.8	432.8
60°	398.7	398.7	396.1	400.1	400.1	397.4	397.4	398.7	396.1	394.8	393.5
62.5°	354.1	355.5	359.4	360.7	362.0	359.4	356.8	358.1	358.1	354.1	355.5
65°	316.1	318.7	324.0	322.7	320.0	321.4	318.7	320.0	316.1	317.4	313.5
67.5°	279.4	278.1	279.4	279.4	282.0	280.7	278.1	278.1	276.8	280.7	276.8
70°	240.0	240.0	240.0	240.0	241.3	242.7	240.0	237.4	238.7	236.1	234.8
72.5°	199.4	200.7	199.4	202.0	198.1	200.7	200.7	199.4	198.1	198.1	198.1
75°	161.3	164.0	160.0	161.3	160.0	162.6	161.3	161.3	158.7	157.4	158.7
77.5°	123.3	124.6	122.0	123.3	122.0	123.3	123.3	122.0	122.0	122.0	122.0
80°	87.9	89.2	87.9	86.6	85.3	87.9	85.3	86.6	87.9	86.6	89.2
82.5°	56.4	56.4	55.1	56.4	53.8	53.8	55.1	55.1	53.8	56.4	53.8
85°	27.5	27.5	30.2	27.5	26.2	26.2	26.2	27.5	26.2	28.9	27.5
87.5°	6.6	5.2	6.6	6.6	5.2	5.2	6.6	5.2	6.6	7.9	5.2
90°	17.4	17.6	17.9	18.2	18.5	18.8	18.5	18.2	17.9	17.6	17.4
92.5°	18.1	18.2	18.3	18.5	18.6	18.8	18.6	18.5	18.3	18.2	18.1
95°	30.6	30.5	30.4	30.2	30.1	29.9	30.1	30.2	30.4	30.5	30.6
97.5°	37.5	37.6	37.7	37.9	38.0	38.2	38.0	37.9	37.7	37.6	37.5
100°	45.2	45.3	45.6	45.9	46.2	46.5	46.2	45.9	45.6	45.3	45.2
102.5°	48.6	48.8	49.3	49.8	50.2	50.7	50.2	49.8	49.3	48.8	48.6
105°	50.0	50.3	50.9	51.6	52.2	52.8	52.2	51.6	50.9	50.3	50.0
107.5°	51.4	51.7	52.3	53.0	53.6	54.2	53.6	53.0	52.3	51.7	51.4
110°	52.1	52.4	53.0	53.7	54.3	54.9	54.3	53.7	53.0	52.4	52.1

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.5	53.7	54.2	54.7	55.1	55.6	55.1	54.7	54.2	53.7	53.5
115°	107.0	101.4	90.3	79.2	68.1	57.0	68.1	79.2	90.3	101.4	107.0
117.5°	366.8	346.6	306.1	265.7	225.2	184.8	225.2	265.7	306.1	346.6	366.8
120°	517.5	507.1	486.2	465.4	444.5	423.7	444.5	465.4	486.2	507.1	517.5
122.5°	554.3	554.4	554.5	554.7	554.8	555.0	554.8	554.7	554.5	554.4	554.3
125°	591.8	592.0	592.5	593.0	593.4	593.9	593.4	593.0	592.5	592.0	591.8
127.5°	627.9	628.0	628.1	628.3	628.4	628.6	628.4	628.3	628.1	628.0	627.9
130°	661.3	661.2	661.1	660.9	660.8	660.6	660.8	660.9	661.1	661.2	661.3
132.5°	692.5	692.4	692.3	692.1	692.0	691.8	692.0	692.1	692.3	692.4	692.5
135°	723.1	722.9	722.6	722.3	722.0	721.7	722.0	722.3	722.6	722.9	723.1
137.5°	751.6	751.4	750.9	750.4	750.0	749.5	750.0	750.4	750.9	751.4	751.6
140°	778.7	778.3	777.5	776.8	776.0	775.2	776.0	776.8	777.5	778.3	778.7
142.5°	803.7	803.3	802.5	801.8	801.0	800.2	801.0	801.8	802.5	803.3	803.7
145°	826.6	826.2	825.4	824.7	823.9	823.1	823.9	824.7	825.4	826.2	826.6
147.5°	846.8	846.5	845.9	845.2	844.6	844.0	844.6	845.2	845.9	846.5	846.8
150°	866.2	865.8	865.0	864.3	863.5	862.7	863.5	864.3	865.0	865.8	866.2
152.5°	883.6	883.1	882.0	880.9	879.8	878.7	879.8	880.9	882.0	883.1	883.6
155°	898.8	898.2	897.0	895.7	894.5	893.3	894.5	895.7	897.0	898.2	898.8
157.5°	912.7	912.1	910.9	909.6	908.4	907.2	908.4	909.6	910.9	912.1	912.7
160°	923.9	923.4	922.3	921.2	920.1	919.0	920.1	921.2	922.3	923.4	923.9
162.5°	935.0	934.3	932.9	931.5	930.1	928.7	930.1	931.5	932.9	934.3	935.0
165°	943.3	942.8	941.7	940.6	939.5	938.4	939.5	940.6	941.7	942.8	943.3
167.5°	950.9	950.2	948.8	947.5	946.1	944.7	946.1	947.5	948.8	950.2	950.9
170°	956.5	955.8	954.4	953.1	951.7	950.3	951.7	953.1	954.4	955.8	956.5
172.5°	960.7	960.0	958.6	957.2	955.8	954.4	955.8	957.2	958.6	960.0	960.7
175°	963.4	962.6	961.1	959.6	958.0	956.5	958.0	959.6	961.1	962.6	963.4
177.5°	964.1	963.4	962.0	960.7	959.3	957.9	959.3	960.7	962.0	963.4	964.1
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5	1706.5
2.5°	1619.9	1630.4	1626.5	1612.0	1629.1	1629.1	1640.9	1640.9	1655.3	1660.6	1668.4
5°	1528.1	1536.0	1542.5	1536.0	1547.8	1566.1	1576.6	1585.8	1605.5	1613.3	1625.2
7.5°	1429.7	1444.1	1450.7	1450.7	1470.4	1491.4	1512.3	1525.5	1553.0	1563.5	1575.3
10°	1334.0	1351.0	1364.1	1362.8	1395.6	1408.7	1435.0	1465.1	1492.7	1508.4	1525.5
12.5°	1233.0	1242.1	1260.5	1286.7	1294.6	1318.2	1348.4	1386.4	1436.3	1450.7	1475.6
15°	1149.0	1173.9	1188.4	1200.2	1218.5	1240.8	1273.6	1310.4	1360.2	1391.7	1417.9
17.5°	1078.2	1111.0	1120.2	1117.5	1141.1	1175.2	1213.3	1240.8	1285.4	1323.5	1348.4
20°	1020.5	1033.6	1049.3	1055.9	1074.3	1111.0	1147.7	1179.2	1215.9	1246.1	1274.9
22.5°	962.8	973.3	986.4	998.2	1012.6	1033.6	1069.0	1108.4	1143.8	1172.6	1205.4
25°	915.5	922.1	933.9	943.1	958.8	973.3	998.2	1041.5	1083.4	1100.5	1129.3
27.5°	869.6	874.9	882.7	893.2	901.1	915.5	937.8	973.3	1016.5	1033.6	1072.9
30°	829.0	832.9	840.8	846.0	850.0	867.0	884.1	911.6	944.4	968.0	996.9
32.5°	790.9	794.9	802.7	804.0	809.3	818.5	834.2	859.1	888.0	907.7	932.6
35°	749.0	751.6	759.5	762.1	766.0	773.9	785.7	804.0	830.3	844.7	867.0
37.5°	716.2	714.9	720.1	724.0	729.3	733.2	737.2	755.5	775.2	788.3	805.4
40°	680.8	678.1	679.4	684.7	687.3	692.6	692.6	710.9	724.0	734.5	747.6
42.5°	645.3	644.0	641.4	644.0	646.6	648.0	649.3	662.4	675.5	684.7	699.1
45°	609.9	608.6	606.0	607.3	607.3	609.9	613.9	619.1	628.3	636.2	644.0
47.5°	577.1	574.5	570.6	569.3	571.9	571.9	571.9	577.1	586.3	588.9	596.8
50°	543.0	539.1	533.8	531.2	531.2	529.9	532.5	533.8	541.7	544.3	550.9
52.5°	506.3	503.7	498.4	493.2	494.5	491.9	493.2	494.5	497.1	501.1	505.0
55°	469.6	464.3	460.4	459.1	455.1	455.1	451.2	456.5	455.1	456.5	461.7
57.5°	434.2	428.9	422.4	419.7	415.8	414.5	411.9	410.6	411.9	415.8	419.7
60°	392.2	389.6	385.6	381.7	379.1	375.1	372.5	372.5	371.2	371.2	372.5
62.5°	351.5	350.2	345.0	343.7	341.0	338.4	334.5	331.9	331.9	334.5	335.8
65°	312.2	310.9	306.9	305.6	299.1	296.4	295.1	293.8	291.2	291.2	291.2
67.5°	275.4	271.5	271.5	265.0	259.7	257.1	254.5	253.2	253.2	253.2	254.5
70°	234.8	234.8	230.9	226.9	221.7	223.0	219.0	215.1	215.1	212.5	213.8
72.5°	195.4	194.1	190.2	188.9	184.9	181.0	178.4	181.0	177.1	175.8	177.1
75°	157.4	156.1	153.5	150.8	152.2	148.2	144.3	143.0	143.0	140.3	140.3
77.5°	120.7	123.3	118.0	116.7	114.1	111.5	110.2	108.9	108.9	108.9	111.5
80°	83.9	85.3	85.3	82.6	83.9	80.0	80.0	80.0	76.1	77.4	78.7
82.5°	53.8	53.8	52.5	53.8	52.5	52.5	51.2	51.2	49.8	49.8	51.2
85°	30.2	28.9	27.5	30.2	28.9	28.9	27.5	27.5	27.5	27.5	27.5
87.5°	6.6	7.9	7.9	7.9	7.9	9.2	9.2	9.2	10.5	10.5	10.5
90°	17.0	16.2	15.5	14.7	13.9	12.7	11.4	10.2	8.9	8.3	7.5
92.5°	17.9	17.6	17.3	17.0	16.7	16.2	15.8	15.3	14.8	14.6	14.9
95°	30.2	29.4	28.7	27.9	27.1	26.0	24.9	23.8	22.7	22.2	24.8
97.5°	37.3	36.8	36.3	35.9	35.4	32.9	30.5	28.0	25.5	24.3	30.6
100°	44.6	43.3	42.1	40.8	39.6	37.0	34.4	31.7	29.1	27.8	38.4
102.5°	47.8	46.1	44.4	42.7	41.0	69.1	97.2	125.3	153.4	167.4	167.6
105°	49.2	47.5	45.8	44.1	42.4	84.5	126.7	168.8	210.9	232.0	229.7
107.5°	50.6	48.9	47.2	45.5	43.8	95.8	147.8	199.9	251.9	277.9	276.0
110°	59.8	75.3	90.7	106.2	121.6	166.2	210.8	255.4	300.0	322.3	320.7

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	86.8	153.3	219.8	286.4	352.9	355.5	358.1	360.8	363.4	364.7	363.3
115°	142.7	214.2	285.7	357.1	428.6	424.7	420.9	417.0	413.1	411.2	409.9
117.5°	377.8	399.9	422.0	444.0	466.1	463.5	460.9	458.2	455.6	454.3	452.8
120°	516.6	514.7	512.9	511.0	509.2	506.4	503.6	500.9	498.1	496.7	495.5
122.5°	553.8	552.9	552.0	551.0	550.1	547.0	544.0	540.9	537.8	536.3	535.1
125°	591.3	590.2	589.1	588.1	587.0	584.1	581.1	578.2	575.3	573.8	572.8
127.5°	627.1	625.6	624.1	622.5	621.0	618.7	616.4	614.1	611.8	610.6	609.5
130°	660.4	658.7	657.0	655.3	653.6	651.9	650.2	648.5	646.8	646.0	644.8
132.5°	691.8	690.4	689.1	687.7	686.3	684.6	682.9	681.2	679.5	678.7	677.7
135°	722.3	720.8	719.3	717.7	716.2	714.8	713.4	712.0	710.6	709.9	708.7
137.5°	750.8	749.3	747.7	746.2	744.6	743.1	741.5	740.0	738.5	737.7	736.8
140°	778.0	776.6	775.2	773.8	772.4	770.7	769.0	767.3	765.6	764.8	764.2
142.5°	803.1	801.8	800.6	799.3	798.1	796.1	794.1	792.1	790.1	789.1	788.6
145°	826.1	825.0	823.9	822.8	821.7	819.1	816.5	813.8	811.2	809.9	810.0
147.5°	846.4	845.6	844.9	844.1	843.3	840.7	838.1	835.4	832.8	831.5	831.7
150°	865.7	864.8	863.9	862.9	862.0	859.5	857.1	854.6	852.1	850.9	851.4
152.5°	883.1	882.2	881.3	880.3	879.4	877.1	874.8	872.5	870.2	869.0	869.6
155°	898.3	897.4	896.5	895.6	894.7	892.8	891.0	889.1	887.2	886.3	887.0
157.5°	912.2	911.1	910.0	909.0	907.9	906.5	905.1	903.7	902.3	901.6	902.2
160°	923.4	922.5	921.6	920.6	919.7	918.8	917.8	916.9	916.0	915.5	916.0
162.5°	934.5	933.4	932.3	931.2	930.1	929.3	928.5	927.8	927.0	926.6	927.1
165°	942.8	941.7	940.6	939.5	938.4	938.0	937.5	937.1	936.6	936.4	936.9
167.5°	950.4	949.3	948.2	947.2	946.1	945.6	945.2	944.7	944.2	944.0	944.5
170°	956.0	954.9	953.8	952.7	951.6	951.3	951.0	950.7	950.4	950.3	950.8
172.5°	960.2	959.1	958.0	956.9	955.8	955.5	955.2	954.9	954.6	954.4	954.9
175°	962.9	961.8	960.7	959.7	958.6	958.3	958.0	957.7	957.4	957.2	957.7
177.5°	963.6	962.5	961.4	960.4	959.3	959.1	959.0	958.8	958.7	958.6	959.1
180°	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0	960.0

TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1706.5	1706.5	1706.5	1706.5
2.5°	1675.0	1675.0	1694.7	1715.7
5°	1638.3	1647.4	1678.9	1707.8
7.5°	1602.9	1618.6	1657.9	1694.7
10°	1559.6	1580.6	1629.1	1672.4
12.5°	1517.6	1537.3	1593.7	1642.2
15°	1458.6	1483.5	1543.8	1604.2
17.5°	1399.5	1424.5	1497.9	1568.7
20°	1330.0	1362.8	1445.5	1539.9
22.5°	1265.8	1306.4	1398.2	1474.3
25°	1194.9	1257.9	1343.1	1441.5
27.5°	1132.0	1194.9	1281.5	1381.2
30°	1061.1	1125.4	1214.6	1306.4
32.5°	992.9	1052.0	1138.5	1251.3
35°	922.1	978.5	1062.4	1176.6
37.5°	857.8	912.9	1004.7	1109.7
40°	794.9	852.6	931.3	1036.2
42.5°	735.8	787.0	857.8	962.8
45°	682.1	718.8	784.4	882.7
47.5°	625.7	658.5	718.8	817.2
50°	573.2	600.7	653.2	745.0
52.5°	522.0	545.7	594.2	667.6
55°	476.1	498.4	533.8	606.0
57.5°	428.9	446.0	480.1	537.8
60°	383.0	398.7	426.3	473.5
62.5°	337.1	350.2	376.4	414.5
65°	296.4	306.9	326.6	359.4
67.5°	257.1	263.6	279.4	305.6
70°	219.0	224.3	237.4	258.4
72.5°	178.4	183.6	198.1	212.5
75°	144.3	145.6	156.1	167.9
77.5°	112.8	111.5	119.4	128.5
80°	77.4	81.3	87.9	91.8
82.5°	52.5	53.8	56.4	59.0
85°	28.9	30.2	30.2	34.1
87.5°	11.8	13.1	13.1	14.4
90°	5.8	4.1	2.4	0.7
92.5°	15.5	16.2	16.8	17.4
95°	29.9	35.0	40.1	45.2
97.5°	43.3	56.0	68.6	81.3
100°	59.5	80.6	101.8	122.9
102.5°	167.9	168.2	168.5	168.8
105°	225.1	220.4	215.8	211.2
107.5°	272.1	268.2	264.4	260.5
110°	317.4	314.2	310.9	307.7



TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	360.5	357.8	355.0	352.2
115°	407.3	404.6	402.0	399.4
117.5°	449.7	446.6	443.5	440.4
120°	493.2	490.9	488.5	486.2
122.5°	532.6	530.1	527.6	525.1
125°	570.8	568.7	566.7	564.7
127.5°	607.4	605.2	603.1	600.9
130°	642.3	639.8	637.4	634.9
132.5°	675.7	673.6	671.6	669.6
135°	706.2	703.7	701.3	698.8
137.5°	734.9	733.1	731.2	729.4
140°	762.9	761.7	760.4	759.2
142.5°	787.5	786.4	785.3	784.2
145°	810.1	810.3	810.4	810.6
147.5°	832.2	832.7	833.1	833.6
150°	852.5	853.6	854.7	855.8
152.5°	870.8	872.1	873.3	874.5
155°	888.4	889.8	891.2	892.6
157.5°	903.5	904.7	906.0	907.2
160°	916.9	917.8	918.8	919.7
162.5°	928.0	928.9	929.9	930.8
165°	937.8	938.7	939.6	940.5
167.5°	945.4	946.3	947.3	948.2
170°	951.7	952.6	953.5	954.4
172.5°	955.8	956.7	957.7	958.6
175°	958.8	959.9	961.0	962.1
177.5°	960.2	961.3	962.3	963.4
180°	960.0	960.0	960.0	960.0



TEST NUMBER: P999161

CATALOG NUMBER: SA2XXDIP-B865D725UB2750-4F0-XX-W2A-A_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.95	18.84	18.85	19.75	20.92	15.44	16.33	16.34	17.25	18.41
	3H	18.76	19.56	19.67	20.48	21.67	16.79	17.58	17.70	18.51	19.70
	4H	18.93	19.68	19.86	20.61	21.81	17.25	18.00	18.18	18.93	20.13
	6H	18.98	19.67	19.92	20.61	21.82	17.56	18.25	18.50	19.19	20.40
	8H	18.96	19.62	19.90	20.57	21.78	17.64	18.30	18.59	19.26	20.47
	12H	18.92	19.55	19.87	20.49	21.73	17.69	18.31	18.64	19.26	20.50
4H	2H	17.99	18.74	18.92	19.67	20.88	15.89	16.64	16.82	17.57	18.77
	3H	18.98	19.60	19.92	20.56	21.78	17.35	17.98	18.30	18.94	20.15
	4H	19.25	19.82	20.21	20.78	22.02	17.89	18.46	18.84	19.41	20.65
	6H	19.39	19.88	20.35	20.85	22.09	18.27	18.76	19.24	19.74	20.98
	8H	19.38	19.84	20.35	20.81	22.07	18.38	18.84	19.35	19.81	21.07
	12H	19.35	19.76	20.34	20.75	22.01	18.44	18.85	19.42	19.84	21.10
8H	4H	19.26	19.72	20.23	20.69	21.95	18.03	18.49	19.00	19.46	20.72
	6H	19.44	19.82	20.44	20.84	22.09	18.47	18.85	19.46	19.86	21.11
	8H	19.47	19.81	20.48	20.81	22.08	18.62	18.95	19.62	19.96	21.23
	12H	19.46	19.75	20.46	20.75	22.07	18.71	19.01	19.72	20.00	21.32
12H	4H	19.22	19.64	20.21	20.62	21.88	18.01	18.42	18.99	19.41	20.67
	6H	19.42	19.76	20.42	20.76	22.03	18.47	18.80	19.47	19.81	21.08
	8H	19.46	19.75	20.46	20.75	22.06	18.63	18.92	19.63	19.92	21.23